



Dimmable glass LED candles and lustres that meet the high standard for light experience

MASTER GLASS LED candles and lustres

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of incandescent candles and lustres with the benefits of the long-lasting LED technology. It is an idea product to provide customers with cosy atmosphere. The MASTER LED candles and lustres can be dimmed for different lumen level and also for the different colour temperature. MASTER Glass Led Bulbs deliver significant energy savings, offering even 30% more compared to normal LED. They provide excellent quality of light. By offering a lifetime of 25,000 hours, the lamps reduce maintenance costs.

Benefits

- energy saving, 30% less energy compared with standard Philips LED candle and luster
- Very long lifetime that reduces the need for replacement
- Easy replacement of conventional lamps

Features

- heritage design with classic shapes
- perfect fit and high quality finishing
- Very good light quality with super high color rendering (CRI>95)
- Designed to be seen, they look good on and off
- Environmentally friendly: contains no mercury or other hazardous substances

MASTER GLASS LED candles and lusters

Application

- Domestic application
- Hospitality: restaurants and hotels

Versions



LEDclassic 25W B35 E14 CL
WGD90 SRT4 1



LEDclassic 40W BA35 E14 CL
WGD90 SRT4 1



LEDclassic 40W P45 E27 CL
WGD90 SRT4 1



LEDclassic 25W P45 E27 CL
WGD90 SRT4 1







LEDclassic 25W BA35 E14 CL
WGD90 SRT4 1



LEDclassic 40W P45 E14 WGD90
CL SRT4 1

MASTER GLASS LED candles and lusters

Dimensional drawing



Product	D	C
MAS LEDCandleDT2.5-25W E14 B35 CL G	35 mm	97 mm
MAS LEDCandleDT3.4-40W E14 927 B35CL G	35 mm	97 mm
MAS LEDCandleDT5.9-60W E14 927 B35 CL G	35 mm	97 mm

Product	D	C
MAS LEDLusterDT3.4-40W E14 927 P45CL G	45 mm	80 mm

Product	D	C
MAS LEDLusterDT2.5-25W E27 927 P45CL G	45 mm	78 mm
MAS LEDLusterDT3.5-40W E27 927 P45CL G	45 mm	78 mm

Product	D	C
MAS LEDCandleDT2.5-25W E14 BA35 CL G	35 mm	119 mm
MAS LEDCandleDT3.4-40W E14927 BA35CL G	35 mm	119 mm

MASTER GLASS LED candles and lusters

General Information	
Switching Cycle	20,000
Nominal lifetime	25,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2200 K
Color rendering index (CRI)	90
Color Code	922-927
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Ambient temperature range	-20 °C to 45 °C

General Information

Order Code	Full Product Name	Cap-Base
44941100	MAS LEDCandleDT3.4-40W E14 927 B35CL G	E14
44957200	MAS LEDCandleDT5.9-60W E14 927 B35 CL G	E14
44935000	MAS LEDCandleDT2.5-25W E14 B35 CL G	E14
44949700	MAS LEDCandleDT3.4-40W E14927 BA35CL G	E14
44953400	MAS LEDLusterDT3.5-40W E27 927 P45CL G	E27
44939800	MAS LEDLusterDT2.5-25W E27 927 P45CL G	E27
47771100	MAS LEDCandleDT2.5-25W E14 BA35 CL G	E14
44951000	MAS LEDLusterDT3.4-40W E14 927 P45CL G	E14

Light Technical

Order Code	Full Product Name	Luminous Flux
44941100	MAS LEDCandleDT3.4-40W E14 927 B35CL G	470 lm
44957200	MAS LEDCandleDT5.9-60W E14 927 B35 CL G	806 lm
44935000	MAS LEDCandleDT2.5-25W E14 B35 CL G	340 lm
44949700	MAS LEDCandleDT3.4-40W E14927 BA35CL G	470 lm

Order Code	Full Product Name	Luminous Flux
44953400	MAS LEDLusterDT3.5-40W E27 927 P45CL G	470 lm
44939800	MAS LEDLusterDT2.5-25W E27 927 P45CL G	340 lm
47771100	MAS LEDCandleDT2.5-25W E14 BA35 CL G	340 lm
44951000	MAS LEDLusterDT3.4-40W E14 927 P45CL G	470 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
44941100	MAS LEDCandleDT3.4-40W E14 927 B35CL G	3.4 W	40 W
44957200	MAS LEDCandleDT5.9-60W E14 927 B35 CL G	5.9 W	60 W
44935000	MAS LEDCandleDT2.5-25W E14 B35 CL G	2.5 W	25 W
44949700	MAS LEDCandleDT3.4-40W E14927 BA35CL G	3.4 W	40 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
44953400	MAS LEDLusterDT3.5-40W E27 927 P45CL G	3.4 W	40 W
44939800	MAS LEDLusterDT2.5-25W E27 927 P45CL G	2.5 W	25 W
47771100	MAS LEDCandleDT2.5-25W E14 BA35 CL G	2.5 W	25 W
44951000	MAS LEDLusterDT3.4-40W E14 927 P45CL G	3.4 W	40 W

Mechanical and Housing



MASTER GLASS LED candles and lusters

Order Code	Full Product Name	Bulb Shape
44941100	MAS LEDCandleDT3.4-40W E14 927 B35CL G	B35
44957200	MAS LEDCandleDT5.9-60W E14 927 B35 CL G	B35
44935000	MAS LEDCandleDT2.5-25W E14 B35 CL G	B35
44949700	MAS LEDCandleDT3.4-40W E14927 BA35CL G	BA35

Order Code	Full Product Name	Bulb Shape
44953400	MAS LEDLusterDT3.5-40W E27 927 P45CL G	P45
44939800	MAS LEDLusterDT2.5-25W E27 927 P45CL G	P45
47771100	MAS LEDCandleDT2.5-25W E14 BA35 CL G	BA35
44951000	MAS LEDLusterDT3.4-40W E14 927 P45CL G	P45

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
44941100	MAS LEDCandleDT3.4-40W E14 927 B35CL G	4 kWh
44957200	MAS LEDCandleDT5.9-60W E14 927 B35 CL G	6 kWh
44935000	MAS LEDCandleDT2.5-25W E14 B35 CL G	3 kWh
44949700	MAS LEDCandleDT3.4-40W E14927 BA35CL G	4 kWh
44953400	MAS LEDLusterDT3.5-40W E27 927 P45CL G	4 kWh
44939800	MAS LEDLusterDT2.5-25W E27 927 P45CL G	3 kWh
47771100	MAS LEDCandleDT2.5-25W E14 BA35 CL G	3 kWh
44951000	MAS LEDLusterDT3.4-40W E14 927 P45CL G	4 kWh



MASTER GLASS LED candles and lusters

