



# Dimmable glass LED candles and lusters that meet the high standard for light experience

## MASTER GLASS LED candles and lusters

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of incandescent candles and lustres with the benefits of the long-lasting LED technology. It is an idea product to provide customers with cosy atmosphere. The MASTER LED candles and lustres can be dimmed for different lumen level and also for the different colour temperature. MASTER Glass Led Bulbs deliver significant energy savings, offering even 30% more compared to normal LED. They provide excellent quality of light. By offering a lifetime of 25,000 hours, the lamps reduce maintenance costs.

### Benefits

- energy saving, 30% less energy compared with standard Philips LED candle and luster
- Very long lifetime that reduces the need for replacement
- Easy replacement of conventional lamps

### Features

- heritage design with classic shapes
- perfect fit and high quality finishing
- Very good light quality with super high color rendering (CRI>95)
- Designed to be seen, they look good on and off
- Environmentally friendly: contains no mercury or other hazardous substances

# MASTER GLASS LED candles and lusters

## Application


- Domestic application
- Hospitality: restaurants and hotels

## Versions



LEDclassic 40W B35 E14 CL  
WGD90 SRT4 1

## Dimensional drawing



Product	D	C
MAS LEDCandleDT3.4-40W E14 927 B35CL G	35 mm	97 mm



## MASTER GLASS LED candles and lusters

