



For an optimal combination of value and performance

MASTER Value GLASS LED candles and lusters

MASTER Value Glass LED lusters features a classic heritage design, these filament LED lamps combine the familiar shapes of incandescent candles and lusters with the benefits of long-lasting LED technology. These glass LED lusters offer more energy savings than normal LED candles and lusters. At the same time, they also provide customers with a good light experience, enhanced by excellent dimming performance (dimable LED candles). MASTER Value Glass LED lusters and lusters deliver significant energy savings, using 30% less energy compared to normal glass LED candles and provide excellent quality of light. By offering a lifetime of 15,000 hours these dimable LED candles and lusters also reduce maintenance costs.

Benefits

- Saves 30% energy compared with standard Philips LED candles and lusters
- Very long lifetime that reduces the need for replacements
- Easy retrofit replacement for conventional lamps

Features

- heritage design with classic shapes
- perfect fit and high-quality finish
- Very good light quality with excellent color rendering (CRI>90)
- Designed to be seen, they look good switched on or off
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Home
- Hospitality

MSTER Value GLASS LED candles and lusters

Versions



LEDlustre MAS P45 E14 CL



LEDclassic 40W B35 E14 CL
WGD90 SRT4 1



LEDclassic 25W B35 E14 CL
WGD90 SRT4 1



CLA LEDcandle 25W E14 827 FR
P45



CLA LEDcandle 25W E27 827 FR
P45



LEDclassic 40W BA35 E14 CL
WGD90 SRT4 1



LEDcandle MAS B35 E14 CL



LEDclassic 40W P45 E27 CL
WGD90 SRT4 1




MSTER Value GLASS LED candles and lusters

Versions



LEDlustre MAS P45 E27 CL

Dimensional drawing




Product	D	C
MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	35 mm	97 mm
MAS VLE LEDCandleDT2.5-25W E14 B35CL G	35 mm	97 mm
MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	35 mm	97 mm
MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	35 mm	97 mm

Product	D	C
MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	45 mm	80 mm
MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	45 mm	80 mm

Product	D	C
MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	45 mm	78 mm
MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	45 mm	78 mm
MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	45 mm	78 mm

MSTER Value GLASS LED candles and lusters

Dimensional drawing



Product	D	C
MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	35 mm	119 mm

General Information	
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

General Information

Order Code	Full Product Name	Cap-Base
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	E14
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	E14
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	E14
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	E14
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	E14

Order Code	Full Product Name	Cap-Base
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	E27
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	E14
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	E14
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	E27
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	E27

Light Technical

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	2700 K	927	470 lm
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	2200 K	922-927	470 lm
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	2200 K	922-927	470 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	2200 K	922-927	340 lm
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	2700 K	927	470 lm
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	2700 K	927	470 lm

MSTER Value GLASS LED candles and lusters

Order Code	Full Product Name	Correlated Color	Color Code	Luminous Flux
		Temperature (Nom)		
929003013002	MAS VLE LEDcandleDT3.4-40W E14927BA35CLG	2200 K	922-927	470 lm
929003059502	MAS VLE LEDcandleD3.4-40W E14 B35 927CLG	2700 K	927	470 lm

Order Code	Full Product Name	Correlated Color	Color Code	Luminous Flux
		Temperature (Nom)		
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	2200 K	922-927	470 lm
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	2700 K	927	470 lm

Operating and Electrical

Order Code	Full Product Name	Power	Wattage Equivalent
		Consumption	
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	3.4 W	40 W
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	3.4 W	40 W
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	3.4 W	40 W
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	2.5 W	25 W
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	3.4 W	40 W

Order Code	Full Product Name	Power	Wattage Equivalent
		Consumption	
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	3.4 W	40 W
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	3.4 W	40 W
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	3.4 W	40 W
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	3.5 W	40 W
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	3.4 W	40 W

Temperature

Order Code	Full Product Name	T-Case Maximum
		(Nom)
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	80 °C
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	70 °C
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	70 °C
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	70 °C
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	80 °C

Order Code	Full Product Name	T-Case Maximum
		(Nom)
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	80 °C
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	70 °C
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	80 °C
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	70 °C
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	80 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	Only with specific dimmers
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	Only with specific dimmers
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	Yes
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	Only with specific dimmers
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	Only with specific dimmers
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	Only with specific dimmers
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	Only with specific dimmers
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	Yes
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	Only with specific dimmers

Mechanical and Housing





MSTER Value GLASS LED candles and lusters

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	Clear	P45
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	Clear	B35
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	Clear	B35
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	Clear	B35
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	Frosted	P45
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	Frosted	P45

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	Clear	BA35
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	Clear	B35
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	Clear	P45
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	Clear	P45

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	4 kWh
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	4 kWh
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	4 kWh
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	3 kWh
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	4 kWh
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	4 kWh
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	4 kWh
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	4 kWh
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	4 kWh
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	4 kWh



MSTER Value GLASS LED candles and lusters

