



For an optimal combination of value and performance

MASTER Value GLASS LED candles and lusters

MASTER Value Glass LED lusters features a classic heritage design, these filament LED lamps combine the familiar shapes of incandescent candles and lusters with the benefits of long-lasting LED technology. These glass LED lusters offer more energy savings than normal LED candles and lusters. At the same time, they also provide customers with a good light experience, enhanced by excellent dimming performance (dimable LED candles). MASTER Value Glass LED lusters and lusters deliver significant energy savings, using 30% less energy compared to normal glass LED candles and provide excellent quality of light. By offering a lifetime of 15,000 hours these dimable LED candles and lusters also reduce maintenance costs.

Benefits

- Saves 30% energy compared with standard Philips LED candles and lusters
- Very long lifetime that reduces the need for replacements
- Easy retrofit replacement for conventional lamps

Features

- heritage design with classic shapes
- perfect fit and high-quality finish
- Very good light quality with excellent color rendering (CRI>90)
- Designed to be seen, they look good switched on or off
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Home
- Hospitality

MSTER Value GLASS LED candles and lusters

Versions





LEDcandle MAS B35 E14 CL



LEDlustre MAS P45 E27 CL

Dimensional drawing



Product	D	C
MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	35 mm	97 mm

Product	D	C
MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	45 mm	78 mm

MSTER Value GLASS LED candles and lusters

General Information	
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	90
Color Code	927
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	470 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Power Consumption	3.4 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	40 W
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Consumption kWh/1000 h	4 kWh

General Information

Order Code	Full Product Name	Cap-Base
35543900	MASTER VLE LEDCandleD3.4-40W E14 B35 927CLG	E14
35551400	MASTER VLE LEDLusterD3.4-40W E27 P45 927CLG	E27

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
35543900	MASTER VLE LEDCandleD3.4-40W E14 B35 927CLG	B35
35551400	MASTER VLE LEDLusterD3.4-40W E27 P45 927CLG	P45



MSTER Value GLASS LED candles and lusters

