

The cost-effective LED replacement for HID and SON Road lamps with MASTER - LED HID SON-T

CorePro - LED HID SON-T

The Philips CorePro LED HID SON-T lamps offer you an easy, short-payback LED solution to replace High Intensity Discharge (HID) lamps. This new generation of products brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while providing instant saving with a low initial investment.

Furthermore, they're designed to have the same lamp size and light distribution as other HID lamps, so you will never know the difference. All thanks to our HighPower LED filament technology. Plus, its unique IP65 design means it can be used for outdoor applications

Benefits

- Cost-saving lamps with short payback time
- Low initial investment
- Easy way to enhance lighting quality

CorePro - LED HID SON-T

Features

- High Energy efficient lamps
- Long lifetime – 25,000 hrs
- Surge protection 2KV
- Pleasant white light with CRI 70
- Omnidirectional light around lamp
- Additional Energy saving by Direct Mains connection
- IP65 product (IP rated sockets required for outdoor application)

Application

- Road and Street
- Tunnel
- Parking Garages

Warnings and Safety


- Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

Versions



LEDTForce Core road Tshape E40

Dimensional drawing



Product	D	C
TForce Core LED road 40W 730 E40 MV	46 mm	225 mm

CorePro - LED HID SON-T

