



The cost-effective LED replacement for HID and SON Road lamps with MASTER - LED HID SON-T

CorePro - LED HID SON-T

The Philips CorePro LED HID SON-T lamps offer you an easy, short-payback LED solution to replace High Intensity Discharge (HID) lamps. This new generation of products brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while providing instant saving with a low initial investment. Furthermore, they're designed to have the same lamp size and light distribution as other HID lamps, so you will never know the difference. All thanks to our HighPower LED filament technology. Plus, its unique IP65 design means it can be used for outdoor applications

Benefits

- Cost-saving lamps with short payback time
- Low initial investment
- Easy way to enhance lighting quality

CorePro - LED HID SON-T

Features

- High Energy efficient lamps
- Long lifetime – 25,000 hrs
- Surge protection 2KV
- Pleasant white light with CRI 70
- Omnidirectional light around lamp
- Additional Energy saving by Direct Mains connection
- IP65 product (IP rated sockets required for outdoor application)



Application

- Road and Street
- Tunnel
- Parking Garages

Warnings and Safety

- Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

Dimensional drawing





Product	D	C
TForce Core LED road 45W 727 E40 MV	53.5 mm	232 mm
TForce Core LED road 45W 730 E40 MV	53.5 mm	232 mm
TForce Core LED road 49W 740 E40 MV	53.5 mm	232 mm

Product	D	C
TForce Core LED road 40W 727 E40 MV	47 mm	229 mm
TForce Core LED road 40W 730 E40 MV	46 mm	225 mm
TForce Core LED road 40W 740 E40 MV	46 mm	225 mm

CorePro - LED HID SON-T

Dimensional drawing



Product	D	C
TForce Core LED road 26W 727 E27 MV	38.5 mm	214 mm
TForce Core LED road 26W 730 E27 MV	38.5 mm	213 mm
TForce Core LED road 26W 740 E27 MV	38.5 mm	213 mm

Product	D	C
TForce Core LED road 17W 727 E27 MV	38.5 mm	168 mm
TForce Core LED road 17W 730 E27 MV	38.5 mm	168 mm
TForce Core LED road 17W 740 E27 MV	38.5 mm	168 mm

General Information	
Nominal lifetime	25,000 hour(s)
Light Technical	
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Ambient temperature range	-30 to +45 °C

General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle
31625600	TForce Core LED road 17W 730 E27 MV	E27	15,000
31627000	TForce Core LED road 17W 740 E27 MV	E27	15,000
26771800	TForce Core LED road 17W 727 E27 MV	E27	50,000
31629400	TForce Core LED road 26W 730 E27 MV	E27	15,000
31631700	TForce Core LED road 26W 740 E27 MV	E27	15,000
26773200	TForce Core LED road 26W 727 E27 MV	E27	50,000
31633100	TForce Core LED road 40W 730 E40 MV	E40	50,000
31635500	TForce Core LED road 40W 740 E40 MV	E40	50,000
26775600	TForce Core LED road 40W 727 E40 MV	E40	50,000
29743200	TForce Core LED road 45W 727 E40 MV	E40	50,000
29745600	TForce Core LED road 49W 740 E40 MV	E40	50,000
29747000	TForce Core LED road 45W 730 E40 MV	E40	50,000

Light Technical

CorePro - LED HID SON-T

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		
			Temperature (Nom)	Color Code	Luminous Flux
31625600	TForce Core LED road 17W 730 E27 MV	-	3000 K	730	2,800 lm
31627000	TForce Core LED road 17W 740 E27 MV	-	4000 K	740	3,000 lm
26771800	TForce Core LED road 17W 727 E27 MV	330 degree(s)	2700 K	727	2,700 lm
31629400	TForce Core LED road 26W 730 E27 MV	-	3000 K	730	4,200 lm
31631700	TForce Core LED road 26W 740 E27 MV	-	4000 K	740	4,500 lm
26773200	TForce Core LED road 26W 727 E27 MV	330 degree(s)	2700 K	727	4,000 lm

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption
31625600	TForce Core LED road 17W 730 E27 MV	50 to 60 Hz	17 W
31627000	TForce Core LED road 17W 740 E27 MV	50 to 60 Hz	17 W
26771800	TForce Core LED road 17W 727 E27 MV	-	17 W
31629400	TForce Core LED road 26W 730 E27 MV	50 to 60 Hz	26 W
31631700	TForce Core LED road 26W 740 E27 MV	50 to 60 Hz	26 W
26773200	TForce Core LED road 26W 727 E27 MV	-	26 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
31625600	TForce Core LED road 17W 730 E27 MV	39.8 °C
31627000	TForce Core LED road 17W 740 E27 MV	39.8 °C
26771800	TForce Core LED road 17W 727 E27 MV	39.8 °C
31629400	TForce Core LED road 26W 730 E27 MV	44.55 °C
31631700	TForce Core LED road 26W 740 E27 MV	44.55 °C
26773200	TForce Core LED road 26W 727 E27 MV	44.55 °C

Mechanical and Housing

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		
			Temperature (Nom)	Color Code	Luminous Flux
31633100	TForce Core LED road 40W 730 E40 MV	330 degree(s)	3000 K	730	7,200 lm
31635500	TForce Core LED road 40W 740 E40 MV	330 degree(s)	4000 K	740	7,500 lm
26775600	TForce Core LED road 40W 727 E40 MV	330 degree(s)	2700 K	727	6,500 lm
29743200	TForce Core LED road 45W 727 E40 MV	300 degree(s)	2700 K	727	8,800 lm
29745600	TForce Core LED road 49W 740 E40 MV	300 degree(s)	4000 K	740	10,000 lm
29747000	TForce Core LED road 45W 730 E40 MV	300 degree(s)	3000 K	730	8,800 lm

Order Code	Full Product Name	Line Frequency	Power Consumption
31633100	TForce Core LED road 40W 730 E40 MV	50 to 60 Hz	40 W
31635500	TForce Core LED road 40W 740 E40 MV	50 to 60 Hz	40 W
26775600	TForce Core LED road 40W 727 E40 MV	-	40 W
29743200	TForce Core LED road 45W 727 E40 MV	-	45 W
29745600	TForce Core LED road 49W 740 E40 MV	-	49 W
29747000	TForce Core LED road 45W 730 E40 MV	-	45 W



Order Code	Full Product Name	T-Case Maximum (Nom)
31633100	TForce Core LED road 40W 730 E40 MV	49 °C
31635500	TForce Core LED road 40W 740 E40 MV	49 °C
26775600	TForce Core LED road 40W 727 E40 MV	48.7 °C
29743200	TForce Core LED road 45W 727 E40 MV	41 °C
29745600	TForce Core LED road 49W 740 E40 MV	45 °C
29747000	TForce Core LED road 45W 730 E40 MV	41 °C

Order Code	Full Product Name	Bulb Shape
31625600	TForce Core LED road 17W 730 E27 MV	T-shape
31627000	TForce Core LED road 17W 740 E27 MV	T-shape
26771800	TForce Core LED road 17W 727 E27 MV	T38
31629400	TForce Core LED road 26W 730 E27 MV	T-shape
31631700	TForce Core LED road 26W 740 E27 MV	T-shape
26773200	TForce Core LED road 26W 727 E27 MV	T38

Order Code	Full Product Name	Bulb Shape
31633100	TForce Core LED road 40W 730 E40 MV	T-shape
31635500	TForce Core LED road 40W 740 E40 MV	T-shape
26775600	TForce Core LED road 40W 727 E40 MV	T46
29743200	TForce Core LED road 45W 727 E40 MV	T52
29745600	TForce Core LED road 49W 740 E40 MV	T52
29747000	TForce Core LED road 45W 730 E40 MV	T52

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
31625600	TForce Core LED road 17W 730 E27 MV	17 kWh
31627000	TForce Core LED road 17W 740 E27 MV	17 kWh
26771800	TForce Core LED road 17W 727 E27 MV	17 kWh
31629400	TForce Core LED road 26W 730 E27 MV	26 kWh
31631700	TForce Core LED road 26W 740 E27 MV	26 kWh
26773200	TForce Core LED road 26W 727 E27 MV	26 kWh
31633100	TForce Core LED road 40W 730 E40 MV	40 kWh
31635500	TForce Core LED road 40W 740 E40 MV	40 kWh
26775600	TForce Core LED road 40W 727 E40 MV	40 kWh
29743200	TForce Core LED road 45W 727 E40 MV	45 kWh
29745600	TForce Core LED road 49W 740 E40 MV	49 kWh
29747000	TForce Core LED road 45W 730 E40 MV	45 kWh



CorePro - LED HID SON-T

