



The right combination of sleek design, performance and value for retail and hospitality

Essential Smartbright Projector (Wide Voltage) Gen 2

Essential SmartBright Projector ST033T is a value for money product designed for Mass market trade. It is designed to replace halogen and CDM-standard-based projectors for retail and hospitality applications. This track based luminaire supports retailers to let their products stand out, or highlight certain objects. The clean and contemporary design with integrated driver makes the Essential SmartBright Projector relevant to many applications. The choice of 2 colors in White and Black helps the Retailer to choose products best suited to blend into the Store Environment. Compared to it's predecessor, it is not only cost effective, but also a more sleek and lighter product design.

Benefits

- Reduced operating costs thanks to energy savings and longer lifetime, compared to conventional CDM-standard-based projectors
- Value for Money product for Mass market retail applications
- Clean, simple finish ensures Essential SmartBright Projector blends into many interior designs.

Essential Smartbright Projector (Wide Voltage) Gen 2


Features

- Unobtrusive design in white or black finish
- Lumen output ranging from 600-2800 Lm.
- Energy-efficient: 80 lm/W
- Integrated driver and uniform track adaptor
- Color temperature 3000 or 4000 K
- CRI90

Application

- Fashion
- Retail
- Hospitality

Versions





ST033T 7W White

ST033T 30W White

ST033T 10W Black

ST033T 7W Black

Dimensional drawing



Essential Smartbright Projector (Wide Voltage) Gen 2

Dimensional drawing



Essential Smartbright Projector (Wide Voltage) Gen 2

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401892782	ST033T LED9/840 10W 110-240V I MB WH TW	4000 K	90 lm/W	900 lm
911401893082	ST033T LED17/830 20W 110-240V I MB WH TW	3000 K	80 lm/W	1,600 lm
911401893182	ST033T LED17/840 20W 110-240V I MB WH TW	4000 K	85 lm/W	1,700 lm
911401892482	ST033T LED6/830 7W 110-240V I WB BK TW	3000 K	80 lm/W	560 lm
911401892582	ST033T LED6/840 7W 110-240V I WB BK TW	4000 K	80 lm/W	560 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401893282	ST033T LED17/830 20W 110-240V I MB BK TW	20 W
911401893382	ST033T LED17/840 20W 110-240V I MB BK TW	20 W
911401892282	ST033T LED6/830 7W 110-240V I WB WH TW	7 W
911401892382	ST033T LED6/840 7W 110-240V I WB WH TW	7 W
911401893682	ST033T LED25/830 30W 110-240V I MB BK TW	30 W
911401893782	ST033T LED25/840 30W 110-240V I MB BK TW	30 W
911401893482	ST033T LED25/830 30W 110-240V I MB WH TW	30 W
911401893582	ST033T LED25/840 30W 110-240V I MB WH TW	30 W

Order Code	Full Product Name	Power Consumption
911401892882	ST033T LED9/830 10W 110-240V I MB BK TW	10 W
911401892982	ST033T LED9/840 10W 110-240V I MB BK TW	10 W
911401892682	ST033T LED9/830 10W 110-240V I MB WH TW	10 W
911401892782	ST033T LED9/840 10W 110-240V I MB WH TW	10 W
911401893082	ST033T LED17/830 20W 110-240V I MB WH TW	20 W
911401893182	ST033T LED17/840 20W 110-240V I MB WH TW	20 W
911401892482	ST033T LED6/830 7W 110-240V I WB BK TW	7 W
911401892582	ST033T LED6/840 7W 110-240V I WB BK TW	7 W

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing
			Color
911401893282	ST033T LED17/830 20W 110-240V I MB BK TW	Collimator with focus angle 24°	Black
911401893382	ST033T LED17/840 20W 110-240V I MB BK TW	Collimator with focus angle 24°	Black
911401892282	ST033T LED6/830 7W 110-240V I WB WH TW	Collimator with focus angle 30°	White
911401892382	ST033T LED6/840 7W 110-240V I WB WH TW	Collimator with focus angle 30°	White
911401893682	ST033T LED25/830 30W 110-240V I MB BK TW	Collimator with focus angle 24°	Black
911401893782	ST033T LED25/840 30W 110-240V I MB BK TW	Collimator with focus angle 24°	Black
911401893482	ST033T LED25/830 30W 110-240V I MB WH TW	Collimator with focus angle 24°	White
911401893582	ST033T LED25/840 30W 110-240V I MB WH TW	Collimator with focus angle 24°	White

Order Code	Full Product Name	Optical cover type	Housing
			Color
911401892882	ST033T LED9/830 10W 110-240V I MB BK TW	Collimator with focus angle 24°	Black
911401892982	ST033T LED9/840 10W 110-240V I MB BK TW	Collimator with focus angle 24°	Black
911401892682	ST033T LED9/830 10W 110-240V I MB WH TW	Collimator with focus angle 24°	White
911401892782	ST033T LED9/840 10W 110-240V I MB WH TW	Collimator with focus angle 24°	White
911401893082	ST033T LED17/830 20W 110-240V I MB WH TW	Collimator with focus angle 24°	White
911401893182	ST033T LED17/840 20W 110-240V I MB WH TW	Collimator with focus angle 24°	White
911401892482	ST033T LED6/830 7W 110-240V I WB BK TW	Collimator with focus angle 30°	Black
911401892582	ST033T LED6/840 7W 110-240V I WB BK TW	Collimator with focus angle 30°	Black

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401893282	ST033T LED17/830 20W 110-240V I MB BK TW	(0.4338, 0.4030) SDCM <5

Order Code	Full Product Name	Initial chromaticity
911401893382	ST033T LED17/840 20W 110-240V I MB BK TW	(0.3818, 0.3797) SDCM <5

Essential Smartbright Projector (Wide Voltage) Gen 2

Order Code	Full Product Name	Initial chromaticity
911401892282	ST033T LED6/830 7W 110-240V I WB WH TW	(0.4338, 0.4030) SDCM <5
911401892382	ST033T LED6/840 7W 110-240V I WB WH TW	(0.3818, 0.3797) SDCM <5
911401893682	ST033T LED25/830 30W 110-240V I MB BK TW	(0.4338, 0.4030) SDCM <5
911401893782	ST033T LED25/840 30W 110-240V I MB BK TW	(0.3818, 0.3797) SDCM <5
911401893482	ST033T LED25/830 30W 110-240V I MB WH TW	(0.4338, 0.4030) SDCM <5
911401893582	ST033T LED25/840 30W 110-240V I MB WH TW	(0.3818, 0.3797) SDCM <5
911401892882	ST033T LED9/830 10W 110-240V I MB BK TW	(0.4338, 0.4030) SDCM <5

Order Code	Full Product Name	Initial chromaticity
911401892982	ST033T LED9/840 10W 110-240V I MB BK TW	(0.3818, 0.3797) SDCM <5
911401892682	ST033T LED9/830 10W 110-240V I MB WH TW	(0.4338, 0.4030) SDCM <5
911401892782	ST033T LED9/840 10W 110-240V I MB WH TW	(0.3818, 0.3797) SDCM <5
911401893082	ST033T LED17/830 20W 110-240V I MB WH TW	(0.4338, 0.4030) SDCM <5
911401893182	ST033T LED17/840 20W 110-240V I MB WH TW	(0.3818, 0.3797) SDCM <5
911401892482	ST033T LED6/830 7W 110-240V I WB BK TW	(0.4338, 0.4030) SDCM <5
911401892582	ST033T LED6/840 7W 110-240V I WB BK TW	(0.3818, 0.3797) SDCM <5

