



# Our most efficient LED bulb

## MASTER UltraEfficient LED bulb

This is the most efficient LED bulb from Philips brand. 210lm/W helps to concrete the company statement of sustainability. 50000 hour lifetime helps to extend the replacement cycle to reduce the waste. This is not only the high SPEC product, but also keep the light quality of Philips brand

### Benefits

- energy saving, 60% less energy comapring with standard Philips LED bulbs
- Very long lifetime that reduces the need for replacement
- Easy replacement of conventional lamps

### Features

- Ultra energy efficient, with 210lm/W
- Long lifetime, more than 3 times longer lifetime than the normal LED products
- Well optimized the look and feel, without impact on the application. Easy for the installation
- Designed to be seen, they look good on and off
- Enviromentally friendly: contains no mercury or other hazardous sustances

### Application

- Domestic application
- Hospitality: restaurants and hotels



# MASTER UltraEfficient LED bulb

## Versions



LEDbulb MAS EU A60 E27 CL 3

## Dimensional drawing



Product	D	C
LED CLA 4W A60 E27 2700K FR UE SRT6	60 mm	104 mm
LED CLA 60W A60 E27 3000K CL EELA SRT AU	60 mm	105 mm
LED CLA 7.3W A60 E27 2700K FR UE SRT6	60 mm	104 mm
LED CLA 7.3W A60 E27 4000K FR UE SRT6	60 mm	104 mm

Product	D	C
LED CLA 4W A60 B22 2700K FR UE SRT6	60 mm	102 mm
LED CLA 7.3W A60 B22 2700K FR UE SRT6	60 mm	102 mm
LED CLA 7.3W A60 B22 4000K FR UE SRT6	60 mm	102 mm

MASTER UltraEfficient LED bulb

General Information	
Switching Cycle	50,000
Nominal lifetime	50,000 hour(s)
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	A60
Approval and Application	
Ambient temperature range	-20 to +45 °C

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	B22	-
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	B22	-
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	B22	-
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	E27	-
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	E27	-
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	E27	-
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	E27	50,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
			Beam Angle (Nom)		
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	300 degree(s)	2700 K	827	840 lm
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	300 degree(s)	2700 K	827	1,535 lm
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	300 degree(s)	4000 K	840	1,535 lm
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	300 degree(s)	2700 K	827	840 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
			Beam Angle (Nom)		
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	300 degree(s)	2700 K	827	1,535 lm
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	300 degree(s)	4000 K	840	1,535 lm
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	-	3000 K	830	840 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	4 W	60 W
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	7.3 W	100 W
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	7.3 W	100 W
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	4 W	60 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	7.3 W	100 W
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	7.3 W	100 W
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	4 W	60 W

MASTER UltraEfficient LED bulb


Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	70 °C
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	70 °C
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	70 °C
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	70 °C


Order Code	Full Product Name	T-Case Maximum (Nom)
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	70 °C
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	70 °C
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	35 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	Frosted
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	Frosted
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	Frosted
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	Frosted
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	Frosted
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	Frosted
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	Clear



MASTER UltraEfficient LED bulb



## MASTER UltraEfficient LED bulb

