



Den ideelle løsning til spotbelysning

MASTER Value LED-spot PAR

Med det robuste design og den varme hvide lysstråle er denne nye generation af PAR-lyskilder ideel til generel belysning og spotbelysning i restauranter og på hoteller. Det er en dæmpbar løsning. De er særligt velegnede til offentlige områder som f.eks. lobbyer, gangarealer og trappeskakter, hvor lyset altid er tændt. Produktet tilbyder større energibesparelse sammenlignet med normale LED-spots.

Fordele

- Energibesparelser på op til 80 % sammenlignet med halogenlamper
- Lavere vedligeholdelsesomkostninger
- Kan eftermonteres og er kompatibel med eksisterende armaturer med E27-holderen

Funktioner

- Dæmpningsområde
- UV- og IR-frit lys giver mindre varme og medvirker dermed til at beskytte varmefølsomme genstande
- Levetid på 25.000 timer
- Indeholder ikke kviksløv eller andre farlige materialer – overholder RoHS-direktivet

Anvendelsesområder

- Hotel og restauration: hotelværelser, korridorer, lobby, receptionsområde, restauranter, barer, caféer
- Hjemmet: stue, soveværelse, entré
- Detailhandel: udstillingslokaler, udstillingsmontre, butikker, prøverum

MASTER Value LED-spot PAR

Versions






LED Classic 100W PAR38 WW 25D
D 1PF 4 S



LED Classic 75W PAR30S WW 25D
D 1PF 4 S

Målskitse



Product	D	C
MAS LEDspot VLE D 13-100W 927 PAR38 25D	122 mm	134 mm

Product	D	C
MAS LEDspot VLE D 6-50W 927 PAR20 25D	65 mm	85 mm
MAS LEDspot VLE D 6-50W 927 PAR20 40D	65 mm	85 mm
MAS LEDspot VLE D 6-50W 930 PAR20 25D	65 mm	85 mm
MAS LEDspot VLE D 6-50W 930 PAR20 40D	65 mm	85 mm
MAS LEDspot VLE D 6-50W 940 PAR20 25D	65 mm	85 mm
MAS LEDspot VLE D 6-50W 940 PAR20 40D	65 mm	85 mm

Product	D	C
MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	95 mm	86 mm
MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	95 mm	86 mm
MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	95 mm	86 mm

MASTER Value LED-spot PAR

Generelle oplysninger	
Fod	E27
Skiftecyklus	50.000
Normeret levetid	25.000 t
Lysteknisk	
Farvegengivelsesindeks (CRI)	90
LLMF ved den nominelle levetids udløb (nom.)	70 %
Drift og el	
Indgangsfrekvens	50 til 60 Hz
Linjefrekvens	50 to 60 Hz
Opstartstid (nom.)	0,5 s
Lysstyringssystemer og dæmpning	
Dæmpbar	Kun med visse lysdæmpere
Mekanik og armaturhus	
Pære finish	Klar

Lysteknisk (1/2)

Order Code	Full Product Name	Spredningsvinkel (nom.)	Korreleret farvetemperatur	Farvekode	Lysstrøm
			(nom.)		
929003485702	MAS LEDspot VLE D 6-50W 927 PAR20 25D	25 °	2700 K	927	500 lm
929003485802	MAS LEDspot VLE D 6-50W 930 PAR20 25D	25 °	3000 K	930	515 lm
929003485902	MAS LEDspot VLE D 6-50W 940 PAR20 25D	25 °	4000 K	940	540 lm
929003486002	MAS LEDspot VLE D 6-50W 927 PAR20 40D	40 °	2700 K	927	500 lm
929003486102	MAS LEDspot VLE D 6-50W 930 PAR20 40D	40 °	3000 K	930	515 lm
929003486202	MAS LEDspot VLE D 6-50W 940 PAR20 40D	40 °	4000 K	940	540 lm
929003485202	MAS LEDspot VLE D 13-100W 927 PAR38 25D	25 °	2700 K	927	1.000 lm
929003485402	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	25 °	2700 K	927	740 lm
929003485502	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	25 °	3000 K	930	760 lm
929003485602	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	25 °	4000 K	940	820 lm

Lysteknisk (2/2)

Order Code	Full Product Name	Lysstyrke (nom.)	Order Code	Full Product Name	Lysstyrke (nom.)
929003485702	MAS LEDspot VLE D 6-50W 927 PAR20 25D	1.500 cd	929003486202	MAS LEDspot VLE D 6-50W 940 PAR20 40D	1.100 cd
929003485802	MAS LEDspot VLE D 6-50W 930 PAR20 25D	1.600 cd	929003485202	MAS LEDspot VLE D 13-100W 927 PAR38 25D	4.800 cd
929003485902	MAS LEDspot VLE D 6-50W 940 PAR20 25D	1.700 cd	929003485402	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	3.000 cd
929003486002	MAS LEDspot VLE D 6-50W 927 PAR20 40D	1.000 cd	929003485502	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	3.000 cd
929003486102	MAS LEDspot VLE D 6-50W 930 PAR20 40D	1.000 cd	929003485602	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	3.000 cd

Drift og el

Order Code	Full Product Name	Strømforsbrug	Wattforbrugsækvivalent	Order Code	Full Product Name	Strømforsbrug	Wattforbrugsækvivalent
929003485702	MAS LEDspot VLE D 6-50W 927 PAR20 25D	6 W	50 W	929003486202	MAS LEDspot VLE D 6-50W 940 PAR20 40D	6 W	50 W
929003485802	MAS LEDspot VLE D 6-50W 930 PAR20 25D	6 W	50 W	929003485202	MAS LEDspot VLE D 13-100W 927 PAR38 25D	13 W	100 W
929003485902	MAS LEDspot VLE D 6-50W 940 PAR20 25D	6 W	50 W	929003485402	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	9,5 W	75 W
929003486002	MAS LEDspot VLE D 6-50W 927 PAR20 40D	6 W	50 W	929003485502	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	9,5 W	75 W
929003486102	MAS LEDspot VLE D 6-50W 930 PAR20 40D	6 W	50 W	929003485602	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	9,5 W	75 W

Temperatur

MASTER Value LED-spot PAR

Order Code	Full Product Name	T-kappe, maks. (nom.)
929003485702	MAS LEDspot VLE D 6-50W 927 PAR20 25D	80 °C
929003485802	MAS LEDspot VLE D 6-50W 930 PAR20 25D	80 °C
929003485902	MAS LEDspot VLE D 6-50W 940 PAR20 25D	80 °C
929003486002	MAS LEDspot VLE D 6-50W 927 PAR20 40D	80 °C
929003486102	MAS LEDspot VLE D 6-50W 930 PAR20 40D	80 °C

Order Code	Full Product Name	T-kappe, maks. (nom.)
929003486202	MAS LEDspot VLE D 6-50W 940 PAR20 40D	80 °C
929003485202	MAS LEDspot VLE D 13-100W 927 PAR38 25D	85 °C
929003485402	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	80 °C
929003485502	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	80 °C
929003485602	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	80 °C





Mekanik og armaturhus

Order Code	Full Product Name	Lyskildeform
929003485702	MAS LEDspot VLE D 6-50W 927 PAR20 25D	PAR20
929003485802	MAS LEDspot VLE D 6-50W 930 PAR20 25D	PAR20
929003485902	MAS LEDspot VLE D 6-50W 940 PAR20 25D	PAR20
929003486002	MAS LEDspot VLE D 6-50W 927 PAR20 40D	PAR20
929003486102	MAS LEDspot VLE D 6-50W 930 PAR20 40D	PAR20



Order Code	Full Product Name	Lyskildeform
929003486202	MAS LEDspot VLE D 6-50W 940 PAR20 40D	PAR20
929003485202	MAS LEDspot VLE D 13-100W 927 PAR38 25D	PAR38
929003485402	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	PAR30S
929003485502	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	PAR30S
929003485602	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	PAR30S

Godkendelse og anvendelsesområde


Order Code	Full Product Name	Energiforbrug kWh/ 1000 t.
929003485702	MAS LEDspot VLE D 6-50W 927 PAR20 25D	6 kWh
929003485802	MAS LEDspot VLE D 6-50W 930 PAR20 25D	6 kWh
929003485902	MAS LEDspot VLE D 6-50W 940 PAR20 25D	6 kWh
929003486002	MAS LEDspot VLE D 6-50W 927 PAR20 40D	6 kWh
929003486102	MAS LEDspot VLE D 6-50W 930 PAR20 40D	6 kWh
929003486202	MAS LEDspot VLE D 6-50W 940 PAR20 40D	6 kWh
929003485202	MAS LEDspot VLE D 13-100W 927 PAR38 25D	13 kWh
929003485402	MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D	10 kWh
929003485502	MAS LEDspot VLE D 9.5-75W 930 PAR30S 25D	10 kWh
929003485602	MAS LEDspot VLE D 9.5-75W 940 PAR30S 25D	10 kWh




MASTER Value LED-spot PAR




Accent Diagrams



Accent Diagram - MAS LEDspot VLE D 6-50W 927 PAR20 40D




Accent Diagram - MAS LEDspot VLE D 6-50W 927 PAR20 25D




Accent Diagram - MAS LEDspot VLE D 9.5-75W 927 PAR30S 25D

MASTER Value LED-spot PAR


Accent Diagrams




Accent Diagram - MAS LEDspot VLE D 6-50W
930 PAR20 25D




Accent Diagram - MAS LEDspot VLE D 6-50W
940 PAR20 25D




Accent Diagram - MAS LEDspot VLE D 6-50W
940 PAR20 40D




Accent Diagram - MAS LEDspot VLE D 9.5-75W
940 PAR30S 25D



Accent Diagram - MAS LEDspot VLE D 9.5-75W
930 PAR30S 25D




Accent Diagram - MAS LEDspot VLE D 13-100W
927 PAR38 25D




Accent Diagram - MAS LEDspot VLE D 6-50W
930 PAR20 40D

MASTER Value LED-spot PAR


Beam Diagrams




Beam diagram - MAS LEDspot VLE D 9.5-75W
927 PAR30S 25D




Beam diagram - MAS LEDspot VLE D 6-50W
927 PAR20 25D




Beam diagram - MAS LEDspot VLE D 6-50W
940 PAR20 40D




Beam diagram - MAS LEDspot VLE D 6-50W
940 PAR20 25D




Beam diagram - MAS LEDspot VLE D 6-50W
930 PAR20 25D




Beam diagram - MAS LEDspot VLE D 13-100W
927 PAR38 25D



Beam diagram - MAS LEDspot VLE D 6-50W
927 PAR20 40D




Beam diagram - MAS LEDspot VLE D 9.5-75W
930 PAR30S 25D



Beam diagram - MAS LEDspot VLE D 6-50W
930 PAR20 40D

MASTER Value LED-spot PAR

Beam Diagrams



Beam diagram - MAS LEDspot VLE D 9.5-75W
940 PAR30S 25D

