



# Trusted Performance, everyday.

## SmartBright Dual Select Waterproof WT072C

Philips Dual select Wide Waterproof batten offers exceptional value. It is Perfect for everyday lighting installations. Available in 2 standard sizes, it has option of 3 CCT selection switch and 2 Wattage selection to provide flexibility to customer and reduce stocking requirement. It is IP65/IK08 design which makes it suitable to be used in all weathers.

### Benefits

- Tri-CCT, Dual wattage selectable
- 50K hours life
- 5 Years warranty

### Features

- Selectable dual power output to suit multiple application environments.
- 3 selectable colour temperatures to suit specific customer need
- IP65/IK08 – Water and dustproof. For all weather
- Reliable with a long service life of 50 000 hours
- 5 years warranty

### Application

- Parking Garages
- Warehouses
- Offices

# SmartBright Dual Select Waterproof WT072C

## Versions




WT072C L600

WT072C L1200

WT072C L1500

## Dimensional drawing



# SmartBright Dual Select Waterproof WT072C

| Light Technical                     |  |
|-------------------------------------|--|
| Correlated Color Temperature (Nom)  | 4000 K   |
| Color rendering index (CRI)         | >80  |
| Operating and Electrical            |  |
| Protection class IEC                | Safety class I                                       |
| Input Voltage                       | 220~240 V  |
| Line Frequency                      | 50 or 60 Hz  |
| Controls and Dimming                |  |
| Dimmable                            | No   |
| Mechanical and Housing              |  |
| Optical cover type                  | Reflector  |
| Housing Color                       | Gray and white                                       |
| Mech. impact protection code        | IK08   |
| Ingress protection code             | IP65   |
| Approval and Application            |  |
| Ambient temperature range           | -20 to +40 °C  |
| CE mark                             | No   |
| Flammability mark                   | For mounting on<br>normally<br>flammable<br>surfaces |
| Initial Performance (IEC Compliant) |  |
| Initial chromaticity                | (0.382,0.380)SDC<br>M<5                              |
| Luminous flux tolerance             | +/-10%   |

## Light Technical

| Order Code   | Full Product Name                  | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|------------------------------------|---------------------------------|---------------|
| 911401802284 | WT072C LED SWT/SCCT L600 PSU Wide  | 110 lm/W                        | 2,000 lm      |
| 911401802384 | WT072C LED SWT/SCCT L1200 PSU Wide | 110 lm/W                        | 4,000 lm      |
| 911401802484 | WT072C LED SWT/SCCT L1500 PSU Wide | 120 lm/W                        | 6,000 lm      |

## Operating and Electrical

| Order Code   | Full Product Name                  | Power Consumption |
|--------------|------------------------------------|-------------------|
| 911401802284 | WT072C LED SWT/SCCT L600 PSU Wide  | 18 W              |
| 911401802384 | WT072C LED SWT/SCCT L1200 PSU Wide | 36 W              |

| Order Code   | Full Product Name                  | Power Consumption |
|--------------|------------------------------------|-------------------|
| 911401802484 | WT072C LED SWT/SCCT L1500 PSU Wide | 50 W              |

