

Pure line of light. Slim PureLine is an elegant and energy-efficient office lighting solution, offering flexibility for the future of workspaces.

Pureline slim

The PureLine Slim family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting with Sleek profile which helps Declutter the ceilings. The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

Benefits

- Optimized lighting for office space: smooth and comfortable
- Dimmable and fixed output drivers
- Suitable for working and non-working areas
- Compliant with office lighting norms
- Sleek with minimal bezel
- Sustainability coupled with comfortable ambience
- Enhance Interiors

Features

- Superior efficacy of 110 lm/W
- Suitable for Standalone & Continuous Mounting
- Up-Down lighting distribution
- Uniform & volumetric light distribution
- Comfortable Light – CRI of 80 to ensure better color rendering.
- Minimum Bezel and 50mm wide
- Lifetime: 50,000 Hrs. @ Ta45°C, BIS Approbation – Safe and Reliable performance
- THD<10% – Higher power factor, lower peak currents, and higher efficiency.
- Flicker Free Lighting Effects – New light platform and optical design with ripple < 5%
- Lighting solution with high uniformity provides comfort in office lighting experience.
- Connected ready(Dali/interact) versions available for Smart offices/workspaces
- Multiple Lumen Packs & CCT – For different office applications and mounting heights


Application

- Modern Workspaces
- Meeting and Conference room
- Institutions
- Community Centers

Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Beam angle of light source	- degree(s)
Optic type	-
Operating and Electrical	
Protection class IEC	Safety class I
Mechanical and Housing	
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	0 to +45 °C
Flammability mark	For mounting on normally flammable surfaces
Initial Performance (IEC Compliant)	
Initial chromaticity	<5

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
919515815225	SP780 H LED25S-6500 PSU W5L112 OD WH	6500 K	>80	125 lm/W	2,500 lm
919515815226	SP780 H LED25S-4000 PSU W5L112 OD WH	4000 K	>80	125 lm/W	2,500 lm
919515815227	SP780 H LED23S-6500 PSU W5L112 OC WH	6500 K	>80	115 lm/W	2,300 lm
919515815228	SP780 H LED23S-4000 PSU W5L112 OC WH	4000 K	>80	115 lm/W	2,300 lm
919515815252	SP780 H LED22S-6500 PSU W5L112 OD WH	6500 K	>80	120 lm/W	2,200 lm
919515815253	SP780 H LED22S-4000 PSU W5L112 OD WH	4000 K	>80	120 lm/W	2,200 lm
919515815254	SP780X H LED22S-6500 PSU W5L112 OD WH	6500 K	>80	120 lm/W	2,200 lm
919515815255	SP780X H LED22S-4000 PSU W5L112 OD WH	4000 K	>80	120 lm/W	2,200 lm
919515815256	SP780X H LED20S-6500 PSU W5L112 OC WH	6500 K	>80	110 lm/W	2,000 lm
919515815257	SP780X H LED20S-4000 PSU W5L112 OC WH	4000 K	>80	110 lm/W	2,000 lm
919515815258	SP780 H LED18S-6500 PSU W5L112 OD WH	6500 K	>80	120 lm/W	1,800 lm
919515815259	SP780 H LED18S-4000 PSU W5L112 OD WH	4000 K	>80	120 lm/W	1,800 lm
919515815260	SP780X H LED18S-6500 PSU W5L112 OD WH	6500 K	>80	120 lm/W	1,800 lm
919515815261	SP780X H LED18S-4000 PSU W5L112 OD WH	4000 K	>80	120 lm/W	1,800 lm
919515815262	SP780 H LED25S-6500 PSD W5L112 OD WH	6500 K	>80	125 lm/W	2,500 lm
919515815263	SP780 H LED25S-4000 PSD W5L112 OD WH	4000 K	>80	125 lm/W	2,500 lm
919515815264	SP780 H LED23S-6500 PSD W5L112 OC WH	6500 K	>80	115 lm/W	2,300 lm
919515815265	SP780 H LED23S-4000 PSD W5L112 OC WH	4000 K	>80	115 lm/W	2,300 lm
919515815266	SP780 H LED22S-6500 PSD W5L112 OD WH	6500 K	>80	120 lm/W	2,200 lm
919515815267	SP780 H LED22S-4000 PSD W5L112 OD WH	4000 K	>80	120 lm/W	2,200 lm
919515815268	SP780X H LED22S-6500 PSD W5L112 OD WH	6500 K	>80	120 lm/W	2,200 lm
919515815269	SP780X H LED22S-4000 PSD W5L112 OD WH	4000 K	>80	120 lm/W	2,200 lm
919515815270	SP780X H LED20S-6500 PSD W5L112 OC WH	6500 K	>80	110 lm/W	2,000 lm
919515815271	SP780X H LED20S-4000 PSD W5L112 OC WH	4000 K	>80	110 lm/W	2,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
919515815272	SP780 H LED18S-6500 PSD W5L112 OD WH	6500 K	>80	120 lm/W	1,800 lm
919515815273	SP780 H LED18S-4000 PSD W5L112 OD WH	4000 K	>80	120 lm/W	1,800 lm
919515815274	SP780X H LED18S-6500 PSD W5L112 OD WH	6500 K	>80	120 lm/W	1,800 lm
919515815275	SP780X H LED18S-4000 PSD W5L112 OD WH	4000 K	>80	120 lm/W	1,800 lm
919515815276	SP780 H LED50S-6500 PSU W5L224 OD WH	6500 K	>80	125 lm/W	5,000 lm
919515815280	SP780 H LED44S-6500 PSU W5L224 OD WH	6500 K	>80	120 lm/W	4,400 lm
919515815305	SP780 H LED25S-5700 PSU W5L112 OD WH	5700 K	>80	125 lm/W	2,500 lm
919515815306	SP780 H LED23S-5700 PSU W5L112 OC WH	5700 K	>80	115 lm/W	2,300 lm
919515815307	SP780 H LED22S-5700 PSU W5L112 OD WH	5700 K	>80	120 lm/W	2,200 lm
919515815308	SP780X H LED22S-5700 PSU W5L112 OD WH	5700 K	>80	120 lm/W	2,200 lm
919515815309	SP780X H LED20S-5700 PSU W5L112 OC WH	5700 K	>80	110 lm/W	2,000 lm
919515815310	SP780 H LED18S-5700 PSU W5L112 OD WH	5700 K	>80	120 lm/W	1,800 lm
919515815311	SP780X H LED18S-5700 PSU W5L112 OD WH	5700 K	>80	120 lm/W	1,800 lm
919515815312	SP780 H LED25S-5700 PSD W5L112 OD WH	5700 K	>80	125 lm/W	2,500 lm
919515815316	SP780X H LED20S-5700 PSD W5L112 OC WH	5700 K	>80	110 lm/W	2,000 lm
919515815899	SP780 H LED25S-6500 PSU W5L112 OD S1 WH	6500 K	80	125 lm/W	2,500 lm
919515815901	SP780 H LED25S-5700 PSU W5L112 OD S1 WH	5700 K	80	125 lm/W	2,500 lm
919515815902	SP780 H LED25S-4000 PSU W5L112 OD S1 WH	4000 K	80	125 lm/W	2,500 lm
919515815903	SP780 H LED23S-6500 PSU W5L112 OC S1 WH	6500 K	80	115 lm/W	2,300 lm
919515815904	SP780 H LED23S-5700 PSU W5L112 OC S1 WH	5700 K	80	115 lm/W	2,300 lm
919515815905	SP780 H LED23S-4000 PSU W5L112 OC S1 WH	4000 K	80	115 lm/W	2,300 lm
919515815906	SP780 H LED22S-6500 PSU W5L112 OD S1 WH	6500 K	80	120 lm/W	2,200 lm
919515815907	SP780 H LED22S-5700 PSU W5L112 OD S1 WH	5700 K	80	120 lm/W	2,200 lm
919515815908	SP780 H LED22S-4000 PSU W5L112 OD S1 WH	4000 K	80	120 lm/W	2,200 lm
919515815909	SP780X H LED22S-6500 PSU W5L112 OD S1 WH	6500 K	80	120 lm/W	2,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
919515815910	SP780X H LED22S-5700 PSU W5L112 OD S1 WH	5700 K	80	120 lm/W	2,200 lm
919515815911	SP780X H LED22S-4000 PSU W5L112 OD S1 WH	4000 K	80	120 lm/W	2,200 lm
919515815912	SP780X H LED20S-6500 PSU W5L112 OC S1 WH	6500 K	80	110 lm/W	2,000 lm
919515815913	SP780X H LED20S-5700 PSU W5L112 OC S1 WH	5700 K	80	110 lm/W	2,000 lm
919515815914	SP780X H LED20S-4000 PSU W5L112 OC S1 WH	4000 K	80	110 lm/W	2,000 lm
919515815915	SP780 H LED50S-6500 PSU W5L224 OD S1 WH	6500 K	80	125 lm/W	5,000 lm
919515815916	SP780 H LED50S-5700 PSU W5L224 OD S1 WH	5700 K	80	125 lm/W	5,000 lm
919515815917	SP780 H LED50S-4000 PSU W5L224 OD S1 WH	4000 K	80	125 lm/W	5,000 lm
919515815918	SP780 H LED46S-6500 PSU W5L224 OC S1 WH	6500 K	80	115 lm/W	4,600 lm
919515815919	SP780 H LED46S-5700 PSU W5L224 OC S1 WH	5700 K	80	115 lm/W	4,600 lm
919515815920	SP780 H LED46S-4000 PSU W5L224 OC S1 WH	4000 K	80	115 lm/W	4,600 lm
919515815921	SP780 H LED44S-6500 PSU W5L224 OD S1 WH	6500 K	80	120 lm/W	4,400 lm
919515815922	SP780 H LED44S-5700 PSU W5L224 OD S1 WH	5700 K	80	120 lm/W	4,400 lm
919515815923	SP780 H LED44S-4000 PSU W5L224 OD S1 WH	4000 K	80	120 lm/W	4,400 lm
919515815924	SP780X H LED44S-6500 PSU W5L224 OD S1 WH	6500 K	80	120 lm/W	4,400 lm
919515815925	SP780X H LED44S-5700 PSU W5L224 OD S1 WH	5700 K	80	120 lm/W	4,400 lm
919515815926	SP780X H LED44S-4000 PSU W5L224 OD S1 WH	4000 K	80	120 lm/W	4,400 lm
919515815927	SP780X H LED40S-6500 PSU W5L224 OC S1 WH	6500 K	80	110 lm/W	4,000 lm
919515815928	SP780X H LED40S-5700 PSU W5L224 OC S1 WH	5700 K	80	110 lm/W	4,000 lm
919515815929	SP780X H LED40S-4000 PSU W5L224 OC S1 WH	4000 K	80	110 lm/W	4,000 lm
919515816241	SP780 HS LED25S-6500 PSU W5L112 OD S1 WH	6500 K	80	125 lm/W	2,500 lm
919515816242	SP780 HS LED25S-5700 PSU W5L112 OD S1 WH	5700 K	80	125 lm/W	2,500 lm
919515816243	SP780 HS LED25S-4000 PSU W5L112 OD S1 WH	4000 K	80	125 lm/W	2,500 lm
919515816244	SP780 HS LED23S-6500 PSU W5L112 OC S1 WH	6500 K	80	115 lm/W	2,300 lm
919515816245	SP780 HS LED23S-5700 PSU W5L112 OC S1 WH	5700 K	80	115 lm/W	2,300 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
919515816246	SP780 HS LED23S-4000 PSU W5L112 OC S1 WH	4000 K	80	115 lm/W	2,300 lm
919515816247	SP780 HS LED22S-6500 PSU W5L112 OD S1 WH	6500 K	80	120 lm/W	2,200 lm
919515816248	SP780 HS LED22S-5700 PSU W5L112 OD S1 WH	5700 K	80	120 lm/W	2,200 lm
919515816249	SP780 HS LED22S-4000 PSU W5L112 OD S1 WH	4000 K	80	120 lm/W	2,200 lm
919515816250	SP780X HS LED22S-6500 PSU W5L112 OD S1 W	6500 K	80	120 lm/W	2,200 lm
919515816251	SP780X HS LED22S-5700 PSU W5L112 OD S1 W	5700 K	80	120 lm/W	2,200 lm
919515816252	SP780X HS LED22S-4000 PSU W5L112 OD S1 W	4000 K	80	120 lm/W	2,200 lm
919515816253	SP780X HS LED20S-6500 PSU W5L112 OC S1 W	6500 K	80	110 lm/W	2,000 lm
919515816254	SP780X HS LED20S-5700 PSU W5L112 OC S1 W	5700 K	80	110 lm/W	2,000 lm
919515816255	SP780X HS LED20S-4000 PSU W5L112 OC S1 W	4000 K	80	110 lm/W	2,000 lm
919515816256	SP780 HS LED50S-6500 PSU W5L224 OD S1 WH	6500 K	80	125 lm/W	5,000 lm
919515816257	SP780 HS LED50S-5700 PSU W5L224 OD S1 WH	5700 K	80	125 lm/W	5,000 lm
919515816258	SP780 HS LED50S-4000 PSU W5L224 OD S1 WH	4000 K	80	125 lm/W	5,000 lm
919515816259	SP780 HS LED46S-6500 PSU W5L224 OC S1 WH	6500 K	80	115 lm/W	4,600 lm
919515816260	SP780 HS LED46S-5700 PSU W5L224 OC S1 WH	5700 K	80	115 lm/W	4,600 lm
919515816261	SP780 HS LED46S-4000 PSU W5L224 OC S1 WH	4000 K	80	115 lm/W	4,600 lm
919515816262	SP780 HS LED44S-6500 PSU W5L224 OD S1 WH	6500 K	80	120 lm/W	4,400 lm
919515816263	SP780 HS LED44S-5700 PSU W5L224 OD S1 WH	5700 K	80	120 lm/W	4,400 lm
919515816264	SP780 HS LED44S-4000 PSU W5L224 OD S1 WH	4000 K	80	120 lm/W	4,400 lm
919515816265	SP780X HS LED44S-6500 PSU W5L224 OD S1 W	6500 K	80	120 lm/W	4,400 lm
919515816266	SP780X HS LED44S-5700 PSU W5L224 OD S1 W	5700 K	80	120 lm/W	4,400 lm
919515816267	SP780X HS LED44S-4000 PSU W5L224 OD S1 W	4000 K	80	120 lm/W	4,400 lm
919515816268	SP780X HS LED40S-6500 PSU W5L224 OC S1 W	6500 K	80	110 lm/W	4,000 lm
919515816269	SP780X HS LED40S-5700 PSU W5L224 OC S1 W	5700 K	80	110 lm/W	4,000 lm
919515816270	SP780X HS LED40S-4000 PSU W5L224 OC S1 W	4000 K	80	110 lm/W	4,000 lm

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power
			Consumption
919515815225	SP780 H LED25S-6500 PSU W5L112 OD WH	220 to 240 V	20 W
919515815226	SP780 H LED25S-4000 PSU W5L112 OD WH	220 to 240 V	20 W
919515815227	SP780 H LED23S-6500 PSU W5L112 OC WH	220 to 240 V	20 W
919515815228	SP780 H LED23S-4000 PSU W5L112 OC WH	220 to 240 V	20 W
919515815252	SP780 H LED22S-6500 PSU W5L112 OD WH	220 to 240 V	18 W
919515815253	SP780 H LED22S-4000 PSU W5L112 OD WH	220 to 240 V	18 W
919515815254	SP780X H LED22S-6500 PSU W5L112 OD WH	220 to 240 V	18 W
919515815255	SP780X H LED22S-4000 PSU W5L112 OD WH	220 to 240 V	18 W
919515815256	SP780X H LED20S-6500 PSU W5L112 OC WH	220 to 240 V	18 W
919515815257	SP780X H LED20S-4000 PSU W5L112 OC WH	220 to 240 V	18 W
919515815258	SP780 H LED18S-6500 PSU W5L112 OD WH	220 to 240 V	15 W
919515815259	SP780 H LED18S-4000 PSU W5L112 OD WH	220 to 240 V	15 W
919515815260	SP780X H LED18S-6500 PSU W5L112 OD WH	220 to 240 V	15 W
919515815261	SP780X H LED18S-4000 PSU W5L112 OD WH	220 to 240 V	15 W
919515815262	SP780 H LED25S-6500 PSD W5L112 OD WH	220 to 240 V	20 W
919515815263	SP780 H LED25S-4000 PSD W5L112 OD WH	220 to 240 V	20 W
919515815264	SP780 H LED23S-6500 PSD W5L112 OC WH	220 to 240 V	20 W
919515815265	SP780 H LED23S-4000 PSD W5L112 OC WH	220 to 240 V	20 W
919515815266	SP780 H LED22S-6500 PSD W5L112 OD WH	220 to 240 V	18 W
919515815267	SP780 H LED22S-4000 PSD W5L112 OD WH	220 to 240 V	18 W
919515815268	SP780X H LED22S-6500 PSD W5L112 OD WH	220 to 240 V	18 W
919515815269	SP780X H LED22S-4000 PSD W5L112 OD WH	220 to 240 V	18 W
919515815270	SP780X H LED20S-6500 PSD W5L112 OC WH	220 to 240 V	18 W
919515815271	SP780X H LED20S-4000 PSD W5L112 OC WH	220 to 240 V	18 W
919515815272	SP780 H LED18S-6500 PSD W5L112 OD WH	220 to 240 V	15 W

Order Code	Full Product Name	Input Voltage	Power
			Consumption
919515815273	SP780 H LED18S-4000 PSD W5L112 OD WH	220 to 240 V	15 W
919515815274	SP780X H LED18S-6500 PSD W5L112 OD WH	220 to 240 V	15 W
919515815275	SP780X H LED18S-4000 PSD W5L112 OD WH	220 to 240 V	15 W
919515815276	SP780 H LED50S-6500 PSU W5L224 OD WH	220 to 240 V	40 W
919515815280	SP780 H LED44S-6500 PSU W5L224 OD WH	220 to 240 V	36 W
919515815305	SP780 H LED25S-5700 PSU W5L112 OD WH	220 to 240 V	20 W
919515815306	SP780 H LED23S-5700 PSU W5L112 OC WH	220 to 240 V	20 W
919515815307	SP780 H LED22S-5700 PSU W5L112 OD WH	220 to 240 V	18 W
919515815308	SP780X H LED22S-5700 PSU W5L112 OD WH	220 to 240 V	18 W
919515815309	SP780X H LED20S-5700 PSU W5L112 OC WH	220 to 240 V	18 W
919515815310	SP780 H LED18S-5700 PSU W5L112 OD WH	220 to 240 V	15 W
919515815311	SP780X H LED18S-5700 PSU W5L112 OD WH	220 to 240 V	15 W
919515815312	SP780 H LED25S-5700 PSD W5L112 OD WH	220 to 240 V	20 W
919515815316	SP780X H LED20S-5700 PSD W5L112 OC WH	220 to 240 V	18 W
919515815899	SP780 H LED25S-6500 PSU W5L112 OD S1 WH	140-270 V	20 W
919515815901	SP780 H LED25S-5700 PSU W5L112 OD S1 WH	140-270 V	20 W
919515815902	SP780 H LED25S-4000 PSU W5L112 OD S1 WH	140-270 V	20 W
919515815903	SP780 H LED23S-6500 PSU W5L112 OC S1 WH	140-270 V	20 W
919515815904	SP780 H LED23S-5700 PSU W5L112 OC S1 WH	140-270 V	20 W
919515815905	SP780 H LED23S-4000 PSU W5L112 OC S1 WH	140-270 V	18 W
919515815906	SP780 H LED22S-6500 PSU W5L112 OD S1 WH	140-270 V	18 W
919515815907	SP780 H LED22S-5700 PSU W5L112 OD S1 WH	140-270 V	18 W
919515815908	SP780 H LED22S-4000 PSU W5L112 OD S1 WH	140-270 V	18 W
919515815909	SP780X H LED22S-6500 PSU W5L112 OD S1 WH	140-270 V	18 W
919515815910	SP780X H LED22S-5700 PSU W5L112 OD S1 WH	140-270 V	18 W

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
919515815911	SP780X H LED22S-4000 PSU W5L112 OD S1 WH	140-270 V	18 W
919515815912	SP780X H LED20S-6500 PSU W5L112 OC S1 WH	140-270 V	18 W
919515815913	SP780X H LED20S-5700 PSU W5L112 OC S1 WH	140-270 V	18 W
919515815914	SP780X H LED20S-4000 PSU W5L112 OC S1 WH	140-270 V	20 W
919515815915	SP780 H LED50S-6500 PSU W5L224 OD S1 WH	140-270 V	40 W
919515815916	SP780 H LED50S-5700 PSU W5L224 OD S1 WH	140-270 V	40 W
919515815917	SP780 H LED50S-4000 PSU W5L224 OD S1 WH	140-270 V	40 W
919515815918	SP780 H LED46S-6500 PSU W5L224 OC S1 WH	140-270 V	40 W
919515815919	SP780 H LED46S-5700 PSU W5L224 OC S1 WH	140-270 V	40 W
919515815920	SP780 H LED46S-4000 PSU W5L224 OC S1 WH	140-270 V	40 W
919515815921	SP780 H LED44S-6500 PSU W5L224 OD S1 WH	140-270 V	36 W
919515815922	SP780 H LED44S-5700 PSU W5L224 OD S1 WH	140-270 V	36 W
919515815923	SP780 H LED44S-4000 PSU W5L224 OD S1 WH	140-270 V	36 W
919515815924	SP780X H LED44S-6500 PSU W5L224 OD S1 WH	140-270 V	36 W
919515815925	SP780X H LED44S-5700 PSU W5L224 OD S1 WH	140-270 V	36 W
919515815926	SP780X H LED44S-4000 PSU W5L224 OD S1 WH	140-270 V	36 W
919515815927	SP780X H LED40S-6500 PSU W5L224 OC S1 WH	140-270 V	36 W
919515815928	SP780X H LED40S-5700 PSU W5L224 OC S1 WH	140-270 V	36 W
919515815929	SP780X H LED40S-4000 PSU W5L224 OC S1 WH	140-270 V	36 W
919515816241	SP780 HS LED25S-6500 PSU W5L112 OD S1 WH	140-270 V	20 W
919515816242	SP780 HS LED25S-5700 PSU W5L112 OD S1 WH	140-270 V	20 W
919515816243	SP780 HS LED25S-4000 PSU W5L112 OD S1 WH	140-270 V	20 W
919515816244	SP780 HS LED23S-6500 PSU W5L112 OC S1 WH	140-270 V	20 W
919515816245	SP780 HS LED23S-5700 PSU W5L112 OC S1 WH	140-270 V	18 W
919515816246	SP780 HS LED23S-4000 PSU W5L112 OC S1 WH	140-270 V	18 W

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
919515816247	SP780 HS LED22S-6500 PSU W5L112 OD S1 WH	140-270 V	18 W
919515816248	SP780 HS LED22S-5700 PSU W5L112 OD S1 WH	140-270 V	18 W
919515816249	SP780 HS LED22S-4000 PSU W5L112 OD S1 WH	140-270 V	18 W
919515816250	SP780X HS LED22S-6500 PSU W5L112 OD S1 W	140-270 V	18 W
919515816251	SP780X HS LED22S-5700 PSU W5L112 OD S1 W	140-270 V	18 W
919515816252	SP780X HS LED22S-4000 PSU W5L112 OD S1 W	140-270 V	18 W
919515816253	SP780X HS LED20S-6500 PSU W5L112 OC S1 W	140-270 V	18 W
919515816254	SP780X HS LED20S-5700 PSU W5L112 OC S1 W	140-270 V	18 W
919515816255	SP780X HS LED20S-4000 PSU W5L112 OC S1 W	140-270 V	18 W
919515816256	SP780 HS LED50S-6500 PSU W5L224 OD S1 WH	140-270 V	40 W
919515816257	SP780 HS LED50S-5700 PSU W5L224 OD S1 WH	140-270 V	40 W
919515816258	SP780 HS LED50S-4000 PSU W5L224 OD S1 WH	140-270 V	40 W
919515816259	SP780 HS LED46S-6500 PSU W5L224 OC S1 WH	140-270 V	40 W
919515816260	SP780 HS LED46S-5700 PSU W5L224 OC S1 WH	140-270 V	40 W
919515816261	SP780 HS LED46S-4000 PSU W5L224 OC S1 WH	140-270 V	40 W
919515816262	SP780 HS LED44S-6500 PSU W5L224 OD S1 WH	140-270 V	36 W
919515816263	SP780 HS LED44S-5700 PSU W5L224 OD S1 WH	140-270 V	36 W
919515816264	SP780 HS LED44S-4000 PSU W5L224 OD S1 WH	140-270 V	36 W
919515816265	SP780X HS LED44S-6500 PSU W5L224 OD S1 W	140-270 V	36 W
919515816266	SP780X HS LED44S-5700 PSU W5L224 OD S1 W	140-270 V	36 W
919515816267	SP780X HS LED44S-4000 PSU W5L224 OD S1 W	140-270 V	36 W
919515816268	SP780X HS LED40S-6500 PSU W5L224 OC S1 W	140-270 V	36 W
919515816269	SP780X HS LED40S-5700 PSU W5L224 OC S1 W	140-270 V	36 W
919515816270	SP780X HS LED40S-4000 PSU W5L224 OC S1 W	140-270 V	36 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
919515815225	SP780 H LED25S-6500 PSU W5L112 OD WH	No
919515815226	SP780 H LED25S-4000 PSU W5L112 OD WH	No
919515815227	SP780 H LED23S-6500 PSU W5L112 OC WH	No
919515815228	SP780 H LED23S-4000 PSU W5L112 OC WH	No
919515815252	SP780 H LED22S-6500 PSU W5L112 OD WH	No
919515815253	SP780 H LED22S-4000 PSU W5L112 OD WH	No
919515815254	SP780X H LED22S-6500 PSU W5L112 OD WH	No
919515815255	SP780X H LED22S-4000 PSU W5L112 OD WH	No
919515815256	SP780X H LED20S-6500 PSU W5L112 OC WH	No
919515815257	SP780X H LED20S-4000 PSU W5L112 OC WH	No
919515815258	SP780 H LED18S-6500 PSU W5L112 OD WH	No
919515815259	SP780 H LED18S-4000 PSU W5L112 OD WH	No
919515815260	SP780X H LED18S-6500 PSU W5L112 OD WH	No
919515815261	SP780X H LED18S-4000 PSU W5L112 OD WH	No
919515815262	SP780 H LED25S-6500 PSD W5L112 OD WH	Yes
919515815263	SP780 H LED25S-4000 PSD W5L112 OD WH	Yes
919515815264	SP780 H LED23S-6500 PSD W5L112 OC WH	Yes
919515815265	SP780 H LED23S-4000 PSD W5L112 OC WH	Yes
919515815266	SP780 H LED22S-6500 PSD W5L112 OD WH	Yes
919515815267	SP780 H LED22S-4000 PSD W5L112 OD WH	Yes
919515815268	SP780X H LED22S-6500 PSD W5L112 OD WH	Yes
919515815269	SP780X H LED22S-4000 PSD W5L112 OD WH	Yes
919515815270	SP780X H LED20S-6500 PSD W5L112 OC WH	Yes
919515815271	SP780X H LED20S-4000 PSD W5L112 OC WH	Yes
919515815272	SP780 H LED18S-6500 PSD W5L112 OD WH	Yes
919515815273	SP780 H LED18S-4000 PSD W5L112 OD WH	Yes
919515815274	SP780X H LED18S-6500 PSD W5L112 OD WH	Yes
919515815275	SP780X H LED18S-4000 PSD W5L112 OD WH	Yes
919515815276	SP780 H LED50S-6500 PSU W5L224 OD WH	No
919515815280	SP780 H LED44S-6500 PSU W5L224 OD WH	No
919515815305	SP780 H LED25S-5700 PSU W5L112 OD WH	No
919515815306	SP780 H LED23S-5700 PSU W5L112 OC WH	No
919515815307	SP780 H LED22S-5700 PSU W5L112 OD WH	No
919515815308	SP780X H LED22S-5700 PSU W5L112 OD WH	No
919515815309	SP780X H LED20S-5700 PSU W5L112 OC WH	No
919515815310	SP780 H LED18S-5700 PSU W5L112 OD WH	No
919515815311	SP780X H LED18S-5700 PSU W5L112 OD WH	No
919515815312	SP780 H LED25S-5700 PSD W5L112 OD WH	Yes
919515815316	SP780X H LED20S-5700 PSD W5L112 OC WH	Yes
919515815899	SP780 H LED25S-6500 PSU W5L112 OD S1 WH	No
919515815901	SP780 H LED25S-5700 PSU W5L112 OD S1 WH	No
919515815902	SP780 H LED25S-4000 PSU W5L112 OD S1 WH	No
919515815903	SP780 H LED23S-6500 PSU W5L112 OC S1 WH	No
919515815904	SP780 H LED23S-5700 PSU W5L112 OC S1 WH	No
919515815905	SP780 H LED23S-4000 PSU W5L112 OC S1 WH	No
919515815906	SP780 H LED22S-6500 PSU W5L112 OD S1 WH	No
919515815907	SP780 H LED22S-5700 PSU W5L112 OD S1 WH	No
919515815908	SP780 H LED22S-4000 PSU W5L112 OD S1 WH	No
919515815909	SP780X H LED22S-6500 PSU W5L112 OD S1 WH	No
919515815910	SP780X H LED22S-5700 PSU W5L112 OD S1 WH	No

Order Code	Full Product Name	Dimmable
919515815911	SP780X H LED22S-4000 PSU W5L112 OD S1 WH	No
919515815912	SP780X H LED20S-6500 PSU W5L112 OC S1 WH	No
919515815913	SP780X H LED20S-5700 PSU W5L112 OC S1 WH	No
919515815914	SP780X H LED20S-4000 PSU W5L112 OC S1 WH	No
919515815915	SP780 H LED50S-6500 PSU W5L224 OD S1 WH	No
919515815916	SP780 H LED50S-5700 PSU W5L224 OD S1 WH	No
919515815917	SP780 H LED50S-4000 PSU W5L224 OD S1 WH	No
919515815918	SP780 H LED46S-6500 PSU W5L224 OC S1 WH	No
919515815919	SP780 H LED46S-5700 PSU W5L224 OC S1 WH	No
919515815920	SP780 H LED46S-4000 PSU W5L224 OC S1 WH	No
919515815921	SP780 H LED44S-6500 PSU W5L224 OD S1 WH	No
919515815922	SP780 H LED44S-5700 PSU W5L224 OD S1 WH	No
919515815923	SP780 H LED44S-4000 PSU W5L224 OD S1 WH	No
919515815924	SP780X H LED44S-6500 PSU W5L224 OD S1 WH	No
919515815925	SP780X H LED44S-5700 PSU W5L224 OD S1 WH	No
919515815926	SP780X H LED44S-4000 PSU W5L224 OD S1 WH	No
919515815927	SP780X H LED40S-6500 PSU W5L224 OC S1 WH	No
919515815928	SP780X H LED40S-5700 PSU W5L224 OC S1 WH	No
919515815929	SP780X H LED40S-4000 PSU W5L224 OC S1 WH	No
919515816241	SP780 HS LED25S-6500 PSU W5L112 OD S1 WH	No
919515816242	SP780 HS LED25S-5700 PSU W5L112 OD S1 WH	No
919515816243	SP780 HS LED25S-4000 PSU W5L112 OD S1 WH	No
919515816244	SP780 HS LED23S-6500 PSU W5L112 OC S1 WH	No
919515816245	SP780 HS LED23S-5700 PSU W5L112 OC S1 WH	No
919515816246	SP780 HS LED23S-4000 PSU W5L112 OC S1 WH	No
919515816247	SP780 HS LED22S-6500 PSU W5L112 OD S1 WH	No
919515816248	SP780 HS LED22S-5700 PSU W5L112 OD S1 WH	No
919515816249	SP780 HS LED22S-4000 PSU W5L112 OD S1 WH	No
919515816250	SP780X HS LED22S-6500 PSU W5L112 OD S1 W	No
919515816251	SP780X HS LED22S-5700 PSU W5L112 OD S1 W	No
919515816252	SP780X HS LED22S-4000 PSU W5L112 OD S1 W	No
919515816253	SP780X HS LED20S-6500 PSU W5L112 OC S1 W	No
919515816254	SP780X HS LED20S-5700 PSU W5L112 OC S1 W	No
919515816255	SP780X HS LED20S-4000 PSU W5L112 OC S1 W	No
919515816256	SP780 HS LED50S-6500 PSU W5L224 OD S1 WH	No
919515816257	SP780 HS LED50S-5700 PSU W5L224 OD S1 WH	No
919515816258	SP780 HS LED50S-4000 PSU W5L224 OD S1 WH	No
919515816259	SP780 HS LED46S-6500 PSU W5L224 OC S1 WH	No
919515816260	SP780 HS LED46S-5700 PSU W5L224 OC S1 WH	No
919515816261	SP780 HS LED46S-4000 PSU W5L224 OC S1 WH	No
919515816262	SP780 HS LED44S-6500 PSU W5L224 OD S1 WH	No
919515816263	SP780 HS LED44S-5700 PSU W5L224 OD S1 WH	No
919515816264	SP780 HS LED44S-4000 PSU W5L224 OD S1 WH	No
919515816265	SP780X HS LED44S-6500 PSU W5L224 OD S1 W	No
919515816266	SP780X HS LED44S-5700 PSU W5L224 OD S1 W	No
919515816267	SP780X HS LED44S-4000 PSU W5L224 OD S1 W	No
919515816268	SP780X HS LED40S-6500 PSU W5L224 OC S1 W	No
919515816269	SP780X HS LED40S-5700 PSU W5L224 OC S1 W	No
919515816270	SP780X HS LED40S-4000 PSU W5L224 OC S1 W	No

Mechanical and Housing

Pureline slim

Order Code	Full Product Name	Optical cover type	Housing
			Color
919515815225	SP780 H LED25S-6500 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815226	SP780 H LED25S-4000 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815227	SP780 H LED23S-6500 PSU W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815228	SP780 H LED23S-4000 PSU W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815252	SP780 H LED22S-6500 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815253	SP780 H LED22S-4000 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815254	SP780X H LED22S-6500 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815255	SP780X H LED22S-4000 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815256	SP780X H LED20S-6500 PSU W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815257	SP780X H LED20S-4000 PSU W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815258	SP780 H LED18S-6500 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815259	SP780 H LED18S-4000 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815260	SP780X H LED18S-6500 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815261	SP780X H LED18S-4000 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815262	SP780 H LED25S-6500 PSD W5L112 OD WH	Polycarbonate Diffuser	White
919515815263	SP780 H LED25S-4000 PSD W5L112 OD WH	Polycarbonate Diffuser	White
919515815264	SP780 H LED23S-6500 PSD W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815265	SP780 H LED23S-4000 PSD W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815266	SP780 H LED22S-6500 PSD W5L112 OD WH	Polycarbonate Diffuser	White
919515815267	SP780 H LED22S-4000 PSD W5L112 OD WH	Polycarbonate Diffuser	White
919515815268	SP780X H LED22S-6500 PSD W5L112 OD WH	Polycarbonate Diffuser	White
919515815269	SP780X H LED22S-4000 PSD W5L112 OD WH	Polycarbonate Diffuser	White
919515815270	SP780X H LED20S-6500 PSD W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815271	SP780X H LED20S-4000 PSD W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815272	SP780 H LED18S-6500 PSD W5L112 OD WH	Polycarbonate Diffuser	White

Order Code	Full Product Name	Optical cover type	Housing
			Color
919515815273	SP780 H LED18S-4000 PSD W5L112 OD WH	Polycarbonate Diffuser	White
919515815274	SP780X H LED18S-6500 PSD W5L112 OD WH	Polycarbonate Diffuser	White
919515815275	SP780X H LED18S-4000 PSD W5L112 OD WH	Polycarbonate Diffuser	White
919515815276	SP780 H LED50S-6500 PSU W5L224 OD WH	Polycarbonate Diffuser	White
919515815280	SP780 H LED44S-6500 PSU W5L224 OD WH	Polycarbonate Diffuser	White
919515815305	SP780 H LED25S-5700 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815306	SP780 H LED23S-5700 PSU W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815307	SP780 H LED22S-5700 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815308	SP780X H LED22S-5700 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815309	SP780X H LED20S-5700 PSU W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815310	SP780 H LED18S-5700 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815311	SP780X H LED18S-5700 PSU W5L112 OD WH	Polycarbonate Diffuser	White
919515815312	SP780 H LED25S-5700 PSD W5L112 OD WH	Polycarbonate Diffuser	White
919515815316	SP780X H LED20S-5700 PSD W5L112 OC WH	Polycarbonate bowl/ cover prismatic	White
919515815899	SP780 H LED25S-6500 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815901	SP780 H LED25S-5700 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815902	SP780 H LED25S-4000 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815903	SP780 H LED23S-6500 PSU W5L112 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815904	SP780 H LED23S-5700 PSU W5L112 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815905	SP780 H LED23S-4000 PSU W5L112 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815906	SP780 H LED22S-6500 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815907	SP780 H LED22S-5700 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815908	SP780 H LED22S-4000 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815909	SP780X H LED22S-6500 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815910	SP780X H LED22S-5700 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016

Pureline slim

Order Code	Full Product Name	Optical cover type	Housing Color
919515815911	SP780X H LED22S-4000 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815912	SP780X H LED20S-6500 PSU W5L112 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815913	SP780X H LED20S-5700 PSU W5L112 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815914	SP780X H LED20S-4000 PSU W5L112 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815915	SP780 H LED50S-6500 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815916	SP780 H LED50S-5700 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815917	SP780 H LED50S-4000 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815918	SP780 H LED46S-6500 PSU W5L224 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815919	SP780 H LED46S-5700 PSU W5L224 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815920	SP780 H LED46S-4000 PSU W5L224 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815921	SP780 H LED44S-6500 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815922	SP780 H LED44S-5700 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815923	SP780 H LED44S-4000 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815924	SP780X H LED44S-6500 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815925	SP780X H LED44S-5700 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815926	SP780X H LED44S-4000 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515815927	SP780X H LED40S-6500 PSU W5L224 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815928	SP780X H LED40S-5700 PSU W5L224 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515815929	SP780X H LED40S-4000 PSU W5L224 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816241	SP780 HS LED25S-6500 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816242	SP780 HS LED25S-5700 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816243	SP780 HS LED25S-4000 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816244	SP780 HS LED23S-6500 PSU W5L112 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816245	SP780 HS LED23S-5700 PSU W5L112 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816246	SP780 HS LED23S-4000 PSU W5L112 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016

Order Code	Full Product Name	Optical cover type	Housing Color
919515816247	SP780 HS LED22S-6500 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816248	SP780 HS LED22S-5700 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816249	SP780 HS LED22S-4000 PSU W5L112 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816250	SP780X HS LED22S-6500 PSU W5L112 OD S1 W	Polycarbonate Diffuser	White RAL9016
919515816251	SP780X HS LED22S-5700 PSU W5L112 OD S1 W	Polycarbonate Diffuser	White RAL9016
919515816252	SP780X HS LED22S-4000 PSU W5L112 OD S1 W	Polycarbonate Diffuser	White RAL9016
919515816253	SP780X HS LED20S-6500 PSU W5L112 OC S1 W	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816254	SP780X HS LED20S-5700 PSU W5L112 OC S1 W	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816255	SP780X HS LED20S-4000 PSU W5L112 OC S1 W	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816256	SP780 HS LED50S-6500 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816257	SP780 HS LED50S-5700 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816258	SP780 HS LED50S-4000 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816259	SP780 HS LED46S-6500 PSU W5L224 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816260	SP780 HS LED46S-5700 PSU W5L224 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816261	SP780 HS LED46S-4000 PSU W5L224 OC S1 WH	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816262	SP780 HS LED44S-6500 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816263	SP780 HS LED44S-5700 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816264	SP780 HS LED44S-4000 PSU W5L224 OD S1 WH	Polycarbonate Diffuser	White RAL9016
919515816265	SP780X HS LED44S-6500 PSU W5L224 OD S1 W	Polycarbonate Diffuser	White RAL9016
919515816266	SP780X HS LED44S-5700 PSU W5L224 OD S1 W	Polycarbonate Diffuser	White RAL9016
919515816267	SP780X HS LED44S-4000 PSU W5L224 OD S1 W	Polycarbonate Diffuser	White RAL9016
919515816268	SP780X HS LED40S-6500 PSU W5L224 OC S1 W	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816269	SP780X HS LED40S-5700 PSU W5L224 OC S1 W	Polycarbonate bowl/ cover prismatic	White RAL9016
919515816270	SP780X HS LED40S-4000 PSU W5L224 OC S1 W	Polycarbonate bowl/ cover prismatic	White RAL9016

Pureline slim

