



Easily upgrade your city's lighting for future-proof energy savings

AluRoad gen2

The AluRoad gen2 family is available in 2 versions, standard AluRoad gen2 and AluRoad gen2 Pro. These are available in 2 sizes, Mini and Medium. Standard AluRoad gen2 as BGP020 Mini and BGP025 Medium, AluRoad gen2 Pro as BGP021 Mini and BGP026 Medium. Standard AluRoad gen2 features a fixed spigot for both post top 0 degrees tilt and side entry with limited negative tilt. AluRoad gen2 Pro is equipped with an adjustable spigot allowing tilt settings in both post top and side entry, positive and negative. AluRoad gen2 enables you to easily upgrade your city's lighting and enjoy the benefits of LED technology, designated to further minimize Total Cost of Investment and Ownership. The family is ideally suited for both new build areas and streets as well as renovation of existing installations. This affordable family not only offers a clean and timeless design to blend in with the environment, but also brings high quality lighting and future proof solutions with significant energy and maintenance savings over a long operational life.

Benefits

- Easy to install in both post top and side entry application.
- Interesting total cost of ownership.
- Limited initial investment.
- Considerable reduction in energy usage and carbon footprint
- further energy savings achievable when using CLO or stand alone dimming such as Dynadim.
- Signify Service tag (unique QR identification) for maintenance, installation, and spare part information.

Features

- Easy to install in both post top and side entry application.
- Interesting total cost of ownership through future proof energy savings.
- Limited initial investment.
- Considerable reduction in energy usage and carbon footprint
- further energy savings achievable when using CLO or standalone dimming such as Dynadim. Certainly, when using the Ultra Efficient versions available within the family.
- Signify Service tag (unique QR identification) for maintenance, installation, and spare part information.

Application

- Road and Street
- Residential
- Walkways
- Industrial area

Versions





AluRoad gen2 Mini Pro product picture



AluRoad gen2 Medium Pro product picture

Dimensional drawing



Product details

AluRoad gen2 Pro Mini top view



AluRoad gen2 Pro Medium bottom view



AluRoad gen2 Pro Mini with Zhaga socket



AluRoad gen2 Pro Mini with OLC



AluRoad gen2 Pro Mini bottom view



AluRoad gen2 Pro tilt indicator



AluRoad gen2 Pro family top view



AluRoad gen2 Pro family top view



AluRoad gen2 Pro interior



AluRoad gen2 Pro family bottom view



AluRoad gen2

Product details



AluRoad gen2 Pro family bottom view



AluRoad gen2 Pro 76mm spigot and tilt indicator



AluRoad gen2 Pro Medium with Zhaga socket



AluRoad gen2 Pro Medium with OLC



AluRoad gen2 Pro toolless opening option



AluRoad gen2 Pro Medium top view

General Information	
Driver included	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	70
Upward light output ratio	0
Mechanical and Housing	
Optical cover type	Flat glass
Housing Color	Gray
Ingress protection code	IP66
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	-

Order Code	Full Product Name	Lamp family code
46995200	BGP021 LED34/740 II DM GR 48/60A	LED34
46996900	BGP021 LED51/740 II DM GR SRT 48/60A	LED51
46997600	BGP021 LED69/740 DM GR SRG10 48/60A	LED69
47001900	BGP021 LED34/740 DW GR SRT 48/60A	LED34
47002600	BGP021 LED51/740 II DW GR SDM10E 48/60A	LED51
47003300	BGP021 LED69/740 II DW GR SRT 48/60A	LED69
47006400	BGP021 LED69/730 II DW GR 48/60A	LED69
47009500	BGP021 LED34/730 DN GR 48/60A	LED34
47010100	BGP021 LED51/730 II DN GR 48/60A	LED51
47011800	BGP021 LED69/730 II DN GR SRT 48/60A	LED69
49921800	BGP021 LED70/740 DM10 GR 48/60A	LED70
76882600	BGP020 LED34/740 II DM CLO-DDF2	LED34
76883300	BGP020 LED51/740 II DM CLO-DDF2	LED51
76884000	BGP020 LED69/740 II DM CLO-DDF2	LED69
76888800	BGP020 LED34/740 II DW CLO-DDF2	LED34
76889500	BGP020 LED51/740 II DW CLO-DDF2	LED51

Order Code	Full Product Name	Lamp family code
76890100	BGP020 LED69/740 II DW CLO-DDF2	LED69
76894900	BGP020 LED34/740 II DN CLO-DDF2	LED34
76895600	BGP020 LED51/740 II DN CLO-DDF2	LED51
76896300	BGP020 LED69/740 II DN CLO-DDF2	LED69
76900700	BGP020 LED34/730 II DM CLO-DDF2	LED34
76901400	BGP020 LED51/730 II DM CLO-DDF2	LED51
76902100	BGP020 LED69/730 II DM CLO-DDF2	LED69
76906900	BGP020 LED34/730 II DW CLO-DDF2	LED34
76907600	BGP020 LED51/730 II DW CLO-DDF2	LED51
76908300	BGP020 LED69/730 II DW CLO-DDF2	LED69
76912000	BGP020 LED34/730 II DN CLO-DDF2	LED34
76913700	BGP020 LED51/730 II DN CLO-DDF2	LED51
76914400	BGP020 LED69/730 II DN CLO-DDF2	LED69
46998300	BGP026 LED91/740 II DM GR SRT 48/60A	LED91
46999000	BGP026 LED113/740 II DM GR 48/60A	LED113
47000200	BGP026 LED147/740 II DM GR SDM10E 48/60A	LED147
47004000	BGP026 LED91/740 II DW GR 48/60A	LED91
47005700	BGP026 LED113/740 II DW GR SRT 48/60A	LED113
47007100	BGP026 LED113/730 DW GR SRG10 48/60A	LED113
47008800	BGP026 LED147/730 II DW GR 48/60A	LED147
47012500	BGP026 LED113/730 II DN GR 48/60A	LED113
47013200	BGP026 LED147/730 II DN GR 48/60A	LED147
49922500	BGP026 LED120/740 DM10 GR 48/60A	LED120
76885700	BGP025 LED91/740 II DM CLO-DDF2	LED91
76886400	BGP025 LED113/740 II DM CLO-DDF2	LED113
76887100	BGP025 LED147/740 II DM CLO-DDF2	LED147
76891800	BGP025 LED91/740 II DW CLO-DDF2	LED91
76892500	BGP025 LED113/740 II DW CLO-DDF2	LED113
76893200	BGP025 LED147/740 II DW CLO-DDF2	LED147
76897000	BGP025 LED91/740 II DN CLO-DDF2	LED91
76898700	BGP025 LED113/740 II DN CLO-DDF2	LED113
76899400	BGP025 LED147/740 II DN CLO-DDF2	LED147
76903800	BGP025 LED91/730 II DM CLO-DDF2	LED91
76904500	BGP025 LED113/730 II DM CLO-DDF2	LED113
76905200	BGP025 LED147/730 II DM CLO-DDF2	LED147
76909000	BGP025 LED91/730 II DW CLO-DDF2	LED91
76910600	BGP025 LED113/730 II DW CLO-DDF2	LED113
76911300	BGP025 LED147/730 II DW CLO-DDF2	LED147
76915100	BGP025 LED91/730 II DN CLO-DDF2	LED91
76916800	BGP025 LED113/730 II DN CLO-DDF2	LED113
76917500	BGP025 LED147/730 II DN CLO-DDF2	LED147

Light Technical (1/2)

		Luminaire	Light	Correlated				Luminaire	Light	Correlated	
Full Product		light beam	source	Temperature	Luminous			light beam	source	Temperature	Luminous
Order Code	Name	spread	color	(Nom)	Flux	Order Code	Name	spread	color	(Nom)	Flux
46995200	BGP021	5° x 55° x 150°	740	4000 K	2,992 lm	46996900	BGP021	5° x 55° x 150°	740	4000 K	4,350 lm
	LED34/740 II DM		neutral				LED51/740 II DM		neutral		
	GR 48/60A		white				GR SRT 48/60A		white		

		Luminaire	Light	Correlated	
Full Product		light beam	source	Color	Luminous
Order Code	Name	spread	color	Temperature (Nom)	Flux
46997600	BGP021	5° x 55° x 150°	740	4000 K	5,848 lm
	LED69/740 DM		neutral		
	GR SRG10		white		
	48/60A				
47001900	BGP021	23° x 59° x 148°	740	4000 K	2,992 lm
	LED34/740 DW		neutral		
	GR SRT 48/60A		white		
47002600	BGP021	23° x 59° x 148°	740	4000 K	4,350 lm
	LED51/740 II DW		neutral		
	GR SDM10E		white		
	48/60A				
47003300	BGP021	23° x 59° x 148°	740	4000 K	5,848 lm
	LED69/740 II DW		neutral		
	GR SRT 48/60A		white		
47006400	BGP021	23° x 59° x 148°	730 warm	3000 K	5,848 lm
	LED69/730 II DW		white		
	GR 48/60A				
47009500	BGP021	23° x 44° x 152°	730 warm	3000 K	3,026 lm
	LED34/730 DN		white		
	GR 48/60A				
47010100	BGP021	23° x 44° x 152°	730 warm	3000 K	4,400 lm
	LED51/730 II DN		white		
	GR 48/60A				
47011800	BGP021	23° x 44° x 152°	730 warm	3000 K	5,916 lm
	LED69/730 II DN		white		
	GR SRT 48/60A				
49921800	BGP021	5° x 55° x 150°	740	4000 K	5,880 lm
	LED70/740 DM10		neutral		
	GR 48/60A		white		
76882600	BGP020	5° x 55° x 150°	740	4000 K	2,937 lm
	LED34/740 II DM		neutral		
	CLO-DDF2		white		
76883300	BGP020	5° x 55° x 150°	740	4000 K	4,312 lm
	LED51/740 II DM		neutral		
	CLO-DDF2		white		
76884000	BGP020	5° x 55° x 150°	740	4000 K	5,742 lm
	LED69/740 II DM		neutral		
	CLO-DDF2		white		
76888800	BGP020	23° x 59° x 148°	740	4000 K	2,904 lm
	LED34/740 II DW		neutral		
	CLO-DDF2		white		
76889500	BGP020	23° x 59° x 148°	740	4000 K	4,263 lm
	LED51/740 II DW		neutral		
	CLO-DDF2		white		
76890100	BGP020	23° x 59° x 148°	740	4000 K	5,742 lm
	LED69/740 II DW		neutral		
	CLO-DDF2		white		

		Luminaire	Light	Correlated	
Full Product		light beam	source	Color	Luminous
Order Code	Name	spread	color	Temperature (Nom)	Flux
76894900	BGP020	23° x 44° x 152°	740	4000 K	2,937 lm
	LED34/740 II DN		neutral		
	CLO-DDF2		white		
76895600	BGP020	23° x 44° x 152°	740	4000 K	4,312 lm
	LED51/740 II DN		neutral		
	CLO-DDF2		white		
76896300	BGP020	23° x 44° x 152°	740	4000 K	5,742 lm
	LED69/740 II DN		neutral		
	CLO-DDF2		white		
76900700	BGP020	5° x 55° x 150°	730 warm	3000 K	2,937 lm
	LED34/730 II DM		white		
	CLO-DDF2				
76901400	BGP020	5° x 55° x 150°	730 warm	3000 K	4,312 lm
	LED51/730 II DM		white		
	CLO-DDF2				
76902100	BGP020	5° x 55° x 150°	730 warm	3000 K	5,568 lm
	LED69/730 II DM		white		
	CLO-DDF2				
76906900	BGP020	23° x 59° x 148°	730 warm	3000 K	2,904 lm
	LED34/730 II DW		white		
	CLO-DDF2				
76907600	BGP020	23° x 59° x 148°	730 warm	3000 K	4,263 lm
	LED51/730 II DW		white		
	CLO-DDF2				
76908300	BGP020	23° x 59° x 148°	730 warm	3000 K	5,568 lm
	LED69/730 II DW		white		
	CLO-DDF2				
76912000	BGP020	23° x 44° x 152°	730 warm	3000 K	2,937 lm
	LED34/730 II DN		white		
	CLO-DDF2				
76913700	BGP020	23° x 44° x 152°	730 warm	3000 K	4,312 lm
	LED51/730 II DN		white		
	CLO-DDF2				
76914400	BGP020	23° x 44° x 152°	730 warm	3000 K	5,568 lm
	LED69/730 II DN		white		
	CLO-DDF2				
46998300	BGP026	5° x 55° x 150°	740	4000 K	7,740 lm
	LED91/740 II DM		neutral		
	GR SRT 48/60A		white		
46999000	BGP026	5° x 55° x 150°	740	4000 K	9,775 lm
	LED113/740 II DM		neutral		
	GR 48/60A		white		
47000200	BGP026	5° x 55° x 150°	740	4000 K	12,325 lm
	LED147/740 II DM		neutral		
	GR SDM10E		white		
47004000	BGP026	23° x 59° x 148°	740	4000 K	7,740 lm
	LED91/740 II DW		neutral		
	GR 48/60A		white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)		Luminous Flux
47005700	BGP026	23° x 59° x 148°	740	4000 K		9,890 lm
	LED113/740 II DW		neutral			
	GR SRT 48/60A		white			
47007100	BGP026	23° x 59° x 148°	730 warm	3000 K		9,890 lm
	LED113/730 DW		white			
	GR SRG10 48/60A					
47008800	BGP026	23° x 59° x 148°	730 warm	3000 K		12,325 lm
	LED147/730 II DW		white			
	GR 48/60A					
47012500	BGP026	23° x 44° x 152°	730 warm	3000 K		9,890 lm
	LED113/730 II DN		white			
	GR 48/60A					
47013200	BGP026	23° x 44° x 152°	730 warm	3000 K		12,325 lm
	LED147/730 II DN		white			
	GR 48/60A					
49922500	BGP026	5° x 55° x 150°	740	4000 K		10,320 lm
	LED120/740		neutral			
	DM10 GR 48/60A		white			
76885700	BGP025	5° x 55° x 150°	740	4000 K		7,482 lm
	LED91/740 II DM		neutral			
	CLO-DDF2		white			
76886400	BGP025	5° x 55° x 150°	740	4000 K		9,030 lm
	LED113/740 II DM		neutral			
	CLO-DDF2		white			
76887100	BGP025	5° x 55° x 150°	740	4000 K		11,475 lm
	LED147/740 II DM		neutral			
	CLO-DDF2		white			
76891800	BGP025	23° x 59° x 148°	740	4000 K		7,482 lm
	LED91/740 II DW		neutral			
	CLO-DDF2		white			
76892500	BGP025	23° x 59° x 148°	740	4000 K		9,030 lm
	LED113/740 II DW		neutral			
	CLO-DDF2		white			
76893200	BGP025	23° x 59° x 148°	740	4000 K		11,475 lm
	LED147/740 II DW		neutral			
	CLO-DDF2		white			

Light Technical (2/2)

Order Code	Full Product Name	Optic type outdoor
46995200	BGP021 LED34/740 II DM GR 48/60A	Distribution medium
46996900	BGP021 LED51/740 II DM GR SRT 48/60A	Distribution medium
46997600	BGP021 LED69/740 DM GR SRG10 48/60A	Distribution medium
47001900	BGP021 LED34/740 DW GR SRT 48/60A	Distribution wide
47002600	BGP021 LED51/740 II DW GR SDM10E 48/60A	Distribution wide
47003300	BGP021 LED69/740 II DW GR SRT 48/60A	Distribution wide
47006400	BGP021 LED69/730 II DW GR 48/60A	Distribution wide
47009500	BGP021 LED34/730 DN GR 48/60A	Distribution narrow

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)		Luminous Flux
76897000	BGP025	23° x 44° x 152°	740	4000 K		7,568 lm
	LED91/740 II DN		neutral			
	CLO-DDF2		white			
76898700	BGP025	23° x 44° x 152°	740	4000 K		9,135 lm
	LED113/740 II DN		neutral			
	CLO-DDF2		white			
76899400	BGP025	23° x 44° x 152°	740	4000 K		11,610 lm
	LED147/740 II DN		neutral			
	CLO-DDF2		white			
76903800	BGP025	5° x 55° x 150°	730 warm	3000 K		7,482 lm
	LED91/730 II DM		white			
	CLO-DDF2					
76904500	BGP025	5° x 55° x 150°	730 warm	3000 K		9,030 lm
	LED113/730 II DM		white			
	CLO-DDF2					
76905200	BGP025	5° x 55° x 150°	730 warm	3000 K		11,475 lm
	LED147/730 II DM		white			
	CLO-DDF2					
76909000	BGP025	23° x 59° x 148°	730 warm	3000 K		7,482 lm
	LED91/730 II DW		white			
	CLO-DDF2					
76910600	BGP025	23° x 59° x 148°	730 warm	3000 K		9,030 lm
	LED113/730 II DW		white			
	CLO-DDF2					
76911300	BGP025	23° x 59° x 148°	730 warm	3000 K		11,475 lm
	LED147/730 II DW		white			
	CLO-DDF2					
76915100	BGP025	23° x 44° x 152°	730 warm	3000 K		7,568 lm
	LED91/730 II DN		white			
	CLO-DDF2					
76916800	BGP025	23° x 44° x 152°	730 warm	3000 K		9,135 lm
	LED113/730 II DN		white			
	CLO-DDF2					
76917500	BGP025	23° x 44° x 152°	730 warm	3000 K		11,610 lm
	LED147/730 II DN		white			
	CLO-DDF2					

Order Code	Full Product Name	Optic type outdoor
76890100	BGP020 LED69/740 II DW CLO-DDF2	Distribution wide
76894900	BGP020 LED34/740 II DN CLO-DDF2	Distribution narrow
76895600	BGP020 LED51/740 II DN CLO-DDF2	Distribution narrow
76896300	BGP020 LED69/740 II DN CLO-DDF2	Distribution narrow
76900700	BGP020 LED34/730 II DM CLO-DDF2	Distribution medium
76901400	BGP020 LED51/730 II DM CLO-DDF2	Distribution medium
76902100	BGP020 LED69/730 II DM CLO-DDF2	Distribution medium
76906900	BGP020 LED34/730 II DW CLO-DDF2	Distribution wide
76907600	BGP020 LED51/730 II DW CLO-DDF2	Distribution wide
76908300	BGP020 LED69/730 II DW CLO-DDF2	Distribution wide
76912000	BGP020 LED34/730 II DN CLO-DDF2	Distribution narrow
76913700	BGP020 LED51/730 II DN CLO-DDF2	Distribution narrow
76914400	BGP020 LED69/730 II DN CLO-DDF2	Distribution narrow
46998300	BGP026 LED91/740 II DM GR SRT 48/60A	Distribution medium
46999000	BGP026 LED113/740 II DM GR 48/60A	Distribution medium
47000200	BGP026 LED147/740 II DM GR SDM10E 48/60A	Distribution medium
47004000	BGP026 LED91/740 II DW GR 48/60A	Distribution wide
47005700	BGP026 LED113/740 II DW GR SRT 48/60A	Distribution wide
47007100	BGP026 LED113/730 DW GR SRG10 48/60A	Distribution wide
47008800	BGP026 LED147/730 II DW GR 48/60A	Distribution wide
47012500	BGP026 LED113/730 II DN GR 48/60A	Distribution narrow

Order Code	Full Product Name	Optic type outdoor
47013200	BGP026 LED147/730 II DN GR 48/60A	Distribution narrow
49922500	BGP026 LED120/740 DM10 GR 48/60A	Distribution wide
76885700	BGP025 LED91/740 II DM CLO-DDF2	Distribution medium
76886400	BGP025 LED113/740 II DM CLO-DDF2	Distribution medium
76887100	BGP025 LED147/740 II DM CLO-DDF2	Distribution medium
76891800	BGP025 LED91/740 II DW CLO-DDF2	Distribution wide
76892500	BGP025 LED113/740 II DW CLO-DDF2	Distribution wide
76893200	BGP025 LED147/740 II DW CLO-DDF2	Distribution wide
76897000	BGP025 LED91/740 II DN CLO-DDF2	Distribution narrow
76898700	BGP025 LED113/740 II DN CLO-DDF2	Distribution narrow
76899400	BGP025 LED147/740 II DN CLO-DDF2	Distribution narrow
76903800	BGP025 LED91/730 II DM CLO-DDF2	Distribution medium
76904500	BGP025 LED113/730 II DM CLO-DDF2	Distribution medium
76905200	BGP025 LED147/730 II DM CLO-DDF2	Distribution medium
76909000	BGP025 LED91/730 II DW CLO-DDF2	Distribution wide
76910600	BGP025 LED113/730 II DW CLO-DDF2	Distribution wide
76911300	BGP025 LED147/730 II DW CLO-DDF2	Distribution wide
76915100	BGP025 LED91/730 II DN CLO-DDF2	Distribution narrow
76916800	BGP025 LED113/730 II DN CLO-DDF2	Distribution narrow
76917500	BGP025 LED147/730 II DN CLO-DDF2	Distribution narrow

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
46995200	BGP021 LED34/740 II DM GR 48/60A	19.4 W	Surge protection level until 6 kV differential mode and 8 kV common mode
46996900	BGP021 LED51/740 II DM GR SRT 48/60A	28 W	Surge protection level until 6 kV differential mode and 8 kV common mode
46997600	BGP021 LED69/740 DM GR SRG10 48/60A	39 W	Surge protection level until 10 kV differential mode and 10 kV common mode
47001900	BGP021 LED34/740 DW GR SRT 48/60A	19 W	Surge protection level until 6 kV differential mode and 8 kV common mode
47002600	BGP021 LED51/740 II DW GR SDM10E 48/60A	28 W	Surge protection level until 6 kV differential mode and 10 kV common mode
47003300	BGP021 LED69/740 II DW GR SRT 48/60A	38.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
47006400	BGP021 LED69/730 II DW GR 48/60A	41 W	Surge protection level until 6 kV differential mode and 8 kV common mode
47009500	BGP021 LED34/730 DN GR 48/60A	20.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
47010100	BGP021 LED51/730 II DN GR 48/60A	29.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
47011800	BGP021 LED69/730 II DN GR SRT 48/60A	40.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
49921800	BGP021 LED70/740 DM10 GR 48/60A	39.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76882600	BGP020 LED34/740 II DM CLO-DDF2	19 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76883300	BGP020 LED51/740 II DM CLO-DDF2	28.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76884000	BGP020 LED69/740 II DM CLO-DDF2	39 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76888800	BGP020 LED34/740 II DW CLO-DDF2	19 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76889500	BGP020 LED51/740 II DW CLO-DDF2	28.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
76890100	BGP020 LED69/740 II DW CLO-DDF2	39 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76894900	BGP020 LED34/740 II DN CLO-DDF2	19 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76895600	BGP020 LED51/740 II DN CLO-DDF2	28.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76896300	BGP020 LED69/740 II DN CLO-DDF2	39 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76900700	BGP020 LED34/730 II DM CLO-DDF2	20 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76901400	BGP020 LED51/730 II DM CLO-DDF2	30 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76902100	BGP020 LED69/730 II DM CLO-DDF2	41 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76906900	BGP020 LED34/730 II DW CLO-DDF2	20 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76907600	BGP020 LED51/730 II DW CLO-DDF2	30 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76908300	BGP020 LED69/730 II DW CLO-DDF2	41 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76912000	BGP020 LED34/730 II DN CLO-DDF2	20 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76913700	BGP020 LED51/730 II DN CLO-DDF2	30 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76914400	BGP020 LED69/730 II DN CLO-DDF2	41 W	Surge protection level until 6 kV differential mode and 8 kV common mode
46998300	BGP026 LED91/740 II DM GR SRT 48/60A	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
46999000	BGP026 LED113/740 II DM GR 48/60A	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
47000200	BGP026 LED147/740 II DM GR SDM10E 48/60A	81 W	Surge protection level until 6 kV differential mode and 10 kV common mode
47004000	BGP026 LED91/740 II DW GR 48/60A	49 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
47005700	BGP026 LED113/740 II DW GR SRT 48/60A	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
47007100	BGP026 LED113/730 DW GR SRG10 48/60A	64 W	Surge protection level until 10 kV differential mode and 10 kV common mode
47008800	BGP026 LED147/730 II DW GR 48/60A	85 W	Surge protection level until 6 kV differential mode and 8 kV common mode
47012500	BGP026 LED113/730 II DN GR 48/60A	64 W	Surge protection level until 6 kV differential mode and 8 kV common mode
47013200	BGP026 LED147/730 II DN GR 48/60A	85 W	Surge protection level until 6 kV differential mode and 8 kV common mode
49922500	BGP026 LED120/740 DM10 GR 48/60A	65 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76885700	BGP025 LED91/740 II DM CLO-DDF2	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76886400	BGP025 LED113/740 II DM CLO-DDF2	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76887100	BGP025 LED147/740 II DM CLO-DDF2	81 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76891800	BGP025 LED91/740 II DW CLO-DDF2	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76892500	BGP025 LED113/740 II DW CLO-DDF2	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76893200	BGP025 LED147/740 II DW CLO-DDF2	81 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76897000	BGP025 LED91/740 II DN CLO-DDF2	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76898700	BGP025 LED113/740 II DN CLO-DDF2	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76899400	BGP025 LED147/740 II DN CLO-DDF2	81 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76903800	BGP025 LED91/730 II DM CLO-DDF2	52 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76904500	BGP025 LED113/730 II DM CLO-DDF2	64 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
76905200	BGP025 LED147/730 II DM CLO-DDF2	85 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76909000	BGP025 LED91/730 II DW CLO-DDF2	52 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76910600	BGP025 LED113/730 II DW CLO-DDF2	64 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76911300	BGP025 LED147/730 II DW CLO-DDF2	85 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
76915100	BGP025 LED91/730 II DN CLO-DDF2	52 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76916800	BGP025 LED113/730 II DN CLO-DDF2	64 W	Surge protection level until 6 kV differential mode and 8 kV common mode
76917500	BGP025 LED147/730 II DN CLO-DDF2	85 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable
46995200	BGP021 LED34/740 II DM GR 48/60A	No
46996900	BGP021 LED51/740 II DM GR SRT 48/60A	Yes
46997600	BGP021 LED69/740 DM GR SRG10 48/60A	No
47001900	BGP021 LED34/740 DW GR SRT 48/60A	Yes
47002600	BGP021 LED51/740 II DW GR SDM10E 48/60A	No
47003300	BGP021 LED69/740 II DW GR SRT 48/60A	Yes
47006400	BGP021 LED69/730 II DW GR 48/60A	No
47009500	BGP021 LED34/730 DN GR 48/60A	No
47010100	BGP021 LED51/730 II DN GR 48/60A	No
47011800	BGP021 LED69/730 II DN GR SRT 48/60A	Yes
49921800	BGP021 LED70/740 DM10 GR 48/60A	Yes
76882600	BGP020 LED34/740 II DM CLO-DDF2	Yes
76883300	BGP020 LED51/740 II DM CLO-DDF2	Yes
76884000	BGP020 LED69/740 II DM CLO-DDF2	Yes
76888800	BGP020 LED34/740 II DW CLO-DDF2	Yes
76889500	BGP020 LED51/740 II DW CLO-DDF2	Yes
76890100	BGP020 LED69/740 II DW CLO-DDF2	Yes
76894900	BGP020 LED34/740 II DN CLO-DDF2	Yes
76895600	BGP020 LED51/740 II DN CLO-DDF2	Yes
76896300	BGP020 LED69/740 II DN CLO-DDF2	Yes
76900700	BGP020 LED34/730 II DM CLO-DDF2	Yes
76901400	BGP020 LED51/730 II DM CLO-DDF2	Yes
76902100	BGP020 LED69/730 II DM CLO-DDF2	Yes
76906900	BGP020 LED34/730 II DW CLO-DDF2	Yes
76907600	BGP020 LED51/730 II DW CLO-DDF2	Yes
76908300	BGP020 LED69/730 II DW CLO-DDF2	Yes
76912000	BGP020 LED34/730 II DN CLO-DDF2	Yes
76913700	BGP020 LED51/730 II DN CLO-DDF2	Yes
76914400	BGP020 LED69/730 II DN CLO-DDF2	Yes

Order Code	Full Product Name	Dimmable
46998300	BGP026 LED91/740 II DM GR SRT 48/60A	Yes
46999000	BGP026 LED113/740 II DM GR 48/60A	No
47000200	BGP026 LED147/740 II DM GR SDM10E 48/60A	No
47004000	BGP026 LED91/740 II DW GR 48/60A	No
47005700	BGP026 LED113/740 II DW GR SRT 48/60A	Yes
47007100	BGP026 LED113/730 DW GR SRG10 48/60A	No
47008800	BGP026 LED147/730 II DW GR 48/60A	No
47012500	BGP026 LED113/730 II DN GR 48/60A	No
47013200	BGP026 LED147/730 II DN GR 48/60A	No
49922500	BGP026 LED120/740 DM10 GR 48/60A	Yes
76885700	BGP025 LED91/740 II DM CLO-DDF2	Yes
76886400	BGP025 LED113/740 II DM CLO-DDF2	Yes
76887100	BGP025 LED147/740 II DM CLO-DDF2	Yes
76891800	BGP025 LED91/740 II DW CLO-DDF2	Yes
76892500	BGP025 LED113/740 II DW CLO-DDF2	Yes
76893200	BGP025 LED147/740 II DW CLO-DDF2	Yes
76897000	BGP025 LED91/740 II DN CLO-DDF2	Yes
76898700	BGP025 LED113/740 II DN CLO-DDF2	Yes
76899400	BGP025 LED147/740 II DN CLO-DDF2	Yes
76903800	BGP025 LED91/730 II DM CLO-DDF2	Yes
76904500	BGP025 LED113/730 II DM CLO-DDF2	Yes
76905200	BGP025 LED147/730 II DM CLO-DDF2	Yes
76909000	BGP025 LED91/730 II DW CLO-DDF2	Yes
76910600	BGP025 LED113/730 II DW CLO-DDF2	Yes
76911300	BGP025 LED147/730 II DW CLO-DDF2	Yes
76915100	BGP025 LED91/730 II DN CLO-DDF2	Yes
76916800	BGP025 LED113/730 II DN CLO-DDF2	Yes
76917500	BGP025 LED147/730 II DN CLO-DDF2	Yes

Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code
46995200	BGP021 LED34/740 II DM GR 48/60A	IK09
46996900	BGP021 LED51/740 II DM GR SRT 48/60A	IK09
46997600	BGP021 LED69/740 DM GR SRG10 48/60A	IK09
47001900	BGP021 LED34/740 DW GR SRT 48/60A	IK09
47002600	BGP021 LED51/740 II DW GR SDM10E 48/60A	IK09
47003300	BGP021 LED69/740 II DW GR SRT 48/60A	IK09
47006400	BGP021 LED69/730 II DW GR 48/60A	IK09
47009500	BGP021 LED34/730 DN GR 48/60A	IK09
47010100	BGP021 LED51/730 II DN GR 48/60A	IK09
47011800	BGP021 LED69/730 II DN GR SRT 48/60A	IK09
49921800	BGP021 LED70/740 DM10 GR 48/60A	IK09
76882600	BGP020 LED34/740 II DM CLO-DDF2	IK08
76883300	BGP020 LED51/740 II DM CLO-DDF2	IK08
76884000	BGP020 LED69/740 II DM CLO-DDF2	IK08
76888800	BGP020 LED34/740 II DW CLO-DDF2	IK08
76889500	BGP020 LED51/740 II DW CLO-DDF2	IK08
76890100	BGP020 LED69/740 II DW CLO-DDF2	IK08
76894900	BGP020 LED34/740 II DN CLO-DDF2	IK08
76895600	BGP020 LED51/740 II DN CLO-DDF2	IK08
76896300	BGP020 LED69/740 II DN CLO-DDF2	IK08
76900700	BGP020 LED34/730 II DM CLO-DDF2	IK08
76901400	BGP020 LED51/730 II DM CLO-DDF2	IK08
76902100	BGP020 LED69/730 II DM CLO-DDF2	IK08
76906900	BGP020 LED34/730 II DW CLO-DDF2	IK08
76907600	BGP020 LED51/730 II DW CLO-DDF2	IK08
76908300	BGP020 LED69/730 II DW CLO-DDF2	IK08
76912000	BGP020 LED34/730 II DN CLO-DDF2	IK08
76913700	BGP020 LED51/730 II DN CLO-DDF2	IK08
76914400	BGP020 LED69/730 II DN CLO-DDF2	IK08

Product Data

Order Code	Full Product Name	Product family code
46995200	BGP021 LED34/740 II DM GR 48/60A	BGP021
46996900	BGP021 LED51/740 II DM GR SRT 48/60A	BGP021
46997600	BGP021 LED69/740 DM GR SRG10 48/60A	BGP021
47001900	BGP021 LED34/740 DW GR SRT 48/60A	BGP021
47002600	BGP021 LED51/740 II DW GR SDM10E 48/60A	BGP021
47003300	BGP021 LED69/740 II DW GR SRT 48/60A	BGP021
47006400	BGP021 LED69/730 II DW GR 48/60A	BGP021
47009500	BGP021 LED34/730 DN GR 48/60A	BGP021
47010100	BGP021 LED51/730 II DN GR 48/60A	BGP021
47011800	BGP021 LED69/730 II DN GR SRT 48/60A	BGP021
49921800	BGP021 LED70/740 DM10 GR 48/60A	BGP021
76882600	BGP020 LED34/740 II DM CLO-DDF2	BGP020
76883300	BGP020 LED51/740 II DM CLO-DDF2	BGP020
76884000	BGP020 LED69/740 II DM CLO-DDF2	BGP020
76888800	BGP020 LED34/740 II DW CLO-DDF2	BGP020
76889500	BGP020 LED51/740 II DW CLO-DDF2	BGP020
76890100	BGP020 LED69/740 II DW CLO-DDF2	BGP020
76894900	BGP020 LED34/740 II DN CLO-DDF2	BGP020

Order Code	Full Product Name	Mech. impact protection code
46998300	BGP026 LED91/740 II DM GR SRT 48/60A	IK09
46999000	BGP026 LED113/740 II DM GR 48/60A	IK09
47000200	BGP026 LED147/740 II DM GR SDM10E 48/60A	IK09
47004000	BGP026 LED91/740 II DW GR 48/60A	IK09
47005700	BGP026 LED113/740 II DW GR SRT 48/60A	IK09
47007100	BGP026 LED113/730 DW GR SRG10 48/60A	IK09
47008800	BGP026 LED147/730 II DW GR 48/60A	IK09
47012500	BGP026 LED113/730 II DN GR 48/60A	IK09
47013200	BGP026 LED147/730 II DN GR 48/60A	IK09
49922500	BGP026 LED120/740 DM10 GR 48/60A	IK09
76885700	BGP025 LED91/740 II DM CLO-DDF2	IK08
76886400	BGP025 LED113/740 II DM CLO-DDF2	IK08
76887100	BGP025 LED147/740 II DM CLO-DDF2	IK08
76891800	BGP025 LED91/740 II DW CLO-DDF2	IK08
76892500	BGP025 LED113/740 II DW CLO-DDF2	IK08
76893200	BGP025 LED147/740 II DW CLO-DDF2	IK08
76897000	BGP025 LED91/740 II DN CLO-DDF2	IK08
76898700	BGP025 LED113/740 II DN CLO-DDF2	IK08
76899400	BGP025 LED147/740 II DN CLO-DDF2	IK08
76903800	BGP025 LED91/730 II DM CLO-DDF2	IK08
76904500	BGP025 LED113/730 II DM CLO-DDF2	IK08
76905200	BGP025 LED147/730 II DM CLO-DDF2	IK08
76909000	BGP025 LED91/730 II DW CLO-DDF2	IK08
76910600	BGP025 LED113/730 II DW CLO-DDF2	IK08
76911300	BGP025 LED147/730 II DW CLO-DDF2	IK08
76915100	BGP025 LED91/730 II DN CLO-DDF2	IK08
76916800	BGP025 LED113/730 II DN CLO-DDF2	IK08
76917500	BGP025 LED147/730 II DN CLO-DDF2	IK08

Order Code	Full Product Name	Product family code
47012500	BGP026 LED113/730 II DN GR 48/60A	BGP026
47013200	BGP026 LED147/730 II DN GR 48/60A	BGP026
49922500	BGP026 LED120/740 DM10 GR 48/60A	BGP026
76885700	BGP025 LED91/740 II DM CLO-DDF2	BGP025
76886400	BGP025 LED113/740 II DM CLO-DDF2	BGP025
76887100	BGP025 LED147/740 II DM CLO-DDF2	BGP025
76891800	BGP025 LED91/740 II DW CLO-DDF2	BGP025
76892500	BGP025 LED113/740 II DW CLO-DDF2	BGP025
76893200	BGP025 LED147/740 II DW CLO-DDF2	BGP025
76897000	BGP025 LED91/740 II DN CLO-DDF2	BGP025
76898700	BGP025 LED113/740 II DN CLO-DDF2	BGP025

Order Code	Full Product Name	Product family code
76899400	BGP025 LED147/740 II DN CLO-DDF2	BGP025
76903800	BGP025 LED91/730 II DM CLO-DDF2	BGP025
76904500	BGP025 LED113/730 II DM CLO-DDF2	BGP025
76905200	BGP025 LED147/730 II DM CLO-DDF2	BGP025
76909000	BGP025 LED91/730 II DW CLO-DDF2	BGP025
76910600	BGP025 LED113/730 II DW CLO-DDF2	BGP025
76911300	BGP025 LED147/730 II DW CLO-DDF2	-
76915100	BGP025 LED91/730 II DN CLO-DDF2	BGP025
76916800	BGP025 LED113/730 II DN CLO-DDF2	BGP025
76917500	BGP025 LED147/730 II DN CLO-DDF2	BGP025

