



# All-in-one Solar street light range up-to 18000 lumens, suitable for high ambient temperature applications

## GreenVision All-in-one Solar Street Light

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and MPPT charge controller built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting. Adjustable LED module for better distribution of light when required.

### Benefits

- Brings light to areas without access to electric grid
- Preserves landscape as no trenching for cabling required
- Sturdy construction
- Suitable for high ambient temperature operation
- Saves energy, environment friendly

# GreenVision All-in-one Solar Street Light

## Features

- High luminous efficacy of > 180 lm/Watt to maximize battery performance
- MPPT charge controller for maximum efficiency
- Specially designed pole mounting bracket with adjustable tilt angles, which can also be used in post top & lateral mounting positions
- 3G compliant pressure die-cast aluminum housing for sturdiness and excellent heat dissipation
- Factory set dimming profile along with microwave sensor for run time maximization. Dimming can be configured at site with the help of configuration remote controller.
- Self diagnostic feature with LED Indicators.

## Application

- Road and streetlighting
- Perimeter lighting
- Parks, pedestrian paths, cycle tracks
- Shopping centers, plazas
- Industries, office and school campuses
- Sub-urban areas

## Versions

|                                                                                     |                                                                                     |                                                                                      |                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|   |   |   |  |
| GreenVision SolarAIO-BRP715 LED90                                                   | Solar Street Lights                                                                 | Solar Street Lights                                                                  | Solar Street Lights                                                                   |
|  |  |  |  |
| GreenVision SolarAIO-BRP715 LED50                                                   | Solar Street Lights                                                                 | GreenVision SolarAIO-BRP715 LED120                                                   | Solar Street Lights                                                                   |

# GreenVision All-in-one Solar Street Light

## Versions



GreenVision SolarAIO-BRP715 LED180

Solar Street Lights



Solar Street Lights

GreenVision SolarAIO-BRP715 LED70


## Solar Street Lights

## Dimensional drawing


BRP715 LED90 CW Solar



BRP715 LED180 CW Solar





BRP715 LED70 CW Solar









GreenVision All-in-one Solar Street Light

Dimensional drawing




BRP715 LED50 CW Solar





# GreenVision All-in-one Solar Street Light

## Dimensional drawing



BRP715 LED120 CW Solar



## Product details



Solar Street Lights



Solar Street Lights



Solar Street Lights



Solar Street Lights



Solar Street Lights



Solar Street Lights

GreenVision All-in-one Solar Street Light

Product details



| Light Technical                       |                  |
|---------------------------------------|------------------|
| Correlated Color Temperature (Nom)    | 5700 K           |
| Color rendering index (CRI)           | >70              |
| Operating and Electrical              |                  |
| Battery charging & discharging cycles | 2000             |
| Charge controller type                | MPPT             |
| Panel type                            | Mono crystalline |
| Controls and Dimming                  |                  |
| Dimmable                              | Yes              |
| Configurability                       | Configurable     |
| Mechanical and Housing                |                  |
| Battery location                      | Inbuilt          |
| Housing Color                         | Black            |
| Ingress protection code               | IP65             |
| Overall height                        | 133 mm           |

Operating and Electrical (1/2)

| Order Code   | Full Product Name                       | Battery<br>ampere hour | Battery type               | Battery<br>voltage | Cable<br>connection kit |
|--------------|-----------------------------------------|------------------------|----------------------------|--------------------|-------------------------|
| 911401625708 | BRP715 LED90 CW Solar                   | 24 Ah                  | Lithium Ferro<br>Phosphate | 12.8 V             | -                       |
| 911401668809 | BRP715 LED120 CW Solar<br>hybrid 3Y     | 18 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401669809 | BRP715 LED120 CW Solar<br>hybrid 5Y     | 18 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401626208 | BRP715 LED90 CW Solar Pro               | 48 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401626708 | BRP715 LED90 CW Solar 5                 | 24 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401627208 | BRP715 LED90 CW Solar Pro<br>5          | 48 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401668508 | BRP715 LED90 WW Solar                   | 24 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401669008 | BRP715 LED90 WW Solar<br>Pro            | 48 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401669508 | BRP715 LED90 WW Solar 5                 | 24 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401670008 | BRP715 LED90 WW Solar<br>Pro 5          | 48 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401669309 | BRP715 LED120 CW Solar<br>Pro hybrid 3Y | 30 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401670309 | BRP715 LED120 CW Solar<br>Pro hybrid 5Y | 30 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401626008 | BRP715 LED50 CW Solar Pro               | 30 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401626508 | BRP715 LED50 CW Solar 5                 | 12 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401627008 | BRP715 LED50 CW Solar Pro<br>5          | 30 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401668308 | BRP715 LED50 WW Solar                   | 12 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401668808 | BRP715 LED50 WW Solar<br>Pro            | 30 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401669308 | BRP715 LED50 WW Solar 5                 | 12 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401669808 | BRP715 LED50 WW Solar<br>Pro 5          | 30 Ah                  | LiFePO4                    | 12.8 V             | -                       |

## GreenVision All-in-one Solar Street Light

| Order Code   | Full Product Name                       | Battery<br>ampere hour | Battery type               | Battery<br>voltage | Cable<br>connection kit |
|--------------|-----------------------------------------|------------------------|----------------------------|--------------------|-------------------------|
| 911401669209 | BRP715 LED90 CW Solar Pro<br>hybrid 3Y  | 30 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401670209 | BRP715 LED90 CW Solar Pro<br>hybrid 5Y  | 30 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401625508 | BRP715 LED50 CW Solar                   | 12 Ah                  | Lithium Ferro<br>Phosphate | 12.8 V             | -                       |
| 911401668709 | BRP715 LED90 CW Solar<br>hybrid 3Y      | 12 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401669709 | BRP715 LED90 CW Solar<br>hybrid 5Y      | 12 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401668509 | BRP715 LED50 CW Solar<br>hybrid 3Y      | 12 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401669509 | BRP715 LED50 CW Solar<br>hybrid 5Y      | 12 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401625808 | BRP715 LED120 CW Solar                  | 30 Ah                  | Lithium Ferro<br>Phosphate | 12.8 V             | -                       |
| 911401626408 | BRP715 LED180 CW Solar<br>Pro           | 48 Ah                  | LiFePO4                    | 25.6 V             | -                       |
| 911401626908 | BRP715 LED180 CW Solar 5                | 24 Ah                  | LiFePO4                    | 25.6 V             | -                       |
| 911401627408 | BRP715 LED180 CW Solar<br>Pro 5         | 48 Ah                  | LiFePO4                    | 25.6 V             | -                       |
| 911401668708 | BRP715 LED180 WW Solar                  | 24 Ah                  | LiFePO4                    | 25.6 V             | -                       |
| 911401669208 | BRP715 LED180 WW Solar<br>Pro           | 48 Ah                  | LiFePO4                    | 25.6 V             | -                       |
| 911401669708 | BRP715 LED180 WW Solar 5                | 24 Ah                  | LiFePO4                    | 25.6 V             | -                       |
| 911401670208 | BRP715 LED180 WW Solar<br>Pro 5         | 48 Ah                  | LiFePO4                    | 25.6 V             | -                       |
| 911401626108 | BRP715 LED70 CW Solar Pro               | 42 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401626608 | BRP715 LED70 CW Solar 5                 | 18 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401627108 | BRP715 LED70 CW Solar Pro<br>5          | 42 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401668408 | BRP715 LED70 WW Solar                   | 18 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401668908 | BRP715 LED70 WW Solar<br>Pro            | 42 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401669408 | BRP715 LED70 WW Solar 5                 | 18 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401669908 | BRP715 LED70 WW Solar<br>Pro 5          | 42 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401669409 | BRP715 LED180 CW Solar<br>Pro hybrid 3Y | 24 Ah                  | LiFePO4                    | 25.6 V             | Excluded                |
| 911401670409 | BRP715 LED180 CW Solar<br>Pro hybrid 5Y | 24 Ah                  | LiFePO4                    | 25.6 V             | Excluded                |
| 911401625908 | BRP715 LED180 CW Solar                  | 24 Ah                  | Lithium Ferro<br>Phosphate | 25.6 V             | -                       |
| 911401669009 | BRP715 LED50 CW Solar Pro<br>hybrid 3Y  | 12 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401670009 | BRP715 LED50 CW Solar Pro<br>hybrid 5Y  | 12 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401668609 | BRP715 LED70 CW Solar<br>hybrid 3Y      | 12 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401669609 | BRP715 LED70 CW Solar<br>hybrid 5Y      | 12 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |

## GreenVision All-in-one Solar Street Light

| Order Code   | Full Product Name                      | Battery<br>ampere hour | Battery type               | Battery<br>voltage | Cable<br>connection kit |
|--------------|----------------------------------------|------------------------|----------------------------|--------------------|-------------------------|
| 911401668909 | BRP715 LED180 CW Solar<br>hybrid 3Y    | 15 Ah                  | LiFePO4                    | 25.6 V             | Excluded                |
| 911401669909 | BRP715 LED180 CW Solar<br>hybrid 5Y    | 15 Ah                  | LiFePO4                    | 25.6 V             | Excluded                |
| 911401626308 | BRP715 LED120 CW Solar<br>Pro          | 66 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401627308 | BRP715 LED120 CW Solar<br>Pro 5        | 66 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401668608 | BRP715 LED120 WW Solar                 | 30 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401669108 | BRP715 LED120 WW Solar<br>Pro          | 66 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401669608 | BRP715 LED120 WW Solar 5               | 30 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401670108 | BRP715 LED120 WW Solar<br>Pro 5        | 66 Ah                  | LiFePO4                    | 12.8 V             | -                       |
| 911401625608 | BRP715 LED70 CW Solar                  | 18 Ah                  | Lithium Ferro<br>Phosphate | 12.8 V             | -                       |
| 911401669109 | BRP715 LED70 CW Solar Pro<br>hybrid 3Y | 18 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |
| 911401670109 | BRP715 LED70 CW Solar Pro<br>hybrid 5Y | 18 Ah                  | LiFePO4                    | 12.8 V             | Excluded                |

### Operating and Electrical (2/2)

| Order Code   | Full Product Name                       | Grid connection<br>type | Panel peak<br>wattage | Panel<br>voltage |
|--------------|-----------------------------------------|-------------------------|-----------------------|------------------|
| 911401625708 | BRP715 LED90 CW<br>Solar                | Off grid                | 50 W                  | 18 V             |
| 911401668809 | BRP715 LED120 CW<br>Solar hybrid 3Y     | Hybrid                  | 70 W                  | 19 V             |
| 911401669809 | BRP715 LED120 CW<br>Solar hybrid 5Y     | Hybrid                  | 70 W                  | 19 V             |
| 911401626208 | BRP715 LED90 CW<br>Solar Pro            | Off grid                | 90 W                  | 18 V             |
| 911401626708 | BRP715 LED90 CW<br>Solar 5              | Off grid                | 50 W                  | 18 V             |
| 911401627208 | BRP715 LED90 CW<br>Solar Pro 5          | Off grid                | 90 W                  | 18 V             |
| 911401668508 | BRP715 LED90 WW<br>Solar                | Off grid                | 50 W                  | 18 V             |
| 911401669008 | BRP715 LED90 WW<br>Solar Pro            | Off grid                | 90 W                  | 18 V             |
| 911401669508 | BRP715 LED90 WW<br>Solar 5              | Off grid                | 50 W                  | 18 V             |
| 911401670008 | BRP715 LED90 WW<br>Solar Pro 5          | Off grid                | 90 W                  | 18 V             |
| 911401669309 | BRP715 LED120 CW<br>Solar Pro hybrid 3Y | Hybrid                  | 110 W                 | 17.5 V           |
| 911401670309 | BRP715 LED120 CW<br>Solar Pro hybrid 5Y | Hybrid                  | 110 W                 | 17.5 V           |
| 911401626008 | BRP715 LED50 CW<br>Solar Pro            | Off grid                | 50 W                  | 18 V             |

| Order Code   | Full Product Name                      | Grid connection<br>type | Panel peak<br>wattage | Panel<br>voltage |
|--------------|----------------------------------------|-------------------------|-----------------------|------------------|
| 911401626508 | BRP715 LED50 CW<br>Solar 5             | Off grid                | 25 W                  | 18 V             |
| 911401627008 | BRP715 LED50 CW<br>Solar Pro 5         | Off grid                | 50 W                  | 18 V             |
| 911401668308 | BRP715 LED50 WW<br>Solar               | Off grid                | 25 W                  | 18 V             |
| 911401668808 | BRP715 LED50 WW<br>Solar Pro           | Off grid                | 50 W                  | 18 V             |
| 911401669308 | BRP715 LED50 WW<br>Solar 5             | Off grid                | 25 W                  | 18 V             |
| 911401669808 | BRP715 LED50 WW<br>Solar Pro 5         | Off grid                | 50 W                  | 18 V             |
| 911401669209 | BRP715 LED90 CW<br>Solar Pro hybrid 3Y | Hybrid                  | 100 W                 | 22 V             |
| 911401670209 | BRP715 LED90 CW<br>Solar Pro hybrid 5Y | Hybrid                  | 100 W                 | 22 V             |
| 911401625508 | BRP715 LED50 CW<br>Solar               | Off grid                | 25 W                  | 18 V             |
| 911401668709 | BRP715 LED90 CW<br>Solar hybrid 3Y     | Hybrid                  | 55 W                  | 19 V             |
| 911401669709 | BRP715 LED90 CW<br>Solar hybrid 5Y     | Hybrid                  | 55 W                  | 19 V             |
| 911401668509 | BRP715 LED50 CW<br>Solar hybrid 3Y     | Hybrid                  | 33 W                  | 17.5 V           |
| 911401669509 | BRP715 LED50 CW<br>Solar hybrid 5Y     | Hybrid                  | 33 W                  | 17.5 V           |

GreenVision All-in-one Solar Street Light

| Order Code   | Full Product Name                    | Grid connection type | Panel peak wattage | Panel voltage |
|--------------|--------------------------------------|----------------------|--------------------|---------------|
| 911401625808 | BRP715 LED120 CW Solar               | Off grid             | 60 W               | 18 V          |
| 911401626408 | BRP715 LED180 CW Solar Pro           | Off grid             | 160 W              | 36 V          |
| 911401626908 | BRP715 LED180 CW Solar 5             | Off grid             | 80 W               | 36 V          |
| 911401627408 | BRP715 LED180 CW Solar Pro 5         | Off grid             | 160 W              | 36 V          |
| 911401668708 | BRP715 LED180 WW Solar               | Off grid             | 80 W               | 36 V          |
| 911401669208 | BRP715 LED180 WW Solar Pro           | Off grid             | 160 W              | 36 V          |
| 911401669708 | BRP715 LED180 WW Solar 5             | Off grid             | 80 W               | 36 V          |
| 911401670208 | BRP715 LED180 WW Solar Pro 5         | Off grid             | 160 W              | 36 V          |
| 911401626108 | BRP715 LED70 CW Solar Pro            | Off grid             | 80 W               | 18 V          |
| 911401626608 | BRP715 LED70 CW Solar 5              | Off grid             | 40 W               | 18 V          |
| 911401627108 | BRP715 LED70 CW Solar Pro 5          | Off grid             | 80 W               | 18 V          |
| 911401668408 | BRP715 LED70 WW Solar                | Off grid             | 40 W               | 18 V          |
| 911401668908 | BRP715 LED70 WW Solar Pro            | Off grid             | 80 W               | 18 V          |
| 911401669408 | BRP715 LED70 WW Solar 5              | Off grid             | 40 W               | 18 V          |
| 911401669908 | BRP715 LED70 WW Solar Pro 5          | Off grid             | 80 W               | 18 V          |
| 911401669409 | BRP715 LED180 CW Solar Pro hybrid 3Y | Hybrid               | 175 W              | 42 V          |
| 911401670409 | BRP715 LED180 CW Solar Pro hybrid 5Y | Hybrid               | 175 W              | 42 V          |

Controls and Dimming

| Order Code   | Full Product Name                | Solar dimming profile                      |
|--------------|----------------------------------|--------------------------------------------|
| 911401625708 | BRP715 LED90 CW Solar            | Dimming along with micriwave sensor        |
| 911401668809 | BRP715 LED120 CW Solar hybrid 3Y | Dimming along with mircowave motion sensor |
| 911401669809 | BRP715 LED120 CW Solar hybrid 5Y | Dimming along with mircowave motion sensor |
| 911401626208 | BRP715 LED90 CW Solar Pro        | Dimming along with mircowave motion sensor |
| 911401626708 | BRP715 LED90 CW Solar 5          | Dimming along with mircowave motion sensor |
| 911401627208 | BRP715 LED90 CW Solar Pro 5      | Dimming along with mircowave motion sensor |
| 911401668508 | BRP715 LED90 WW Solar            | Dimming along with mircowave motion sensor |

| Order Code   | Full Product Name                   | Grid connection type | Panel peak wattage | Panel voltage |
|--------------|-------------------------------------|----------------------|--------------------|---------------|
| 911401625908 | BRP715 LED180 CW Solar              | Off grid             | 80 W               | 36 V          |
| 911401669009 | BRP715 LED50 CW Solar Pro hybrid 3Y | Hybrid               | 55 W               | 19 V          |
| 911401670009 | BRP715 LED50 CW Solar Pro hybrid 5Y | Hybrid               | 55 W               | 19 V          |
| 911401668609 | BRP715 LED70 CW Solar hybrid 3Y     | Hybrid               | 45 W               | 19 V          |
| 911401669609 | BRP715 LED70 CW Solar hybrid 5Y     | Hybrid               | 45 W               | 19 V          |
| 911401668909 | BRP715 LED180 CW Solar hybrid 3Y    | Hybrid               | 90 W               | 36 V          |
| 911401669909 | BRP715 LED180 CW Solar hybrid 5Y    | Hybrid               | 90 W               | 36 V          |
| 911401626308 | BRP715 LED120 CW Solar Pro          | Off grid             | 100 W              | 18 V          |
| 911401627308 | BRP715 LED120 CW Solar Pro 5        | Off grid             | 100 W              | 18 V          |
| 911401668608 | BRP715 LED120 WW Solar              | Off grid             | 60 W               | 18 V          |
| 911401669108 | BRP715 LED120 WW Solar Pro          | Off grid             | 100 W              | 18 V          |
| 911401669608 | BRP715 LED120 WW Solar 5            | Off grid             | 60 W               | 18 V          |
| 911401670108 | BRP715 LED120 WW Solar Pro 5        | Off grid             | 100 W              | 18 V          |
| 911401625608 | BRP715 LED70 CW Solar               | Off grid             | 40 W               | 18 V          |
| 911401669109 | BRP715 LED70 CW Solar Pro hybrid 3Y | Hybrid               | 90 W               | 19 V          |
| 911401670109 | BRP715 LED70 CW Solar Pro hybrid 5Y | Hybrid               | 90 W               | 19 V          |

| Order Code   | Full Product Name                    | Solar dimming profile                      |
|--------------|--------------------------------------|--------------------------------------------|
| 911401669008 | BRP715 LED90 WW Solar Pro            | Dimming along with mircowave motion sensor |
| 911401669508 | BRP715 LED90 WW Solar 5              | Dimming along with mircowave motion sensor |
| 911401670008 | BRP715 LED90 WW Solar Pro 5          | Dimming along with mircowave motion sensor |
| 911401669309 | BRP715 LED120 CW Solar Pro hybrid 3Y | Dimming along with mircowave motion sensor |
| 911401670309 | BRP715 LED120 CW Solar Pro hybrid 5Y | Dimming along with mircowave motion sensor |
| 911401626008 | BRP715 LED50 CW Solar Pro            | Dimming along with mircowave motion sensor |

## GreenVision All-in-one Solar Street Light

| Order Code   | Full Product Name                   | Solar dimming profile                      |
|--------------|-------------------------------------|--------------------------------------------|
| 911401626508 | BRP715 LED50 CW Solar 5             | Dimming along with microwave motion sensor |
| 911401627008 | BRP715 LED50 CW Solar Pro 5         | Dimming along with microwave motion sensor |
| 911401668308 | BRP715 LED50 WW Solar               | Dimming along with microwave motion sensor |
| 911401668808 | BRP715 LED50 WW Solar Pro           | Dimming along with microwave motion sensor |
| 911401669308 | BRP715 LED50 WW Solar 5             | Dimming along with microwave motion sensor |
| 911401669808 | BRP715 LED50 WW Solar Pro 5         | Dimming along with microwave motion sensor |
| 911401669209 | BRP715 LED90 CW Solar Pro hybrid 3Y | Dimming along with microwave motion sensor |
| 911401670209 | BRP715 LED90 CW Solar Pro hybrid 5Y | Dimming along with microwave motion sensor |
| 911401625508 | BRP715 LED50 CW Solar               | Dimming along with micriwave sensor        |
| 911401668709 | BRP715 LED90 CW Solar hybrid 3Y     | Dimming along with microwave motion sensor |
| 911401669709 | BRP715 LED90 CW Solar hybrid 5Y     | Dimming along with microwave motion sensor |
| 911401668509 | BRP715 LED50 CW Solar hybrid 3Y     | Dimming along with microwave motion sensor |
| 911401669509 | BRP715 LED50 CW Solar hybrid 5Y     | Dimming along with microwave motion sensor |
| 911401625808 | BRP715 LED120 CW Solar              | Dimming along with micriwave sensor        |
| 911401626408 | BRP715 LED180 CW Solar Pro          | Dimming along with microwave motion sensor |
| 911401626908 | BRP715 LED180 CW Solar 5            | Dimming along with microwave motion sensor |
| 911401627408 | BRP715 LED180 CW Solar Pro 5        | Dimming along with microwave motion sensor |
| 911401668708 | BRP715 LED180 WW Solar              | Dimming along with microwave motion sensor |
| 911401669208 | BRP715 LED180 WW Solar Pro          | Dimming along with microwave motion sensor |
| 911401669708 | BRP715 LED180 WW Solar 5            | Dimming along with microwave motion sensor |
| 911401670208 | BRP715 LED180 WW Solar Pro 5        | Dimming along with microwave motion sensor |
| 911401626108 | BRP715 LED70 CW Solar Pro           | Dimming along with microwave motion sensor |
| 911401626608 | BRP715 LED70 CW Solar 5             | Dimming along with microwave motion sensor |

### Mechanical and Housing

| Order Code   | Full Product Name                | Overall length | Overall width |
|--------------|----------------------------------|----------------|---------------|
| 911401625708 | BRP715 LED90 CW Solar            | 910 mm         | 366 mm        |
| 911401668809 | BRP715 LED120 CW Solar hybrid 3Y | 1,080 mm       | 366 mm        |
| 911401669809 | BRP715 LED120 CW Solar hybrid 5Y | 1,080 mm       | 366 mm        |
| 911401626208 | BRP715 LED90 CW Solar Pro        | 1,535 mm       | 366 mm        |

| Order Code   | Full Product Name                    | Solar dimming profile                      |
|--------------|--------------------------------------|--------------------------------------------|
| 911401627108 | BRP715 LED70 CW Solar Pro 5          | Dimming along with microwave motion sensor |
| 911401668408 | BRP715 LED70 WW Solar                | Dimming along with microwave motion sensor |
| 911401668908 | BRP715 LED70 WW Solar Pro            | Dimming along with microwave motion sensor |
| 911401669408 | BRP715 LED70 WW Solar 5              | Dimming along with microwave motion sensor |
| 911401669908 | BRP715 LED70 WW Solar Pro 5          | Dimming along with microwave motion sensor |
| 911401669409 | BRP715 LED180 CW Solar Pro hybrid 3Y | Dimming along with microwave motion sensor |
| 911401670409 | BRP715 LED180 CW Solar Pro hybrid 5Y | Dimming along with microwave motion sensor |
| 911401625908 | BRP715 LED180 CW Solar               | Dimming along with micriwave sensor        |
| 911401669009 | BRP715 LED50 CW Solar Pro hybrid 3Y  | Dimming along with microwave motion sensor |
| 911401670009 | BRP715 LED50 CW Solar Pro hybrid 5Y  | Dimming along with microwave motion sensor |
| 911401668609 | BRP715 LED70 CW Solar hybrid 3Y      | Dimming along with microwave motion sensor |
| 911401669609 | BRP715 LED70 CW Solar hybrid 5Y      | Dimming along with microwave motion sensor |
| 911401668909 | BRP715 LED180 CW Solar hybrid 3Y     | Dimming along with microwave motion sensor |
| 911401669909 | BRP715 LED180 CW Solar hybrid 5Y     | Dimming along with microwave motion sensor |
| 911401626308 | BRP715 LED120 CW Solar Pro           | Dimming along with microwave motion sensor |
| 911401627308 | BRP715 LED120 CW Solar Pro 5         | Dimming along with microwave motion sensor |
| 911401668608 | BRP715 LED120 WW Solar               | Dimming along with microwave motion sensor |
| 911401669108 | BRP715 LED120 WW Solar Pro           | Dimming along with microwave motion sensor |
| 911401669608 | BRP715 LED120 WW Solar 5             | Dimming along with microwave motion sensor |
| 911401670108 | BRP715 LED120 WW Solar Pro 5         | Dimming along with microwave motion sensor |
| 911401625608 | BRP715 LED70 CW Solar                | Dimming along with micriwave sensor        |
| 911401669109 | BRP715 LED70 CW Solar Pro hybrid 3Y  | Dimming along with microwave motion sensor |
| 911401670109 | BRP715 LED70 CW Solar Pro hybrid 5Y  | Dimming along with microwave motion sensor |

GreenVision All-in-one Solar Street Light

| Order Code   | Full Product Name                    | Overall length | Overall width |
|--------------|--------------------------------------|----------------|---------------|
| 911401669508 | BRP715 LED90 WW Solar 5              | 910 mm         | 366 mm        |
| 911401670008 | BRP715 LED90 WW Solar Pro 5          | 1,535 mm       | 366 mm        |
| 911401669309 | BRP715 LED120 CW Solar Pro hybrid 3Y | 1,670 mm       | 366 mm        |
| 911401670309 | BRP715 LED120 CW Solar Pro hybrid 5Y | 1,670 mm       | 366 mm        |
| 911401626008 | BRP715 LED50 CW Solar Pro            | 910 mm         | 366 mm        |
| 911401626508 | BRP715 LED50 CW Solar 5              | 560 mm         | 355 mm        |
| 911401627008 | BRP715 LED50 CW Solar Pro 5          | 910 mm         | 366 mm        |
| 911401668308 | BRP715 LED50 WW Solar                | 560 mm         | 355 mm        |
| 911401668808 | BRP715 LED50 WW Solar Pro            | 910 mm         | 366 mm        |
| 911401669308 | BRP715 LED50 WW Solar 5              | 560 mm         | 355 mm        |
| 911401669808 | BRP715 LED50 WW Solar Pro 5          | 910 mm         | 366 mm        |
| 911401669209 | BRP715 LED90 CW Solar Pro hybrid 3Y  | 1,535 mm       | 366 mm        |
| 911401670209 | BRP715 LED90 CW Solar Pro hybrid 5Y  | 1,535 mm       | 366 mm        |
| 911401625508 | BRP715 LED50 CW Solar                | 560 mm         | 366 mm        |
| 911401668709 | BRP715 LED90 CW Solar hybrid 3Y      | 910 mm         | 366 mm        |
| 911401669709 | BRP715 LED90 CW Solar hybrid 5Y      | 910 mm         | 366 mm        |
| 911401668509 | BRP715 LED50 CW Solar hybrid 3Y      | 560 mm         | 366 mm        |
| 911401669509 | BRP715 LED50 CW Solar hybrid 5Y      | 560 mm         | 366 mm        |
| 911401625808 | BRP715 LED120 CW Solar               | 1,080 mm       | 366 mm        |
| 911401626408 | BRP715 LED180 CW Solar Pro           | 1,812 mm       | 523 mm        |
| 911401626908 | BRP715 LED180 CW Solar 5             | 1,345 mm       | 366 mm        |
| 911401627408 | BRP715 LED180 CW Solar Pro 5         | 1,812 mm       | 523 mm        |
| 911401668708 | BRP715 LED180 WW Solar               | 1,345 mm       | 366 mm        |
| 911401669208 | BRP715 LED180 WW Solar Pro           | 1,812 mm       | 523 mm        |
| 911401669708 | BRP715 LED180 WW Solar 5             | 1,345 mm       | 366 mm        |
| 911401670208 | BRP715 LED180 WW Solar Pro 5         | 1,812 mm       | 523 mm        |

| Order Code   | Full Product Name                    | Overall length | Overall width |
|--------------|--------------------------------------|----------------|---------------|
| 911401626108 | BRP715 LED70 CW Solar Pro            | 1,345 mm       | 366 mm        |
| 911401626608 | BRP715 LED70 CW Solar 5              | 750 mm         | 366 mm        |
| 911401627108 | BRP715 LED70 CW Solar Pro 5          | 1,345 mm       | 366 mm        |
| 911401668408 | BRP715 LED70 WW Solar                | 750 mm         | 366 mm        |
| 911401668908 | BRP715 LED70 WW Solar Pro            | 1,345 mm       | 366 mm        |
| 911401669408 | BRP715 LED70 WW Solar 5              | 750 mm         | 366 mm        |
| 911401669908 | BRP715 LED70 WW Solar Pro 5          | 1,345 mm       | 366 mm        |
| 911401669409 | BRP715 LED180 CW Solar Pro hybrid 3Y | 1,812 mm       | 523 mm        |
| 911401670409 | BRP715 LED180 CW Solar Pro hybrid 5Y | 1,812 mm       | 523 mm        |
| 911401625908 | BRP715 LED180 CW Solar               | 1,345 mm       | 366 mm        |
| 911401669009 | BRP715 LED50 CW Solar Pro hybrid 3Y  | 910 mm         | 366 mm        |
| 911401670009 | BRP715 LED50 CW Solar Pro hybrid 5Y  | 910 mm         | 366 mm        |
| 911401668609 | BRP715 LED70 CW Solar hybrid 3Y      | 750 mm         | 366 mm        |
| 911401669609 | BRP715 LED70 CW Solar hybrid 5Y      | 750 mm         | 366 mm        |
| 911401668909 | BRP715 LED180 CW Solar hybrid 3Y     | 1,345 mm       | 366 mm        |
| 911401669909 | BRP715 LED180 CW Solar hybrid 5Y     | 1,345 mm       | 366 mm        |
| 911401626308 | BRP715 LED120 CW Solar Pro           | 1,670 mm       | 366 mm        |
| 911401627308 | BRP715 LED120 CW Solar Pro 5         | 1,670 mm       | 366 mm        |
| 911401668608 | BRP715 LED120 WW Solar               | 1,080 mm       | 366 mm        |
| 911401669108 | BRP715 LED120 WW Solar Pro           | 1,670 mm       | 366 mm        |
| 911401669608 | BRP715 LED120 WW Solar 5             | 1,080 mm       | 366 mm        |
| 911401670108 | BRP715 LED120 WW Solar Pro 5         | 1,670 mm       | 366 mm        |
| 911401625608 | BRP715 LED70 CW Solar                | 750 mm         | 366 mm        |
| 911401669109 | BRP715 LED70 CW Solar Pro hybrid 3Y  | 1,345 mm       | 366 mm        |
| 911401670109 | BRP715 LED70 CW Solar Pro hybrid 5Y  | 1,345 mm       | 366 mm        |

Approval and Application

| Order Code   | Full Product Name                    | Ambient temperature range |
|--------------|--------------------------------------|---------------------------|
| 911401625708 | BRP715 LED90 CW Solar                | -20 to +55 °C             |
| 911401668809 | BRP715 LED120 CW Solar hybrid 3Y     | -10 °C to 55 °C           |
| 911401669809 | BRP715 LED120 CW Solar hybrid 5Y     | -10 °C to 55 °C           |
| 911401626208 | BRP715 LED90 CW Solar Pro            | -20 °C to 55 °C           |
| 911401626708 | BRP715 LED90 CW Solar 5              | -20 °C to 55 °C           |
| 911401627208 | BRP715 LED90 CW Solar Pro 5          | -20 °C to 55 °C           |
| 911401668508 | BRP715 LED90 WW Solar                | -20 °C to 55 °C           |
| 911401669008 | BRP715 LED90 WW Solar Pro            | -20 °C to 55 °C           |
| 911401669508 | BRP715 LED90 WW Solar 5              | -20 °C to 55 °C           |
| 911401670008 | BRP715 LED90 WW Solar Pro 5          | -20 °C to 55 °C           |
| 911401669309 | BRP715 LED120 CW Solar Pro hybrid 3Y | -10 °C to 55 °C           |
| 911401670309 | BRP715 LED120 CW Solar Pro hybrid 5Y | -10 °C to 55 °C           |
| 911401626008 | BRP715 LED50 CW Solar Pro            | -20 °C to 55 °C           |
| 911401626508 | BRP715 LED50 CW Solar 5              | -20 °C to 55 °C           |
| 911401627008 | BRP715 LED50 CW Solar Pro 5          | -20 °C to 55 °C           |
| 911401668308 | BRP715 LED50 WW Solar                | -20 °C to 55 °C           |
| 911401668808 | BRP715 LED50 WW Solar Pro            | -20 °C to 55 °C           |
| 911401669308 | BRP715 LED50 WW Solar 5              | -20 °C to 55 °C           |
| 911401669808 | BRP715 LED50 WW Solar Pro 5          | -20 °C to 55 °C           |
| 911401669209 | BRP715 LED90 CW Solar Pro hybrid 3Y  | -10 °C to 55 °C           |
| 911401670209 | BRP715 LED90 CW Solar Pro hybrid 5Y  | -10 °C to 55 °C           |
| 911401625508 | BRP715 LED50 CW Solar                | -20 to +55 °C             |

| Order Code   | Full Product Name                    | Ambient temperature range |
|--------------|--------------------------------------|---------------------------|
| 911401668709 | BRP715 LED90 CW Solar hybrid 3Y      | -10 °C to 55 °C           |
| 911401669709 | BRP715 LED90 CW Solar hybrid 5Y      | -10 °C to 55 °C           |
| 911401668509 | BRP715 LED50 CW Solar hybrid 3Y      | -10 °C to 55 °C           |
| 911401669509 | BRP715 LED50 CW Solar hybrid 5Y      | -10 °C to 55 °C           |
| 911401625808 | BRP715 LED120 CW Solar               | -20 to +55 °C             |
| 911401626408 | BRP715 LED180 CW Solar Pro           | -20 °C to 55 °C           |
| 911401626908 | BRP715 LED180 CW Solar 5             | -20 °C to 55 °C           |
| 911401627408 | BRP715 LED180 CW Solar Pro 5         | -20 °C to 55 °C           |
| 911401668708 | BRP715 LED180 WW Solar               | -20 °C to 55 °C           |
| 911401669208 | BRP715 LED180 WW Solar Pro           | -20 °C to 55 °C           |
| 911401669708 | BRP715 LED180 WW Solar 5             | -20 °C to 55 °C           |
| 911401670208 | BRP715 LED180 WW Solar Pro 5         | -20 °C to 55 °C           |
| 911401626108 | BRP715 LED70 CW Solar Pro            | -20 °C to 55 °C           |
| 911401626608 | BRP715 LED70 CW Solar 5              | -20 °C to 55 °C           |
| 911401627108 | BRP715 LED70 CW Solar Pro 5          | -20 °C to 55 °C           |
| 911401668408 | BRP715 LED70 WW Solar                | -20 °C to 55 °C           |
| 911401668908 | BRP715 LED70 WW Solar Pro            | -20 °C to 55 °C           |
| 911401669408 | BRP715 LED70 WW Solar 5              | -20 °C to 55 °C           |
| 911401669908 | BRP715 LED70 WW Solar Pro 5          | -20 °C to 55 °C           |
| 911401669409 | BRP715 LED180 CW Solar Pro hybrid 3Y | -10 °C to 55 °C           |
| 911401670409 | BRP715 LED180 CW Solar Pro hybrid 5Y | -10 °C to 55 °C           |
| 911401625908 | BRP715 LED180 CW Solar               | -20 to +55 °C             |

GreenVision All-in-one Solar Street Light

| Order Code   | Full Product Name                   | Ambient temperature range |
|--------------|-------------------------------------|---------------------------|
| 911401669009 | BRP715 LED50 CW Solar Pro hybrid 3Y | -10 °C to 55 °C           |
| 911401670009 | BRP715 LED50 CW Solar Pro hybrid 5Y | -10 °C to 55 °C           |
| 911401668609 | BRP715 LED70 CW Solar hybrid 3Y     | -10 °C to 55 °C           |
| 911401669609 | BRP715 LED70 CW Solar hybrid 5Y     | -10 °C to 55 °C           |
| 911401668909 | BRP715 LED180 CW Solar hybrid 3Y    | -10 °C to 55 °C           |
| 911401669909 | BRP715 LED180 CW Solar hybrid 5Y    | -10 °C to 55 °C           |
| 911401626308 | BRP715 LED120 CW Solar Pro          | -20 °C to 55 °C           |
| 911401627308 | BRP715 LED120 CW Solar Pro 5        | -20 °C to 55 °C           |

| Order Code   | Full Product Name                   | Ambient temperature range |
|--------------|-------------------------------------|---------------------------|
| 911401668608 | BRP715 LED120 WW Solar              | -20 °C to 55 °C           |
| 911401669108 | BRP715 LED120 WW Solar Pro          | -20 °C to 55 °C           |
| 911401669608 | BRP715 LED120 WW Solar 5            | -20 °C to 55 °C           |
| 911401670108 | BRP715 LED120 WW Solar Pro 5        | -20 °C to 55 °C           |
| 911401625608 | BRP715 LED70 CW Solar               | -20 to +55 °C             |
| 911401669109 | BRP715 LED70 CW Solar Pro hybrid 3Y | -10 °C to 55 °C           |
| 911401670109 | BRP715 LED70 CW Solar Pro hybrid 5Y | -10 °C to 55 °C           |

Application Conditions

| Order Code   | Full Product Name                    | Ambient temperature range for charging | Ambient temperature range for discharging (when light is on) |
|--------------|--------------------------------------|----------------------------------------|--------------------------------------------------------------|
| 911401625708 | BRP715 LED90 CW Solar                | 0 °C to +55 °C                         | -20 °C to +55 °C                                             |
| 911401668809 | BRP715 LED120 CW Solar hybrid 3Y     | -                                      | -                                                            |
| 911401669809 | BRP715 LED120 CW Solar hybrid 5Y     | -                                      | -                                                            |
| 911401626208 | BRP715 LED90 CW Solar Pro            | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401626708 | BRP715 LED90 CW Solar 5              | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401627208 | BRP715 LED90 CW Solar Pro 5          | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401668508 | BRP715 LED90 WW Solar                | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669008 | BRP715 LED90 WW Solar Pro            | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669508 | BRP715 LED90 WW Solar 5              | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401670008 | BRP715 LED90 WW Solar Pro 5          | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669309 | BRP715 LED120 CW Solar Pro hybrid 3Y | -                                      | -                                                            |
| 911401670309 | BRP715 LED120 CW Solar Pro hybrid 5Y | -                                      | -                                                            |
| 911401626008 | BRP715 LED50 CW Solar Pro            | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401626508 | BRP715 LED50 CW Solar 5              | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401627008 | BRP715 LED50 CW Solar Pro 5          | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401668308 | BRP715 LED50 WW Solar                | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401668808 | BRP715 LED50 WW Solar Pro            | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669308 | BRP715 LED50 WW Solar 5              | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669808 | BRP715 LED50 WW Solar Pro 5          | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |

| Order Code   | Full Product Name                   | Ambient temperature range for charging | Ambient temperature range for discharging (when light is on) |
|--------------|-------------------------------------|----------------------------------------|--------------------------------------------------------------|
| 911401669209 | BRP715 LED90 CW Solar Pro hybrid 3Y | -                                      | -                                                            |
| 911401670209 | BRP715 LED90 CW Solar Pro hybrid 5Y | -                                      | -                                                            |
| 911401625508 | BRP715 LED50 CW Solar               | 0 °C to +55 °C                         | -20 °C to +55 °C                                             |
| 911401668709 | BRP715 LED90 CW Solar hybrid 3Y     | -                                      | -                                                            |
| 911401669709 | BRP715 LED90 CW Solar hybrid 5Y     | -                                      | -                                                            |
| 911401668509 | BRP715 LED50 CW Solar hybrid 3Y     | -                                      | -                                                            |
| 911401669509 | BRP715 LED50 CW Solar hybrid 5Y     | -                                      | -                                                            |
| 911401625808 | BRP715 LED120 CW Solar              | 0 °C to +55 °C                         | -20 °C to +55 °C                                             |
| 911401626408 | BRP715 LED180 CW Solar Pro          | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401626908 | BRP715 LED180 CW Solar 5            | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401627408 | BRP715 LED180 CW Solar Pro 5        | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401668708 | BRP715 LED180 WW Solar              | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669208 | BRP715 LED180 WW Solar Pro          | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669708 | BRP715 LED180 WW Solar 5            | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401670208 | BRP715 LED180 WW Solar Pro 5        | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401626108 | BRP715 LED70 CW Solar Pro           | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401626608 | BRP715 LED70 CW Solar 5             | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401627108 | BRP715 LED70 CW Solar Pro 5         | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401668408 | BRP715 LED70 WW Solar               | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |

GreenVision All-in-one Solar Street Light

| Order Code   | Full Product Name                       | Ambient temperature range for charging | Ambient temperature range for discharging (when light is on) |
|--------------|-----------------------------------------|----------------------------------------|--------------------------------------------------------------|
| 911401668908 | BRP715 LED70 WW<br>Solar Pro            | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669408 | BRP715 LED70 WW<br>Solar 5              | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669908 | BRP715 LED70 WW<br>Solar Pro 5          | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669409 | BRP715 LED180 CW<br>Solar Pro hybrid 3Y | -                                      | -                                                            |
| 911401670409 | BRP715 LED180 CW<br>Solar Pro hybrid 5Y | -                                      | -                                                            |
| 911401625908 | BRP715 LED180 CW<br>Solar               | 0 °C to +55 °C                         | -20 °C to +55 °C                                             |
| 911401669009 | BRP715 LED50 CW<br>Solar Pro hybrid 3Y  | -                                      | -                                                            |
| 911401670009 | BRP715 LED50 CW<br>Solar Pro hybrid 5Y  | -                                      | -                                                            |
| 911401668609 | BRP715 LED70 CW<br>Solar hybrid 3Y      | -                                      | -                                                            |
| 911401669609 | BRP715 LED70 CW<br>Solar hybrid 5Y      | -                                      | -                                                            |
| 911401668909 | BRP715 LED180 CW<br>Solar hybrid 3Y     | -                                      | -                                                            |

| Order Code   | Full Product Name                      | Ambient temperature range for charging | Ambient temperature range for discharging (when light is on) |
|--------------|----------------------------------------|----------------------------------------|--------------------------------------------------------------|
| 911401669909 | BRP715 LED180 CW<br>Solar hybrid 5Y    | -                                      | -                                                            |
| 911401626308 | BRP715 LED120 CW<br>Solar Pro          | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401627308 | BRP715 LED120 CW<br>Solar Pro 5        | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401668608 | BRP715 LED120 WW<br>Solar              | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669108 | BRP715 LED120 WW<br>Solar Pro          | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401669608 | BRP715 LED120 WW<br>Solar 5            | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401670108 | BRP715 LED120 WW<br>Solar Pro 5        | 0 °C to 55 °C                          | -20 °C to 55 °C                                              |
| 911401625608 | BRP715 LED70 CW<br>Solar               | 0 °C to +55 °C                         | -20 °C to +55 °C                                             |
| 911401669109 | BRP715 LED70 CW<br>Solar Pro hybrid 3Y | -                                      | -                                                            |
| 911401670109 | BRP715 LED70 CW<br>Solar Pro hybrid 5Y | -                                      | -                                                            |

