



A full indirect light troffer

CoreView G4 RC420B

RC420B G4 inherits the elegant and classic indirect light design from previous generation but with slimmer outlook. It offers 3 types, 600x600, 300x1200, and 600x1200 (Customized offer)mm with max: 108lm/w. Air slot option applies to 600x1200mm type to give fast and easy support to the projects where air outlet is required from the office lighting fittings. Full indirect light design provides visual comfort in the office area as well.

Benefits

- Full range offer from 600x600, 300x1200 to 600x1200(Customized offer) to cover key applications
- High system efficacy from indirect light design to provide additional energy saving
- Dali, Tunable white, Interact Office options are available for total system offer
- Slim design for critical office space installation

Features

- System efficiency 108lm/W(max)
- CRI80 and CRI90 (with customized solution)
- Max height <=90mm (without driver)
- Lifetime: 50K hours (L70@25deg)

Application

- Open plan office
- Public indoor area
- Meeting/Training room

Specifications

Mounting type	Recessed	Mains Voltage	220-240V / 50-60Hz
Ceiling type	T-bar ceiling		

CoreView G4 RC420B

Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
Material	Housing: metal sheet
Lumen maintenance at median useful life	L70B50
50.000h	

Color Rendering index - 840, 850, 940, 950	
CRI	
Risk Group	RG0
Ingress protection	IP20
Driver replaceable	Yes

Versions



CoreView G4 RC420 600600

Dimensional drawing

