



One choice, five colors

Dipswitch LED bulb

Not sure about the color that will best fit your application? No need to worry. Philips Dipswitch LED bulb offer 5 colors in one product and is easy-to-operate by switching the button to change the color.

Benefits

- Enjoy 5 possible light colors in one product
- Change the color of your light easily with by switching the button on the product
- No guesswork

Features

- 5 color temperatures
- Dimmable
- Change the color by switching the button
- Lifetime up to 15,000 hours
- Easy retrofit

Application

- Home
- Offices
- Education

Dipswitch LED bulb

Versions



LEDBulb 9W B22 DS FR DIM 1PF 6
AU RTP



LED 8A19 DipS 5CCT FR P E26
DIM T20 3 4CT



LEDStick 14W E27 DS FR DIM 1PF
6 AU RTP



LEDBulb 14W E27 DS FR DIM 1PF 6
AU RTP



LEDStick 10W B22 DS FR DIM 1PF
6 AU RTP



LEDBulb 14W B22 DS FR DIM 1PF 6
AU RTP



LEDBulb 9W E27 DS FR DIM 1PF 6
AU RTP



LEDStick 10W E27 DS FR DIM 1PF
6 AU RTP

Dipswitch LED bulb

Versions






LEDStick 14W B22 DS FR DIM 1PF
6 AU RTP



LED 14A19 DipS 5CCT FR P E26
DIM T20 2 2PF

Dimensional drawing






Product	D	C
14A19/DipS/5CCT/FR/P/E26/DIM/T20 2/2PF	60 mm	116 mm
8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT	60 mm	112 mm
LEDBulb 14W E27 DS FR DIM 1PF/6 AU	60 mm	119 mm
LEDBulb 9W E27 DS FR DIM 1PF/6 AU	60 mm	115 mm

Product	D	C
LEDStick 10W B22 DS FR DIM 1PF/6 AU	41 mm	106 mm

Product	D	C
LEDStick 14W E27 DS FR DIM 1PF/6 AU	41 mm	133 mm

Dipswitch LED bulb

Dimensional drawing



Product	D	C
LEDStick 14W B22 DS FR DIM 1PF/6 AU	41 mm	132 mm

Product	D	C
LEDBulb 14W B22 DS FR DIM 1PF/6 AU	60 mm	118 mm
LEDBulb 9W B22 DS FR DIM 1PF/6 AU	60 mm	114 mm

Product	D	C
LEDStick 10W E27 DS FR DIM 1PF/6 AU	41 mm	107 mm

Dipswitch LED bulb

General Information	
Switching Cycle	50,000
Nominal lifetime	15,000 hour(s)
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Approval and Application	
Ambient temperature range	-20 to +45 °C

General Information

Order Code	Full Product Name	Cap-Base	Order Code	Full Product Name	Cap-Base
929003785319	LEDBulb 9W B22 DS FR DIM 1PF/6 AU	B22	929003785519	LEDBulb 14W B22 DS FR DIM 1PF/6 AU	B22
929003620333	8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT	E26	929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	E27
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	E27	929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	E27
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	E27	929003785919	LEDStick 14W B22 DS FR DIM 1PF/6 AU	B22
929003785719	LEDStick 10W B22 DS FR DIM 1PF/6 AU	B22	929003620433	14A19/DipS/5CCT/FR/P/E26/DIM/T20 2/2PF	E26

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Color rendering	
			Temperature (Nom)	index (CRI)	Color Code	Luminous Flux
929003785319	LEDBulb 9W B22 DS FR DIM 1PF/6 AU	200 degree(s)	2700 K	80	2700K/3000K/4000K/5000K/6500K	900 lm
929003620333	8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT	220 degree(s)	Selectable	90	2700/3000/3500/4000/5000	800 lm
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	200 degree(s)	2700 K	80	2700K/3000K/4000K/5000K/6500K	1,400 lm
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	200 degree(s)	2700 K	80	2700K/3000K/4000K/5000K/6500K	1,400 lm
929003785719	LEDStick 10W B22 DS FR DIM 1PF/6 AU	200 degree(s)	2700 K	80	2700K/3000K/4000K/5000K/6500K	1,000 lm
929003785519	LEDBulb 14W B22 DS FR DIM 1PF/6 AU	200 degree(s)	2700 K	80	2700K/3000K/4000K/5000K/6500K	1,400 lm
929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	200 degree(s)	2700 K	80	2700K/3000K/4000K/5000K/6500K	900 lm
929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	200 degree(s)	2700 K	80	2700K/3000K/4000K/5000K/6500K	1,000 lm
929003785919	LEDStick 14W B22 DS FR DIM 1PF/6 AU	200 degree(s)	2700 K	80	2700K/3000K/4000K/5000K/6500K	1,400 lm
929003620433	14A19/DipS/5CCT/FR/P/E26/DIM/T20 2/2PF	220 degree(s)	Selectable	90	2700/3000/3500/4000/5000	1,500 lm

Operating and Electrical

Order Code	Full Product Name	Input	Power	Wattage	Order Code	Full Product Name	Input	Power	Wattage
		Frequency	Consumption	Equivalent			Frequency	Consumption	Equivalent
929003785319	LEDBulb 9W B22 DS FR DIM 1PF/6 AU	50 to 60 Hz	9 W	60 W	929003620333	8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT	60 Hz	8 W	60 W

Dipswitch LED bulb

Order Code	Full Product Name	Input	Power	Wattage
		Frequency	Consumption	Equivalent
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	50 to 60 Hz	14 W	100 W
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	50 to 60 Hz	14 W	100 W
929003785719	LEDStick 10W B22 DS FR DIM 1PF/6 AU	50 to 60 Hz	10 W	75 W
929003785519	LEDBulb 14W B22 DS FR DIM 1PF/6 AU	50 to 60 Hz	14 W	100 W
929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	50 to 60 Hz	9 W	60 W

Order Code	Full Product Name	Input	Power	Wattage
		Frequency	Consumption	Equivalent
929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	50 to 60 Hz	10 W	75 W
929003785919	LEDStick 14W B22 DS FR DIM 1PF/6 AU	50 to 60 Hz	14 W	100 W
929003620433	14A19/DipS/5CCT/FR/P/E26/DI M/T20 2/2PF	60 Hz	14 W	100 W



Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003785319	LEDBulb 9W B22 DS FR DIM 1PF/6 AU	80 °C
929003620333	8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT	90 °C
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	80 °C
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	80 °C
929003785719	LEDStick 10W B22 DS FR DIM 1PF/6 AU	80 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003785519	LEDBulb 14W B22 DS FR DIM 1PF/6 AU	80 °C
929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	80 °C
929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	80 °C
929003785919	LEDStick 14W B22 DS FR DIM 1PF/6 AU	80 °C
929003620433	14A19/DipS/5CCT/FR/P/E26/DIM/T20 2/2PF	90 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929003785319	LEDBulb 9W B22 DS FR DIM 1PF/6 AU	A60
929003620333	8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT	A19
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	Stick
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	A60
929003785719	LEDStick 10W B22 DS FR DIM 1PF/6 AU	Stick
929003785519	LEDBulb 14W B22 DS FR DIM 1PF/6 AU	A60
929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	A60
929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	Stick
929003785919	LEDStick 14W B22 DS FR DIM 1PF/6 AU	Stick
929003620433	14A19/DipS/5CCT/FR/P/E26/DIM/T20 2/2PF	A19



Dipswitch LED bulb

