



# Philips GreenSpace G6: Low energy LED downlights with high visual comfort

## GreenSpace G6

Philips GreenSpace G6 builds on the GreenSpace family's reputation for superb performance, extremely low energy use, and high visual comfort. This next generation of reliable LED downlights comes in a highly-compact design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. GreenSpace G6 is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 600 to 3,550 lumen, with the option to choose fixed, dimmable, or Interact Ready variants. This makes GreenSpace G6 the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

### Benefits

- Energy-efficient LED
- Compact design
- Visual comfort
- Option of glossy faceted (UGR19) or matte white reflector
- Durable LED quality and reliability

### Features

- High system efficacy – average 120 lm/W
- Deep recessed architecture with increased reflector depth
- Spacious installation area with improved narrow rim width
- 50,000 hours lifetime @L80/B50 Ta 25°C
- DALI and wireless Interact compatible

Application

- Offices
- retail
- Hospitality
- other potential indoor open areas

Specifications

|                                         |                                                                                                                                                |
|-----------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| Mounting type                           | Recessed                                                                                                                                       |
| Operating Temperature range             | -20°C to +40°C                                                                                                                                 |
| Light Source                            | LED module                                                                                                                                     |
| Mains Voltage                           | 220-240V / 50-60Hz                                                                                                                             |
| Mains connection                        | flying cable                                                                                                                                   |
| Dimming                                 | PSU: non-dimmablePSD: Dimmable via Dali protocolWIA: Wireless control                                                                          |
| Control system input                    | DALI/1-10V/ WIA                                                                                                                                |
| Material                                | Housing: Die-cat Aluminium<br>Reflector: Plastic                                                                                               |
| Main color of the luminaire             | Black heat sink                                                                                                                                |
| Lumen maintenance at median useful life | L80<br>50.000h                                                                                                                                 |
| Flicker / Pst / SVM                     | MD<3.2%<br>PST<=0.5<br>SVM<=1                                                                                                                  |
| Luminous flux                           | 4inch: 650lm-800lm, 1100lm-1150lm, 1270-1350lm<br>6inch: 1150-1200lm, 1700-1800lm, 1860-2000lm<br>8inch: 1650-1760lm, 2250-2400lm, 3450-3550lm |
| Power consumption                       | 4inch: 5.8W - 12W<br>6inch: 9.8W - 16.6W<br>8inch: 14.2W - 29.3W                                                                               |
| Luminaire efficacy                      | PSU: 105-124lm/W @840<br>PSD/WIA: 100-122lm/W @840                                                                                             |
| Correlated color temperature - CCT      | 3000K, 4000K, 6500                                                                                                                             |






|                                |                                                                                                                                                       |
|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Color Rendering index - 80, 90 |                                                                                                                                                       |
| CRI                            |                                                                                                                                                       |
| Risk Group                     | RG1                                                                                                                                                   |
| Beam angle                     | 4inch - WH reflector - 78degree<br>6inch - WH reflector - 82degree<br>8inch - WH reflector - 83degree<br>4/6/8inch - Aluminizing reflector - 60degree |
| Reflector material             | WH: Plastic<br>AL: Aluminum coated                                                                                                                    |
| Optic                          | White (WH) UGR 23-26 (NOC) based on lumen output.<br>Aluminizing (AL) UGR<19 (OC)                                                                     |
| Protection Class               | Class II                                                                                                                                              |
| IEC61140                       |                                                                                                                                                       |
| Mechanical impact protection   | IK03                                                                                                                                                  |
| Ingress protection             | IP20 / IP54 (light exit window)                                                                                                                       |
| Overall diameter               | 4inch: D100<br>6inch: D150<br>8inch: D200                                                                                                             |
| Overall height                 | 4inch: 69mm<br>6inch: 82mm<br>8inch: 105mm                                                                                                            |
| UGR                            | AL coating reflector: UGR19<br>WH reflector: UGR 23-26                                                                                                |
| Installation                   | recessed<br>Fixation by means of spring fasteners                                                                                                     |

Versions



GreenSpace G6

Dimensional drawing



## General Information

|      |   |
|------|---|
| Gear | - |
|------|---|

## Operating and Electrical

|                      |                 |
|----------------------|-----------------|
| Protection class IEC | Safety class II |
|----------------------|-----------------|

|               |              |
|---------------|--------------|
| Input Voltage | 220 to 240 V |
|---------------|--------------|

|                |             |
|----------------|-------------|
| Line Frequency | 50 or 60 Hz |
|----------------|-------------|

## Mechanical and Housing

|                    |                           |
|--------------------|---------------------------|
| Optical cover type | Polycarbonate<br>Diffuser |
|--------------------|---------------------------|

|                              |      |
|------------------------------|------|
| Mech. impact protection code | IK03 |
|------------------------------|------|

## Approval and Application

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | -20 to +40 °C |
|---------------------------|---------------|

|         |     |
|---------|-----|
| CE mark | Yes |
|---------|-----|

|           |   |
|-----------|---|
| ENEC mark | - |
|-----------|---|

|                   |   |
|-------------------|---|
| Flammability mark | - |
|-------------------|---|

|                |                                     |
|----------------|-------------------------------------|
| Glow-wire test | Temperature 650<br>°C, duration 5 s |
|----------------|-------------------------------------|

## General Information

| Order Code   | Full Product Name                        | Driver included | Number of gear units | Service tag |
|--------------|------------------------------------------|-----------------|----------------------|-------------|
| 911401504045 | DN391X LED8/9TNW P7PSD D100 WH WP G2     | Yes             | 1 unit               | -           |
| 911401504345 | DN391X LED8/9TNW P7PSD D100 WH WPCAUG2   | Yes             | 1 unit               | -           |
| 911401520244 | DN390B LED7/840 P6PSU D100WHWP CAUG2HE   | Yes             | -                    | Yes         |
| 911401520644 | DN390B LED7/840 P6PSU D100 WH CAUG2HE    | Yes             | -                    | Yes         |
| 911401533644 | DN391B LED15/865 P11PSU D100 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401533744 | DN391B LED15/840 P11PSU D100 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401533844 | DN391B LED15/830 P11PSU D100 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401534244 | DN391B LED15/865 PSU D100 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401534344 | DN391B LED15/840 PSU D100 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401534444 | DN391B LED15/830 PSU D100 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401534844 | DN391B LED12/865 P10PSU D100 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401534944 | DN391B LED12/840 P10PSU D100 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401535044 | DN391B LED12/830 P10PSU D100 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401535544 | DN391B LED12/865 PSU D100 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401535644 | DN391B LED12/840 PSU D100 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401535744 | DN391B LED12/830 PSU D100 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401536144 | DN390B LED7/865 P6PSU D100 WH GMG2HE     | Yes             | -                    | Yes         |
| 911401536244 | DN390B LED7/840 P6PSU D100 WH GMG2HE     | Yes             | -                    | Yes         |
| 911401536344 | DN390B LED7/830 P6PSU D100 WH GMG2HE     | Yes             | -                    | Yes         |
| 911401536744 | DN390B LED7/865 PSU D100 WH GCG2HE       | Yes             | -                    | Yes         |
| 911401536844 | DN390B LED7/840 PSU D100 WH GCG2HE       | Yes             | -                    | Yes         |
| 911401536944 | DN390B LED7/830 PSU D100 WH GCG2HE       | Yes             | -                    | Yes         |
| 911401537544 | DN391X LED15/865 P12WIA D100 WH G2HE     | Yes             | -                    | Yes         |
| 911401538144 | DN391X LED15/830 P12WIA D100 WH G2HE     | Yes             | -                    | Yes         |
| 911401538744 | DN391X LED15/840 P12WIA D100WH G2HE      | Yes             | -                    | Yes         |
| 911401578244 | DN391B LED15/865 P12PSD D100 WH GMG2HE   | No              | -                    | Yes         |
| 911401578344 | DN391B LED15/840 P12PSD D100 WH GMG2HE   | No              | -                    | Yes         |
| 911401578444 | DN391B LED15/830 P12PSD D100 WH GMG2HE   | No              | -                    | Yes         |
| 911401578844 | DN391B LED15/865 PSD D100 WH GCG2HE      | No              | -                    | Yes         |
| 911401578944 | DN391B LED15/840 PSD D100 WH GCG2HE      | No              | -                    | Yes         |
| 911401579044 | DN391B LED15/830 PSD D100 WH GCG2HE      | No              | -                    | Yes         |
| 911401579444 | DN391B LED12/865 P10PSD D100 WH GMG2HE   | No              | -                    | Yes         |
| 911401579544 | DN391B LED12/840 P10PSD D100 WH GMG2HE   | No              | -                    | Yes         |
| 911401579644 | DN391B LED12/830 P10PSD D100 WH GMG2HE   | No              | -                    | Yes         |
| 911401580044 | DN391B LED12/865 PSD D100 WH GCG2HE      | No              | -                    | Yes         |
| 911401580144 | DN391B LED12/840 PSD D100 WH GCG2HE      | No              | -                    | Yes         |
| 911401580244 | DN391B LED12/830 PSD D100 WH GCG2HE      | No              | -                    | Yes         |
| 911401584832 | DN390B LED6/840 P8PSU D100 WH CAUG2      | Yes             | -                    | Yes         |
| 911401587632 | DN390B LED6/840 P8PSU D100 WH WP CAUG2   | Yes             | -                    | Yes         |
| 911401503645 | DN392X LED16/9TNW P15PSD D150 AL WP G2   | Yes             | 1 unit               | -           |
| 911401521944 | DN392B LED20/865 P16PSU D150 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401522044 | DN392B LED20/840 P16PSU D150 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401522144 | DN392B LED20/830 P16PSU D150 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401522244 | DN392B LED20/865 PSU D150 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401522344 | DN392B LED20/840 PSU D150 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401522444 | DN392B LED20/830 PSU D150 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401523144 | DN392B LED18/865 P14PSU D150 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401523244 | DN392B LED18/840 P14PSU D150 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401523344 | DN392B LED18/830 P14PSU D150 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401523444 | DN392B LED18/865 PSU D150 AL WP GCG2HE   | Yes             | -                    | Yes         |

| Order Code   | Full Product Name                        | Driver included | Number of gear units | Service tag |
|--------------|------------------------------------------|-----------------|----------------------|-------------|
| 911401523544 | DN392B LED18/840 PSU D150 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401523644 | DN392B LED18/830 PSU D150 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401523744 | DN391B LED12/865 P10PSU D150 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401523844 | DN391B LED12/840 P10PSU D150 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401523944 | DN391B LED12/830 P10PSU D150 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401524044 | DN391B LED12/865 PSU D150 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401524144 | DN391B LED12/840 PSU D150 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401524244 | DN391B LED12/830 PSU D150 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401528544 | DN392B LED20/865 P16PSU D150 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401528644 | DN392B LED20/840 P16PSU D150 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401528744 | DN392B LED20/830 P16PSU D150 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401529144 | DN392B LED20/865 PSU D150 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401529244 | DN392B LED20/840 PSU D150 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401529344 | DN392B LED20/830 PSU D150 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401530944 | DN392B LED18/865 P14PSU D150 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401531044 | DN392B LED18/840 P14PSU D150 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401531144 | DN392B LED18/830 P14PSU D150 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401531544 | DN392B LED18/865 PSU D150 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401531644 | DN392B LED18/840 PSU D150 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401531744 | DN392B LED18/830 PSU D150 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401532144 | DN391B LED12/865 P10PSU D150 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401532244 | DN391B LED12/840 P10PSU D150 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401532344 | DN391B LED12/830 P10PSU D150 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401532744 | DN391B LED12/865 PSU D150 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401532844 | DN391B LED12/840 PSU D150 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401532944 | DN391B LED12/830 PSU D150 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401537244 | DN392X LED18/865 P15WIA D150 AL G2HE     | Yes             | -                    | Yes         |
| 911401537844 | DN392X LED18/830 P15WIA D150 AL G2HE     | Yes             | -                    | Yes         |
| 911401538444 | DN392X LED18/840 P15WIA D150 AL G2HE     | Yes             | -                    | Yes         |
| 911401565944 | DN392B LED18/865 P14PSD D150 ALWP GMG2HE | No              | -                    | Yes         |
| 911401566044 | DN392B LED18/840 P14PSD D150 ALWP GMG2HE | No              | -                    | Yes         |
| 911401566144 | DN392B LED18/830 P14PSD D150 ALWP GMG2HE | No              | -                    | Yes         |
| 911401566244 | DN392B LED18/865 P14PSD D150 AL GMG2HE   | No              | -                    | Yes         |
| 911401566344 | DN392B LED18/840 P14PSD D150 AL GMG2HE   | No              | -                    | Yes         |
| 911401566444 | DN392B LED18/830 P14PSD D150 AL GMG2HE   | No              | -                    | Yes         |
| 911401568044 | DN392B LED22/865 P17PSD D150 ALWP GMG2HE | No              | -                    | Yes         |
| 911401568144 | DN392B LED22/840 P17PSD D150 ALWP GMG2HE | No              | -                    | Yes         |
| 911401568244 | DN392B LED22/830 P17PSD D150 ALWP GMG2HE | No              | -                    | Yes         |
| 911401568344 | DN392B LED22/865 PSD D150 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401568444 | DN392B LED22/840 PSD D150 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401568544 | DN392B LED22/830 PSD D150 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401569244 | DN392B LED18/865 PSD D150 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401569344 | DN392B LED18/840 PSD D150 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401569444 | DN392B LED18/830 PSD D150 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401569544 | DN391B LED12/865 P11PSD D150 ALWP GMG2HE | No              | -                    | Yes         |
| 911401569644 | DN391B LED12/840 P11PSD D150 ALWP GMG2HE | No              | -                    | Yes         |
| 911401569744 | DN391B LED12/830 P11PSD D150 ALWP GMG2HE | No              | -                    | Yes         |
| 911401569844 | DN391B LED12/865 PSD D150 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401569944 | DN391B LED12/840 PSD D150 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401570044 | DN391B LED12/830 PSD D150 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401573744 | DN392B LED22/865 P17PSD D150 AL GMG2HE   | No              | -                    | Yes         |

| Order Code   | Full Product Name                        | Driver included | Number of gear units | Service tag |
|--------------|------------------------------------------|-----------------|----------------------|-------------|
| 911401573844 | DN392B LED22/840 P17PSD D150 AL GMG2HE   | No              | -                    | Yes         |
| 911401573944 | DN392B LED22/830 P17PSD D150 AL GMG2HE   | No              | -                    | Yes         |
| 911401574344 | DN392B LED22/865 PSD D150 AL GCG2HE      | No              | -                    | Yes         |
| 911401574444 | DN392B LED22/840 PSD D150 AL GCG2HE      | No              | -                    | Yes         |
| 911401574544 | DN392B LED22/830 PSD D150 AL GCG2HE      | No              | -                    | Yes         |
| 911401576144 | DN392B LED18/865 PSD D150 AL GCG2HE      | No              | -                    | Yes         |
| 911401576244 | DN392B LED18/840 PSD D150 AL GCG2HE      | No              | -                    | Yes         |
| 911401576344 | DN392B LED18/830 PSD D150 AL GCG2HE      | No              | -                    | Yes         |
| 911401576744 | DN391B LED12/865 P11PSD D150 AL GMG2HE   | No              | -                    | Yes         |
| 911401576844 | DN391B LED12/840 P11PSD D150 AL GMG2HE   | No              | -                    | Yes         |
| 911401576944 | DN391B LED12/830 P11PSD D150 AL GMG2HE   | No              | -                    | Yes         |
| 911401577344 | DN391B LED12/865 PSD D150 AL GCG2HE      | No              | -                    | Yes         |
| 911401577444 | DN391B LED12/840 PSD D150 AL GCG2HE      | No              | -                    | Yes         |
| 911401577544 | DN391B LED12/830 PSD D150 AL GCG2HE      | No              | -                    | Yes         |
| 911401577142 | DN393X LED22/840 P20L1W D200 AL CAUG2    | Yes             | -                    | Yes         |
| 911401577442 | DN392X LED17/840 P15L1W D150 AL CAUG2    | Yes             | -                    | Yes         |
| 911401503745 | DN391X LED7/9TNW P7PSD D100 AL WP G2     | Yes             | 1 unit               | -           |
| 911401524344 | DN391B LED14/865 P11PSU D100 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401524444 | DN391B LED14/840 P11PSU D100 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401524544 | DN391B LED14/830 P11PSU D100 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401524644 | DN391B LED14/865 PSU D100 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401524744 | DN391B LED14/840 PSU D100 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401524844 | DN391B LED14/830 PSU D100 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401524944 | DN391B LED12/865 P10PSU D100 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401525044 | DN391B LED12/840 P10PSU D100 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401525144 | DN391B LED12/830 P10PSU D100 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401525244 | DN391B LED12/865 PSU D100 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401525344 | DN391B LED12/840 PSU D100 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401525444 | DN391B LED12/830 PSU D100 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401525544 | DN390B LED7/865 P6PSU D100 AL WP GMG2HE  | Yes             | -                    | Yes         |
| 911401525644 | DN390B LED7/840 P6PSU D100 AL WP GMG2HE  | Yes             | -                    | Yes         |
| 911401525744 | DN390B LED7/830 P6PSU D100 AL WP GMG2HE  | Yes             | -                    | Yes         |
| 911401525844 | DN390B LED7/865 PSU D100 AL WP GCG2HE    | Yes             | -                    | Yes         |
| 911401525944 | DN390B LED7/840 PSU D100 AL WP GCG2HE    | Yes             | -                    | Yes         |
| 911401526044 | DN390B LED7/830 PSU D100 AL WP GCG2HE    | Yes             | -                    | Yes         |
| 911401533344 | DN391B LED14/865 P11PSU D100 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401533444 | DN391B LED14/840 P11PSU D100 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401533544 | DN391B LED14/830 P11PSU D100 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401533944 | DN391B LED14/865 PSU D100 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401534044 | DN391B LED14/840 PSU D100 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401534144 | DN391B LED14/830 PSU D100 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401534544 | DN391B LED12/865 P10PSU D100 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401534644 | DN391B LED12/840 P10PSU D100 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401534744 | DN391B LED12/830 P10PSU D100 AL GMG2HE   | Yes             | -                    | Yes         |
| 911401535144 | DN391B LED12/865 PSU D100 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401535244 | DN391B LED12/840 PSU D100 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401535444 | DN391B LED12/830 PSU D100 AL GCG2HE      | Yes             | -                    | Yes         |
| 911401535844 | DN390B LED7/865 P6PSU D100 AL GMG2HE     | Yes             | -                    | Yes         |
| 911401535944 | DN390B LED7/840 P6PSU D100 AL GMG2HE     | Yes             | -                    | Yes         |
| 911401536044 | DN390B LED7/830 P6PSU D100 AL GMG2HE     | Yes             | -                    | Yes         |
| 911401536444 | DN390B LED7/865 PSU D100 AL GCG2HE       | Yes             | -                    | Yes         |

| Order Code   | Full Product Name                        | Driver included | Number of gear units | Service tag |
|--------------|------------------------------------------|-----------------|----------------------|-------------|
| 911401536544 | DN390B LED7/840 PSU D100 AL GCG2HE       | Yes             | -                    | Yes         |
| 911401536644 | DN390B LED7/830 PSU D100 AL GCG2HE       | Yes             | -                    | Yes         |
| 911401537444 | DN391X LED14/865 P12WIA D100 AL G2HE     | Yes             | -                    | Yes         |
| 911401538044 | DN391X LED14/830 P12WIA D100 AL G2HE     | Yes             | -                    | Yes         |
| 911401538644 | DN391X LED14/840 P12WIA D100 AL G2HE     | Yes             | -                    | Yes         |
| 911401570144 | DN391B LED14/865 P12PSD D100 ALWP GMG2HE | No              | -                    | Yes         |
| 911401570244 | DN391B LED14/840 P12PSD D100 ALWP GMG2HE | No              | -                    | Yes         |
| 911401570344 | DN391B LED14/830 P12PSD D100 ALWP GMG2HE | No              | -                    | Yes         |
| 911401570444 | DN391B LED14/865 PSD D100 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401570544 | DN391B LED14/840 PSD D100 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401570644 | DN391B LED14/830 PSD D100 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401570744 | DN391B LED12/865 P10PSD D100 ALWP GMG2HE | No              | -                    | Yes         |
| 911401570844 | DN391B LED12/840 P10PSD D100 ALWP GMG2HE | No              | -                    | Yes         |
| 911401570944 | DN391B LED12/830 P10PSD D100 ALWP GMG2HE | No              | -                    | Yes         |
| 911401571044 | DN391B LED12/865 PSD D100 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401571144 | DN391B LED12/840 PSD D100 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401571244 | DN391B LED12/830 PSD D100 AL WP GCG2HE   | No              | -                    | Yes         |
| 911401577944 | DN391B LED14/865 P12PSD D100 AL GMG2HE   | No              | -                    | Yes         |
| 911401578044 | DN391B LED14/840 P12PSD D100 AL GMG2HE   | No              | -                    | Yes         |
| 911401578144 | DN391B LED14/830 P12PSD D100 AL GMG2HE   | No              | -                    | Yes         |
| 911401578544 | DN391B LED14/865 PSD D100 AL GCG2HE      | No              | -                    | Yes         |
| 911401578644 | DN391B LED14/840 PSD D100 AL GCG2HE      | No              | -                    | Yes         |
| 911401578744 | DN391B LED14/830 PSD D100 AL GCG2HE      | No              | -                    | Yes         |
| 911401579144 | DN391B LED12/865 P10PSD D100 AL GMG2HE   | No              | -                    | Yes         |
| 911401579244 | DN391B LED12/840 P10PSD D100 AL GMG2HE   | No              | -                    | Yes         |
| 911401579344 | DN391B LED12/830 P10PSD D100 AL GMG2HE   | No              | -                    | Yes         |
| 911401579744 | DN391B LED12/865 PSD D100 AL GCG2HE      | No              | -                    | Yes         |
| 911401579844 | DN391B LED12/840 PSD D100 AL GCG2HE      | No              | -                    | Yes         |
| 911401579944 | DN391B LED12/830 PSD D100 AL GCG2HE      | No              | -                    | Yes         |
| 911401503845 | DN394X LED34/9TNW P27PSD D200 WH WP G2   | Yes             | 1 unit               | -           |
| 911401504145 | DN394X LED34/9TNW P27PSD D200 WH WPCAUG2 | Yes             | 1 unit               | -           |
| 911401519944 | DN393B LED26/840 P20PSU D200WHWP CAUG2HE | Yes             | -                    | Yes         |
| 911401520344 | DN393B LED26/840 P20PSU D200 WH CAUG2HE  | Yes             | -                    | Yes         |
| 911401526444 | DN394B LED40/865 P29PSU D200 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401526544 | DN394B LED40/840 P29PSU D200 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401526644 | DN394B LED40/830 P29PSU D200 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401527044 | DN394B LED40/865 PSU D200 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401527144 | DN394B LED40/840 PSU D200 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401527244 | DN394B LED40/830 PSU D200 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401527644 | DN393B LED26/865 P19PSU D200 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401527744 | DN393B LED26/840 P19PSU D200 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401527844 | DN393B LED26/830 P19PSU D200 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401528244 | DN393B LED26/865 PSU D200 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401528344 | DN393B LED26/840 PSU D200 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401528444 | DN393B LED26/830 PSU D200 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401530044 | DN392B LED20/865 P14PSU D200 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401530144 | DN392B LED20/840 P14PSU D200 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401530244 | DN392B LED20/830 P14PSU D200 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401530644 | DN392B LED20/865 PSU D200 WH GCG2HE      | Yes             | -                    | Yes         |

| Order Code   | Full Product Name                        | Driver included | Number of gear units | Service tag |
|--------------|------------------------------------------|-----------------|----------------------|-------------|
| 911401530744 | DN392B LED20/840 PSU D200 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401530844 | DN392B LED20/830 PSU D200 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401537144 | DN393X LED26/865 P20WIA D200 WH G2HE     | Yes             | -                    | Yes         |
| 911401537744 | DN393X LED26/830 P20WIA D200 WH G2HE     | Yes             | -                    | Yes         |
| 911401538344 | DN393X LED26/840 P20WIA D200 WH G2HE     | Yes             | -                    | Yes         |
| 911401571644 | DN394B LED40/865 P29PSD D200 WH GMG2HE   | No              | -                    | Yes         |
| 911401571744 | DN394B LED40/840 P29PSD D200 WH GMG2HE   | No              | -                    | Yes         |
| 911401571844 | DN394B LED40/830 P29PSD D200 WH GMG2HE   | No              | -                    | Yes         |
| 911401572244 | DN394B LED40/865 PSD D200 WH GCG2HE      | No              | -                    | Yes         |
| 911401572344 | DN394B LED40/840 PSD D200 WH GCG2HE      | No              | -                    | Yes         |
| 911401572444 | DN394B LED40/830 PSD D200 WH GCG2HE      | No              | -                    | Yes         |
| 911401572844 | DN393B LED26/865 P20PSD D200 WH GMG2HE   | No              | -                    | Yes         |
| 911401572944 | DN393B LED26/840 P20PSD D200 WH GMG2HE   | No              | -                    | Yes         |
| 911401573044 | DN393B LED26/830 P20PSD D200 WH GMG2HE   | No              | -                    | Yes         |
| 911401573444 | DN393B LED26/865 PSD D200 WH GCG2HE      | No              | -                    | Yes         |
| 911401573544 | DN393B LED26/840 PSD D200 WH GCG2HE      | No              | -                    | Yes         |
| 911401573644 | DN393B LED26/830 PSD D200 WH GCG2HE      | No              | -                    | Yes         |
| 911401575244 | DN392B LED18/865 P14PSD D200 WH GMG2HE   | No              | -                    | Yes         |
| 911401575344 | DN392B LED18/840 P14PSD D200 WH GMG2HE   | No              | -                    | Yes         |
| 911401575444 | DN392B LED18/830 P14PSD D200 WH GMG2HE   | No              | -                    | Yes         |
| 911401575844 | DN392B LED18/865 PSD D200 WH GCG2HE      | No              | -                    | Yes         |
| 911401575944 | DN392B LED18/840 PSD D200 WH GCG2HE      | No              | -                    | Yes         |
| 911401576044 | DN392B LED18/830 PSD D200 WH GCG2HE      | No              | -                    | Yes         |
| 911401586932 | DN393B LED22/840 P20PSU D200 WH CAUG2    | Yes             | -                    | Yes         |
| 911401588632 | DN393B LED22/840 P20PSU D200 WH WP CAUG2 | Yes             | -                    | Yes         |
| 911401503545 | DN394X LED33/9TNW P27PSD D200 AL WP G2   | Yes             | 1 unit               | -           |
| 911401520744 | DN394B LED38/865 P29PSU D200 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401520844 | DN394B LED38/840 P29PSU D200 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401520944 | DN394B LED38/830 P29PSU D200 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401521044 | DN394B LED38/865 PSU D200 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401521144 | DN394B LED38/840 PSU D200 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401521244 | DN394B LED38/830 PSU D200 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401521344 | DN393B LED25/865 P19PSU D200 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401521444 | DN393B LED25/840 P19PSU D200 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401521544 | DN393B LED25/830 P19PSU D200 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401521644 | DN393B LED25/865 PSU D200 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401521744 | DN393B LED25/840 PSU D200 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401521844 | DN393B LED25/830 PSU D200 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401522544 | DN392B LED18/865 P14PSU D200 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401522644 | DN392B LED18/840 P14PSU D200 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401522744 | DN392B LED18/830 P14PSU D200 ALWP GMG2HE | Yes             | -                    | Yes         |
| 911401522844 | DN392B LED18/865 PSU D200 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401522944 | DN392B LED18/840 PSU D200 AL WP GCG2HE   | Yes             | -                    | Yes         |
| 911401523044 | DN392B LED18/830 PSU D200 AL WP GCG2HE   | Yes             | -                    | Yes         |

| Order Code   | Full Product Name                           | Driver included | Number of gear units | Service tag |
|--------------|---------------------------------------------|-----------------|----------------------|-------------|
| 911401526144 | DN394B LED38/865 P29PSU D200 AL GMG2HE      | Yes             | -                    | Yes         |
| 911401526244 | DN394B LED38/840 P29PSU D200 AL GMG2HE      | Yes             | -                    | Yes         |
| 911401526344 | DN394B LED38/830 P29PSU D200 AL GMG2HE      | Yes             | -                    | Yes         |
| 911401526744 | DN394B LED38/865 PSU D200 AL GCG2HE         | Yes             | -                    | Yes         |
| 911401526844 | DN394B LED38/840 PSU D200 AL GCG2HE         | Yes             | -                    | Yes         |
| 911401526944 | DN394B LED38/830 PSU D200 AL GCG2HE         | Yes             | -                    | Yes         |
| 911401527344 | DN393B LED25/865 P19PSU D200 AL GMG2HE      | Yes             | -                    | Yes         |
| 911401527444 | DN393B LED25/840 P19PSU D200 AL GMG2HE      | Yes             | -                    | Yes         |
| 911401527544 | DN393B LED25/830 P19PSU D200 AL GMG2HE      | Yes             | -                    | Yes         |
| 911401527944 | DN393B LED25/865 PSU D200 AL GCG2HE         | Yes             | -                    | Yes         |
| 911401528044 | DN393B LED25/840 PSU D200 AL GCG2HE         | Yes             | -                    | Yes         |
| 911401528144 | DN393B LED25/830 PSU D200 AL GCG2HE         | Yes             | -                    | Yes         |
| 911401529744 | DN392B LED18/865 P14PSU D200 AL GMG2HE      | Yes             | -                    | Yes         |
| 911401529844 | DN392B LED18/840 P14PSU D200 AL GMG2HE      | Yes             | -                    | Yes         |
| 911401529944 | DN392B LED18/830 P14PSU D200 AL GMG2HE      | Yes             | -                    | Yes         |
| 911401530344 | DN392B LED18/865 PSU D200 AL GCG2HE         | Yes             | -                    | Yes         |
| 911401530444 | DN392B LED18/840 PSU D200 AL GCG2HE         | Yes             | -                    | Yes         |
| 911401530544 | DN392B LED18/830 PSU D200 AL GCG2HE         | Yes             | -                    | Yes         |
| 911401537044 | DN393X LED25/865 P20WIA D200 AL G2HE        | Yes             | -                    | Yes         |
| 911401537644 | DN393X LED25/830 P20WIA D200 AL G2HE        | Yes             | -                    | Yes         |
| 911401538244 | DN393X LED25/840 P20WIA D200 AL G2HE        | Yes             | -                    | Yes         |
| 911401566844 | DN394B LED38/865 P29PSD D200 ALWP<br>GMG2HE | No              | -                    | Yes         |
| 911401566944 | DN394B LED38/840 P29PSD D200 ALWP<br>GMG2HE | No              | -                    | Yes         |
| 911401567044 | DN394B LED38/830 P29PSD D200 ALWP<br>GMG2HE | No              | -                    | Yes         |
| 911401567144 | DN394B LED38/865 PSD D200 AL WP GCG2HE      | No              | -                    | Yes         |
| 911401567244 | DN394B LED38/840 PSD D200 AL WP GCG2HE      | No              | -                    | Yes         |
| 911401567344 | DN394B LED38/830 PSD D200 AL WP GCG2HE      | No              | -                    | Yes         |
| 911401567444 | DN393B LED25/865 P20PSD D200 ALWP<br>GMG2HE | No              | -                    | Yes         |
| 911401567544 | DN393B LED25/840 P20PSD D200 ALWP<br>GMG2HE | No              | -                    | Yes         |
| 911401567644 | DN393B LED25/830 P20PSD D200 ALWP<br>GMG2HE | No              | -                    | Yes         |
| 911401567744 | DN393B LED25/865 PSD D200 AL WP GCG2HE      | No              | -                    | Yes         |
| 911401567844 | DN393B LED25/840 PSD D200 AL WP GCG2HE      | No              | -                    | Yes         |
| 911401567944 | DN393B LED25/830 PSD D200 AL WP GCG2HE      | No              | -                    | Yes         |
| 911401568644 | DN392B LED18/865 P14PSD D200 ALWP GMG2HE    | No              | -                    | Yes         |
| 911401568744 | DN392B LED18/840 P14PSD D200 ALWP<br>GMG2HE | No              | -                    | Yes         |
| 911401568844 | DN392B LED18/830 P14PSD D200 ALWP<br>GMG2HE | No              | -                    | Yes         |
| 911401568944 | DN392B LED18/865 PSD D200 AL WP GCG2HE      | No              | -                    | Yes         |
| 911401569044 | DN392B LED18/840 PSD D200 AL WP GCG2HE      | No              | -                    | Yes         |
| 911401569144 | DN392B LED18/830 PSD D200 AL WP GCG2HE      | No              | -                    | Yes         |
| 911401571344 | DN394B LED38/865 P29PSD D200 AL GMG2HE      | No              | -                    | Yes         |
| 911401571444 | DN394B LED38/840 P29PSD D200 AL GMG2HE      | No              | -                    | Yes         |
| 911401571544 | DN394B LED38/830 P29PSD D200 AL GMG2HE      | No              | -                    | Yes         |
| 911401571944 | DN394B LED38/865 PSD D200 AL GCG2HE         | No              | -                    | Yes         |

| Order Code   | Full Product Name                        | Driver included | Number of gear units | Service tag |
|--------------|------------------------------------------|-----------------|----------------------|-------------|
| 911401572044 | DN394B LED38/840 PSD D200 AL GCG2HE      | No              | -                    | Yes         |
| 911401572144 | DN394B LED38/830 PSD D200 AL GCG2HE      | No              | -                    | Yes         |
| 911401572544 | DN393B LED25/865 P20PSD D200 AL GMG2HE   | No              | -                    | Yes         |
| 911401572644 | DN393B LED25/840 P20PSD D200 AL GMG2HE   | No              | -                    | Yes         |
| 911401572744 | DN393B LED25/830 P20PSD D200 AL GMG2HE   | No              | -                    | Yes         |
| 911401573144 | DN393B LED25/865 PSD D200 AL GCG2HE      | No              | -                    | Yes         |
| 911401573244 | DN393B LED25/840 PSD D200 AL GCG2HE      | No              | -                    | Yes         |
| 911401573344 | DN393B LED25/830 PSD D200 AL GCG2HE      | No              | -                    | Yes         |
| 911401574944 | DN392B LED18/865 P14PSD D200 AL GMG2HE   | No              | -                    | Yes         |
| 911401575044 | DN392B LED18/840 P14PSD D200 AL GMG2HE   | No              | -                    | Yes         |
| 911401575144 | DN392B LED18/830 P14PSD D200 AL GMG2HE   | No              | -                    | Yes         |
| 911401575544 | DN392B LED18/865 PSD D200 AL GCG2HE      | No              | -                    | Yes         |
| 911401575644 | DN392B LED18/840 PSD D200 AL GCG2HE      | No              | -                    | Yes         |
| 911401575744 | DN392B LED18/830 PSD D200 AL GCG2HE      | No              | -                    | Yes         |
| 911401577042 | DN393X LED22/840 P20L1W D200 WH CAUG2    | Yes             | -                    | Yes         |
| 911401577542 | DN392X LED17/840 P15L1W D150 WH CAUG2    | Yes             | -                    | Yes         |
| 911401503945 | DN392X LED17/9TNW P15PSD D150 WH WP G2   | Yes             | 1 unit               | -           |
| 911401504245 | DN392X LED17/9TNW P15PSD D150 WH WPCAUG2 | Yes             | 1 unit               | -           |
| 911401520044 | DN392B LED20/840 P15PSU D150WHWP CAUG2HE | Yes             | -                    | Yes         |
| 911401520144 | DN391B LED13/840 P11PSU D150WHWP CAUG2HE | Yes             | -                    | Yes         |
| 911401520444 | DN392B LED20/840 P15PSU D150 WH CAUG2HE  | Yes             | -                    | Yes         |
| 911401520544 | DN391B LED13/840 P11PSU D150 WH CAUG2HE  | Yes             | -                    | Yes         |
| 911401528844 | DN392B LED22/865 P16PSU D150 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401528944 | DN392B LED22/840 P16PSU D150 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401529044 | DN392B LED22/830 P16PSU D150 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401529444 | DN392B LED22/865 PSU D150 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401529544 | DN392B LED22/840 PSU D150 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401529644 | DN392B LED22/830 PSU D150 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401531244 | DN392B LED20/865 P14PSU D150 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401531344 | DN392B LED20/840 P14PSU D150 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401531444 | DN392B LED20/830 P14PSU D150 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401531844 | DN392B LED20/865 PSU D150 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401531944 | DN392B LED20/840 PSU D150 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401532044 | DN392B LED20/830 PSU D150 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401532444 | DN391B LED13/865 P10PSU D150 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401532544 | DN391B LED13/840 P10PSU D150 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401532644 | DN391B LED13/830 P10PSU D150 WH GMG2HE   | Yes             | -                    | Yes         |
| 911401533044 | DN391B LED13/865 PSU D150 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401533144 | DN391B LED13/840 PSU D150 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401533244 | DN391B LED13/830 PSU D150 WH GCG2HE      | Yes             | -                    | Yes         |
| 911401537344 | DN392X LED20/865 P15WIA D150 WH G2HE     | Yes             | -                    | Yes         |
| 911401537944 | DN392X LED20/830 P15WIA D150 WH G2HE     | Yes             | -                    | Yes         |
| 911401538544 | DN392X LED20/840 P15WIA D150 WH G2HE     | Yes             | -                    | Yes         |
| 911401566544 | DN392B LED19/865 P14PSD D150 WH GMG2HE   | No              | -                    | Yes         |
| 911401566644 | DN392B LED19/840 P14PSD D150 WH GMG2HE   | No              | -                    | Yes         |
| 911401566744 | DN392B LED19/830 P14PSD D150 WH GMG2HE   | No              | -                    | Yes         |
| 911401574044 | DN392B LED23/865 P17PSD D150 WH GMG2HE   | No              | -                    | Yes         |
| 911401574144 | DN392B LED23/840 P17PSD D150 WH GMG2HE   | No              | -                    | Yes         |
| 911401574244 | DN392B LED23/830 P17PSD D150 WH GMG2HE   | No              | -                    | Yes         |

| Order Code   | Full Product Name                        | Driver included | Number of gear units | Service tag |
|--------------|------------------------------------------|-----------------|----------------------|-------------|
| 911401574644 | DN392B LED23/865 PSD D150 WH GCG2HE      | No              | -                    | Yes         |
| 911401574744 | DN392B LED23/840 PSD D150 WH GCG2HE      | No              | -                    | Yes         |
| 911401574844 | DN392B LED23/830 PSD D150 WH GCG2HE      | No              | -                    | Yes         |
| 911401576444 | DN392B LED19/865 PSD D150 WH GCG2HE      | No              | -                    | Yes         |
| 911401576544 | DN392B LED19/840 PSD D150 WH GCG2HE      | No              | -                    | Yes         |
| 911401576644 | DN392B LED19/830 PSD D150 WH GCG2HE      | No              | -                    | Yes         |
| 911401577044 | DN391B LED13/865 P11PSD D150 WH GMG2HE   | No              | -                    | Yes         |
| 911401577144 | DN391B LED13/840 P11PSD D150 WH GMG2HE   | No              | -                    | Yes         |
| 911401577244 | DN391B LED13/830 P11PSD D150 WH GMG2HE   | No              | -                    | Yes         |
| 911401577644 | DN391B LED13/865 PSD D150 WH GCG2HE      | No              | -                    | Yes         |
| 911401577744 | DN391B LED13/840 PSD D150 WH GCG2HE      | No              | -                    | Yes         |
| 911401577844 | DN391B LED13/830 PSD D150 WH GCG2HE      | No              | -                    | Yes         |
| 911401585532 | DN391B LED11/840 P11PSU D150 WH CAUG2    | Yes             | -                    | Yes         |
| 911401585632 | DN392B LED17/840 P15PSU D150 WH CAUG2    | Yes             | -                    | Yes         |
| 911401587832 | DN391B LED11/840 P11PSU D150 WH WP CAUG2 | Yes             | -                    | Yes         |
| 911401587932 | DN392B LED17/840 P15PSU D150 WH WP CAUG2 | Yes             | -                    | Yes         |

Light Technical (1/2)

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401504045 | DN391X<br>LED8/9TNW<br>P7PSD D100 WH<br>WP G2   | -<br>degree(s)             | Tunable white<br>2700-6500 K       | ≥90                         | 115 lm/W                        | 911401534244 | DN391B<br>LED15/865 PSU<br>D100 WH<br>GCG2HE    | -                          | 6500 K                             | >80                         | 130 lm/W                        |
| 911401504345 | DN391X<br>LED8/9TNW<br>P7PSD D100 WH<br>WPCAUG2 | -<br>degree(s)             | Tunable white<br>2700-6500 K       | ≥90                         | 115 lm/W                        | 911401534344 | DN391B<br>LED15/840 PSU<br>D100 WH<br>GCG2HE    | -                          | 4000 K                             | >80                         | 130 lm/W                        |
| 911401520244 | DN390B<br>LED7/840 P6PSU<br>D100WHWP<br>CAUG2HE | -                          | 4000 K                             | >80                         | 130 lm/W                        | 911401534444 | DN391B<br>LED15/830 PSU<br>D100 WH<br>GCG2HE    | -                          | 3000 K                             | >80                         | 120 lm/W                        |
| 911401520644 | DN390B<br>LED7/840 P6PSU<br>D100 WH<br>CAUG2HE  | -                          | 4000 K                             | >80                         | 130 lm/W                        | 911401534844 | DN391B<br>LED12/865<br>P10PSU D100 WH<br>GMG2HE | -                          | 6500 K                             | >80                         | 130 lm/W                        |
| 911401533644 | DN391B<br>LED15/865<br>P11PSU D100 WH<br>GMG2HE | -                          | 6500 K                             | >80                         | 130 lm/W                        | 911401534944 | DN391B<br>LED12/840<br>P10PSU D100 WH<br>GMG2HE | -                          | 4000 K                             | >80                         | 130 lm/W                        |
| 911401533744 | DN391B<br>LED15/840<br>P11PSU D100 WH<br>GMG2HE | -                          | 4000 K                             | >80                         | 130 lm/W                        | 911401535044 | DN391B<br>LED12/830<br>P10PSU D100 WH<br>GMG2HE | -                          | 3000 K                             | >80                         | 120 lm/W                        |
| 911401533844 | DN391B<br>LED15/830<br>P11PSU D100 WH<br>GMG2HE | -                          | 3000 K                             | >80                         | 120 lm/W                        | 911401535544 | DN391B<br>LED12/865 PSU<br>D100 WH<br>GCG2HE    | -                          | 6500 K                             | >80                         | 130 lm/W                        |

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401535644 | DN391B<br>LED12/840 PSU<br>D100 WH<br>GCG2HE    | -                          | 4000 K                             | >80                         | 130 lm/W                        |
| 911401535744 | DN391B<br>LED12/830 PSU<br>D100 WH<br>GCG2HE    | -                          | 3000 K                             | >80                         | 120 lm/W                        |
| 911401536144 | DN390B<br>LED7/865 P6PSU<br>D100 WH<br>GMG2HE   | -                          | 6500 K                             | >80                         | 130 lm/W                        |
| 911401536244 | DN390B<br>LED7/840 P6PSU<br>D100 WH<br>GMG2HE   | -                          | 4000 K                             | >80                         | 130 lm/W                        |
| 911401536344 | DN390B<br>LED7/830 P6PSU<br>D100 WH<br>GMG2HE   | -                          | 3000 K                             | >80                         | 120 lm/W                        |
| 911401536744 | DN390B<br>LED7/865 PSU<br>D100 WH<br>GCG2HE     | -                          | 6500 K                             | >80                         | 130 lm/W                        |
| 911401536844 | DN390B<br>LED7/840 PSU<br>D100 WH<br>GCG2HE     | -                          | 4000 K                             | >80                         | 130 lm/W                        |
| 911401536944 | DN390B<br>LED7/830 PSU<br>D100 WH<br>GCG2HE     | -                          | 3000 K                             | >80                         | 120 lm/W                        |
| 911401537544 | DN391X<br>LED15/865<br>P12WIA D100 WH<br>G2HE   | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401538144 | DN391X<br>LED15/830<br>P12WIA D100 WH<br>G2HE   | -                          | 3000 K                             | >80                         | 116 lm/W                        |
| 911401538744 | DN391X<br>LED15/840<br>P12WIA D100WH<br>G2HE    | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401578244 | DN391B<br>LED15/865<br>P12PSD D100 WH<br>GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 125 lm/W                        |
| 911401578344 | DN391B<br>LED15/840<br>P12PSD D100 WH<br>GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 125 lm/W                        |
| 911401578444 | DN391B<br>LED15/830<br>P12PSD D100 WH<br>GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 116 lm/W                        |
| 911401578844 | DN391B<br>LED15/865 PSD<br>D100 WH<br>GCG2HE    | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 125 lm/W                        |
| 911401578944 | DN391B<br>LED15/840 PSD<br>D100 WH<br>GCG2HE    | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 125 lm/W                        |
| 911401579044 | DN391B<br>LED15/830 PSD<br>D100 WH<br>GCG2HE    | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 116 lm/W                        |
| 911401579444 | DN391B<br>LED12/865<br>P10PSD D100 WH<br>GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 125 lm/W                        |
| 911401579544 | DN391B<br>LED12/840<br>P10PSD D100 WH<br>GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 125 lm/W                        |
| 911401579644 | DN391B<br>LED12/830<br>P10PSD D100 WH<br>GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 116 lm/W                        |
| 911401580044 | DN391B<br>LED12/865 PSD<br>D100 WH<br>GCG2HE    | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 125 lm/W                        |
| 911401580144 | DN391B<br>LED12/840 PSD<br>D100 WH<br>GCG2HE    | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 125 lm/W                        |
| 911401580244 | DN391B<br>LED12/830 PSD<br>D100 WH<br>GCG2HE    | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 116 lm/W                        |
| 911401584832 | DN390B<br>LED6/840 P8PSU<br>D100 WH CAUG2       | - degree(s)                | 4000 K                             | ≥80                         | 103 lm/W                        |
| 911401587632 | DN390B<br>LED6/840 P8PSU                        | - degree(s)                | 4000 K                             | ≥80                         | 103 lm/W                        |

| Order Code   | Full Product Name                        | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
|              | D100 WH WP CAUG2                         |                            |                                    |                             |                                 |
| 911401503645 | DN392X LED16/9TNW P15PSD D150 AL WP G2   | - degree(s)                | Tunable white 2700-6500 K          | ≥90                         | 115 lm/W                        |
| 911401521944 | DN392B LED20/865 P16PSU D150 ALWP GMG2HE | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401522044 | DN392B LED20/840 P16PSU D150 ALWP GMG2HE | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401522144 | DN392B LED20/830 P16PSU D150 ALWP GMG2HE | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401522244 | DN392B LED20/865 PSU D150 AL WP GCG2HE   | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401522344 | DN392B LED20/840 PSU D150 AL WP GCG2HE   | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401522444 | DN392B LED20/830 PSU D150 AL WP GCG2HE   | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401523144 | DN392B LED18/865 P14PSU D150 ALWP GMG2HE | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401523244 | DN392B LED18/840 P14PSU D150 ALWP GMG2HE | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401523344 | DN392B LED18/830 P14PSU D150 ALWP GMG2HE | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401523444 | DN392B LED18/865 PSU D150 AL WP GCG2HE   | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401523544 | DN392B LED18/840 PSU                     | -                          | 4000 K                             | >80                         | 132 lm/W                        |

| Order Code   | Full Product Name                        | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
|              | D150 AL WP GCG2HE                        |                            |                                    |                             |                                 |
| 911401523644 | DN392B LED18/830 PSU D150 AL WP GCG2HE   | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401523744 | DN391B LED12/865 P10PSU D150 ALWP GMG2HE | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401523844 | DN391B LED12/840 P10PSU D150 ALWP GMG2HE | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401523944 | DN391B LED12/830 P10PSU D150 ALWP GMG2HE | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401524044 | DN391B LED12/865 PSU D150 AL WP GCG2HE   | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401524144 | DN391B LED12/840 PSU D150 AL WP GCG2HE   | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401524244 | DN391B LED12/830 PSU D150 AL WP GCG2HE   | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401528544 | DN392B LED20/865 P16PSU D150 AL GMG2HE   | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401528644 | DN392B LED20/840 P16PSU D150 AL GMG2HE   | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401528744 | DN392B LED20/830 P16PSU D150 AL GMG2HE   | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401529144 | DN392B LED20/865 PSU D150 AL GCG2HE      | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401529244 | DN392B LED20/840 PSU D150 AL GCG2HE      | -                          | 4000 K                             | >80                         | 132 lm/W                        |

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401529344 | DN392B<br>LED20/830 PSU<br>D150 AL GCG2HE       | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401530944 | DN392B<br>LED18/865<br>P14PSU D150 AL<br>GMG2HE | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401531044 | DN392B<br>LED18/840<br>P14PSU D150 AL<br>GMG2HE | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401531144 | DN392B<br>LED18/830<br>P14PSU D150 AL<br>GMG2HE | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401531544 | DN392B<br>LED18/865 PSU<br>D150 AL GCG2HE       | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401531644 | DN392B<br>LED18/840 PSU<br>D150 AL GCG2HE       | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401531744 | DN392B<br>LED18/830 PSU<br>D150 AL GCG2HE       | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401532144 | DN391B<br>LED12/865<br>P10PSU D150 AL<br>GMG2HE | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401532244 | DN391B<br>LED12/840<br>P10PSU D150 AL<br>GMG2HE | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401532344 | DN391B<br>LED12/830<br>P10PSU D150 AL<br>GMG2HE | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401532744 | DN391B<br>LED12/865 PSU<br>D150 AL GCG2HE       | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401532844 | DN391B<br>LED12/840 PSU<br>D150 AL GCG2HE       | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401532944 | DN391B<br>LED13/830 PSU<br>D150 AL GCG2HE       | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401537244 | DN392X<br>LED18/865<br>P15WIA D150 AL<br>G2HE   | -                          | 6500 K                             | >80                         | 130 lm/W                        |

| Order Code   | Full Product Name                                 | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401537844 | DN392X<br>LED18/830<br>P15WIA D150 AL<br>G2HE     | -                          | 3000 K                             | >80                         | 120 lm/W                        |
| 911401538444 | DN392X<br>LED18/840<br>P15WIA D150 AL<br>G2HE     | -                          | 4000 K                             | >80                         | 130 lm/W                        |
| 911401565944 | DN392B<br>LED18/865<br>P14PSD D150<br>ALWP GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401566044 | DN392B<br>LED18/840<br>P14PSD D150<br>ALWP GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401566144 | DN392B<br>LED18/830<br>P14PSD D150<br>ALWP GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401566244 | DN392B<br>LED18/865<br>P14PSD D150 AL<br>GMG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401566344 | DN392B<br>LED18/840<br>P14PSD D150 AL<br>GMG2HE   | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401566444 | DN392B<br>LED18/830<br>P14PSD D150 AL<br>GMG2HE   | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401568044 | DN392B<br>LED22/865<br>P17PSD D150<br>ALWP GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401568144 | DN392B<br>LED22/840<br>P17PSD D150<br>ALWP GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401568244 | DN392B<br>LED22/830<br>P17PSD D150<br>ALWP GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401568344 | DN392B<br>LED22/865 PSD<br>D150 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |

| Order Code   | Full Product Name                                 | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401568444 | DN392B<br>LED22/840 PSD<br>D150 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401568544 | DN392B<br>LED22/830 PSD<br>D150 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401569244 | DN392B<br>LED18/865 PSD<br>D150 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401569344 | DN392B<br>LED18/840 PSD<br>D150 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401569444 | DN392B<br>LED18/830 PSD<br>D150 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401569544 | DN391B<br>LED12/865<br>P11PSD D150<br>ALWP GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401569644 | DN391B<br>LED12/840<br>P11PSD D150<br>ALWP GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401569744 | DN391B<br>LED12/830<br>P11PSD D150<br>ALWP GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401569844 | DN391B<br>LED12/865 PSD<br>D150 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401569944 | DN391B<br>LED12/840 PSD<br>D150 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401570044 | DN391B<br>LED12/830 PSD<br>D150 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401573744 | DN392B<br>LED22/865<br>P17PSD D150 AL<br>GMG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401573844 | DN392B<br>LED22/840<br>P17PSD D150 AL<br>GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401573944 | DN392B<br>LED22/830<br>P17PSD D150 AL<br>GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401574344 | DN392B<br>LED22/865 PSD<br>D150 AL GCG2HE       | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401574444 | DN392B<br>LED22/840 PSD<br>D150 AL GCG2HE       | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401574544 | DN392B<br>LED22/830 PSD<br>D150 AL GCG2HE       | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401576144 | DN392B<br>LED18/865 PSD<br>D150 AL GCG2HE       | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401576244 | DN392B<br>LED18/840 PSD<br>D150 AL GCG2HE       | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401576344 | DN392B<br>LED18/830 PSD<br>D150 AL GCG2HE       | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401576744 | DN391B<br>LED12/865<br>P11PSD D150 AL<br>GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401576844 | DN391B<br>LED12/840<br>P11PSD D150 AL<br>GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401576944 | DN391B<br>LED12/830<br>P11PSD D150 AL<br>GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401577344 | DN391B<br>LED12/865 PSD<br>D150 AL GCG2HE       | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401577444 | DN391B<br>LED12/840 PSD<br>D150 AL GCG2HE       | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401577544 | DN391B<br>LED12/830 PSD<br>D150 AL GCG2HE       | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401577142 | DN393X<br>LED22/840                             | - degree(s)                | 4000 K                             | ≥80                         | 115 lm/W                        |

| Order Code   | Full Product Name                        | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
|              | P20L1W D200 AL CAUG2                     |                            |                                    |                             |                                 |
| 911401577442 | DN392X LED17/840 P15L1W D150 AL CAUG2    | - degree(s)                | 4000 K                             | ≥80                         | 115 lm/W                        |
| 911401503745 | DN391X LED7/9TNW P7PSD D100 AL WP G2     | - degree(s)                | Tunable white 2700-6500 K          | ≥90                         | 110 lm/W                        |
| 911401524344 | DN391B LED14/865 P11PSU D100 ALWP GMG2HE | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401524444 | DN391B LED14/840 P11PSU D100 ALWP GMG2HE | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401524544 | DN391B LED14/830 P11PSU D100 ALWP GMG2HE | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401524644 | DN391B LED14/865 PSU D100 AL WP GCG2HE   | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401524744 | DN391B LED14/840 PSU D100 AL WP GCG2HE   | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401524844 | DN391B LED14/830 PSU D100 AL WP GCG2HE   | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401524944 | DN391B LED12/865 P10PSU D100 ALWP GMG2HE | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401525044 | DN391B LED12/840 P10PSU D100 ALWP GMG2HE | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401525144 | DN391B LED12/830 P10PSU D100 ALWP GMG2HE | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401525244 | DN391B LED12/865 PSU                     | -                          | 6500 K                             | >80                         | 125 lm/W                        |

| Order Code   | Full Product Name                       | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-----------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
|              | D100 AL WP GCG2HE                       |                            |                                    |                             |                                 |
| 911401525344 | DN391B LED12/840 PSU D100 AL WP GCG2HE  | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401525444 | DN391B LED12/830 PSU D100 AL WP GCG2HE  | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401525544 | DN390B LED7/865 P6PSU D100 AL WP GMG2HE | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401525644 | DN390B LED7/840 P6PSU D100 AL WP GMG2HE | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401525744 | DN390B LED7/830 P6PSU D100 AL WP GMG2HE | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401525844 | DN390B LED7/865 PSU D100 AL WP GCG2HE   | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401525944 | DN390B LED7/840 PSU D100 AL WP GCG2HE   | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401526044 | DN390B LED7/830 PSU D100 AL WP GCG2HE   | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401533344 | DN391B LED14/865 P11PSU D100 AL GMG2HE  | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401533444 | DN391B LED14/840 P11PSU D100 AL GMG2HE  | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401533544 | DN391B LED14/830 P11PSU D100 AL GMG2HE  | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401533944 | DN391B LED14/865 PSU D100 AL GCG2HE     | -                          | 6500 K                             | >80                         | 125 lm/W                        |

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401534044 | DN391B<br>LED14/840 PSU<br>D100 AL GCG2HE       | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401534144 | DN391B<br>LED14/830 PSU<br>D100 AL GCG2HE       | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401534544 | DN391B<br>LED12/865<br>P10PSU D100 AL<br>GMG2HE | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401534644 | DN391B<br>LED12/840<br>P10PSU D100 AL<br>GMG2HE | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401534744 | DN391B<br>LED12/830<br>P10PSU D100 AL<br>GMG2HE | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401535144 | DN391B<br>LED12/865 PSU<br>D100 AL GCG2HE       | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401535244 | DN391B<br>LED12/840 PSU<br>D100 AL GCG2HE       | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401535444 | DN391B<br>LED12/830 PSU<br>D100 AL GCG2HE       | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401535844 | DN390B<br>LED7/865 P6PSU<br>D100 AL GMG2HE      | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401535944 | DN390B<br>LED7/840 P6PSU<br>D100 AL GMG2HE      | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401536044 | DN390B<br>LED7/830 P6PSU<br>D100 AL GMG2HE      | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401536444 | DN390B<br>LED7/865 PSU<br>D100 AL GCG2HE        | -                          | 6500 K                             | >80                         | 125 lm/W                        |
| 911401536544 | DN390B<br>LED7/840 PSU<br>D100 AL GCG2HE        | -                          | 4000 K                             | >80                         | 125 lm/W                        |
| 911401536644 | DN390B<br>LED7/830 PSU<br>D100 AL GCG2HE        | -                          | 3000 K                             | >80                         | 118 lm/W                        |
| 911401537444 | DN391X<br>LED14/865<br>P12WIA D100 AL<br>G2HE   | -                          | 6500 K                             | >80                         | 120 lm/W                        |

| Order Code   | Full Product Name                                 | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401538044 | DN391X<br>LED14/830<br>P12WIA D100 AL<br>G2HE     | -                          | 3000 K                             | >80                         | 111 lm/W                        |
| 911401538644 | DN391X<br>LED14/840<br>P12WIA D100 AL<br>G2HE     | -                          | 4000 K                             | >80                         | 120 lm/W                        |
| 911401570144 | DN391B<br>LED14/865<br>P12PSD D100<br>ALWP GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401570244 | DN391B<br>LED14/840<br>P12PSD D100<br>ALWP GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401570344 | DN391B<br>LED14/830<br>P12PSD D100<br>ALWP GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401570444 | DN391B<br>LED14/865 PSD<br>D100 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401570544 | DN391B<br>LED14/840 PSD<br>D100 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401570644 | DN391B<br>LED14/830 PSD<br>D100 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401570744 | DN391B<br>LED12/865<br>P10PSD D100<br>ALWP GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401570844 | DN391B<br>LED12/840<br>P10PSD D100<br>ALWP GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401570944 | DN391B<br>LED12/830<br>P10PSD D100<br>ALWP GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401571044 | DN391B<br>LED12/865 PSD<br>D100 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401571144 | DN391B<br>LED12/840 PSD<br>D100 AL WP<br>GCG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401571244 | DN391B<br>LED12/830 PSD<br>D100 AL WP<br>GCG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401577944 | DN391B<br>LED14/865<br>P12PSD D100 AL<br>GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401578044 | DN391B<br>LED14/840<br>P12PSD D100 AL<br>GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401578144 | DN391B<br>LED14/830<br>P12PSD D100 AL<br>GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401578544 | DN391B<br>LED14/865 PSD<br>D100 AL GCG2HE       | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401578644 | DN391B<br>LED14/840 PSD<br>D100 AL GCG2HE       | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401578744 | DN391B<br>LED14/830 PSD<br>D100 AL GCG2HE       | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401579144 | DN391B<br>LED12/865<br>P10PSD D100 AL<br>GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401579244 | DN391B<br>LED12/840<br>P10PSD D100 AL<br>GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401579344 | DN391B<br>LED12/830<br>P10PSD D100 AL<br>GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401579744 | DN391B<br>LED12/865 PSD<br>D100 AL GCG2HE       | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 120 lm/W                        |
| 911401579844 | DN391B<br>LED12/840 PSD<br>D100 AL GCG2HE       | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 120 lm/W                        |

| Order Code   | Full Product Name                                    | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|------------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401579944 | DN391B<br>LED12/830 PSD<br>D100 AL GCG2HE            | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 111 lm/W                        |
| 911401503845 | DN394X<br>LED34/9TNW<br>P27PSD D200<br>WH WP G2      | - degree(s)                | Tunable white 2700–6500 K          | ≥90                         | 125 lm/W                        |
| 911401504145 | DN394X<br>LED34/9TNW<br>P27PSD D200<br>WH WPCAUG2    | - degree(s)                | Tunable white 2700–6500 K          | ≥90                         | 125 lm/W                        |
| 911401519944 | DN393B<br>LED26/840<br>P20PSU<br>D200WHWP<br>CAUG2HE | -                          | 4000 K                             | >80                         | 140 lm/W                        |
| 911401520344 | DN393B<br>LED26/840<br>P20PSU D200<br>WH CAUG2HE     | -                          | 4000 K                             | >80                         | 140 lm/W                        |
| 911401526444 | DN394B<br>LED40/865<br>P29PSU D200<br>WH GMG2HE      | -                          | 6500 K                             | >80                         | 140 lm/W                        |
| 911401526544 | DN394B<br>LED40/840<br>P29PSU D200<br>WH GMG2HE      | -                          | 4000 K                             | >80                         | 140 lm/W                        |
| 911401526644 | DN394B<br>LED40/830<br>P29PSU D200<br>WH GMG2HE      | -                          | 3000 K                             | >80                         | 130 lm/W                        |
| 911401527044 | DN394B<br>LED40/865 PSU<br>D200 WH<br>GCG2HE         | -                          | 6500 K                             | >80                         | 140 lm/W                        |
| 911401527144 | DN394B<br>LED40/840 PSU<br>D200 WH<br>GCG2HE         | -                          | 4000 K                             | >80                         | 140 lm/W                        |
| 911401527244 | DN394B<br>LED40/830 PSU<br>D200 WH<br>GCG2HE         | -                          | 3000 K                             | >80                         | 130 lm/W                        |
| 911401527644 | DN393B<br>LED26/865<br>P19PSU D200 WH<br>GMG2HE      | -                          | 6500 K                             | >80                         | 140 lm/W                        |

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401527744 | DN393B<br>LED26/840<br>P19PSU D200 WH<br>GMG2HE | -                          | 4000 K                             | >80                         | 140 lm/W                        |
| 911401527844 | DN393B<br>LED26/830<br>P19PSU D200 WH<br>GMG2HE | -                          | 3000 K                             | >80                         | 130 lm/W                        |
| 911401528244 | DN393B<br>LED26/865 PSU<br>D200 WH<br>GCG2HE    | -                          | 6500 K                             | >80                         | 140 lm/W                        |
| 911401528344 | DN393B<br>LED26/840 PSU<br>D200 WH<br>GCG2HE    | -                          | 4000 K                             | >80                         | 140 lm/W                        |
| 911401528444 | DN393B<br>LED26/830 PSU<br>D200 WH<br>GCG2HE    | -                          | 3000 K                             | >80                         | 130 lm/W                        |
| 911401530044 | DN392B<br>LED20/865<br>P14PSU D200 WH<br>GMG2HE | -                          | 6500 K                             | >80                         | 140 lm/W                        |
| 911401530144 | DN392B<br>LED20/840<br>P14PSU D200 WH<br>GMG2HE | -                          | 4000 K                             | >80                         | 140 lm/W                        |
| 911401530244 | DN392B<br>LED20/830<br>P14PSU D200 WH<br>GMG2HE | -                          | 3000 K                             | >80                         | 130 lm/W                        |
| 911401530644 | DN392B<br>LED20/865 PSU<br>D200 WH<br>GCG2HE    | -                          | 6500 K                             | >80                         | 140 lm/W                        |
| 911401530744 | DN392B<br>LED20/840 PSU<br>D200 WH<br>GCG2HE    | -                          | 4000 K                             | >80                         | 140 lm/W                        |
| 911401530844 | DN392B<br>LED20/830 PSU<br>D200 WH<br>GCG2HE    | -                          | 3000 K                             | >80                         | 130 lm/W                        |
| 911401537144 | DN393X<br>LED26/865<br>P20WIA D200<br>WH G2HE   | -                          | 6500 K                             | >80                         | 137 lm/W                        |

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401537744 | DN393X<br>LED26/830<br>P20WIA D200<br>WH G2HE   | -                          | 3000 K                             | >80                         | 127 lm/W                        |
| 911401538344 | DN393X<br>LED26/840<br>P20WIA D200<br>WH G2HE   | -                          | 4000 K                             | >80                         | 137 lm/W                        |
| 911401571644 | DN394B<br>LED40/865<br>P29PSD D200<br>WH GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 137 lm/W                        |
| 911401571744 | DN394B<br>LED40/840<br>P29PSD D200<br>WH GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 137 lm/W                        |
| 911401571844 | DN394B<br>LED40/830<br>P29PSD D200<br>WH GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 127 lm/W                        |
| 911401572244 | DN394B<br>LED40/865 PSD<br>D200 WH<br>GCG2HE    | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 137 lm/W                        |
| 911401572344 | DN394B<br>LED40/840 PSD<br>D200 WH<br>GCG2HE    | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 137 lm/W                        |
| 911401572444 | DN394B<br>LED40/830 PSD<br>D200 WH<br>GCG2HE    | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 127 lm/W                        |
| 911401572844 | DN393B<br>LED26/865<br>P20PSD D200<br>WH GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 137 lm/W                        |
| 911401572944 | DN393B<br>LED26/840<br>P20PSD D200<br>WH GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 137 lm/W                        |
| 911401573044 | DN393B<br>LED26/830<br>P20PSD D200<br>WH GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 127 lm/W                        |
| 911401573444 | DN393B<br>LED26/865 PSD<br>D200 WH<br>GCG2HE    | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 137 lm/W                        |

| Order Code   | Full Product Name                                 | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401573544 | DN393B<br>LED26/840 PSD<br>D200 WH<br>GCG2HE      | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 137 lm/W                        |
| 911401573644 | DN393B<br>LED26/830 PSD<br>D200 WH<br>GCG2HE      | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 127 lm/W                        |
| 911401575244 | DN392B<br>LED18/865<br>P14PSD D200 WH<br>GMG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 137 lm/W                        |
| 911401575344 | DN392B<br>LED18/840<br>P14PSD D200 WH<br>GMG2HE   | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 137 lm/W                        |
| 911401575444 | DN392B<br>LED18/830<br>P14PSD D200 WH<br>GMG2HE   | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 127 lm/W                        |
| 911401575844 | DN392B<br>LED18/865 PSD<br>D200 WH<br>GCG2HE      | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 137 lm/W                        |
| 911401575944 | DN392B<br>LED18/840 PSD<br>D200 WH<br>GCG2HE      | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 137 lm/W                        |
| 911401576044 | DN392B<br>LED18/830 PSD<br>D200 WH<br>GCG2HE      | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 127 lm/W                        |
| 911401586932 | DN393B<br>LED22/840<br>P20PSU D200<br>WH CAUG2    | - degree(s)                | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401588632 | DN393B<br>LED22/840<br>P20PSU D200<br>WH WP CAUG2 | - degree(s)                | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401503545 | DN394X<br>LED33/9TNW<br>P27PSD D200 AL<br>WP G2   | - degree(s)                | Tunable white<br>2700-6500 K       | ≥90                         | 120 lm/W                        |
| 911401520744 | DN394B<br>LED38/865<br>P29PSU D200<br>ALWP GMG2HE | -                          | 6500 K                             | >80                         | 132 lm/W                        |

| Order Code   | Full Product Name                                 | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401520844 | DN394B<br>LED38/840<br>P29PSU D200<br>ALWP GMG2HE | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401520944 | DN394B<br>LED38/830<br>P29PSU D200<br>ALWP GMG2HE | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401521044 | DN394B<br>LED38/865 PSU<br>D200 AL WP<br>GCG2HE   | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401521144 | DN394B<br>LED38/840 PSU<br>D200 AL WP<br>GCG2HE   | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401521244 | DN394B<br>LED38/830 PSU<br>D200 AL WP<br>GCG2HE   | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401521344 | DN393B<br>LED25/865<br>P19PSU D200<br>ALWP GMG2HE | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401521444 | DN393B<br>LED25/840<br>P19PSU D200<br>ALWP GMG2HE | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401521544 | DN393B<br>LED25/830<br>P19PSU D200<br>ALWP GMG2HE | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401521644 | DN393B<br>LED25/865 PSU<br>D200 AL WP<br>GCG2HE   | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401521744 | DN393B<br>LED25/840 PSU<br>D200 AL WP<br>GCG2HE   | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401521844 | DN393B<br>LED25/830 PSU<br>D200 AL WP<br>GCG2HE   | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401522544 | DN392B<br>LED18/865<br>P14PSU D200<br>ALWP GMG2HE | -                          | 6500 K                             | >80                         | 132 lm/W                        |

| Order Code   | Full Product Name                                 | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401522644 | DN392B<br>LED18/840<br>P14PSU D200<br>ALWP GMG2HE | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401522744 | DN392B<br>LED18/830<br>P14PSU D200<br>ALWP GMG2HE | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401522844 | DN392B<br>LED18/865 PSU<br>D200 AL WP<br>GCG2HE   | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401522944 | DN392B<br>LED18/840 PSU<br>D200 AL WP<br>GCG2HE   | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401523044 | DN392B<br>LED18/830 PSU<br>D200 AL WP<br>GCG2HE   | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401526144 | DN394B<br>LED38/865<br>P29PSU D200 AL<br>GMG2HE   | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401526244 | DN394B<br>LED38/840<br>P29PSU D200 AL<br>GMG2HE   | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401526344 | DN394B<br>LED38/830<br>P29PSU D200 AL<br>GMG2HE   | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401526744 | DN394B<br>LED38/865 PSU<br>D200 AL GCG2HE         | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401526844 | DN394B<br>LED38/840 PSU<br>D200 AL GCG2HE         | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401526944 | DN394B<br>LED38/830 PSU<br>D200 AL GCG2HE         | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401527344 | DN393B<br>LED25/865<br>P19PSU D200 AL<br>GMG2HE   | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401527444 | DN393B<br>LED25/840<br>P19PSU D200 AL<br>GMG2HE   | -                          | 4000 K                             | >80                         | 132 lm/W                        |

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401527544 | DN393B<br>LED25/830<br>P19PSU D200 AL<br>GMG2HE | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401527944 | DN393B<br>LED25/865 PSU<br>D200 AL GCG2HE       | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401528044 | DN393B<br>LED25/840 PSU<br>D200 AL GCG2HE       | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401528144 | DN393B<br>LED25/830 PSU<br>D200 AL GCG2HE       | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401529744 | DN392B<br>LED18/865<br>P14PSU D200 AL<br>GMG2HE | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401529844 | DN392B<br>LED18/840<br>P14PSU D200 AL<br>GMG2HE | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401529944 | DN392B<br>LED18/830<br>P14PSU D200 AL<br>GMG2HE | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401530344 | DN392B<br>LED18/865 PSU<br>D200 AL GCG2HE       | -                          | 6500 K                             | >80                         | 132 lm/W                        |
| 911401530444 | DN392B<br>LED18/840 PSU<br>D200 AL GCG2HE       | -                          | 4000 K                             | >80                         | 132 lm/W                        |
| 911401530544 | DN392B<br>LED18/830 PSU<br>D200 AL GCG2HE       | -                          | 3000 K                             | >80                         | 122 lm/W                        |
| 911401537044 | DN393X<br>LED25/865<br>P20WIA D200 AL<br>G2HE   | -                          | 6500 K                             | >80                         | 130 lm/W                        |
| 911401537644 | DN393X<br>LED25/830<br>P20WIA D200 AL<br>G2HE   | -                          | 3000 K                             | >80                         | 120 lm/W                        |
| 911401538244 | DN393X<br>LED25/840<br>P20WIA D200 AL<br>G2HE   | -                          | 4000 K                             | >80                         | 130 lm/W                        |
| 911401566844 | DN394B<br>LED38/865                             | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |

| Order Code   | Full Product Name                                 | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
|              | P29PSD D200<br>ALWP GMG2HE                        |                            |                                    |                             |                                 |
| 911401566944 | DN394B<br>LED38/840<br>P29PSD D200<br>ALWP GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401567044 | DN394B<br>LED38/830<br>P29PSD D200<br>ALWP GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401567144 | DN394B<br>LED38/865 PSD<br>D200 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401567244 | DN394B<br>LED38/840 PSD<br>D200 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401567344 | DN394B<br>LED38/830 PSD<br>D200 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401567444 | DN393B<br>LED25/865<br>P20PSD D200<br>ALWP GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401567544 | DN393B<br>LED25/840<br>P20PSD D200<br>ALWP GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401567644 | DN393B<br>LED25/830<br>P20PSD D200<br>ALWP GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401567744 | DN393B<br>LED25/865 PSD<br>D200 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401567844 | DN393B<br>LED25/840 PSD<br>D200 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401567944 | DN393B<br>LED25/830 PSD<br>D200 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401568644 | DN392B<br>LED18/865                               | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |

| Order Code   | Full Product Name                                 | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
|              | P14PSD D200<br>ALWP GMG2HE                        |                            |                                    |                             |                                 |
| 911401568744 | DN392B<br>LED18/840<br>P14PSD D200<br>ALWP GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401568844 | DN392B<br>LED18/830<br>P14PSD D200<br>ALWP GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401568944 | DN392B<br>LED18/865 PSD<br>D200 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401569044 | DN392B<br>LED18/840 PSD<br>D200 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401569144 | DN392B<br>LED18/830 PSD<br>D200 AL WP<br>GCG2HE   | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401571344 | DN394B<br>LED38/865<br>P29PSD D200 AL<br>GMG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401571444 | DN394B<br>LED38/840<br>P29PSD D200 AL<br>GMG2HE   | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401571544 | DN394B<br>LED38/830<br>P29PSD D200 AL<br>GMG2HE   | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401571944 | DN394B<br>LED38/865 PSD<br>D200 AL GCG2HE         | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401572044 | DN394B<br>LED38/840 PSD<br>D200 AL GCG2HE         | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401572144 | DN394B<br>LED38/830 PSD<br>D200 AL GCG2HE         | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401572544 | DN393B<br>LED25/865<br>P20PSD D200 AL<br>GMG2HE   | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401572644 | DN393B<br>LED25/840                               | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 130 lm/W                        |

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
|              | P20PSD D200 AL<br>GMG2HE                        |                            |                                    |                             |                                 |
| 911401572744 | DN393B<br>LED25/830<br>P20PSD D200 AL<br>GMG2HE | 10 or 40<br>degree(s)      | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401573144 | DN393B<br>LED25/865 PSD<br>D200 AL GCG2HE       | 10 or 40<br>degree(s)      | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401573244 | DN393B<br>LED25/840 PSD<br>D200 AL GCG2HE       | 10 or 40<br>degree(s)      | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401573344 | DN393B<br>LED25/830 PSD<br>D200 AL GCG2HE       | 10 or 40<br>degree(s)      | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401574944 | DN392B<br>LED18/865<br>P14PSD D200 AL<br>GMG2HE | 10 or 40<br>degree(s)      | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401575044 | DN392B<br>LED18/840<br>P14PSD D200 AL<br>GMG2HE | 10 or 40<br>degree(s)      | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401575144 | DN392B<br>LED18/830<br>P14PSD D200 AL<br>GMG2HE | 10 or 40<br>degree(s)      | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401575544 | DN392B<br>LED18/865 PSD<br>D200 AL GCG2HE       | 10 or 40<br>degree(s)      | 6500 K                             | ≥80                         | 130 lm/W                        |
| 911401575644 | DN392B<br>LED18/840 PSD<br>D200 AL GCG2HE       | 10 or 40<br>degree(s)      | 4000 K                             | ≥80                         | 130 lm/W                        |
| 911401575744 | DN392B<br>LED18/830 PSD<br>D200 AL GCG2HE       | 10 or 40<br>degree(s)      | 3000 K                             | ≥80                         | 120 lm/W                        |
| 911401577042 | DN393X<br>LED22/840<br>P20LIW D200<br>WH CAUG2  | -<br>degree(s)             | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401577542 | DN392X<br>LED17/840<br>P15LIW D150 WH<br>CAUG2  | -<br>degree(s)             | 4000 K                             | ≥80                         | 120 lm/W                        |
| 911401503945 | DN392X<br>LED17/9TNW<br>P15PSD D150 WH<br>WP G2 | -<br>degree(s)             | Tunable white<br>2700-6500 K       | ≥90                         | 120 lm/W                        |

| Order Code   | Full Product Name                                    | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|------------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401504245 | DN392X<br>LED17/9TNW<br>P15PSD D150 WH<br>WPCAUG2    | -<br>degree(s)             | Tunable white<br>2700-6500 K       | ≥90                         | 120 lm/W                        |
| 911401520044 | DN392B<br>LED20/840<br>P15PSU<br>D150WHWP<br>CAUG2HE | -                          | 4000 K                             | >80                         | 138 lm/W                        |
| 911401520144 | DN391B<br>LED13/840<br>P11PSU<br>D150WHWP<br>CAUG2HE | -                          | 4000 K                             | >80                         | 138 lm/W                        |
| 911401520444 | DN392B<br>LED20/840<br>P15PSU D150 WH<br>CAUG2HE     | -                          | 4000 K                             | >80                         | 138 lm/W                        |
| 911401520544 | DN391B<br>LED13/840<br>P11PSU D150 WH<br>CAUG2HE     | -                          | 4000 K                             | >80                         | 138 lm/W                        |
| 911401528844 | DN392B<br>LED22/865<br>P16PSU D150 WH<br>GMG2HE      | -                          | 6500 K                             | >80                         | 138 lm/W                        |
| 911401528944 | DN392B<br>LED22/840<br>P16PSU D150 WH<br>GMG2HE      | -                          | 4000 K                             | >80                         | 138 lm/W                        |
| 911401529044 | DN392B<br>LED22/830<br>P16PSU D150 WH<br>GMG2HE      | -                          | 3000 K                             | >80                         | 130 lm/W                        |
| 911401529444 | DN392B<br>LED22/865 PSU<br>D150 WH<br>GCG2HE         | -                          | 6500 K                             | >80                         | 138 lm/W                        |
| 911401529544 | DN392B<br>LED22/840 PSU<br>D150 WH<br>GCG2HE         | -                          | 4000 K                             | >80                         | 138 lm/W                        |
| 911401529644 | DN392B<br>LED22/830 PSU<br>D150 WH<br>GCG2HE         | -                          | 3000 K                             | >80                         | 130 lm/W                        |
| 911401531244 | DN392B<br>LED20/865                                  | -                          | 6500 K                             | >80                         | 138 lm/W                        |

| Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Order Code   | Full Product Name                               | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|--------------|-------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
|              | P14PSU D150 WH<br>GMG2HE                        |                            |                                    |                             |                                 |              | P15WIA D150 WH<br>G2HE                          |                            |                                    |                             |                                 |
| 911401531344 | DN392B<br>LED20/840<br>P14PSU D150 WH<br>GMG2HE | -                          | 4000 K                             | >80                         | 138 lm/W                        | 911401537944 | DN392X<br>LED20/830<br>P15WIA D150 WH<br>G2HE   | -                          | 3000 K                             | >80                         | 125 lm/W                        |
| 911401531444 | DN392B<br>LED20/830<br>P14PSU D150 WH<br>GMG2HE | -                          | 3000 K                             | >80                         | 130 lm/W                        | 911401538544 | DN392X<br>LED20/840<br>P15WIA D150 WH<br>G2HE   | -                          | 4000 K                             | >80                         | 135 lm/W                        |
| 911401531844 | DN392B<br>LED20/865 PSU<br>D150 WH<br>GCG2HE    | -                          | 6500 K                             | >80                         | 138 lm/W                        | 911401566544 | DN392B<br>LED19/865<br>P14PSD D150 WH<br>GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 135 lm/W                        |
| 911401531944 | DN392B<br>LED20/840 PSU<br>D150 WH<br>GCG2HE    | -                          | 4000 K                             | >80                         | 138 lm/W                        | 911401566644 | DN392B<br>LED19/840<br>P14PSD D150 WH<br>GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 135 lm/W                        |
| 911401532044 | DN392B<br>LED20/830 PSU<br>D150 WH<br>GCG2HE    | -                          | 3000 K                             | >80                         | 130 lm/W                        | 911401566744 | DN392B<br>LED19/830<br>P14PSD D150 WH<br>GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 125 lm/W                        |
| 911401532444 | DN391B<br>LED13/865<br>P10PSU D150 WH<br>GMG2HE | -                          | 6500 K                             | >80                         | 138 lm/W                        | 911401574044 | DN392B<br>LED23/865<br>P17PSD D150 WH<br>GMG2HE | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 135 lm/W                        |
| 911401532544 | DN391B<br>LED13/840<br>P10PSU D150 WH<br>GMG2HE | -                          | 4000 K                             | >80                         | 138 lm/W                        | 911401574144 | DN392B<br>LED23/840<br>P17PSD D150 WH<br>GMG2HE | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 135 lm/W                        |
| 911401532644 | DN391B<br>LED13/830<br>P10PSU D150 WH<br>GMG2HE | -                          | 3000 K                             | >80                         | 130 lm/W                        | 911401574244 | DN392B<br>LED23/830<br>P17PSD D150 WH<br>GMG2HE | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 125 lm/W                        |
| 911401533044 | DN391B<br>LED13/865 PSU<br>D150 WH<br>GCG2HE    | -                          | 6500 K                             | >80                         | 138 lm/W                        | 911401574644 | DN392B<br>LED23/865 PSD<br>D150 WH<br>GCG2HE    | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 135 lm/W                        |
| 911401533144 | DN391B<br>LED13/840 PSU<br>D150 WH<br>GCG2HE    | -                          | 4000 K                             | >80                         | 138 lm/W                        | 911401574744 | DN392B<br>LED23/840 PSD<br>D150 WH<br>GCG2HE    | 10 or 40 degree(s)         | 4000 K                             | ≥80                         | 135 lm/W                        |
| 911401533244 | DN391B<br>LED13/830 PSU<br>D150 WH<br>GCG2HE    | -                          | 3000 K                             | >80                         | 130 lm/W                        | 911401574844 | DN392B<br>LED23/830 PSD<br>D150 WH<br>GCG2HE    | 10 or 40 degree(s)         | 3000 K                             | ≥80                         | 125 lm/W                        |
| 911401537344 | DN392X<br>LED20/865                             | -                          | 6500 K                             | >80                         | 135 lm/W                        | 911401576444 | DN392B<br>LED19/865 PSD                         | 10 or 40 degree(s)         | 6500 K                             | ≥80                         | 135 lm/W                        |

| Order Code   | Full Product Name | Beam                  | Correlated              | Color                 | Luminous               |
|--------------|-------------------|-----------------------|-------------------------|-----------------------|------------------------|
|              |                   | angle of light source | Color Temperature (Nom) | rendering index (CRI) | Efficacy (rated) (Nom) |
| 911401576544 | D150 WH           | 10 or 40 degree(s)    | 4000 K                  | ≥80                   | 135 lm/W               |
|              | GCG2HE            |                       |                         |                       |                        |
| 911401576644 | DN392B            | 10 or 40 degree(s)    | 3000 K                  | ≥80                   | 116 lm/W               |
|              | LED19/840 PSD     |                       |                         |                       |                        |
| 911401577044 | D150 WH           | 10 or 40 degree(s)    | 6500 K                  | ≥80                   | 125 lm/W               |
|              | GCG2HE            |                       |                         |                       |                        |
| 911401577144 | DN391B            | 10 or 40 degree(s)    | 4000 K                  | ≥80                   | 125 lm/W               |
|              | LED13/865         |                       |                         |                       |                        |
| 911401577244 | P11PSD D150 WH    | 10 or 40 degree(s)    | 3000 K                  | ≥80                   | 116 lm/W               |
|              | GMG2HE            |                       |                         |                       |                        |
| 911401577644 | DN391B            | 10 or 40 degree(s)    | 6500 K                  | ≥80                   | 125 lm/W               |
|              | LED13/865 PSD     |                       |                         |                       |                        |

| Order Code   | Full Product Name | Beam                  | Correlated              | Color                 | Luminous               |
|--------------|-------------------|-----------------------|-------------------------|-----------------------|------------------------|
|              |                   | angle of light source | Color Temperature (Nom) | rendering index (CRI) | Efficacy (rated) (Nom) |
| 911401577744 | D150 WH           | 10 or 40 degree(s)    | 4000 K                  | ≥80                   | 125 lm/W               |
|              | GCG2HE            |                       |                         |                       |                        |
| 911401577844 | DN391B            | 10 or 40 degree(s)    | 3000 K                  | ≥80                   | 116 lm/W               |
|              | LED13/830 PSD     |                       |                         |                       |                        |
| 911401585532 | D150 WH           | -                     | 4000 K                  | ≥80                   | 113 lm/W               |
|              | GCG2HE            |                       |                         |                       |                        |
| 911401585632 | DN391B            | -                     | 4000 K                  | ≥80                   | 120 lm/W               |
|              | LED11/840         |                       |                         |                       |                        |
| 911401587832 | P11PSU D150 WH    | -                     | 4000 K                  | ≥80                   | 113 lm/W               |
|              | CAUG2             |                       |                         |                       |                        |
| 911401587932 | DN392B            | -                     | 4000 K                  | ≥80                   | 120 lm/W               |
|              | LED17/840         |                       |                         |                       |                        |

Light Technical (2/2)

| Order Code   | Full Product Name       | Luminous | Number           | Optic type                     |
|--------------|-------------------------|----------|------------------|--------------------------------|
|              |                         | Flux     | of light sources |                                |
| 911401504045 | DN391X LED8/9TNW        | 800 lm   | 20               | White reflector and opal cover |
|              | P7PSD D100 WH WP G2     |          |                  |                                |
| 911401504345 | DN391X LED8/9TNW        | 800 lm   | 20               | White reflector and opal cover |
|              | P7PSD D100 WH WPCAUG2   |          |                  |                                |
| 911401520244 | DN390B LED7/840 P6PSU   | 750 lm   | 1                | Facetted reflector             |
|              | D100WHWP CAUG2HE        |          |                  |                                |
| 911401520644 | DN390B LED7/840 P6PSU   | 750 lm   | 1                | White reflector and opal cover |
|              | D100 WH CAUG2HE         |          |                  |                                |
| 911401533644 | DN391B LED15/865 P11PSU | 1,500 lm | 1                | White reflector and opal cover |
|              | D100 WH GMG2HE          |          |                  |                                |
| 911401533744 | DN391B LED15/840 P11PSU | 1,500 lm | 1                | White reflector and opal cover |
|              | D100 WH GMG2HE          |          |                  |                                |
| 911401533844 | DN391B LED15/830 P11PSU | 1,350 lm | 1                | White reflector and opal cover |
|              | D100 WH GMG2HE          |          |                  |                                |
| 911401534244 | DN391B LED15/865 PSU    | 1,500 lm | 1                | White reflector and opal cover |
|              | D100 WH GCG2HE          |          |                  |                                |

| Order Code   | Full Product Name     | Luminous | Number           | Optic type                     |
|--------------|-----------------------|----------|------------------|--------------------------------|
|              |                       | Flux     | of light sources |                                |
| 911401534344 | DN391B LED15/840 PSU  | 1,500 lm | 1                | White reflector and opal cover |
|              | D100 WH GCG2HE        |          |                  |                                |
| 911401534444 | DN391B LED15/830 PSU  | 1,350 lm | 1                | White reflector and opal cover |
|              | D100 WH GCG2HE        |          |                  |                                |
| 911401534844 | DN391B LED12/865      | 1,250 lm | 1                | White reflector and opal cover |
|              | P10PSU D100 WH GMG2HE |          |                  |                                |
| 911401534944 | DN391B LED12/840      | 1,250 lm | 1                | White reflector and opal cover |
|              | P10PSU D100 WH GMG2HE |          |                  |                                |
| 911401535044 | DN391B LED12/830      | 1,150 lm | 1                | White reflector and opal cover |
|              | P10PSU D100 WH GMG2HE |          |                  |                                |
| 911401535544 | DN391B LED12/865 PSU  | 1,250 lm | 1                | White reflector and opal cover |
|              | D100 WH GCG2HE        |          |                  |                                |
| 911401535644 | DN391B LED12/840 PSU  | 1,250 lm | 1                | White reflector and opal cover |
|              | D100 WH GCG2HE        |          |                  |                                |

| Order Code   | Full Product Name                            | Luminous Flux | Number of light sources | Optic type                        |
|--------------|----------------------------------------------|---------------|-------------------------|-----------------------------------|
| 911401535744 | DN391B LED12/830 PSU<br>D100 WH GCG2HE       | 1,150 lm      | 1                       | White reflector<br>and opal cover |
| 911401536144 | DN390B LED7/865 P6PSU<br>D100 WH GMG2HE      | 750 lm        | 1                       | White reflector<br>and opal cover |
| 911401536244 | DN390B LED7/840 P6PSU<br>D100 WH GMG2HE      | 750 lm        | 1                       | White reflector<br>and opal cover |
| 911401536344 | DN390B LED7/830 P6PSU<br>D100 WH GMG2HE      | 700 lm        | 1                       | White reflector<br>and opal cover |
| 911401536744 | DN390B LED7/865 PSU<br>D100 WH GCG2HE        | 750 lm        | 1                       | White reflector<br>and opal cover |
| 911401536844 | DN390B LED7/840 PSU<br>D100 WH GCG2HE        | 750 lm        | 1                       | White reflector<br>and opal cover |
| 911401536944 | DN390B LED7/830 PSU<br>D100 WH GCG2HE        | 700 lm        | 1                       | White reflector<br>and opal cover |
| 911401537544 | DN391X LED15/865<br>P12WIA D100 WH G2HE      | 1,500 lm      | 1                       | White reflector<br>and opal cover |
| 911401538144 | DN391X LED15/830<br>P12WIA D100 WH G2HE      | 1,500 lm      | 1                       | White reflector<br>and opal cover |
| 911401538744 | DN391X LED15/840<br>P12WIA D100WH G2HE       | 1,500 lm      | 1                       | White reflector<br>and opal cover |
| 911401578244 | DN391B LED15/865<br>P12PSD D100 WH<br>GMG2HE | 1,500 lm      | 28                      | White reflector<br>and opal cover |
| 911401578344 | DN391B LED15/840<br>P12PSD D100 WH<br>GMG2HE | 1,500 lm      | 28                      | White reflector<br>and opal cover |
| 911401578444 | DN391B LED15/830<br>P12PSD D100 WH<br>GMG2HE | 1,350 lm      | 28                      | White reflector<br>and opal cover |
| 911401578844 | DN391B LED15/865 PSD<br>D100 WH GCG2HE       | 1,500 lm      | 28                      | White reflector<br>and opal cover |
| 911401578944 | DN391B LED15/840 PSD<br>D100 WH GCG2HE       | 1,500 lm      | 28                      | White reflector<br>and opal cover |
| 911401579044 | DN391B LED15/830 PSD<br>D100 WH GCG2HE       | 1,350 lm      | 28                      | White reflector<br>and opal cover |
| 911401579444 | DN391B LED12/865<br>P10PSD D100 WH<br>GMG2HE | 1,200 lm      | 28                      | White reflector<br>and opal cover |
| 911401579544 | DN391B LED12/840<br>P10PSD D100 WH<br>GMG2HE | 1,200 lm      | 28                      | White reflector<br>and opal cover |
| 911401579644 | DN391B LED12/830<br>P10PSD D100 WH<br>GMG2HE | 1,100 lm      | 28                      | White reflector<br>and opal cover |
| 911401580044 | DN391B LED12/865 PSD<br>D100 WH GCG2HE       | 1,200 lm      | 28                      | White reflector<br>and opal cover |
| 911401580144 | DN391B LED12/840 PSD<br>D100 WH GCG2HE       | 1,200 lm      | 28                      | White reflector<br>and opal cover |
| 911401580244 | DN391B LED12/830 PSD<br>D100 WH GCG2HE       | 1,100 lm      | 28                      | White reflector<br>and opal cover |

| Order Code   | Full Product Name                              | Luminous Flux | Number of light sources | Optic type                        |
|--------------|------------------------------------------------|---------------|-------------------------|-----------------------------------|
| 911401584832 | DN390B LED6/840 P8PSU<br>D100 WH CAUG2         | 800 lm        | 14                      | White reflector<br>and opal cover |
| 911401587632 | DN390B LED6/840 P8PSU<br>D100 WH WP CAUG2      | 800 lm        | 14                      | White reflector<br>and opal cover |
| 911401503645 | DN392X LED16/9TNW<br>P15PSD D150 AL WP G2      | 1,650 lm      | 48                      | Facetted<br>reflector             |
| 911401521944 | DN392B LED20/865<br>P16PSU D150 ALWP<br>GMG2HE | 2,000 lm      | 1                       | Facetted<br>reflector             |
| 911401522044 | DN392B LED20/840<br>P16PSU D150 ALWP<br>GMG2HE | 2,000 lm      | 1                       | Facetted<br>reflector             |
| 911401522144 | DN392B LED20/830<br>P16PSU D150 ALWP<br>GMG2HE | 1,850 lm      | 1                       | Facetted<br>reflector             |
| 911401522244 | DN392B LED20/865 PSU<br>D150 AL WP GCG2HE      | 2,000 lm      | 1                       | Facetted<br>reflector             |
| 911401522344 | DN392B LED20/840 PSU<br>D150 AL WP GCG2HE      | 2,000 lm      | 1                       | Facetted<br>reflector             |
| 911401522444 | DN392B LED20/830 PSU<br>D150 AL WP GCG2HE      | 1,850 lm      | 1                       | Facetted<br>reflector             |
| 911401523144 | DN392B LED18/865<br>P14PSU D150 ALWP<br>GMG2HE | 1,850 lm      | 1                       | Facetted<br>reflector             |
| 911401523244 | DN392B LED18/840<br>P14PSU D150 ALWP<br>GMG2HE | 1,850 lm      | 1                       | Facetted<br>reflector             |
| 911401523344 | DN392B LED18/830<br>P14PSU D150 ALWP<br>GMG2HE | 1,700 lm      | 1                       | Facetted<br>reflector             |
| 911401523444 | DN392B LED18/865 PSU<br>D150 AL WP GCG2HE      | 1,850 lm      | 1                       | Facetted<br>reflector             |
| 911401523544 | DN392B LED18/840 PSU<br>D150 AL WP GCG2HE      | 1,850 lm      | 1                       | Facetted<br>reflector             |
| 911401523644 | DN392B LED18/830 PSU<br>D150 AL WP GCG2HE      | 1,700 lm      | 1                       | Facetted<br>reflector             |
| 911401523744 | DN391B LED12/865<br>P10PSU D150 ALWP<br>GMG2HE | 1,250 lm      | 1                       | Facetted<br>reflector             |
| 911401523844 | DN391B LED12/840<br>P10PSU D150 ALWP<br>GMG2HE | 1,250 lm      | 1                       | Facetted<br>reflector             |
| 911401523944 | DN391B LED12/830<br>P10PSU D150 ALWP<br>GMG2HE | 1,150 lm      | 1                       | Facetted<br>reflector             |
| 911401524044 | DN391B LED12/865 PSU<br>D150 AL WP GCG2HE      | 1,250 lm      | 1                       | Facetted<br>reflector             |
| 911401524144 | DN391B LED12/840 PSU<br>D150 AL WP GCG2HE      | 1,250 lm      | 1                       | Facetted<br>reflector             |

| Order Code   | Full Product Name                              | Luminous<br>Flux | Number<br>of light<br>sources | Optic type            |
|--------------|------------------------------------------------|------------------|-------------------------------|-----------------------|
| 911401524244 | DN391B LED12/830 PSU<br>D150 AL WP GCG2HE      | 1,150 lm         | 1                             | Facetted<br>reflector |
| 911401528544 | DN392B LED20/865<br>P16PSU D150 AL GMG2HE      | 2,000 lm         | 1                             | Facetted<br>reflector |
| 911401528644 | DN392B LED20/840<br>P16PSU D150 AL GMG2HE      | 2,000 lm         | 1                             | Facetted<br>reflector |
| 911401528744 | DN392B LED20/830<br>P16PSU D150 AL GMG2HE      | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401529144 | DN392B LED20/865 PSU<br>D150 AL GCG2HE         | 2,000 lm         | 1                             | Facetted<br>reflector |
| 911401529244 | DN392B LED20/840 PSU<br>D150 AL GCG2HE         | 2,000 lm         | 1                             | Facetted<br>reflector |
| 911401529344 | DN392B LED20/830 PSU<br>D150 AL GCG2HE         | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401530944 | DN392B LED18/865<br>P14PSU D150 AL GMG2HE      | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401531044 | DN392B LED18/840<br>P14PSU D150 AL GMG2HE      | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401531144 | DN392B LED18/830<br>P14PSU D150 AL GMG2HE      | 1,700 lm         | 1                             | Facetted<br>reflector |
| 911401531544 | DN392B LED18/865 PSU<br>D150 AL GCG2HE         | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401531644 | DN392B LED18/840 PSU<br>D150 AL GCG2HE         | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401531744 | DN392B LED18/830 PSU<br>D150 AL GCG2HE         | 1,700 lm         | 1                             | Facetted<br>reflector |
| 911401532144 | DN391B LED12/865<br>P10PSU D150 AL GMG2HE      | 1,250 lm         | 1                             | Facetted<br>reflector |
| 911401532244 | DN391B LED12/840<br>P10PSU D150 AL GMG2HE      | 1,250 lm         | 1                             | Facetted<br>reflector |
| 911401532344 | DN391B LED12/830<br>P10PSU D150 AL GMG2HE      | 1,150 lm         | 1                             | Facetted<br>reflector |
| 911401532744 | DN391B LED12/865 PSU<br>D150 AL GCG2HE         | 1,250 lm         | 1                             | Facetted<br>reflector |
| 911401532844 | DN391B LED12/840 PSU<br>D150 AL GCG2HE         | 1,250 lm         | 1                             | Facetted<br>reflector |
| 911401532944 | DN391B LED13/830 PSU<br>D150 AL GCG2HE         | 1,150 lm         | 1                             | Facetted<br>reflector |
| 911401537244 | DN392X LED18/865<br>P15WIA D150 AL G2HE        | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401537844 | DN392X LED18/830<br>P15WIA D150 AL G2HE        | 1,700 lm         | 1                             | Facetted<br>reflector |
| 911401538444 | DN392X LED18/840<br>P15WIA D150 AL G2HE        | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401565944 | DN392B LED18/865<br>P14PSD D150 ALWP<br>GMG2HE | 1,800 lm         | 48                            | Facetted<br>reflector |
| 911401566044 | DN392B LED18/840<br>P14PSD D150 ALWP<br>GMG2HE | 1,800 lm         | 48                            | Facetted<br>reflector |

| Order Code   | Full Product Name                              | Luminous<br>Flux | Number<br>of light<br>sources | Optic type            |
|--------------|------------------------------------------------|------------------|-------------------------------|-----------------------|
| 911401566144 | DN392B LED18/830<br>P14PSD D150 ALWP<br>GMG2HE | 1,650 lm         | 48                            | Facetted<br>reflector |
| 911401566244 | DN392B LED18/865<br>P14PSD D150 AL GMG2HE      | 1,800 lm         | 48                            | Facetted<br>reflector |
| 911401566344 | DN392B LED18/840<br>P14PSD D150 AL GMG2HE      | 1,800 lm         | 48                            | Facetted<br>reflector |
| 911401566444 | DN392B LED18/830<br>P14PSD D150 AL GMG2HE      | 1,650 lm         | 48                            | Facetted<br>reflector |
| 911401568044 | DN392B LED22/865<br>P17PSD D150 ALWP<br>GMG2HE | 2,200 lm         | 48                            | Facetted<br>reflector |
| 911401568144 | DN392B LED22/840<br>P17PSD D150 ALWP<br>GMG2HE | 2,200 lm         | 48                            | Facetted<br>reflector |
| 911401568244 | DN392B LED22/830<br>P17PSD D150 ALWP<br>GMG2HE | 2,000 lm         | 48                            | Facetted<br>reflector |
| 911401568344 | DN392B LED22/865 PSD<br>D150 AL WP GCG2HE      | 2,200 lm         | 48                            | Facetted<br>reflector |
| 911401568444 | DN392B LED22/840 PSD<br>D150 AL WP GCG2HE      | 2,200 lm         | 48                            | Facetted<br>reflector |
| 911401568544 | DN392B LED22/830 PSD<br>D150 AL WP GCG2HE      | 2,000 lm         | 48                            | Facetted<br>reflector |
| 911401569244 | DN392B LED18/865 PSD<br>D150 AL WP GCG2HE      | 1,800 lm         | 48                            | Facetted<br>reflector |
| 911401569344 | DN392B LED18/840 PSD<br>D150 AL WP GCG2HE      | 1,800 lm         | 48                            | Facetted<br>reflector |
| 911401569444 | DN392B LED18/830 PSD<br>D150 AL WP GCG2HE      | 1,650 lm         | 48                            | Facetted<br>reflector |
| 911401569544 | DN391B LED12/865 P11PSD<br>D150 ALWP GMG2HE    | 1,250 lm         | 24                            | Facetted<br>reflector |
| 911401569644 | DN391B LED12/840 P11PSD<br>D150 ALWP GMG2HE    | 1,250 lm         | 24                            | Facetted<br>reflector |
| 911401569744 | DN391B LED12/830 P11PSD<br>D150 ALWP GMG2HE    | 1,150 lm         | 24                            | Facetted<br>reflector |
| 911401569844 | DN391B LED12/865 PSD<br>D150 AL WP GCG2HE      | 1,250 lm         | 24                            | Facetted<br>reflector |
| 911401569944 | DN391B LED12/840 PSD<br>D150 AL WP GCG2HE      | 1,250 lm         | 24                            | Facetted<br>reflector |
| 911401570044 | DN391B LED12/830 PSD<br>D150 AL WP GCG2HE      | 1,150 lm         | 24                            | Facetted<br>reflector |
| 911401573744 | DN392B LED22/865<br>P17PSD D150 AL GMG2HE      | 2,200 lm         | 48                            | Facetted<br>reflector |
| 911401573844 | DN392B LED22/840<br>P17PSD D150 AL GMG2HE      | 2,200 lm         | 48                            | Facetted<br>reflector |
| 911401573944 | DN392B LED22/830<br>P17PSD D150 AL GMG2HE      | 2,000 lm         | 48                            | Facetted<br>reflector |
| 911401574344 | DN392B LED22/865 PSD<br>D150 AL GCG2HE         | 2,200 lm         | 48                            | Facetted<br>reflector |

| Order Code   | Full Product Name                              | Luminous<br>Flux | Number<br>of light<br>sources | Optic type                        |
|--------------|------------------------------------------------|------------------|-------------------------------|-----------------------------------|
| 911401574444 | DN392B LED22/840 PSD<br>D150 AL GCG2HE         | 2,200 lm         | 48                            | Facetted<br>reflector             |
| 911401574544 | DN392B LED22/830 PSD<br>D150 AL GCG2HE         | 2,000 lm         | 48                            | Facetted<br>reflector             |
| 911401576144 | DN392B LED18/865 PSD<br>D150 AL GCG2HE         | 1,800 lm         | 48                            | Facetted<br>reflector             |
| 911401576244 | DN392B LED18/840 PSD<br>D150 AL GCG2HE         | 1,800 lm         | 48                            | Facetted<br>reflector             |
| 911401576344 | DN392B LED18/830 PSD<br>D150 AL GCG2HE         | 1,650 lm         | 48                            | Facetted<br>reflector             |
| 911401576744 | DN391B LED12/865 P11PSD<br>D150 AL GMG2HE      | 1,250 lm         | 24                            | Facetted<br>reflector             |
| 911401576844 | DN391B LED12/840 P11PSD<br>D150 AL GMG2HE      | 1,250 lm         | 24                            | Facetted<br>reflector             |
| 911401576944 | DN391B LED12/830 P11PSD<br>D150 AL GMG2HE      | 1,150 lm         | 24                            | Facetted<br>reflector             |
| 911401577344 | DN391B LED12/865 PSD<br>D150 AL GCG2HE         | 1,250 lm         | 24                            | Facetted<br>reflector             |
| 911401577444 | DN391B LED12/840 PSD<br>D150 AL GCG2HE         | 1,250 lm         | 24                            | Facetted<br>reflector             |
| 911401577544 | DN391B LED12/830 PSD<br>D150 AL GCG2HE         | 1,150 lm         | 24                            | Facetted<br>reflector             |
| 911401577142 | DN393X LED22/840<br>P20L1W D200 AL CAUG2       | 2,250 lm         | 1                             | White reflector<br>and opal cover |
| 911401577442 | DN392X LED17/840<br>P15L1W D150 AL CAUG2       | 1,650 lm         | 1                             | Facetted<br>reflector             |
| 911401503745 | DN391X LED7/9TNW<br>P7PSD D100 AL WP G2        | 750 lm           | 20                            | Facetted<br>reflector             |
| 911401524344 | DN391B LED14/865 P11PSU<br>D100 ALWP GMG2HE    | 1,400 lm         | 1                             | Facetted<br>reflector             |
| 911401524444 | DN391B LED14/840 P11PSU<br>D100 ALWP GMG2HE    | 1,400 lm         | 1                             | Facetted<br>reflector             |
| 911401524544 | DN391B LED14/830 P11PSU<br>D100 ALWP GMG2HE    | 1,300 lm         | 1                             | Facetted<br>reflector             |
| 911401524644 | DN391B LED14/865 PSU<br>D100 AL WP GCG2HE      | 1,400 lm         | 1                             | Facetted<br>reflector             |
| 911401524744 | DN391B LED14/840 PSU<br>D100 AL WP GCG2HE      | 1,400 lm         | 1                             | Facetted<br>reflector             |
| 911401524844 | DN391B LED14/830 PSU<br>D100 AL WP GCG2HE      | 1,300 lm         | 1                             | Facetted<br>reflector             |
| 911401524944 | DN391B LED12/865<br>P10PSU D100 ALWP<br>GMG2HE | 1,200 lm         | 1                             | Facetted<br>reflector             |
| 911401525044 | DN391B LED12/840<br>P10PSU D100 ALWP<br>GMG2HE | 1,200 lm         | 1                             | Facetted<br>reflector             |
| 911401525144 | DN391B LED12/830<br>P10PSU D100 ALWP<br>GMG2HE | 1,100 lm         | 1                             | Facetted<br>reflector             |

| Order Code   | Full Product Name                          | Luminous<br>Flux | Number<br>of light<br>sources | Optic type            |
|--------------|--------------------------------------------|------------------|-------------------------------|-----------------------|
| 911401525244 | DN391B LED12/865 PSU<br>D100 AL WP GCG2HE  | 1,200 lm         | 1                             | Facetted<br>reflector |
| 911401525344 | DN391B LED12/840 PSU<br>D100 AL WP GCG2HE  | 1,200 lm         | 1                             | Facetted<br>reflector |
| 911401525444 | DN391B LED12/830 PSU<br>D100 AL WP GCG2HE  | 1,100 lm         | 1                             | Facetted<br>reflector |
| 911401525544 | DN390B LED7/865 P6PSU<br>D100 AL WP GMG2HE | 700 lm           | 1                             | Facetted<br>reflector |
| 911401525644 | DN390B LED7/840 P6PSU<br>D100 AL WP GMG2HE | 700 lm           | 1                             | Facetted<br>reflector |
| 911401525744 | DN390B LED7/830 P6PSU<br>D100 AL WP GMG2HE | 650 lm           | 1                             | Facetted<br>reflector |
| 911401525844 | DN390B LED7/865 PSU<br>D100 AL WP GCG2HE   | 700 lm           | 1                             | Facetted<br>reflector |
| 911401525944 | DN390B LED7/840 PSU<br>D100 AL WP GCG2HE   | 700 lm           | 1                             | Facetted<br>reflector |
| 911401526044 | DN390B LED7/830 PSU<br>D100 AL WP GCG2HE   | 650 lm           | 1                             | Facetted<br>reflector |
| 911401533344 | DN391B LED14/865 P11PSU<br>D100 AL GMG2HE  | 1,400 lm         | 1                             | Facetted<br>reflector |
| 911401533444 | DN391B LED14/840 P11PSU<br>D100 AL GMG2HE  | 1,400 lm         | 1                             | Facetted<br>reflector |
| 911401533544 | DN391B LED14/830 P11PSU<br>D100 AL GMG2HE  | 1,300 lm         | 1                             | Facetted<br>reflector |
| 911401533944 | DN391B LED14/865 PSU<br>D100 AL GCG2HE     | 1,400 lm         | 1                             | Facetted<br>reflector |
| 911401534044 | DN391B LED14/840 PSU<br>D100 AL GCG2HE     | 1,400 lm         | 1                             | Facetted<br>reflector |
| 911401534144 | DN391B LED14/830 PSU<br>D100 AL GCG2HE     | 1,300 lm         | 1                             | Facetted<br>reflector |
| 911401534544 | DN391B LED12/865<br>P10PSU D100 AL GMG2HE  | 1,200 lm         | 1                             | Facetted<br>reflector |
| 911401534644 | DN391B LED12/840<br>P10PSU D100 AL GMG2HE  | 1,200 lm         | 1                             | Facetted<br>reflector |
| 911401534744 | DN391B LED12/830<br>P10PSU D100 AL GMG2HE  | 1,100 lm         | 1                             | Facetted<br>reflector |
| 911401535144 | DN391B LED12/865 PSU<br>D100 AL GCG2HE     | 1,200 lm         | 1                             | Facetted<br>reflector |
| 911401535244 | DN391B LED12/840 PSU<br>D100 AL GCG2HE     | 1,200 lm         | 1                             | Facetted<br>reflector |
| 911401535444 | DN391B LED12/830 PSU<br>D100 AL GCG2HE     | 1,100 lm         | 1                             | Facetted<br>reflector |
| 911401535844 | DN390B LED7/865 P6PSU<br>D100 AL GMG2HE    | 700 lm           | 1                             | Facetted<br>reflector |
| 911401535944 | DN390B LED7/840 P6PSU<br>D100 AL GMG2HE    | 700 lm           | 1                             | Facetted<br>reflector |
| 911401536044 | DN390B LED7/830 P6PSU<br>D100 AL GMG2HE    | 650 lm           | 1                             | Facetted<br>reflector |
| 911401536444 | DN390B LED7/865 PSU<br>D100 AL GCG2HE      | 700 lm           | 1                             | Facetted<br>reflector |

| Order Code   | Full Product Name                              | Luminous Flux | Number of light sources | Optic type         |
|--------------|------------------------------------------------|---------------|-------------------------|--------------------|
| 911401536544 | DN390B LED7/840 PSU<br>D100 AL GCG2HE          | 700 lm        | 1                       | Facetted reflector |
| 911401536644 | DN390B LED7/830 PSU<br>D100 AL GCG2HE          | 650 lm        | 1                       | Facetted reflector |
| 911401537444 | DN391X LED14/865<br>P12WIA D100 AL G2HE        | 1,400 lm      | 1                       | Facetted reflector |
| 911401538044 | DN391X LED14/830<br>P12WIA D100 AL G2HE        | 1,400 lm      | 1                       | Facetted reflector |
| 911401538644 | DN391X LED14/840<br>P12WIA D100 AL G2HE        | 1,400 lm      | 1                       | Facetted reflector |
| 911401570144 | DN391B LED14/865<br>P12PSD D100 ALWP<br>GMG2HE | 1,400 lm      | 28                      | Facetted reflector |
| 911401570244 | DN391B LED14/840<br>P12PSD D100 ALWP<br>GMG2HE | 1,400 lm      | 28                      | Facetted reflector |
| 911401570344 | DN391B LED14/830<br>P12PSD D100 ALWP<br>GMG2HE | 1,300 lm      | 28                      | Facetted reflector |
| 911401570444 | DN391B LED14/865 PSD<br>D100 AL WP GCG2HE      | 1,400 lm      | 28                      | Facetted reflector |
| 911401570544 | DN391B LED14/840 PSD<br>D100 AL WP GCG2HE      | 1,400 lm      | 28                      | Facetted reflector |
| 911401570644 | DN391B LED14/830 PSD<br>D100 AL WP GCG2HE      | 1,300 lm      | 28                      | Facetted reflector |
| 911401570744 | DN391B LED12/865<br>P10PSD D100 ALWP<br>GMG2HE | 1,200 lm      | 28                      | Facetted reflector |
| 911401570844 | DN391B LED12/840<br>P10PSD D100 ALWP<br>GMG2HE | 1,200 lm      | 28                      | Facetted reflector |
| 911401570944 | DN391B LED12/830<br>P10PSD D100 ALWP<br>GMG2HE | 1,100 lm      | 28                      | Facetted reflector |
| 911401571044 | DN391B LED12/865 PSD<br>D100 AL WP GCG2HE      | 1,200 lm      | 28                      | Facetted reflector |
| 911401571144 | DN391B LED12/840 PSD<br>D100 AL WP GCG2HE      | 1,200 lm      | 28                      | Facetted reflector |
| 911401571244 | DN391B LED12/830 PSD<br>D100 AL WP GCG2HE      | 1,100 lm      | 28                      | Facetted reflector |
| 911401577944 | DN391B LED14/865<br>P12PSD D100 AL GMG2HE      | 1,400 lm      | 28                      | Facetted reflector |
| 911401578044 | DN391B LED14/840<br>P12PSD D100 AL GMG2HE      | 1,400 lm      | 28                      | Facetted reflector |
| 911401578144 | DN391B LED14/830<br>P12PSD D100 AL GMG2HE      | 1,300 lm      | 28                      | Facetted reflector |
| 911401578544 | DN391B LED14/865 PSD<br>D100 AL GCG2HE         | 1,400 lm      | 28                      | Facetted reflector |
| 911401578644 | DN391B LED14/840 PSD<br>D100 AL GCG2HE         | 1,400 lm      | 28                      | Facetted reflector |

| Order Code   | Full Product Name                              | Luminous Flux | Number of light sources | Optic type                     |
|--------------|------------------------------------------------|---------------|-------------------------|--------------------------------|
| 911401578744 | DN391B LED14/830 PSD<br>D100 AL GCG2HE         | 1,300 lm      | 28                      | Facetted reflector             |
| 911401579144 | DN391B LED12/865<br>P10PSD D100 AL GMG2HE      | 1,200 lm      | 28                      | Facetted reflector             |
| 911401579244 | DN391B LED12/840<br>P10PSD D100 AL GMG2HE      | 1,200 lm      | 28                      | Facetted reflector             |
| 911401579344 | DN391B LED12/830<br>P10PSD D100 AL GMG2HE      | 1,100 lm      | 28                      | Facetted reflector             |
| 911401579744 | DN391B LED12/865 PSD<br>D100 AL GCG2HE         | 1,200 lm      | 28                      | Facetted reflector             |
| 911401579844 | DN391B LED12/840 PSD<br>D100 AL GCG2HE         | 1,200 lm      | 28                      | Facetted reflector             |
| 911401579944 | DN391B LED12/830 PSD<br>D100 AL GCG2HE         | 1,100 lm      | 28                      | Facetted reflector             |
| 911401503845 | DN394X LED34/9TNW<br>P27PSD D200 WH WP G2      | 3,400 lm      | 96                      | White reflector and opal cover |
| 911401504145 | DN394X LED34/9TNW<br>P27PSD D200 WH<br>WPCAUG2 | 3,400 lm      | 96                      | White reflector and opal cover |
| 911401519944 | DN393B LED26/840<br>P20PSU D200WHWP<br>CAUG2HE | 2,600 lm      | 1                       | White reflector and opal cover |
| 911401520344 | DN393B LED26/840<br>P20PSU D200 WH<br>CAUG2HE  | 2,600 lm      | 1                       | White reflector and opal cover |
| 911401526444 | DN394B LED40/865<br>P29PSU D200 WH<br>GMG2HE   | 4,000 lm      | 1                       | White reflector and opal cover |
| 911401526544 | DN394B LED40/840<br>P29PSU D200 WH<br>GMG2HE   | 4,000 lm      | 1                       | White reflector and opal cover |
| 911401526644 | DN394B LED40/830<br>P29PSU D200 WH<br>GMG2HE   | 3,700 lm      | 1                       | White reflector and opal cover |
| 911401527044 | DN394B LED40/865 PSU<br>D200 WH GCG2HE         | 4,000 lm      | 1                       | White reflector and opal cover |
| 911401527144 | DN394B LED40/840 PSU<br>D200 WH GCG2HE         | 4,000 lm      | 1                       | White reflector and opal cover |
| 911401527244 | DN394B LED40/830 PSU<br>D200 WH GCG2HE         | 3,700 lm      | 1                       | White reflector and opal cover |
| 911401527644 | DN393B LED26/865<br>P19PSU D200 WH<br>GMG2HE   | 2,600 lm      | 1                       | White reflector and opal cover |
| 911401527744 | DN393B LED26/840<br>P19PSU D200 WH<br>GMG2HE   | 2,600 lm      | 1                       | White reflector and opal cover |
| 911401527844 | DN393B LED26/830<br>P19PSU D200 WH<br>GMG2HE   | 2,400 lm      | 1                       | White reflector and opal cover |

| Order Code   | Full Product Name                      | Luminous Flux | Number of light sources | Optic type                     |
|--------------|----------------------------------------|---------------|-------------------------|--------------------------------|
| 911401528244 | DN393B LED26/865 PSU D200 WH GCG2HE    | 2,600 lm      | 1                       | White reflector and opal cover |
| 911401528344 | DN393B LED26/840 PSU D200 WH GCG2HE    | 2,600 lm      | 1                       | White reflector and opal cover |
| 911401528444 | DN393B LED26/830 PSU D200 WH GCG2HE    | 2,400 lm      | 1                       | White reflector and opal cover |
| 911401530044 | DN392B LED20/865 P14PSU D200 WH GMG2HE | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401530144 | DN392B LED20/840 P14PSU D200 WH GMG2HE | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401530244 | DN392B LED20/830 P14PSU D200 WH GMG2HE | 1,850 lm      | 1                       | White reflector and opal cover |
| 911401530644 | DN392B LED20/865 PSU D200 WH GCG2HE    | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401530744 | DN392B LED20/840 PSU D200 WH GCG2HE    | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401530844 | DN392B LED20/830 PSU D200 WH GCG2HE    | 1,850 lm      | 1                       | White reflector and opal cover |
| 911401537144 | DN393X LED26/865 P20WIA D200 WH G2HE   | 2,600 lm      | 1                       | White reflector and opal cover |
| 911401537744 | DN393X LED26/830 P20WIA D200 WH G2HE   | 2,400 lm      | 1                       | White reflector and opal cover |
| 911401538344 | DN393X LED26/840 P20WIA D200 WH G2HE   | 2,600 lm      | 1                       | White reflector and opal cover |
| 911401571644 | DN394B LED40/865 P29PSD D200 WH GMG2HE | 4,000 lm      | 78                      | White reflector and opal cover |
| 911401571744 | DN394B LED40/840 P29PSD D200 WH GMG2HE | 4,000 lm      | 78                      | White reflector and opal cover |
| 911401571844 | DN394B LED40/830 P29PSD D200 WH GMG2HE | 3,700 lm      | 78                      | White reflector and opal cover |
| 911401572244 | DN394B LED40/865 PSD D200 WH GCG2HE    | 4,000 lm      | 78                      | White reflector and opal cover |
| 911401572344 | DN394B LED40/840 PSD D200 WH GCG2HE    | 4,000 lm      | 78                      | White reflector and opal cover |
| 911401572444 | DN394B LED40/830 PSD D200 WH GCG2HE    | 3,700 lm      | 78                      | White reflector and opal cover |
| 911401572844 | DN393B LED26/865 P20PSD D200 WH GMG2HE | 2,600 lm      | 48                      | White reflector and opal cover |
| 911401572944 | DN393B LED26/840 P20PSD D200 WH GMG2HE | 2,600 lm      | 48                      | White reflector and opal cover |

| Order Code   | Full Product Name                        | Luminous Flux | Number of light sources | Optic type                     |
|--------------|------------------------------------------|---------------|-------------------------|--------------------------------|
| 911401573044 | DN393B LED26/830 P20PSD D200 WH GMG2HE   | 2,400 lm      | 48                      | White reflector and opal cover |
| 911401573444 | DN393B LED26/865 PSD D200 WH GCG2HE      | 2,600 lm      | 48                      | White reflector and opal cover |
| 911401573544 | DN393B LED26/840 PSD D200 WH GCG2HE      | 2,600 lm      | 48                      | White reflector and opal cover |
| 911401573644 | DN393B LED26/830 PSD D200 WH GCG2HE      | 2,400 lm      | 48                      | White reflector and opal cover |
| 911401575244 | DN392B LED18/865 P14PSD D200 WH GMG2HE   | 1,850 lm      | 48                      | White reflector and opal cover |
| 911401575344 | DN392B LED18/840 P14PSD D200 WH GMG2HE   | 1,850 lm      | 48                      | White reflector and opal cover |
| 911401575444 | DN392B LED18/830 P14PSD D200 WH GMG2HE   | 1,700 lm      | 48                      | White reflector and opal cover |
| 911401575844 | DN392B LED18/865 PSD D200 WH GCG2HE      | 1,850 lm      | 48                      | White reflector and opal cover |
| 911401575944 | DN392B LED18/840 PSD D200 WH GCG2HE      | 1,850 lm      | 48                      | White reflector and opal cover |
| 911401576044 | DN392B LED18/830 PSD D200 WH GCG2HE      | 1,700 lm      | 48                      | White reflector and opal cover |
| 911401586932 | DN393B LED22/840 P20PSU D200 WH CAUG2    | 2,400 lm      | 48                      | White reflector and opal cover |
| 911401588632 | DN393B LED22/840 P20PSU D200 WH WP CAUG2 | 2,400 lm      | 48                      | White reflector and opal cover |
| 911401503545 | DN394X LED33/9TNW P27PSD D200 AL WP G2   | 3,300 lm      | 96                      | Facetted reflector             |
| 911401520744 | DN394B LED38/865 P29PSU D200 ALWP GMG2HE | 3,800 lm      | 1                       | Facetted reflector             |
| 911401520844 | DN394B LED38/840 P29PSU D200 ALWP GMG2HE | 3,800 lm      | 1                       | Facetted reflector             |
| 911401520944 | DN394B LED38/830 P29PSU D200 ALWP GMG2HE | 3,500 lm      | 1                       | Facetted reflector             |
| 911401521044 | DN394B LED38/865 PSU D200 AL WP GCG2HE   | 3,800 lm      | 1                       | Facetted reflector             |
| 911401521144 | DN394B LED38/840 PSU D200 AL WP GCG2HE   | 3,800 lm      | 1                       | Facetted reflector             |
| 911401521244 | DN394B LED38/830 PSU D200 AL WP GCG2HE   | 3,500 lm      | 1                       | Facetted reflector             |
| 911401521344 | DN393B LED25/865 P19PSU D200 ALWP GMG2HE | 2,500 lm      | 1                       | Facetted reflector             |

| Order Code   | Full Product Name                              | Luminous<br>Flux | Number<br>of light<br>sources | Optic type            |
|--------------|------------------------------------------------|------------------|-------------------------------|-----------------------|
| 911401521444 | DN393B LED25/840<br>P19PSU D200 ALWP<br>GMG2HE | 2,500 lm         | 1                             | Facetted<br>reflector |
| 911401521544 | DN393B LED25/830<br>P19PSU D200 ALWP<br>GMG2HE | 2,300 lm         | 1                             | Facetted<br>reflector |
| 911401521644 | DN393B LED25/865 PSU<br>D200 AL WP GCG2HE      | 2,500 lm         | 1                             | Facetted<br>reflector |
| 911401521744 | DN393B LED25/840 PSU<br>D200 AL WP GCG2HE      | 2,500 lm         | 1                             | Facetted<br>reflector |
| 911401521844 | DN393B LED25/830 PSU<br>D200 AL WP GCG2HE      | 2,300 lm         | 1                             | Facetted<br>reflector |
| 911401522544 | DN392B LED18/865<br>P14PSU D200 ALWP<br>GMG2HE | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401522644 | DN392B LED18/840<br>P14PSU D200 ALWP<br>GMG2HE | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401522744 | DN392B LED18/830<br>P14PSU D200 ALWP<br>GMG2HE | 1,700 lm         | 1                             | Facetted<br>reflector |
| 911401522844 | DN392B LED18/865 PSU<br>D200 AL WP GCG2HE      | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401522944 | DN392B LED18/840 PSU<br>D200 AL WP GCG2HE      | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401523044 | DN392B LED18/830 PSU<br>D200 AL WP GCG2HE      | 1,700 lm         | 1                             | Facetted<br>reflector |
| 911401526144 | DN394B LED38/865<br>P29PSU D200 AL GMG2HE      | 3,800 lm         | 1                             | Facetted<br>reflector |
| 911401526244 | DN394B LED38/840<br>P29PSU D200 AL GMG2HE      | 3,800 lm         | 1                             | Facetted<br>reflector |
| 911401526344 | DN394B LED38/830<br>P29PSU D200 AL GMG2HE      | 3,500 lm         | 1                             | Facetted<br>reflector |
| 911401526744 | DN394B LED38/865 PSU<br>D200 AL GCG2HE         | 3,800 lm         | 1                             | Facetted<br>reflector |
| 911401526844 | DN394B LED38/840 PSU<br>D200 AL GCG2HE         | 3,800 lm         | 1                             | Facetted<br>reflector |
| 911401526944 | DN394B LED38/830 PSU<br>D200 AL GCG2HE         | 3,500 lm         | 1                             | Facetted<br>reflector |
| 911401527344 | DN393B LED25/865<br>P19PSU D200 AL GMG2HE      | 2,500 lm         | 1                             | Facetted<br>reflector |
| 911401527444 | DN393B LED25/840<br>P19PSU D200 AL GMG2HE      | 2,500 lm         | 1                             | Facetted<br>reflector |
| 911401527544 | DN393B LED25/830<br>P19PSU D200 AL GMG2HE      | 2,300 lm         | 1                             | Facetted<br>reflector |
| 911401527944 | DN393B LED25/865 PSU<br>D200 AL GCG2HE         | 2,500 lm         | 1                             | Facetted<br>reflector |
| 911401528044 | DN393B LED25/840 PSU<br>D200 AL GCG2HE         | 2,500 lm         | 1                             | Facetted<br>reflector |

| Order Code   | Full Product Name                              | Luminous<br>Flux | Number<br>of light<br>sources | Optic type            |
|--------------|------------------------------------------------|------------------|-------------------------------|-----------------------|
| 911401528144 | DN393B LED25/830 PSU<br>D200 AL GCG2HE         | 2,300 lm         | 1                             | Facetted<br>reflector |
| 911401529744 | DN392B LED18/865<br>P14PSU D200 AL GMG2HE      | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401529844 | DN392B LED18/840<br>P14PSU D200 AL GMG2HE      | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401529944 | DN392B LED18/830<br>P14PSU D200 AL GMG2HE      | 1,700 lm         | 1                             | Facetted<br>reflector |
| 911401530344 | DN392B LED18/865 PSU<br>D200 AL GCG2HE         | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401530444 | DN392B LED18/840 PSU<br>D200 AL GCG2HE         | 1,850 lm         | 1                             | Facetted<br>reflector |
| 911401530544 | DN392B LED18/830 PSU<br>D200 AL GCG2HE         | 1,700 lm         | 1                             | Facetted<br>reflector |
| 911401537044 | DN393X LED25/865<br>P20WIA D200 AL G2HE        | 2,500 lm         | 1                             | Facetted<br>reflector |
| 911401537644 | DN393X LED25/830<br>P20WIA D200 AL G2HE        | 2,300 lm         | 1                             | Facetted<br>reflector |
| 911401538244 | DN393X LED25/840<br>P20WIA D200 AL G2HE        | 2,500 lm         | 1                             | Facetted<br>reflector |
| 911401566844 | DN394B LED38/865<br>P29PSD D200 ALWP<br>GMG2HE | 3,800 lm         | 78                            | Facetted<br>reflector |
| 911401566944 | DN394B LED38/840<br>P29PSD D200 ALWP<br>GMG2HE | 3,800 lm         | 78                            | Facetted<br>reflector |
| 911401567044 | DN394B LED38/830<br>P29PSD D200 ALWP<br>GMG2HE | 3,800 lm         | 78                            | Facetted<br>reflector |
| 911401567144 | DN394B LED38/865 PSD<br>D200 AL WP GCG2HE      | 3,800 lm         | 78                            | Facetted<br>reflector |
| 911401567244 | DN394B LED38/840 PSD<br>D200 AL WP GCG2HE      | 3,800 lm         | 78                            | Facetted<br>reflector |
| 911401567344 | DN394B LED38/830 PSD<br>D200 AL WP GCG2HE      | 3,500 lm         | 78                            | Facetted<br>reflector |
| 911401567444 | DN393B LED25/865<br>P20PSD D200 ALWP<br>GMG2HE | 2,500 lm         | 48                            | Facetted<br>reflector |
| 911401567544 | DN393B LED25/840<br>P20PSD D200 ALWP<br>GMG2HE | 2,500 lm         | 48                            | Facetted<br>reflector |
| 911401567644 | DN393B LED25/830<br>P20PSD D200 ALWP<br>GMG2HE | 2,300 lm         | 48                            | Facetted<br>reflector |
| 911401567744 | DN393B LED25/865 PSD<br>D200 AL WP GCG2HE      | 2,500 lm         | 48                            | Facetted<br>reflector |
| 911401567844 | DN393B LED25/840 PSD<br>D200 AL WP GCG2HE      | 2,500 lm         | 48                            | Facetted<br>reflector |
| 911401567944 | DN393B LED25/830 PSD<br>D200 AL WP GCG2HE      | 2,300 lm         | 48                            | Facetted<br>reflector |

| Order Code   | Full Product Name                              | Luminous Flux | Number of light sources | Optic type         |
|--------------|------------------------------------------------|---------------|-------------------------|--------------------|
| 911401568644 | DN392B LED18/865<br>P14PSD D200 ALWP<br>GMG2HE | 1,750 lm      | 48                      | Facetted reflector |
| 911401568744 | DN392B LED18/840<br>P14PSD D200 ALWP<br>GMG2HE | 1,750 lm      | 48                      | Facetted reflector |
| 911401568844 | DN392B LED18/830<br>P14PSD D200 ALWP<br>GMG2HE | 1,650 lm      | 48                      | Facetted reflector |
| 911401568944 | DN392B LED18/865 PSD<br>D200 AL WP GCG2HE      | 1,750 lm      | 48                      | Facetted reflector |
| 911401569044 | DN392B LED18/840 PSD<br>D200 AL WP GCG2HE      | 1,750 lm      | 48                      | Facetted reflector |
| 911401569144 | DN392B LED18/830 PSD<br>D200 AL WP GCG2HE      | 1,650 lm      | 48                      | Facetted reflector |
| 911401571344 | DN394B LED38/865<br>P29PSD D200 AL<br>GMG2HE   | 3,800 lm      | 78                      | Facetted reflector |
| 911401571444 | DN394B LED38/840<br>P29PSD D200 AL<br>GMG2HE   | 3,800 lm      | 78                      | Facetted reflector |
| 911401571544 | DN394B LED38/830<br>P29PSD D200 AL<br>GMG2HE   | 3,500 lm      | 78                      | Facetted reflector |
| 911401571944 | DN394B LED38/865 PSD<br>D200 AL GCG2HE         | 3,800 lm      | 78                      | Facetted reflector |
| 911401572044 | DN394B LED38/840 PSD<br>D200 AL GCG2HE         | 3,800 lm      | 78                      | Facetted reflector |
| 911401572144 | DN394B LED38/830 PSD<br>D200 AL GCG2HE         | 3,500 lm      | 78                      | Facetted reflector |
| 911401572544 | DN393B LED25/865<br>P20PSD D200 AL<br>GMG2HE   | 2,500 lm      | 48                      | Facetted reflector |
| 911401572644 | DN393B LED25/840<br>P20PSD D200 AL<br>GMG2HE   | 2,500 lm      | 48                      | Facetted reflector |
| 911401572744 | DN393B LED25/830<br>P20PSD D200 AL<br>GMG2HE   | 2,300 lm      | 48                      | Facetted reflector |
| 911401573144 | DN393B LED25/865 PSD<br>D200 AL GCG2HE         | 2,500 lm      | 48                      | Facetted reflector |
| 911401573244 | DN393B LED25/840 PSD<br>D200 AL GCG2HE         | 2,500 lm      | 48                      | Facetted reflector |
| 911401573344 | DN393B LED25/830 PSD<br>D200 AL GCG2HE         | 2,300 lm      | 48                      | Facetted reflector |
| 911401574944 | DN392B LED18/865<br>P14PSD D200 AL GMG2HE      | 1,850 lm      | 48                      | Facetted reflector |
| 911401575044 | DN392B LED18/840<br>P14PSD D200 AL GMG2HE      | 1,850 lm      | 48                      | Facetted reflector |

| Order Code   | Full Product Name                              | Luminous Flux | Number of light sources | Optic type                     |
|--------------|------------------------------------------------|---------------|-------------------------|--------------------------------|
| 911401575144 | DN392B LED18/830<br>P14PSD D200 AL GMG2HE      | 1,700 lm      | 48                      | Facetted reflector             |
| 911401575544 | DN392B LED18/865 PSD<br>D200 AL GCG2HE         | 1,750 lm      | 48                      | Facetted reflector             |
| 911401575644 | DN392B LED18/840 PSD<br>D200 AL GCG2HE         | 1,750 lm      | 48                      | Facetted reflector             |
| 911401575744 | DN392B LED18/830 PSD<br>D200 AL GCG2HE         | 1,650 lm      | 48                      | Facetted reflector             |
| 911401577042 | DN393X LED22/840<br>P20L1W D200 WH CAUG2       | 2,450 lm      | 1                       | Facetted reflector             |
| 911401577542 | DN392X LED17/840<br>P15L1W D150 WH CAUG2       | 1,750 lm      | 1                       | Facetted reflector             |
| 911401503945 | DN392X LED17/9TNW<br>P15PSD D150 WH WP G2      | 1,700 lm      | 48                      | White reflector and opal cover |
| 911401504245 | DN392X LED17/9TNW<br>P15PSD D150 WH<br>WPCAUG2 | 1,700 lm      | 48                      | White reflector and opal cover |
| 911401520044 | DN392B LED20/840<br>P15PSU D150WHWP<br>CAUG2HE | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401520144 | DN391B LED13/840 P11PSU<br>D150WHWP CAUG2HE    | 1,300 lm      | 1                       | White reflector and opal cover |
| 911401520444 | DN392B LED20/840<br>P15PSU D150 WH<br>CAUG2HE  | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401520544 | DN391B LED13/840 P11PSU<br>D150 WH CAUG2HE     | 1,300 lm      | 1                       | White reflector and opal cover |
| 911401528844 | DN392B LED22/865<br>P16PSU D150 WH GMG2HE      | 2,200 lm      | 1                       | White reflector and opal cover |
| 911401528944 | DN392B LED22/840<br>P16PSU D150 WH GMG2HE      | 2,200 lm      | 1                       | White reflector and opal cover |
| 911401529044 | DN392B LED22/830<br>P16PSU D150 WH GMG2HE      | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401529444 | DN392B LED22/865 PSU<br>D150 WH GCG2HE         | 2,200 lm      | 1                       | White reflector and opal cover |
| 911401529544 | DN392B LED22/840 PSU<br>D150 WH GCG2HE         | 2,200 lm      | 1                       | White reflector and opal cover |
| 911401529644 | DN392B LED22/830 PSU<br>D150 WH GCG2HE         | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401531244 | DN392B LED20/865<br>P14PSU D150 WH GMG2HE      | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401531344 | DN392B LED20/840<br>P14PSU D150 WH GMG2HE      | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401531444 | DN392B LED20/830<br>P14PSU D150 WH GMG2HE      | 1,850 lm      | 1                       | White reflector and opal cover |
| 911401531844 | DN392B LED20/865 PSU<br>D150 WH GCG2HE         | 2,000 lm      | 1                       | White reflector and opal cover |
| 911401531944 | DN392B LED20/840 PSU<br>D150 WH GCG2HE         | 2,000 lm      | 1                       | White reflector and opal cover |

| Order Code   | Full Product Name                         | Luminous<br>Flux | Number<br>of light<br>sources | Optic type                        |
|--------------|-------------------------------------------|------------------|-------------------------------|-----------------------------------|
| 911401532044 | DN392B LED20/830 PSU<br>D150 WH GCG2HE    | 1,850 lm         | 1                             | White reflector<br>and opal cover |
| 911401532444 | DN391B LED13/865<br>P10PSU D150 WH GMG2HE | 1,300 lm         | 1                             | White reflector<br>and opal cover |
| 911401532544 | DN391B LED13/840<br>P10PSU D150 WH GMG2HE | 1,300 lm         | 1                             | White reflector<br>and opal cover |
| 911401532644 | DN391B LED13/830<br>P10PSU D150 WH GMG2HE | 1,200 lm         | 1                             | White reflector<br>and opal cover |
| 911401533044 | DN391B LED13/865 PSU<br>D150 WH GCG2HE    | 1,300 lm         | 1                             | White reflector<br>and opal cover |
| 911401533144 | DN391B LED13/840 PSU<br>D150 WH GCG2HE    | 1,300 lm         | 1                             | White reflector<br>and opal cover |
| 911401533244 | DN391B LED13/830 PSU<br>D150 WH GCG2HE    | 1,200 lm         | 1                             | White reflector<br>and opal cover |
| 911401537344 | DN392X LED20/865<br>P15WIA D150 WH G2HE   | 2,000 lm         | 1                             | White reflector<br>and opal cover |
| 911401537944 | DN392X LED20/830<br>P15WIA D150 WH G2HE   | 1,850 lm         | 1                             | White reflector<br>and opal cover |
| 911401538544 | DN392X LED20/840<br>P15WIA D150 WH G2HE   | 2,000 lm         | 1                             | White reflector<br>and opal cover |
| 911401566544 | DN392B LED19/865<br>P14PSD D150 WH GMG2HE | 1,900 lm         | 48                            | White reflector<br>and opal cover |
| 911401566644 | DN392B LED19/840<br>P14PSD D150 WH GMG2HE | 1,900 lm         | 48                            | White reflector<br>and opal cover |
| 911401566744 | DN392B LED19/830<br>P14PSD D150 WH GMG2HE | 1,750 lm         | 48                            | White reflector<br>and opal cover |
| 911401574044 | DN392B LED23/865<br>P17PSD D150 WH GMG2HE | 2,300 lm         | 48                            | White reflector<br>and opal cover |
| 911401574144 | DN392B LED23/840<br>P17PSD D150 WH GMG2HE | 2,300 lm         | 48                            | White reflector<br>and opal cover |
| 911401574244 | DN392B LED23/830<br>P17PSD D150 WH GMG2HE | 2,100 lm         | 48                            | White reflector<br>and opal cover |
| 911401574644 | DN392B LED23/865 PSD<br>D150 WH GCG2HE    | 2,300 lm         | 48                            | White reflector<br>and opal cover |

| Order Code   | Full Product Name                              | Luminous<br>Flux | Number<br>of light<br>sources | Optic type                        |
|--------------|------------------------------------------------|------------------|-------------------------------|-----------------------------------|
| 911401574744 | DN392B LED23/840 PSD<br>D150 WH GCG2HE         | 2,300 lm         | 48                            | White reflector<br>and opal cover |
| 911401574844 | DN392B LED23/830 PSD<br>D150 WH GCG2HE         | 2,100 lm         | 48                            | White reflector<br>and opal cover |
| 911401576444 | DN392B LED19/865 PSD<br>D150 WH GCG2HE         | 1,900 lm         | 48                            | White reflector<br>and opal cover |
| 911401576544 | DN392B LED19/840 PSD<br>D150 WH GCG2HE         | 1,900 lm         | 48                            | White reflector<br>and opal cover |
| 911401576644 | DN392B LED19/830 PSD<br>D150 WH GCG2HE         | 1,750 lm         | 48                            | White reflector<br>and opal cover |
| 911401577044 | DN391B LED13/865 P11PSD<br>D150 WH GMG2HE      | 1,300 lm         | 24                            | White reflector<br>and opal cover |
| 911401577144 | DN391B LED13/840<br>P11PSD D150 WH GMG2HE      | 1,300 lm         | 24                            | White reflector<br>and opal cover |
| 911401577244 | DN391B LED13/830 P11PSD<br>D150 WH GMG2HE      | 1,200 lm         | 24                            | White reflector<br>and opal cover |
| 911401577644 | DN391B LED13/865 PSD<br>D150 WH GCG2HE         | 1,300 lm         | 24                            | White reflector<br>and opal cover |
| 911401577744 | DN391B LED13/840 PSD<br>D150 WH GCG2HE         | 1,300 lm         | 24                            | White reflector<br>and opal cover |
| 911401577844 | DN391B LED13/830 PSD<br>D150 WH GCG2HE         | 1,200 lm         | 24                            | White reflector<br>and opal cover |
| 911401585532 | DN391B LED11/840 P11PSU<br>D150 WH CAUG2       | 1,200 lm         | 24                            | White reflector<br>and opal cover |
| 911401585632 | DN392B LED17/840<br>P15PSU D150 WH CAUG2       | 1,800 lm         | 40                            | White reflector<br>and opal cover |
| 911401587832 | DN391B LED11/840 P11PSU<br>D150 WH WP CAUG2    | 1,200 lm         | 24                            | White reflector<br>and opal cover |
| 911401587932 | DN392B LED17/840<br>P15PSU D150 WH WP<br>CAUG2 | 1,800 lm         | 40                            | White reflector<br>and opal cover |

## Operating and Electrical

| Order Code   | Full Product Name                         | Power Consumption | Suitable for<br>random<br>switching |
|--------------|-------------------------------------------|-------------------|-------------------------------------|
| 911401504045 | DN391X LED8/9TNW P7PSD D100<br>WH WP G2   | 7 W               | Yes                                 |
| 911401504345 | DN391X LED8/9TNW P7PSD D100<br>WH WPCAUG2 | 7 W               | Yes                                 |
| 911401520244 | DN390B LED7/840 P6PSU<br>D100WHWP CAUG2HE | 5.8 W             | No                                  |
| 911401520644 | DN390B LED7/840 P6PSU D100<br>WH CAUG2HE  | 5.8 W             | No                                  |
| 911401533644 | DN391B LED15/865 P11PSU D100<br>WH GMG2HE | 11.4 W            | No                                  |

| Order Code   | Full Product Name                         | Power Consumption | Suitable for<br>random<br>switching |
|--------------|-------------------------------------------|-------------------|-------------------------------------|
| 911401533744 | DN391B LED15/840 P11PSU D100<br>WH GMG2HE | 11.4 W            | No                                  |
| 911401533844 | DN391B LED15/830 P11PSU D100<br>WH GMG2HE | 11.4 W            | No                                  |
| 911401534244 | DN391B LED15/865 PSU D100 WH<br>GCG2HE    | 11.4 W            | No                                  |
| 911401534344 | DN391B LED15/840 PSU D100 WH<br>GCG2HE    | 11.4 W            | No                                  |
| 911401534444 | DN391B LED15/830 PSU D100 WH<br>GCG2HE    | 11.4 W            | No                                  |

| Order Code   | Full Product Name                      | Power Consumption | Suitable for random switching |
|--------------|----------------------------------------|-------------------|-------------------------------|
| 911401534844 | DN391B LED12/865 P10PSU D100 WH GMG2HE | 9.8 W             | No                            |
| 911401534944 | DN391B LED12/840 P10PSU D100 WH GMG2HE | 9.8 W             | No                            |
| 911401535044 | DN391B LED12/830 P10PSU D100 WH GMG2HE | 9.8 W             | No                            |
| 911401535544 | DN391B LED12/865 PSU D100 WH GCG2HE    | 9.8 W             | No                            |
| 911401535644 | DN391B LED12/840 PSU D100 WH GCG2HE    | 9.8 W             | No                            |
| 911401535744 | DN391B LED12/830 PSU D100 WH GCG2HE    | 9.8 W             | No                            |
| 911401536144 | DN390B LED7/865 P6PSU D100 WH GMG2HE   | 5.8 W             | No                            |
| 911401536244 | DN390B LED7/840 P6PSU D100 WH GMG2HE   | 5.8 W             | No                            |
| 911401536344 | DN390B LED7/830 P6PSU D100 WH GMG2HE   | 5.8 W             | No                            |
| 911401536744 | DN390B LED7/865 PSU D100 WH GCG2HE     | 5.8 W             | No                            |
| 911401536844 | DN390B LED7/840 PSU D100 WH GCG2HE     | 5.8 W             | No                            |
| 911401536944 | DN390B LED7/830 PSU D100 WH GCG2HE     | 5.8 W             | No                            |
| 911401537544 | DN391X LED15/865 P12WIA D100 WH G2HE   | 12 W              | No                            |
| 911401538144 | DN391X LED15/830 P12WIA D100 WH G2HE   | 12 W              | No                            |
| 911401538744 | DN391X LED15/840 P12WIA D100WH G2HE    | 12 W              | No                            |
| 911401578244 | DN391B LED15/865 P12PSD D100 WH GMG2HE | 12 W              | No                            |
| 911401578344 | DN391B LED15/840 P12PSD D100 WH GMG2HE | 12 W              | No                            |
| 911401578444 | DN391B LED15/830 P12PSD D100 WH GMG2HE | 12 W              | No                            |
| 911401578844 | DN391B LED15/865 PSD D100 WH GCG2HE    | 12 W              | No                            |
| 911401578944 | DN391B LED15/840 PSD D100 WH GCG2HE    | 12 W              | No                            |
| 911401579044 | DN391B LED15/830 PSD D100 WH GCG2HE    | 12 W              | No                            |
| 911401579444 | DN391B LED12/865 P10PSD D100 WH GMG2HE | 10.2 W            | No                            |
| 911401579544 | DN391B LED12/840 P10PSD D100 WH GMG2HE | 10.2 W            | No                            |
| 911401579644 | DN391B LED12/830 P10PSD D100 WH GMG2HE | 10.2 W            | No                            |
| 911401580044 | DN391B LED12/865 PSD D100 WH GCG2HE    | 10.2 W            | No                            |

| Order Code   | Full Product Name                        | Power Consumption | Suitable for random switching |
|--------------|------------------------------------------|-------------------|-------------------------------|
| 911401580144 | DN391B LED12/840 PSD D100 WH GCG2HE      | 10.2 W            | No                            |
| 911401580244 | DN391B LED12/830 PSD D100 WH GCG2HE      | 10.2 W            | No                            |
| 911401584832 | DN390B LED6/840 P8PSU D100 WH CAUG2      | 7.8 W             | No                            |
| 911401587632 | DN390B LED6/840 P8PSU D100 WH WP CAUG2   | 7.8 W             | No                            |
| 911401503645 | DN392X LED16/9TNW P15PSD D150 AL WP G2   | 15 W              | Yes                           |
| 911401521944 | DN392B LED20/865 P16PSU D150 ALWP GMG2HE | 16 W              | No                            |
| 911401522044 | DN392B LED20/840 P16PSU D150 ALWP GMG2HE | 16 W              | No                            |
| 911401522144 | DN392B LED20/830 P16PSU D150 ALWP GMG2HE | 16 W              | No                            |
| 911401522244 | DN392B LED20/865 PSU D150 AL WP GCG2HE   | 16 W              | No                            |
| 911401522344 | DN392B LED20/840 PSU D150 AL WP GCG2HE   | 16 W              | No                            |
| 911401522444 | DN392B LED20/830 PSU D150 AL WP GCG2HE   | 16 W              | No                            |
| 911401523144 | DN392B LED18/865 P14PSU D150 ALWP GMG2HE | 14.4 W            | No                            |
| 911401523244 | DN392B LED18/840 P14PSU D150 ALWP GMG2HE | 14.4 W            | No                            |
| 911401523344 | DN392B LED18/830 P14PSU D150 ALWP GMG2HE | 14.4 W            | No                            |
| 911401523444 | DN392B LED18/865 PSU D150 AL WP GCG2HE   | 14.4 W            | No                            |
| 911401523544 | DN392B LED18/840 PSU D150 AL WP GCG2HE   | 14.4 W            | No                            |
| 911401523644 | DN392B LED18/830 PSU D150 AL WP GCG2HE   | 14.4 W            | No                            |
| 911401523744 | DN391B LED12/865 P10PSU D150 ALWP GMG2HE | 9.8 W             | No                            |
| 911401523844 | DN391B LED12/840 P10PSU D150 ALWP GMG2HE | 9.8 W             | No                            |
| 911401523944 | DN391B LED12/830 P10PSU D150 ALWP GMG2HE | 9.8 W             | No                            |
| 911401524044 | DN391B LED12/865 PSU D150 AL WP GCG2HE   | 9.8 W             | No                            |
| 911401524144 | DN391B LED12/840 PSU D150 AL WP GCG2HE   | 9.8 W             | No                            |
| 911401524244 | DN391B LED12/830 PSU D150 AL WP GCG2HE   | 9.8 W             | No                            |
| 911401528544 | DN392B LED20/865 P16PSU D150 AL GMG2HE   | 16 W              | No                            |
| 911401528644 | DN392B LED20/840 P16PSU D150 AL GMG2HE   | 16 W              | No                            |

| Order Code   | Full Product Name                        | Power Consumption | Suitable for random switching |
|--------------|------------------------------------------|-------------------|-------------------------------|
| 911401528744 | DN392B LED20/830 P16PSU D150 AL GMG2HE   | 16 W              | No                            |
| 911401529144 | DN392B LED20/865 PSU D150 AL GCG2HE      | 16 W              | No                            |
| 911401529244 | DN392B LED20/840 PSU D150 AL GCG2HE      | 16 W              | No                            |
| 911401529344 | DN392B LED20/830 PSU D150 AL GCG2HE      | 16 W              | No                            |
| 911401530944 | DN392B LED18/865 P14PSU D150 AL GMG2HE   | 14.4 W            | No                            |
| 911401531044 | DN392B LED18/840 P14PSU D150 AL GMG2HE   | 14.4 W            | No                            |
| 911401531144 | DN392B LED18/830 P14PSU D150 AL GMG2HE   | 14.4 W            | No                            |
| 911401531544 | DN392B LED18/865 PSU D150 AL GCG2HE      | 14.4 W            | No                            |
| 911401531644 | DN392B LED18/840 PSU D150 AL GCG2HE      | 14.4 W            | No                            |
| 911401531744 | DN392B LED18/830 PSU D150 AL GCG2HE      | 14.4 W            | No                            |
| 911401532144 | DN391B LED12/865 P10PSU D150 AL GMG2HE   | 9.8 W             | No                            |
| 911401532244 | DN391B LED12/840 P10PSU D150 AL GMG2HE   | 9.8 W             | No                            |
| 911401532344 | DN391B LED12/830 P10PSU D150 AL GMG2HE   | 9.8 W             | No                            |
| 911401532744 | DN391B LED12/865 PSU D150 AL GCG2HE      | 9.8 W             | No                            |
| 911401532844 | DN391B LED12/840 PSU D150 AL GCG2HE      | 9.8 W             | No                            |
| 911401532944 | DN391B LED13/830 PSU D150 AL GCG2HE      | 9.8 W             | No                            |
| 911401537244 | DN392X LED18/865 P15WIA D150 AL G2HE     | 15 W              | No                            |
| 911401537844 | DN392X LED18/830 P15WIA D150 AL G2HE     | 15 W              | No                            |
| 911401538444 | DN392X LED18/840 P15WIA D150 AL G2HE     | 15 W              | No                            |
| 911401565944 | DN392B LED18/865 P14PSD D150 ALWP GMG2HE | 13.4 W            | No                            |
| 911401566044 | DN392B LED18/840 P14PSD D150 ALWP GMG2HE | 13.4 W            | No                            |
| 911401566144 | DN392B LED18/830 P14PSD D150 ALWP GMG2HE | 13.4 W            | No                            |
| 911401566244 | DN392B LED18/865 P14PSD D150 AL GMG2HE   | 13.4 W            | No                            |
| 911401566344 | DN392B LED18/840 P14PSD D150 AL GMG2HE   | 13.4 W            | No                            |
| 911401566444 | DN392B LED18/830 P14PSD D150 AL GMG2HE   | 13.4 W            | No                            |

| Order Code   | Full Product Name                        | Power Consumption | Suitable for random switching |
|--------------|------------------------------------------|-------------------|-------------------------------|
| 911401568044 | DN392B LED22/865 P17PSD D150 ALWP GMG2HE | 17.3 W            | No                            |
| 911401568144 | DN392B LED22/840 P17PSD D150 ALWP GMG2HE | 17.3 W            | No                            |
| 911401568244 | DN392B LED22/830 P17PSD D150 ALWP GMG2HE | 17.3 W            | No                            |
| 911401568344 | DN392B LED22/865 PSD D150 AL WP GCG2HE   | 17.3 W            | No                            |
| 911401568444 | DN392B LED22/840 PSD D150 AL WP GCG2HE   | 17.3 W            | No                            |
| 911401568544 | DN392B LED22/830 PSD D150 AL WP GCG2HE   | 17.3 W            | No                            |
| 911401569244 | DN392B LED18/865 PSD D150 AL WP GCG2HE   | 13.4 W            | No                            |
| 911401569344 | DN392B LED18/840 PSD D150 AL WP GCG2HE   | 13.4 W            | No                            |
| 911401569444 | DN392B LED18/830 PSD D150 AL WP GCG2HE   | 13.4 W            | No                            |
| 911401569544 | DN391B LED12/865 P11PSD D150 ALWP GMG2HE | 10.6 W            | No                            |
| 911401569644 | DN391B LED12/840 P11PSD D150 ALWP GMG2HE | 10.6 W            | No                            |
| 911401569744 | DN391B LED12/830 P11PSD D150 ALWP GMG2HE | 10.6 W            | No                            |
| 911401569844 | DN391B LED12/865 PSD D150 AL WP GCG2HE   | 10.6 W            | No                            |
| 911401569944 | DN391B LED12/840 PSD D150 AL WP GCG2HE   | 10.6 W            | No                            |
| 911401570044 | DN391B LED12/830 PSD D150 AL WP GCG2HE   | 10.6 W            | No                            |
| 911401573744 | DN392B LED22/865 P17PSD D150 AL GMG2HE   | 17.3 W            | No                            |
| 911401573844 | DN392B LED22/840 P17PSD D150 AL GMG2HE   | 17.3 W            | No                            |
| 911401573944 | DN392B LED22/830 P17PSD D150 AL GMG2HE   | 17.3 W            | No                            |
| 911401574344 | DN392B LED22/865 PSD D150 AL GCG2HE      | 17.3 W            | No                            |
| 911401574444 | DN392B LED22/840 PSD D150 AL GCG2HE      | 17.3 W            | No                            |
| 911401574544 | DN392B LED22/830 PSD D150 AL GCG2HE      | 17.3 W            | No                            |
| 911401576144 | DN392B LED18/865 PSD D150 AL GCG2HE      | 13.4 W            | No                            |
| 911401576244 | DN392B LED18/840 PSD D150 AL GCG2HE      | 13.4 W            | No                            |
| 911401576344 | DN392B LED18/830 PSD D150 AL GCG2HE      | 13.4 W            | No                            |
| 911401576744 | DN391B LED12/865 P11PSD D150 AL GMG2HE   | 10.6 W            | No                            |

| Order Code   | Full Product Name                           | Power Consumption | Suitable for random switching |
|--------------|---------------------------------------------|-------------------|-------------------------------|
| 911401576844 | DN391B LED12/840 P11PSD D150<br>AL GMG2HE   | 10.6 W            | No                            |
| 911401576944 | DN391B LED12/830 P11PSD D150<br>AL GMG2HE   | 10.6 W            | No                            |
| 911401577344 | DN391B LED12/865 PSD D150 AL<br>GCG2HE      | 10.6 W            | No                            |
| 911401577444 | DN391B LED12/840 PSD D150 AL<br>GCG2HE      | 10.6 W            | No                            |
| 911401577544 | DN391B LED12/830 PSD D150 AL<br>GCG2HE      | 10.6 W            | No                            |
| 911401577142 | DN393X LED22/840 P20L1W D200<br>AL CAUG2    | 19.9 W            | No                            |
| 911401577442 | DN392X LED17/840 P15L1W D150<br>AL CAUG2    | 15 W              | No                            |
| 911401503745 | DN391X LED7/9TNW P7PSD D100<br>AL WP G2     | 7 W               | Yes                           |
| 911401524344 | DN391B LED14/865 P11PSU D100<br>ALWP GMG2HE | 11.4 W            | No                            |
| 911401524444 | DN391B LED14/840 P11PSU D100<br>ALWP GMG2HE | 11.4 W            | No                            |
| 911401524544 | DN391B LED14/830 P11PSU D100<br>ALWP GMG2HE | 11.4 W            | No                            |
| 911401524644 | DN391B LED14/865 PSU D100 AL<br>WP GCG2HE   | 11.4 W            | No                            |
| 911401524744 | DN391B LED14/840 PSU D100 AL<br>WP GCG2HE   | 11.4 W            | No                            |
| 911401524844 | DN391B LED14/830 PSU D100 AL<br>WP GCG2HE   | 11.4 W            | No                            |
| 911401524944 | DN391B LED12/865 P10PSU D100<br>ALWP GMG2HE | 9.8 W             | No                            |
| 911401525044 | DN391B LED12/840 P10PSU D100<br>ALWP GMG2HE | 9.8 W             | No                            |
| 911401525144 | DN391B LED12/830 P10PSU D100<br>ALWP GMG2HE | 9.8 W             | No                            |
| 911401525244 | DN391B LED12/865 PSU D100 AL<br>WP GCG2HE   | 9.8 W             | No                            |
| 911401525344 | DN391B LED12/840 PSU D100 AL<br>WP GCG2HE   | 9.8 W             | No                            |
| 911401525444 | DN391B LED12/830 PSU D100 AL<br>WP GCG2HE   | 9.8 W             | No                            |
| 911401525544 | DN390B LED7/865 P6PSU D100<br>AL WP GMG2HE  | 5.8 W             | No                            |
| 911401525644 | DN390B LED7/840 P6PSU D100<br>AL WP GMG2HE  | 5.8 W             | No                            |
| 911401525744 | DN390B LED7/830 P6PSU D100<br>AL WP GMG2HE  | 5.8 W             | No                            |
| 911401525844 | DN390B LED7/865 PSU D100 AL<br>WP GCG2HE    | 5.8 W             | No                            |
| 911401525944 | DN390B LED7/840 PSU D100 AL<br>WP GCG2HE    | 5.8 W             | No                            |

| Order Code   | Full Product Name                           | Power Consumption | Suitable for random switching |
|--------------|---------------------------------------------|-------------------|-------------------------------|
| 911401526044 | DN390B LED7/830 PSU D100 AL<br>WP GCG2HE    | 5.8 W             | No                            |
| 911401533344 | DN391B LED14/865 P11PSU D100<br>AL GMG2HE   | 11.4 W            | No                            |
| 911401533444 | DN391B LED14/840 P11PSU D100<br>AL GMG2HE   | 11.4 W            | No                            |
| 911401533544 | DN391B LED14/830 P11PSU D100<br>AL GMG2HE   | 11.4 W            | No                            |
| 911401533944 | DN391B LED14/865 PSU D100 AL<br>GCG2HE      | 11.4 W            | No                            |
| 911401534044 | DN391B LED14/840 PSU D100 AL<br>GCG2HE      | 11.4 W            | No                            |
| 911401534144 | DN391B LED14/830 PSU D100 AL<br>GCG2HE      | 11.4 W            | No                            |
| 911401534544 | DN391B LED12/865 P10PSU D100<br>AL GMG2HE   | 9.8 W             | No                            |
| 911401534644 | DN391B LED12/840 P10PSU D100<br>AL GMG2HE   | 9.8 W             | No                            |
| 911401534744 | DN391B LED12/830 P10PSU D100<br>AL GMG2HE   | 9.8 W             | No                            |
| 911401535144 | DN391B LED12/865 PSU D100 AL<br>GCG2HE      | 9.8 W             | No                            |
| 911401535244 | DN391B LED12/840 PSU D100 AL<br>GCG2HE      | 9.8 W             | No                            |
| 911401535444 | DN391B LED12/830 PSU D100 AL<br>GCG2HE      | 9.8 W             | No                            |
| 911401535844 | DN390B LED7/865 P6PSU D100<br>AL GMG2HE     | 5.8 W             | No                            |
| 911401535944 | DN390B LED7/840 P6PSU D100<br>AL GMG2HE     | 5.8 W             | No                            |
| 911401536044 | DN390B LED7/830 P6PSU D100<br>AL GMG2HE     | 5.8 W             | No                            |
| 911401536444 | DN390B LED7/865 PSU D100 AL<br>GCG2HE       | 5.8 W             | No                            |
| 911401536544 | DN390B LED7/840 PSU D100 AL<br>GCG2HE       | 5.8 W             | No                            |
| 911401536644 | DN390B LED7/830 PSU D100 AL<br>GCG2HE       | 5.8 W             | No                            |
| 911401537444 | DN391X LED14/865 P12WIA D100<br>AL G2HE     | 12 W              | No                            |
| 911401538044 | DN391X LED14/830 P12WIA D100<br>AL G2HE     | 12 W              | No                            |
| 911401538644 | DN391X LED14/840 P12WIA D100<br>AL G2HE     | 12 W              | No                            |
| 911401570144 | DN391B LED14/865 P12PSD D100<br>ALWP GMG2HE | 12 W              | No                            |
| 911401570244 | DN391B LED14/840 P12PSD D100<br>ALWP GMG2HE | 12 W              | No                            |
| 911401570344 | DN391B LED14/830 P12PSD D100<br>ALWP GMG2HE | 12 W              | No                            |

| Order Code   | Full Product Name                        | Power Consumption | Suitable for random switching |
|--------------|------------------------------------------|-------------------|-------------------------------|
| 911401570444 | DN391B LED14/865 PSD D100 AL WP GCG2HE   | 12 W              | No                            |
| 911401570544 | DN391B LED14/840 PSD D100 AL WP GCG2HE   | 12 W              | No                            |
| 911401570644 | DN391B LED14/830 PSD D100 AL WP GCG2HE   | 12 W              | No                            |
| 911401570744 | DN391B LED12/865 P10PSD D100 ALWP GMG2HE | 10.2 W            | No                            |
| 911401570844 | DN391B LED12/840 P10PSD D100 ALWP GMG2HE | 10.2 W            | No                            |
| 911401570944 | DN391B LED12/830 P10PSD D100 ALWP GMG2HE | 10.2 W            | No                            |
| 911401571044 | DN391B LED12/865 PSD D100 AL WP GCG2HE   | 10.2 W            | No                            |
| 911401571144 | DN391B LED12/840 PSD D100 AL WP GCG2HE   | 10.2 W            | No                            |
| 911401571244 | DN391B LED12/830 PSD D100 AL WP GCG2HE   | 10.2 W            | No                            |
| 911401577944 | DN391B LED14/865 P12PSD D100 AL GMG2HE   | 12 W              | No                            |
| 911401578044 | DN391B LED14/840 P12PSD D100 AL GMG2HE   | 12 W              | No                            |
| 911401578144 | DN391B LED14/830 P12PSD D100 AL GMG2HE   | 12 W              | No                            |
| 911401578544 | DN391B LED14/865 PSD D100 AL GCG2HE      | 12 W              | No                            |
| 911401578644 | DN391B LED14/840 PSD D100 AL GCG2HE      | 12 W              | No                            |
| 911401578744 | DN391B LED14/830 PSD D100 AL GCG2HE      | 12 W              | No                            |
| 911401579144 | DN391B LED12/865 P10PSD D100 AL GMG2HE   | 10.2 W            | No                            |
| 911401579244 | DN391B LED12/840 P10PSD D100 AL GMG2HE   | 10.2 W            | No                            |
| 911401579344 | DN391B LED12/830 P10PSD D100 AL GMG2HE   | 10.2 W            | No                            |
| 911401579744 | DN391B LED12/865 PSD D100 AL GCG2HE      | 10.2 W            | No                            |
| 911401579844 | DN391B LED12/840 PSD D100 AL GCG2HE      | 10.2 W            | No                            |
| 911401579944 | DN391B LED12/830 PSD D100 AL GCG2HE      | 10.2 W            | No                            |
| 911401503845 | DN394X LED34/9TNW P27PSD D200 WH WP G2   | 27 W              | Yes                           |
| 911401504145 | DN394X LED34/9TNW P27PSD D200 WH WPCAUG2 | 27 W              | Yes                           |
| 911401519944 | DN393B LED26/840 P20PSU D200WHWP CAUG2HE | 19.9 W            | No                            |
| 911401520344 | DN393B LED26/840 P20PSU D200 WH CAUG2HE  | 19.9 W            | No                            |

| Order Code   | Full Product Name                      | Power Consumption | Suitable for random switching |
|--------------|----------------------------------------|-------------------|-------------------------------|
| 911401526444 | DN394B LED40/865 P29PSU D200 WH GMG2HE | 29.3 W            | No                            |
| 911401526544 | DN394B LED40/840 P29PSU D200 WH GMG2HE | 29.3 W            | No                            |
| 911401526644 | DN394B LED40/830 P29PSU D200 WH GMG2HE | 29.3 W            | No                            |
| 911401527044 | DN394B LED40/865 PSU D200 WH GCG2HE    | 29.3 W            | No                            |
| 911401527144 | DN394B LED40/840 PSU D200 WH GCG2HE    | 29.3 W            | No                            |
| 911401527244 | DN394B LED40/830 PSU D200 WH GCG2HE    | 29.3 W            | No                            |
| 911401527644 | DN393B LED26/865 P19PSU D200 WH GMG2HE | 19.2 W            | No                            |
| 911401527744 | DN393B LED26/840 P19PSU D200 WH GMG2HE | 19.2 W            | No                            |
| 911401527844 | DN393B LED26/830 P19PSU D200 WH GMG2HE | 19.2 W            | No                            |
| 911401528244 | DN393B LED26/865 PSU D200 WH GCG2HE    | 19.2 W            | No                            |
| 911401528344 | DN393B LED26/840 PSU D200 WH GCG2HE    | 19.2 W            | No                            |
| 911401528444 | DN393B LED26/830 PSU D200 WH GCG2HE    | 19.2 W            | No                            |
| 911401530044 | DN392B LED20/865 P14PSU D200 WH GMG2HE | 14.4 W            | No                            |
| 911401530144 | DN392B LED20/840 P14PSU D200 WH GMG2HE | 14.4 W            | No                            |
| 911401530244 | DN392B LED20/830 P14PSU D200 WH GMG2HE | 14.4 W            | No                            |
| 911401530644 | DN392B LED20/865 PSU D200 WH GCG2HE    | 14.4 W            | No                            |
| 911401530744 | DN392B LED20/840 PSU D200 WH GCG2HE    | 14.4 W            | No                            |
| 911401530844 | DN392B LED20/830 PSU D200 WH GCG2HE    | 14.4 W            | No                            |
| 911401537144 | DN393X LED26/865 P20WIA D200 WH G2HE   | 19.9 W            | No                            |
| 911401537744 | DN393X LED26/830 P20WIA D200 WH G2HE   | 19.9 W            | No                            |
| 911401538344 | DN393X LED26/840 P20WIA D200 WH G2HE   | 19.9 W            | No                            |
| 911401571644 | DN394B LED40/865 P29PSD D200 WH GMG2HE | 29.3 W            | No                            |
| 911401571744 | DN394B LED40/840 P29PSD D200 WH GMG2HE | 29.3 W            | No                            |
| 911401571844 | DN394B LED40/830 P29PSD D200 WH GMG2HE | 29.3 W            | No                            |
| 911401572244 | DN394B LED40/865 PSD D200 WH GCG2HE    | 29.3 W            | No                            |

| Order Code   | Full Product Name                        | Power Consumption | Suitable for random switching |
|--------------|------------------------------------------|-------------------|-------------------------------|
| 911401572344 | DN394B LED40/840 PSD D200 WH GCG2HE      | 29.3 W            | No                            |
| 911401572444 | DN394B LED40/830 PSD D200 WH GCG2HE      | 29.3 W            | No                            |
| 911401572844 | DN393B LED26/865 P20PSD D200 WH GMG2HE   | 19.9 W            | No                            |
| 911401572944 | DN393B LED26/840 P20PSD D200 WH GMG2HE   | 19.9 W            | No                            |
| 911401573044 | DN393B LED26/830 P20PSD D200 WH GMG2HE   | 19.9 W            | No                            |
| 911401573444 | DN393B LED26/865 PSD D200 WH GCG2HE      | 19.9 W            | No                            |
| 911401573544 | DN393B LED26/840 PSD D200 WH GCG2HE      | 19.9 W            | No                            |
| 911401573644 | DN393B LED26/830 PSD D200 WH GCG2HE      | 19.9 W            | No                            |
| 911401575244 | DN392B LED18/865 P14PSD D200 WH GMG2HE   | 14.2 W            | No                            |
| 911401575344 | DN392B LED18/840 P14PSD D200 WH GMG2HE   | 14.2 W            | No                            |
| 911401575444 | DN392B LED18/830 P14PSD D200 WH GMG2HE   | 14.2 W            | No                            |
| 911401575844 | DN392B LED18/865 PSD D200 WH GCG2HE      | 14.2 W            | No                            |
| 911401575944 | DN392B LED18/840 PSD D200 WH GCG2HE      | 14.2 W            | No                            |
| 911401576044 | DN392B LED18/830 PSD D200 WH GCG2HE      | 14.2 W            | No                            |
| 911401586932 | DN393B LED22/840 P20PSU D200 WH CAUG2    | 19.9 W            | No                            |
| 911401588632 | DN393B LED22/840 P20PSU D200 WH WP CAUG2 | 19.9 W            | No                            |
| 911401503545 | DN394X LED33/9TNW P27PSD D200 AL WP G2   | 27 W              | Yes                           |
| 911401520744 | DN394B LED38/865 P29PSU D200 ALWP GMG2HE | 29.3 W            | No                            |
| 911401520844 | DN394B LED38/840 P29PSU D200 ALWP GMG2HE | 29.3 W            | No                            |
| 911401520944 | DN394B LED38/830 P29PSU D200 ALWP GMG2HE | 29.3 W            | No                            |
| 911401521044 | DN394B LED38/865 PSU D200 AL WP GCG2HE   | 29.3 W            | No                            |
| 911401521144 | DN394B LED38/840 PSU D200 AL WP GCG2HE   | 29.3 W            | No                            |
| 911401521244 | DN394B LED38/830 PSU D200 AL WP GCG2HE   | 29.3 W            | No                            |
| 911401521344 | DN393B LED25/865 P19PSU D200 ALWP GMG2HE | 19.2 W            | No                            |
| 911401521444 | DN393B LED25/840 P19PSU D200 ALWP GMG2HE | 19.2 W            | No                            |

| Order Code   | Full Product Name                        | Power Consumption | Suitable for random switching |
|--------------|------------------------------------------|-------------------|-------------------------------|
| 911401521544 | DN393B LED25/830 P19PSU D200 ALWP GMG2HE | 19.2 W            | No                            |
| 911401521644 | DN393B LED25/865 PSU D200 AL WP GCG2HE   | 19.2 W            | No                            |
| 911401521744 | DN393B LED25/840 PSU D200 AL WP GCG2HE   | 19.2 W            | No                            |
| 911401521844 | DN393B LED25/830 PSU D200 AL WP GCG2HE   | 19.2 W            | No                            |
| 911401522544 | DN392B LED18/865 P14PSU D200 ALWP GMG2HE | 14.4 W            | No                            |
| 911401522644 | DN392B LED18/840 P14PSU D200 ALWP GMG2HE | 14.4 W            | No                            |
| 911401522744 | DN392B LED18/830 P14PSU D200 ALWP GMG2HE | 14.4 W            | No                            |
| 911401522844 | DN392B LED18/865 PSU D200 AL WP GCG2HE   | 14.4 W            | No                            |
| 911401522944 | DN392B LED18/840 PSU D200 AL WP GCG2HE   | 14.4 W            | No                            |
| 911401523044 | DN392B LED18/830 PSU D200 AL WP GCG2HE   | 14.4 W            | No                            |
| 911401526144 | DN394B LED38/865 P29PSU D200 AL GMG2HE   | 29.3 W            | No                            |
| 911401526244 | DN394B LED38/840 P29PSU D200 AL GMG2HE   | 29.3 W            | No                            |
| 911401526344 | DN394B LED38/830 P29PSU D200 AL GMG2HE   | 29.3 W            | No                            |
| 911401526744 | DN394B LED38/865 PSU D200 AL GCG2HE      | 29.3 W            | No                            |
| 911401526844 | DN394B LED38/840 PSU D200 AL GCG2HE      | 29.3 W            | No                            |
| 911401526944 | DN394B LED38/830 PSU D200 AL GCG2HE      | 29.3 W            | No                            |
| 911401527344 | DN393B LED25/865 P19PSU D200 AL GMG2HE   | 19.2 W            | No                            |
| 911401527444 | DN393B LED25/840 P19PSU D200 AL GMG2HE   | 19.2 W            | No                            |
| 911401527544 | DN393B LED25/830 P19PSU D200 AL GMG2HE   | 19.2 W            | No                            |
| 911401527944 | DN393B LED25/865 PSU D200 AL GCG2HE      | 19.2 W            | No                            |
| 911401528044 | DN393B LED25/840 PSU D200 AL GCG2HE      | 19.2 W            | No                            |
| 911401528144 | DN393B LED25/830 PSU D200 AL GCG2HE      | 19.2 W            | No                            |
| 911401529744 | DN392B LED18/865 P14PSU D200 AL GMG2HE   | 14.4 W            | No                            |
| 911401529844 | DN392B LED18/840 P14PSU D200 AL GMG2HE   | 14.4 W            | No                            |
| 911401529944 | DN392B LED18/830 P14PSU D200 AL GMG2HE   | 14.4 W            | No                            |

| Order Code   | Full Product Name                        | Power Consumption | Suitable for random switching |
|--------------|------------------------------------------|-------------------|-------------------------------|
| 911401530344 | DN392B LED18/865 PSU D200 AL GCG2HE      | 14.4 W            | No                            |
| 911401530444 | DN392B LED18/840 PSU D200 AL GCG2HE      | 14.4 W            | No                            |
| 911401530544 | DN392B LED18/830 PSU D200 AL GCG2HE      | 14.4 W            | No                            |
| 911401537044 | DN393X LED25/865 P20WIA D200 AL G2HE     | 19.9 W            | No                            |
| 911401537644 | DN393X LED25/830 P20WIA D200 AL G2HE     | 19.9 W            | No                            |
| 911401538244 | DN393X LED25/840 P20WIA D200 AL G2HE     | 19.9 W            | No                            |
| 911401566844 | DN394B LED38/865 P29PSD D200 ALWP GMG2HE | 29.3 W            | No                            |
| 911401566944 | DN394B LED38/840 P29PSD D200 ALWP GMG2HE | 29.3 W            | No                            |
| 911401567044 | DN394B LED38/830 P29PSD D200 ALWP GMG2HE | 29.3 W            | No                            |
| 911401567144 | DN394B LED38/865 PSD D200 AL WP GCG2HE   | 29.3 W            | No                            |
| 911401567244 | DN394B LED38/840 PSD D200 AL WP GCG2HE   | 29.3 W            | No                            |
| 911401567344 | DN394B LED38/830 PSD D200 AL WP GCG2HE   | 29.3 W            | No                            |
| 911401567444 | DN393B LED25/865 P20PSD D200 ALWP GMG2HE | 19.9 W            | No                            |
| 911401567544 | DN393B LED25/840 P20PSD D200 ALWP GMG2HE | 19.9 W            | No                            |
| 911401567644 | DN393B LED25/830 P20PSD D200 ALWP GMG2HE | 19.9 W            | No                            |
| 911401567744 | DN393B LED25/865 PSD D200 AL WP GCG2HE   | 19.9 W            | No                            |
| 911401567844 | DN393B LED25/840 PSD D200 AL WP GCG2HE   | 19.9 W            | No                            |
| 911401567944 | DN393B LED25/830 PSD D200 AL WP GCG2HE   | 19.9 W            | No                            |
| 911401568644 | DN392B LED18/865 P14PSD D200 ALWP GMG2HE | 14.2 W            | No                            |
| 911401568744 | DN392B LED18/840 P14PSD D200 ALWP GMG2HE | 14.2 W            | No                            |
| 911401568844 | DN392B LED18/830 P14PSD D200 ALWP GMG2HE | 14.2 W            | No                            |
| 911401568944 | DN392B LED18/865 PSD D200 AL WP GCG2HE   | 14.2 W            | No                            |
| 911401569044 | DN392B LED18/840 PSD D200 AL WP GCG2HE   | 14.2 W            | No                            |
| 911401569144 | DN392B LED18/830 PSD D200 AL WP GCG2HE   | 14.2 W            | No                            |
| 911401571344 | DN394B LED38/865 P29PSD D200 AL GMG2HE   | 29.3 W            | No                            |

| Order Code   | Full Product Name                        | Power Consumption | Suitable for random switching |
|--------------|------------------------------------------|-------------------|-------------------------------|
| 911401571444 | DN394B LED38/840 P29PSD D200 AL GMG2HE   | 29.3 W            | No                            |
| 911401571544 | DN394B LED38/830 P29PSD D200 AL GMG2HE   | 29.3 W            | No                            |
| 911401571944 | DN394B LED38/865 PSD D200 AL GCG2HE      | 29.3 W            | No                            |
| 911401572044 | DN394B LED38/840 PSD D200 AL GCG2HE      | 29.3 W            | No                            |
| 911401572144 | DN394B LED38/830 PSD D200 AL GCG2HE      | 29.3 W            | No                            |
| 911401572544 | DN393B LED25/865 P20PSD D200 AL GMG2HE   | 19.9 W            | No                            |
| 911401572644 | DN393B LED25/840 P20PSD D200 AL GMG2HE   | 19.9 W            | No                            |
| 911401572744 | DN393B LED25/830 P20PSD D200 AL GMG2HE   | 19.9 W            | No                            |
| 911401573144 | DN393B LED25/865 PSD D200 AL GCG2HE      | 19.9 W            | No                            |
| 911401573244 | DN393B LED25/840 PSD D200 AL GCG2HE      | 19.9 W            | No                            |
| 911401573344 | DN393B LED25/830 PSD D200 AL GCG2HE      | 19.9 W            | No                            |
| 911401574944 | DN392B LED18/865 P14PSD D200 AL GMG2HE   | 14.2 W            | No                            |
| 911401575044 | DN392B LED18/840 P14PSD D200 AL GMG2HE   | 14.2 W            | No                            |
| 911401575144 | DN392B LED18/830 P14PSD D200 AL GMG2HE   | 14.2 W            | No                            |
| 911401575544 | DN392B LED18/865 PSD D200 AL GCG2HE      | 14.2 W            | No                            |
| 911401575644 | DN392B LED18/840 PSD D200 AL GCG2HE      | 14.2 W            | No                            |
| 911401575744 | DN392B LED18/830 PSD D200 AL GCG2HE      | 14.2 W            | No                            |
| 911401577042 | DN393X LED22/840 P20L1W D200 WH CAUG2    | 19.9 W            | No                            |
| 911401577542 | DN392X LED17/840 P15L1W D150 WH CAUG2    | 15 W              | No                            |
| 911401503945 | DN392X LED17/9TNW P15PSD D150 WH WP G2   | 15 W              | Yes                           |
| 911401504245 | DN392X LED17/9TNW P15PSD D150 WH WPCAUG2 | 15 W              | Yes                           |
| 911401520044 | DN392B LED20/840 P15PSU D150WHWP CAUG2HE | 15 W              | No                            |
| 911401520144 | DN391B LED13/840 P11PSU D150WHWP CAUG2HE | 10.6 W            | No                            |
| 911401520444 | DN392B LED20/840 P15PSU D150 WH CAUG2HE  | 15 W              | No                            |
| 911401520544 | DN391B LED13/840 P11PSU D150 WH CAUG2HE  | 10.6 W            | No                            |

| Order Code   | Full Product Name                      | Power Consumption | Suitable for random switching |
|--------------|----------------------------------------|-------------------|-------------------------------|
| 911401528844 | DN392B LED22/865 P16PSU D150 WH GMG2HE | 16 W              | No                            |
| 911401528944 | DN392B LED22/840 P16PSU D150 WH GMG2HE | 16 W              | No                            |
| 911401529044 | DN392B LED22/830 P16PSU D150 WH GMG2HE | 16 W              | No                            |
| 911401529444 | DN392B LED22/865 PSU D150 WH GCG2HE    | 16 W              | No                            |
| 911401529544 | DN392B LED22/840 PSU D150 WH GCG2HE    | 16 W              | No                            |
| 911401529644 | DN392B LED22/830 PSU D150 WH GCG2HE    | 16 W              | No                            |
| 911401531244 | DN392B LED20/865 P14PSU D150 WH GMG2HE | 14.4 W            | No                            |
| 911401531344 | DN392B LED20/840 P14PSU D150 WH GMG2HE | 14.4 W            | No                            |
| 911401531444 | DN392B LED20/830 P14PSU D150 WH GMG2HE | 14.4 W            | No                            |
| 911401531844 | DN392B LED20/865 PSU D150 WH GCG2HE    | 14.4 W            | No                            |
| 911401531944 | DN392B LED20/840 PSU D150 WH GCG2HE    | 14.4 W            | No                            |
| 911401532044 | DN392B LED20/830 PSU D150 WH GCG2HE    | 14.4 W            | No                            |
| 911401532444 | DN391B LED13/865 P10PSU D150 WH GMG2HE | 9.8 W             | No                            |
| 911401532544 | DN391B LED13/840 P10PSU D150 WH GMG2HE | 9.8 W             | No                            |
| 911401532644 | DN391B LED13/830 P10PSU D150 WH GMG2HE | 9.8 W             | No                            |
| 911401533044 | DN391B LED13/865 PSU D150 WH GCG2HE    | 9.8 W             | No                            |
| 911401533144 | DN391B LED13/840 PSU D150 WH GCG2HE    | 9.8 W             | No                            |
| 911401533244 | DN391B LED13/830 PSU D150 WH GCG2HE    | 9.8 W             | No                            |
| 911401537344 | DN392X LED20/865 P15WIA D150 WH G2HE   | 15 W              | No                            |
| 911401537944 | DN392X LED20/830 P15WIA D150 WH G2HE   | 15 W              | No                            |
| 911401538544 | DN392X LED20/840 P15WIA D150 WH G2HE   | 15 W              | No                            |
| 911401566544 | DN392B LED19/865 P14PSD D150 WH GMG2HE | 13.4 W            | No                            |

## Controls and Dimming

| Order Code   | Full Product Name                        | Power Consumption | Suitable for random switching |
|--------------|------------------------------------------|-------------------|-------------------------------|
| 911401566644 | DN392B LED19/840 P14PSD D150 WH GMG2HE   | 13.4 W            | No                            |
| 911401566744 | DN392B LED19/830 P14PSD D150 WH GMG2HE   | 13.4 W            | No                            |
| 911401574044 | DN392B LED23/865 P17PSD D150 WH GMG2HE   | 17.3 W            | No                            |
| 911401574144 | DN392B LED23/840 P17PSD D150 WH GMG2HE   | 17.3 W            | No                            |
| 911401574244 | DN392B LED23/830 P17PSD D150 WH GMG2HE   | 17.3 W            | No                            |
| 911401574644 | DN392B LED23/865 PSD D150 WH GCG2HE      | 17.3 W            | No                            |
| 911401574744 | DN392B LED23/840 PSD D150 WH GCG2HE      | 17.3 W            | No                            |
| 911401574844 | DN392B LED23/830 PSD D150 WH GCG2HE      | 17.3 W            | No                            |
| 911401576444 | DN392B LED19/865 PSD D150 WH GCG2HE      | 13.4 W            | No                            |
| 911401576544 | DN392B LED19/840 PSD D150 WH GCG2HE      | 13.4 W            | No                            |
| 911401576644 | DN392B LED19/830 PSD D150 WH GCG2HE      | 13.4 W            | No                            |
| 911401577044 | DN391B LED13/865 P11PSD D150 WH GMG2HE   | 10.6 W            | No                            |
| 911401577144 | DN391B LED13/840 P11PSD D150 WH GMG2HE   | 10.6 W            | No                            |
| 911401577244 | DN391B LED13/830 P11PSD D150 WH GMG2HE   | 10.6 W            | No                            |
| 911401577644 | DN391B LED13/865 PSD D150 WH GCG2HE      | 10.6 W            | No                            |
| 911401577744 | DN391B LED13/840 PSD D150 WH GCG2HE      | 10.6 W            | No                            |
| 911401577844 | DN391B LED13/830 PSD D150 WH GCG2HE      | 10.6 W            | No                            |
| 911401585532 | DN391B LED11/840 P11PSU D150 WH CAUG2    | 10.6 W            | No                            |
| 911401585632 | DN392B LED17/840 P15PSU D150 WH CAUG2    | 15 W              | No                            |
| 911401587832 | DN391B LED11/840 P11PSU D150 WH WP CAUG2 | 10.6 W            | No                            |
| 911401587932 | DN392B LED17/840 P15PSU D150 WH WP CAUG2 | 15 W              | No                            |

| Order Code   | Full Product Name                      | Maximum dim |                |
|--------------|----------------------------------------|-------------|----------------|
|              |                                        | Dimmable    | level          |
| 911401504045 | DN391X LED8/9TNW P7PSD D100 WH WP G2   | DALI        | 1%             |
| 911401504345 | DN391X LED8/9TNW P7PSD D100 WH WPCAUG2 | DALI        | 1%             |
| 911401520244 | DN390B LED7/840 P6PSU D100WHWP CAUG2HE | No          | Not applicable |
| 911401520644 | DN390B LED7/840 P6PSU D100 WH CAUG2HE  | No          | Not applicable |
| 911401533644 | DN391B LED15/865 P11PSU D100 WH GMG2HE | No          | Not applicable |
| 911401533744 | DN391B LED15/840 P11PSU D100 WH GMG2HE | No          | Not applicable |
| 911401533844 | DN391B LED15/830 P11PSU D100 WH GMG2HE | No          | Not applicable |
| 911401534244 | DN391B LED15/865 PSU D100 WH GCG2HE    | No          | Not applicable |
| 911401534344 | DN391B LED15/840 PSU D100 WH GCG2HE    | No          | Not applicable |
| 911401534444 | DN391B LED15/830 PSU D100 WH GCG2HE    | No          | Not applicable |
| 911401534844 | DN391B LED12/865 P10PSU D100 WH GMG2HE | No          | Not applicable |
| 911401534944 | DN391B LED12/840 P10PSU D100 WH GMG2HE | No          | Not applicable |
| 911401535044 | DN391B LED12/830 P10PSU D100 WH GMG2HE | No          | Not applicable |
| 911401535544 | DN391B LED12/865 PSU D100 WH GCG2HE    | No          | Not applicable |
| 911401535644 | DN391B LED12/840 PSU D100 WH GCG2HE    | No          | Not applicable |
| 911401535744 | DN391B LED12/830 PSU D100 WH GCG2HE    | No          | Not applicable |
| 911401536144 | DN390B LED7/865 P6PSU D100 WH GMG2HE   | No          | Not applicable |
| 911401536244 | DN390B LED7/840 P6PSU D100 WH GMG2HE   | No          | Not applicable |
| 911401536344 | DN390B LED7/830 P6PSU D100 WH GMG2HE   | No          | Not applicable |
| 911401536744 | DN390B LED7/865 PSU D100 WH GCG2HE     | No          | Not applicable |
| 911401536844 | DN390B LED7/840 PSU D100 WH GCG2HE     | No          | Not applicable |
| 911401536944 | DN390B LED7/830 PSU D100 WH GCG2HE     | No          | Not applicable |
| 911401537544 | DN391X LED15/865 P12WIA D100 WH G2HE   | DALI        | 1%             |
| 911401538144 | DN391X LED15/830 P12WIA D100 WH G2HE   | DALI        | 1%             |
| 911401538744 | DN391X LED15/840 P12WIA D100WH G2HE    | DALI        | 1%             |

| Order Code   | Full Product Name                        | Maximum dim |                |
|--------------|------------------------------------------|-------------|----------------|
|              |                                          | Dimmable    | level          |
| 911401578244 | DN391B LED15/865 P12PSD D100 WH GMG2HE   | DALI        | 1%             |
| 911401578344 | DN391B LED15/840 P12PSD D100 WH GMG2HE   | DALI        | 1%             |
| 911401578444 | DN391B LED15/830 P12PSD D100 WH GMG2HE   | DALI        | 1%             |
| 911401578844 | DN391B LED15/865 PSD D100 WH GCG2HE      | DALI        | 1%             |
| 911401578944 | DN391B LED15/840 PSD D100 WH GCG2HE      | DALI        | 1%             |
| 911401579044 | DN391B LED15/830 PSD D100 WH GCG2HE      | DALI        | 1%             |
| 911401579444 | DN391B LED12/865 P10PSD D100 WH GMG2HE   | DALI        | 1%             |
| 911401579544 | DN391B LED12/840 P10PSD D100 WH GMG2HE   | DALI        | 1%             |
| 911401579644 | DN391B LED12/830 P10PSD D100 WH GMG2HE   | DALI        | 1%             |
| 911401580044 | DN391B LED12/865 PSD D100 WH GCG2HE      | DALI        | 1%             |
| 911401580144 | DN391B LED12/840 PSD D100 WH GCG2HE      | DALI        | 1%             |
| 911401580244 | DN391B LED12/830 PSD D100 WH GCG2HE      | DALI        | 1%             |
| 911401584832 | DN390B LED6/840 P8PSU D100 WH CAUG2      | No          | Not applicable |
| 911401587632 | DN390B LED6/840 P8PSU D100 WH WP CAUG2   | No          | Not applicable |
| 911401503645 | DN392X LED16/9TNW P15PSD D150 AL WP G2   | DALI        | 1%             |
| 911401521944 | DN392B LED20/865 P16PSU D150 ALWP GMG2HE | No          | Not applicable |
| 911401522044 | DN392B LED20/840 P16PSU D150 ALWP GMG2HE | No          | Not applicable |
| 911401522144 | DN392B LED20/830 P16PSU D150 ALWP GMG2HE | No          | Not applicable |
| 911401522244 | DN392B LED20/865 PSU D150 AL WP GCG2HE   | No          | Not applicable |
| 911401522344 | DN392B LED20/840 PSU D150 AL WP GCG2HE   | No          | Not applicable |
| 911401522444 | DN392B LED20/830 PSU D150 AL WP GCG2HE   | No          | Not applicable |
| 911401523144 | DN392B LED18/865 P14PSU D150 ALWP GMG2HE | No          | Not applicable |
| 911401523244 | DN392B LED18/840 P14PSU D150 ALWP GMG2HE | No          | Not applicable |
| 911401523344 | DN392B LED18/830 P14PSU D150 ALWP GMG2HE | No          | Not applicable |
| 911401523444 | DN392B LED18/865 PSU D150 AL WP GCG2HE   | No          | Not applicable |

| Order Code   | Full Product Name                           | Maximum dim |                |
|--------------|---------------------------------------------|-------------|----------------|
|              |                                             | Dimmable    | level          |
| 911401523544 | DN392B LED18/840 PSU D150 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401523644 | DN392B LED18/830 PSU D150 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401523744 | DN391B LED12/865 P10PSU D150 ALWP<br>GMG2HE | No          | Not applicable |
| 911401523844 | DN391B LED12/840 P10PSU D150 ALWP<br>GMG2HE | No          | Not applicable |
| 911401523944 | DN391B LED12/830 P10PSU D150 ALWP<br>GMG2HE | No          | Not applicable |
| 911401524044 | DN391B LED12/865 PSU D150 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401524144 | DN391B LED12/840 PSU D150 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401524244 | DN391B LED12/830 PSU D150 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401528544 | DN392B LED20/865 P16PSU D150 AL<br>GMG2HE   | No          | Not applicable |
| 911401528644 | DN392B LED20/840 P16PSU D150 AL<br>GMG2HE   | No          | Not applicable |
| 911401528744 | DN392B LED20/830 P16PSU D150 AL<br>GMG2HE   | No          | Not applicable |
| 911401529144 | DN392B LED20/865 PSU D150 AL<br>GCG2HE      | No          | Not applicable |
| 911401529244 | DN392B LED20/840 PSU D150 AL<br>GCG2HE      | No          | Not applicable |
| 911401529344 | DN392B LED20/830 PSU D150 AL<br>GCG2HE      | No          | Not applicable |
| 911401530944 | DN392B LED18/865 P14PSU D150 AL<br>GMG2HE   | No          | Not applicable |
| 911401531044 | DN392B LED18/840 P14PSU D150 AL<br>GMG2HE   | No          | Not applicable |
| 911401531144 | DN392B LED18/830 P14PSU D150 AL<br>GMG2HE   | No          | Not applicable |
| 911401531544 | DN392B LED18/865 PSU D150 AL<br>GCG2HE      | No          | Not applicable |
| 911401531644 | DN392B LED18/840 PSU D150 AL<br>GCG2HE      | No          | Not applicable |
| 911401531744 | DN392B LED18/830 PSU D150 AL<br>GCG2HE      | No          | Not applicable |
| 911401532144 | DN391B LED12/865 P10PSU D150 AL<br>GMG2HE   | No          | Not applicable |
| 911401532244 | DN391B LED12/840 P10PSU D150 AL<br>GMG2HE   | No          | Not applicable |
| 911401532344 | DN391B LED12/830 P10PSU D150 AL<br>GMG2HE   | No          | Not applicable |
| 911401532744 | DN391B LED12/865 PSU D150 AL<br>GCG2HE      | No          | Not applicable |
| 911401532844 | DN391B LED12/840 PSU D150 AL<br>GCG2HE      | No          | Not applicable |

| Order Code   | Full Product Name                           | Maximum dim |                |
|--------------|---------------------------------------------|-------------|----------------|
|              |                                             | Dimmable    | level          |
| 911401532944 | DN391B LED13/830 PSU D150 AL<br>GCG2HE      | No          | Not applicable |
| 911401537244 | DN392X LED18/865 P15WIA D150 AL<br>G2HE     | DALI        | 1%             |
| 911401537844 | DN392X LED18/830 P15WIA D150 AL<br>G2HE     | DALI        | 1%             |
| 911401538444 | DN392X LED18/840 P15WIA D150 AL<br>G2HE     | DALI        | 1%             |
| 911401565944 | DN392B LED18/865 P14PSD D150 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401566044 | DN392B LED18/840 P14PSD D150 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401566144 | DN392B LED18/830 P14PSD D150 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401566244 | DN392B LED18/865 P14PSD D150 AL<br>GMG2HE   | DALI        | 1%             |
| 911401566344 | DN392B LED18/840 P14PSD D150 AL<br>GMG2HE   | DALI        | 1%             |
| 911401566444 | DN392B LED18/830 P14PSD D150 AL<br>GMG2HE   | DALI        | 1%             |
| 911401568044 | DN392B LED22/865 P17PSD D150 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401568144 | DN392B LED22/840 P17PSD D150 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401568244 | DN392B LED22/830 P17PSD D150 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401568344 | DN392B LED22/865 PSD D150 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401568444 | DN392B LED22/840 PSD D150 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401568544 | DN392B LED22/830 PSD D150 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401569244 | DN392B LED18/865 PSD D150 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401569344 | DN392B LED18/840 PSD D150 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401569444 | DN392B LED18/830 PSD D150 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401569544 | DN391B LED12/865 P11PSD D150 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401569644 | DN391B LED12/840 P11PSD D150 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401569744 | DN391B LED12/830 P11PSD D150 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401569844 | DN391B LED12/865 PSD D150 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401569944 | DN391B LED12/840 PSD D150 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401570044 | DN391B LED12/830 PSD D150 AL WP<br>GCG2HE   | DALI        | 1%             |

| Order Code   | Full Product Name                           | Maximum dim |                |
|--------------|---------------------------------------------|-------------|----------------|
|              |                                             | Dimmable    | level          |
| 911401573744 | DN392B LED22/865 P17PSD D150 AL<br>GMG2HE   | DALI        | 1%             |
| 911401573844 | DN392B LED22/840 P17PSD D150 AL<br>GMG2HE   | DALI        | 1%             |
| 911401573944 | DN392B LED22/830 P17PSD D150 AL<br>GMG2HE   | DALI        | 1%             |
| 911401574344 | DN392B LED22/865 PSD D150 AL<br>GCG2HE      | DALI        | 1%             |
| 911401574444 | DN392B LED22/840 PSD D150 AL<br>GCG2HE      | DALI        | 1%             |
| 911401574544 | DN392B LED22/830 PSD D150 AL<br>GCG2HE      | DALI        | 1%             |
| 911401576144 | DN392B LED18/865 PSD D150 AL<br>GCG2HE      | DALI        | 1%             |
| 911401576244 | DN392B LED18/840 PSD D150 AL<br>GCG2HE      | DALI        | 1%             |
| 911401576344 | DN392B LED18/830 PSD D150 AL<br>GCG2HE      | DALI        | 1%             |
| 911401576744 | DN391B LED12/865 P11PSD D150 AL<br>GMG2HE   | DALI        | 1%             |
| 911401576844 | DN391B LED12/840 P11PSD D150 AL<br>GMG2HE   | DALI        | 1%             |
| 911401576944 | DN391B LED12/830 P11PSD D150 AL<br>GMG2HE   | DALI        | 1%             |
| 911401577344 | DN391B LED12/865 PSD D150 AL<br>GCG2HE      | DALI        | 1%             |
| 911401577444 | DN391B LED12/840 PSD D150 AL<br>GCG2HE      | DALI        | 1%             |
| 911401577544 | DN391B LED12/830 PSD D150 AL<br>GCG2HE      | DALI        | 1%             |
| 911401577142 | DN393X LED22/840 P20L1W D200 AL<br>CAUG2    | No          | 1%             |
| 911401577442 | DN392X LED17/840 P15L1W D150 AL<br>CAUG2    | No          | 1%             |
| 911401503745 | DN391X LED7/9TNW P7PSD D100 AL WP<br>G2     | DALI        | 1%             |
| 911401524344 | DN391B LED14/865 P11PSU D100 ALWP<br>GMG2HE | No          | Not applicable |
| 911401524444 | DN391B LED14/840 P11PSU D100 ALWP<br>GMG2HE | No          | Not applicable |
| 911401524544 | DN391B LED14/830 P11PSU D100 ALWP<br>GMG2HE | No          | Not applicable |
| 911401524644 | DN391B LED14/865 PSU D100 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401524744 | DN391B LED14/840 PSU D100 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401524844 | DN391B LED14/830 PSU D100 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401524944 | DN391B LED12/865 P10PSU D100 ALWP<br>GMG2HE | No          | Not applicable |

| Order Code   | Full Product Name                           | Maximum dim |                |
|--------------|---------------------------------------------|-------------|----------------|
|              |                                             | Dimmable    | level          |
| 911401525044 | DN391B LED12/840 P10PSU D100 ALWP<br>GMG2HE | No          | Not applicable |
| 911401525144 | DN391B LED12/830 P10PSU D100 ALWP<br>GMG2HE | No          | Not applicable |
| 911401525244 | DN391B LED12/865 PSU D100 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401525344 | DN391B LED12/840 PSU D100 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401525444 | DN391B LED12/830 PSU D100 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401525544 | DN390B LED7/865 P6PSU D100 AL WP<br>GMG2HE  | No          | Not applicable |
| 911401525644 | DN390B LED7/840 P6PSU D100 AL WP<br>GMG2HE  | No          | Not applicable |
| 911401525744 | DN390B LED7/830 P6PSU D100 AL WP<br>GMG2HE  | No          | Not applicable |
| 911401525844 | DN390B LED7/865 PSU D100 AL WP<br>GCG2HE    | No          | Not applicable |
| 911401525944 | DN390B LED7/840 PSU D100 AL WP<br>GCG2HE    | No          | Not applicable |
| 911401526044 | DN390B LED7/830 PSU D100 AL WP<br>GCG2HE    | No          | Not applicable |
| 911401533344 | DN391B LED14/865 P11PSU D100 AL<br>GMG2HE   | No          | Not applicable |
| 911401533444 | DN391B LED14/840 P11PSU D100 AL<br>GMG2HE   | No          | Not applicable |
| 911401533544 | DN391B LED14/830 P11PSU D100 AL<br>GMG2HE   | No          | Not applicable |
| 911401533944 | DN391B LED14/865 PSU D100 AL<br>GCG2HE      | No          | Not applicable |
| 911401534044 | DN391B LED14/840 PSU D100 AL<br>GCG2HE      | No          | Not applicable |
| 911401534144 | DN391B LED14/830 PSU D100 AL<br>GCG2HE      | No          | Not applicable |
| 911401534544 | DN391B LED12/865 P10PSU D100 AL<br>GMG2HE   | No          | Not applicable |
| 911401534644 | DN391B LED12/840 P10PSU D100 AL<br>GMG2HE   | No          | Not applicable |
| 911401534744 | DN391B LED12/830 P10PSU D100 AL<br>GMG2HE   | No          | Not applicable |
| 911401535144 | DN391B LED12/865 PSU D100 AL<br>GCG2HE      | No          | Not applicable |
| 911401535244 | DN391B LED12/840 PSU D100 AL<br>GCG2HE      | No          | Not applicable |
| 911401535444 | DN391B LED12/830 PSU D100 AL<br>GCG2HE      | No          | Not applicable |
| 911401535844 | DN390B LED7/865 P6PSU D100 AL<br>GMG2HE     | No          | Not applicable |
| 911401535944 | DN390B LED7/840 P6PSU D100 AL<br>GMG2HE     | No          | Not applicable |

| Order Code   | Full Product Name                           | Maximum dim |                |
|--------------|---------------------------------------------|-------------|----------------|
|              |                                             | Dimmable    | level          |
| 911401536044 | DN390B LED7/830 P6PSU D100 AL<br>GMG2HE     | No          | Not applicable |
| 911401536444 | DN390B LED7/865 PSU D100 AL<br>GCG2HE       | No          | Not applicable |
| 911401536544 | DN390B LED7/840 PSU D100 AL<br>GCG2HE       | No          | Not applicable |
| 911401536644 | DN390B LED7/830 PSU D100 AL<br>GCG2HE       | No          | Not applicable |
| 911401537444 | DN391X LED14/865 P12WIA D100 AL<br>G2HE     | DALI        | 1%             |
| 911401538044 | DN391X LED14/830 P12WIA D100 AL<br>G2HE     | DALI        | 1%             |
| 911401538644 | DN391X LED14/840 P12WIA D100 AL<br>G2HE     | DALI        | 1%             |
| 911401570144 | DN391B LED14/865 P12PSD D100 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401570244 | DN391B LED14/840 P12PSD D100 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401570344 | DN391B LED14/830 P12PSD D100 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401570444 | DN391B LED14/865 PSD D100 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401570544 | DN391B LED14/840 PSD D100 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401570644 | DN391B LED14/830 PSD D100 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401570744 | DN391B LED12/865 P10PSD D100 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401570844 | DN391B LED12/840 P10PSD D100 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401570944 | DN391B LED12/830 P10PSD D100 ALWP<br>GMG2HE | DALI        | 1%             |
| 911401571044 | DN391B LED12/865 PSD D100 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401571144 | DN391B LED12/840 PSD D100 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401571244 | DN391B LED12/830 PSD D100 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401577944 | DN391B LED14/865 P12PSD D100 AL<br>GMG2HE   | DALI        | 1%             |
| 911401578044 | DN391B LED14/840 P12PSD D100 AL<br>GMG2HE   | DALI        | 1%             |
| 911401578144 | DN391B LED14/830 P12PSD D100 AL<br>GMG2HE   | DALI        | 1%             |
| 911401578544 | DN391B LED14/865 PSD D100 AL<br>GCG2HE      | DALI        | 1%             |
| 911401578644 | DN391B LED14/840 PSD D100 AL<br>GCG2HE      | DALI        | 1%             |
| 911401578744 | DN391B LED14/830 PSD D100 AL<br>GCG2HE      | DALI        | 1%             |

| Order Code   | Full Product Name                           | Maximum dim |                |
|--------------|---------------------------------------------|-------------|----------------|
|              |                                             | Dimmable    | level          |
| 911401579144 | DN391B LED12/865 P10PSD D100 AL<br>GMG2HE   | DALI        | 1%             |
| 911401579244 | DN391B LED12/840 P10PSD D100 AL<br>GMG2HE   | DALI        | 1%             |
| 911401579344 | DN391B LED12/830 P10PSD D100 AL<br>GMG2HE   | DALI        | 1%             |
| 911401579744 | DN391B LED12/865 PSD D100 AL<br>GCG2HE      | DALI        | 1%             |
| 911401579844 | DN391B LED12/840 PSD D100 AL<br>GCG2HE      | DALI        | 1%             |
| 911401579944 | DN391B LED12/830 PSD D100 AL<br>GCG2HE      | DALI        | 1%             |
| 911401503845 | DN394X LED34/9TNW P27PSD D200<br>WH WP G2   | DALI        | 1%             |
| 911401504145 | DN394X LED34/9TNW P27PSD D200<br>WH WPCAUG2 | DALI        | 1%             |
| 911401519944 | DN393B LED26/840 P20PSU<br>D200WHWP CAUG2HE | No          | Not applicable |
| 911401520344 | DN393B LED26/840 P20PSU D200 WH<br>CAUG2HE  | No          | Not applicable |
| 911401526444 | DN394B LED40/865 P29PSU D200 WH<br>GMG2HE   | No          | Not applicable |
| 911401526544 | DN394B LED40/840 P29PSU D200 WH<br>GMG2HE   | No          | Not applicable |
| 911401526644 | DN394B LED40/830 P29PSU D200 WH<br>GMG2HE   | No          | Not applicable |
| 911401527044 | DN394B LED40/865 PSU D200 WH<br>GCG2HE      | No          | Not applicable |
| 911401527144 | DN394B LED40/840 PSU D200 WH<br>GCG2HE      | No          | Not applicable |
| 911401527244 | DN394B LED40/830 PSU D200 WH<br>GCG2HE      | No          | Not applicable |
| 911401527644 | DN393B LED26/865 P19PSU D200 WH<br>GMG2HE   | No          | Not applicable |
| 911401527744 | DN393B LED26/840 P19PSU D200 WH<br>GMG2HE   | No          | Not applicable |
| 911401527844 | DN393B LED26/830 P19PSU D200 WH<br>GMG2HE   | No          | Not applicable |
| 911401528244 | DN393B LED26/865 PSU D200 WH<br>GCG2HE      | No          | Not applicable |
| 911401528344 | DN393B LED26/840 PSU D200 WH<br>GCG2HE      | No          | Not applicable |
| 911401528444 | DN393B LED26/830 PSU D200 WH<br>GCG2HE      | No          | Not applicable |
| 911401530044 | DN392B LED20/865 P14PSU D200 WH<br>GMG2HE   | No          | Not applicable |
| 911401530144 | DN392B LED20/840 P14PSU D200 WH<br>GMG2HE   | No          | Not applicable |
| 911401530244 | DN392B LED20/830 P14PSU D200 WH<br>GMG2HE   | No          | Not applicable |

| Order Code   | Full Product Name                         | Maximum dim |                |
|--------------|-------------------------------------------|-------------|----------------|
|              |                                           | Dimmable    | level          |
| 911401530644 | DN392B LED20/865 PSU D200 WH<br>GCG2HE    | No          | Not applicable |
| 911401530744 | DN392B LED20/840 PSU D200 WH<br>GCG2HE    | No          | Not applicable |
| 911401530844 | DN392B LED20/830 PSU D200 WH<br>GCG2HE    | No          | Not applicable |
| 911401537144 | DN393X LED26/865 P20WIA D200 WH<br>G2HE   | DALI        | 1%             |
| 911401537744 | DN393X LED26/830 P20WIA D200 WH<br>G2HE   | DALI        | 1%             |
| 911401538344 | DN393X LED26/840 P20WIA D200 WH<br>G2HE   | DALI        | 1%             |
| 911401571644 | DN394B LED40/865 P29PSD D200 WH<br>GMG2HE | DALI        | 1%             |
| 911401571744 | DN394B LED40/840 P29PSD D200 WH<br>GMG2HE | DALI        | 1%             |
| 911401571844 | DN394B LED40/830 P29PSD D200 WH<br>GMG2HE | DALI        | 1%             |
| 911401572244 | DN394B LED40/865 PSD D200 WH<br>GCG2HE    | DALI        | 1%             |
| 911401572344 | DN394B LED40/840 PSD D200 WH<br>GCG2HE    | DALI        | 1%             |
| 911401572444 | DN394B LED40/830 PSD D200 WH<br>GCG2HE    | DALI        | 1%             |
| 911401572844 | DN393B LED26/865 P20PSD D200 WH<br>GMG2HE | DALI        | 1%             |
| 911401572944 | DN393B LED26/840 P20PSD D200 WH<br>GMG2HE | DALI        | 1%             |
| 911401573044 | DN393B LED26/830 P20PSD D200 WH<br>GMG2HE | DALI        | 1%             |
| 911401573444 | DN393B LED26/865 PSD D200 WH<br>GCG2HE    | DALI        | 1%             |
| 911401573544 | DN393B LED26/840 PSD D200 WH<br>GCG2HE    | DALI        | 1%             |
| 911401573644 | DN393B LED26/830 PSD D200 WH<br>GCG2HE    | DALI        | 1%             |
| 911401575244 | DN392B LED18/865 P14PSD D200 WH<br>GMG2HE | DALI        | 1%             |
| 911401575344 | DN392B LED18/840 P14PSD D200 WH<br>GMG2HE | DALI        | 1%             |
| 911401575444 | DN392B LED18/830 P14PSD D200 WH<br>GMG2HE | DALI        | 1%             |
| 911401575844 | DN392B LED18/865 PSD D200 WH<br>GCG2HE    | DALI        | 1%             |
| 911401575944 | DN392B LED18/840 PSD D200 WH<br>GCG2HE    | DALI        | 1%             |
| 911401576044 | DN392B LED18/830 PSD D200 WH<br>GCG2HE    | DALI        | 1%             |
| 911401586932 | DN393B LED22/840 P20PSU D200 WH<br>CAUG2  | No          | Not applicable |

| Order Code   | Full Product Name                           | Maximum dim |                |
|--------------|---------------------------------------------|-------------|----------------|
|              |                                             | Dimmable    | level          |
| 911401588632 | DN393B LED22/840 P20PSU D200 WH<br>WP CAUG2 | No          | Not applicable |
| 911401503545 | DN394X LED33/9TNW P27PSD D200 AL<br>WP G2   | DALI        | 1%             |
| 911401520744 | DN394B LED38/865 P29PSU D200<br>ALWP GMG2HE | No          | Not applicable |
| 911401520844 | DN394B LED38/840 P29PSU D200<br>ALWP GMG2HE | No          | Not applicable |
| 911401520944 | DN394B LED38/830 P29PSU D200<br>ALWP GMG2HE | No          | Not applicable |
| 911401521044 | DN394B LED38/865 PSU D200 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401521144 | DN394B LED38/840 PSU D200 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401521244 | DN394B LED38/830 PSU D200 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401521344 | DN393B LED25/865 P19PSU D200 ALWP<br>GMG2HE | No          | Not applicable |
| 911401521444 | DN393B LED25/840 P19PSU D200<br>ALWP GMG2HE | No          | Not applicable |
| 911401521544 | DN393B LED25/830 P19PSU D200 ALWP<br>GMG2HE | No          | Not applicable |
| 911401521644 | DN393B LED25/865 PSU D200 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401521744 | DN393B LED25/840 PSU D200 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401521844 | DN393B LED25/830 PSU D200 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401522544 | DN392B LED18/865 P14PSU D200 ALWP<br>GMG2HE | No          | Not applicable |
| 911401522644 | DN392B LED18/840 P14PSU D200 ALWP<br>GMG2HE | No          | Not applicable |
| 911401522744 | DN392B LED18/830 P14PSU D200 ALWP<br>GMG2HE | No          | Not applicable |
| 911401522844 | DN392B LED18/865 PSU D200 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401522944 | DN392B LED18/840 PSU D200 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401523044 | DN392B LED18/830 PSU D200 AL WP<br>GCG2HE   | No          | Not applicable |
| 911401526144 | DN394B LED38/865 P29PSU D200 AL<br>GMG2HE   | No          | Not applicable |
| 911401526244 | DN394B LED38/840 P29PSU D200 AL<br>GMG2HE   | No          | Not applicable |
| 911401526344 | DN394B LED38/830 P29PSU D200 AL<br>GMG2HE   | No          | Not applicable |
| 911401526744 | DN394B LED38/865 PSU D200 AL<br>GCG2HE      | No          | Not applicable |
| 911401526844 | DN394B LED38/840 PSU D200 AL<br>GCG2HE      | No          | Not applicable |

| Order Code   | Full Product Name                           | Maximum dim |                |
|--------------|---------------------------------------------|-------------|----------------|
|              |                                             | Dimmable    | level          |
| 911401526944 | DN394B LED38/830 PSU D200 AL<br>GCG2HE      | No          | Not applicable |
| 911401527344 | DN393B LED25/865 P19PSU D200 AL<br>GMG2HE   | No          | Not applicable |
| 911401527444 | DN393B LED25/840 P19PSU D200 AL<br>GMG2HE   | No          | Not applicable |
| 911401527544 | DN393B LED25/830 P19PSU D200 AL<br>GMG2HE   | No          | Not applicable |
| 911401527944 | DN393B LED25/865 PSU D200 AL<br>GCG2HE      | No          | Not applicable |
| 911401528044 | DN393B LED25/840 PSU D200 AL<br>GCG2HE      | No          | Not applicable |
| 911401528144 | DN393B LED25/830 PSU D200 AL<br>GCG2HE      | No          | Not applicable |
| 911401529744 | DN392B LED18/865 P14PSU D200 AL<br>GMG2HE   | No          | Not applicable |
| 911401529844 | DN392B LED18/840 P14PSU D200 AL<br>GMG2HE   | No          | Not applicable |
| 911401529944 | DN392B LED18/830 P14PSU D200 AL<br>GMG2HE   | No          | Not applicable |
| 911401530344 | DN392B LED18/865 PSU D200 AL<br>GCG2HE      | No          | Not applicable |
| 911401530444 | DN392B LED18/840 PSU D200 AL<br>GCG2HE      | No          | Not applicable |
| 911401530544 | DN392B LED18/830 PSU D200 AL<br>GCG2HE      | No          | Not applicable |
| 911401537044 | DN393X LED25/865 P20WIA D200 AL<br>G2HE     | DALI        | 1%             |
| 911401537644 | DN393X LED25/830 P20WIA D200 AL<br>G2HE     | DALI        | 1%             |
| 911401538244 | DN393X LED25/840 P20WIA D200 AL<br>G2HE     | DALI        | 1%             |
| 911401566844 | DN394B LED38/865 P29PSD D200<br>ALWP GMG2HE | DALI        | 1%             |
| 911401566944 | DN394B LED38/840 P29PSD D200<br>ALWP GMG2HE | DALI        | 1%             |
| 911401567044 | DN394B LED38/830 P29PSD D200<br>ALWP GMG2HE | DALI        | 1%             |
| 911401567144 | DN394B LED38/865 PSD D200 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401567244 | DN394B LED38/840 PSD D200 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401567344 | DN394B LED38/830 PSD D200 AL WP<br>GCG2HE   | DALI        | 1%             |
| 911401567444 | DN393B LED25/865 P20PSD D200<br>ALWP GMG2HE | DALI        | 1%             |
| 911401567544 | DN393B LED25/840 P20PSD D200<br>ALWP GMG2HE | DALI        | 1%             |
| 911401567644 | DN393B LED25/830 P20PSD D200<br>ALWP GMG2HE | DALI        | 1%             |

| Order Code   | Full Product Name                           | Maximum dim |       |
|--------------|---------------------------------------------|-------------|-------|
|              |                                             | Dimmable    | level |
| 911401567744 | DN393B LED25/865 PSD D200 AL WP<br>GCG2HE   | DALI        | 1%    |
| 911401567844 | DN393B LED25/840 PSD D200 AL WP<br>GCG2HE   | DALI        | 1%    |
| 911401567944 | DN393B LED25/830 PSD D200 AL WP<br>GCG2HE   | DALI        | 1%    |
| 911401568644 | DN392B LED18/865 P14PSD D200 ALWP<br>GMG2HE | DALI        | 1%    |
| 911401568744 | DN392B LED18/840 P14PSD D200 ALWP<br>GMG2HE | DALI        | 1%    |
| 911401568844 | DN392B LED18/830 P14PSD D200 ALWP<br>GMG2HE | DALI        | 1%    |
| 911401568944 | DN392B LED18/865 PSD D200 AL WP<br>GCG2HE   | DALI        | 1%    |
| 911401569044 | DN392B LED18/840 PSD D200 AL WP<br>GCG2HE   | DALI        | 1%    |
| 911401569144 | DN392B LED18/830 PSD D200 AL WP<br>GCG2HE   | DALI        | 1%    |
| 911401571344 | DN394B LED38/865 P29PSD D200 AL<br>GMG2HE   | DALI        | 1%    |
| 911401571444 | DN394B LED38/840 P29PSD D200 AL<br>GMG2HE   | DALI        | 1%    |
| 911401571544 | DN394B LED38/830 P29PSD D200 AL<br>GMG2HE   | DALI        | 1%    |
| 911401571944 | DN394B LED38/865 PSD D200 AL<br>GCG2HE      | DALI        | 1%    |
| 911401572044 | DN394B LED38/840 PSD D200 AL<br>GCG2HE      | DALI        | 1%    |
| 911401572144 | DN394B LED38/830 PSD D200 AL<br>GCG2HE      | DALI        | 1%    |
| 911401572544 | DN393B LED25/865 P20PSD D200 AL<br>GMG2HE   | DALI        | 1%    |
| 911401572644 | DN393B LED25/840 P20PSD D200 AL<br>GMG2HE   | DALI        | 1%    |
| 911401572744 | DN393B LED25/830 P20PSD D200 AL<br>GMG2HE   | DALI        | 1%    |
| 911401573144 | DN393B LED25/865 PSD D200 AL<br>GCG2HE      | DALI        | 1%    |
| 911401573244 | DN393B LED25/840 PSD D200 AL<br>GCG2HE      | DALI        | 1%    |
| 911401573344 | DN393B LED25/830 PSD D200 AL<br>GCG2HE      | DALI        | 1%    |
| 911401574944 | DN392B LED18/865 P14PSD D200 AL<br>GMG2HE   | DALI        | 1%    |
| 911401575044 | DN392B LED18/840 P14PSD D200 AL<br>GMG2HE   | DALI        | 1%    |
| 911401575144 | DN392B LED18/830 P14PSD D200 AL<br>GMG2HE   | DALI        | 1%    |
| 911401575544 | DN392B LED18/865 PSD D200 AL<br>GCG2HE      | DALI        | 1%    |

| Order Code   | Full Product Name                           | Maximum dim |                |
|--------------|---------------------------------------------|-------------|----------------|
|              |                                             | Dimmable    | level          |
| 911401575644 | DN392B LED18/840 PSD D200 AL<br>GCG2HE      | DALI        | 1%             |
| 911401575744 | DN392B LED18/830 PSD D200 AL<br>GCG2HE      | DALI        | 1%             |
| 911401577042 | DN393X LED22/840 P20L1W D200 WH<br>CAUG2    | No          | 1%             |
| 911401577542 | DN392X LED17/840 P15L1W D150 WH<br>CAUG2    | No          | 1%             |
| 911401503945 | DN392X LED17/9TNW P15PSD D150 WH<br>WP G2   | DALI        | 1%             |
| 911401504245 | DN392X LED17/9TNW P15PSD D150 WH<br>WPCAUG2 | DALI        | 1%             |
| 911401520044 | DN392B LED20/840 P15PSU D150WHWP<br>CAUG2HE | No          | Not applicable |
| 911401520144 | DN391B LED13/840 P11PSU D150WHWP<br>CAUG2HE | No          | Not applicable |
| 911401520444 | DN392B LED20/840 P15PSU D150 WH<br>CAUG2HE  | No          | Not applicable |
| 911401520544 | DN391B LED13/840 P11PSU D150 WH<br>CAUG2HE  | No          | Not applicable |
| 911401528844 | DN392B LED22/865 P16PSU D150 WH<br>GMG2HE   | No          | Not applicable |
| 911401528944 | DN392B LED22/840 P16PSU D150 WH<br>GMG2HE   | No          | Not applicable |
| 911401529044 | DN392B LED22/830 P16PSU D150 WH<br>GMG2HE   | No          | Not applicable |
| 911401529444 | DN392B LED22/865 PSU D150 WH<br>GCG2HE      | No          | Not applicable |
| 911401529544 | DN392B LED22/840 PSU D150 WH<br>GCG2HE      | No          | Not applicable |
| 911401529644 | DN392B LED22/830 PSU D150 WH<br>GCG2HE      | No          | Not applicable |
| 911401531244 | DN392B LED20/865 P14PSU D150 WH<br>GMG2HE   | No          | Not applicable |
| 911401531344 | DN392B LED20/840 P14PSU D150 WH<br>GMG2HE   | No          | Not applicable |
| 911401531444 | DN392B LED20/830 P14PSU D150 WH<br>GMG2HE   | No          | Not applicable |
| 911401531844 | DN392B LED20/865 PSU D150 WH<br>GCG2HE      | No          | Not applicable |
| 911401531944 | DN392B LED20/840 PSU D150 WH<br>GCG2HE      | No          | Not applicable |
| 911401532044 | DN392B LED20/830 PSU D150 WH<br>GCG2HE      | No          | Not applicable |
| 911401532444 | DN391B LED13/865 P10PSU D150 WH<br>GMG2HE   | No          | Not applicable |
| 911401532544 | DN391B LED13/840 P10PSU D150 WH<br>GMG2HE   | No          | Not applicable |
| 911401532644 | DN391B LED13/830 P10PSU D150 WH<br>GMG2HE   | No          | Not applicable |

| Order Code   | Full Product Name                         | Maximum dim |                |
|--------------|-------------------------------------------|-------------|----------------|
|              |                                           | Dimmable    | level          |
| 911401533044 | DN391B LED13/865 PSU D150 WH<br>GCG2HE    | No          | Not applicable |
| 911401533144 | DN391B LED13/840 PSU D150 WH<br>GCG2HE    | No          | Not applicable |
| 911401533244 | DN391B LED13/830 PSU D150 WH<br>GCG2HE    | No          | Not applicable |
| 911401537344 | DN392X LED20/865 P15WIA D150 WH<br>G2HE   | DALI        | 1%             |
| 911401537944 | DN392X LED20/830 P15WIA D150 WH<br>G2HE   | DALI        | 1%             |
| 911401538544 | DN392X LED20/840 P15WIA D150 WH<br>G2HE   | DALI        | 1%             |
| 911401566544 | DN392B LED19/865 P14PSD D150 WH<br>GMG2HE | DALI        | 1%             |
| 911401566644 | DN392B LED19/840 P14PSD D150 WH<br>GMG2HE | DALI        | 1%             |
| 911401566744 | DN392B LED19/830 P14PSD D150 WH<br>GMG2HE | DALI        | 1%             |
| 911401574044 | DN392B LED23/865 P17PSD D150 WH<br>GMG2HE | DALI        | 1%             |
| 911401574144 | DN392B LED23/840 P17PSD D150 WH<br>GMG2HE | DALI        | 1%             |
| 911401574244 | DN392B LED23/830 P17PSD D150 WH<br>GMG2HE | DALI        | 1%             |
| 911401574644 | DN392B LED23/865 PSD D150 WH<br>GCG2HE    | DALI        | 1%             |
| 911401574744 | DN392B LED23/840 PSD D150 WH<br>GCG2HE    | DALI        | 1%             |
| 911401574844 | DN392B LED23/830 PSD D150 WH<br>GCG2HE    | DALI        | 1%             |
| 911401576444 | DN392B LED19/865 PSD D150 WH<br>GCG2HE    | DALI        | 1%             |
| 911401576544 | DN392B LED19/840 PSD D150 WH<br>GCG2HE    | DALI        | 1%             |
| 911401576644 | DN392B LED19/830 PSD D150 WH<br>GCG2HE    | DALI        | 1%             |
| 911401577044 | DN391B LED13/865 P11PSD D150 WH<br>GMG2HE | DALI        | 1%             |
| 911401577144 | DN391B LED13/840 P11PSD D150 WH<br>GMG2HE | DALI        | 1%             |
| 911401577244 | DN391B LED13/830 P11PSD D150 WH<br>GMG2HE | DALI        | 1%             |
| 911401577644 | DN391B LED13/865 PSD D150 WH<br>GCG2HE    | DALI        | 1%             |
| 911401577744 | DN391B LED13/840 PSD D150 WH<br>GCG2HE    | DALI        | 1%             |
| 911401577844 | DN391B LED13/830 PSD D150 WH<br>GCG2HE    | DALI        | 1%             |
| 911401585532 | DN391B LED11/840 P11PSU D150 WH<br>CAUG2  | No          | Not applicable |

| Order Code   | Full Product Name                        | Maximum dim |                |
|--------------|------------------------------------------|-------------|----------------|
|              |                                          | Dimmable    | level          |
| 911401585632 | DN392B LED17/840 P15PSU D150 WH CAUG2    | No          | Not applicable |
| 911401587832 | DN391B LED11/840 P11PSU D150 WH WP CAUG2 | No          | Not applicable |

| Order Code   | Full Product Name                        | Maximum dim |                |
|--------------|------------------------------------------|-------------|----------------|
|              |                                          | Dimmable    | level          |
| 911401587932 | DN392B LED17/840 P15PSU D150 WH WP CAUG2 | No          | Not applicable |

Mechanical and Housing

| Order Code   | Full Product Name                      | Housing Color | Ingress protection |
|--------------|----------------------------------------|---------------|--------------------|
|              |                                        |               | code               |
| 911401504045 | DN391X LED8/9TNW P7PSD D100 WH WP G2   | Black         | IP54               |
| 911401504345 | DN391X LED8/9TNW P7PSD D100 WH WPCAUG2 | Black         | IP54               |
| 911401520244 | DN390B LED7/840 P6PSU D100WHWP CAUG2HE | Aluminum      | IP20/54            |
| 911401520644 | DN390B LED7/840 P6PSU D100 WH CAUG2HE  | Aluminum      | IP20               |
| 911401533644 | DN391B LED15/865 P11PSU D100 WH GMG2HE | Aluminum      | IP20               |
| 911401533744 | DN391B LED15/840 P11PSU D100 WH GMG2HE | Aluminum      | IP20               |
| 911401533844 | DN391B LED15/830 P11PSU D100 WH GMG2HE | Aluminum      | IP20               |
| 911401534244 | DN391B LED15/865 PSU D100 WH GCG2HE    | Aluminum      | IP20               |
| 911401534344 | DN391B LED15/840 PSU D100 WH GCG2HE    | Aluminum      | IP20               |
| 911401534444 | DN391B LED15/830 PSU D100 WH GCG2HE    | Aluminum      | IP20               |
| 911401534844 | DN391B LED12/865 P10PSU D100 WH GMG2HE | Aluminum      | IP20               |
| 911401534944 | DN391B LED12/840 P10PSU D100 WH GMG2HE | Aluminum      | IP20               |
| 911401535044 | DN391B LED12/830 P10PSU D100 WH GMG2HE | Aluminum      | IP20               |
| 911401535544 | DN391B LED12/865 PSU D100 WH GCG2HE    | Aluminum      | IP20               |
| 911401535644 | DN391B LED12/840 PSU D100 WH GCG2HE    | Aluminum      | IP20               |
| 911401535744 | DN391B LED12/830 PSU D100 WH GCG2HE    | Aluminum      | IP20               |
| 911401536144 | DN390B LED7/865 P6PSU D100 WH GMG2HE   | Aluminum      | IP20               |
| 911401536244 | DN390B LED7/840 P6PSU D100 WH GMG2HE   | Aluminum      | IP20               |
| 911401536344 | DN390B LED7/830 P6PSU D100 WH GMG2HE   | Aluminum      | IP20               |
| 911401536744 | DN390B LED7/865 PSU D100 WH GCG2HE     | Aluminum      | IP20               |

| Order Code   | Full Product Name                      | Housing Color                    | Ingress protection |
|--------------|----------------------------------------|----------------------------------|--------------------|
|              |                                        |                                  | code               |
| 911401536844 | DN390B LED7/840 PSU D100 WH GCG2HE     | Aluminum                         | IP20               |
| 911401536944 | DN390B LED7/830 PSU D100 WH GCG2HE     | Aluminum                         | IP20               |
| 911401537544 | DN391X LED15/865 P12WIA D100 WH G2HE   | Aluminum                         | IP20               |
| 911401538144 | DN391X LED15/830 P12WIA D100 WH G2HE   | Aluminum                         | IP20               |
| 911401538744 | DN391X LED15/840 P12WIA D100WH G2HE    | Aluminum                         | IP20               |
| 911401578244 | DN391B LED15/865 P12PSD D100 WH GMG2HE | Aluminum and RAL (to be defined) | IP20               |
| 911401578344 | DN391B LED15/840 P12PSD D100 WH GMG2HE | Aluminum and RAL (to be defined) | IP20               |
| 911401578444 | DN391B LED15/830 P12PSD D100 WH GMG2HE | Aluminum and RAL (to be defined) | IP20               |
| 911401578844 | DN391B LED15/865 PSD D100 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20               |
| 911401578944 | DN391B LED15/840 PSD D100 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20               |
| 911401579044 | DN391B LED15/830 PSD D100 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20               |
| 911401579444 | DN391B LED12/865 P10PSD D100 WH GMG2HE | Aluminum and RAL (to be defined) | IP20               |
| 911401579544 | DN391B LED12/840 P10PSD D100 WH GMG2HE | Aluminum and RAL (to be defined) | IP20               |
| 911401579644 | DN391B LED12/830 P10PSD D100 WH GMG2HE | Aluminum and RAL (to be defined) | IP20               |
| 911401580044 | DN391B LED12/865 PSD D100 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20               |
| 911401580144 | DN391B LED12/840 PSD D100 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20               |
| 911401580244 | DN391B LED12/830 PSD D100 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20               |
| 911401584832 | DN390B LED6/840 P8PSU D100 WH CAUG2    | Black and white                  | IP20               |
| 911401587632 | DN390B LED6/840 P8PSU D100 WH WP CAUG2 | Black and white                  | IP20/54            |
| 911401503645 | DN392X LED16/9TNW P15PSD D150 AL WP G2 | Black                            | IP54               |

| Order Code   | Full Product Name                        | Housing Color | Ingress protection code |
|--------------|------------------------------------------|---------------|-------------------------|
| 911401521944 | DN392B LED20/865 P16PSU D150 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401522044 | DN392B LED20/840 P16PSU D150 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401522144 | DN392B LED20/830 P16PSU D150 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401522244 | DN392B LED20/865 PSU D150 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401522344 | DN392B LED20/840 PSU D150 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401522444 | DN392B LED20/830 PSU D150 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401523144 | DN392B LED18/865 P14PSU D150 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401523244 | DN392B LED18/840 P14PSU D150 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401523344 | DN392B LED18/830 P14PSU D150 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401523444 | DN392B LED18/865 PSU D150 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401523544 | DN392B LED18/840 PSU D150 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401523644 | DN392B LED18/830 PSU D150 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401523744 | DN391B LED12/865 P10PSU D150 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401523844 | DN391B LED12/840 P10PSU D150 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401523944 | DN391B LED12/830 P10PSU D150 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401524044 | DN391B LED12/865 PSU D150 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401524144 | DN391B LED12/840 PSU D150 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401524244 | DN391B LED12/830 PSU D150 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401528544 | DN392B LED20/865 P16PSU D150 AL GMG2HE   | Aluminum      | IP20                    |
| 911401528644 | DN392B LED20/840 P16PSU D150 AL GMG2HE   | Aluminum      | IP20                    |
| 911401528744 | DN392B LED20/830 P16PSU D150 AL GMG2HE   | Aluminum      | IP20                    |
| 911401529144 | DN392B LED20/865 PSU D150 AL GCG2HE      | Aluminum      | IP20                    |
| 911401529244 | DN392B LED20/840 PSU D150 AL GCG2HE      | Aluminum      | IP20                    |
| 911401529344 | DN392B LED20/830 PSU D150 AL GCG2HE      | Aluminum      | IP20                    |
| 911401530944 | DN392B LED18/865 P14PSU D150 AL GMG2HE   | Aluminum      | IP20                    |

| Order Code   | Full Product Name                        | Housing Color                    | Ingress protection code |
|--------------|------------------------------------------|----------------------------------|-------------------------|
| 911401531044 | DN392B LED18/840 P14PSU D150 AL GMG2HE   | Aluminum                         | IP20                    |
| 911401531144 | DN392B LED18/830 P14PSU D150 AL GMG2HE   | Aluminum                         | IP20                    |
| 911401531544 | DN392B LED18/865 PSU D150 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401531644 | DN392B LED18/840 PSU D150 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401531744 | DN392B LED18/830 PSU D150 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401532144 | DN391B LED12/865 P10PSU D150 AL GMG2HE   | Aluminum                         | IP20                    |
| 911401532244 | DN391B LED12/840 P10PSU D150 AL GMG2HE   | Aluminum                         | IP20                    |
| 911401532344 | DN391B LED12/830 P10PSU D150 AL GMG2HE   | Aluminum                         | IP20                    |
| 911401532744 | DN391B LED12/865 PSU D150 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401532844 | DN391B LED12/840 PSU D150 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401532944 | DN391B LED13/830 PSU D150 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401537244 | DN392X LED18/865 P15WIA D150 AL G2HE     | Aluminum                         | IP20                    |
| 911401537844 | DN392X LED18/830 P15WIA D150 AL G2HE     | Aluminum                         | IP20                    |
| 911401538444 | DN392X LED18/840 P15WIA D150 AL G2HE     | Aluminum                         | IP20                    |
| 911401565944 | DN392B LED18/865 P14PSD D150 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401566044 | DN392B LED18/840 P14PSD D150 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401566144 | DN392B LED18/830 P14PSD D150 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401566244 | DN392B LED18/865 P14PSD D150 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401566344 | DN392B LED18/840 P14PSD D150 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401566444 | DN392B LED18/830 P14PSD D150 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401568044 | DN392B LED22/865 P17PSD D150 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401568144 | DN392B LED22/840 P17PSD D150 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401568244 | DN392B LED22/830 P17PSD D150 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401568344 | DN392B LED22/865 PSD D150 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401568444 | DN392B LED22/840 PSD D150 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |

| Order Code   | Full Product Name                        | Housing Color                    | Ingress protection code |
|--------------|------------------------------------------|----------------------------------|-------------------------|
| 911401568544 | DN392B LED22/830 PSD D150 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401569244 | DN392B LED18/865 PSD D150 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401569344 | DN392B LED18/840 PSD D150 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401569444 | DN392B LED18/830 PSD D150 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401569544 | DN391B LED12/865 P11PSD D150 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401569644 | DN391B LED12/840 P11PSD D150 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401569744 | DN391B LED12/830 P11PSD D150 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401569844 | DN391B LED12/865 PSD D150 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401569944 | DN391B LED12/840 PSD D150 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401570044 | DN391B LED12/830 PSD D150 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401573744 | DN392B LED22/865 P17PSD D150 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401573844 | DN392B LED22/840 P17PSD D150 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401573944 | DN392B LED22/830 P17PSD D150 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401574344 | DN392B LED22/865 PSD D150 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401574444 | DN392B LED22/840 PSD D150 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401574544 | DN392B LED22/830 PSD D150 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401576144 | DN392B LED18/865 PSD D150 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401576244 | DN392B LED18/840 PSD D150 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401576344 | DN392B LED18/830 PSD D150 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401576744 | DN391B LED12/865 P11PSD D150 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401576844 | DN391B LED12/840 P11PSD D150 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401576944 | DN391B LED12/830 P11PSD D150 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401577344 | DN391B LED12/865 PSD D150 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401577444 | DN391B LED12/840 PSD D150 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401577544 | DN391B LED12/830 PSD D150 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |

| Order Code   | Full Product Name                        | Housing Color   | Ingress protection code |
|--------------|------------------------------------------|-----------------|-------------------------|
| 911401577142 | DN393X LED22/840 P20L1W D200 AL CAUG2    | Black and white | IP20                    |
| 911401577442 | DN392X LED17/840 P15L1W D150 AL CAUG2    | Black and white | IP20                    |
| 911401503745 | DN391X LED7/9TNW P7PSD D100 AL WP G2     | Black           | IP54                    |
| 911401524344 | DN391B LED14/865 P11PSU D100 ALWP GMG2HE | Aluminum        | IP20/54                 |
| 911401524444 | DN391B LED14/840 P11PSU D100 ALWP GMG2HE | Aluminum        | IP20/54                 |
| 911401524544 | DN391B LED14/830 P11PSU D100 ALWP GMG2HE | Aluminum        | IP20/54                 |
| 911401524644 | DN391B LED14/865 PSU D100 AL WP GCG2HE   | Aluminum        | IP20/54                 |
| 911401524744 | DN391B LED14/840 PSU D100 AL WP GCG2HE   | Aluminum        | IP20/54                 |
| 911401524844 | DN391B LED14/830 PSU D100 AL WP GCG2HE   | Aluminum        | IP20/54                 |
| 911401524944 | DN391B LED12/865 P10PSU D100 ALWP GMG2HE | Aluminum        | IP20/54                 |
| 911401525044 | DN391B LED12/840 P10PSU D100 ALWP GMG2HE | Aluminum        | IP20/54                 |
| 911401525144 | DN391B LED12/830 P10PSU D100 ALWP GMG2HE | Aluminum        | IP20/54                 |
| 911401525244 | DN391B LED12/865 PSU D100 AL WP GCG2HE   | Aluminum        | IP20/54                 |
| 911401525344 | DN391B LED12/840 PSU D100 AL WP GCG2HE   | Aluminum        | IP20/54                 |
| 911401525444 | DN391B LED12/830 PSU D100 AL WP GCG2HE   | Aluminum        | IP20/54                 |
| 911401525544 | DN390B LED7/865 P6PSU D100 AL WP GMG2HE  | Aluminum        | IP20/54                 |
| 911401525644 | DN390B LED7/840 P6PSU D100 AL WP GMG2HE  | Aluminum        | IP20/54                 |
| 911401525744 | DN390B LED7/830 P6PSU D100 AL WP GMG2HE  | Aluminum        | IP20/54                 |
| 911401525844 | DN390B LED7/865 PSU D100 AL WP GCG2HE    | Aluminum        | IP20/54                 |
| 911401525944 | DN390B LED7/840 PSU D100 AL WP GCG2HE    | Aluminum        | IP20/54                 |
| 911401526044 | DN390B LED7/830 PSU D100 AL WP GCG2HE    | Aluminum        | IP20/54                 |
| 911401533344 | DN391B LED14/865 P11PSU D100 AL GMG2HE   | Aluminum        | IP20                    |
| 911401533444 | DN391B LED14/840 P11PSU D100 AL GMG2HE   | Aluminum        | IP20                    |
| 911401533544 | DN391B LED14/830 P11PSU D100 AL GMG2HE   | Aluminum        | IP20                    |
| 911401533944 | DN391B LED14/865 PSU D100 AL GCG2HE      | Aluminum        | IP20                    |

| Order Code   | Full Product Name                        | Housing Color                    | Ingress protection code |
|--------------|------------------------------------------|----------------------------------|-------------------------|
| 911401534044 | DN391B LED14/840 PSU D100 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401534144 | DN391B LED14/830 PSU D100 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401534544 | DN391B LED12/865 P10PSU D100 AL GMG2HE   | Aluminum                         | IP20                    |
| 911401534644 | DN391B LED12/840 P10PSU D100 AL GMG2HE   | Aluminum                         | IP20                    |
| 911401534744 | DN391B LED12/830 P10PSU D100 AL GMG2HE   | Aluminum                         | IP20                    |
| 911401535144 | DN391B LED12/865 PSU D100 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401535244 | DN391B LED12/840 PSU D100 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401535444 | DN391B LED12/830 PSU D100 AL GCG2HE      | Aluminum                         | IP20                    |
| 911401535844 | DN390B LED7/865 P6PSU D100 AL GMG2HE     | Aluminum                         | IP20                    |
| 911401535944 | DN390B LED7/840 P6PSU D100 AL GMG2HE     | Aluminum                         | IP20                    |
| 911401536044 | DN390B LED7/830 P6PSU D100 AL GMG2HE     | Aluminum                         | IP20                    |
| 911401536444 | DN390B LED7/865 PSU D100 AL GCG2HE       | Aluminum                         | IP20                    |
| 911401536544 | DN390B LED7/840 PSU D100 AL GCG2HE       | Aluminum                         | IP20                    |
| 911401536644 | DN390B LED7/830 PSU D100 AL GCG2HE       | Aluminum                         | IP20                    |
| 911401537444 | DN391X LED14/865 P12WIA D100 AL G2HE     | Aluminum                         | IP20                    |
| 911401538044 | DN391X LED14/830 P12WIA D100 AL G2HE     | Aluminum                         | IP20                    |
| 911401538644 | DN391X LED14/840 P12WIA D100 AL G2HE     | Aluminum                         | IP20                    |
| 911401570144 | DN391B LED14/865 P12PSD D100 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401570244 | DN391B LED14/840 P12PSD D100 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401570344 | DN391B LED14/830 P12PSD D100 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401570444 | DN391B LED14/865 PSD D100 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401570544 | DN391B LED14/840 PSD D100 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401570644 | DN391B LED14/830 PSD D100 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401570744 | DN391B LED12/865 P10PSD D100 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401570844 | DN391B LED12/840 P10PSD D100 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |

| Order Code   | Full Product Name                        | Housing Color                    | Ingress protection code |
|--------------|------------------------------------------|----------------------------------|-------------------------|
| 911401570944 | DN391B LED12/830 P10PSD D100 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401571044 | DN391B LED12/865 PSD D100 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401571144 | DN391B LED12/840 PSD D100 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401571244 | DN391B LED12/830 PSD D100 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401577944 | DN391B LED14/865 P12PSD D100 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401578044 | DN391B LED14/840 P12PSD D100 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401578144 | DN391B LED14/830 P12PSD D100 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401578544 | DN391B LED14/865 PSD D100 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401578644 | DN391B LED14/840 PSD D100 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401578744 | DN391B LED14/830 PSD D100 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401579144 | DN391B LED12/865 P10PSD D100 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401579244 | DN391B LED12/840 P10PSD D100 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401579344 | DN391B LED12/830 P10PSD D100 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401579744 | DN391B LED12/865 PSD D100 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401579844 | DN391B LED12/840 PSD D100 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401579944 | DN391B LED12/830 PSD D100 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401503845 | DN394X LED34/9TNW P27PSD D200 WH WP G2   | Black                            | IP54                    |
| 911401504145 | DN394X LED34/9TNW P27PSD D200 WH WPCAUG2 | Black                            | IP54                    |
| 911401519944 | DN393B LED26/840 P20PSU D200WHWP CAUG2HE | Aluminum                         | IP20/54                 |
| 911401520344 | DN393B LED26/840 P20PSU D200 WH CAUG2HE  | Aluminum                         | IP20                    |
| 911401526444 | DN394B LED40/865 P29PSU D200 WH GMG2HE   | Aluminum                         | IP20                    |
| 911401526544 | DN394B LED40/840 P29PSU D200 WH GMG2HE   | Aluminum                         | IP20                    |
| 911401526644 | DN394B LED40/830 P29PSU D200 WH GMG2HE   | Aluminum                         | IP20                    |
| 911401527044 | DN394B LED40/865 PSU D200 WH GCG2HE      | Aluminum                         | IP20                    |
| 911401527144 | DN394B LED40/840 PSU D200 WH GCG2HE      | Aluminum                         | IP20                    |

| Order Code   | Full Product Name                      | Housing Color                    | Ingress protection code |
|--------------|----------------------------------------|----------------------------------|-------------------------|
| 911401527244 | DN394B LED40/830 PSU D200 WH GCG2HE    | Aluminum                         | IP20                    |
| 911401527644 | DN393B LED26/865 P19PSU D200 WH GMG2HE | Aluminum                         | IP20                    |
| 911401527744 | DN393B LED26/840 P19PSU D200 WH GMG2HE | Aluminum                         | IP20                    |
| 911401527844 | DN393B LED26/830 P19PSU D200 WH GMG2HE | Aluminum                         | IP20                    |
| 911401528244 | DN393B LED26/865 PSU D200 WH GCG2HE    | Aluminum                         | IP20                    |
| 911401528344 | DN393B LED26/840 PSU D200 WH GCG2HE    | Aluminum                         | IP20                    |
| 911401528444 | DN393B LED26/830 PSU D200 WH GCG2HE    | Aluminum                         | IP20                    |
| 911401530044 | DN392B LED20/865 P14PSU D200 WH GMG2HE | Aluminum                         | IP20                    |
| 911401530144 | DN392B LED20/840 P14PSU D200 WH GMG2HE | Aluminum                         | IP20                    |
| 911401530244 | DN392B LED20/830 P14PSU D200 WH GMG2HE | Aluminum                         | IP20                    |
| 911401530644 | DN392B LED20/865 PSU D200 WH GCG2HE    | Aluminum                         | IP20                    |
| 911401530744 | DN392B LED20/840 PSU D200 WH GCG2HE    | Aluminum                         | IP20                    |
| 911401530844 | DN392B LED20/830 PSU D200 WH GCG2HE    | Aluminum                         | IP20                    |
| 911401537144 | DN393X LED26/865 P20WIA D200 WH G2HE   | Aluminum                         | IP20                    |
| 911401537744 | DN393X LED26/830 P20WIA D200 WH G2HE   | Aluminum                         | IP20                    |
| 911401538344 | DN393X LED26/840 P20WIA D200 WH G2HE   | Aluminum                         | IP20                    |
| 911401571644 | DN394B LED40/865 P29PSD D200 WH GMG2HE | Aluminum and RAL (to be defined) | IP20                    |
| 911401571744 | DN394B LED40/840 P29PSD D200 WH GMG2HE | Aluminum and RAL (to be defined) | IP20                    |
| 911401571844 | DN394B LED40/830 P29PSD D200 WH GMG2HE | Aluminum and RAL (to be defined) | IP20                    |
| 911401572244 | DN394B LED40/865 PSD D200 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20                    |
| 911401572344 | DN394B LED40/840 PSD D200 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20                    |
| 911401572444 | DN394B LED40/830 PSD D200 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20                    |
| 911401572844 | DN393B LED26/865 P20PSD D200 WH GMG2HE | Aluminum and RAL (to be defined) | IP20                    |
| 911401572944 | DN393B LED26/840 P20PSD D200 WH GMG2HE | Aluminum and RAL (to be defined) | IP20                    |
| 911401573044 | DN393B LED26/830 P20PSD D200 WH GMG2HE | Aluminum and RAL (to be defined) | IP20                    |

| Order Code   | Full Product Name                        | Housing Color                    | Ingress protection code |
|--------------|------------------------------------------|----------------------------------|-------------------------|
| 911401573444 | DN393B LED26/865 PSD D200 WH GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401573544 | DN393B LED26/840 PSD D200 WH GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401573644 | DN393B LED26/830 PSD D200 WH GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401575244 | DN392B LED18/865 P14PSD D200 WH GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401575344 | DN392B LED18/840 P14PSD D200 WH GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401575444 | DN392B LED18/830 P14PSD D200 WH GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401575844 | DN392B LED18/865 PSD D200 WH GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401575944 | DN392B LED18/840 PSD D200 WH GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401576044 | DN392B LED18/830 PSD D200 WH GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401586932 | DN393B LED22/840 P20PSU D200 WH CAUG2    | Black and white                  | IP20                    |
| 911401588632 | DN393B LED22/840 P20PSU D200 WH WP CAUG2 | Black and white                  | IP20/54                 |
| 911401503545 | DN394X LED33/9TNW P27PSD D200 AL WP G2   | Black                            | IP54                    |
| 911401520744 | DN394B LED38/865 P29PSU D200 ALWP GMG2HE | Aluminum                         | IP20/54                 |
| 911401520844 | DN394B LED38/840 P29PSU D200 ALWP GMG2HE | Aluminum                         | IP20/54                 |
| 911401520944 | DN394B LED38/830 P29PSU D200 ALWP GMG2HE | Aluminum                         | IP20/54                 |
| 911401521044 | DN394B LED38/865 PSU D200 AL WP GCG2HE   | Aluminum                         | IP20/54                 |
| 911401521144 | DN394B LED38/840 PSU D200 AL WP GCG2HE   | Aluminum                         | IP20/54                 |
| 911401521244 | DN394B LED38/830 PSU D200 AL WP GCG2HE   | Aluminum                         | IP20/54                 |
| 911401521344 | DN393B LED25/865 P19PSU D200 ALWP GMG2HE | Aluminum                         | IP20/54                 |
| 911401521444 | DN393B LED25/840 P19PSU D200 ALWP GMG2HE | Aluminum                         | IP20/54                 |
| 911401521544 | DN393B LED25/830 P19PSU D200 ALWP GMG2HE | Aluminum                         | IP20/54                 |
| 911401521644 | DN393B LED25/865 PSU D200 AL WP GCG2HE   | Aluminum                         | IP20/54                 |
| 911401521744 | DN393B LED25/840 PSU D200 AL WP GCG2HE   | Aluminum                         | IP20/54                 |
| 911401521844 | DN393B LED25/830 PSU D200 AL WP GCG2HE   | Aluminum                         | IP20/54                 |
| 911401522544 | DN392B LED18/865 P14PSU D200 ALWP GMG2HE | Aluminum                         | IP20/54                 |

| Order Code   | Full Product Name                        | Housing Color | Ingress protection code |
|--------------|------------------------------------------|---------------|-------------------------|
| 911401522644 | DN392B LED18/840 P14PSU D200 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401522744 | DN392B LED18/830 P14PSU D200 ALWP GMG2HE | Aluminum      | IP20/54                 |
| 911401522844 | DN392B LED18/865 PSU D200 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401522944 | DN392B LED18/840 PSU D200 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401523044 | DN392B LED18/830 PSU D200 AL WP GCG2HE   | Aluminum      | IP20/54                 |
| 911401526144 | DN394B LED38/865 P29PSU D200 AL GMG2HE   | Aluminum      | IP20                    |
| 911401526244 | DN394B LED38/840 P29PSU D200 AL GMG2HE   | Aluminum      | IP20                    |
| 911401526344 | DN394B LED38/830 P29PSU D200 AL GMG2HE   | Aluminum      | IP20                    |
| 911401526744 | DN394B LED38/865 PSU D200 AL GCG2HE      | Aluminum      | IP20                    |
| 911401526844 | DN394B LED38/840 PSU D200 AL GCG2HE      | Aluminum      | IP20                    |
| 911401526944 | DN394B LED38/830 PSU D200 AL GCG2HE      | Aluminum      | IP20                    |
| 911401527344 | DN393B LED25/865 P19PSU D200 AL GMG2HE   | Aluminum      | IP20                    |
| 911401527444 | DN393B LED25/840 P19PSU D200 AL GMG2HE   | Aluminum      | IP20                    |
| 911401527544 | DN393B LED25/830 P19PSU D200 AL GMG2HE   | Aluminum      | IP20                    |
| 911401527944 | DN393B LED25/865 PSU D200 AL GCG2HE      | Aluminum      | IP20                    |
| 911401528044 | DN393B LED25/840 PSU D200 AL GCG2HE      | Aluminum      | IP20                    |
| 911401528144 | DN393B LED25/830 PSU D200 AL GCG2HE      | Aluminum      | IP20                    |
| 911401529744 | DN392B LED18/865 P14PSU D200 AL GMG2HE   | Aluminum      | IP20                    |
| 911401529844 | DN392B LED18/840 P14PSU D200 AL GMG2HE   | Aluminum      | IP20                    |
| 911401529944 | DN392B LED18/830 P14PSU D200 AL GMG2HE   | Aluminum      | IP20                    |
| 911401530344 | DN392B LED18/865 PSU D200 AL GCG2HE      | Aluminum      | IP20                    |
| 911401530444 | DN392B LED18/840 PSU D200 AL GCG2HE      | Aluminum      | IP20                    |
| 911401530544 | DN392B LED18/830 PSU D200 AL GCG2HE      | Aluminum      | IP20                    |
| 911401537044 | DN393X LED25/865 P20WIA D200 AL G2HE     | Aluminum      | IP20                    |
| 911401537644 | DN393X LED25/830 P20WIA D200 AL G2HE     | Aluminum      | IP20                    |

| Order Code   | Full Product Name                        | Housing Color                    | Ingress protection code |
|--------------|------------------------------------------|----------------------------------|-------------------------|
| 911401538244 | DN393X LED25/840 P20WIA D200 AL G2HE     | Aluminum                         | IP20                    |
| 911401566844 | DN394B LED38/865 P29PSD D200 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401566944 | DN394B LED38/840 P29PSD D200 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401567044 | DN394B LED38/830 P29PSD D200 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401567144 | DN394B LED38/865 PSD D200 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401567244 | DN394B LED38/840 PSD D200 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401567344 | DN394B LED38/830 PSD D200 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401567444 | DN393B LED25/865 P20PSD D200 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401567544 | DN393B LED25/840 P20PSD D200 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401567644 | DN393B LED25/830 P20PSD D200 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401567744 | DN393B LED25/865 PSD D200 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401567844 | DN393B LED25/840 PSD D200 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401567944 | DN393B LED25/830 PSD D200 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401568644 | DN392B LED18/865 P14PSD D200 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401568744 | DN392B LED18/840 P14PSD D200 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401568844 | DN392B LED18/830 P14PSD D200 ALWP GMG2HE | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401568944 | DN392B LED18/865 PSD D200 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401569044 | DN392B LED18/840 PSD D200 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401569144 | DN392B LED18/830 PSD D200 AL WP GCG2HE   | Aluminum and RAL (to be defined) | IP20/54                 |
| 911401571344 | DN394B LED38/865 P29PSD D200 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401571444 | DN394B LED38/840 P29PSD D200 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401571544 | DN394B LED38/830 P29PSD D200 AL GMG2HE   | Aluminum and RAL (to be defined) | IP20                    |
| 911401571944 | DN394B LED38/865 PSD D200 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401572044 | DN394B LED38/840 PSD D200 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401572144 | DN394B LED38/830 PSD D200 AL GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |

| Order Code   | Full Product Name                           | Housing Color                       | Ingress protection code |
|--------------|---------------------------------------------|-------------------------------------|-------------------------|
| 911401572544 | DN393B LED25/865 P20PSD D200<br>AL GMG2HE   | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401572644 | DN393B LED25/840 P20PSD D200<br>AL GMG2HE   | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401572744 | DN393B LED25/830 P20PSD D200<br>AL GMG2HE   | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401573144 | DN393B LED25/865 PSD D200 AL<br>GCG2HE      | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401573244 | DN393B LED25/840 PSD D200 AL<br>GCG2HE      | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401573344 | DN393B LED25/830 PSD D200 AL<br>GCG2HE      | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401574944 | DN392B LED18/865 P14PSD D200<br>AL GMG2HE   | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401575044 | DN392B LED18/840 P14PSD D200<br>AL GMG2HE   | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401575144 | DN392B LED18/830 P14PSD D200<br>AL GMG2HE   | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401575544 | DN392B LED18/865 PSD D200 AL<br>GCG2HE      | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401575644 | DN392B LED18/840 PSD D200 AL<br>GCG2HE      | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401575744 | DN392B LED18/830 PSD D200 AL<br>GCG2HE      | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401577042 | DN393X LED22/840 P20L1W D200<br>WH CAUG2    | Black and white                     | IP20                    |
| 911401577542 | DN392X LED17/840 P15L1W D150<br>WH CAUG2    | Black and white                     | IP20                    |
| 911401503945 | DN392X LED17/9TNW P15PSD<br>D150 WH WP G2   | Black                               | IP54                    |
| 911401504245 | DN392X LED17/9TNW P15PSD<br>D150 WH WPCAUG2 | Black                               | IP54                    |
| 911401520044 | DN392B LED20/840 P15PSU<br>D150WHWP CAUG2HE | Aluminum                            | IP20/54                 |
| 911401520144 | DN391B LED13/840 P11PSU<br>D150WHWP CAUG2HE | Aluminum                            | IP20/54                 |
| 911401520444 | DN392B LED20/840 P15PSU D150<br>WH CAUG2HE  | Aluminum                            | IP20                    |
| 911401520544 | DN391B LED13/840 P11PSU D150<br>WH CAUG2HE  | Aluminum                            | IP20                    |
| 911401528844 | DN392B LED22/865 P16PSU D150<br>WH GMG2HE   | Aluminum                            | IP20                    |
| 911401528944 | DN392B LED22/840 P16PSU D150<br>WH GMG2HE   | Aluminum                            | IP20                    |
| 911401529044 | DN392B LED22/830 P16PSU D150<br>WH GMG2HE   | Aluminum                            | IP20                    |
| 911401529444 | DN392B LED22/865 PSU D150 WH<br>GCG2HE      | Aluminum                            | IP20                    |
| 911401529544 | DN392B LED22/840 PSU D150 WH<br>GCG2HE      | Aluminum                            | IP20                    |

| Order Code   | Full Product Name                         | Housing Color                       | Ingress protection code |
|--------------|-------------------------------------------|-------------------------------------|-------------------------|
| 911401529644 | DN392B LED22/830 PSU D150 WH<br>GCG2HE    | Aluminum                            | IP20                    |
| 911401531244 | DN392B LED20/865 P14PSU D150<br>WH GMG2HE | Aluminum                            | IP20                    |
| 911401531344 | DN392B LED20/840 P14PSU D150<br>WH GMG2HE | Aluminum                            | IP20                    |
| 911401531444 | DN392B LED20/830 P14PSU D150<br>WH GMG2HE | Aluminum                            | IP20                    |
| 911401531844 | DN392B LED20/865 PSU D150 WH<br>GCG2HE    | Aluminum                            | IP20                    |
| 911401531944 | DN392B LED20/840 PSU D150 WH<br>GCG2HE    | Aluminum                            | IP20                    |
| 911401532044 | DN392B LED20/830 PSU D150 WH<br>GCG2HE    | Aluminum                            | IP20                    |
| 911401532444 | DN391B LED13/865 P10PSU D150<br>WH GMG2HE | Aluminum                            | IP20                    |
| 911401532544 | DN391B LED13/840 P10PSU D150<br>WH GMG2HE | Aluminum                            | IP20                    |
| 911401532644 | DN391B LED13/830 P10PSU D150<br>WH GMG2HE | Aluminum                            | IP20                    |
| 911401533044 | DN391B LED13/865 PSU D150 WH<br>GCG2HE    | Aluminum                            | IP20                    |
| 911401533144 | DN391B LED13/840 PSU D150 WH<br>GCG2HE    | Aluminum                            | IP20                    |
| 911401533244 | DN391B LED13/830 PSU D150 WH<br>GCG2HE    | Aluminum                            | IP20                    |
| 911401537344 | DN392X LED20/865 P15WIA D150<br>WH G2HE   | Aluminum                            | IP20                    |
| 911401537944 | DN392X LED20/830 P15WIA D150<br>WH G2HE   | Aluminum                            | IP20                    |
| 911401538544 | DN392X LED20/840 P15WIA D150<br>WH G2HE   | Aluminum                            | IP20                    |
| 911401566544 | DN392B LED19/865 P14PSD D150<br>WH GMG2HE | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401566644 | DN392B LED19/840 P14PSD D150<br>WH GMG2HE | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401566744 | DN392B LED19/830 P14PSD D150<br>WH GMG2HE | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401574044 | DN392B LED23/865 P17PSD D150<br>WH GMG2HE | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401574144 | DN392B LED23/840 P17PSD D150<br>WH GMG2HE | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401574244 | DN392B LED23/830 P17PSD D150<br>WH GMG2HE | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401574644 | DN392B LED23/865 PSD D150 WH<br>GCG2HE    | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401574744 | DN392B LED23/840 PSD D150 WH<br>GCG2HE    | Aluminum and RAL<br>(to be defined) | IP20                    |
| 911401574844 | DN392B LED23/830 PSD D150 WH<br>GCG2HE    | Aluminum and RAL<br>(to be defined) | IP20                    |

| Order Code   | Full Product Name                      | Housing Color                    | Ingress protection code |
|--------------|----------------------------------------|----------------------------------|-------------------------|
| 911401576444 | DN392B LED19/865 PSD D150 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20                    |
| 911401576544 | DN392B LED19/840 PSD D150 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20                    |
| 911401576644 | DN392B LED19/830 PSD D150 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20                    |
| 911401577044 | DN391B LED13/865 P11PSD D150 WH GMG2HE | Aluminum and RAL (to be defined) | IP20                    |
| 911401577144 | DN391B LED13/840 P11PSD D150 WH GMG2HE | Aluminum and RAL (to be defined) | IP20                    |
| 911401577244 | DN391B LED13/830 P11PSD D150 WH GMG2HE | Aluminum and RAL (to be defined) | IP20                    |
| 911401577644 | DN391B LED13/865 PSD D150 WH GCG2HE    | Aluminum and RAL (to be defined) | IP20                    |

Initial Performance (IEC Compliant)

| Order Code   | Full Product Name                      | Initial chromaticity | Luminous flux tolerance |
|--------------|----------------------------------------|----------------------|-------------------------|
| 911401504045 | DN391X LED8/9TNW P7PSD D100 WH WP G2   | SDCM5                | +/-10%                  |
| 911401504345 | DN391X LED8/9TNW P7PSD D100 WH WPCAUG2 | SDCM5                | +/-10%                  |
| 911401520244 | DN390B LED7/840 P6PSU D100WHWP CAUG2HE | 5                    | +/-10%                  |
| 911401520644 | DN390B LED7/840 P6PSU D100 WH CAUG2HE  | 5                    | +/-10%                  |
| 911401533644 | DN391B LED15/865 P11PSU D100 WH GMG2HE | 5                    | +/-10%                  |
| 911401533744 | DN391B LED15/840 P11PSU D100 WH GMG2HE | 5                    | +/-10%                  |
| 911401533844 | DN391B LED15/830 P11PSU D100 WH GMG2HE | 5                    | +/-10%                  |
| 911401534244 | DN391B LED15/865 PSU D100 WH GCG2HE    | 5                    | +/-10%                  |
| 911401534344 | DN391B LED15/840 PSU D100 WH GCG2HE    | 5                    | +/-10%                  |
| 911401534444 | DN391B LED15/830 PSU D100 WH GCG2HE    | 5                    | +/-10%                  |
| 911401534844 | DN391B LED12/865 P10PSU D100 WH GMG2HE | 5                    | +/-10%                  |
| 911401534944 | DN391B LED12/840 P10PSU D100 WH GMG2HE | 5                    | +/-10%                  |
| 911401535044 | DN391B LED12/830 P10PSU D100 WH GMG2HE | 5                    | +/-10%                  |
| 911401535544 | DN391B LED12/865 PSU D100 WH GCG2HE    | 5                    | +/-10%                  |
| 911401535644 | DN391B LED12/840 PSU D100 WH GCG2HE    | 5                    | +/-10%                  |

| Order Code   | Full Product Name                        | Housing Color                    | Ingress protection code |
|--------------|------------------------------------------|----------------------------------|-------------------------|
| 911401577744 | DN391B LED13/840 PSD D150 WH GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401577844 | DN391B LED13/830 PSD D150 WH GCG2HE      | Aluminum and RAL (to be defined) | IP20                    |
| 911401585532 | DN391B LED11/840 P11PSU D150 WH CAUG2    | Black and white                  | IP20                    |
| 911401585632 | DN392B LED17/840 P15PSU D150 WH CAUG2    | Black and white                  | IP20                    |
| 911401587832 | DN391B LED11/840 P11PSU D150 WH WP CAUG2 | Black and white                  | IP20/54                 |
| 911401587932 | DN392B LED17/840 P15PSU D150 WH WP CAUG2 | Black and white                  | IP20/54                 |

| Order Code   | Full Product Name                      | Initial chromaticity | Luminous flux tolerance |
|--------------|----------------------------------------|----------------------|-------------------------|
| 911401535744 | DN391B LED12/830 PSU D100 WH GCG2HE    | 5                    | +/-10%                  |
| 911401536144 | DN390B LED7/865 P6PSU D100 WH GMG2HE   | 5                    | +/-10%                  |
| 911401536244 | DN390B LED7/840 P6PSU D100 WH GMG2HE   | 5                    | +/-10%                  |
| 911401536344 | DN390B LED7/830 P6PSU D100 WH GMG2HE   | 5                    | +/-10%                  |
| 911401536744 | DN390B LED7/865 PSU D100 WH GCG2HE     | 5                    | +/-10%                  |
| 911401536844 | DN390B LED7/840 PSU D100 WH GCG2HE     | 5                    | +/-10%                  |
| 911401536944 | DN390B LED7/830 PSU D100 WH GCG2HE     | 5                    | +/-10%                  |
| 911401537544 | DN391X LED15/865 P12WIA D100 WH G2HE   | 5                    | +/-10%                  |
| 911401538144 | DN391X LED15/830 P12WIA D100 WH G2HE   | 5                    | +/-10%                  |
| 911401538744 | DN391X LED15/840 P12WIA D100WH G2HE    | 5                    | +/-10%                  |
| 911401578244 | DN391B LED15/865 P12PSD D100 WH GMG2HE | 5                    | -10% / +10%             |
| 911401578344 | DN391B LED15/840 P12PSD D100 WH GMG2HE | 5                    | -10% / +10%             |
| 911401578444 | DN391B LED15/830 P12PSD D100 WH GMG2HE | 5                    | -10% / +10%             |
| 911401578844 | DN391B LED15/865 PSD D100 WH GCG2HE    | 5                    | -10% / +10%             |
| 911401578944 | DN391B LED15/840 PSD D100 WH GCG2HE    | 5                    | -10% / +10%             |

| Order Code   | Full Product Name                           | Initial chromaticity | Luminous flux tolerance |
|--------------|---------------------------------------------|----------------------|-------------------------|
| 911401579044 | DN391B LED15/830 PSD D100 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401579444 | DN391B LED12/865 P10PSD D100<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401579544 | DN391B LED12/840 P10PSD D100<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401579644 | DN391B LED12/830 P10PSD D100<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401580044 | DN391B LED12/865 PSD D100 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401580144 | DN391B LED12/840 PSD D100 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401580244 | DN391B LED12/830 PSD D100 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401584832 | DN390B LED6/840 P8PSU D100 WH<br>CAUG2      | 5                    | +/-10%                  |
| 911401587632 | DN390B LED6/840 P8PSU D100 WH<br>WP CAUG2   | 5                    | +/-10%                  |
| 911401503645 | DN392X LED16/9TNW P15PSD D150<br>AL WP G2   | SDCM5                | +/-10%                  |
| 911401521944 | DN392B LED20/865 P16PSU D150<br>ALWP GMG2HE | 5                    | +/-10%                  |
| 911401522044 | DN392B LED20/840 P16PSU D150<br>ALWP GMG2HE | 5                    | +/-10%                  |
| 911401522144 | DN392B LED20/830 P16PSU D150<br>ALWP GMG2HE | 5                    | +/-10%                  |
| 911401522244 | DN392B LED20/865 PSU D150 AL<br>WP GCG2HE   | 5                    | +/-10%                  |
| 911401522344 | DN392B LED20/840 PSU D150 AL<br>WP GCG2HE   | 5                    | +/-10%                  |
| 911401522444 | DN392B LED20/830 PSU D150 AL<br>WP GCG2HE   | 5                    | +/-10%                  |
| 911401523144 | DN392B LED18/865 P14PSU D150<br>ALWP GMG2HE | 5                    | +/-10%                  |
| 911401523244 | DN392B LED18/840 P14PSU D150<br>ALWP GMG2HE | 5                    | +/-10%                  |
| 911401523344 | DN392B LED18/830 P14PSU D150<br>ALWP GMG2HE | 5                    | +/-10%                  |
| 911401523444 | DN392B LED18/865 PSU D150 AL WP<br>GCG2HE   | 5                    | +/-10%                  |
| 911401523544 | DN392B LED18/840 PSU D150 AL WP<br>GCG2HE   | 5                    | +/-10%                  |
| 911401523644 | DN392B LED18/830 PSU D150 AL WP<br>GCG2HE   | 5                    | +/-10%                  |
| 911401523744 | DN391B LED12/865 P10PSU D150<br>ALWP GMG2HE | 5                    | +/-10%                  |
| 911401523844 | DN391B LED12/840 P10PSU D150<br>ALWP GMG2HE | 5                    | +/-10%                  |
| 911401523944 | DN391B LED12/830 P10PSU D150<br>ALWP GMG2HE | 5                    | +/-10%                  |

| Order Code   | Full Product Name                           | Initial chromaticity | Luminous flux tolerance |
|--------------|---------------------------------------------|----------------------|-------------------------|
| 911401524044 | DN391B LED12/865 PSU D150 AL WP<br>GCG2HE   | 5                    | +/-10%                  |
| 911401524144 | DN391B LED12/840 PSU D150 AL WP<br>GCG2HE   | 5                    | +/-10%                  |
| 911401524244 | DN391B LED12/830 PSU D150 AL WP<br>GCG2HE   | 5                    | +/-10%                  |
| 911401528544 | DN392B LED20/865 P16PSU D150 AL<br>GMG2HE   | 5                    | +/-10%                  |
| 911401528644 | DN392B LED20/840 P16PSU D150 AL<br>GMG2HE   | 5                    | +/-10%                  |
| 911401528744 | DN392B LED20/830 P16PSU D150 AL<br>GMG2HE   | 5                    | +/-10%                  |
| 911401529144 | DN392B LED20/865 PSU D150 AL<br>GCG2HE      | 5                    | +/-10%                  |
| 911401529244 | DN392B LED20/840 PSU D150 AL<br>GCG2HE      | 5                    | +/-10%                  |
| 911401529344 | DN392B LED20/830 PSU D150 AL<br>GCG2HE      | 5                    | +/-10%                  |
| 911401530944 | DN392B LED18/865 P14PSU D150 AL<br>GMG2HE   | 5                    | +/-10%                  |
| 911401531044 | DN392B LED18/840 P14PSU D150 AL<br>GMG2HE   | 5                    | +/-10%                  |
| 911401531144 | DN392B LED18/830 P14PSU D150 AL<br>GMG2HE   | 5                    | +/-10%                  |
| 911401531544 | DN392B LED18/865 PSU D150 AL<br>GCG2HE      | 5                    | +/-10%                  |
| 911401531644 | DN392B LED18/840 PSU D150 AL<br>GCG2HE      | 5                    | +/-10%                  |
| 911401531744 | DN392B LED18/830 PSU D150 AL<br>GCG2HE      | 5                    | +/-10%                  |
| 911401532144 | DN391B LED12/865 P10PSU D150 AL<br>GMG2HE   | 5                    | +/-10%                  |
| 911401532244 | DN391B LED12/840 P10PSU D150 AL<br>GMG2HE   | 5                    | +/-10%                  |
| 911401532344 | DN391B LED12/830 P10PSU D150 AL<br>GMG2HE   | 5                    | +/-10%                  |
| 911401532744 | DN391B LED12/865 PSU D150 AL<br>GCG2HE      | 5                    | +/-10%                  |
| 911401532844 | DN391B LED12/840 PSU D150 AL<br>GCG2HE      | 5                    | +/-10%                  |
| 911401532944 | DN391B LED13/830 PSU D150 AL<br>GCG2HE      | 5                    | +/-10%                  |
| 911401537244 | DN392X LED18/865 P15WIA D150 AL<br>G2HE     | 5                    | +/-10%                  |
| 911401537844 | DN392X LED18/830 P15WIA D150 AL<br>G2HE     | 5                    | +/-10%                  |
| 911401538444 | DN392X LED18/840 P15WIA D150 AL<br>G2HE     | 5                    | +/-10%                  |
| 911401565944 | DN392B LED18/865 P14PSD D150<br>ALWP GMG2HE | 5                    | -10% / +10%             |

| Order Code   | Full Product Name                        | Initial chromaticity | Luminous flux tolerance |
|--------------|------------------------------------------|----------------------|-------------------------|
| 911401566044 | DN392B LED18/840 P14PSD D150 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401566144 | DN392B LED18/830 P14PSD D150 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401566244 | DN392B LED18/865 P14PSD D150 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401566344 | DN392B LED18/840 P14PSD D150 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401566444 | DN392B LED18/830 P14PSD D150 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401568044 | DN392B LED22/865 P17PSD D150 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401568144 | DN392B LED22/840 P17PSD D150 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401568244 | DN392B LED22/830 P17PSD D150 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401568344 | DN392B LED22/865 PSD D150 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401568444 | DN392B LED22/840 PSD D150 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401568544 | DN392B LED22/830 PSD D150 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401569244 | DN392B LED18/865 PSD D150 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401569344 | DN392B LED18/840 PSD D150 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401569444 | DN392B LED18/830 PSD D150 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401569544 | DN391B LED12/865 P11PSD D150 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401569644 | DN391B LED12/840 P11PSD D150 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401569744 | DN391B LED12/830 P11PSD D150 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401569844 | DN391B LED12/865 PSD D150 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401569944 | DN391B LED12/840 PSD D150 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401570044 | DN391B LED12/830 PSD D150 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401573744 | DN392B LED22/865 P17PSD D150 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401573844 | DN392B LED22/840 P17PSD D150 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401573944 | DN392B LED22/830 P17PSD D150 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401574344 | DN392B LED22/865 PSD D150 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401574444 | DN392B LED22/840 PSD D150 AL GCG2HE      | 5                    | -10% / +10%             |

| Order Code   | Full Product Name                          | Initial chromaticity | Luminous flux tolerance |
|--------------|--------------------------------------------|----------------------|-------------------------|
| 911401574544 | DN392B LED22/830 PSD D150 AL GCG2HE        | 5                    | -10% / +10%             |
| 911401576144 | DN392B LED18/865 PSD D150 AL GCG2HE        | 5                    | -10% / +10%             |
| 911401576244 | DN392B LED18/840 PSD D150 AL GCG2HE        | 5                    | -10% / +10%             |
| 911401576344 | DN392B LED18/830 PSD D150 AL GCG2HE        | 5                    | -10% / +10%             |
| 911401576744 | DN391B LED12/865 P11PSD D150 AL GMG2HE     | 5                    | -10% / +10%             |
| 911401576844 | DN391B LED12/840 P11PSD D150 AL GMG2HE     | 5                    | -10% / +10%             |
| 911401576944 | DN391B LED12/830 P11PSD D150 AL GMG2HE     | 5                    | -10% / +10%             |
| 911401577344 | DN391B LED12/865 PSD D150 AL GCG2HE        | 5                    | -10% / +10%             |
| 911401577444 | DN391B LED12/840 PSD D150 AL GCG2HE        | 5                    | -10% / +10%             |
| 911401577544 | DN391B LED12/830 PSD D150 AL GCG2HE        | 5                    | -10% / +10%             |
| 911401577142 | DN393X LED22/840 P20L1W D200 AL CAUG2      | 5                    | +/-10%                  |
| 911401577442 | DN392X LED17/840 P15L1W D150 AL CAUG2      | 5                    | +/-10%                  |
| 911401503745 | DN391X LED7/9TNW P7PSD D100 AL WP G2 SDCM5 | 5                    | +/-10%                  |
| 911401524344 | DN391B LED14/865 P11PSU D100 ALWP GMG2HE   | 5                    | +/-10%                  |
| 911401524444 | DN391B LED14/840 P11PSU D100 ALWP GMG2HE   | 5                    | +/-10%                  |
| 911401524544 | DN391B LED14/830 P11PSU D100 ALWP GMG2HE   | 5                    | +/-10%                  |
| 911401524644 | DN391B LED14/865 PSU D100 AL WP GCG2HE     | 5                    | +/-10%                  |
| 911401524744 | DN391B LED14/840 PSU D100 AL WP GCG2HE     | 5                    | +/-10%                  |
| 911401524844 | DN391B LED14/830 PSU D100 AL WP GCG2HE     | 5                    | +/-10%                  |
| 911401524944 | DN391B LED12/865 P10PSU D100 ALWP GMG2HE   | 5                    | +/-10%                  |
| 911401525044 | DN391B LED12/840 P10PSU D100 ALWP GMG2HE   | 5                    | +/-10%                  |
| 911401525144 | DN391B LED12/830 P10PSU D100 ALWP GMG2HE   | 5                    | +/-10%                  |
| 911401525244 | DN391B LED12/865 PSU D100 AL WP GCG2HE     | 5                    | +/-10%                  |
| 911401525344 | DN391B LED12/840 PSU D100 AL WP GCG2HE     | 5                    | +/-10%                  |
| 911401525444 | DN391B LED12/830 PSU D100 AL WP GCG2HE     | 5                    | +/-10%                  |

| Order Code   | Full Product Name                       | Initial chromaticity | Luminous flux tolerance |
|--------------|-----------------------------------------|----------------------|-------------------------|
| 911401525544 | DN390B LED7/865 P6PSU D100 AL WP GMG2HE | 5                    | +/-10%                  |
| 911401525644 | DN390B LED7/840 P6PSU D100 AL WP GMG2HE | 5                    | +/-10%                  |
| 911401525744 | DN390B LED7/830 P6PSU D100 AL WP GMG2HE | 5                    | +/-10%                  |
| 911401525844 | DN390B LED7/865 PSU D100 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401525944 | DN390B LED7/840 PSU D100 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401526044 | DN390B LED7/830 PSU D100 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401533344 | DN391B LED14/865 P11PSU D100 AL GMG2HE  | 5                    | +/-10%                  |
| 911401533444 | DN391B LED14/840 P11PSU D100 AL GMG2HE  | 5                    | +/-10%                  |
| 911401533544 | DN391B LED14/830 P11PSU D100 AL GMG2HE  | 5                    | +/-10%                  |
| 911401533944 | DN391B LED14/865 PSU D100 AL GCG2HE     | 5                    | +/-10%                  |
| 911401534044 | DN391B LED14/840 PSU D100 AL GCG2HE     | 5                    | +/-10%                  |
| 911401534144 | DN391B LED14/830 PSU D100 AL GCG2HE     | 5                    | +/-10%                  |
| 911401534544 | DN391B LED12/865 P10PSU D100 AL GMG2HE  | 5                    | +/-10%                  |
| 911401534644 | DN391B LED12/840 P10PSU D100 AL GMG2HE  | 5                    | +/-10%                  |
| 911401534744 | DN391B LED12/830 P10PSU D100 AL GMG2HE  | 5                    | +/-10%                  |
| 911401535144 | DN391B LED12/865 PSU D100 AL GCG2HE     | 5                    | +/-10%                  |
| 911401535244 | DN391B LED12/840 PSU D100 AL GCG2HE     | 5                    | +/-10%                  |
| 911401535444 | DN391B LED12/830 PSU D100 AL GCG2HE     | 5                    | +/-10%                  |
| 911401535844 | DN390B LED7/865 P6PSU D100 AL GMG2HE    | 5                    | +/-10%                  |
| 911401535944 | DN390B LED7/840 P6PSU D100 AL GMG2HE    | 5                    | +/-10%                  |
| 911401536044 | DN390B LED7/830 P6PSU D100 AL GMG2HE    | 5                    | +/-10%                  |
| 911401536444 | DN390B LED7/865 PSU D100 AL GCG2HE      | 5                    | +/-10%                  |
| 911401536544 | DN390B LED7/840 PSU D100 AL GCG2HE      | 5                    | +/-10%                  |
| 911401536644 | DN390B LED7/830 PSU D100 AL GCG2HE      | 5                    | +/-10%                  |
| 911401537444 | DN391X LED14/865 P12WIA D100 AL G2HE    | 5                    | +/-10%                  |

| Order Code   | Full Product Name                        | Initial chromaticity | Luminous flux tolerance |
|--------------|------------------------------------------|----------------------|-------------------------|
| 911401538044 | DN391X LED14/830 P12WIA D100 AL G2HE     | 5                    | +/-10%                  |
| 911401538644 | DN391X LED14/840 P12WIA D100 AL G2HE     | 5                    | +/-10%                  |
| 911401570144 | DN391B LED14/865 P12PSD D100 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401570244 | DN391B LED14/840 P12PSD D100 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401570344 | DN391B LED14/830 P12PSD D100 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401570444 | DN391B LED14/865 PSD D100 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401570544 | DN391B LED14/840 PSD D100 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401570644 | DN391B LED14/830 PSD D100 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401570744 | DN391B LED12/865 P10PSD D100 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401570844 | DN391B LED12/840 P10PSD D100 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401570944 | DN391B LED12/830 P10PSD D100 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401571044 | DN391B LED12/865 PSD D100 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401571144 | DN391B LED12/840 PSD D100 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401571244 | DN391B LED12/830 PSD D100 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401577944 | DN391B LED14/865 P12PSD D100 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401578044 | DN391B LED14/840 P12PSD D100 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401578144 | DN391B LED14/830 P12PSD D100 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401578544 | DN391B LED14/865 PSD D100 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401578644 | DN391B LED14/840 PSD D100 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401578744 | DN391B LED14/830 PSD D100 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401579144 | DN391B LED12/865 P10PSD D100 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401579244 | DN391B LED12/840 P10PSD D100 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401579344 | DN391B LED12/830 P10PSD D100 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401579744 | DN391B LED12/865 PSD D100 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401579844 | DN391B LED12/840 PSD D100 AL GCG2HE      | 5                    | -10% / +10%             |

| Order Code   | Full Product Name                           | Initial chromaticity | Luminous flux tolerance |
|--------------|---------------------------------------------|----------------------|-------------------------|
| 911401579944 | DN391B LED12/830 PSD D100 AL<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401503845 | DN394X LED34/9TNW P27PSD D200<br>WH WP G2   | SDCM5                | +/-10%                  |
| 911401504145 | DN394X LED34/9TNW P27PSD D200<br>WH WPCAUG2 | SDCM5                | +/-10%                  |
| 911401519944 | DN393B LED26/840 P20PSU<br>D200WHWP CAUG2HE | 5                    | +/-10%                  |
| 911401520344 | DN393B LED26/840 P20PSU D200<br>WH CAUG2HE  | 5                    | +/-10%                  |
| 911401526444 | DN394B LED40/865 P29PSU D200<br>WH GMG2HE   | 5                    | +/-10%                  |
| 911401526544 | DN394B LED40/840 P29PSU D200<br>WH GMG2HE   | 5                    | +/-10%                  |
| 911401526644 | DN394B LED40/830 P29PSU D200<br>WH GMG2HE   | 5                    | +/-10%                  |
| 911401527044 | DN394B LED40/865 PSU D200 WH<br>GCG2HE      | 5                    | +/-10%                  |
| 911401527144 | DN394B LED40/840 PSU D200 WH<br>GCG2HE      | 5                    | +/-10%                  |
| 911401527244 | DN394B LED40/830 PSU D200 WH<br>GCG2HE      | 5                    | +/-10%                  |
| 911401527644 | DN393B LED26/865 P19PSU D200<br>WH GMG2HE   | 5                    | +/-10%                  |
| 911401527744 | DN393B LED26/840 P19PSU D200<br>WH GMG2HE   | 5                    | +/-10%                  |
| 911401527844 | DN393B LED26/830 P19PSU D200<br>WH GMG2HE   | 5                    | +/-10%                  |
| 911401528244 | DN393B LED26/865 PSU D200 WH<br>GCG2HE      | 5                    | +/-10%                  |
| 911401528344 | DN393B LED26/840 PSU D200 WH<br>GCG2HE      | 5                    | +/-10%                  |
| 911401528444 | DN393B LED26/830 PSU D200 WH<br>GCG2HE      | 5                    | +/-10%                  |
| 911401530044 | DN392B LED20/865 P14PSU D200<br>WH GMG2HE   | 5                    | +/-10%                  |
| 911401530144 | DN392B LED20/840 P14PSU D200<br>WH GMG2HE   | 5                    | +/-10%                  |
| 911401530244 | DN392B LED20/830 P14PSU D200<br>WH GMG2HE   | 5                    | +/-10%                  |
| 911401530644 | DN392B LED20/865 PSU D200 WH<br>GCG2HE      | 5                    | +/-10%                  |
| 911401530744 | DN392B LED20/840 PSU D200 WH<br>GCG2HE      | 5                    | +/-10%                  |
| 911401530844 | DN392B LED20/830 PSU D200 WH<br>GCG2HE      | 5                    | +/-10%                  |
| 911401537144 | DN393X LED26/865 P20WIA D200<br>WH G2HE     | 5                    | +/-10%                  |
| 911401537744 | DN393X LED26/830 P20WIA D200<br>WH G2HE     | 5                    | +/-10%                  |

| Order Code   | Full Product Name                           | Initial chromaticity | Luminous flux tolerance |
|--------------|---------------------------------------------|----------------------|-------------------------|
| 911401538344 | DN393X LED26/840 P20WIA D200<br>WH G2HE     | 5                    | +/-10%                  |
| 911401571644 | DN394B LED40/865 P29PSD D200<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401571744 | DN394B LED40/840 P29PSD D200<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401571844 | DN394B LED40/830 P29PSD D200<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401572244 | DN394B LED40/865 PSD D200 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401572344 | DN394B LED40/840 PSD D200 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401572444 | DN394B LED40/830 PSD D200 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401572844 | DN393B LED26/865 P20PSD D200<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401572944 | DN393B LED26/840 P20PSD D200<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401573044 | DN393B LED26/830 P20PSD D200<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401573444 | DN393B LED26/865 PSD D200 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401573544 | DN393B LED26/840 PSD D200 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401573644 | DN393B LED26/830 PSD D200 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401575244 | DN392B LED18/865 P14PSD D200<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401575344 | DN392B LED18/840 P14PSD D200<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401575444 | DN392B LED18/830 P14PSD D200<br>WH GMG2HE   | 5                    | -10% / +10%             |
| 911401575844 | DN392B LED18/865 PSD D200 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401575944 | DN392B LED18/840 PSD D200 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401576044 | DN392B LED18/830 PSD D200 WH<br>GCG2HE      | 5                    | -10% / +10%             |
| 911401586932 | DN393B LED22/840 P20PSU D200<br>WH CAUG2    | 5                    | +/-10%                  |
| 911401588632 | DN393B LED22/840 P20PSU D200<br>WH WP CAUG2 | 5                    | +/-10%                  |
| 911401503545 | DN394X LED33/9TNW P27PSD D200<br>AL WP G2   | SDCM5                | +/-10%                  |
| 911401520744 | DN394B LED38/865 P29PSU D200<br>ALWP GMG2HE | 5                    | +/-10%                  |
| 911401520844 | DN394B LED38/840 P29PSU D200<br>ALWP GMG2HE | 5                    | +/-10%                  |
| 911401520944 | DN394B LED38/830 P29PSU D200<br>ALWP GMG2HE | 5                    | +/-10%                  |

| Order Code   | Full Product Name                        | Initial chromaticity | Luminous flux tolerance |
|--------------|------------------------------------------|----------------------|-------------------------|
| 911401521044 | DN394B LED38/865 PSU D200 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401521144 | DN394B LED38/840 PSU D200 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401521244 | DN394B LED38/830 PSU D200 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401521344 | DN393B LED25/865 P19PSU D200 ALWP GMG2HE | 5                    | +/-10%                  |
| 911401521444 | DN393B LED25/840 P19PSU D200 ALWP GMG2HE | 5                    | +/-10%                  |
| 911401521544 | DN393B LED25/830 P19PSU D200 ALWP GMG2HE | 5                    | +/-10%                  |
| 911401521644 | DN393B LED25/865 PSU D200 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401521744 | DN393B LED25/840 PSU D200 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401521844 | DN393B LED25/830 PSU D200 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401522544 | DN392B LED18/865 P14PSU D200 ALWP GMG2HE | 5                    | +/-10%                  |
| 911401522644 | DN392B LED18/840 P14PSU D200 ALWP GMG2HE | 5                    | +/-10%                  |
| 911401522744 | DN392B LED18/830 P14PSU D200 ALWP GMG2HE | 5                    | +/-10%                  |
| 911401522844 | DN392B LED18/865 PSU D200 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401522944 | DN392B LED18/840 PSU D200 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401523044 | DN392B LED18/830 PSU D200 AL WP GCG2HE   | 5                    | +/-10%                  |
| 911401526144 | DN394B LED38/865 P29PSU D200 AL GMG2HE   | 5                    | +/-10%                  |
| 911401526244 | DN394B LED38/840 P29PSU D200 AL GMG2HE   | 5                    | +/-10%                  |
| 911401526344 | DN394B LED38/830 P29PSU D200 AL GMG2HE   | 5                    | +/-10%                  |
| 911401526744 | DN394B LED38/865 PSU D200 AL GCG2HE      | 5                    | +/-10%                  |
| 911401526844 | DN394B LED38/840 PSU D200 AL GCG2HE      | 5                    | +/-10%                  |
| 911401526944 | DN394B LED38/830 PSU D200 AL GCG2HE      | 5                    | +/-10%                  |
| 911401527344 | DN393B LED25/865 P19PSU D200 AL GMG2HE   | 5                    | +/-10%                  |
| 911401527444 | DN393B LED25/840 P19PSU D200 AL GMG2HE   | 5                    | +/-10%                  |
| 911401527544 | DN393B LED25/830 P19PSU D200 AL GMG2HE   | 5                    | +/-10%                  |
| 911401527944 | DN393B LED25/865 PSU D200 AL GCG2HE      | 5                    | +/-10%                  |

| Order Code   | Full Product Name                        | Initial chromaticity | Luminous flux tolerance |
|--------------|------------------------------------------|----------------------|-------------------------|
| 911401528044 | DN393B LED25/840 PSU D200 AL GCG2HE      | 5                    | +/-10%                  |
| 911401528144 | DN393B LED25/830 PSU D200 AL GCG2HE      | 5                    | +/-10%                  |
| 911401529744 | DN392B LED18/865 P14PSU D200 AL GMG2HE   | 5                    | +/-10%                  |
| 911401529844 | DN392B LED18/840 P14PSU D200 AL GMG2HE   | 5                    | +/-10%                  |
| 911401529944 | DN392B LED18/830 P14PSU D200 AL GMG2HE   | 5                    | +/-10%                  |
| 911401530344 | DN392B LED18/865 PSU D200 AL GCG2HE      | 5                    | +/-10%                  |
| 911401530444 | DN392B LED18/840 PSU D200 AL GCG2HE      | 5                    | +/-10%                  |
| 911401530544 | DN392B LED18/830 PSU D200 AL GCG2HE      | 5                    | +/-10%                  |
| 911401537044 | DN393X LED25/865 P20WIA D200 AL G2HE     | 5                    | +/-10%                  |
| 911401537644 | DN393X LED25/830 P20WIA D200 AL G2HE     | 5                    | +/-10%                  |
| 911401538244 | DN393X LED25/840 P20WIA D200 AL G2HE     | 5                    | +/-10%                  |
| 911401566844 | DN394B LED38/865 P29PSD D200 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401566944 | DN394B LED38/840 P29PSD D200 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401567044 | DN394B LED38/830 P29PSD D200 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401567144 | DN394B LED38/865 PSD D200 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401567244 | DN394B LED38/840 PSD D200 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401567344 | DN394B LED38/830 PSD D200 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401567444 | DN393B LED25/865 P20PSD D200 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401567544 | DN393B LED25/840 P20PSD D200 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401567644 | DN393B LED25/830 P20PSD D200 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401567744 | DN393B LED25/865 PSD D200 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401567844 | DN393B LED25/840 PSD D200 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401567944 | DN393B LED25/830 PSD D200 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401568644 | DN392B LED18/865 P14PSD D200 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401568744 | DN392B LED18/840 P14PSD D200 ALWP GMG2HE | 5                    | -10% / +10%             |

| Order Code   | Full Product Name                        | Initial chromaticity | Luminous flux tolerance |
|--------------|------------------------------------------|----------------------|-------------------------|
| 911401568844 | DN392B LED18/830 P14PSD D200 ALWP GMG2HE | 5                    | -10% / +10%             |
| 911401568944 | DN392B LED18/865 PSD D200 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401569044 | DN392B LED18/840 PSD D200 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401569144 | DN392B LED18/830 PSD D200 AL WP GCG2HE   | 5                    | -10% / +10%             |
| 911401571344 | DN394B LED38/865 P29PSD D200 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401571444 | DN394B LED38/840 P29PSD D200 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401571544 | DN394B LED38/830 P29PSD D200 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401571944 | DN394B LED38/865 PSD D200 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401572044 | DN394B LED38/840 PSD D200 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401572144 | DN394B LED38/830 PSD D200 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401572544 | DN393B LED25/865 P20PSD D200 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401572644 | DN393B LED25/840 P20PSD D200 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401572744 | DN393B LED25/830 P20PSD D200 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401573144 | DN393B LED25/865 PSD D200 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401573244 | DN393B LED25/840 PSD D200 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401573344 | DN393B LED25/830 PSD D200 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401574944 | DN392B LED18/865 P14PSD D200 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401575044 | DN392B LED18/840 P14PSD D200 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401575144 | DN392B LED18/830 P14PSD D200 AL GMG2HE   | 5                    | -10% / +10%             |
| 911401575544 | DN392B LED18/865 PSD D200 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401575644 | DN392B LED18/840 PSD D200 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401575744 | DN392B LED18/830 PSD D200 AL GCG2HE      | 5                    | -10% / +10%             |
| 911401577042 | DN393X LED22/840 P20L1W D200 WH CAUG2    | 5                    | +/-10%                  |
| 911401577542 | DN392X LED17/840 P15L1W D150 WH CAUG2    | 5                    | +/-10%                  |
| 911401503945 | DN392X LED17/9TNW P15PSD D150 WH WP G2   | SDCM5                | +/-10%                  |

| Order Code   | Full Product Name                        | Initial chromaticity | Luminous flux tolerance |
|--------------|------------------------------------------|----------------------|-------------------------|
| 911401504245 | DN392X LED17/9TNW P15PSD D150 WH WPCAUG2 | SDCM5                | +/-10%                  |
| 911401520044 | DN392B LED20/840 P15PSU D150WHWP CAUG2HE | 5                    | +/-10%                  |
| 911401520144 | DN391B LED13/840 P11PSU D150WHWP CAUG2HE | 5                    | +/-10%                  |
| 911401520444 | DN392B LED20/840 P15PSU D150 WH CAUG2HE  | 5                    | +/-10%                  |
| 911401520544 | DN391B LED13/840 P11PSU D150 WH CAUG2HE  | 5                    | +/-10%                  |
| 911401528844 | DN392B LED22/865 P16PSU D150 WH GMG2HE   | 5                    | +/-10%                  |
| 911401528944 | DN392B LED22/840 P16PSU D150 WH GMG2HE   | 5                    | +/-10%                  |
| 911401529044 | DN392B LED22/830 P16PSU D150 WH GMG2HE   | 5                    | +/-10%                  |
| 911401529444 | DN392B LED22/865 PSU D150 WH GCG2HE      | 5                    | +/-10%                  |
| 911401529544 | DN392B LED22/840 PSU D150 WH GCG2HE      | 5                    | +/-10%                  |
| 911401529644 | DN392B LED22/830 PSU D150 WH GCG2HE      | 5                    | +/-10%                  |
| 911401531244 | DN392B LED20/865 P14PSU D150 WH GMG2HE   | 5                    | +/-10%                  |
| 911401531344 | DN392B LED20/840 P14PSU D150 WH GMG2HE   | 5                    | +/-10%                  |
| 911401531444 | DN392B LED20/830 P14PSU D150 WH GMG2HE   | 5                    | +/-10%                  |
| 911401531844 | DN392B LED20/865 PSU D150 WH GCG2HE      | 5                    | +/-10%                  |
| 911401531944 | DN392B LED20/840 PSU D150 WH GCG2HE      | 5                    | +/-10%                  |
| 911401532044 | DN392B LED20/830 PSU D150 WH GCG2HE      | 5                    | +/-10%                  |
| 911401532444 | DN391B LED13/865 P10PSU D150 WH GMG2HE   | 5                    | +/-10%                  |
| 911401532544 | DN391B LED13/840 P10PSU D150 WH GMG2HE   | 5                    | +/-10%                  |
| 911401532644 | DN391B LED13/830 P10PSU D150 WH GMG2HE   | 5                    | +/-10%                  |
| 911401533044 | DN391B LED13/865 PSU D150 WH GCG2HE      | 5                    | +/-10%                  |
| 911401533144 | DN391B LED13/840 PSU D150 WH GCG2HE      | 5                    | +/-10%                  |
| 911401533244 | DN391B LED13/830 PSU D150 WH GCG2HE      | 5                    | +/-10%                  |
| 911401537344 | DN392X LED20/865 P15WIA D150 WH G2HE     | 5                    | +/-10%                  |
| 911401537944 | DN392X LED20/830 P15WIA D150 WH G2HE     | 5                    | +/-10%                  |

| Order Code   | Full Product Name                      | Initial chromaticity | Luminous flux tolerance |
|--------------|----------------------------------------|----------------------|-------------------------|
| 911401538544 | DN392X LED20/840 P15WIA D150 WH G2HE   | 5                    | +/-10%                  |
| 911401566544 | DN392B LED19/865 P14PSD D150 WH GMG2HE | 5                    | -10% / +10%             |
| 911401566644 | DN392B LED19/840 P14PSD D150 WH GMG2HE | 5                    | -10% / +10%             |
| 911401566744 | DN392B LED19/830 P14PSD D150 WH GMG2HE | 5                    | -10% / +10%             |
| 911401574044 | DN392B LED23/865 P17PSD D150 WH GMG2HE | 5                    | -10% / +10%             |
| 911401574144 | DN392B LED23/840 P17PSD D150 WH GMG2HE | 5                    | -10% / +10%             |
| 911401574244 | DN392B LED23/830 P17PSD D150 WH GMG2HE | 5                    | -10% / +10%             |
| 911401574644 | DN392B LED23/865 PSD D150 WH GCG2HE    | 5                    | -10% / +10%             |
| 911401574744 | DN392B LED23/840 PSD D150 WH GCG2HE    | 5                    | -10% / +10%             |
| 911401574844 | DN392B LED23/830 PSD D150 WH GCG2HE    | 5                    | -10% / +10%             |
| 911401576444 | DN392B LED19/865 PSD D150 WH GCG2HE    | 5                    | -10% / +10%             |
| 911401576544 | DN392B LED19/840 PSD D150 WH GCG2HE    | 5                    | -10% / +10%             |

| Order Code   | Full Product Name                        | Initial chromaticity | Luminous flux tolerance |
|--------------|------------------------------------------|----------------------|-------------------------|
| 911401576644 | DN392B LED19/830 PSD D150 WH GCG2HE      | 5                    | -10% / +10%             |
| 911401577044 | DN391B LED13/865 P11PSD D150 WH GMG2HE   | 5                    | -10% / +10%             |
| 911401577144 | DN391B LED13/840 P11PSD D150 WH GMG2HE   | 5                    | -10% / +10%             |
| 911401577244 | DN391B LED13/830 P11PSD D150 WH GMG2HE   | 5                    | -10% / +10%             |
| 911401577644 | DN391B LED13/865 PSD D150 WH GCG2HE      | 5                    | -10% / +10%             |
| 911401577744 | DN391B LED13/840 PSD D150 WH GCG2HE      | 5                    | -10% / +10%             |
| 911401577844 | DN391B LED13/830 PSD D150 WH GCG2HE      | 5                    | -10% / +10%             |
| 911401585532 | DN391B LED11/840 P11PSU D150 WH CAUG2    | 5                    | +/-10%                  |
| 911401585632 | DN392B LED17/840 P15PSU D150 WH CAUG2    | 5                    | +/-10%                  |
| 911401587832 | DN391B LED11/840 P11PSU D150 WH WP CAUG2 | 5                    | +/-10%                  |
| 911401587932 | DN392B LED17/840 P15PSU D150 WH WP CAUG2 | 5                    | +/-10%                  |

