



More reliable, more professional, the most affordable LED solution for offices.

Essential LED Panel RC035

The Essential LED Panel is the most cost-effective LED solution, offering qualified and reliable lighting in work areas, with an extended life cycle, creating a brighter and healthier office environment.

Benefits

- Slim and elegant design: luminaire height of about 3 cm
- PMMA as "Light Guide" material: excellent anti-yellowing performance over the entire life cycle
- System efficiency of 100 lm/W, energy savings of more than 50% compared to traditional offerings
- Provides comfortable light with excellent uniformity
- Long life of 30 000 hours
- 3 years warranty

Features

- 4000 lm
- 100 lm/W
- 30 000 h L65B50 at 25 °C
- 120-277V, 50/60 Hz
- 4000K, 6500K

Essential LED Panel RC035

Application

- Open offices
- Meeting rooms
- Circulation areas
- Hospitals
- Libraries

Warnings and Safety

- For indoor use only
- The luminaire must not be used or stored in a corrosive environment where hazardous material such as sulfur, chlorine, etc. is present

General Information	
Driver included	Yes
Light source replaceable	No
Light Technical	
Color rendering index (CRI)	≥80
Luminous Efficacy (rated) (Nom)	100 lm/W
Luminous Flux	4,000 lm
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	120 to 277 V
Line Frequency	50 to 60 Hz
Power Consumption	40 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +35 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)
911401897284	RC035B LED40S/840 120-277 W59L59 LA	4000 K
911401897384	RC035B LED40S/865 120-277 W59L59 LA	6500 K
911401897484	RC035B LED40S/840 120-277 W60L60 LA	4000 K
911401897584	RC035B LED40S/865 120-277 W60L60 LA	6500 K

