



Product Description

TL-E 80

Fluorescent lamps with a circular tube having a diameter of 26 mm

优点

- /80 colors have good color rendering and high efficacy compared with standard colors
- Symmetrical, omnidirectional light distribution
- Create atmospheres from warm white to cool daylight

特点

- Available in various color designations

应用

- Suitable for use in a wide range of luminaires for various purposes, including decorative luminaires
- Ideal for 'human' applications such as schools, offices, shops and homes


Versions



TL-E 1CT

TL-E 80

二维绘图



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
22 W G10q Cool daylight Circular fluorescent	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm
22 W G10q Cool white Circular fluorescent	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm

一般信息	
底盖	G10q
标称使用寿命	8,000 小时
灯技术	
显色指数 (CRI)	80
操作和电气	
灯具电流 (标称)	0.400 A
电压 (标称)	62 V
控制和调光	
可调光	是
机械和外壳	
灯泡外形	C-T29
审批和申请	
能耗 kWh/1000 h	24 kWh
汞 (Hg) 含量 (标称)	8 mg

灯技术

Order Code	Full Product Name	颜色名称	相关色温 (标称)	光效 (额定) (标称)	光通量
928026284074	22 W G10q Cool white Circular fluorescent	冷白色 (CW)	4000 K	59 lm/W	1,285 lm
928026286574	22 W G10q Cool daylight Circular fluorescent	冷日光	6500 K	57 lm/W	1,250 lm

操作和电气

Order Code	Full Product Name	功耗	Order Code	Full Product Name	功耗
928026284074	22 W G10q Cool white Circular fluorescent	22 W	928026286574	22 W G10q Cool daylight Circular fluorescent	22.0 W

