



UniEdge - Make Your Boundaries Stand Out

UniEdge

UniEdge is a surface mounted, exterior-rated and compact sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments. Available in white, monochromatic colors, RGB, RGBW and tunable white. Unique spread lens with DMX control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- Unique Optical Distribution 3x90° to highlight the inner frames or outer edges of windows, balconies or doors.
- Compact Size, Light Weight and Tilttable Brackets.
- Through Wiring for power and DMX512 Signal.

Features

- Robust design & IP66 for outdoor applications
- Unique 3x90° optical distribution to illuminate architectural edges
- Drainage design to reduce dirt and water accumulation
- Adjustable -5° to +85° tilting angle
- Through wiring for power and DMX data via IP67 connectors

Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

Warnings and Safety

- For outdoor use only


Versions



UniEdge 3LED

UniEdge 4LED

Dimensional drawing



General Information

Driver included No

Light Technical

Correlated Color Temperature (Nom) -

Mechanical and Housing

Optical cover type Tempered glass

Housing Color Dark gray

Mech. impact protection code IK06

Ingress protection code IP66

Approval and Application

CE mark No

Flammability mark For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Light source color	Color rendering	
			index (CRI)	Luminous Flux
911401737273	BCP390 3LED RGB 24V 3x90 DMX D3	Red, green and blue	-	67 lm
911401737283	BCP390 4LED 27K 24V 3x90 D3	Warm white	80	118 lm
911401737293	BCP390 4LED 27K 24V 3x90 DMX D3	Warm white	80	115 lm
911401737303	BCP390 4LED 30K 24V 3x90 D3	Warm white	80	127 lm
911401737313	BCP390 4LED 30K 24V 3x90 DMX D3	Warm white	80	124 lm
911401737323	BCP390 4LED 40K 24V 3x90 D3	Neutral white	80	144 lm
911401737333	BCP390 4LED 40K 24V 3x90 DMX D3	Neutral white	80	142 lm
911401737343	BCP390 4LED RGBNW 24V 3x90 DMX D3	Red, green, blue and white	-	102 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401737273	BCP390 3LED RGB 24V 3x90 DMX D3	7 W

Order Code	Full Product Name	Power Consumption
911401737283	BCP390 4LED 27K 24V 3x90 D3	10 W

Order Code	Full Product Name	Power Consumption
911401737293	BCP390 4LED 27K 24V 3x90 DMX D3	10 W
911401737303	BCP390 4LED 30K 24V 3x90 D3	10 W
911401737313	BCP390 4LED 30K 24V 3x90 DMX D3	10 W

Order Code	Full Product Name	Power Consumption
911401737323	BCP390 4LED 40K 24V 3x90 D3	10 W
911401737333	BCP390 4LED 40K 24V 3x90 DMX D3	10 W
911401737343	BCP390 4LED RGBNW 24V 3x90 DMX D3	10 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401737273	BCP390 3LED RGB 24V 3x90 DMX D3	Yes
911401737283	BCP390 4LED 27K 24V 3x90 D3	No
911401737293	BCP390 4LED 27K 24V 3x90 DMX D3	Yes
911401737303	BCP390 4LED 30K 24V 3x90 D3	No

Order Code	Full Product Name	Dimmable
911401737313	BCP390 4LED 30K 24V 3x90 DMX D3	Yes
911401737323	BCP390 4LED 40K 24V 3x90 D3	No
911401737333	BCP390 4LED 40K 24V 3x90 DMX D3	Yes
911401737343	BCP390 4LED RGBNW 24V 3x90 DMX D3	Yes

