



TownTune Central Post Top - Extending the home feel onto the street

TownTune Central Post-Top DTC

Designed to enhance existing and scalable urban spaces, the TownTune family offers all the latest lighting innovations in terms of performance, quality of light and connectivity. The family consists of four solutions: a Central Post Top (CPT), an Asymmetric Spigot Post Top / Side Entry version (ASY), a version with an extending Lyre post top bracket (Lyre), and a Central Post Top with a Conical Comfort Bowl (CCB). Each TownTune luminaire can be customized with a choice of different shapes on top of the housing, plus there's the option to add a decorative ring, which comes in two colors (excluding CCB). Design options that enable you to create your very own lighting signature and bring a distinctive identity to districts and cities. In addition, every luminaire in the TownTune family is uniquely identifiable, thanks to the Signify Service tag app. By simply scanning a QR code, placed inside the door of the mast or directly on the luminaire, you can instantly access the configuration of the luminaire. This makes maintenance and programming operations faster and easier and enables you to create your digital library of lighting assets and spare parts. TownTune also uses the LEDGINE-O lighting platform, ensuring you always have the right amount and direction of light on your street. Furthermore, thanks to being system ready (SR), TownTune is also future proof. A solution that's ready to be paired with both standalone and advanced control and lighting software applications such as Interact City.

TownTune Central Post-Top DTC

Benefits

- LEDGINE-O platform for great performance, choice color temperatures and light distributions
- Optimized Total Cost of Ownership (L-Tune for flux tuning, standalone controls e.g., LumiStep, Dynadimmer, CLO (Constant Light output), LineSwitch)
- Ready to pair with advanced systems and software applications e.g., Interact City
- Long lifetime: 100,000 hours @L85 and higher
- Easy access to gear, vandal resistant (IK10), high ingress protection (IP66)

Features

- Simple design for easy integration into urban spaces, wide range of accessories for customization
- Suitable for new and retrofit installations
- Range of lumen packages (1200 to 12000 lm) and CCTs (2200K, 2700K, 3000K, 4000K)
- Dedicated bowl for visual comfort and comfortable lighting experiences
- Service tag for easy installation and maintenance.

Application

- Urban and residential areas
- Cycle paths, footpaths and pedestrian crossings
- City centers and squares
- Car parks

Versions



TownTune CPT DTC BDP262





TownTune CPT DTC DR BDP262



TownTune CPT DTC BDP262

Dimensional drawing



TownTune Central Post-Top DTC

General Information	
Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Upward light output ratio	0
Operating and Electrical	
Surge Protection (Common/Differential)	Standard surge protection level
Controls and Dimming	
Maximum dim level	10%
Mechanical and Housing	
Optical cover type	Polycarbonate bowl/cover UV-resistant
Housing Color	Gray
Mech. impact protection code	IK10
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.5 %
Product Data	
Product family code	BDP262

General Information

Order Code	Full Product Name	Lamp family code
912300024161	BDP262 LED24-4S/740 II DM33 CLO SRTB 62P	LED24
912300024157	BDP262 LED59-4S/830 II DW50 DR CLO LS-6	LED59
912300024450	BDP262 LED79-4S/830 PSU II DS50 62P	LED79
912300024451	BDP262 LED50-4S/830 PSU II DM10 62P	LED50

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
912300024161	BDP262 LED24-4S/740 II DM33 CLO SRTB 62P	4° - 57° x 149°	740 neutral white	4000 K	70
912300024157	BDP262 LED59-4S/830	23° - 8° x 152°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
	II DW50 DR CLO LS-6				
912300024450	BDP262 LED79-4S/830 PSU II DS50 62P	152° x 155°	830 warm white	3000 K	80
912300024451	BDP262 LED50-4S/830	77° - 11° x 156°	830 warm white	3000 K	80

TownTune Central Post-Top DTC

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
	PSU II DM10 62P				

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
912300024161	BDP262 LED24-4S/740 II DM33 CLO SRTB 62P	1,725 lm	-	Distribution medium 33
912300024157	BDP262 LED59-4S/830 II DW50 DR CLO LS-6	3,886 lm	-	Distribution wide 50

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
912300024450	BDP262 LED79-4S/830 PSU II DS50 62P	5,520 lm	40	Distribution symmetrical 50
912300024451	BDP262 LED50-4S/830 PSU II DM10 62P	3,500 lm	20	Distribution medium 10

Operating and Electrical

Order Code	Full Product Name	Power Consumption
912300024161	BDP262 LED24-4S/740 II DM33 CLO SRTB 62P	15 W
912300024157	BDP262 LED59-4S/830 II DW50 DR CLO LS-6	42.5 W

Order Code	Full Product Name	Power Consumption
912300024450	BDP262 LED79-4S/830 PSU II DS50 62P	60 W
912300024451	BDP262 LED50-4S/830 PSU II DM10 62P	40.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
912300024161	BDP262 LED24-4S/740 II DM33 CLO SRTB 62P	Yes
912300024157	BDP262 LED59-4S/830 II DW50 DR CLO LS-6	Yes

Order Code	Full Product Name	Dimmable
912300024450	BDP262 LED79-4S/830 PSU II DS50 62P	No
912300024451	BDP262 LED50-4S/830 PSU II DM10 62P	No

