



The easy way to ledify your road lighting – UniStreet gen2

UniStreet gen2

Designed for large-scale ledification projects, the UniStreet gen2 is the ideal 1:1 luminaire replacement for municipalities. Thanks to its high efficiency and low initial cost, the UniStreet gen2 luminaire enables a fast payback and significant savings in terms of energy consumption within a short period of time. The ease of installation and maintenance is enabled by the Service tag and the SR (System Ready) socket makes it future-ready and you can pair this luminaire with lighting control and software applications such as Interact City. Available with a number of different optics and lumen packages that can even be tuned further to fit exact project requirements, UniStreet gen2 is a true point-to-point replacement solution for conventional light sources. The compact luminaire, using high-quality materials is also easy to dismantle and recycle at the end of its lifetime.

Benefits

- 1 to 1 replacement for conventional luminaires
- Offers high efficiency and energy savings
- Made of high-quality materials for longer lifetime and minimized maintenance

Features

- Good application coverage thanks to wide range of optics, tunable flux and tillable spigot
- Easy luminaire identification due to the Service tag
- Future-ready thanks to the SR (System Ready) socket
- Luminaire is also equipped with dedicated light recipes that help with: 1) maintaining an optimal ecosystems for bats or 2) preserving a dark night sky and reduce light pollution
- Increased shock resistance with optional IK09 glass cover

Application

- Roads and streets
- Residential streets

Versions






UniStreet LumiStreet gen2 Nano



UniStreet LumiStreet gen2 Nano
with Zhaga sockets



Dimensional drawing



Product details

UniStreet LumiStreet gen2 Nano
top side view with Zhaga sockets



UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



UniStreet LumiStreet gen2 Nano
profile view



UniStreet gen2 spigot regulation




UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



UniStreet LumiStreet gen2 Nano
gear compartment



UniStreet_LumiStreet_gen2

UniStreet_LumiStreet_gen2



Product details



UniStreet_LumiStreet_gen2

UniStreet_LumiStreet_gen2



UniStreet LumiStreet gen2 Nano
spigot view

Bottom view for spigot regulation
and screw



UniStreet LumiStreet gen2 Nano
spigot view

UniStreet LumiStreet gen2 Nano
profile view with Zhaga sockets



UniStreet_LumiStreet_gen2

UniStreet LumiStreet gen2 Nano
top view



Product details



UniStreet LumiStreet gen2 Nano
bottom view



UniStreet_LumiStreet_gen2



UniStreet LumiStreet gen2 Nano
bottom view with louvre



UniStreet LumiStreet gen2 Nano
gear compartment



UniStreet LumiStreet gen2 Nano
gear compartment

UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



General Information	
Driver included	Yes
Light source replaceable	Yes
Service tag	Yes
Light Technical	
Upward light output ratio	0
Mechanical and Housing	
Optical cover type	Flat glass
Housing Color	Gray
Ingress protection code	IP66
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

General Information

Order Code	Full Product Name	Lamp family code	Number of gear units
62780200	BGP280 LED50-1F/740 I DM10 48/60S	LED50	1 unit
62783300	BGP280 LED50-1F/740 II DM10 48/60S	LED50	1 unit
44930800	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	LED100	1 unit
44942100	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	LED120	1 unit
44944500	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	LED70	1 unit
05872900	BGP282 LED120-4S/740 I DM11 48/60S	LED120	1 unit
06040100	BGP282 LED59-4S/740 II DM50 D9 48/60S	LED59	1 unit
07943400	BGP282 LED60-4S/740 I DM50 D948/60S	LED60	1 unit
07944100	BGP282 LED120-4S/740 I DM50 D9 48/60S	LED120	1 unit
07958800	BGP282 LED80-4S/740 I DM11 D948/60S	LED80	1 unit
07959500	BGP282 LED90-4S/740 I DM11 D948/60S	LED90	1 unit
07966300	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	LED80	1 unit
07971700	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	LED60	1 unit
07975500	BGP282 LED70-4S/740 I DM50 D948/60S	LED70	1 unit
10006000	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	LED54	1 unit
10017600	BGP282 LED80-4S/740 I DM11 D948/60S	LED80	1 unit
10019000	BGP282 LED70-4S/740 I DN10 48/60S	LED70	1 unit
10029900	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	LED69	1 unit
10035000	BGP282 LED120-4S/740 I DM11 D9 48/60S	LED120	1 unit
10055800	BGP282 LED30-4S/740 I DW10 48/60S	LED30	1 unit
10059600	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	LED70	1 unit
10067100	BGP282 LED70-4S/740 I DM50 D948/60S	LED70	1 unit
10070100	BGP282 LED100-4S/740 I DM50 48/60S	LED100	1 unit
10075600	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	LED64	1 unit
10076300	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	LED74	1 unit
10080000	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	LED100	1 unit
44948300	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	LED149	1 unit
05873600	BGP283 LED240-4S/740 I DM11 48/60S	LED240	1 unit
05885900	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	LED240	1 unit
07946500	BGP283 LED70-4S/740 II DM50 D9 48/60S	LED70	1 unit
07947200	BGP283 LED80-4S/740 II DM50 D9 48/60S	LED80	1 unit
07948900	BGP283 LED90-4S/740 II DM50 D9 48/60S	LED90	1 unit
07949600	BGP283 LED100-4S/740 II DM50 D9 48/60S	LED100	1 unit
07950200	BGP283 LED120-4S/740 II DM50 D9 48/60S	LED120	1 unit
07951900	BGP283 LED139-4S/740 II DM50 D9 48/60S	LED139	1 unit
07952600	BGP283 LED149-4S/740 II DM50 D9 48/60S	LED149	1 unit
07961800	BGP283 LED160-4S/740 I DM11 D9 48/60S	LED160	1 unit
07997700	BGP283 LED149-4S/740 II DM50 D9 48/60S	LED149	1 unit
10010700	BGP283 LED149-4S/740 I DM50 D9 48/60S	LED149	1 unit
10011400	BGP283 LED139-4S/740 I DM50 D9 48/60S	LED139	1 unit
10034300	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	LED139	1 unit
10039800	BGP283 LED200-4S/740 I DX10 ALU 48/60S	LED200	1 unit
10040400	BGP283 LED100-4S/740 I DM50 D9 48/60S	LED100	1 unit
10041100	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	LED100	1 unit
10053400	BGP283 LED120-4S/740 I DM50 D9 48/60S	LED120	1 unit
10071800	BGP283 LED120-4S/740 II DM50 D9 48/60S	LED120	1 unit
62786400	BGP280 LED50-1F/740 I DM10 SRG10 SRT SRB	LED50	1 unit
07936600	BGP284 LED240-4S/740 II DM11 D9 48/60S P	LED240	2 units
07937300	BGP284 LED280-4S/740 II DM11 D9 48/60S P	LED280	2 units
07938000	BGP284 LED340-4S/740 II DM11 D9 48/60S P	LED340	2 units
18172400	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	LED300	2 units

Order Code	Full Product Name	Lamp family code	Number of gear units
44929200	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	LED25	1 unit
44931500	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	LED40	1 unit
44932200	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	LED50	1 unit
44933900	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	LED25	1 unit
44935300	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	LED60	1 unit
44940700	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	LED25	1 unit
44941400	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	LED45	1 unit
44953700	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	LED35	1 unit
44954400	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	LED40	1 unit
05871200	BGP281 LED50-4S/740 I DM11 48/60S	LED50	1 unit
05883500	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	LED50	1 unit
07939700	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	LED16	1 unit
07940300	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	LED20	1 unit
07941000	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	LED25	1 unit
07942700	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	LED54	1 unit
07973100	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	LED40	1 unit
07974800	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	LED40	1 unit
07978600	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	LED20	1 unit
07979300	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	LED45	1 unit
07984700	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	LED45	1 unit
07990800	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	LED30	1 unit
10001500	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	LED60	1 unit
10002200	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	LED54	1 unit
10005300	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	LED20	1 unit
10008400	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	LED35	1 unit
10009100	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	LED50	1 unit
10015200	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	LED40	1 unit
10028200	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	LED20	1 unit
10033600	BGP281 LED45-4S/740 I DN10 48/60S	LED45	1 unit
10047300	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	LED45	1 unit
10049700	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	LED60	1 unit
10050300	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	LED40	1 unit
10079400	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	LED16	1 unit

Light Technical (1/2)

		Luminaire	Light	Correlated	Color
		light beam	source	Color	rendering
Order Code	Full Product Name	spread	color	Temperature (Nom)	index (CRI)
62780200	BGP280	157° - 33° x 55°	740	4000 K	70
	LED50-1F/740 I		neutral		
	DM10 48/60S		white		
62783300	BGP280	157° - 33° x 55°	740	4000 K	70
	LED50-1F/740 II		neutral		
	DM10 48/60S		white		
44930800	BGP282	157° - 33° x 55°	740	4000 K	70
	LED100-4S/740 II		neutral		
	DM10 CLO-DDF2		white		
	D1				
44942100	BGP282	157° - 33° x 55°	740	4000 K	70
	LED120-4S/740 II		neutral		
	DM10 CLO-DDF2		white		
44944500	BGP282	157° - 33° x 55°	740	4000 K	70
	LED70-4S/740 II		neutral		
	DM10 CLO-DDF2		white		
05872900	BGP282	160° - 42° x 54°	740	4000 K	70
	LED120-4S/740 I		neutral		
	DM11 48/60S		white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
06040100	BGP282	154° - 31° x 54°	740	4000 K	70
	LED59-4S/740 II		neutral		
	DM50 D9 48/60S		white		
07943400	BGP282	154° - 31° x 54°	740	4000 K	70
	LED60-4S/740 I		neutral		
	DM50 D948/60S		white		
07944100	BGP282	154° - 31° x 54°	740	4000 K	70
	LED120-4S/740 I		neutral		
	DM50 D9 48/60S		white		
07958800	BGP282	160° - 42° x	740	4000 K	70
	LED80-4S/740 I	54°	neutral		
	DM11 D948/60S		white		
07959500	BGP282	160° - 42° x	740	4000 K	70
	LED90-4S/740 I	54°	neutral		
	DM11 D948/60S		white		
07966300	BGP282	157° - 33° x 55°	740	4000 K	70
	LED80-4S/740 II		neutral		
	DM10 CLO-DDF2 D18		white		
07971700	BGP282	157° - 33° x 55°	740	4000 K	70
	LED60-4S/740 II		neutral		
	DM10 CLO-DDF2 D18		white		
07975500	BGP282	154° - 31° x 54°	740	4000 K	70
	LED70-4S/740 I		neutral		
	DM50 D948/60S		white		
10006000	BGP282	68° x 158°	740	4000 K	70
	LED54-4S/740 I		neutral		
	DN10 DDF2 D18 SRG1		white		
10017600	BGP282	160° - 42° x	740	4000 K	70
	LED80-4S/740 I	54°	neutral		
	DM11 D948/60S		white		
10019000	BGP282	68° x 158°	740	4000 K	70
	LED70-4S/740 I		neutral		
	DN10 48/60S		white		
10029900	BGP282	68° x 158°	830	3000 K	80
	LED69-4S/830 II		warm		
	DN10 DDF2 D18 SRG		white		
10035000	BGP282	160° - 42° x	740	4000 K	70
	LED120-4S/740 I	54°	neutral		
	DM11 D9 48/60S		white		
10055800	BGP282	61° x 150°	740	4000 K	70
	LED30-4S/740 I		neutral		
	DW10 48/60S		white		
10059600	BGP282	160° - 42° x	830	3000 K	80
	LED70-4S/830 II	54°	warm		
			white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
	DM11 SRG10 48/60S				
10067100	BGP282	154° - 31° x 54°	740	4000 K	70
	LED70-4S/740 I		neutral		
	DM50 D948/60S		white		
10070100	BGP282	154° - 31° x 54°	740	4000 K	70
	LED100-4S/740 I		neutral		
	DM50 48/60S		white		
10075600	BGP282	61° x 150°	740	4000 K	70
	LED64-4S/740 I		neutral		
	DW10 DDF2 D18 SRG1		white		
10076300	BGP282	160° - 42° x	830	3000 K	80
	LED74-4S/830 II	54°	warm		
	DM11 DDF2 D18 SRG		white		
10080000	BGP282	160° - 42° x	740	4000 K	70
	LED100-4S/740 I	54°	neutral		
	DM11 DDF3 D18 48/		white		
44948300	BGP283	157° - 33° x 55°	740	4000 K	70
	LED149-4S/740 II		neutral		
	DM10 CLO-DDF2 D1		white		
05873600	BGP283	160° - 42° x	740	4000 K	70
	LED240-4S/740 I	54°	neutral		
	DM11 48/60S		white		
05885900	BGP283	160° - 42° x	740	4000 K	70
	LED240-4S/740 I	54°	neutral		
	DM11 SRT SRB SRG1		white		
07946500	BGP283	154° - 31° x 54°	740	4000 K	70
	LED70-4S/740 II		neutral		
	DM50 D9 48/60S		white		
07947200	BGP283	154° - 31° x 54°	740	4000 K	70
	LED80-4S/740 II		neutral		
	DM50 D9 48/60S		white		
07948900	BGP283	154° - 31° x 54°	740	4000 K	70
	LED90-4S/740 II		neutral		
	DM50 D9 48/60S		white		
07949600	BGP283	154° - 31° x 54°	740	4000 K	70
	LED100-4S/740 II		neutral		
	DM50 D9 48/60S		white		
07950200	BGP283	154° - 31° x 54°	740	4000 K	70
	LED120-4S/740 II		neutral		
	DM50 D9 48/60S		white		
07951900	BGP283	154° - 31° x 54°	740	4000 K	70
	LED139-4S/740 II		neutral		
	DM50 D9 48/60S		white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
07952600	BGP283 LED149-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
07961800	BGP283 LED160-4S/740 I DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
07997700	BGP283 LED149-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
10010700	BGP283 LED149-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
10011400	BGP283 LED139-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
10034300	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	53° x 71°	740 neutral white	4000 K	70
10039800	BGP283 LED200-4S/740 I DX10 ALU 48/60S	150° - 43° x 67°	740 neutral white	4000 K	70
10040400	BGP283 LED100-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
10041100	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	68° x 158°	830 warm white	3000 K	80
10053400	BGP283 LED120-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
10071800	BGP283 LED120-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
62786400	BGP280 LED50-1F/740 I DM10 SRG10 SRT SRB	157° - 33° x 55°	740 neutral white	4000 K	70
07936600	BGP284 LED240-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	4000 K	70
07937300	BGP284 LED280-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	4000 K	70
07938000	BGP284 LED340-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
18172400	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	4000 K	70
44929200	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	4000 K	70
44931500	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	4000 K	70
44932200	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	4000 K	70
44933900	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	68° x 158°	740 neutral white	4000 K	70
44935300	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	4000 K	70
44940700	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	4000 K	70
44941400	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	53° x 71°	740 neutral white	4000 K	70
44953700	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
44954400	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	68° x 158°	740 neutral white	4000 K	70
05871200	BGP281 LED50-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
05883500	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	160° - 42° x 54°	740 neutral white	4000 K	70
07939700	BGP281 LED16-4S/740 I	157° - 33° x 55°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
	DM10 DDF27 D18 48/				
07940300	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	4000 K	70
07941000	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	4000 K	70
07942700	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	4000 K	70
07973100	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	68° x 158°	830 warm white	3000 K	80
07974800	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	160° - 42° x 54°	740 neutral white	4000 K	70
07978600	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	68° x 158°	740 neutral white	4000 K	70
07979300	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	68° x 158°	830 warm white	3000 K	80
07984700	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	68° x 158°	830 warm white	3000 K	80
07990800	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	157° - 33° x 55°	830 warm white	3000 K	80
10001500	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
10002200	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
10005300	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	4000 K	70
10008400	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	4000 K	70
10009100	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	68° x 158°	830 warm white	3000 K	80
10015200	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	160° - 42° x 54°	830 warm white	3000 K	80
10028200	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
10033600	BGP281 LED45-4S/740 I DN10 48/60S	68° x 158°	740 neutral white	4000 K	70
10047300	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	157° - 33° x 55°	740 neutral white	4000 K	70
10049700	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	160° - 42° x 54°	740 neutral white	4000 K	70
10050300	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	4000 K	70
10079400	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	160° - 42° x 54°	740 neutral white	4000 K	70

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
62780200	BGP280 LED50-1F/740 I DM10 48/60S	4,100 lm	Distribution medium 10
62783300	BGP280 LED50-1F/740 II DM10 48/60S	4,100 lm	Distribution medium 10
44930800	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	8,256 lm	Distribution medium 10
44942100	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	9,890 lm	Distribution medium 10
44944500	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	5,916 lm	Distribution medium 10
05872900	BGP282 LED120-4S/740 I DM11 48/60S	10,200 lm	Distribution medium 11
06040100	BGP282 LED59-4S/740 II DM50 D9 48/60S	5,220 lm	Distribution medium 50
07943400	BGP282 LED60-4S/740 I DM50 D948/60S	5,220 lm	Distribution medium 50
07944100	BGP282 LED120-4S/740 I DM50 D9 48/60S	10,200 lm	Distribution medium 50
07958800	BGP282 LED80-4S/740 I DM11 D948/60S	6,960 lm	Distribution medium 11
07959500	BGP282 LED90-4S/740 I DM11 D948/60S	7,740 lm	Distribution medium 11
07966300	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	6,612 lm	Distribution medium 10
07971700	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	5,046 lm	Distribution medium 10
07975500	BGP282 LED70-4S/740 I DM50 D948/60S	6,090 lm	Distribution medium 50
10006000	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	4,698 lm	Distribution narrow 10
10017600	BGP282 LED80-4S/740 I DM11 D948/60S	6,960 lm	Distribution medium 11
10019000	BGP282 LED70-4S/740 I DN10 48/60S	6,090 lm	Distribution narrow 10
10029900	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	6,090 lm	Distribution narrow 10
10035000	BGP282 LED120-4S/740 I DM11 D9 48/60S	10,200 lm	Distribution medium 11
10055800	BGP282 LED30-4S/740 I DW10 48/60S	2,640 lm	Distribution wide 10
10059600	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	6,090 lm	Distribution medium 11
10067100	BGP282 LED70-4S/740 I DM50 D948/60S	6,090 lm	Distribution medium 50
10070100	BGP282 LED100-4S/740 I DM50 48/60S	8,600 lm	Distribution medium 50
10075600	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	5,568 lm	Distribution wide 10
10076300	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	6,364 lm	Distribution medium 11
10080000	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	8,600 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
44948300	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	12,470 lm	Distribution medium 10
05873600	BGP283 LED240-4S/740 I DM11 48/60S	20,160 lm	Distribution medium 11
05885900	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	20,160 lm	Distribution medium 11
07946500	BGP283 LED70-4S/740 II DM50 D9 48/60S	6,160 lm	Distribution medium 50
07947200	BGP283 LED80-4S/740 II DM50 D9 48/60S	7,040 lm	Distribution medium 50
07948900	BGP283 LED90-4S/740 II DM50 D9 48/60S	7,920 lm	Distribution medium 50
07949600	BGP283 LED100-4S/740 II DM50 D9 48/60S	8,800 lm	Distribution medium 50
07950200	BGP283 LED120-4S/740 II DM50 D9 48/60S	10,440 lm	Distribution medium 50
07951900	BGP283 LED139-4S/740 II DM50 D9 48/60S	12,180 lm	Distribution medium 50
07952600	BGP283 LED149-4S/740 II DM50 D9 48/60S	12,900 lm	Distribution medium 50
07961800	BGP283 LED160-4S/740 I DM11 D9 48/60S	13,760 lm	Distribution medium 11
07997700	BGP283 LED149-4S/740 II DM50 D9 48/60S	12,900 lm	Distribution medium 50
10010700	BGP283 LED149-4S/740 I DM50 D9 48/60S	12,900 lm	Distribution medium 50
10011400	BGP283 LED139-4S/740 I DM50 D9 48/60S	12,180 lm	Distribution medium 50
10034300	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	12,180 lm	Distribution medium 12
10039800	BGP283 LED200-4S/740 I DX10 ALU 48/60S	17,000 lm	Distribution extra wide 10
10040400	BGP283 LED100-4S/740 I DM50 D9 48/60S	8,800 lm	Distribution medium 50
10041100	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	8,700 lm	Distribution narrow 10
10053400	BGP283 LED120-4S/740 I DM50 D9 48/60S	10,440 lm	Distribution medium 50
10071800	BGP283 LED120-4S/740 II DM50 D9 48/60S	10,440 lm	Distribution medium 50
62786400	BGP280 LED50-1F/740 I DM10 SRG10 SRT SRB	4,100 lm	Distribution medium 10
07936600	BGP284 LED240-4S/740 II DM11 D9 48/60S P	20,880 lm	Distribution medium 11
07937300	BGP284 LED280-4S/740 II DM11 D9 48/60S P	24,080 lm	Distribution medium 11
07938000	BGP284 LED340-4S/740 II DM11 D9 48/60S P	29,240 lm	Distribution medium 11
18172400	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	24,940 lm	Distribution medium 11
44929200	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	2,200 lm	Distribution narrow 10

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
44931500	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	3,432 lm	Distribution medium 10
44932200	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	4,263 lm	Distribution medium 10
44933900	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	2,200 lm	Distribution narrow 10
44935300	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	5,046 lm	Distribution medium 10
44940700	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	2,200 lm	Distribution narrow 10
44941400	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	3,960 lm	Distribution medium 12
44953700	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	3,080 lm	Distribution medium 11
44954400	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	3,520 lm	Distribution narrow 10
05871200	BGP281 LED50-4S/740 I DM11 48/60S	4,350 lm	Distribution medium 11
05883500	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	4,350 lm	Distribution medium 11
07939700	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	1,424 lm	Distribution medium 10
07940300	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	1,760 lm	Distribution medium 10
07941000	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	2,200 lm	Distribution medium 10
07942700	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	4,698 lm	Distribution medium 10
07973100	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	3,520 lm	Distribution narrow 10
07974800	BGP281 LED40-4S/740 I DM11 CLO- DDF2 D184	3,432 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
07978600	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	1,760 lm	Distribution narrow 10
07979300	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	3,915 lm	Distribution narrow 10
07984700	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	3,915 lm	Distribution narrow 10
07990800	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	2,640 lm	Distribution medium 10
10001500	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	5,220 lm	Distribution medium 11
10002200	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	4,698 lm	Distribution narrow 10
10005300	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	1,716 lm	Distribution medium 10
10008400	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	3,080 lm	Distribution narrow 10
10009100	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	4,350 lm	Distribution narrow 10
10015200	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	3,520 lm	Distribution medium 11
10028200	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	1,716 lm	Distribution medium 11
10033600	BGP281 LED45-4S/740 I DN10 48/60S	3,960 lm	Distribution narrow 10
10047300	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	3,960 lm	Distribution medium 10
10049700	BGP281 LED60-4S/740 I DM11 CLO- DDF2 D184	5,046 lm	Distribution medium 11
10050300	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	3,520 lm	Distribution narrow 10
10079400	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	1,424 lm	Distribution medium 11

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/ Differential)
62780200	BGP280 LED50-1F/740 I DM10 48/60S	31 W	Surge protection level until 6 kV differential mode and 8 kV common mode
62783300	BGP280 LED50-1F/740 II DM10 48/60S	31 W	Surge protection level until 6 kV differential mode and 8 kV common mode
44930800	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
44942100	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	70 W	Surge protection level until 6 kV differential mode and 8 kV common mode
44944500	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	40.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/ Differential)
05872900	BGP282 LED120-4S/740 I DM11 48/60S	70 W	Surge protection level until 6 kV differential mode and 8 kV common mode
06040100	BGP282 LED59-4S/740 II DM50 D9 48/60S	36 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07943400	BGP282 LED60-4S/740 I DM50 D948/60S	36.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07944100	BGP282 LED120-4S/740 I DM50 D9 48/60S	70 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07958800	BGP282 LED80-4S/740 I DM11 D948/60S	47 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
07959500	BGP282 LED90-4S/740 I DM11 D948/60S	54 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07966300	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	46.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07971700	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	36.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07975500	BGP282 LED70-4S/740 I DM50 D948/60S	40.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10006000	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	32.5 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10017600	BGP282 LED80-4S/740 I DM11 D948/60S	47 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10019000	BGP282 LED70-4S/740 I DN10 48/60S	40.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10029900	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	48.5 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10035000	BGP282 LED120-4S/740 I DM11 D9 48/60S	70 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10055800	BGP282 LED30-4S/740 I DW10 48/60S	17.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10059600	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	49 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10067100	BGP282 LED70-4S/740 I DM50 D948/60S	40.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10070100	BGP282 LED100-4S/740 I DM50 48/60S	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10075600	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	37 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10076300	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	52 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10080000	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
44948300	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	84 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
05873600	BGP283 LED240-4S/740 I DM11 48/60S	138 W	Surge protection level until 6 kV differential mode and 8 kV common mode
05885900	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	138 W	Surge protection level until 10 kV differential mode and 10 kV common mode
07946500	BGP283 LED70-4S/740 II DM50 D9 48/60S	38.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07947200	BGP283 LED80-4S/740 II DM50 D9 48/60S	44 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07948900	BGP283 LED90-4S/740 II DM50 D9 48/60S	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07949600	BGP283 LED100-4S/740 II DM50 D9 48/60S	55 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07950200	BGP283 LED120-4S/740 II DM50 D9 48/60S	67 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07951900	BGP283 LED139-4S/740 II DM50 D9 48/60S	78 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07952600	BGP283 LED149-4S/740 II DM50 D9 48/60S	84 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07961800	BGP283 LED160-4S/740 I DM11 D9 48/60S	91 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07997700	BGP283 LED149-4S/740 II DM50 D9 48/60S	84 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10010700	BGP283 LED149-4S/740 I DM50 D9 48/60S	84 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10011400	BGP283 LED139-4S/740 I DM50 D9 48/60S	78 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10034300	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	78 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10039800	BGP283 LED200-4S/740 I DX10 ALU 48/60S	112 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10040400	BGP283 LED100-4S/740 I DM50 D9 48/60S	55 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10041100	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	66 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
10053400	BGP283 LED120-4S/740 I DM50 D9 48/60S	67 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10071800	BGP283 LED120-4S/740 II DM50 D9 48/60S	67 W	Surge protection level until 6 kV differential mode and 8 kV common mode
62786400	BGP280 LED50-1F/740 I DM10 SRG10 SRT SRB	31.5 W	Surge protection level until 10 kV differential mode and 10 kV common mode
07936600	BGP284 LED240-4S/740 II DM11 D9 48/60S P	134 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07937300	BGP284 LED280-4S/740 II DM11 D9 48/60S P	158 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07938000	BGP284 LED340-4S/740 II DM11 D9 48/60S P	186 W	Surge protection level until 6 kV differential mode and 8 kV common mode
18172400	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	168 W	Standard surge protection level
44929200	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	15.8 W	Surge protection level until 10 kV differential mode and 10 kV common mode
44931500	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	23.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
44932200	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	30 W	Surge protection level until 6 kV differential mode and 8 kV common mode
44933900	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	15.8 W	Surge protection level until 10 kV differential mode and 10 kV common mode
44935300	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	36.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
44940700	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	15.8 W	Surge protection level until 10 kV differential mode and 10 kV common mode
44941400	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	27 W	Surge protection level until 10 kV differential mode and 10 kV common mode
44953700	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	22.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
44954400	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	23.5 W	Surge protection level until 10 kV differential mode and 10 kV common mode
05871200	BGP281 LED50-4S/740 I DM11 48/60S	30 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
05883500	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	30 W	Surge protection level until 10 kV differential mode and 10 kV common mode
07939700	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	10.6 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07940300	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	13.6 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07941000	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	15.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07942700	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	32.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07973100	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	28.5 W	Surge protection level until 10 kV differential mode and 10 kV common mode
07974800	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	23.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
07978600	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	13.6 W	Surge protection level until 10 kV differential mode and 10 kV common mode
07979300	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	32 W	Surge protection level until 10 kV differential mode and 10 kV common mode
07984700	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	32 W	Surge protection level until 10 kV differential mode and 10 kV common mode
07990800	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	21 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10001500	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	36.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10002200	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	32.5 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10005300	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	13.6 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10008400	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	22.5 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10009100	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	36 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10015200	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	28.5 W	Surge protection level until 10 kV differential mode and 10 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
10028200	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	13.6 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10033600	BGP281 LED45-4S/740 I DN10 48/60S	27 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10047300	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	27 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
10049700	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	36.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
10050300	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	23.5 W	Surge protection level until 10 kV differential mode and 10 kV common mode
10079400	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	10.6 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
62780200	BGP280 LED50-1F/740 I DM10 48/60S	No	0% (digital)
62783300	BGP280 LED50-1F/740 II DM10 48/60S	No	0% (digital)
44930800	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	Yes	0% (digital)
44942100	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	Yes	0% (digital)
44944500	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	Yes	0% (digital)
05872900	BGP282 LED120-4S/740 I DM11 48/60S	No	0% (digital)
06040100	BGP282 LED59-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
07943400	BGP282 LED60-4S/740 I DM50 D948/60S	Yes	0% (digital)
07944100	BGP282 LED120-4S/740 I DM50 D9 48/60S	Yes	0% (digital)
07958800	BGP282 LED80-4S/740 I DM11 D948/60S	Yes	0% (digital)
07959500	BGP282 LED90-4S/740 I DM11 D948/60S	Yes	0% (digital)
07966300	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	Yes	0% (digital)
07971700	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	Yes	0% (digital)
07975500	BGP282 LED70-4S/740 I DM50 D948/60S	Yes	0% (digital)
10006000	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	Yes	0% (digital)
10017600	BGP282 LED80-4S/740 I DM11 D948/60S	Yes	0% (digital)
10019000	BGP282 LED70-4S/740 I DN10 48/60S	No	0% (digital)
10029900	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	Yes	0% (digital)
10035000	BGP282 LED120-4S/740 I DM11 D9 48/60S	Yes	0% (digital)
10055800	BGP282 LED30-4S/740 I DW10 48/60S	No	0% (digital)
10059600	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	No	0% (digital)
10067100	BGP282 LED70-4S/740 I DM50 D948/60S	Yes	0% (digital)
10070100	BGP282 LED100-4S/740 I DM50 48/60S	No	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
10075600	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	Yes	0% (digital)
10076300	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	Yes	0% (digital)
10080000	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	Yes	0% (digital)
44948300	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	Yes	0% (digital)
05873600	BGP283 LED240-4S/740 I DM11 48/60S	No	0% (digital)
05885900	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	No	0% (digital)
07946500	BGP283 LED70-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
07947200	BGP283 LED80-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
07948900	BGP283 LED90-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
07949600	BGP283 LED100-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
07950200	BGP283 LED120-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
07951900	BGP283 LED139-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
07952600	BGP283 LED149-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
07961800	BGP283 LED160-4S/740 I DM11 D9 48/60S	Yes	0% (digital)
07997700	BGP283 LED149-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
10010700	BGP283 LED149-4S/740 I DM50 D9 48/60S	Yes	0% (digital)
10011400	BGP283 LED139-4S/740 I DM50 D9 48/60S	Yes	0% (digital)
10034300	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	Yes	0% (digital)
10039800	BGP283 LED200-4S/740 I DX10 ALU 48/60S	No	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
10040400	BGP283 LED100-4S/740 I DM50 D9 48/60S	Yes	0% (digital)
10041100	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	Yes	0% (digital)
10053400	BGP283 LED120-4S/740 I DM50 D9 48/60S	Yes	0% (digital)
10071800	BGP283 LED120-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
62786400	BGP280 LED50-1F/740 I DM10 SRG10 SRT SRB	No	0% (digital)
07936600	BGP284 LED240-4S/740 II DM11 D9 48/60S P	Yes	0% (digital)
07937300	BGP284 LED280-4S/740 II DM11 D9 48/60S P	Yes	0% (digital)
07938000	BGP284 LED340-4S/740 II DM11 D9 48/60S P	Yes	0% (digital)
18172400	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	Yes	Programmable
44929200	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Yes	0% (digital)
44931500	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	Yes	0% (digital)
44932200	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	Yes	0% (digital)
44933900	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	No	0% (digital)
44935300	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	Yes	0% (digital)
44940700	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Yes	0% (digital)
44941400	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	Yes	0% (digital)
44953700	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	Yes	0% (digital)
44954400	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	Yes	0% (digital)
05871200	BGP281 LED50-4S/740 I DM11 48/60S	No	0% (digital)
05883500	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	No	0% (digital)
07939700	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	Yes	0% (digital)

Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code
62780200	BGP280 LED50-1F/740 I DM10 48/60S	IK08
62783300	BGP280 LED50-1F/740 II DM10 48/60S	IK08
44930800	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	IK09
44942100	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	IK09
44944500	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	IK09
05872900	BGP282 LED120-4S/740 I DM11 48/60S	IK09

Order Code	Full Product Name	Dimmable	Maximum dim level
07940300	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	Yes	0% (digital)
07941000	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	Yes	0% (digital)
07942700	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	Yes	0% (digital)
07973100	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	Yes	0% (digital)
07974800	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	Yes	0% (digital)
07978600	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	No	0% (digital)
07979300	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Yes	0% (digital)
07984700	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Yes	0% (digital)
07990800	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	Yes	0% (digital)
10001500	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	Yes	0% (digital)
10002200	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	Yes	0% (digital)
10005300	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	Yes	0% (digital)
10008400	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	Yes	0% (digital)
10009100	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	Yes	0% (digital)
10015200	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	Yes	0% (digital)
10028200	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	Yes	0% (digital)
10033600	BGP281 LED45-4S/740 I DN10 48/60S	No	0% (digital)
10047300	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	Yes	0% (digital)
10049700	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	Yes	0% (digital)
10050300	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	Yes	0% (digital)
10079400	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	Yes	0% (digital)

Order Code	Full Product Name	Mech. impact protection code
06040100	BGP282 LED59-4S/740 II DM50 D9 48/60S	IK09
07943400	BGP282 LED60-4S/740 I DM50 D948/60S	IK09
07944100	BGP282 LED120-4S/740 I DM50 D9 48/60S	IK09
07958800	BGP282 LED80-4S/740 I DM11 D948/60S	IK09
07959500	BGP282 LED90-4S/740 I DM11 D948/60S	IK09
07966300	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	IK09

Order Code	Full Product Name	Mech. impact protection code
07971700	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	IK09
07975500	BGP282 LED70-4S/740 I DM50 D948/60S	IK09
10006000	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	IK09
10017600	BGP282 LED80-4S/740 I DM11 D948/60S	IK09
10019000	BGP282 LED70-4S/740 I DN10 48/60S	IK09
10029900	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	IK09
10035000	BGP282 LED120-4S/740 I DM11 D9 48/60S	IK09
10055800	BGP282 LED30-4S/740 I DW10 48/60S	IK09
10059600	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	IK09
10067100	BGP282 LED70-4S/740 I DM50 D948/60S	IK09
10070100	BGP282 LED100-4S/740 I DM50 48/60S	IK09
10075600	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	IK09
10076300	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	IK09
10080000	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	IK09
44948300	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	IK09
05873600	BGP283 LED240-4S/740 I DM11 48/60S	IK09
05885900	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	IK09
07946500	BGP283 LED70-4S/740 II DM50 D9 48/60S	IK09
07947200	BGP283 LED80-4S/740 II DM50 D9 48/60S	IK09
07948900	BGP283 LED90-4S/740 II DM50 D9 48/60S	IK09
07949600	BGP283 LED100-4S/740 II DM50 D9 48/60S	IK09
07950200	BGP283 LED120-4S/740 II DM50 D9 48/60S	IK09
07951900	BGP283 LED139-4S/740 II DM50 D9 48/60S	IK09
07952600	BGP283 LED149-4S/740 II DM50 D9 48/60S	IK09
07961800	BGP283 LED160-4S/740 I DM11 D9 48/60S	IK09
07997700	BGP283 LED149-4S/740 II DM50 D9 48/60S	IK09
10010700	BGP283 LED149-4S/740 I DM50 D9 48/60S	IK09
10011400	BGP283 LED139-4S/740 I DM50 D9 48/60S	IK09
10034300	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	IK09
10039800	BGP283 LED200-4S/740 I DX10 ALU 48/60S	IK09
10040400	BGP283 LED100-4S/740 I DM50 D9 48/60S	IK09
10041100	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	IK09
10053400	BGP283 LED120-4S/740 I DM50 D9 48/60S	IK09
10071800	BGP283 LED120-4S/740 II DM50 D9 48/60S	IK09
62786400	BGP280 LED50-1F/740 I DM10 SRG10 SRT SRB	IK08
07936600	BGP284 LED240-4S/740 II DM11 D9 48/60S P	IK09

Order Code	Full Product Name	Mech. impact protection code
07937300	BGP284 LED280-4S/740 II DM11 D9 48/60S P	IK09
07938000	BGP284 LED340-4S/740 II DM11 D9 48/60S P	IK09
18172400	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	IK09
44929200	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	IK09
44931500	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	IK09
44932200	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	IK09
44933900	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	IK09
44935300	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	IK09
44940700	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	IK09
44941400	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	IK09
44953700	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	IK09
44954400	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	IK09
05871200	BGP281 LED50-4S/740 I DM11 48/60S	IK09
05883500	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	IK09
07939700	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	IK09
07940300	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	IK09
07941000	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	IK09
07942700	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	IK09
07973100	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	IK09
07974800	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	IK09
07978600	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	IK09
07979300	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	IK09
07984700	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	IK09
07990800	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	IK09
10001500	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	IK09
10002200	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	IK09
10005300	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	IK09
10008400	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	IK09
10009100	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	IK09
10015200	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	IK09
10028200	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	IK09
10033600	BGP281 LED45-4S/740 I DN10 48/60S	IK09
10047300	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	IK09
10049700	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	IK09
10050300	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	IK09
10079400	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	IK09

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
62780200	BGP280 LED50-1F/740 I DM10 48/60S	-
62783300	BGP280 LED50-1F/740 II DM10 48/60S	-
44930800	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	0.5 %
44942100	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	0.5 %
44944500	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	0.5 %
05872900	BGP282 LED120-4S/740 I DM11 48/60S	0.5 %
06040100	BGP282 LED59-4S/740 II DM50 D9 48/60S	0.5 %
07943400	BGP282 LED60-4S/740 I DM50 D948/60S	0.5 %
07944100	BGP282 LED120-4S/740 I DM50 D9 48/60S	0.5 %
07958800	BGP282 LED80-4S/740 I DM11 D948/60S	-

Order Code	Full Product Name	Driver failure rate at 5000 h
07959500	BGP282 LED90-4S/740 I DM11 D948/60S	-
07966300	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	0.5 %
07971700	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	0.5 %
07975500	BGP282 LED70-4S/740 I DM50 D948/60S	0.5 %
10006000	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	0.5 %
10017600	BGP282 LED80-4S/740 I DM11 D948/60S	0.5 %
10019000	BGP282 LED70-4S/740 I DN10 48/60S	0.5 %
10029900	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	0.5 %
10035000	BGP282 LED120-4S/740 I DM11 D9 48/60S	0.5 %
10055800	BGP282 LED30-4S/740 I DW10 48/60S	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
10059600	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	0.5 %
10067100	BGP282 LED70-4S/740 I DM50 D948/60S	0.5 %
10070100	BGP282 LED100-4S/740 I DM50 48/60S	0.5 %
10075600	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	0.5 %
10076300	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	0.5 %
10080000	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	0.5 %
44948300	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	0.5 %
05873600	BGP283 LED240-4S/740 I DM11 48/60S	0.5 %
05885900	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	0.5 %
07946500	BGP283 LED70-4S/740 II DM50 D9 48/60S	0.5 %
07947200	BGP283 LED80-4S/740 II DM50 D9 48/60S	0.5 %
07948900	BGP283 LED90-4S/740 II DM50 D9 48/60S	0.5 %
07949600	BGP283 LED100-4S/740 II DM50 D9 48/60S	0.5 %
07950200	BGP283 LED120-4S/740 II DM50 D9 48/60S	0.5 %
07951900	BGP283 LED139-4S/740 II DM50 D9 48/60S	0.5 %
07952600	BGP283 LED149-4S/740 II DM50 D9 48/60S	0.5 %
07961800	BGP283 LED160-4S/740 I DM11 D9 48/60S	-
07997700	BGP283 LED149-4S/740 II DM50 D9 48/60S	0.5 %
10010700	BGP283 LED149-4S/740 I DM50 D9 48/60S	0.5 %
10011400	BGP283 LED139-4S/740 I DM50 D9 48/60S	0.5 %
10034300	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	0.5 %
10039800	BGP283 LED200-4S/740 I DX10 ALU 48/60S	0.5 %
10040400	BGP283 LED100-4S/740 I DM50 D9 48/60S	0.5 %
10041100	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	0.5 %
10053400	BGP283 LED120-4S/740 I DM50 D9 48/60S	0.5 %
10071800	BGP283 LED120-4S/740 II DM50 D9 48/60S	0.5 %
62786400	BGP280 LED50-1F/740 I DM10 SRG10 SRT SRB	-
07936600	BGP284 LED240-4S/740 II DM11 D9 48/60S P	-
07937300	BGP284 LED280-4S/740 II DM11 D9 48/60S P	-
07938000	BGP284 LED340-4S/740 II DM11 D9 48/60S P	-
18172400	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	-
44929200	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
44931500	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	0.5 %
44932200	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	0.5 %
44933900	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	0.5 %
44935300	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	0.5 %
44940700	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	0.5 %
44941400	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	0.5 %
44953700	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	0.5 %
44954400	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	0.5 %
05871200	BGP281 LED50-4S/740 I DM11 48/60S	0.5 %
05883500	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	0.5 %
07939700	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	0.5 %
07940300	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	0.5 %
07941000	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	0.5 %
07942700	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	0.5 %
07973100	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	0.5 %
07974800	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	0.5 %
07978600	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	0.5 %
07979300	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	0.5 %
07984700	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	0.5 %
07990800	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	0.5 %
10001500	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	0.5 %
10002200	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	0.5 %
10005300	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	0.5 %
10008400	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	0.5 %
10009100	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	0.5 %
10015200	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	0.5 %
10028200	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	0.5 %
10033600	BGP281 LED45-4S/740 I DN10 48/60S	0.5 %
10047300	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	0.5 %
10049700	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	0.5 %
10050300	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	0.5 %
10079400	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	0.5 %

Product Data


Order Code	Full Product Name	Product family code
62780200	BGP280 LED50-1F/740 I DM10 48/60S	BGP280
62783300	BGP280 LED50-1F/740 II DM10 48/60S	BGP280
44930800	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	BGP282
44942100	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	BGP282
44944500	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	BGP282
05872900	BGP282 LED120-4S/740 I DM11 48/60S	BGP282
06040100	BGP282 LED59-4S/740 II DM50 D9 48/60S	BGP282
07943400	BGP282 LED60-4S/740 I DM50 D948/60S	BGP282
07944100	BGP282 LED120-4S/740 I DM50 D9 48/60S	BGP282
07958800	BGP282 LED80-4S/740 I DM11 D948/60S	BGP282
07959500	BGP282 LED90-4S/740 I DM11 D948/60S	BGP282
07966300	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	BGP282
07971700	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	BGP282
07975500	BGP282 LED70-4S/740 I DM50 D948/60S	BGP282
10006000	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	BGP282

Order Code	Full Product Name	Product family code
10017600	BGP282 LED80-4S/740 I DM11 D948/60S	BGP282
10019000	BGP282 LED70-4S/740 I DN10 48/60S	BGP282
10029900	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	BGP282
10035000	BGP282 LED120-4S/740 I DM11 D9 48/60S	BGP282
10055800	BGP282 LED30-4S/740 I DW10 48/60S	BGP282
10059600	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	BGP282
10067100	BGP282 LED70-4S/740 I DM50 D948/60S	BGP282
10070100	BGP282 LED100-4S/740 I DM50 48/60S	BGP282
10075600	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	BGP282
10076300	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	BGP282
10080000	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	BGP282
44948300	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	BGP283
05873600	BGP283 LED240-4S/740 I DM11 48/60S	BGP283
05885900	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	BGP283
07946500	BGP283 LED70-4S/740 II DM50 D9 48/60S	BGP283


Order Code	Full Product Name	Product family code
07947200	BGP283 LED80-4S/740 II DM50 D9 48/60S	BGP283
07948900	BGP283 LED90-4S/740 II DM50 D9 48/60S	BGP283
07949600	BGP283 LED100-4S/740 II DM50 D9 48/60S	BGP283
07950200	BGP283 LED120-4S/740 II DM50 D9 48/60S	BGP283
07951900	BGP283 LED139-4S/740 II DM50 D9 48/60S	BGP283
07952600	BGP283 LED149-4S/740 II DM50 D9 48/60S	BGP283
07961800	BGP283 LED160-4S/740 I DM11 D9 48/60S	BGP283
07997700	BGP283 LED149-4S/740 II DM50 D9 48/60S	BGP283
10010700	BGP283 LED149-4S/740 I DM50 D9 48/60S	BGP283
10011400	BGP283 LED139-4S/740 I DM50 D9 48/60S	BGP283
10034300	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	BGP283
10039800	BGP283 LED200-4S/740 I DX10 ALU 48/60S	BGP283
10040400	BGP283 LED100-4S/740 I DM50 D9 48/60S	BGP283
10041100	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	BGP283
10053400	BGP283 LED120-4S/740 I DM50 D9 48/60S	BGP283
10071800	BGP283 LED120-4S/740 II DM50 D9 48/60S	BGP283
62786400	BGP280 LED50-1F/740 I DM10 SRG10 SRT SRB	BGP280
07936600	BGP284 LED240-4S/740 II DM11 D9 48/60S P	BGP284
07937300	BGP284 LED280-4S/740 II DM11 D9 48/60S P	BGP284
07938000	BGP284 LED340-4S/740 II DM11 D9 48/60S P	BGP284
18172400	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	BGP294
44929200	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	BGP281
44931500	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	BGP281
44932200	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	BGP281
44933900	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	BGP281
44935300	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	BGP281
44940700	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	BGP281

Order Code	Full Product Name	Product family code
44941400	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	BGP281
44953700	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	BGP281
44954400	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	BGP281
05871200	BGP281 LED50-4S/740 I DM11 48/60S	BGP281
05883500	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	BGP281
07939700	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	BGP281
07940300	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	BGP281
07941000	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	BGP281
07942700	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	BGP281
07973100	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	BGP281
07974800	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	BGP281
07978600	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	BGP281
07979300	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	BGP281
07984700	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	BGP281
07990800	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	BGP281
10001500	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	BGP281
10002200	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	BGP281
10005300	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	BGP281
10008400	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	BGP281
10009100	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	BGP281
10015200	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	BGP281
10028200	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	BGP281
10033600	BGP281 LED45-4S/740 I DN10 48/60S	BGP281
10047300	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	BGP281
10049700	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	BGP281
10050300	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	BGP281
10079400	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	BGP281


Polar Wide Diagrams



Polar Normal (separate) - BGP281I - 910925865663




Polar Normal (separate) - BGP282I - 910925865664




Polar Normal (separate) - BGP281I - 910925865687


Polar Wide Diagrams




Polar Normal (separate) - BGP281I - 910925865688




Polar Normal (separate) - BGP282I - 910925866439




Polar Normal (separate) - BGP281I - 910925866740




Polar Normal (separate) - BGP282I - 910925866701




Polar Normal (separate) - BGP281I - 910925866744




Polar Normal (separate) - BGP282I - 910925866609



Polar Normal (separate) - BGP284I - 910925866670




Polar Normal (separate) - BGP281I - 910925866675




Polar Normal (separate) - BGP283I - 910925866680


Polar Wide Diagrams




Polar Normal (separate) - BGP281I - 910925866708




Polar Normal (separate) - BGP283I - 910925866685




Polar Normal (separate) - BGP281I - 910925866714




Polar Normal (separate) - BGP283I - 910925866745




Polar Normal (separate) - BGP282I - 910925866790




Polar Normal (separate) - BGP282I - 910925866812



Polar Normal (separate) - BGP280I - 910925868726




Polar Normal (separate) - BGP281I - 910925865669




Polar Normal (separate) - BGP282I - 910925865676


Polar Wide Diagrams




Polar Normal (separate) - BGP281I - 910925865665




Polar Normal (separate) - BGP283I - 910925865682




Polar Normal (separate) - BGP281I - 910925865675




Polar Normal (separate) - BGP281I - 910925865666




Polar Normal (separate) - BGP282I - 910925865678




Polar Normal (separate) - BGP283I - 910925866452



Polar Normal (separate) - BGP284I - 910925866672




Polar Normal (separate) - BGP281I - 910925866438




Polar Normal (separate) - BGP281I - 910925866676


Polar Wide Diagrams




Polar Normal (separate) - BGP281I - 910925866673




Polar Normal (separate) - BGP283I - 910925866684




Polar Normal (separate) - BGP283I - 910925866682




Polar Normal (separate) - BGP281I - 910925866736




Polar Normal (separate) - BGP284I - 910925866671




Polar Normal (separate) - BGP282I - 910925866678



Polar Normal (separate) - BGP282I - 910925866710




Polar Normal (separate) - BGP282I - 910925866752




Polar Normal (separate) - BGP282I - 910925866764


Polar Wide Diagrams




Polar Normal (separate) - BGP283I - 910925866683




Polar Normal (separate) - BGP281I - 910925866709




Polar Normal (separate) - BGP281I - 910925866725




Polar Normal (separate) - BGP282I - 910925866741




Polar Normal (separate) - BGP281I - 910925866743




Polar Normal (separate) - BGP283I - 910925866774



Polar Normal (separate) - BGP281I - 910925866713




Polar Normal (separate) - BGP281I - 910925866750




Polar Normal (separate) - BGP283I - 910925866769


Polar Wide Diagrams




Polar Normal (separate) - BGP282I - 91092586677




Polar Normal (separate) - BGP283I - 91092586681




Polar Normal (separate) - BGP282I - 910925866706




Polar Normal (separate) - BGP282I - 910925866754




Polar Normal (separate) - BGP281I - 910925866768




Polar Normal (separate) - BGP282I - 910925866794



Polar Normal (separate) - BGP282I - 910925866806




Polar Normal (separate) - BGP281I - 910925866815




Polar Normal (separate) - BGP282I - 910925866816


Polar Wide Diagrams




Polar Normal (separate) - BGP283I - 91092586695




Polar Normal (separate) - BGP281I - 910925866737




Polar Normal (separate) - BGP283I - 910925866776




Polar Normal (separate) - BGP281I - 910925866763




Polar Normal (separate) - BGP284I - 910925868093



Polar Normal (separate) - BGP281I - 910925866782



Polar Normal (separate) - BGP282I - 910925866811



Polar Normal (separate) - BGP282I - 91092586693

