



# Versatile and cost-efficient LED lighting

## ClearWay gen2

ClearWay Gen2 enables you to enjoy the benefits of LED technology for urban lighting right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimize your Total Cost of Ownership. ClearWay Gen2 significantly improves the most important aspects of the street lighting experience compared to conventional urban lighting. Ideal for new streets and for renovating existing installations, this affordable range of urban ClearWay lighting solutions combines clean design, high-quality light with significant energy and maintenance savings. In short, ClearWay Gen2 means good quality light with all the added benefits of LED - energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design, which makes it easier to install.

### Benefits

- A range of benefits packaged in one single luminaire architecture
- Easy to install
- Low initial cost
- Reasonable Total Cost of Ownership
- Signify Service tag (unique QR identification) for maintenance, installation and spare part information


### Features

- One flexible design that offers different options depending on application needs
- Includes a dedicated light recipe that preserves dark night skies
- Compact and efficient design
- Tilt regulation with no need to open the cover

Application

- Urban and residential roads
- Bicycle and pedestrian paths
- Minor roads
- Parking lots

Dimensional drawing



| General Information                    |                                                                          |
|----------------------------------------|--------------------------------------------------------------------------|
| Driver included                        | Yes                                                                      |
| Light source replaceable               | Yes                                                                      |
| Number of gear units                   | 1 unit                                                                   |
| Service tag                            | Yes                                                                      |
| Light Technical                        |                                                                          |
| Upward light output ratio              | 0                                                                        |
| Operating and Electrical               |                                                                          |
| Surge Protection (Common/Differential) | Surge protection level until 6 kV differential mode and 8 kV common mode |
| Mechanical and Housing                 |                                                                          |
| Optical cover type                     | Flat glass                                                               |
| Housing Color                          | Gray                                                                     |
| Mech. impact protection code           | IK09                                                                     |
| Ingress protection code                | IP66                                                                     |
| Standard tilt angle side entry         | 0°                                                                       |
| Standard tilt angle posttop            | 0°                                                                       |
| Approval and Application               |                                                                          |
| CE mark                                | Yes                                                                      |
| Flammability mark                      | -                                                                        |
| Product Data                           |                                                                          |
| Product family code                    | BGP307                                                                   |

General Information

| Order Code   | Full Product Name                        | Lamp family code |
|--------------|------------------------------------------|------------------|
| 910925864583 | BGP307 LED18-4S/740 I DM50 48/60S        | LED18            |
| 910925864584 | BGP307 LED25-4S/740 I DM50 48/60S        | LED25            |
| 910925864585 | BGP307 LED30-4S/740 I DM50 48/60S        | LED30            |
| 910925864586 | BGP307 LED35-4S/740 I DM50 48/60S        | LED35            |
| 910925864587 | BGP307 LED40-4S/740 I DM50 48/60S        | LED40            |
| 910925864588 | BGP307 LED45-4S/740 I DM50 48/60S        | LED45            |
| 910925864589 | BGP307 LED54-4S/740 I DM50 48/60S        | LED54            |
| 910925864590 | BGP307 LED69-4S/740 I DM50 48/60S        | LED69            |
| 910925864591 | BGP307 LED84-4S/740 I DM50 48/60S        | LED84            |
| 910925864592 | BGP307 LED99-4S/740 I DM50 48/60S        | LED99            |
| 910925864593 | BGP307 LED109-4S/740 I DM50 48/60S       | LED109           |
| 910925864594 | BGP307 LED120-4S/740 I DM50 48/60S       | LED120           |
| 910925864595 | BGP307 LED18-4S/740 II DM50 48/60S       | LED18            |
| 910925864596 | BGP307 LED25-4S/740 II DM50 48/60S       | LED25            |
| 910925864597 | BGP307 LED30-4S/740 II DM50 48/60S       | LED30            |
| 910925864598 | BGP307 LED35-4S/740 II DM50 48/60S       | LED35            |
| 910925864599 | BGP307 LED40-4S/740 II DM50 48/60S       | LED40            |
| 910925864601 | BGP307 LED45-4S/740 II DM50 48/60A       | LED45            |
| 910925864602 | BGP307 LED54-4S/740 II DM50 48/60S       | LED54            |
| 910925864603 | BGP307 LED69-4S/740 II DM50 48/60S       | LED69            |
| 910925864604 | BGP307 LED84-4S/740 II DM50 48/60S       | LED84            |
| 910925864605 | BGP307 LED99-4S/740 II DM50 48/60S       | LED99            |
| 910925864606 | BGP307 LED109-4S/740 II DM50 48/60S      | LED109           |
| 910925864607 | BGP307 LED120-4S/740 II DM50 48/60S      | LED120           |
| 910925865129 | BGP307 LED18-4S/740 I DM50 DDF27 D18 48/ | LED18            |
| 910925865130 | BGP307 LED30-4S/740 I DM50 DDF27 D18 48/ | LED30            |
| 910925865131 | BGP307 LED35-4S/740 I DM50 DDF27 D18 48/ | LED35            |
| 910925865132 | BGP307 LED54-4S/740 I DM50 DDF27 D18 48/ | LED54            |
| 910925865133 | BGP307 LED69-4S/740 I DM50 DDF27 D18 48/ | LED69            |

| Order Code   | Full Product Name                        | Lamp family code |
|--------------|------------------------------------------|------------------|
| 910925865134 | BGP307 LED120-4S/740 I DM50 DDF27 D18 48 | LED120           |
| 910925865210 | BGP307 LED18-4S/830 II DM11 CLO 48/60S   | LED18            |
| 910925865211 | BGP307 LED25-4S/830 II DM11 CLO 48/60S   | LED25            |
| 910925865212 | BGP307 LED35-4S/830 II DM11 CLO 48/60S   | LED35            |
| 910925865213 | BGP307 LED45-4S/830 II DM11 CLO 48/60S   | LED45            |
| 910925865214 | BGP307 LED54-4S/830 II DM11 CLO 48/60S   | LED54            |
| 910925865215 | BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18 | LED18            |
| 910925865216 | BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18 | LED25            |
| 910925865217 | BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18 | LED35            |
| 910925865218 | BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18 | LED45            |
| 910925865219 | BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18 | LED54            |
| 910925865220 | BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18 | LED18            |
| 910925865221 | BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18 | LED25            |
| 910925865222 | BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18 | LED35            |
| 910925865223 | BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18 | LED45            |
| 910925865224 | BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18 | LED54            |
| 910925865225 | BGP307 LED18-4S/740 II DM11 CLO 48/60S   | LED18            |
| 910925865226 | BGP307 LED25-4S/740 II DM11 CLO 48/60S   | LED25            |
| 910925865227 | BGP307 LED35-4S/740 II DM11 CLO 48/60S   | LED35            |
| 910925865228 | BGP307 LED45-4S/740 II DM11 CLO 48/60S   | LED45            |
| 910925865229 | BGP307 LED54-4S/740 II DM11 CLO 48/60S   | LED54            |
| 910925865230 | BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18 | LED18            |
| 910925865231 | BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18 | LED25            |
| 910925865232 | BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18 | LED35            |
| 910925865233 | BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18 | LED45            |
| 910925865234 | BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18 | LED54            |
| 910925865235 | BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18 | LED18            |
| 910925865236 | BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18 | LED25            |
| 910925865237 | BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18 | LED35            |
| 910925865238 | BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18 | LED45            |
| 910925865239 | BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18 | LED54            |
| 910925865240 | BGP307 LED69-4S/740 II DM11 CLO 48/60S   | LED69            |
| 910925865241 | BGP307 LED84-4S/740 II DM11 CLO 48/60S   | LED84            |
| 910925865242 | BGP307 LED99-4S/740 II DM11 CLO 48/60S   | LED99            |
| 910925865243 | BGP307 LED109-4S/740 II DM11 CLO 48/60S  | LED109           |
| 910925865244 | BGP307 LED120-4S/740 II DM11 CLO 48/60S  | LED120           |
| 910925865245 | BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18 | LED69            |
| 910925865246 | BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18 | LED84            |
| 910925865247 | BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18 | LED99            |
| 910925865248 | BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1 | LED109           |
| 910925865249 | BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1 | LED120           |
| 910925865250 | BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18 | LED69            |
| 910925865251 | BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18 | LED84            |
| 910925865252 | BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18 | LED99            |
| 910925865253 | BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1 | LED109           |
| 910925865254 | BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1 | LED120           |

Light Technical (1/2)

|              |                 | Luminaire    | Light   | Correlated        | Color       |
|--------------|-----------------|--------------|---------|-------------------|-------------|
|              | Full Product    | light beam   | source  | Color             | rendering   |
| Order Code   | Name            | spread       | color   | Temperature (Nom) | index (CRI) |
| 910925864583 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED18-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864584 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED25-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864585 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED30-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864586 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED35-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864587 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED40-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864588 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED45-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864589 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED54-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864590 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED69-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864591 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED84-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864592 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED99-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864593 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED109-4S/740 I | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864594 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED120-4S/740 I | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864595 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED18-4S/740 II | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864596 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED25-4S/740 II | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864597 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED30-4S/740 II | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |
| 910925864598 | BGP307          | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED35-4S/740 II | 54°          | neutral |                   |             |
|              | DM50 48/60S     |              | white   |                   |             |

|              |                  | Luminaire    | Light   | Correlated        | Color       |
|--------------|------------------|--------------|---------|-------------------|-------------|
|              | Full Product     | light beam   | source  | Color             | rendering   |
| Order Code   | Name             | spread       | color   | Temperature (Nom) | index (CRI) |
| 910925864599 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED40-4S/740 II  | 54°          | neutral |                   |             |
|              | DM50 48/60S      |              | white   |                   |             |
| 910925864601 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED45-4S/740 II  | 54°          | neutral |                   |             |
|              | DM50 48/60A      |              | white   |                   |             |
| 910925864602 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED54-4S/740 II  | 54°          | neutral |                   |             |
|              | DM50 48/60S      |              | white   |                   |             |
| 910925864603 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED69-4S/740 II  | 54°          | neutral |                   |             |
|              | DM50 48/60S      |              | white   |                   |             |
| 910925864604 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED84-4S/740 II  | 54°          | neutral |                   |             |
|              | DM50 48/60S      |              | white   |                   |             |
| 910925864605 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED99-4S/740 II  | 54°          | neutral |                   |             |
|              | DM50 48/60S      |              | white   |                   |             |
| 910925864606 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED109-4S/740 II | 54°          | neutral |                   |             |
|              | DM50 48/60S      |              | white   |                   |             |
| 910925864607 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED120-4S/740 II | 54°          | neutral |                   |             |
|              | DM50 48/60S      |              | white   |                   |             |
| 910925865129 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED18-4S/740 I   | 54°          | neutral |                   |             |
|              | DM50 DDF27       |              | white   |                   |             |
| 910925865130 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED30-4S/740 I   | 54°          | neutral |                   |             |
|              | DM50 DDF27       |              | white   |                   |             |
| 910925865131 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED35-4S/740 I   | 54°          | neutral |                   |             |
|              | DM50 DDF27       |              | white   |                   |             |
| 910925865132 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED54-4S/740 I   | 54°          | neutral |                   |             |
|              | DM50 DDF27       |              | white   |                   |             |
| 910925865133 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED69-4S/740 I   | 54°          | neutral |                   |             |
|              | DM50 DDF27       |              | white   |                   |             |
| 910925865134 | BGP307           | 154° - 31° x | 740     | 4000 K            | 70          |
|              | LED120-4S/740 I  | 54°          | neutral |                   |             |
|              | DM50 DDF27       |              | white   |                   |             |

|              |                 | Luminaire    | Light  | Correlated        | Color       |
|--------------|-----------------|--------------|--------|-------------------|-------------|
|              | Full Product    | light beam   | source | Color             | rendering   |
| Order Code   | Name            | spread       | color  | Temperature (Nom) | index (CRI) |
| 910925865210 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED18-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO        |              | white  |                   |             |
|              | 48/60S          |              |        |                   |             |
| 910925865211 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED25-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO        |              | white  |                   |             |
|              | 48/60S          |              |        |                   |             |
| 910925865212 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED35-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO        |              | white  |                   |             |
|              | 48/60S          |              |        |                   |             |
| 910925865213 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED45-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO        |              | white  |                   |             |
|              | 48/60S          |              |        |                   |             |
| 910925865214 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED54-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO        |              | white  |                   |             |
|              | 48/60S          |              |        |                   |             |
| 910925865215 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED18-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO-DDF1   |              | white  |                   |             |
|              | D18             |              |        |                   |             |
| 910925865216 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED25-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO-DDF1   |              | white  |                   |             |
|              | D18             |              |        |                   |             |
| 910925865217 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED35-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO-DDF1   |              | white  |                   |             |
|              | D18             |              |        |                   |             |
| 910925865218 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED45-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO-DDF1   |              | white  |                   |             |
|              | D18             |              |        |                   |             |
| 910925865219 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED54-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO-DDF1   |              | white  |                   |             |
|              | D18             |              |        |                   |             |
| 910925865220 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED18-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO-DDF2   |              | white  |                   |             |
|              | D18             |              |        |                   |             |
| 910925865221 | BGP307          | 160° - 42° x | 830    | 3000 K            | 80          |
|              | LED25-4S/830 II | 54°          | warm   |                   |             |
|              | DM11 CLO-DDF2   |              | white  |                   |             |
|              | D18             |              |        |                   |             |

|              |                 | Luminaire    | Light   | Correlated        | Color       |
|--------------|-----------------|--------------|---------|-------------------|-------------|
|              | Full Product    | light beam   | source  | Color             | rendering   |
| Order Code   | Name            | spread       | color   | Temperature (Nom) | index (CRI) |
| 910925865222 | BGP307          | 160° - 42° x | 830     | 3000 K            | 80          |
|              | LED35-4S/830 II | 54°          | warm    |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865223 | BGP307          | 160° - 42° x | 830     | 3000 K            | 80          |
|              | LED45-4S/830 II | 54°          | warm    |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865224 | BGP307          | 160° - 42° x | 830     | 3000 K            | 80          |
|              | LED54-4S/830 II | 54°          | warm    |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865225 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED18-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO        |              | white   |                   |             |
|              | 48/60S          |              |         |                   |             |
| 910925865226 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED25-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO        |              | white   |                   |             |
|              | 48/60S          |              |         |                   |             |
| 910925865227 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED35-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO        |              | white   |                   |             |
|              | 48/60S          |              |         |                   |             |
| 910925865228 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED45-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO        |              | white   |                   |             |
|              | 48/60S          |              |         |                   |             |
| 910925865229 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED54-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO        |              | white   |                   |             |
|              | 48/60S          |              |         |                   |             |
| 910925865230 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED18-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF1   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865231 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED25-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF1   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865232 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED35-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF1   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865233 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED45-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF1   |              | white   |                   |             |
|              | D18             |              |         |                   |             |

|              |                 | Luminaire    | Light   | Correlated        | Color       |
|--------------|-----------------|--------------|---------|-------------------|-------------|
|              | Full Product    | light beam   | source  | Color             | rendering   |
| Order Code   | Name            | spread       | color   | Temperature (Nom) | index (CRI) |
| 910925865234 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED54-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF1   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865235 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED18-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865236 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED25-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865237 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED35-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865238 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED45-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865239 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED54-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865240 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED69-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO        |              | white   |                   |             |
|              | 48/60S          |              |         |                   |             |
| 910925865241 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED84-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO        |              | white   |                   |             |
|              | 48/60S          |              |         |                   |             |
| 910925865242 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED99-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO        |              | white   |                   |             |
|              | 48/60S          |              |         |                   |             |
| 910925865243 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED109-4S/740   | 54°          | neutral |                   |             |
|              | II DM11 CLO     |              | white   |                   |             |
|              | 48/60S          |              |         |                   |             |
| 910925865244 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED120-4S/740   | 54°          | neutral |                   |             |
|              | II DM11 CLO     |              | white   |                   |             |
|              | 48/60S          |              |         |                   |             |

|              |                 | Luminaire    | Light   | Correlated        | Color       |
|--------------|-----------------|--------------|---------|-------------------|-------------|
|              | Full Product    | light beam   | source  | Color             | rendering   |
| Order Code   | Name            | spread       | color   | Temperature (Nom) | index (CRI) |
| 910925865245 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED69-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF1   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865246 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED84-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF1   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865247 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED99-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF1   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865248 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED109-4S/740   | 54°          | neutral |                   |             |
|              | II DM11 CLO-    |              | white   |                   |             |
|              | DDF1 D1         |              |         |                   |             |
| 910925865249 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED120-4S/740   | 54°          | neutral |                   |             |
|              | II DM11 CLO-    |              | white   |                   |             |
|              | DDF1 D1         |              |         |                   |             |
| 910925865250 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED69-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865251 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED84-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865252 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED99-4S/740 II | 54°          | neutral |                   |             |
|              | DM11 CLO-DDF2   |              | white   |                   |             |
|              | D18             |              |         |                   |             |
| 910925865253 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED109-4S/740   | 54°          | neutral |                   |             |
|              | II DM11 CLO-    |              | white   |                   |             |
|              | DDF2 D1         |              |         |                   |             |
| 910925865254 | BGP307          | 160° - 42° x | 740     | 4000 K            | 70          |
|              | LED120-4S/740   | 54°          | neutral |                   |             |
|              | II DM11 CLO-    |              | white   |                   |             |
|              | DDF2 D1         |              |         |                   |             |

Light Technical (2/2)

| Order Code   | Full Product Name                           | Luminous Flux | Optic type outdoor        |
|--------------|---------------------------------------------|---------------|---------------------------|
| 910925864583 | BGP307 LED18-4S/740 I DM50<br>48/60S        | 1,584 lm      | Distribution medium<br>50 |
| 910925864584 | BGP307 LED25-4S/740 I DM50<br>48/60S        | 2,175 lm      | Distribution medium<br>50 |
| 910925864585 | BGP307 LED30-4S/740 I DM50<br>48/60S        | 2,610 lm      | Distribution medium<br>50 |
| 910925864586 | BGP307 LED35-4S/740 I DM50<br>48/60S        | 3,080 lm      | Distribution medium<br>50 |
| 910925864587 | BGP307 LED40-4S/740 I DM50<br>48/60S        | 3,520 lm      | Distribution medium<br>50 |
| 910925864588 | BGP307 LED45-4S/740 I DM50<br>48/60S        | 3,960 lm      | Distribution medium<br>50 |
| 910925864589 | BGP307 LED54-4S/740 I DM50<br>48/60S        | 4,698 lm      | Distribution medium<br>50 |
| 910925864590 | BGP307 LED69-4S/740 I DM50<br>48/60S        | 6,160 lm      | Distribution medium<br>50 |
| 910925864591 | BGP307 LED84-4S/740 I DM50<br>48/60S        | 7,308 lm      | Distribution medium<br>50 |
| 910925864592 | BGP307 LED99-4S/740 I DM50<br>48/60S        | 8,600 lm      | Distribution medium<br>50 |
| 910925864593 | BGP307 LED109-4S/740 I DM50<br>48/60S       | 9,460 lm      | Distribution medium<br>50 |
| 910925864594 | BGP307 LED120-4S/740 I DM50<br>48/60S       | 10,200 lm     | Distribution medium<br>50 |
| 910925864595 | BGP307 LED18-4S/740 II DM50<br>48/60S       | 1,584 lm      | Distribution medium<br>50 |
| 910925864596 | BGP307 LED25-4S/740 II DM50<br>48/60S       | 2,175 lm      | Distribution medium<br>50 |
| 910925864597 | BGP307 LED30-4S/740 II DM50<br>48/60S       | 2,610 lm      | Distribution medium<br>50 |
| 910925864598 | BGP307 LED35-4S/740 II DM50<br>48/60S       | 3,080 lm      | Distribution medium<br>50 |
| 910925864599 | BGP307 LED40-4S/740 II DM50<br>48/60S       | 3,520 lm      | Distribution medium<br>50 |
| 910925864601 | BGP307 LED45-4S/740 II DM50<br>48/60A       | 3,960 lm      | Distribution medium<br>50 |
| 910925864602 | BGP307 LED54-4S/740 II DM50<br>48/60S       | 4,698 lm      | Distribution medium<br>50 |
| 910925864603 | BGP307 LED69-4S/740 II DM50<br>48/60S       | 6,160 lm      | Distribution medium<br>50 |
| 910925864604 | BGP307 LED84-4S/740 II DM50<br>48/60S       | 7,308 lm      | Distribution medium<br>50 |
| 910925864605 | BGP307 LED99-4S/740 II DM50<br>48/60S       | 8,600 lm      | Distribution medium<br>50 |
| 910925864606 | BGP307 LED109-4S/740 II DM50<br>48/60S      | 9,460 lm      | Distribution medium<br>50 |
| 910925864607 | BGP307 LED120-4S/740 II DM50<br>48/60S      | 10,200 lm     | Distribution medium<br>50 |
| 910925865129 | BGP307 LED18-4S/740 I DM50<br>DDF27 D18 48/ | 1,584 lm      | Distribution medium<br>50 |
| 910925865130 | BGP307 LED30-4S/740 I DM50<br>DDF27 D18 48/ | 2,610 lm      | Distribution medium<br>50 |

| Order Code   | Full Product Name                           | Luminous Flux | Optic type outdoor        |
|--------------|---------------------------------------------|---------------|---------------------------|
| 910925865131 | BGP307 LED35-4S/740 I DM50<br>DDF27 D18 48/ | 3,080 lm      | Distribution medium<br>50 |
| 910925865132 | BGP307 LED54-4S/740 I DM50<br>DDF27 D18 48/ | 4,698 lm      | Distribution medium<br>50 |
| 910925865133 | BGP307 LED69-4S/740 I DM50<br>DDF27 D18 48/ | 6,160 lm      | Distribution medium<br>50 |
| 910925865134 | BGP307 LED120-4S/740 I DM50<br>DDF27 D18 48 | 10,200 lm     | Distribution medium<br>50 |
| 910925865210 | BGP307 LED18-4S/830 II DM11<br>CLO 48/60S   | 1,522.5 lm    | Distribution medium<br>11 |
| 910925865211 | BGP307 LED25-4S/830 II DM11<br>CLO 48/60S   | 2,088 lm      | Distribution medium<br>11 |
| 910925865212 | BGP307 LED35-4S/830 II DM11<br>CLO 48/60S   | 2,958 lm      | Distribution medium<br>11 |
| 910925865213 | BGP307 LED45-4S/830 II DM11<br>CLO 48/60S   | 3,741 lm      | Distribution medium<br>11 |
| 910925865214 | BGP307 LED54-4S/830 II DM11<br>CLO 48/60S   | 4,524 lm      | Distribution medium<br>11 |
| 910925865215 | BGP307 LED18-4S/830 II DM11<br>CLO-DDF1 D18 | 1,522.5 lm    | Distribution medium<br>11 |
| 910925865216 | BGP307 LED25-4S/830 II DM11<br>CLO-DDF1 D18 | 2,088 lm      | Distribution medium<br>11 |
| 910925865217 | BGP307 LED35-4S/830 II DM11<br>CLO-DDF1 D18 | 2,958 lm      | Distribution medium<br>11 |
| 910925865218 | BGP307 LED45-4S/830 II DM11<br>CLO-DDF1 D18 | 3,741 lm      | Distribution medium<br>11 |
| 910925865219 | BGP307 LED54-4S/830 II DM11<br>CLO-DDF1 D18 | 4,524 lm      | Distribution medium<br>11 |
| 910925865220 | BGP307 LED18-4S/830 II DM11<br>CLO-DDF2 D18 | 1,522.5 lm    | Distribution medium<br>11 |
| 910925865221 | BGP307 LED25-4S/830 II DM11<br>CLO-DDF2 D18 | 2,088 lm      | Distribution medium<br>11 |
| 910925865222 | BGP307 LED35-4S/830 II DM11<br>CLO-DDF2 D18 | 2,958 lm      | Distribution medium<br>11 |
| 910925865223 | BGP307 LED45-4S/830 II DM11<br>CLO-DDF2 D18 | 3,741 lm      | Distribution medium<br>11 |
| 910925865224 | BGP307 LED54-4S/830 II DM11<br>CLO-DDF2 D18 | 4,524 lm      | Distribution medium<br>11 |
| 910925865225 | BGP307 LED18-4S/740 II DM11<br>CLO 48/60S   | 1,522.5 lm    | Distribution medium<br>11 |
| 910925865226 | BGP307 LED25-4S/740 II DM11<br>CLO 48/60S   | 2,088 lm      | Distribution medium<br>11 |
| 910925865227 | BGP307 LED35-4S/740 II DM11<br>CLO 48/60S   | 2,958 lm      | Distribution medium<br>11 |
| 910925865228 | BGP307 LED45-4S/740 II DM11<br>CLO 48/60S   | 3,828 lm      | Distribution medium<br>11 |
| 910925865229 | BGP307 LED54-4S/740 II DM11<br>CLO 48/60S   | 4,524 lm      | Distribution medium<br>11 |
| 910925865230 | BGP307 LED18-4S/740 II DM11<br>CLO-DDF1 D18 | 1,522.5 lm    | Distribution medium<br>11 |
| 910925865231 | BGP307 LED25-4S/740 II DM11<br>CLO-DDF1 D18 | 2,088 lm      | Distribution medium<br>11 |

| Order Code   | Full Product Name                           | Luminous Flux | Optic type outdoor        |
|--------------|---------------------------------------------|---------------|---------------------------|
| 910925865232 | BGP307 LED35-4S/740 II DM11<br>CLO-DDF1 D18 | 2,958 lm      | Distribution medium<br>11 |
| 910925865233 | BGP307 LED45-4S/740 II DM11<br>CLO-DDF1 D18 | 3,828 lm      | Distribution medium<br>11 |
| 910925865234 | BGP307 LED54-4S/740 II DM11<br>CLO-DDF1 D18 | 4,524 lm      | Distribution medium<br>11 |
| 910925865235 | BGP307 LED18-4S/740 II DM11<br>CLO-DDF2 D18 | 1,522.5 lm    | Distribution medium<br>11 |
| 910925865236 | BGP307 LED25-4S/740 II DM11<br>CLO-DDF2 D18 | 2,088 lm      | Distribution medium<br>11 |
| 910925865237 | BGP307 LED35-4S/740 II DM11<br>CLO-DDF2 D18 | 2,958 lm      | Distribution medium<br>11 |
| 910925865238 | BGP307 LED45-4S/740 II DM11<br>CLO-DDF2 D18 | 3,828 lm      | Distribution medium<br>11 |
| 910925865239 | BGP307 LED54-4S/740 II DM11<br>CLO-DDF2 D18 | 4,524 lm      | Distribution medium<br>11 |
| 910925865240 | BGP307 LED69-4S/740 II DM11<br>CLO 48/60S   | 5,916 lm      | Distribution medium<br>11 |
| 910925865241 | BGP307 LED84-4S/740 II DM11<br>CLO 48/60S   | 7,134 lm      | Distribution medium<br>11 |
| 910925865242 | BGP307 LED99-4S/740 II DM11<br>CLO 48/60S   | 8,256 lm      | Distribution medium<br>11 |
| 910925865243 | BGP307 LED109-4S/740 II DM11<br>CLO 48/60S  | 9,030 lm      | Distribution medium<br>11 |

| Order Code   | Full Product Name                           | Luminous Flux | Optic type outdoor        |
|--------------|---------------------------------------------|---------------|---------------------------|
| 910925865244 | BGP307 LED120-4S/740 II DM11<br>CLO 48/60S  | 9,775 lm      | Distribution medium<br>11 |
| 910925865245 | BGP307 LED69-4S/740 II DM11<br>CLO-DDF1 D18 | 5,916 lm      | Distribution medium<br>11 |
| 910925865246 | BGP307 LED84-4S/740 II DM11<br>CLO-DDF1 D18 | 7,134 lm      | Distribution medium<br>11 |
| 910925865247 | BGP307 LED99-4S/740 II DM11<br>CLO-DDF1 D18 | 8,256 lm      | Distribution medium<br>11 |
| 910925865248 | BGP307 LED109-4S/740 II DM11<br>CLO-DDF1 D1 | 9,030 lm      | Distribution medium<br>11 |
| 910925865249 | BGP307 LED120-4S/740 II DM11<br>CLO-DDF1 D1 | 9,775 lm      | Distribution medium<br>11 |
| 910925865250 | BGP307 LED69-4S/740 II DM11<br>CLO-DDF2 D18 | 5,916 lm      | Distribution medium<br>11 |
| 910925865251 | BGP307 LED84-4S/740 II DM11<br>CLO-DDF2 D18 | 7,134 lm      | Distribution medium<br>11 |
| 910925865252 | BGP307 LED99-4S/740 II DM11<br>CLO-DDF2 D18 | 8,256 lm      | Distribution medium<br>11 |
| 910925865253 | BGP307 LED109-4S/740 II DM11<br>CLO-DDF2 D1 | 9,030 lm      | Distribution medium<br>11 |
| 910925865254 | BGP307 LED120-4S/740 II DM11<br>CLO-DDF2 D1 | 9,775 lm      | Distribution medium<br>11 |

Operating and Electrical

| Order Code   | Full Product Name                   | Power Consumption |
|--------------|-------------------------------------|-------------------|
| 910925864583 | BGP307 LED18-4S/740 I DM50 48/60S   | 11.6 W            |
| 910925864584 | BGP307 LED25-4S/740 I DM50 48/60S   | 16.2 W            |
| 910925864585 | BGP307 LED30-4S/740 I DM50 48/60S   | 19.6 W            |
| 910925864586 | BGP307 LED35-4S/740 I DM50 48/60S   | 21.5 W            |
| 910925864587 | BGP307 LED40-4S/740 I DM50 48/60S   | 24.5 W            |
| 910925864588 | BGP307 LED45-4S/740 I DM50 48/60S   | 27.5 W            |
| 910925864589 | BGP307 LED54-4S/740 I DM50 48/60S   | 33.5 W            |
| 910925864590 | BGP307 LED69-4S/740 I DM50 48/60S   | 40.5 W            |
| 910925864591 | BGP307 LED84-4S/740 I DM50 48/60S   | 49.5 W            |
| 910925864592 | BGP307 LED99-4S/740 I DM50 48/60S   | 59 W              |
| 910925864593 | BGP307 LED109-4S/740 I DM50 48/60S  | 65 W              |
| 910925864594 | BGP307 LED120-4S/740 I DM50 48/60S  | 72 W              |
| 910925864595 | BGP307 LED18-4S/740 II DM50 48/60S  | 11.6 W            |
| 910925864596 | BGP307 LED25-4S/740 II DM50 48/60S  | 16.2 W            |
| 910925864597 | BGP307 LED30-4S/740 II DM50 48/60S  | 19.6 W            |
| 910925864598 | BGP307 LED35-4S/740 II DM50 48/60S  | 21.5 W            |
| 910925864599 | BGP307 LED40-4S/740 II DM50 48/60S  | 24.5 W            |
| 910925864601 | BGP307 LED45-4S/740 II DM50 48/60A  | 27.5 W            |
| 910925864602 | BGP307 LED54-4S/740 II DM50 48/60S  | 33.5 W            |
| 910925864603 | BGP307 LED69-4S/740 II DM50 48/60S  | 40.5 W            |
| 910925864604 | BGP307 LED84-4S/740 II DM50 48/60S  | 49.5 W            |
| 910925864605 | BGP307 LED99-4S/740 II DM50 48/60S  | 59 W              |
| 910925864606 | BGP307 LED109-4S/740 II DM50 48/60S | 65 W              |
| 910925864607 | BGP307 LED120-4S/740 II DM50 48/60S | 72 W              |

| Order Code   | Full Product Name                        | Power Consumption |
|--------------|------------------------------------------|-------------------|
| 910925865129 | BGP307 LED18-4S/740 I DM50 DDF27 D18 48/ | 11.6 W            |
| 910925865130 | BGP307 LED30-4S/740 I DM50 DDF27 D18 48/ | 19.6 W            |
| 910925865131 | BGP307 LED35-4S/740 I DM50 DDF27 D18 48/ | 21.5 W            |
| 910925865132 | BGP307 LED54-4S/740 I DM50 DDF27 D18 48/ | 33.5 W            |
| 910925865133 | BGP307 LED69-4S/740 I DM50 DDF27 D18 48/ | 40.5 W            |
| 910925865134 | BGP307 LED120-4S/740 I DM50 DDF27 D18 48 | 72 W              |
| 910925865210 | BGP307 LED18-4S/830 II DM11 CLO 48/60S   | 14.4 W            |
| 910925865211 | BGP307 LED25-4S/830 II DM11 CLO 48/60S   | 20 W              |
| 910925865212 | BGP307 LED35-4S/830 II DM11 CLO 48/60S   | 26.5 W            |
| 910925865213 | BGP307 LED45-4S/830 II DM11 CLO 48/60S   | 34.5 W            |
| 910925865214 | BGP307 LED54-4S/830 II DM11 CLO 48/60S   | 39 W              |
| 910925865215 | BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18 | 14.4 W            |
| 910925865216 | BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18 | 20 W              |
| 910925865217 | BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18 | 26.5 W            |
| 910925865218 | BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18 | 34.5 W            |
| 910925865219 | BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18 | 39 W              |
| 910925865220 | BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18 | 14.4 W            |
| 910925865221 | BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18 | 20 W              |
| 910925865222 | BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18 | 26.5 W            |
| 910925865223 | BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18 | 34.5 W            |
| 910925865224 | BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18 | 39 W              |
| 910925865225 | BGP307 LED18-4S/740 II DM11 CLO 48/60S   | 11.4 W            |
| 910925865226 | BGP307 LED25-4S/740 II DM11 CLO 48/60S   | 15.6 W            |
| 910925865227 | BGP307 LED35-4S/740 II DM11 CLO 48/60S   | 21 W              |

| Order Code   | Full Product Name                        | Power Consumption |
|--------------|------------------------------------------|-------------------|
| 910925865228 | BGP307 LED45-4S/740 II DM11 CLO 48/60S   | 27 W              |
| 910925865229 | BGP307 LED54-4S/740 II DM11 CLO 48/60S   | 32 W              |
| 910925865230 | BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18 | 11.4 W            |
| 910925865231 | BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18 | 15.6 W            |
| 910925865232 | BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18 | 21 W              |
| 910925865233 | BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18 | 27 W              |
| 910925865234 | BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18 | 32 W              |
| 910925865235 | BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18 | 11.4 W            |
| 910925865236 | BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18 | 15.6 W            |
| 910925865237 | BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18 | 21 W              |
| 910925865238 | BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18 | 27 W              |
| 910925865239 | BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18 | 32 W              |
| 910925865240 | BGP307 LED69-4S/740 II DM11 CLO 48/60S   | 39.5 W            |
| 910925865241 | BGP307 LED84-4S/740 II DM11 CLO 48/60S   | 48 W              |

| Order Code   | Full Product Name                        | Power Consumption |
|--------------|------------------------------------------|-------------------|
| 910925865242 | BGP307 LED99-4S/740 II DM11 CLO 48/60S   | 56 W              |
| 910925865243 | BGP307 LED109-4S/740 II DM11 CLO 48/60S  | 62 W              |
| 910925865244 | BGP307 LED120-4S/740 II DM11 CLO 48/60S  | 69 W              |
| 910925865245 | BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18 | 39.5 W            |
| 910925865246 | BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18 | 48 W              |
| 910925865247 | BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18 | 56 W              |
| 910925865248 | BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1 | 62 W              |
| 910925865249 | BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1 | 69 W              |
| 910925865250 | BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18 | 39.5 W            |
| 910925865251 | BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18 | 48 W              |
| 910925865252 | BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18 | 56 W              |
| 910925865253 | BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1 | 62 W              |
| 910925865254 | BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1 | 69 W              |

Controls and Dimming

| Order Code   | Full Product Name                  | Maximum dim |                |
|--------------|------------------------------------|-------------|----------------|
|              |                                    | Dimmable    | level          |
| 910925864583 | BGP307 LED18-4S/740 I DM50 48/60S  | No          | Not applicable |
| 910925864584 | BGP307 LED25-4S/740 I DM50 48/60S  | No          | Not applicable |
| 910925864585 | BGP307 LED30-4S/740 I DM50 48/60S  | No          | Not applicable |
| 910925864586 | BGP307 LED35-4S/740 I DM50 48/60S  | No          | Not applicable |
| 910925864587 | BGP307 LED40-4S/740 I DM50 48/60S  | No          | Not applicable |
| 910925864588 | BGP307 LED45-4S/740 I DM50 48/60S  | No          | Not applicable |
| 910925864589 | BGP307 LED54-4S/740 I DM50 48/60S  | No          | Not applicable |
| 910925864590 | BGP307 LED69-4S/740 I DM50 48/60S  | No          | Not applicable |
| 910925864591 | BGP307 LED84-4S/740 I DM50 48/60S  | No          | Not applicable |
| 910925864592 | BGP307 LED99-4S/740 I DM50 48/60S  | No          | Not applicable |
| 910925864593 | BGP307 LED109-4S/740 I DM50 48/60S | No          | Not applicable |
| 910925864594 | BGP307 LED120-4S/740 I DM50 48/60S | No          | Not applicable |
| 910925864595 | BGP307 LED18-4S/740 II DM50 48/60S | No          | Not applicable |
| 910925864596 | BGP307 LED25-4S/740 II DM50 48/60S | No          | Not applicable |
| 910925864597 | BGP307 LED30-4S/740 II DM50 48/60S | No          | Not applicable |
| 910925864598 | BGP307 LED35-4S/740 II DM50 48/60S | No          | Not applicable |
| 910925864599 | BGP307 LED40-4S/740 II DM50 48/60S | No          | Not applicable |
| 910925864601 | BGP307 LED45-4S/740 II DM50 48/60A | No          | Not applicable |
| 910925864602 | BGP307 LED54-4S/740 II DM50 48/60S | No          | Not applicable |
| 910925864603 | BGP307 LED69-4S/740 II DM50 48/60S | No          | Not applicable |
| 910925864604 | BGP307 LED84-4S/740 II DM50 48/60S | No          | Not applicable |

| Order Code   | Full Product Name                        | Maximum dim |                |
|--------------|------------------------------------------|-------------|----------------|
|              |                                          | Dimmable    | level          |
| 910925864605 | BGP307 LED99-4S/740 II DM50 48/60S       | No          | Not applicable |
| 910925864606 | BGP307 LED109-4S/740 II DM50 48/60S      | No          | Not applicable |
| 910925864607 | BGP307 LED120-4S/740 II DM50 48/60S      | No          | Not applicable |
| 910925865129 | BGP307 LED18-4S/740 I DM50 DDF27 D18 48/ | Yes         | 0% (digital)   |
| 910925865130 | BGP307 LED30-4S/740 I DM50 DDF27 D18 48/ | Yes         | 0% (digital)   |
| 910925865131 | BGP307 LED35-4S/740 I DM50 DDF27 D18 48/ | Yes         | 0% (digital)   |
| 910925865132 | BGP307 LED54-4S/740 I DM50 DDF27 D18 48/ | Yes         | 0% (digital)   |
| 910925865133 | BGP307 LED69-4S/740 I DM50 DDF27 D18 48/ | Yes         | 0% (digital)   |
| 910925865134 | BGP307 LED120-4S/740 I DM50 DDF27 D18 48 | Yes         | 0% (digital)   |
| 910925865210 | BGP307 LED18-4S/830 II DM11 CLO 48/60S   | No          | 0% (digital)   |
| 910925865211 | BGP307 LED25-4S/830 II DM11 CLO 48/60S   | No          | 0% (digital)   |
| 910925865212 | BGP307 LED35-4S/830 II DM11 CLO 48/60S   | No          | 0% (digital)   |
| 910925865213 | BGP307 LED45-4S/830 II DM11 CLO 48/60S   | No          | 0% (digital)   |
| 910925865214 | BGP307 LED54-4S/830 II DM11 CLO 48/60S   | No          | 0% (digital)   |
| 910925865215 | BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital)   |
| 910925865216 | BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital)   |

| Order Code   | Full Product Name                        | Maximum dim |              |
|--------------|------------------------------------------|-------------|--------------|
|              |                                          | Dimmable    | level        |
| 910925865217 | BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865218 | BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865219 | BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865220 | BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865221 | BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865222 | BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865223 | BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865224 | BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865225 | BGP307 LED18-4S/740 II DM11 CLO 48/60S   | No          | 0% (digital) |
| 910925865226 | BGP307 LED25-4S/740 II DM11 CLO 48/60S   | No          | 0% (digital) |
| 910925865227 | BGP307 LED35-4S/740 II DM11 CLO 48/60S   | No          | 0% (digital) |
| 910925865228 | BGP307 LED45-4S/740 II DM11 CLO 48/60S   | No          | 0% (digital) |
| 910925865229 | BGP307 LED54-4S/740 II DM11 CLO 48/60S   | No          | 0% (digital) |
| 910925865230 | BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865231 | BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865232 | BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865233 | BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865234 | BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865235 | BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |

| Order Code   | Full Product Name                        | Maximum dim |              |
|--------------|------------------------------------------|-------------|--------------|
|              |                                          | Dimmable    | level        |
| 910925865236 | BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865237 | BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865238 | BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865239 | BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865240 | BGP307 LED69-4S/740 II DM11 CLO 48/60S   | No          | 0% (digital) |
| 910925865241 | BGP307 LED84-4S/740 II DM11 CLO 48/60S   | No          | 0% (digital) |
| 910925865242 | BGP307 LED99-4S/740 II DM11 CLO 48/60S   | No          | 0% (digital) |
| 910925865243 | BGP307 LED109-4S/740 II DM11 CLO 48/60S  | No          | 0% (digital) |
| 910925865244 | BGP307 LED120-4S/740 II DM11 CLO 48/60S  | No          | 0% (digital) |
| 910925865245 | BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865246 | BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865247 | BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18 | Yes         | 0% (digital) |
| 910925865248 | BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1 | Yes         | 0% (digital) |
| 910925865249 | BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1 | Yes         | 0% (digital) |
| 910925865250 | BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865251 | BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865252 | BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18 | Yes         | 0% (digital) |
| 910925865253 | BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1 | Yes         | 0% (digital) |
| 910925865254 | BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1 | Yes         | 0% (digital) |

Over Time Performance (IEC Compliant)


| Order Code   | Full Product Name                 | Driver failure rate at |
|--------------|-----------------------------------|------------------------|
|              |                                   | 5000 h                 |
| 910925864583 | BGP307 LED18-4S/740 I DM50 48/60S | 0.5 %                  |
| 910925864584 | BGP307 LED25-4S/740 I DM50 48/60S | 0.5 %                  |
| 910925864585 | BGP307 LED30-4S/740 I DM50 48/60S | 0.5 %                  |
| 910925864586 | BGP307 LED35-4S/740 I DM50 48/60S | 0.5 %                  |
| 910925864587 | BGP307 LED40-4S/740 I DM50 48/60S | 0.5 %                  |
| 910925864588 | BGP307 LED45-4S/740 I DM50 48/60S | 0.5 %                  |
| 910925864589 | BGP307 LED54-4S/740 I DM50 48/60S | 0.5 %                  |
| 910925864590 | BGP307 LED69-4S/740 I DM50 48/60S | 0.5 %                  |

| Order Code   | Full Product Name                  | Driver failure rate at |
|--------------|------------------------------------|------------------------|
|              |                                    | 5000 h                 |
| 910925864591 | BGP307 LED84-4S/740 I DM50 48/60S  | 0.5 %                  |
| 910925864592 | BGP307 LED99-4S/740 I DM50 48/60S  | 0.5 %                  |
| 910925864593 | BGP307 LED109-4S/740 I DM50 48/60S | 0.5 %                  |
| 910925864594 | BGP307 LED120-4S/740 I DM50 48/60S | 0.5 %                  |
| 910925864595 | BGP307 LED18-4S/740 II DM50 48/60S | 0.5 %                  |
| 910925864596 | BGP307 LED25-4S/740 II DM50 48/60S | 0.5 %                  |
| 910925864597 | BGP307 LED30-4S/740 II DM50 48/60S | 0.5 %                  |
| 910925864598 | BGP307 LED35-4S/740 II DM50 48/60S | 0.5 %                  |


| Order Code   | Full Product Name                        | Driver failure rate at 5000 h |
|--------------|------------------------------------------|-------------------------------|
| 910925864599 | BGP307 LED40-4S/740 II DM50 48/60S       | 0.5 %                         |
| 910925864601 | BGP307 LED45-4S/740 II DM50 48/60A       | 0.5 %                         |
| 910925864602 | BGP307 LED54-4S/740 II DM50 48/60S       | 0.5 %                         |
| 910925864603 | BGP307 LED69-4S/740 II DM50 48/60S       | 0.5 %                         |
| 910925864604 | BGP307 LED84-4S/740 II DM50 48/60S       | 0.5 %                         |
| 910925864605 | BGP307 LED99-4S/740 II DM50 48/60S       | 0.5 %                         |
| 910925864606 | BGP307 LED109-4S/740 II DM50 48/60S      | 0.5 %                         |
| 910925864607 | BGP307 LED120-4S/740 II DM50 48/60S      | 0.5 %                         |
| 910925865129 | BGP307 LED18-4S/740 I DM50 DDF27 D18 48/ | 0.5 %                         |
| 910925865130 | BGP307 LED30-4S/740 I DM50 DDF27 D18 48/ | 0.5 %                         |
| 910925865131 | BGP307 LED35-4S/740 I DM50 DDF27 D18 48/ | 0.5 %                         |
| 910925865132 | BGP307 LED54-4S/740 I DM50 DDF27 D18 48/ | 0.5 %                         |
| 910925865133 | BGP307 LED69-4S/740 I DM50 DDF27 D18 48/ | 0.5 %                         |
| 910925865134 | BGP307 LED120-4S/740 I DM50 DDF27 D18 48 | 0.5 %                         |
| 910925865210 | BGP307 LED18-4S/830 II DM11 CLO 48/60S   | -                             |
| 910925865211 | BGP307 LED25-4S/830 II DM11 CLO 48/60S   | 0.5 %                         |
| 910925865212 | BGP307 LED35-4S/830 II DM11 CLO 48/60S   | -                             |
| 910925865213 | BGP307 LED45-4S/830 II DM11 CLO 48/60S   | 0.5 %                         |
| 910925865214 | BGP307 LED54-4S/830 II DM11 CLO 48/60S   | -                             |
| 910925865215 | BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18 | 0.5 %                         |
| 910925865216 | BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18 | -                             |
| 910925865217 | BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18 | 0.5 %                         |
| 910925865218 | BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18 | -                             |
| 910925865219 | BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18 | 0.5 %                         |
| 910925865220 | BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18 | -                             |
| 910925865221 | BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18 | 0.5 %                         |
| 910925865222 | BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18 | -                             |
| 910925865223 | BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18 | 0.5 %                         |
| 910925865224 | BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18 | -                             |
| 910925865225 | BGP307 LED18-4S/740 II DM11 CLO 48/60S   | 0.5 %                         |

| Order Code   | Full Product Name                        | Driver failure rate at 5000 h |
|--------------|------------------------------------------|-------------------------------|
| 910925865226 | BGP307 LED25-4S/740 II DM11 CLO 48/60S   | -                             |
| 910925865227 | BGP307 LED35-4S/740 II DM11 CLO 48/60S   | 0.5 %                         |
| 910925865228 | BGP307 LED45-4S/740 II DM11 CLO 48/60S   | -                             |
| 910925865229 | BGP307 LED54-4S/740 II DM11 CLO 48/60S   | 0.5 %                         |
| 910925865230 | BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18 | -                             |
| 910925865231 | BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18 | 0.5 %                         |
| 910925865232 | BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18 | -                             |
| 910925865233 | BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18 | 0.5 %                         |
| 910925865234 | BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18 | -                             |
| 910925865235 | BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18 | 0.5 %                         |
| 910925865236 | BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18 | -                             |
| 910925865237 | BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18 | 0.5 %                         |
| 910925865238 | BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18 | -                             |
| 910925865239 | BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18 | 0.5 %                         |
| 910925865240 | BGP307 LED69-4S/740 II DM11 CLO 48/60S   | -                             |
| 910925865241 | BGP307 LED84-4S/740 II DM11 CLO 48/60S   | 0.5 %                         |
| 910925865242 | BGP307 LED99-4S/740 II DM11 CLO 48/60S   | -                             |
| 910925865243 | BGP307 LED109-4S/740 II DM11 CLO 48/60S  | 0.5 %                         |
| 910925865244 | BGP307 LED120-4S/740 II DM11 CLO 48/60S  | -                             |
| 910925865245 | BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18 | 0.5 %                         |
| 910925865246 | BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18 | -                             |
| 910925865247 | BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18 | 0.5 %                         |
| 910925865248 | BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1 | -                             |
| 910925865249 | BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1 | 0.5 %                         |
| 910925865250 | BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18 | -                             |
| 910925865251 | BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18 | 0.5 %                         |
| 910925865252 | BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18 | -                             |
| 910925865253 | BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1 | 0.5 %                         |
| 910925865254 | BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1 | -                             |


Polar Wide Diagrams



Polar Normal (separate) - BGP307I - 910925864604




Polar Normal (separate) - BGP307I - 910925864592




Polar Normal (separate) - BGP307I - 910925864597


Polar Wide Diagrams




Polar Normal (separate) - BGP307I - 910925864587




Polar Normal (separate) - BGP307I - 910925864586




Polar Normal (separate) - BGP307I - 910925864590




Polar Normal (separate) - BGP307I - 910925865134




Polar Normal (separate) - BGP307I - 910925865226




Polar Normal (separate) - BGP307I - 910925865248



Polar Normal (separate) - BGP307I - 910925865213




Polar Normal (separate) - BGP307I - 910925865215




Polar Normal (separate) - BGP307I - 910925865151


Polar Wide Diagrams




Polar Normal (separate) - BGP307I - 910925865235




Polar Normal (separate) - BGP307I - 910925865211




Polar Normal (separate) - BGP307I - 910925864593




Polar Normal (separate) - BGP307I - 910925864595




Polar Normal (separate) - BGP307I - 910925864584




Polar Normal (separate) - BGP307I - 910925864588



Polar Normal (separate) - BGP307I - 910925864589




Polar Normal (separate) - BGP307I - 910925865153




Polar Normal (separate) - BGP307I - 910925865214


Polar Wide Diagrams




Polar Normal (separate) - BGP307I - 910925865222




Polar Normal (separate) - BGP307I - 910925865234




Polar Normal (separate) - BGP307I - 910925865238



Polar Normal (separate) - BGP307I - 910925865251



Polar Normal (separate) - BGP307I - 910925865245



Polar Normal (separate) - BGP307I - 910925865242

