



The most cost-effective outdoor spot light with better efficient and performance

UniPoint

Our UniPoint is designed to produce both general and accent lighting while concealing the body of the device, allowing only the light to be exposed. This design can be used to change the surroundings by adding subtle or dramatic contrasting effects. It also includes exclusive features such as energy efficiency, chromatic quality and miniaturization. We guarantee extreme reliability and high level of resistance to adverse weather conditions and vandalism

Benefits

- In stylish and very compact design
- Price point versus PHILIPS standards
- Effortless and flexible installation
- Customizing for you

Features

- High quality LED
- Different choice of light source and beam angles
- Die-cast aluminum housing + dark grey sand coating to ensure anticorrosion
- Structural waterproof technology
- IP66
- IK06
- Quality and reliability in line with all regulations

Application

- Buildings
- Statues
- Columns
- Pillars
- Eaves

Versions



UniPoint BGP312 5LED

Dimensional drawing

