



Get your city ready for the future with DigiStreet

DigiStreet

Developed with the aim to become your long term partner, the system ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come!. Its two sockets enable you to connect directly to the CityTouch system and is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain an optimal ecosystem for bats or 2) preserve a dark night sky.

Benefits

- Prepared for the future, it is easy to upgrade directly after installation or later with future CMS nodes and sensors to enable new functionalities
- Large availability of lens optics to match international road and street geometries
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information


Features

- Easy luminaire identification due to the Service tag
- High efficacy up to 161 lm/W
- Choice of 30+ different beams and different internal louvers
- Surge protection, 10 kV
- L-tune tool available
- Lifetime 100Khrs up to L96 at Tq +25 °C
- Internal louver (optional)

Application

- Traffic routes and main access road
- Urban and residential area
- City centers and main streets
- Cycle paths, footpaths and pedestrian crossings

Dimensional drawing



Product details

Digistreet-BGP760-DP06.tif



Digistreet-BGP760-DP09.tif



Digistreet-BGP760-DP10.tif



Digistreet-BGP760-DP11.tif




Digistreet-BGP761-DP17.tif



Digistreet-BGP761-DP18.tif



Digistreet-BGP761-DP19.tif



Digistreet-BGP761-DP20.tif



Product details



Digistreet-BGP761-DP21.tif



Digistreet-BGP761-DP22.tif



Digistreet-BGP761-DP23.tif



Digistreet-BGP761-DP24.tif



Digistreet-BGP761-DP25.tif



Digistreet-BGP761-DP26.tif

General Information	
Driver included	Yes
Light source replaceable	Yes
Service tag	Yes
Light Technical	
Upward light output ratio	0
Mechanical and Housing	
Optical cover type	Flat glass
Mech. impact protection code	IK09
Ingress protection code	IP66
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	-

General Information

Order Code	Full Product Name	Lamp family		
		Gear	code	Number of gear units
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	-	LED95	1 unit
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	-	LED95	1 unit
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	-	LED120	1 unit
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	-	LED159	1 unit
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	-	LED129	1 unit
910925866223	BGP762 LED169-/740 I DS50 DGR 62	-	LED169	1 unit
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	-	LED110	1 unit
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	-	LED149	1 unit
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	-	LED180	1 unit
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	-	LED100	1 unit
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	-	LED139	1 unit
910925866229	BGP762 LED170-/830 II DW10 DGR 76	-	LED170	1 unit
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	-	LED95	1 unit
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	-	LED169	1 unit
910925866245	BGP762 LED200-/740 I DW50 DGR 62	-	LED200	1 unit
910925866246	BGP762 LED210-/740 II DX70 DGR 76	-	LED210	1 unit
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	-	LED190	1 unit
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	-	LED220	1 unit
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	-	LED120	1 unit
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	-	LED159	1 unit
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	-	LED239	1 unit
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	-	LED220	1 unit
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	-	LED239	1 unit
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	-	LED239	1 unit
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	-	LED149	1 unit
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	-	LED239	1 unit
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	EB	LED10	1 unit
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	EB	LED12	1 unit
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	EB	LED14	1 unit
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	EB	LED16	1 unit
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	EB	LED22	1 unit
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	EB	LED24	1 unit
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	EB	LED27	1 unit
910925863563	BGP760 LED30-/830 II DW10 DGR 62	EB	LED30	1 unit
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	EB	LED34	1 unit
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	EB	LED44	1 unit
910925863567	BGP760 LED49-/740 II DX70 DGR 62	EB	LED49	1 unit
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	-	LED24	1 unit
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	-	LED44	1 unit
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	-	LED16	1 unit
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	-	LED16	1 unit
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	-	LED60	1 unit
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	-	LED60	1 unit
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	-	LED60	1 unit
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	-	LED49	1 unit
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	-	LED49	1 unit
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	-	LED280	2 units
910925866249	BGP763 LED300-/740 I DW50 DGR 62	-	LED300	2 units
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	-	LED260	2 units
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	-	LED340	2 units

Order Code	Full Product Name	Lamp family		
		Gear	code	Number of gear units
910925866253	BGP763 LED320-/740 II DX70 DGR 76	-	LED320	2 units
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	-	LED260	2 units
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	-	LED360	2 units
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	-	LED340	2 units
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	-	LED360	2 units
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	-	LED360	2 units
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	-	LED45	1 unit
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	-	LED45	1 unit
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	-	LED45	1 unit
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	-	LED74	1 unit
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	-	LED94	1 unit
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	-	LED109	1 unit
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	-	LED55	1 unit
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	-	LED84	1 unit
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	-	LED55	1 unit
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	-	LED84	1 unit
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	-	LED50	1 unit
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	-	LED79	1 unit
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	-	LED59	1 unit
910925866241	BGP761 LED90-/740 II DW10 DGR 62	-	LED90	1 unit
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	-	LED74	1 unit
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	-	LED84	1 unit
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	-	LED119	1 unit
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	-	LED119	1 unit
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	-	LED84	1 unit

Light Technical (1/2)

Order Code	Full Product Name	Luminaire	Light	Correlated	Color
		light beam	source	Color	rendering
Order Code	Name	light beam	source	Temperature	index
		spread	color	(Nom)	(CRI)
910925865607	BGP762	160° - 42° x	518	1800 K	50
	LED95-4S/518 II	53°	ClearStar		
	DM11 DGR 62		WW		
910925865608	BGP762	160° - 42° x	420	2000 K	40
	LED95-4S/420 II	53°	ClearStar		
	DM11 DGR 62		NW		
910925866220	BGP762	53° x 71°	830 warm	3000 K	80
	LED120-/830 II		white		
	DN11 DGR D11 76				
910925866221	BGP762	-	830 warm	3000 K	80
	LED159-/830 II		white		
	DM70 DGR				
	DDF27 D18				
910925866222	BGP762	160° - 42° x	740	4000 K	70
	LED129-/740 I	54°	neutral		
	DM11 DGR 32-48		white		
910925866223	BGP762	32° x 29°	740	4000 K	70
	LED169-/740 I		neutral		
	DS50 DGR 62		white		
910925866224	BGP762	68° x 158°	740	4000 K	70
	LED110-/740 I		neutral		
	DN10 DGR 32-48		white		
910925866225	BGP762	154° - 31° x	740	4000 K	70
	LED149-/740 I	54°	neutral		
	DM50 DGR		white		
	32-48				
910925866226	BGP762	150° - 43° x	740	4000 K	70
	LED180-/740 I	67°	neutral		
	DX10 DGR 32-48		white		
910925866227	BGP762	160° - 42° x	830 warm	3000 K	80
	LED100-/830 II	54°	white		
	DM11 DGR D9 62				
910925866228	BGP762	160° - 42° x	830 warm	3000 K	80
	LED139-/830 II	54°	white		
	DM11 DGR D9 62				
910925866229	BGP762	61° x 150°	830 warm	3000 K	80
	LED170-/830 II		white		
	DW10 DGR 76				

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	157° - 33° x 55°	740 neutral white	4000 K	70
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	30°	740 neutral white	4000 K	70
910925866245	BGP762 LED200-/740 I DW50 DGR 62	152° - 24° x 66°	740 neutral white	4000 K	70
910925866246	BGP762 LED210-/740 II DX70 DGR 76	106° x 86°	740 neutral white	4000 K	70
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	61° x 150°	740 neutral white	4000 K	70
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	61° x 150°	740 neutral white	4000 K	70
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	149° - 10° x 57°	740 neutral white	4000 K	70
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	152° - 25° x 66°	740 neutral white	4000 K	70
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	151° - 43° x 67°	740 neutral white	4000 K	70
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	152° - 25° x 66°	740 neutral white	4000 K	70
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	149° - 10° x 57°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	149° - 10° x 57°	740 neutral white	4000 K	70
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	157° - 33° x 55°	740 neutral white	4000 K	70
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	68° x 157°	740 neutral white	4000 K	70
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	53° x 71°	830 warm white	3000 K	80
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	154° - 31° x 54°	740 neutral white	4000 K	70
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	-	830 warm white	3000 K	80
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	32° x 29°	740 neutral white	4000 K	70
910925863563	BGP760 LED30-/830 II DW10 DGR 62	61° x 150°	830 warm white	3000 K	80
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	150° - 43° x 67°	740 neutral white	4000 K	70
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	152° - 24° x 66°	740 neutral white	4000 K	70
910925863567	BGP760 LED49-/740 II DX70 DGR 62	106° x 44°	740 neutral white	4000 K	70
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	157° - 33° x 55°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866306	BGP760	160° - 42° x	518	1800 K	50
	LED16-/518 II	53°	ClearStar		
	DM11 DGR 62 S		WW		
910925866307	BGP760	160° - 42° x	420	2000 K	40
	LED16-/420 II	53°	ClearStar		
	DM11 DGR 62 S		NW		
910925866495	BGP760	157° - 33° x	740	4000 K	70
	LED60-/740 I	55°	neutral		
	DM10 DGR 62 S		white		
910925867978	BGP760	151° - 43° x	740	4000 K	70
	LED60/740 I	67°	neutral		
	DX10 DGR CLO		white		
	IACZ-4-D				
910925867979	BGP760	152° - 25° x	740	4000 K	70
	LED60/740 I	66°	neutral		
	DW50 BL1 DGR		white		
	CLO IACZ				
910925867987	BGP760	149° - 10° x	740	4000 K	70
	LED49/740 II	57°	neutral		
	DM32 7042 MSP		white		
	CLO-DD				
910925867995	BGP760 LED-HB/740 II DM32	149° - 10° x	740	4000 K	70
	DGR MSP CLO	57°	neutral		
	D1		white		
910925866248	BGP763	61° x 150°	830 warm	3000 K	80
	LED240-/830 II		white		
	DW10 DGR				
	SRG10 62				
910925866249	BGP763	152° - 24° x	740	4000 K	70
	LED300-/740 I	66°	neutral		
	DW50 DGR 62		white		
910925866250	BGP763	150° - 43° x	740	4000 K	70
	LED260-/740 I	67°	neutral		
	DX10 DGR 32-48		white		
910925866251	BGP763	61° x 150°	740	4000 K	70
	LED340-/740 II		neutral		
	DW10 DGR		white		
	SRG10 62				
910925866253	BGP763	106° x 44°	740	4000 K	70
	LED320-/740 II		neutral		
	DX70 DGR 76		white		
910925866494	BGP763	157° - 33° x	740	4000 K	70
	LED260/740 I	55°	neutral		
	DM10 DGR 62 S		white		
910925866498	BGP763	157° - 33° x	740	4000 K	70
	LED360/740 I	55°	neutral		
	DM10 DGR 62 S		white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925867852	BGP763	152° - 25° x	740	4000 K	70
	LED340/740 I	66°	neutral		
	DW50 DGR D9		white		
	62 S				
910925867984	BGP763	151° - 43° x	740	4000 K	70
	LED360/740 I	67°	neutral		
	DX10 DGR CLO		white		
	IACZ-4-				
910925867985	BGP763	152° - 25° x	740	4000 K	70
	LED360/740 I	66°	neutral		
	DW50 BL1 DGR		white		
	IACZ-4-				
910925865604	BGP761	160° - 42° x	518	1800 K	50
	LED45-4S/518 II	53°	ClearStar		
	DM11 DGR 62		WW		
910925865605	BGP761	160° - 42° x	420	2000 K	40
	LED45-4S/420 II	53°	ClearStar		
	DM11 DGR 62		NW		
910925866230	BGP761	157° - 33° x	740	4000 K	70
	LED45-/740 I	55°	neutral		
	DM10 DGR		white		
	32-48				
910925866231	BGP761	154° - 31° x	740	4000 K	70
	LED74-/740 I	54°	neutral		
	DM50 DGR		white		
	32-48				
910925866232	BGP761	150° - 43° x	740	4000 K	70
	LED94-/740 I	67°	neutral		
	DX10 DGR 32-48		white		
910925866233	BGP761	157° - 33° x	740	4000 K	70
	LED109-/740 I	55°	neutral		
	DM10 DGR		white		
	DDF27 D18				
910925866234	BGP761	68° x 157°	740	4000 K	70
	LED55-/740 I		neutral		
	DN10 DGR 32-48		white		
910925866235	BGP761	32° x 29°	740	4000 K	70
	LED84-/740 I		neutral		
	DS50 DGR 32-48		white		
910925866236	BGP761	160° - 42° x	740	4000 K	70
	LED55-/740 I	54°	neutral		
	DM11 DGR SRB		white		
	62				
910925866237	BGP761	157° - 33° x	740	4000 K	70
	LED84-/740 I	55°	neutral		
	DM10 DGR		white		
	DDF27 D18 S				

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	160° - 42° x 54°	830 warm white	3000 K	80
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	-	830 warm white	3000 K	80
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	53° x 71°	830 warm white	3000 K	80
910925866241	BGP761 LED90-/740 II DW10 DGR 62	61° x 150°	740 neutral white	4000 K	70
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	154° - 31° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	157° - 33° x 55°	740 neutral white	4000 K	70
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	152° - 25° x 66°	740 neutral white	4000 K	70
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	149° - 10° x 57°	740 neutral white	4000 K	70

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	5,952 lm	-	Distribution medium 11
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	5,952 lm	-	Distribution medium 11
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	10,800 lm	-	Distribution narrow 11
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	13,920 lm	-	Distribution medium 70
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	11,830 lm	-	Distribution medium 11
910925866223	BGP762 LED169-/740 I DS50 DGR 62	14,960 lm	-	Distribution symmetrical 50
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	10,010 lm	-	Distribution narrow 10
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	13,500 lm	-	Distribution medium 50
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	15,480 lm	-	Distribution extra wide 10
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	9,100 lm	-	Distribution medium 11
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	12,740 lm	-	Distribution medium 11
910925866229	BGP762 LED170-/830 II DW10 DGR 76	15,300 lm	-	Distribution wide 10

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	8,640 lm	-	Distribution medium 10
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	14,960 lm	-	Distribution symmetrical 50
910925866245	BGP762 LED200-/740 I DW50 DGR 62	17,200 lm	-	Distribution wide 50
910925866246	BGP762 LED210-/740 II DX70 DGR 76	18,060 lm	-	Distribution extra wide 70
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	17,100 lm	-	Distribution wide 10
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	19,800 lm	-	Distribution wide 10
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	10,800 lm	-	Distribution medium 10
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	14,240 lm	-	Distribution medium 10
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	20,700 lm	-	Distribution medium 32
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	18,920 lm	-	Distribution wide 50
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	19,550 lm	-	Distribution extra wide 10
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	13,800 lm	-	Distribution wide 50

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925867989	BGP762 LED149-/740 II DM32 7042 MSP CLO-D	13,195 lm	-	Distribution medium 32
910925867990	BGP762 LED239-/740 II DM32 7042 MSP CLO-D	20,700 lm	-	Distribution medium 32
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	900 lm	1	Distribution medium 10
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	1,092 lm	1	Distribution medium 11
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	1,274 lm	1	Distribution narrow 10
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	1,456 lm	1	Distribution narrow 11
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	2,002 lm	1	Distribution medium 50
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	2,136 lm	1	Distribution medium 70
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	2,403 lm	1	Distribution symmetrical 50
910925863563	BGP760 LED30-/830 II DW10 DGR 62	2,730 lm	1	Distribution wide 10
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	2,958 lm	1	Distribution extra wide 10
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	3,784 lm	1	Distribution wide 50
910925863567	BGP760 LED49-/740 II DX70 DGR 62	4,263 lm	1	Distribution extra wide 70
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	2,070 lm	-	Distribution medium 10
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	3,827 lm	-	Distribution medium 10
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	992 lm	-	Distribution medium 11
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	992 lm	-	Distribution medium 11
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	5,340 lm	-	Distribution medium 10
910925867978	BGP760 LED60-/740 I DX10 DGR CLO IACZ-4-D	4,988 lm	-	Distribution extra wide 10
910925867979	BGP760 LED60-/740 I DW50 BL1 DGR CLO IACZ	4,988 lm	-	Distribution wide 50
910925867987	BGP760 LED49-/740 II DM32 7042 MSP CLO-DD	3,588 lm	-	Distribution medium 32
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	4,900 lm	-	Distribution medium 32
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	21,360 lm	-	Distribution wide 10
910925866249	BGP763 LED300-/740 I DW50 DGR 62	25,200 lm	-	Distribution wide 50
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	22,100 lm	-	Distribution extra wide 10
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	29,920 lm	-	Distribution wide 10

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor
910925866253	BGP763 LED320-/740 II DX70 DGR 76	26,880 lm	-	Distribution extra wide 70
910925866494	BGP763 LED260-/740 I DM10 DGR 62 S	23,140 lm	-	Distribution medium 10
910925866498	BGP763 LED360-/740 I DM10 DGR 62 S	31,320 lm	-	Distribution medium 10
910925867852	BGP763 LED340-/740 I DW50 DGR D9 62 S	28,560 lm	-	Distribution medium 50
910925867984	BGP763 LED360-/740 I DX10 DGR CLO IACZ-4-	28,560 lm	-	Distribution extra wide 10
910925867985	BGP763 LED360-/740 I DW50 BL1 DGR IACZ-4-	20,060 lm	-	Distribution wide 50
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	2,790 lm	-	Distribution medium 11
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	2,790 lm	-	Distribution medium 11
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	4,050 lm	-	Distribution medium 10
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	6,660 lm	-	Distribution medium 50
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	8,084 lm	-	Distribution extra wide 10
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	9,790 lm	-	Distribution medium 10
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	5,096 lm	-	Distribution narrow 10
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	7,392 lm	-	Distribution symmetrical 50
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	5,096 lm	-	Distribution medium 11
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	7,476 lm	-	Distribution medium 10
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	4,550 lm	-	Distribution medium 11
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	6,688 lm	-	Distribution medium 70
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	5,400 lm	-	Distribution narrow 11
910925866241	BGP761 LED90-/740 II DW10 DGR 62	8,100 lm	-	Distribution wide 10
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	6,660 lm	-	Distribution medium 50
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	7,476 lm	-	Distribution medium 10
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	10,680 lm	-	Distribution medium 10
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	6,900 lm	-	Distribution wide 50
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	7,462 lm	-	Distribution medium 32

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	69 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	55 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	81 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	106 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	72 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866223	BGP762 LED169-/740 I DS50 DGR 62	98 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	61 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	85 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	100 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	66 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	91 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866229	BGP762 LED170-/830 II DW10 DGR 76	114 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	53 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	99 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866245	BGP762 LED200-/740 I DW50 DGR 62	114 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866246	BGP762 LED210-/740 II DX70 DGR 76	120 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	106 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	126 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	70 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	91 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO- D	138 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	126 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	138 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	138 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO- D	86 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO- D	138 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	6.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	9 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	11.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	13.8 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	17 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	16 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863563	BGP760 LED30-/830 II DW10 DGR 62	21 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	20 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	26 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925863567	BGP760 LED49-/740 II DX70 DGR 62	29.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	15 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	26 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	13.6 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	11.2 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	38 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	37 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	37 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	29.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	33.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	160 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866249	BGP763 LED300-/740 I DW50 DGR 62	176 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	150 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	196 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866253	BGP763 LED320-/740 II DX70 DGR 76	182 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	154 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	215 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	196 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	198 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	198 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	34 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	27.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	27 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	43.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	54 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	63 W	Surge protection level until 10 kV differential mode and 10 kV common mode
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	31.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	31.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	50 W	Surge protection level until 10 kV differential mode and 10 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	34 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	54 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	41 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866241	BGP761 LED90-/740 II DW10 DGR 62	51 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	43.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	49.5 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	72 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	70 W	Surge protection level until 6 kV differential mode and 8 kV common mode
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	50 W	Surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	Yes	Not applicable
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	Yes	Not applicable
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	Yes	Not applicable
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	Yes	50%
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	No	Not applicable
910925866223	BGP762 LED169-/740 I DS50 DGR 62	No	Not applicable
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	No	Not applicable
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	No	Not applicable
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	No	Not applicable
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	Yes	Not applicable
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	Yes	Not applicable
910925866229	BGP762 LED170-/830 II DW10 DGR 76	No	Not applicable
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	Yes	0% (digital)
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	Yes	Not applicable
910925866245	BGP762 LED200-/740 I DW50 DGR 62	No	Not applicable
910925866246	BGP762 LED210-/740 II DX70 DGR 76	No	Not applicable
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	No	Not applicable
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	No	Not applicable
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	Yes	Not applicable
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	No	Not applicable
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	Yes	Not applicable
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	Yes	0% (digital)
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	Yes	0% (digital)
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	Yes	50%
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Yes	0% (digital)
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	No	Not applicable
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	Yes	Not applicable
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	No	Not applicable
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	Yes	Not applicable
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	No	Not applicable
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	Yes	50%
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	No	Not applicable
910925863563	BGP760 LED30-/830 II DW10 DGR 62	No	Not applicable
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	No	Not applicable
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	No	Not applicable
910925863567	BGP760 LED49-/740 II DX70 DGR 62	No	Not applicable
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	Yes	50%
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	Yes	50%
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	Yes	Not applicable
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	Yes	Not applicable
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	Yes	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910925867978	BGP760 LED60-/740 I DX10 DGR CLO IACZ-4-D	Yes	0% (digital)
910925867979	BGP760 LED60-/740 I DW50 BL1 DGR CLO IACZ	Yes	0% (digital)
910925867987	BGP760 LED49-/740 II DM32 7042 MSP CLO-DD	Yes	50%
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	Yes	50%
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	No	Not applicable
910925866249	BGP763 LED300-/740 I DW50 DGR 62	No	Not applicable
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	No	Not applicable
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	No	Not applicable
910925866253	BGP763 LED320-/740 II DX70 DGR 76	No	Not applicable
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	Yes	Not applicable
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	Yes	Not applicable
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	Yes	Not applicable
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	No	0% (digital)
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	No	0% (digital)
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	Yes	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	Dark gray
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	Dark gray
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	Dark gray
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	Dark gray
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	Dark gray
910925866223	BGP762 LED169-/740 I DS50 DGR 62	Dark gray
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	Dark gray
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	Dark gray
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	Dark gray
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	Dark gray
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	Dark gray
910925866229	BGP762 LED170-/830 II DW10 DGR 76	Dark gray
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	Dark gray
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	Dark gray
910925866245	BGP762 LED200-/740 I DW50 DGR 62	Dark gray
910925866246	BGP762 LED210-/740 II DX70 DGR 76	Dark gray
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	Dark gray
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	Dark gray
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	Dark gray
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	Dark gray
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	Gray
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	Dark gray

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	Yes	Not applicable
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	No	Not applicable
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	No	Not applicable
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	No	Not applicable
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	Yes	50%
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	No	Not applicable
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	No	Not applicable
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	Yes	Not applicable
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	Yes	50%
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	Yes	Not applicable
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	Yes	50%
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	Yes	Not applicable
910925866241	BGP761 LED90-/740 II DW10 DGR 62	No	Not applicable
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	Yes	Not applicable
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	No	Not applicable
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	Yes	Not applicable
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	Yes	0% (digital)
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	Yes	50%

Order Code	Full Product Name	Housing Color
910925867987	BGP760 LED49-/740 II DM32 7042 MSP CLO-DD	Gray
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	Dark gray
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	Dark gray
910925866249	BGP763 LED300-/740 I DW50 DGR 62	Dark gray
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	Dark gray
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	Dark gray
910925866253	BGP763 LED320-/740 II DX70 DGR 76	Dark gray
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	Dark gray
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	Dark gray
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	Dark gray
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	Dark gray
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	Dark gray
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	Dark gray
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	Dark gray
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	Dark gray
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	Dark gray

Approval and Application

Order Code	Full Product Name	Glow-wire test
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	-
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	-
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	-
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	-
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	-
910925866223	BGP762 LED169-/740 I DS50 DGR 62	-
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	-
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	-
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	-
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	-
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	-
910925866229	BGP762 LED170-/830 II DW10 DGR 76	-
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	-
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	-
910925866245	BGP762 LED200-/740 I DW50 DGR 62	-
910925866246	BGP762 LED210-/740 II DX70 DGR 76	-
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	-
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	-
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	-
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	-
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	-
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	-
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	-
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	-
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	-
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	-
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	Temperature 650 °C, duration 5 s
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	Temperature 650 °C, duration 5 s
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	Temperature 650 °C, duration 5 s

Order Code	Full Product Name	Housing Color
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	Dark gray
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	Dark gray
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	Dark gray
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	Dark gray
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	Dark gray
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	Dark gray
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	Dark gray
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	Dark gray
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	Dark gray
910925866241	BGP761 LED90-/740 II DW10 DGR 62	Dark gray
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	Dark gray
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	Dark gray
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	Dark gray
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	Dark gray
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	Gray

Order Code	Full Product Name	Glow-wire test
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	Temperature 650 °C, duration 5 s
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	Temperature 650 °C, duration 5 s
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	Temperature 650 °C, duration 5 s
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	Temperature 650 °C, duration 5 s
910925863563	BGP760 LED30-/830 II DW10 DGR 62	Temperature 650 °C, duration 5 s
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	Temperature 650 °C, duration 5 s
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	Temperature 650 °C, duration 5 s
910925863567	BGP760 LED49-/740 II DX70 DGR 62	Temperature 650 °C, duration 5 s
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	-
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	-
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	-
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	-
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	-
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	-
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	-
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	-
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	-
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	-
910925866249	BGP763 LED300-/740 I DW50 DGR 62	-
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	-
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	-
910925866253	BGP763 LED320-/740 II DX70 DGR 76	-
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	-
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	-

Order Code	Full Product Name	Glow-wire test
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	-
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	-
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	-
910925865604	BGP761 LED45-/4S/518 II DM11 DGR 62	-
910925865605	BGP761 LED45-/4S/420 II DM11 DGR 62	-
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	-
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	-
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	-
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	-
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	-
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	-

Order Code	Full Product Name	Glow-wire test
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	-
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	-
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	-
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	-
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	-
910925866241	BGP761 LED90-/740 II DW10 DGR 62	-
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	-
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	-
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	-
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	-
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	-


Product Data

Order Code	Full Product Name	Product family code
910925865607	BGP762 LED95-4S/518 II DM11 DGR 62	BGP762
910925865608	BGP762 LED95-4S/420 II DM11 DGR 62	BGP762
910925866220	BGP762 LED120-/830 II DN11 DGR D11 76	BGP762
910925866221	BGP762 LED159-/830 II DM70 DGR DDF27 D18	BGP762
910925866222	BGP762 LED129-/740 I DM11 DGR 32-48	BGP762
910925866223	BGP762 LED169-/740 I DS50 DGR 62	BGP762
910925866224	BGP762 LED110-/740 I DN10 DGR 32-48	BGP762
910925866225	BGP762 LED149-/740 I DM50 DGR 32-48	BGP762
910925866226	BGP762 LED180-/740 I DX10 DGR 32-48	BGP762
910925866227	BGP762 LED100-/830 II DM11 DGR D9 62	BGP762
910925866228	BGP762 LED139-/830 II DM11 DGR D9 62	BGP762
910925866229	BGP762 LED170-/830 II DW10 DGR 76	BGP762
910925866243	BGP762 LW10 LED95-/740 I DM10 DGR SRB 32	BGP762
910925866244	BGP762 LED169-/740 I DS50 DGR SRB 62	BGP762
910925866245	BGP762 LED200-/740 I DW50 DGR 62	BGP762
910925866246	BGP762 LED210-/740 II DX70 DGR 76	BGP762
910925866247	BGP762 LED190-/740 II DW10 DGR SRG10 62	BGP762
910925866252	BGP762 LED220-/740 II DW10 DGR SRG10 62	BGP762
910925866492	BGP762 LED120/740 I DM10 DGR 62 S	BGP762
910925866493	BGP762 LED159/740 I DM10 DGR 62 S	BGP762
910925866963	BGP762 LED239/740 II DM32 7042 MSP CLO-D	BGP762
910925867851	BGP762 LED220/740 I DW50 DGR D9 62 S	BGP762
910925867982	BGP762 LED239/740 I DX10 DGR CLO IACZ-4-	BGP762
910925867983	BGP762 LED239/740 I DW50 BL1 DGR CLO IAC	BGP762
910925867989	BGP762 LED149/740 II DM32 7042 MSP CLO-D	BGP762
910925867990	BGP762 LED239/740 II DM32 7042 MSP CLO-D	BGP762
910925863554	BGP760 LED10-/740 I DM10 DGR 32-48	BGP760
910925863555	BGP760 LED12-/830 II DM11 DGR D9 62	BGP760
910925863556	BGP760 LED14-/740 I DN10 DGR 32-48	BGP760
910925863557	BGP760 LED16-/830 II DN11 DGR D11 62	BGP760
910925863560	BGP760 LED22-/740 I DM50 DGR 32-48	BGP760
910925863561	BGP760 LED24-/830 II DM70 DGR DDF27 D18	BGP760
910925863562	BGP760 LED27-/740 I DS50 DGR 32-48	BGP760
910925863563	BGP760 LED30-/830 II DW10 DGR 62	BGP760
910925863564	BGP760 LED34-/740 I DX10 DGR 32-48	BGP760
910925863566	BGP760 LED44-/740 I DW50 DGR 32-48	BGP760
910925863567	BGP760 LED49-/740 II DX70 DGR 62	BGP760


Order Code	Full Product Name	Product family code
910925864083	BGP760 LED24-/740 I DM10 DGR DDF27 D18 S	BGP760
910925864084	BGP760 LED44-/740 I DM10 DGR DDF27 D18 S	BGP760
910925866306	BGP760 LED16-/518 II DM11 DGR 62 S	BGP760
910925866307	BGP760 LED16-/420 II DM11 DGR 62 S	BGP760
910925866495	BGP760 LED60-/740 I DM10 DGR 62 S	BGP760
910925867978	BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D	BGP760
910925867979	BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ	BGP760
910925867987	BGP760 LED49/740 II DM32 7042 MSP CLO-DD	BGP760
910925867995	BGP760 LED-HB/740 II DM32 DGR MSP CLO D1	BGP760
910925866248	BGP763 LED240-/830 II DW10 DGR SRG10 62	BGP763
910925866249	BGP763 LED300-/740 I DW50 DGR 62	BGP763
910925866250	BGP763 LED260-/740 I DX10 DGR 32-48	BGP763
910925866251	BGP763 LED340-/740 II DW10 DGR SRG10 62	BGP763
910925866253	BGP763 LED320-/740 II DX70 DGR 76	BGP763
910925866494	BGP763 LED260/740 I DM10 DGR 62 S	BGP763
910925866498	BGP763 LED360/740 I DM10 DGR 62 S	BGP763
910925867852	BGP763 LED340/740 I DW50 DGR D9 62 S	BGP763
910925867984	BGP763 LED360/740 I DX10 DGR CLO IACZ-4-	BGP763
910925867985	BGP763 LED360/740 I DW50 BL1 DGR IACZ-4-	BGP763
910925865604	BGP761 LED45-4S/518 II DM11 DGR 62	BGP761
910925865605	BGP761 LED45-4S/420 II DM11 DGR 62	BGP761
910925866230	BGP761 LED45-/740 I DM10 DGR 32-48	BGP761
910925866231	BGP761 LED74-/740 I DM50 DGR 32-48	BGP761
910925866232	BGP761 LED94-/740 I DX10 DGR 32-48	BGP761
910925866233	BGP761 LED109-/740 I DM10 DGR DDF27 D18	BGP761
910925866234	BGP761 LED55-/740 I DN10 DGR 32-48	BGP761
910925866235	BGP761 LED84-/740 I DS50 DGR 32-48	BGP761
910925866236	BGP761 LED55-/740 I DM11 DGR SRB 62	BGP761
910925866237	BGP761 LED84-/740 I DM10 DGR DDF27 D18 S	BGP761
910925866238	BGP761 LED50-/830 II DM11 DGR D9 62	BGP761
910925866239	BGP761 LED79-/830 II DM70 DGR DDF27 D18	BGP761
910925866240	BGP761 LED59-/830 II DN11 DGR D11 62	BGP761
910925866241	BGP761 LED90-/740 II DW10 DGR 62	BGP761
910925866242	BGP761 LED74-/740 I DM50 DGR SRB 62	BGP761
910925866496	BGP761 LED84/740 I DM10 DGR 62 S	BGP761
910925866497	BGP761 LED119/740 I DM10 DGR 62 S	BGP761
910925867981	BGP761 LED119/740 I DW50 BL1 DGR CLO IAC	BGP761

Order Code	Full Product Name	Product family code
910925867988	BGP761 LED84/740 II DM32 7042 MSP CLO-DD	BGP761


Polar Wide Diagrams




Polar Normal (separate) - BGP762I - 910925866229




Polar Normal (separate) - BGP761I - 910925866232




Polar Normal (separate) - BGP761I - 910925866242




Polar Normal (separate) - BGP762I - 910925866225



Polar Normal (separate) - BGP763I - 910925866249



Polar Normal (separate) - BGP762I - 910925866228



Polar Normal (separate) - BGP763I - 910925866251




Polar Normal (separate) - BGP762I - 910925866220




Polar Normal (separate) - BGP762I - 910925866221




Polar Wide Diagrams




Polar Normal (separate) - BGP762I - 910925866246




Polar Normal (separate) - BGP761I - 910925866497




Polar Normal (separate) - BGP762I - 910925866492




Polar Normal (separate) - BGP760I - 910925863562




Polar Normal (separate) - BGP760I - 910925863561




Polar Normal (separate) - BGP760I - 910925863564



Polar Normal (separate) - BGP760I - 910925863554




Polar Normal (separate) - BGP760I - 910925863567




Polar Normal (separate) - BGP760I - 910925863563


Polar Wide Diagrams




Polar Normal (separate) - BGP760I - 910925863566




Polar Normal (separate) - BGP760I - 910925863560




Polar Normal (separate) - BGP760I - 910925864083




Polar Normal (separate) - BGP762I - 910925866223




Polar Normal (separate) - BGP761I - 910925866230




Polar Normal (separate) - BGP761I - 910925866238



Polar Normal (separate) - BGP763I - 910925866250




Polar Normal (separate) - BGP762I - 910925866227




Polar Normal (separate) - BGP761I - 910925866233


Polar Wide Diagrams




Polar Normal (separate) - BGP762I - 910925866224




Polar Normal (separate) - BGP761I - 910925866235




Polar Normal (separate) - BGP761I - 910925866241




Polar Normal (separate) - BGP762I - 910925866222




Polar Normal (separate) - BGP761I - 910925866234




Polar Normal (separate) - BGP762I - 910925866247



Polar Normal (separate) - BGP762I - 910925866252




Polar Normal (separate) - BGP763I -
910925866248




Polar Normal (separate) - BGP762I - 910925866226


Polar Wide Diagrams




Polar Normal (separate) - BGP761I - 910925866237




Polar Normal (separate) - BGP761I - 910925866239




Polar Normal (separate) - BGP761I - 910925866240




Polar Normal (separate) - BGP762I - 910925866245




Polar Normal (separate) - BGP763I - 910925866253




Polar Normal (separate) - BGP760I - 910925863556



Polar Normal (separate) - BGP760I - 910925863557




Polar Normal (separate) - BGP760I - 910925863555




Polar Normal (separate) - BGP760I - 910925864084


Polar Wide Diagrams




Polar Normal (separate) - BGP760I - 910925868855




Polar Normal (separate) - BGP762I - 910925866493




Polar Normal (separate) - BGP763I - 910925866494




Polar Normal (separate) - BGP760I - 910925866495




Polar Normal (separate) - BGP763I - 910925866498




Polar Normal (separate) - BGP762I - 910925866963



Polar Normal (separate) - BGP762I - 910925868786




Polar Normal (separate) - BGP763I - 910925867852




Polar Normal (separate) - BGP762I - 910925867851


Polar Wide Diagrams




Polar Normal (separate) - BGP760I - 910925867978




Polar Normal (separate) - BGP760I - 910925867979




Polar Normal (separate) - BGP762I - 910925867982




Polar Normal (separate) - BGP762I - 910925867983




Polar Normal (separate) - BGP761I - 910925867981



Polar Normal (separate) - BGP763I - 910925867984



Polar Normal (separate) - BGP761I - 910925867988



Polar Normal (separate) - BGP760I - 910925867995

