



An Easier Way to More Savings

SmartBright LED Batten G2

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

Benefits

- More slim: One piece PC extrusion housing
- Easier for installation: Central and side cable entry
- More types: Interconnectable version – Turnkable version added BN013C (NEW)

Features

- One piece PC extrusion housing: Single piece Integral design for better aesthetics
- Central and side cable entry Ready solution for both new point and replacement
- Newly designed male/female socket Enables continuous light line
- 2,000lm@4ft and 1,000lm@2ft Greater brightness
- CRI 80, SDCM <6, 100lm/W Superior light quality combined with good energy savings
- Uniform Light Optimal optical design to ensure no spottiness
- L70 25k hours Reliable long lasting solution

Application

- General lighting, indoor
- Indoor car park, industry, shop, office, school
- Long distance linear lighting


SmartBright LED Batten G2

Versions



SmartBright LED batten G2 BN012C

Dimensional drawing



Product details



SmartBright LED batten G2
BN012C middle



SmartBright LED batten G2
BN012C side

SmartBright LED Batten G2

