



# Streamlined lights for brighter streets

## RoadFlair Pro

Municipalities value energy saving more than ever, as energy price hikes put increasing pressure on the budgets. Street lighting consumes substantial energy, so large-scale upgrades to energy-efficient LED streetlights are fundamental to cities' cost-saving efforts. RoadFlair Pro has been upgraded to minimize costs while maximizing efficacy, safety, and functionality. And the best part - RoadFlair Pro offers a streamlined design, so it maintains an attractive aesthetic on city streets. These streetlights not only look good, they also offer excellent performance. Future-proof technology combines with high efficacy (160 lm/W and 200 lm/W), innovative design, and smart connectivity in a light that makes your street look brighter and better.

### Benefits

- High efficacy
- Appealing and sustainable design
- Connected and system-ready
- Higher durability and reliability
- World-class photometric design
- Equipped with a Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation, and spare part information

### Features

- 170+ lm/W system efficacy (up to 300W)
- 200 lm/W system efficacy (up to 100W)
- Long service lifetime 100Khrs L80@Ta 35°C
- With 10kV or 15kV Surge protection Device
- Ready to be paired with lighting management systems and sensors

# RoadFlair Pro

## Application

- Motorways, inter-urban main roads, boulevards and avenues, roundabouts, pedestrian crossings
- Residential streets, side streets, squares, parks, cycle and pedestrian paths, playgrounds
- Parking areas, industrial areas, petrol stations, rail yards, airports, harbors, waterways

## Specifications

|                                    |                                                  |
|------------------------------------|--------------------------------------------------|
| Material                           | Housing: Die-cast Aluminum                       |
|                                    | Optic cover: Polycarbonate                       |
| Light Source                       | 5050 LED's                                       |
| Installation                       | Side entry 42~60mm<br>optional adjustable spigot |
| Luminous flux                      | system flux up to 52500 lumens                   |
| Correlated color temperature - CCT | 5700K                                            |
|                                    | 4000K                                            |
|                                    | 3000K                                            |
|                                    | 2700K                                            |
|                                    | 2200K                                            |
| Luminaire efficacy                 | 5700K: 160lm/W                                   |
|                                    | 4000K: 170lm/W                                   |
|                                    | 3000K: 165lm/W                                   |
|                                    | 2700K: 150lm/W                                   |
|                                    | 2200K: 135lm/W                                   |
|                                    | 4000K: 200lm/W (option)                          |

|                             |                                                          |
|-----------------------------|----------------------------------------------------------|
| Color Rendering index - 70  |                                                          |
| CRI                         |                                                          |
| Power                       | up to 300W                                               |
| Mains Voltage               | 220-240V / 50-60Hz 120-277 /60-60Hz available as option. |
| Control system input        | DALI/1-10V/D4i options                                   |
| Dimming                     | PSR: 1-10V                                               |
|                             | PSD: Dali                                                |
|                             | PSC: Coded Mains                                         |
|                             | PSA: 1-10V, AOC                                          |
|                             | PSRD: 1-10V, Step dimming, AOC                           |
|                             | SR: D4i                                                  |
| Operating Temperature range |                                                          |
| -40 to +50C Ta              |                                                          |
| Ingress protection          | IP66                                                     |
| Certification               | IECEE CB, CE, CQC, RCM, ZD4i                             |

## Versions



RoadFlair Pro

Versions



RoadFlair Pro

RoadFlair Pro

RoadFlair Pro

RoadFlair Pro




RoadFlair Pro

RoadFlair Pro









RoadFlair Pro

RoadFlair Pro

Dimensional drawing




Dimensional drawing



# RoadFlair Pro

## Dimensional drawing



| General Information          |            |
|------------------------------|------------|
| Driver included              | Yes        |
| Mechanical and Housing       |            |
| Optical cover type           | Clear dome |
| Mech. impact protection code | IK08       |
| Ingress protection code      | IP66       |
| Approval and Application     |            |
| CE mark                      | Yes        |
| Flammability mark            | -          |

## General Information

| Order Code   | Full Product Name                        | Service tag |
|--------------|------------------------------------------|-------------|
| 911401652108 | BRP591 LED115/NW 70W DW2 PSA GC          | Yes         |
| 911401652208 | BRP591 LED116/NW 70W DM PSA GM           | Yes         |
| 911401652508 | BRP591 LED129/NW 80W DW2 PSA GC          | Yes         |
| 911401652608 | BRP591 LED130/NW 80W DM PSA GM           | Yes         |
| 911401653908 | BRP591 LED142/NW 90W DW2 PSR GC          | Yes         |
| 911401654008 | BRP591 LED143/NW 90W DM PSR GM           | Yes         |
| 911401656708 | BRP591 LED23/NW 15W DWP II PSD P7L8ANZ   | Yes         |
| 911401656208 | BRP593 LED223/NW 138W DWV II PSDP7L15ANZ | Yes         |
| 911401657808 | BRP593 LED240/NW 150W DW2 PSA P7 GC      | Yes         |
| 911401658208 | BRP593 LED242/NW 150W DM PSA P7 GM       | Yes         |
| 911401659108 | BRP593 LED61/NW 35W DWP3 II PSD P7L8ANZ  | Yes         |
| 911401661408 | BRP595 LED403/NW 250W DM PSA GM          | Yes         |
| 911401661508 | BRP595 LED405/NW 250W DW2 PSA GC         | Yes         |
| 911401662008 | BRP595 LED427/NW 260W DW2 PSA GC         | Yes         |
| 911401662108 | BRP595 LED432/NW 260W DM PSA GM          | Yes         |
| 911401662408 | BRP595 LED454/NW 280W DW2 PSA GC         | Yes         |
| 911401662508 | BRP595 LED459/NW 280W DM PSA GM          | Yes         |
| 911401663608 | BRP595 LED484/NW 300W DW2 PSR GC         | Yes         |
| 911401664008 | BRP595 LED489/NW 300W DM PSR GM          | Yes         |
| 911401671508 | BRP595 LED130/NW 65W DW2 PSRD O5         | Yes         |
| 911401672008 | BRP595 LED195/NW 100W DW2 PSRD O5        | Yes         |
| 911401663208 | BRP595 LED480/NW 300W DW2 PSA P7 GC      | Yes         |
| 911401663808 | BRP595 LED485/NW 300W DM PSA P7 GM       | Yes         |
| 911401649109 | BRP593 LED263/NW 150W DW2 PSA GC         | Yes         |
| 911401649209 | BRP593 LED250/WW 150W DW2 PSA GC         | Yes         |
| 911401672509 | BRP593 LED244/NW 150W DM PSRD PE GM      | -           |
| 911401673409 | BRP593 LED240/NW 150W DM PSD PE GM       | -           |
| 911401674009 | BRP593 LED240/NW 150W DM GL PE GM        | -           |
| 911401673609 | BRP595 LED479/NW 300W DM SR 7TSB PE GM   | -           |
| 911401673209 | BRP591 LED142/NW 90W DM PSA P7 PE GM     | -           |
| 911401672909 | BRP594 LED389/NW 240W DM PSA P7 PE GM    | -           |
| 911401648709 | BRP591 LED147/NW 85W DW2 PSA GC          | Yes         |
| 911401648809 | BRP591 LED136/WW 80W DW2 PSA GC          | Yes         |
| 911401672709 | BRP591 LED143/NW 90W DM PSRD PE GM       | -           |
| 911401673509 | BRP591 LED65/NW 40W DM PSD PE GM         | -           |
| 911401674209 | BRP591 LED139/NW 90W DM GL PE GM         | -           |
| 911401674409 | BRP591 LED143/NW 90W DM PSR PE GM        | -           |
| 911401661608 | BRP594 LED388/NW 240W DW2 PSA P7 GC      | Yes         |
| 911401661708 | BRP594 LED392/NW 240W DM PSA P7 GM       | Yes         |

| Order Code   | Full Product Name                      | Service tag |
|--------------|----------------------------------------|-------------|
| 911401673109 | BRP592 LED192/NW 120W DM PSA P7 PE GM  | -           |
| 911401673009 | BRP593 LED240/NW 150W DM PSA P7 PE GM  | -           |
| 911401664108 | BRP595 LED489/NW 300W DM SR P7T SRB GM | Yes         |
| 911401672809 | BRP595 LED479/NW 300W DM PSA P7 PE GM  | -           |
| 911401648909 | BRP592 LED209/NW 120W DW2 PSA GC       | Yes         |
| 911401649009 | BRP592 LED193/WW 120W DW2 PSA GC       | Yes         |
| 911401672609 | BRP592 LED194/NW 120W DM PSRD PE GM    | -           |
| 911401674109 | BRP592 LED163/NW 100W DM GL PE GM      | -           |
| 911401674309 | BRP592 LED203/NW 130W DM PSR PE GM     | -           |
| 911401649309 | BRP594 LED423/NW 240W DW2 PSA GC       | Yes         |
| 911401649409 | BRP594 LED402/WW 240W DW2 PSA GC       | Yes         |
| 911401672409 | BRP594 LED389/NW 240W DM PSRD PE GM    | -           |
| 911401673909 | BRP594 LED358/NW 220W DM GL PE GM      | -           |
| 911401649509 | BRP595 LED525/NW 300W DW2 PSA GC       | Yes         |
| 911401649609 | BRP595 LED499/WW 300W DW2 PSA GC       | Yes         |
| 911401672309 | BRP595 LED487/NW 300W DM PSRD PE GM    | -           |
| 911401673309 | BRP595 LED479/NW 300W DM PSD PE GM     | -           |
| 911401673809 | BRP595 LED479/NW 300W DM GL PE GM      | -           |
| 911401673709 | BRP593 LED240/NW 150W DM SR 7TSB PE GM | -           |
| 911401659508 | BRP594 LED298/NW 180W DW2 PSA GC       | Yes         |
| 911401659608 | BRP594 LED301/NW 180W DM PSA GM        | Yes         |
| 911401659908 | BRP594 LED326/NW 200W DW2 PSA GC       | Yes         |
| 911401660008 | BRP594 LED329/NW 200W DM PSA GM        | Yes         |
| 911401660308 | BRP594 LED352/NW 220W DW2 PSA GC       | Yes         |
| 911401660408 | BRP594 LED356/NW 220W DM PSA GM        | Yes         |
| 911401661008 | BRP594 LED388/NW 240W DW2 PSA GC       | Yes         |
| 911401661108 | BRP594 LED392/NW 240W DM PSA GM        | Yes         |
| 911401658808 | BRP593 LED244/NW 150W DM SR P7T SRB GM | Yes         |
| 911401654508 | BRP592 LED165/NW 100W DW2 PSA GC       | Yes         |
| 911401654608 | BRP592 LED167/NW 100W DM PSA GM        | Yes         |
| 911401655008 | BRP592 LED192/NW 120W DW2 PSA GC       | Yes         |
| 911401655308 | BRP592 LED195/NW 120W DM PSA GM        | Yes         |
| 911401655808 | BRP592 LED201/NW 130W DW2 PSR GC       | Yes         |
| 911401655908 | BRP592 LED203/NW 130W DM PSR GM        | Yes         |
| 911401656508 | BRP593 LED227/NW 140W DW2 PSA GC       | Yes         |
| 911401656608 | BRP593 LED229/NW 140W DM PSA GM        | Yes         |
| 911401658708 | BRP593 LED243/NW 150W DW2 PSR GC       | Yes         |
| 911401658908 | BRP593 LED245/NW 150W DM PSR GM        | Yes         |

Light Technical

| Order Code   | Full Product Name               | Light source color      | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Flux |
|--------------|---------------------------------|-------------------------|------------------------------------|-----------------------------|---------------|
| 911401652108 | BRP591 LED115/NW 70W DW2 PSA GC | 740<br>neutral<br>white | 4000 K                             | >70                         | 11,500 lm     |
| 911401652208 | BRP591 LED116/NW 70W DM PSA GM  | 740<br>neutral<br>white | 4000 K                             | >70                         | 11,600 lm     |

| Order Code   | Full Product Name               | Light source color      | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Flux |
|--------------|---------------------------------|-------------------------|------------------------------------|-----------------------------|---------------|
| 911401652508 | BRP591 LED129/NW 80W DW2 PSA GC | 740<br>neutral<br>white | 4000 K                             | >70                         | 12,900 lm     |
| 911401652608 | BRP591 LED130/NW 80W DM PSA GM  | 740<br>neutral<br>white | 4000 K                             | >70                         | 13,000 lm     |

| Order Code   | Full Product Name                                 | Light source color      | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Flux |
|--------------|---------------------------------------------------|-------------------------|------------------------------------|-----------------------------|---------------|
| 911401653908 | BRP591<br>LED142/NW 90W<br>DW2 PSR GC             | 740<br>neutral<br>white | 4000 K                             | >70                         | 14,200 lm     |
| 911401654008 | BRP591<br>LED143/NW 90W<br>DM PSR GM              | 740<br>neutral<br>white | 4000 K                             | >70                         | 14,300 lm     |
| 911401656708 | BRP591 LED23/NW<br>15W DWP II PSD<br>P7L8ANZ      | 740<br>neutral<br>white | 4000 K                             | >70                         | 2,300 lm      |
| 911401656208 | BRP593<br>LED223/NW 138W<br>DWV II<br>PSDP7L15ANZ | 740<br>neutral<br>white | 4000 K                             | >70                         | 22,300 lm     |
| 911401657808 | BRP593<br>LED240/NW 150W<br>DW2 PSA P7 GC         | 740<br>neutral<br>white | 4000 K                             | >70                         | 24,000 lm     |
| 911401658208 | BRP593<br>LED242/NW 150W<br>DM PSA P7 GM          | 740<br>neutral<br>white | 4000 K                             | >70                         | 24,200 lm     |
| 911401659108 | BRP593 LED61/NW<br>35W DWP3 II PSD<br>P7L8ANZ     | 740<br>neutral<br>white | 4000 K                             | >70                         | 6,100 lm      |
| 911401661408 | BRP595<br>LED403/NW 250W<br>DM PSA GM             | 740<br>neutral<br>white | 4000 K                             | >70                         | 40,300 lm     |
| 911401661508 | BRP595<br>LED405/NW 250W<br>DW2 PSA GC            | 740<br>neutral<br>white | 4000 K                             | >70                         | 40,500 lm     |
| 911401662008 | BRP595<br>LED427/NW 260W<br>DW2 PSA GC            | 740<br>neutral<br>white | 4000 K                             | >70                         | 42,700 lm     |
| 911401662108 | BRP595<br>LED432/NW 260W<br>DM PSA GM             | 740<br>neutral<br>white | 4000 K                             | >70                         | 43,200 lm     |
| 911401662408 | BRP595<br>LED454/NW 280W<br>DW2 PSA GC            | 740<br>neutral<br>white | 4000 K                             | >70                         | 45,400 lm     |
| 911401662508 | BRP595<br>LED459/NW 280W<br>DM PSA GM             | 740<br>neutral<br>white | 4000 K                             | >70                         | 45,900 lm     |
| 911401663608 | BRP595<br>LED484/NW 300W<br>DW2 PSR GC            | 740<br>neutral<br>white | 4000 K                             | >70                         | 48,400 lm     |
| 911401664008 | BRP595<br>LED489/NW 300W<br>DM PSR GM             | 740<br>neutral<br>white | 4000 K                             | >70                         | 48,900 lm     |
| 911401671508 | BRP595<br>LED130/NW 65W<br>DW2 PSRD O5            | 740<br>neutral<br>white | 4000 K                             | >70                         | 13,000 lm     |

| Order Code   | Full Product Name                            | Light source color      | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Flux |
|--------------|----------------------------------------------|-------------------------|------------------------------------|-----------------------------|---------------|
| 911401672008 | BRP595<br>LED195/NW 100W<br>DW2 PSRD O5      | 740<br>neutral<br>white | 4000 K                             | >70                         | 19,500 lm     |
| 911401663208 | BRP595<br>LED480/NW 300W<br>DW2 PSA P7 GC    | 740<br>neutral<br>white | 4000 K                             | >70                         | 48,000 lm     |
| 911401663808 | BRP595<br>LED485/NW 300W<br>DM PSA P7 GM     | 740<br>neutral<br>white | 4000 K                             | >70                         | 48,500 lm     |
| 911401649109 | BRP593<br>LED263/NW 150W<br>DW2 PSA GC       | 740<br>neutral<br>white | 4000 K                             | 70                          | 26,300 lm     |
| 911401649209 | BRP593<br>LED250/WW 150W<br>DW2 PSA GC       | 730<br>warm<br>white    | 3000 K                             | 70                          | 25,000 lm     |
| 911401672509 | BRP593<br>LED244/NW 150W<br>DM PSRD PE GM    | 740<br>neutral<br>white | 4000 K                             | >70                         | 24,400 lm     |
| 911401673409 | BRP593<br>LED240/NW 150W<br>DM PSD PE GM     | 740<br>neutral<br>white | 4000 K                             | >70                         | 24,000 lm     |
| 911401674009 | BRP593<br>LED240/NW 150W<br>DM GL PE GM      | 740<br>neutral<br>white | 4000 K                             | >70                         | 24,000 lm     |
| 911401673609 | BRP595<br>LED479/NW 300W<br>DM SR 7TSB PE GM | 740<br>neutral<br>white | 4000 K                             | >70                         | 47,900 lm     |
| 911401673209 | BRP591<br>LED142/NW 90W<br>DM PSA P7 PE GM   | 740<br>neutral<br>white | 4000 K                             | >70                         | 14,200 lm     |
| 911401672909 | BRP594<br>LED389/NW 240W<br>DM PSA P7 PE GM  | 740<br>neutral<br>white | 4000 K                             | >70                         | 38,900 lm     |
| 911401648709 | BRP591 LED147/NW<br>85W DW2 PSA GC           | 740<br>neutral<br>white | 4000 K                             | 70                          | 14,700 lm     |
| 911401648809 | BRP591<br>LED136/WW 80W<br>DW2 PSA GC        | 730<br>warm<br>white    | 3000 K                             | 70                          | 13,600 lm     |
| 911401672709 | BRP591<br>LED143/NW 90W<br>DM PSRD PE GM     | 740<br>neutral<br>white | 4000 K                             | >70                         | 14,300 lm     |
| 911401673509 | BRP591 LED65/NW<br>40W DM PSD PE<br>GM       | 740<br>neutral<br>white | 4000 K                             | >70                         | 6,500 lm      |
| 911401674209 | BRP591<br>LED139/NW 90W<br>DM GL PE GM       | 740<br>neutral<br>white | 4000 K                             | >70                         | 13,900 lm     |

| Order Code   | Full Product Name                            | Light source color      | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Flux |
|--------------|----------------------------------------------|-------------------------|------------------------------------|-----------------------------|---------------|
| 911401674409 | BRP591<br>LED143/NW 90W<br>DM PSR PE GM      | 740<br>neutral<br>white | 4000 K                             | >70                         | 14,300 lm     |
| 911401661608 | BRP594<br>LED388/NW 240W<br>DW2 PSA P7 GC    | 740<br>neutral<br>white | 4000 K                             | >70                         | 38,800 lm     |
| 911401661708 | BRP594<br>LED392/NW 240W<br>DM PSA P7 GM     | 740<br>neutral<br>white | 4000 K                             | >70                         | 39,200 lm     |
| 911401673109 | BRP592<br>LED192/NW 120W<br>DM PSA P7 PE GM  | 740<br>neutral<br>white | 4000 K                             | >70                         | 19,200 lm     |
| 911401673009 | BRP593<br>LED240/NW 150W<br>DM PSA P7 PE GM  | 740<br>neutral<br>white | 4000 K                             | >70                         | 24,000 lm     |
| 911401664108 | BRP595<br>LED489/NW 300W<br>DM SR P7T SRB GM | 740<br>neutral<br>white | 4000 K                             | >70                         | 48,900 lm     |
| 911401672809 | BRP595<br>LED479/NW 300W<br>DM PSA P7 PE GM  | 740<br>neutral<br>white | 4000 K                             | >70                         | 47,900 lm     |
| 911401648909 | BRP592<br>LED209/NW 120W<br>DW2 PSA GC       | 740<br>neutral<br>white | 4000 K                             | 70                          | 20,900 lm     |
| 911401649009 | BRP592<br>LED193/WW 120W<br>DW2 PSA GC       | 730<br>warm<br>white    | 3000 K                             | 70                          | 19,300 lm     |
| 911401672609 | BRP592<br>LED194/NW 120W<br>DM PSRD PE GM    | 740<br>neutral<br>white | 4000 K                             | >70                         | 19,400 lm     |
| 911401674109 | BRP592<br>LED163/NW 100W<br>DM GL PE GM      | 740<br>neutral<br>white | 4000 K                             | >70                         | 16,300 lm     |
| 911401674309 | BRP592<br>LED203/NW 130W<br>DM PSR PE GM     | 740<br>neutral<br>white | 4000 K                             | >70                         | 20,300 lm     |
| 911401649309 | BRP594<br>LED423/NW 240W<br>DW2 PSA GC       | 740<br>neutral<br>white | 4000 K                             | 70                          | 42,300 lm     |
| 911401649409 | BRP594<br>LED402/WW 240W<br>DW2 PSA GC       | 730<br>warm<br>white    | 3000 K                             | 70                          | 40,200 lm     |
| 911401672409 | BRP594<br>LED389/NW 240W<br>DM PSRD PE GM    | 740<br>neutral<br>white | 4000 K                             | >70                         | 38,900 lm     |
| 911401673909 | BRP594<br>LED358/NW 220W<br>DM GL PE GM      | 740<br>neutral<br>white | 4000 K                             | >70                         | 35,800 lm     |

| Order Code   | Full Product Name                            | Light source color      | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Flux |
|--------------|----------------------------------------------|-------------------------|------------------------------------|-----------------------------|---------------|
| 911401649509 | BRP595<br>LED525/NW 300W<br>DW2 PSA GC       | 740<br>neutral<br>white | 4000 K                             | 70                          | 52,500 lm     |
| 911401649609 | BRP595<br>LED499/WW 300W<br>DW2 PSA GC       | 730<br>warm<br>white    | 3000 K                             | 70                          | 49,900 lm     |
| 911401672309 | BRP595<br>LED487/NW 300W<br>DM PSRD PE GM    | 740<br>neutral<br>white | 4000 K                             | >70                         | 48,700 lm     |
| 911401673309 | BRP595<br>LED479/NW 300W<br>DM PSD PE GM     | 740<br>neutral<br>white | 4000 K                             | >70                         | 47,900 lm     |
| 911401673809 | BRP595<br>LED479/NW 300W<br>DM GL PE GM      | 740<br>neutral<br>white | 4000 K                             | >70                         | 47,900 lm     |
| 911401673709 | BRP593<br>LED240/NW 150W<br>DM SR 7TSB PE GM | 740<br>neutral<br>white | 4000 K                             | >70                         | 24,000 lm     |
| 911401659508 | BRP594<br>LED298/NW 180W<br>DW2 PSA GC       | 740<br>neutral<br>white | 4000 K                             | >70                         | 29,800 lm     |
| 911401659608 | BRP594<br>LED301/NW 180W<br>DM PSA GM        | 740<br>neutral<br>white | 4000 K                             | >70                         | 30,100 lm     |
| 911401659908 | BRP594<br>LED326/NW 200W<br>DW2 PSA GC       | 740<br>neutral<br>white | 4000 K                             | >70                         | 32,600 lm     |
| 911401660008 | BRP594<br>LED329/NW 200W<br>DM PSA GM        | 740<br>neutral<br>white | 4000 K                             | >70                         | 32,900 lm     |
| 911401660308 | BRP594<br>LED352/NW 220W<br>DW2 PSA GC       | 740<br>neutral<br>white | 4000 K                             | >70                         | 35,200 lm     |
| 911401660408 | BRP594<br>LED356/NW 220W<br>DM PSA GM        | 740<br>neutral<br>white | 4000 K                             | >70                         | 35,600 lm     |
| 911401661008 | BRP594<br>LED388/NW 240W<br>DW2 PSA GC       | 740<br>neutral<br>white | 4000 K                             | >70                         | 38,800 lm     |
| 911401661108 | BRP594<br>LED392/NW 240W<br>DM PSA GM        | 740<br>neutral<br>white | 4000 K                             | >70                         | 39,200 lm     |
| 911401658808 | BRP593<br>LED244/NW 150W<br>DM SR P7T SRB GM | 740<br>neutral<br>white | 4000 K                             | >70                         | 24,400 lm     |
| 911401654508 | BRP592<br>LED165/NW 100W<br>DW2 PSA GC       | 740<br>neutral<br>white | 4000 K                             | >70                         | 16,500 lm     |



| Order Code   | Full Product Name | Light   | Correlated  | Color     | Luminous  |
|--------------|-------------------|---------|-------------|-----------|-----------|
|              |                   | source  | Color       | rendering |           |
|              |                   | color   | Temperature | index     | Flux      |
|              |                   | (Nom)   | (CRI)       |           |           |
| 911401654608 | BRP592            | 740     | 4000 K      | >70       | 16,700 lm |
|              | LED167/NW 100W    | neutral |             |           |           |
|              | DM PSA GM         | white   |             |           |           |
| 911401655008 | BRP592            | 740     | 4000 K      | >70       | 19,200 lm |
|              | LED192/NW 120W    | neutral |             |           |           |
|              | DW2 PSA GC        | white   |             |           |           |
| 911401655308 | BRP592            | 740     | 4000 K      | >70       | 19,500 lm |
|              | LED195/NW 120W    | neutral |             |           |           |
|              | DM PSA GM         | white   |             |           |           |
| 911401655808 | BRP592            | 740     | 4000 K      | >70       | 20,100 lm |
|              | LED201/NW 130W    | neutral |             |           |           |
|              | DW2 PSR GC        | white   |             |           |           |
| 911401655908 | BRP592            | 740     | 4000 K      | >70       | 20,300 lm |
|              | LED203/NW 130W    | neutral |             |           |           |
|              | DM PSR GM         | white   |             |           |           |

Operating and Electrical

| Order Code   | Full Product Name                        | Power Consumption |
|--------------|------------------------------------------|-------------------|
| 911401652108 | BRP591 LED115/NW 70W DW2 PSA GC          | 70 W              |
| 911401652208 | BRP591 LED116/NW 70W DM PSA GM           | 70 W              |
| 911401652508 | BRP591 LED129/NW 80W DW2 PSA GC          | 80 W              |
| 911401652608 | BRP591 LED130/NW 80W DM PSA GM           | 80 W              |
| 911401653908 | BRP591 LED142/NW 90W DW2 PSR GC          | 90 W              |
| 911401654008 | BRP591 LED143/NW 90W DM PSR GM           | 90 W              |
| 911401656708 | BRP591 LED23/NW 15W DWP II PSD P7L8ANZ   | 13 W              |
| 911401656208 | BRP593 LED223/NW 138W DWV II PSDP7L15ANZ | 134 W             |
| 911401657808 | BRP593 LED240/NW 150W DW2 PSA P7 GC      | 150 W             |
| 911401658208 | BRP593 LED242/NW 150W DM PSA P7 GM       | 150 W             |
| 911401659108 | BRP593 LED61/NW 35W DWP3 II PSD P7L8ANZ  | 34 W              |
| 911401661408 | BRP595 LED403/NW 250W DM PSA GM          | 250 W             |
| 911401661508 | BRP595 LED405/NW 250W DW2 PSA GC         | 250 W             |
| 911401662008 | BRP595 LED427/NW 260W DW2 PSA GC         | 260 W             |
| 911401662108 | BRP595 LED432/NW 260W DM PSA GM          | 260 W             |
| 911401662408 | BRP595 LED454/NW 280W DW2 PSA GC         | 280 W             |
| 911401662508 | BRP595 LED459/NW 280W DM PSA GM          | 280 W             |
| 911401663608 | BRP595 LED484/NW 300W DW2 PSR GC         | 300 W             |
| 911401664008 | BRP595 LED489/NW 300W DM PSR GM          | 300 W             |
| 911401671508 | BRP595 LED130/NW 65W DW2 PSRD O5         | 65 W              |
| 911401672008 | BRP595 LED195/NW 100W DW2 PSRD O5        | 100 W             |
| 911401663208 | BRP595 LED480/NW 300W DW2 PSA P7 GC      | 300 W             |
| 911401663808 | BRP595 LED485/NW 300W DM PSA P7 GM       | 300 W             |
| 911401649109 | BRP593 LED263/NW 150W DW2 PSA GC         | 150 W             |
| 911401649209 | BRP593 LED250/WW 150W DW2 PSA GC         | 150 W             |
| 911401672509 | BRP593 LED244/NW 150W DM PSRD PE GM      | 150 W             |
| 911401673409 | BRP593 LED240/NW 150W DM PSD PE GM       | 150 W             |
| 911401674009 | BRP593 LED240/NW 150W DM GL PE GM        | 150 W             |
| 911401673609 | BRP595 LED479/NW 300W DM SR 7TSB PE GM   | 300 W             |
| 911401673209 | BRP591 LED142/NW 90W DM PSA P7 PE GM     | 90 W              |

| Order Code   | Full Product Name | Light   | Correlated  | Color     | Luminous  |
|--------------|-------------------|---------|-------------|-----------|-----------|
|              |                   | source  | Color       | rendering |           |
|              |                   | color   | Temperature | index     | Flux      |
|              |                   | (Nom)   | (CRI)       |           |           |
| 911401656508 | BRP593            | 740     | 4000 K      | >70       | 22,700 lm |
|              | LED227/NW 140W    | neutral |             |           |           |
|              | DW2 PSA GC        | white   |             |           |           |
| 911401656608 | BRP593            | 740     | 4000 K      | >70       | 22,900 lm |
|              | LED229/NW 140W    | neutral |             |           |           |
|              | DM PSA GM         | white   |             |           |           |
| 911401658708 | BRP593            | 740     | 4000 K      | >70       | 24,300 lm |
|              | LED243/NW 150W    | neutral |             |           |           |
|              | DW2 PSR GC        | white   |             |           |           |
| 911401658908 | BRP593            | 740     | 4000 K      | >70       | 24,500 lm |
|              | LED245/NW 150W    | neutral |             |           |           |
|              | DM PSR GM         | white   |             |           |           |

| Order Code   | Full Product Name                      | Power Consumption |
|--------------|----------------------------------------|-------------------|
| 911401672909 | BRP594 LED389/NW 240W DM PSA P7 PE GM  | 240 W             |
| 911401648709 | BRP591 LED147/NW 85W DW2 PSA GC        | 85 W              |
| 911401648809 | BRP591 LED136/WW 80W DW2 PSA GC        | 85 W              |
| 911401672709 | BRP591 LED143/NW 90W DM PSRD PE GM     | 90 W              |
| 911401673509 | BRP591 LED65/NW 40W DM PSD PE GM       | 40 W              |
| 911401674209 | BRP591 LED139/NW 90W DM GL PE GM       | 90 W              |
| 911401674409 | BRP591 LED143/NW 90W DM PSR PE GM      | 90 W              |
| 911401661608 | BRP594 LED388/NW 240W DW2 PSA P7 GC    | 240 W             |
| 911401661708 | BRP594 LED392/NW 240W DM PSA P7 GM     | 240 W             |
| 911401673109 | BRP592 LED192/NW 120W DM PSA P7 PE GM  | 120 W             |
| 911401673009 | BRP593 LED240/NW 150W DM PSA P7 PE GM  | 150 W             |
| 911401664108 | BRP595 LED489/NW 300W DM SR P7T SRB GM | 300 W             |
| 911401672809 | BRP595 LED479/NW 300W DM PSA P7 PE GM  | 300 W             |
| 911401648909 | BRP592 LED209/NW 120W DW2 PSA GC       | 120 W             |
| 911401649009 | BRP592 LED193/WW 120W DW2 PSA GC       | 120 W             |
| 911401672609 | BRP592 LED194/NW 120W DM PSRD PE GM    | 120 W             |
| 911401674109 | BRP592 LED163/NW 100W DM GL PE GM      | 100 W             |
| 911401674309 | BRP592 LED203/NW 130W DM PSR PE GM     | 130 W             |
| 911401649309 | BRP594 LED423/NW 240W DW2 PSA GC       | 240 W             |
| 911401649409 | BRP594 LED402/WW 240W DW2 PSA GC       | 240 W             |
| 911401672409 | BRP594 LED389/NW 240W DM PSRD PE GM    | 240 W             |
| 911401673909 | BRP594 LED358/NW 220W DM GL PE GM      | 220 W             |
| 911401649509 | BRP595 LED525/NW 300W DW2 PSA GC       | 300 W             |
| 911401649609 | BRP595 LED499/WW 300W DW2 PSA GC       | 300 W             |
| 911401672309 | BRP595 LED487/NW 300W DM PSRD PE GM    | 300 W             |
| 911401673309 | BRP595 LED479/NW 300W DM PSD PE GM     | 300 W             |
| 911401673809 | BRP595 LED479/NW 300W DM GL PE GM      | 300 W             |
| 911401673709 | BRP593 LED240/NW 150W DM SR 7TSB PE GM | 150 W             |
| 911401659508 | BRP594 LED298/NW 180W DW2 PSA GC       | 180 W             |
| 911401659608 | BRP594 LED301/NW 180W DM PSA GM        | 180 W             |

| Order Code   | Full Product Name                      | Power Consumption |
|--------------|----------------------------------------|-------------------|
| 911401659908 | BRP594 LED326/NW 200W DW2 PSA GC       | 200 W             |
| 911401660008 | BRP594 LED329/NW 200W DM PSA GM        | 200 W             |
| 911401660308 | BRP594 LED352/NW 220W DW2 PSA GC       | 220 W             |
| 911401660408 | BRP594 LED356/NW 220W DM PSA GM        | 220 W             |
| 911401661008 | BRP594 LED388/NW 240W DW2 PSA GC       | 240 W             |
| 911401661108 | BRP594 LED392/NW 240W DM PSA GM        | 240 W             |
| 911401658808 | BRP593 LED244/NW 150W DM SR P7T SRB GM | 150 W             |
| 911401654508 | BRP592 LED165/NW 100W DW2 PSA GC       | 100 W             |
| 911401654608 | BRP592 LED167/NW 100W DM PSA GM        | 100 W             |

| Order Code   | Full Product Name                | Power Consumption |
|--------------|----------------------------------|-------------------|
| 911401655008 | BRP592 LED192/NW 120W DW2 PSA GC | 120 W             |
| 911401655308 | BRP592 LED195/NW 120W DM PSA GM  | 120 W             |
| 911401655808 | BRP592 LED201/NW 130W DW2 PSR GC | 130 W             |
| 911401655908 | BRP592 LED203/NW 130W DM PSR GM  | 130 W             |
| 911401656508 | BRP593 LED227/NW 140W DW2 PSA GC | 140 W             |
| 911401656608 | BRP593 LED229/NW 140W DM PSA GM  | 140 W             |
| 911401658708 | BRP593 LED243/NW 150W DW2 PSR GC | 150 W             |
| 911401658908 | BRP593 LED245/NW 150W DM PSR GM  | 150 W             |

Controls and Dimming

| Order Code   | Full Product Name                        | Dimmable |
|--------------|------------------------------------------|----------|
| 911401652108 | BRP591 LED115/NW 70W DW2 PSA GC          | Yes      |
| 911401652208 | BRP591 LED116/NW 70W DM PSA GM           | Yes      |
| 911401652508 | BRP591 LED129/NW 80W DW2 PSA GC          | Yes      |
| 911401652608 | BRP591 LED130/NW 80W DM PSA GM           | Yes      |
| 911401653908 | BRP591 LED142/NW 90W DW2 PSR GC          | Yes      |
| 911401654008 | BRP591 LED143/NW 90W DM PSR GM           | Yes      |
| 911401656708 | BRP591 LED23/NW 15W DWP II PSD P7L8ANZ   | Yes      |
| 911401656208 | BRP593 LED223/NW 138W DWV II PSDP7L15ANZ | Yes      |
| 911401657808 | BRP593 LED240/NW 150W DW2 PSA P7 GC      | Yes      |
| 911401658208 | BRP593 LED242/NW 150W DM PSA P7 GM       | Yes      |
| 911401659108 | BRP593 LED61/NW 35W DWP3 II PSD P7L8ANZ  | Yes      |
| 911401661408 | BRP595 LED403/NW 250W DM PSA GM          | Yes      |
| 911401661508 | BRP595 LED405/NW 250W DW2 PSA GC         | Yes      |
| 911401662008 | BRP595 LED427/NW 260W DW2 PSA GC         | Yes      |
| 911401662108 | BRP595 LED432/NW 260W DM PSA GM          | Yes      |
| 911401662408 | BRP595 LED454/NW 280W DW2 PSA GC         | Yes      |
| 911401662508 | BRP595 LED459/NW 280W DM PSA GM          | Yes      |
| 911401663608 | BRP595 LED484/NW 300W DW2 PSR GC         | Yes      |
| 911401664008 | BRP595 LED489/NW 300W DM PSR GM          | Yes      |
| 911401671508 | BRP595 LED130/NW 65W DW2 PSRD O5         | Yes      |
| 911401672008 | BRP595 LED195/NW 100W DW2 PSRD O5        | Yes      |
| 911401663208 | BRP595 LED480/NW 300W DW2 PSA P7 GC      | Yes      |
| 911401663808 | BRP595 LED485/NW 300W DM PSA P7 GM       | Yes      |
| 911401649109 | BRP593 LED263/NW 150W DW2 PSA GC         | 1-10V    |
| 911401649209 | BRP593 LED250/WW 150W DW2 PSA GC         | 1-10V    |
| 911401672509 | BRP593 LED244/NW 150W DM PSRD PE GM      | Yes      |
| 911401673409 | BRP593 LED240/NW 150W DM PSD PE GM       | Yes      |
| 911401674009 | BRP593 LED240/NW 150W DM GL PE GM        | Yes      |
| 911401673609 | BRP595 LED479/NW 300W DM SR 7TSB PE GM   | Yes      |
| 911401673209 | BRP591 LED142/NW 90W DM PSA P7 PE GM     | Yes      |
| 911401672909 | BRP594 LED389/NW 240W DM PSA P7 PE GM    | Yes      |
| 911401648709 | BRP591 LED147/NW 85W DW2 PSA GC          | 1-10V    |
| 911401648809 | BRP591 LED136/WW 80W DW2 PSA GC          | 1-10V    |
| 911401672709 | BRP591 LED143/NW 90W DM PSRD PE GM       | Yes      |
| 911401673509 | BRP591 LED65/NW 40W DM PSD PE GM         | Yes      |
| 911401674209 | BRP591 LED139/NW 90W DM GL PE GM         | Yes      |
| 911401674409 | BRP591 LED143/NW 90W DM PSR PE GM        | Yes      |
| 911401661608 | BRP594 LED388/NW 240W DW2 PSA P7 GC      | Yes      |
| 911401661708 | BRP594 LED392/NW 240W DM PSA P7 GM       | Yes      |

| Order Code   | Full Product Name                      | Dimmable |
|--------------|----------------------------------------|----------|
| 911401673109 | BRP592 LED192/NW 120W DM PSA P7 PE GM  | Yes      |
| 911401673009 | BRP593 LED240/NW 150W DM PSA P7 PE GM  | Yes      |
| 911401664108 | BRP595 LED489/NW 300W DM SR P7T SRB GM | Yes      |
| 911401672809 | BRP595 LED479/NW 300W DM PSA P7 PE GM  | Yes      |
| 911401648909 | BRP592 LED209/NW 120W DW2 PSA GC       | 1-10V    |
| 911401649009 | BRP592 LED193/WW 120W DW2 PSA GC       | 1-10V    |
| 911401672609 | BRP592 LED194/NW 120W DM PSRD PE GM    | Yes      |
| 911401674109 | BRP592 LED163/NW 100W DM GL PE GM      | Yes      |
| 911401674309 | BRP592 LED203/NW 130W DM PSR PE GM     | Yes      |
| 911401649309 | BRP594 LED423/NW 240W DW2 PSA GC       | 1-10V    |
| 911401649409 | BRP594 LED402/WW 240W DW2 PSA GC       | 1-10V    |
| 911401672409 | BRP594 LED389/NW 240W DM PSRD PE GM    | Yes      |
| 911401673909 | BRP594 LED358/NW 220W DM GL PE GM      | Yes      |
| 911401649509 | BRP595 LED525/NW 300W DW2 PSA GC       | 1-10V    |
| 911401649609 | BRP595 LED499/WW 300W DW2 PSA GC       | 1-10V    |
| 911401672309 | BRP595 LED487/NW 300W DM PSRD PE GM    | Yes      |
| 911401673309 | BRP595 LED479/NW 300W DM PSD PE GM     | Yes      |
| 911401673809 | BRP595 LED479/NW 300W DM GL PE GM      | Yes      |
| 911401673709 | BRP593 LED240/NW 150W DM SR 7TSB PE GM | Yes      |
| 911401659508 | BRP594 LED298/NW 180W DW2 PSA GC       | Yes      |
| 911401659608 | BRP594 LED301/NW 180W DM PSA GM        | Yes      |
| 911401659908 | BRP594 LED326/NW 200W DW2 PSA GC       | Yes      |
| 911401660008 | BRP594 LED329/NW 200W DM PSA GM        | Yes      |
| 911401660308 | BRP594 LED352/NW 220W DW2 PSA GC       | Yes      |
| 911401660408 | BRP594 LED356/NW 220W DM PSA GM        | Yes      |
| 911401661008 | BRP594 LED388/NW 240W DW2 PSA GC       | Yes      |
| 911401661108 | BRP594 LED392/NW 240W DM PSA GM        | Yes      |
| 911401658808 | BRP593 LED244/NW 150W DM SR P7T SRB GM | Yes      |
| 911401654508 | BRP592 LED165/NW 100W DW2 PSA GC       | Yes      |
| 911401654608 | BRP592 LED167/NW 100W DM PSA GM        | Yes      |
| 911401655008 | BRP592 LED192/NW 120W DW2 PSA GC       | Yes      |
| 911401655308 | BRP592 LED195/NW 120W DM PSA GM        | Yes      |
| 911401655808 | BRP592 LED201/NW 130W DW2 PSR GC       | Yes      |
| 911401655908 | BRP592 LED203/NW 130W DM PSR GM        | Yes      |
| 911401656508 | BRP593 LED227/NW 140W DW2 PSA GC       | Yes      |
| 911401656608 | BRP593 LED229/NW 140W DM PSA GM        | Yes      |
| 911401658708 | BRP593 LED243/NW 150W DW2 PSR GC       | Yes      |
| 911401658908 | BRP593 LED245/NW 150W DM PSR GM        | Yes      |

Mechanical and Housing

| Order Code   | Full Product Name                        | Housing Color |
|--------------|------------------------------------------|---------------|
| 911401652108 | BRP591 LED115/NW 70W DW2 PSA GC          | Grey          |
| 911401652208 | BRP591 LED116/NW 70W DM PSA GM           | Grey          |
| 911401652508 | BRP591 LED129/NW 80W DW2 PSA GC          | Grey          |
| 911401652608 | BRP591 LED130/NW 80W DM PSA GM           | Grey          |
| 911401653908 | BRP591 LED142/NW 90W DW2 PSR GC          | Grey          |
| 911401654008 | BRP591 LED143/NW 90W DM PSR GM           | Grey          |
| 911401656708 | BRP591 LED23/NW 15W DWP II PSD P7L8ANZ   | Grey          |
| 911401656208 | BRP593 LED223/NW 138W DWV II PSDP7L15ANZ | Grey          |
| 911401657808 | BRP593 LED240/NW 150W DW2 PSA P7 GC      | Grey          |
| 911401658208 | BRP593 LED242/NW 150W DM PSA P7 GM       | Grey          |
| 911401659108 | BRP593 LED61/NW 35W DWP3 II PSD P7L8ANZ  | Grey          |
| 911401661408 | BRP595 LED403/NW 250W DM PSA GM          | Grey          |
| 911401661508 | BRP595 LED405/NW 250W DW2 PSA GC         | Grey          |
| 911401662008 | BRP595 LED427/NW 260W DW2 PSA GC         | Grey          |
| 911401662108 | BRP595 LED432/NW 260W DM PSA GM          | Grey          |
| 911401662408 | BRP595 LED454/NW 280W DW2 PSA GC         | Grey          |
| 911401662508 | BRP595 LED459/NW 280W DM PSA GM          | Grey          |
| 911401663608 | BRP595 LED484/NW 300W DW2 PSR GC         | Grey          |
| 911401664008 | BRP595 LED489/NW 300W DM PSR GM          | Grey          |
| 911401671508 | BRP595 LED130/NW 65W DW2 PSRD O5         | Grey          |
| 911401672008 | BRP595 LED195/NW 100W DW2 PSRD O5        | Grey          |
| 911401663208 | BRP595 LED480/NW 300W DW2 PSA P7 GC      | Grey          |
| 911401663808 | BRP595 LED485/NW 300W DM PSA P7 GM       | Grey          |
| 911401649109 | BRP593 LED263/NW 150W DW2 PSA GC         | RAL7040       |
| 911401649209 | BRP593 LED250/WW 150W DW2 PSA GC         | RAL7040       |
| 911401672509 | BRP593 LED244/NW 150W DM PSRD PE GM      | Gray          |
| 911401673409 | BRP593 LED240/NW 150W DM PSD PE GM       | Gray          |
| 911401674009 | BRP593 LED240/NW 150W DM GL PE GM        | Gray          |
| 911401673609 | BRP595 LED479/NW 300W DM SR 7TSB PE GM   | Gray          |
| 911401673209 | BRP591 LED142/NW 90W DM PSA P7 PE GM     | Gray          |
| 911401672909 | BRP594 LED389/NW 240W DM PSA P7 PE GM    | Gray          |
| 911401648709 | BRP591 LED147/NW 85W DW2 PSA GC          | RAL7040       |
| 911401648809 | BRP591 LED136/WW 80W DW2 PSA GC          | RAL7040       |
| 911401672709 | BRP591 LED143/NW 90W DM PSRD PE GM       | Gray          |
| 911401673509 | BRP591 LED65/NW 40W DM PSD PE GM         | Gray          |
| 911401674209 | BRP591 LED139/NW 90W DM GL PE GM         | Gray          |
| 911401674409 | BRP591 LED143/NW 90W DM PSR PE GM        | Gray          |
| 911401661608 | BRP594 LED388/NW 240W DW2 PSA P7 GC      | Grey          |
| 911401661708 | BRP594 LED392/NW 240W DM PSA P7 GM       | Grey          |

| Order Code   | Full Product Name                      | Housing Color |
|--------------|----------------------------------------|---------------|
| 911401673109 | BRP592 LED192/NW 120W DM PSA P7 PE GM  | Gray          |
| 911401673009 | BRP593 LED240/NW 150W DM PSA P7 PE GM  | Gray          |
| 911401664108 | BRP595 LED489/NW 300W DM SR P7T SRB GM | Grey          |
| 911401672809 | BRP595 LED479/NW 300W DM PSA P7 PE GM  | Gray          |
| 911401648909 | BRP592 LED209/NW 120W DW2 PSA GC       | RAL7040       |
| 911401649009 | BRP592 LED193/WW 120W DW2 PSA GC       | RAL7040       |
| 911401672609 | BRP592 LED194/NW 120W DM PSRD PE GM    | Gray          |
| 911401674109 | BRP592 LED163/NW 100W DM GL PE GM      | Gray          |
| 911401674309 | BRP592 LED203/NW 130W DM PSR PE GM     | Gray          |
| 911401649309 | BRP594 LED423/NW 240W DW2 PSA GC       | RAL7040       |
| 911401649409 | BRP594 LED402/WW 240W DW2 PSA GC       | RAL7040       |
| 911401672409 | BRP594 LED389/NW 240W DM PSRD PE GM    | Gray          |
| 911401673909 | BRP594 LED358/NW 220W DM GL PE GM      | Gray          |
| 911401649509 | BRP595 LED525/NW 300W DW2 PSA GC       | RAL7040       |
| 911401649609 | BRP595 LED499/WW 300W DW2 PSA GC       | RAL7040       |
| 911401672309 | BRP595 LED487/NW 300W DM PSRD PE GM    | Gray          |
| 911401673309 | BRP595 LED479/NW 300W DM PSD PE GM     | Gray          |
| 911401673809 | BRP595 LED479/NW 300W DM GL PE GM      | Gray          |
| 911401673709 | BRP593 LED240/NW 150W DM SR 7TSB PE GM | Gray          |
| 911401659508 | BRP594 LED298/NW 180W DW2 PSA GC       | Grey          |
| 911401659608 | BRP594 LED301/NW 180W DM PSA GM        | Grey          |
| 911401659908 | BRP594 LED326/NW 200W DW2 PSA GC       | Grey          |
| 911401660008 | BRP594 LED329/NW 200W DM PSA GM        | Grey          |
| 911401660308 | BRP594 LED352/NW 220W DW2 PSA GC       | Grey          |
| 911401660408 | BRP594 LED356/NW 220W DM PSA GM        | Grey          |
| 911401661008 | BRP594 LED388/NW 240W DW2 PSA GC       | Grey          |
| 911401661108 | BRP594 LED392/NW 240W DM PSA GM        | Grey          |
| 911401658808 | BRP593 LED244/NW 150W DM SR P7T SRB GM | Grey          |
| 911401654508 | BRP592 LED165/NW 100W DW2 PSA GC       | Grey          |
| 911401654608 | BRP592 LED167/NW 100W DM PSA GM        | Grey          |
| 911401655008 | BRP592 LED192/NW 120W DW2 PSA GC       | Grey          |
| 911401655308 | BRP592 LED195/NW 120W DM PSA GM        | Grey          |
| 911401655808 | BRP592 LED201/NW 130W DW2 PSR GC       | Grey          |
| 911401655908 | BRP592 LED203/NW 130W DM PSR GM        | Grey          |
| 911401656508 | BRP593 LED227/NW 140W DW2 PSA GC       | Grey          |
| 911401656608 | BRP593 LED229/NW 140W DM PSA GM        | Grey          |
| 911401658708 | BRP593 LED243/NW 150W DW2 PSR GC       | Grey          |
| 911401658908 | BRP593 LED245/NW 150W DM PSR GM        | Grey          |

