



A 1:1 retrofit replacement for every project where light really matters

Coreline tempo large

CoreLine tempo large delivers on the CoreLine promise of innovative, easy to use and high quality luminaires. A narrow range of options makes it easy to find the best lux-for-lux replacement for 150W, 250W, and 400W HID lamps. The CoreLine tempo large floodlighting range offers lumen packages for many different application areas as well as a choice of high-performance asymmetrical and symmetrical optics. The installation is made easy thanks to the U-shaped universal mounting bracket and the external quick 3-poles connector. It is an ideal solution for outdoor areas such as tempo floodlights for industrial/commercial areas, parking lots, etc.

Benefits

- The same light levels as your existing conventional solution while saving on energy
- High quality bvp130 tempo large floodlight
- Easy to use
- The option of asset management and/or wireless lighting control

Coreline tempo large


Features

- All standard Ledgine O platform light distributions, lumen packages from 21,000 lm up to 30,000 lm
- Seaside-resistant treatment and swimming pool protection options
- Long lifetime of 100,000 hours, integrated surge protection, the option of an additional surge protection device, high impact resistance IK08, IP66
- Plug and play installation with 1m cable and IP66 connector, horizontal bracket for pole top mounting
- Ready to be connected to Interact City and Interact Sports recreational thanks to an SR socket

Application

- Indoor multi-purpose gymnasiums and swimming pool
- Outdoor recreational sports fields e.g. basket courts, etc.
- Harbors, airports, parking lots

Dimensional drawing



Product details



Coreline_tempo_large-BVP130-DP01.tif




Coreline_tempo_large-BVP130-DP02.tif

Coreline tempo large

Product details



Coreline_tempo_large-BVP130-DP03.tif



Coreline_tempo_large-BVP130-DP04.tif



Coreline_tempo_large-BVP130-DP05.tif



Coreline_tempo_large-BVP130-DP06.tif



Coreline_Tempo_Large-BVP125-DPP.TIF

Coreline tempo large

General Information	
Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Light source color	740 neutral white
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	70
Upward light output ratio	0
Operating and Electrical	
Surge Protection (Common/ Differential)	Surge protection level until 6 kV differential mode and 8 kV common mode
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Flat glass
Housing Color	Grey
Mech. impact protection code	IK08
Ingress protection code	IP66
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Emergency Operation	
Central Emergency	No
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Product Data	
Product family code	BVP130

General Information

Order Code	Full Product Name	Lamp family code
912300023660	BVP130 LED260-4S/740 PSU OFA52 ALU C1KC3	LED260-4S
912300023662	BVP130 LED160-4S/740 PSU OFA52 ALU C1KC3	LED160-4S
912300023663	BVP130 LED260-4S/740 PSU S ALU C1KC3 T35	LED260-4S
912300023664	BVP130 LED210-4S/740 PSU S ALU C1KC3	LED210-4S
912300023665	BVP130 LED160-4S/740 PSU S ALU C1KC3	LED160-4S

Light Technical

Order Code	Full Product Name	Luminaire	Luminous Flux	Number of light sources	Optic type outdoor
		light beam spread			
912300023660	BVP130 LED260-4S/740 PSU OFA52 ALU C1KC3	52° x 102°	26,000 lm	80	Asymmetrical

Order Code	Full Product Name	Luminaire	Luminous Flux	Number of light sources	Optic type outdoor
		light beam spread			
912300023662	BVP130 LED160-4S/740 PSU OFA52 ALU C1KC3	52° x 102°	16,000 lm	60	Asymmetrical

Coreline tempo large

Order Code	Full Product Name	Luminaire	Luminous Flux	Number of light sources	Optic type outdoor
		light beam spread			
912300023663	BVP130 LED260-4S/740 PSU S ALU C1KC3 T35	70° x 21°	26,000 lm	80	Symmetrical
912300023664	BVP130 LED210-4S/740 PSU S ALU C1KC3	70° x 21°	21,000 lm	80	Symmetrical




Order Code	Full Product Name	Luminaire	Luminous Flux	Number of light sources	Optic type outdoor
		light beam spread			
912300023665	BVP130 LED160-4S/740 PSU S ALU C1KC3	70° x 21°	16,000 lm	60	Symmetrical

Operating and Electrical


Order Code	Full Product Name	Power Consumption
912300023660	BVP130 LED260-4S/740 PSU OFA52 ALU C1KC3	182 W
912300023662	BVP130 LED160-4S/740 PSU OFA52 ALU C1KC3	109 W
912300023663	BVP130 LED260-4S/740 PSU S ALU C1KC3 T35	182 W

Order Code	Full Product Name	Power Consumption
912300023664	BVP130 LED210-4S/740 PSU S ALU C1KC3	141 W
912300023665	BVP130 LED160-4S/740 PSU S ALU C1KC3	109 W


Polar Wide Diagrams



Polar Normal (separate) - BVP130I - 912300023660



Polar Normal (separate) - BVP130I - 912300023663



Polar Normal (separate) - BVP130I - 912300023662

Polar Normal (separate) - BVP130I - 912300023665

Polar Normal (separate) - BVP130I - 912300023664

