



Reliable, Energy saving LED Floodlight

Essential SmartBright G5 LED Floodlight

The Essential SmartBright G5 LED Floodlight is the new successor with robust die-cast aluminum housing suitable for general outdoor application. Lightweight, with a robust die-cast aluminum housing and corrosion-proof coating, it's suitable for general outdoor applications. Plus, with a higher efficacy than the previous generation, it also saves more energy.

Benefits

- Reliable quality and performance
- Outstanding savings
- Easy to install & adjust

Features

- CCT: 3000K, 4000K, 6500K
- Power: 10W, 20W, 30W, 50W, 70W, 100W, 150W and 200W
- Input voltage: 220V-240V
- Lumen efficacy up to 100lm/w
- Working temperature: -40°C to +50°C
- 20khrs life

Application

- Warehouses
- Landscape
- Arena and Sports
- Billboard
- Parking area lighting
- Amenity

Essential SmartBright G5 LED Floodlight

Versions



ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT



ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT



ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT



ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT







ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT










ESSENTIAL SMARTBRIGHT G5
LED FLOODLIGHT

Dimensional drawing



Essential SmartBright G5 LED Floodlight

Dimensional drawing



Essential SmartBright G5 LED Floodlight

Product details



BVP150 front side

General Information

Driver included	Yes
Gear	-
Number of gear units	1 unit

Light Technical

Luminaire light beam spread	110°
Color rendering index (CRI)	80
Number of light sources	1

Controls and Dimming

Dimmable	No
Maximum dim level	Not applicable

Mechanical and Housing

Optical cover type	Tempered glass
Housing Color	Black
Mech. impact protection code	IK06
Ingress protection code	IP65

Approval and Application

CE mark	No
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
911401815286	BVP150 LED70/WW PSU 70W SWB G3 GM	830 warm white	3000 K		6,580 lm
911401835286	BVP150 LED70/CW PSU 70W SWB G3 GM	865 cool daylight	6500 K		7,000 lm
911401802086	BVP150 LED30/CW PSU 30W SWB MDU G3 GM	865 cool daylight	6500 K		3,000 lm
911401814286	BVP150 LED50/WW PSU 50W SWB G3 GM	830 warm white	3000 K		4,700 lm
911401834286	BVP150 LED50/CW PSU 50W SWB G3 GM	865 cool daylight	6500 K		5,000 lm
911401812286	BVP150 LED20/WW PSU 20W SWB G3 GM	830 warm white	3000 K		1,880 lm
911401832286	BVP150 LED20/CW PSU 20W SWB G3 GM	865 cool daylight	6500 K		2,000 lm
911401818286	BVP150 LED200/WW PSU 200W SWB G3 GM	830 warm white	3000 K		18,800 lm
911401838286	BVP150 LED200/CW PSU 200W SWB G3 GM	865 cool daylight	6500 K		20,000 lm
911401813286	BVP150 LED30/WW PSU 30W SWB G3 GM	830 warm white	3000 K		2,820 lm
911401833286	BVP150 LED30/CW PSU 30W SWB G3 GM	865 cool daylight	6500 K		3,000 lm
911401811286	BVP150 LED10/WW PSU 10W SWB G3 GM	830 warm white	3000 K		940 lm
911401831286	BVP150 LED10/CW PSU 10W SWB G3 GM	865 cool daylight	6500 K		1,000 lm
911401801786	BVP150 LED20/CW PSU 20W SWB MDU G3 GM	865 cool daylight	6500 K		2,000 lm
911401816286	BVP150 LED100/WW PSU 100W SWB G3 GM	830 warm white	3000 K		9,400 lm
911401836286	BVP150 LED100/CW PSU 100W SWB G3 GM	865 cool daylight	6500 K		10,000 lm
911401802386	BVP150 LED50/CW PSU 50W SWB MDU G3 GM	865 cool daylight	6500 K		5,000 lm
911401817286	BVP150 LED150/WW PSU 150W SWB G3 GM	830 warm white	3000 K		14,100 lm
911401837286	BVP150 LED150/CW PSU 150W SWB G3 GM	865 cool daylight	6500 K		15,000 lm

Essential SmartBright G5 LED Floodlight

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401815286	BVP150 LED70/WW PSU 70W SWB G3 GM	70 W
911401835286	BVP150 LED70/CW PSU 70W SWB G3 GM	70 W
911401802086	BVP150 LED30/CW PSU 30W SWB MDU G3 GM	30 W
911401814286	BVP150 LED50/WW PSU 50W SWB G3 GM	50 W
911401834286	BVP150 LED50/CW PSU 50W SWB G3 GM	50 W
911401812286	BVP150 LED20/WW PSU 20W SWB G3 GM	20 W
911401832286	BVP150 LED20/CW PSU 20W SWB G3 GM	20 W
911401818286	BVP150 LED200/WW PSU 200W SWB G3 GM	200 W
911401838286	BVP150 LED200/CW PSU 200W SWB G3 GM	200 W
911401813286	BVP150 LED30/WW PSU 30W SWB G3 GM	30 W

Order Code	Full Product Name	Power Consumption
911401833286	BVP150 LED30/CW PSU 30W SWB G3 GM	30 W
911401811286	BVP150 LED10/WW PSU 10W SWB G3 GM	10 W
911401831286	BVP150 LED10/CW PSU 10W SWB G3 GM	10 W
911401801786	BVP150 LED20/CW PSU 20W SWB MDU G3 GM	20 W
911401816286	BVP150 LED100/WW PSU 100W SWB G3 GM	100 W
911401836286	BVP150 LED100/CW PSU 100W SWB G3 GM	100 W
911401802386	BVP150 LED50/CW PSU 50W SWB MDU G3 GM	50 W
911401817286	BVP150 LED150/WW PSU 150W SWB G3 GM	150 W
911401837286	BVP150 LED150/CW PSU 150W SWB G3 GM	150 W

