



Philips UniFlood M gen2: A high power floodlight with true modularity

UniFlood M G2

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

UniFlood M G2

Application

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape

Warnings and Safety





- For outdoor use only.

Versions











UniFlood M Gen2

Dimensional drawing



Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Color rendering index (CRI)	>80
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

Light Technical

		Light source	Correlated Color	Luminous Flux
Order Code	Full Product Name	color	Temperature (Nom)	
911401746863	BVP353 30LED 27K 220V L30 10	827 warm white	2700 K	4,515 lm
911401746873	BVP353 30LED 30K 220V L30 10	830 warm white	3000 K	4,710 lm
911401746883	BVP353 30LED 40K 220V L30 10	840 neutral white	4000 K	5,255 lm
911401746893	BVP353 30LED 27K 220V L30 10 DMX	827 warm white	2700 K	4,220 lm
911401746903	BVP353 30LED 30K 220V L30 10 DMX	830 warm white	3000 K	4,400 lm
911401746913	BVP353 30LED 40K 220V L30 10 DMX	840 neutral white	4000 K	4,910 lm
911401746923	BVP353 30LED RGB 220V L30 10 DMX	RGB	-	2,495 lm
911401746933	BVP353 32LED RGBWW 220V L30 10 DMX	RGBW	-	2,855 lm
911401746943	BVP353 32LED RGBNW 220V L30 10 DMX	RGBW	-	2,985 lm
911401746953	BVP353 30LED 27K 220V L30 15	827 warm white	2700 K	4,740 lm
911401746963	BVP353 30LED 30K 220V L30 15	830 warm white	3000 K	4,945 lm
911401746973	BVP353 30LED 40K 220V L30 15	840 neutral white	4000 K	5,520 lm
911401746983	BVP353 30LED 27K 220V L30 15 DMX	827 warm white	2700 K	4,430 lm
911401746993	BVP353 30LED 30K 220V L30 15 DMX	830 warm white	3000 K	4,620 lm
911401747003	BVP353 30LED 40K 220V L30 15 DMX	840 neutral white	4000 K	5,155 lm
911401747013	BVP353 30LED RGB 220V L30 15 DMX	RGB	-	2,620 lm
911401747023	BVP353 32LED RGBWW 220V L30 15 DMX	RGBW	-	3,000 lm
911401747033	BVP353 32LED RGBNW 220V L30 15 DMX	RGBW	-	3,130 lm
911401747043	BVP353 30LED 27K 220V L30 30	827 warm white	2700 K	4,910 lm
911401747053	BVP353 30LED 30K 220V L30 30	830 warm white	3000 K	5,125 lm
911401747063	BVP353 30LED 40K 220V L30 30	840 neutral white	4000 K	5,715 lm
911401747073	BVP353 30LED 27K 220V L30 30 DMX	827 warm white	2700 K	4,585 lm
911401747083	BVP353 30LED 30K 220V L30 30 DMX	830 warm white	3000 K	4,785 lm
911401747093	BVP353 30LED 40K 220V L30 30 DMX	840 neutral white	4000 K	5,340 lm
911401747103	BVP353 30LED RGB 220V L30 30 DMX	RGB	-	2,715 lm
911401747113	BVP353 32LED RGBWW 220V L30 30 DMX	RGBW	-	3,105 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401747123	BVP353 32LED RGBNW 220V L30 30 DMX	RGBW	-	3,245 lm
911401747133	BVP353 30LED 27K 220V L30 45	827 warm white	2700 K	4,740 lm
911401747143	BVP353 30LED 30K 220V L30 45	830 warm white	3000 K	4,945 lm
911401747153	BVP353 30LED 40K 220V L30 45	840 neutral white	4000 K	5,520 lm
911401747163	BVP353 30LED 27K 220V L30 45 DMX	827 warm white	2700 K	4,430 lm
911401747173	BVP353 30LED 30K 220V L30 45 DMX	830 warm white	3000 K	4,620 lm
911401747183	BVP353 30LED 40K 220V L30 45 DMX	840 neutral white	4000 K	5,155 lm
911401747193	BVP353 30LED RGB 220V L30 45 DMX	RGB	-	2,620 lm
911401747203	BVP353 32LED RGBWW 220V L30 45 DMX	RGBW	-	3,000 lm
911401747213	BVP353 32LED RGBNW 220V L30 45 DMX	RGBW	-	3,130 lm
911401748663	BVP354 96LED 27K 220V L40 10	827 warm white	2700 K	15,870 lm
911401748673	BVP354 96LED 30K 220V L40 10	830 warm white	3000 K	16,555 lm
911401748683	BVP354 96LED 40K 220V L40 10	840 neutral white	4000 K	18,470 lm
911401748693	BVP354 96LED 27K 220V L40 10 DMX	827 warm white	2700 K	14,640 lm
911401748703	BVP354 96LED 30K 220V L40 10 DMX	830 warm white	3000 K	15,270 lm
911401748713	BVP354 96LED 40K 220V L40 10 DMX	840 neutral white	4000 K	17,035 lm
911401748723	BVP354 96LED RGB 220V L40 10 DMX	RGB	-	8,170 lm
911401748733	BVP354 96LED RGBWW 220V L40 10 DMX	RGBW	-	10,505 lm
911401748743	BVP354 96LED RGBNW 220V L40 10 DMX	RGBW	-	10,975 lm
911401748753	BVP354 96LED 27K 220V L40 15	827 warm white	2700 K	16,665 lm
911401748763	BVP354 96LED 30K 220V L40 15	830 warm white	3000 K	17,385 lm
911401748773	BVP354 96LED 40K 220V L40 15	840 neutral white	4000 K	19,395 lm
911401748783	BVP354 96LED 27K 220V L40 15 DMX	827 warm white	2700 K	15,370 lm
911401748793	BVP354 96LED 30K 220V L40 15 DMX	830 warm white	3000 K	16,035 lm
911401748803	BVP354 96LED 40K 220V L40 15 DMX	840 neutral white	4000 K	17,890 lm
911401748813	BVP354 96LED RGB 220V L40 15 DMX	RGB	-	8,580 lm
911401748823	BVP354 96LED RGBWW 220V L40 15 DMX	RGBW	-	11,030 lm
911401748833	BVP354 96LED RGBNW 220V L40 15 DMX	RGBW	-	11,520 lm
911401748843	BVP354 96LED 27K 220V L40 30	827 warm white	2700 K	17,260 lm
911401748853	BVP354 96LED 30K 220V L40 30	830 warm white	3000 K	18,005 lm
911401748863	BVP354 96LED 40K 220V L40 30	840 neutral white	4000 K	20,085 lm
911401748873	BVP354 96LED 27K 220V L40 30 DMX	827 warm white	2700 K	15,920 lm
911401748883	BVP354 96LED 30K 220V L40 30 DMX	830 warm white	3000 K	16,605 lm
911401748893	BVP354 96LED 40K 220V L40 30 DMX	840 neutral white	4000 K	18,525 lm
911401748903	BVP354 96LED RGB 220V L40 30 DMX	RGB	-	8,885 lm
911401748913	BVP354 96LED RGBWW 220V L40 30 DMX	RGBW	-	11,425 lm
911401748923	BVP354 96LED RGBNW 220V L40 30 DMX	RGBW	-	11,935 lm

Order Code	Full Product Name	Light source	Correlated Color	
		color	Temperature (Nom)	Luminous Flux
911401748933	BVP354 96LED 27K 220V L40 45	827 warm white	2700 K	16,665 lm
911401748943	BVP354 96LED 30K 220V L40 45	830 warm white	3000 K	17,385 lm
911401748953	BVP354 96LED 40K 220V L40 45	840 neutral white	4000 K	19,395 lm
911401748963	BVP354 96LED 27K 220V L40 45 DMX	827 warm white	2700 K	15,370 lm
911401748973	BVP354 96LED 30K 220V L40 45 DMX	830 warm white	3000 K	16,035 lm
911401748983	BVP354 96LED 40K 220V L40 45 DMX	840 neutral white	4000 K	17,890 lm
911401748993	BVP354 96LED RGB 220V L40 45 DMX	RGB	-	8,580 lm
911401749003	BVP354 96LED RGBWW 220V L40 45 DMX	RGBW	-	11,030 lm
911401749013	BVP354 96LED RGBNW 220V L40 45 DMX	RGBW	-	11,520 lm
911401749023	BVP354 120LED 27K 220V L50 10	827 warm white	2700 K	18,075 lm
911401749033	BVP354 120LED 30K 220V L50 10	830 warm white	3000 K	18,850 lm
911401749043	BVP354 120LED 40K 220V L50 10	840 neutral white	4000 K	21,035 lm
911401749053	BVP354 120LED 27K 220V L50 10 DMX	827 warm white	2700 K	16,880 lm
911401749063	BVP354 120LED 30K 220V L50 10 DMX	830 warm white	3000 K	17,605 lm
911401749073	BVP354 120LED 40K 220V L50 10 DMX	840 neutral white	4000 K	19,645 lm
911401749083	BVP354 120LED RGB 220V L50 10 DMX	RGB	-	9,985 lm
911401749093	BVP354 120LED RGBWW 220V L50 10 DMX	RGBW	-	10,720 lm
911401749103	BVP354 120LED RGBNW 220V L50 10 DMX	RGBW	-	11,190 lm
911401749113	BVP354 120LED 27K 220V L50 15	827 warm white	2700 K	18,975 lm
911401749123	BVP354 120LED 30K 220V L50 15	830 warm white	3000 K	19,795 lm
911401749133	BVP354 120LED 40K 220V L50 15	840 neutral white	4000 K	22,085 lm
911401749143	BVP354 120LED 27K 220V L50 15 DMX	827 warm white	2700 K	17,720 lm
911401749153	BVP354 120LED 30K 220V L50 15 DMX	830 warm white	3000 K	18,485 lm
911401749163	BVP354 120LED 40K 220V L50 15 DMX	840 neutral white	4000 K	20,625 lm
911401749173	BVP354 120LED RGB 220V L50 15 DMX	RGB	-	10,485 lm
911401749183	BVP354 120LED RGBWW 220V L50 15 DMX	RGBW	-	11,255 lm
911401749193	BVP354 120LED RGBNW 220V L50 15 DMX	RGBW	-	11,750 lm
911401749203	BVP354 120LED 27K 220V L50 30	827 warm white	2700 K	19,655 lm
911401749213	BVP354 120LED 30K 220V L50 30	830 warm white	3000 K	20,500 lm
911401749223	BVP354 120LED 40K 220V L50 30	840 neutral white	4000 K	22,875 lm
911401749233	BVP354 120LED 27K 220V L50 30 DMX	827 warm white	2700 K	18,355 lm
911401749243	BVP354 120LED 30K 220V L50 30 DMX	830 warm white	3000 K	19,145 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401749253	BVP354 120LED 40K 220V L50 30 DMX	840 neutral white	4000 K	21,360 lm
911401749263	BVP354 120LED RGB 220V L50 30 DMX	RGB	-	10,860 lm
911401749273	BVP354 120LED RGBWW 220V L50 30 DMX	RGBW	-	11,655 lm
911401749283	BVP354 120LED RGBNW 220V L50 30 DMX	RGBW	-	12,170 lm
911401749293	BVP354 120LED 27K 220V L50 45	827 warm white	2700 K	18,975 lm
911401749303	BVP354 120LED 30K 220V L50 45	830 warm white	3000 K	19,795 lm
911401749313	BVP354 120LED 40K 220V L50 45	840 neutral white	4000 K	22,085 lm
911401749323	BVP354 120LED 27K 220V L50 45 DMX	827 warm white	2700 K	17,720 lm
911401749333	BVP354 120LED 30K 220V L50 45 DMX	830 warm white	3000 K	18,485 lm
911401749343	BVP354 120LED 40K 220V L50 45 DMX	840 neutral white	4000 K	20,625 lm
911401749353	BVP354 120LED RGB 220V L50 45 DMX	RGB	-	10,485 lm
911401749363	BVP354 120LED RGBWW 220V L50 45 DMX	RGBW	-	11,255 lm
911401749373	BVP354 120LED RGBNW 220V L50 45 DMX	RGBW	-	11,750 lm
911401749383	BVP354 144LED 27K 220V L57 10	827 warm white	2700 K	22,765 lm
911401749393	BVP354 144LED 30K 220V L57 10	830 warm white	3000 K	23,745 lm
911401749403	BVP354 144LED 40K 220V L57 10	840 neutral white	4000 K	26,490 lm
911401749413	BVP354 144LED 27K 220V L57 10 DMX	827 warm white	2700 K	21,690 lm
911401749423	BVP354 144LED 30K 220V L57 10 DMX	830 warm white	3000 K	22,625 lm
911401749433	BVP354 144LED 40K 220V L57 10 DMX	840 neutral white	4000 K	25,240 lm
911401749443	BVP354 144LED RGB 220V L57 10 DMX	RGB	-	13,410 lm
911401749453	BVP354 144LED RGBWW 220V L57 10 DMX	RGBW	-	14,395 lm
911401749463	BVP354 144LED RGBNW 220V L57 10 DMX	RGBW	-	15,030 lm
911401749473	BVP354 144LED 27K 220V L57 15	827 warm white	2700 K	23,900 lm
911401749483	BVP354 144LED 30K 220V L57 15	830 warm white	3000 K	24,930 lm
911401749493	BVP354 144LED 40K 220V L57 15	840 neutral white	4000 K	27,815 lm
911401749503	BVP354 144LED 27K 220V L57 15 DMX	827 warm white	2700 K	22,775 lm
911401749513	BVP354 144LED 30K 220V L57 15 DMX	830 warm white	3000 K	23,755 lm
911401749523	BVP354 144LED 40K 220V L57 15 DMX	840 neutral white	4000 K	26,505 lm
911401749533	BVP354 144LED RGB 220V L57 15 DMX	RGB	-	14,080 lm
911401749543	BVP354 144LED RGBWW 220V L57 15 DMX	RGBW	-	15,115 lm
911401749553	BVP354 144LED RGBNW 220V L57 15 DMX	RGBW	-	15,785 lm
911401749563	BVP354 144LED 27K 220V L57 30	827 warm white	2700 K	24,755 lm
911401749573	BVP354 144LED 30K 220V L57 30	830 warm white	3000 K	25,820 lm
911401749583	BVP354 144LED 40K 220V L57 30	840 neutral white	4000 K	28,810 lm

Order Code	Full Product Name	Light source	Correlated Color	
		color	Temperature (Nom)	Luminous Flux
911401749593	BVP354 144LED 27K 220V L57 30 DMX	827 warm white	2700 K	23,585 lm
911401749603	BVP354 144LED 30K 220V L57 30 DMX	830 warm white	3000 K	24,605 lm
911401749613	BVP354 144LED 40K 220V L57 30 DMX	840 neutral white	4000 K	27,450 lm
911401749623	BVP354 144LED RGB 220V L57 30 DMX	RGB	-	14,585 lm
911401749633	BVP354 144LED RGBWW 220V L57 30 DMX	RGBW	-	15,655 lm
911401749643	BVP354 144LED RGBNW 220V L57 30 DMX	RGBW	-	16,345 lm
911401749653	BVP354 144LED 27K 220V L57 45	827 warm white	2700 K	23,900 lm
911401749663	BVP354 144LED 30K 220V L57 45	830 warm white	3000 K	24,930 lm
911401749673	BVP354 144LED 40K 220V L57 45	840 neutral white	4000 K	27,815 lm
911401749683	BVP354 144LED 27K 220V L57 45 DMX	827 warm white	2700 K	22,775 lm
911401749693	BVP354 144LED 30K 220V L57 45 DMX	830 warm white	3000 K	23,755 lm
911401749703	BVP354 144LED 40K 220V L57 45 DMX	840 neutral white	4000 K	26,505 lm
911401749713	BVP354 144LED RGB 220V L57 45 DMX	RGB	-	14,080 lm
911401749723	BVP354 144LED RGBWW 220V L57 45 DMX	RGBW	-	15,115 lm
911401749733	BVP354 144LED RGBNW 220V L57 45 DMX	RGBW	-	15,785 lm
911401748303	BVP353 72LED 27K 220V L57 10	827 warm white	2700 K	11,380 lm
911401748313	BVP353 72LED 30K 220V L57 10	830 warm white	3000 K	11,870 lm
911401748323	BVP353 72LED 40K 220V L57 10	840 neutral white	4000 K	13,245 lm
911401748333	BVP353 72LED 27K 220V L57 10 DMX	827 warm white	2700 K	10,845 lm
911401748343	BVP353 72LED 30K 220V L57 10 DMX	830 warm white	3000 K	11,310 lm
911401748353	BVP353 72LED 40K 220V L57 10 DMX	840 neutral white	4000 K	12,620 lm
911401748363	BVP353 72LED RGB 220V L57 10 DMX	RGB	-	6,705 lm
911401748373	BVP353 72LED RGBWW 220V L57 10 DMX	RGBW	-	7,195 lm
911401748383	BVP353 72LED RGBNW 220V L57 10 DMX	RGBW	-	7,515 lm
911401748393	BVP353 72LED 27K 220V L57 15	827 warm white	2700 K	11,950 lm
911401748403	BVP353 72LED 30K 220V L57 15	830 warm white	3000 K	12,465 lm
911401748413	BVP353 72LED 40K 220V L57 15	840 neutral white	4000 K	13,905 lm
911401748423	BVP353 72LED 27K 220V L57 15 DMX	827 warm white	2700 K	11,385 lm
911401748433	BVP353 72LED 30K 220V L57 15 DMX	830 warm white	3000 K	11,875 lm
911401748443	BVP353 72LED 40K 220V L57 15 DMX	840 neutral white	4000 K	13,250 lm
911401748453	BVP353 72LED RGB 220V L57 15 DMX	RGB	-	7,040 lm
911401748463	BVP353 72LED RGBWW 220V L57 15 DMX	RGBW	-	7,555 lm
911401748473	BVP353 72LED RGBNW 220V L57 15 DMX	RGBW	-	7,890 lm
911401748483	BVP353 72LED 27K 220V L57 30	827 warm white	2700 K	12,375 lm
911401748493	BVP353 72LED 30K 220V L57 30	830 warm white	3000 K	12,910 lm
911401748503	BVP353 72LED 40K 220V L57 30	840 neutral white	4000 K	14,405 lm
911401748513	BVP353 72LED 27K 220V L57 30 DMX	827 warm white	2700 K	11,790 lm

Order Code	Full Product Name	Light source	Correlated Color	Luminous Flux
		color	Temperature (Nom)	
911401748523	BVP353 72LED 30K 220V L57 30 DMX	830 warm white	3000 K	12,300 lm
911401748533	BVP353 72LED 40K 220V L57 30 DMX	840 neutral white	4000 K	13,725 lm
911401748543	BVP353 72LED RGB 220V L57 30 DMX	RGB	-	7,290 lm
911401748553	BVP353 72LED RGBWW 220V L57 30 DMX	RGBW	-	7,825 lm
911401748563	BVP353 72LED RGBNW 220V L57 30 DMX	RGBW	-	8,170 lm
911401748573	BVP353 72LED 27K 220V L57 45	827 warm white	2700 K	11,950 lm
911401748583	BVP353 72LED 30K 220V L57 45	830 warm white	3000 K	12,465 lm
911401748593	BVP353 72LED 40K 220V L57 45	840 neutral white	4000 K	13,905 lm
911401748603	BVP353 72LED 27K 220V L57 45 DMX	827 warm white	2700 K	11,385 lm
911401748613	BVP353 72LED 30K 220V L57 45 DMX	830 warm white	3000 K	11,875 lm
911401748623	BVP353 72LED 40K 220V L57 45 DMX	840 neutral white	4000 K	13,250 lm
911401748633	BVP353 72LED RGB 220V L57 45 DMX	RGB	-	7,040 lm
911401748643	BVP353 72LED RGBWW 220V L57 45 DMX	RGBW	-	7,555 lm
911401748653	BVP353 72LED RGBNW 220V L57 45 DMX	RGBW	-	7,890 lm
911401746143	BVP353 18LED 27K 220V L21 10	827 warm white	2700 K	2,845 lm
911401746153	BVP353 18LED 30K 220V L21 10	830 warm white	3000 K	2,965 lm
911401746163	BVP353 18LED 40K 220V L21 10	840 neutral white	4000 K	3,310 lm
911401746173	BVP353 18LED 27K 220V L21 10 DMX	827 warm white	2700 K	2,640 lm
911401746183	BVP353 18LED 30K 220V L21 10 DMX	830 warm white	3000 K	2,755 lm
911401746193	BVP353 18LED 40K 220V L21 10 DMX	840 neutral white	4000 K	3,075 lm
911401746203	BVP353 18LED RGB 220V L21 10 DMX	RGB	-	1,565 lm
911401746213	BVP353 20LED RGBWW 220V L21 10 DMX	RGBW	-	1,860 lm
911401746223	BVP353 20LED RGBNW 220V L21 10 DMX	RGBW	-	1,945 lm
911401746233	BVP353 18LED 27K 220V L21 15	827 warm white	2700 K	2,985 lm
911401746243	BVP353 18LED 30K 220V L21 15	830 warm white	3000 K	3,115 lm
911401746253	BVP353 18LED 40K 220V L21 15	840 neutral white	4000 K	3,475 lm
911401746263	BVP353 18LED 27K 220V L21 15 DMX	827 warm white	2700 K	2,770 lm
911401746273	BVP353 18LED 30K 220V L21 15 DMX	830 warm white	3000 K	2,890 lm
911401746283	BVP353 18LED 40K 220V L21 15 DMX	840 neutral white	4000 K	3,225 lm
911401746293	BVP353 18LED RGB 220V L21 15 DMX	RGB	-	1,640 lm
911401746303	BVP353 20LED RGBWW 220V L21 15 DMX	RGBW	-	1,955 lm
911401746313	BVP353 20LED RGBNW 220V L21 15 DMX	RGBW	-	2,040 lm
911401746323	BVP353 18LED 27K 220V L21 30	827 warm white	2700 K	3,090 lm
911401746333	BVP353 18LED 30K 220V L21 30	830 warm white	3000 K	3,225 lm
911401746343	BVP353 18LED 40K 220V L21 30	840 neutral white	4000 K	3,600 lm
911401746353	BVP353 18LED 27K 220V L21 30 DMX	827 warm white	2700 K	2,870 lm
911401746363	BVP353 18LED 30K 220V L21 30 DMX	830 warm white	3000 K	2,995 lm
911401746373	BVP353 18LED 40K 220V L21 30 DMX	840 neutral white	4000 K	3,340 lm
911401746383	BVP353 18LED RGB 220V L21 30 DMX	RGB	-	1,700 lm
911401746393	BVP353 20LED RGBWW 220V L21 30 DMX	RGBW	-	2,025 lm
911401746403	BVP353 20LED RGBNW 220V L21 30 DMX	RGBW	-	2,115 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401746413	BVP353 18LED 27K 220V L21 45	827 warm white	2700 K	2,985 lm
911401746423	BVP353 18LED 30K 220V L21 45	830 warm white	3000 K	3,115 lm
911401746433	BVP353 18LED 40K 220V L21 45	840 neutral white	4000 K	3,475 lm
911401746443	BVP353 18LED 27K 220V L21 45 DMX	827 warm white	2700 K	2,770 lm
911401746453	BVP353 18LED 30K 220V L21 45 DMX	830 warm white	3000 K	2,890 lm
911401746463	BVP353 18LED 40K 220V L21 45 DMX	840 neutral white	4000 K	3,225 lm
911401746473	BVP353 18LED RGB 220V L21 45 DMX	RGB	-	1,640 lm
911401746483	BVP353 20LED RGBWW 220V L21 45 DMX	RGBW	-	1,955 lm
911401746493	BVP353 20LED RGBNW 220V L21 45 DMX	RGBW	-	2,040 lm
911401745423	BVP353 12LED 27K 220V L15 10	827 warm white	2700 K	1,760 lm
911401745433	BVP353 12LED 30K 220V L15 10	830 warm white	3000 K	1,835 lm
911401745443	BVP353 12LED 40K 220V L15 10	840 neutral white	4000 K	2,050 lm
911401745453	BVP353 12LED 27K 220V L15 10 DMX	827 warm white	2700 K	1,615 lm
911401745463	BVP353 12LED 30K 220V L15 10 DMX	830 warm white	3000 K	1,685 lm
911401745473	BVP353 12LED 40K 220V L15 10 DMX	840 neutral white	4000 K	1,880 lm
911401745483	BVP353 12LED RGB 220V L15 10 DMX	RGB	-	960 lm
911401745493	BVP353 12LED RGBWW 220V L15 10 DMX	RGBW	-	1,175 lm
911401745503	BVP353 12LED RGBNW 220V L15 10 DMX	RGBW	-	1,225 lm
911401745513	BVP353 12LED 27K 220V L15 15	827 warm white	2700 K	1,845 lm
911401745523	BVP353 12LED 30K 220V L15 15	830 warm white	3000 K	1,925 lm
911401745533	BVP353 12LED 40K 220V L15 15	840 neutral white	4000 K	2,150 lm
911401745543	BVP353 12LED 27K 220V L15 15 DMX	827 warm white	2700 K	1,695 lm
911401745553	BVP353 12LED 30K 220V L15 15 DMX	830 warm white	3000 K	1,770 lm
911401745563	BVP353 12LED 40K 220V L15 15 DMX	840 neutral white	4000 K	1,975 lm
911401745573	BVP353 12LED RGB 220V L15 15 DMX	RGB	-	1,010 lm
911401745583	BVP353 12LED RGBWW 220V L15 15 DMX	RGBW	-	1,230 lm
911401745593	BVP353 12LED RGBNW 220V L15 15 DMX	RGBW	-	1,285 lm
911401745603	BVP353 12LED 27K 220V L15 30	827 warm white	2700 K	1,915 lm
911401745613	BVP353 12LED 30K 220V L15 30	830 warm white	3000 K	1,995 lm
911401745623	BVP353 12LED 40K 220V L15 30	840 neutral white	4000 K	2,225 lm
911401745633	BVP353 12LED 27K 220V L15 30 DMX	827 warm white	2700 K	1,755 lm
911401745643	BVP353 12LED 30K 220V L15 30 DMX	830 warm white	3000 K	1,830 lm
911401745653	BVP353 12LED 40K 220V L15 30 DMX	840 neutral white	4000 K	2,045 lm
911401745663	BVP353 12LED RGB 220V L15 30 DMX	RGB	-	1,045 lm
911401745673	BVP353 12LED RGBWW 220V L15 30 DMX	RGBW	-	1,275 lm
911401745683	BVP353 12LED RGBNW 220V L15 30 DMX	RGBW	-	1,330 lm
911401745693	BVP353 12LED 27K 220V L15 45	827 warm white	2700 K	1,845 lm
911401745703	BVP353 12LED 30K 220V L15 45	830 warm white	3000 K	1,925 lm
911401745713	BVP353 12LED 40K 220V L15 45	840 neutral white	4000 K	2,150 lm
911401745723	BVP353 12LED 27K 220V L15 45 DMX	827 warm white	2700 K	1,695 lm
911401745733	BVP353 12LED 30K 220V L15 45 DMX	830 warm white	3000 K	1,770 lm
911401745743	BVP353 12LED 40K 220V L15 45 DMX	840 neutral white	4000 K	1,975 lm
911401745753	BVP353 12LED RGB 220V L15 45 DMX	RGB	-	1,010 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401745763	BVP353 12LED RGBWW 220V L15 45 DMX	RGBW	-	1,230 lm
911401745773	BVP353 12LED RGBNW 220V L15 45 DMX	RGBW	-	1,285 lm
911401747223	BVP353 36LED 27K 220V L35 10	827 warm white	2700 K	5,950 lm
911401747233	BVP353 36LED 30K 220V L35 10	830 warm white	3000 K	6,205 lm
911401747243	BVP353 36LED 40K 220V L35 10	840 neutral white	4000 K	6,925 lm
911401747253	BVP353 36LED 27K 220V L35 10 DMX	827 warm white	2700 K	5,350 lm
911401747263	BVP353 36LED 30K 220V L35 10 DMX	830 warm white	3000 K	5,585 lm
911401747273	BVP353 36LED 40K 220V L35 10 DMX	840 neutral white	4000 K	6,230 lm
911401747283	BVP353 36LED RGB 220V L35 10 DMX	RGB	-	3,290 lm
911401747293	BVP353 36LED RGBWW 220V L35 10 DMX	RGBW	-	3,640 lm
911401747303	BVP353 36LED RGBNW 220V L35 10 DMX	RGBW	-	3,805 lm
911401747313	BVP353 36LED 27K 220V L35 15	827 warm white	2700 K	6,245 lm
911401747323	BVP353 36LED 30K 220V L35 15	830 warm white	3000 K	6,515 lm
911401747333	BVP353 36LED 40K 220V L35 15	840 neutral white	4000 K	7,270 lm
911401747343	BVP353 36LED 27K 220V L35 15 DMX	827 warm white	2700 K	5,620 lm
911401747353	BVP353 36LED 30K 220V L35 15 DMX	830 warm white	3000 K	5,860 lm
911401747363	BVP353 36LED 40K 220V L35 15 DMX	840 neutral white	4000 K	6,540 lm
911401747373	BVP353 36LED RGB 220V L35 15 DMX	RGB	-	3,455 lm
911401747383	BVP353 36LED RGBWW 220V L35 15 DMX	RGBW	-	3,825 lm
911401747393	BVP353 36LED RGBNW 220V L35 15 DMX	RGBW	-	3,995 lm
911401747403	BVP353 36LED 27K 220V L35 30	827 warm white	2700 K	6,470 lm
911401747413	BVP353 36LED 30K 220V L35 30	830 warm white	3000 K	6,750 lm
911401747423	BVP353 36LED 40K 220V L35 30	840 neutral white	4000 K	7,530 lm
911401747433	BVP353 36LED 27K 220V L35 30 DMX	827 warm white	2700 K	5,820 lm
911401747443	BVP353 36LED 30K 220V L35 30 DMX	830 warm white	3000 K	6,070 lm
911401747453	BVP353 36LED 40K 220V L35 30 DMX	840 neutral white	4000 K	6,775 lm
911401747463	BVP353 36LED RGB 220V L35 30 DMX	RGB	-	3,580 lm
911401747473	BVP353 36LED RGBWW 220V L35 30 DMX	RGBW	-	3,960 lm
911401747483	BVP353 36LED RGBNW 220V L35 30 DMX	RGBW	-	4,135 lm
911401747493	BVP353 36LED 27K 220V L35 45	827 warm white	2700 K	6,245 lm
911401747503	BVP353 36LED 30K 220V L35 45	830 warm white	3000 K	6,515 lm
911401747513	BVP353 36LED 40K 220V L35 45	840 neutral white	4000 K	7,270 lm
911401747523	BVP353 36LED 27K 220V L35 45 DMX	827 warm white	2700 K	5,620 lm
911401747533	BVP353 36LED 30K 220V L35 45 DMX	830 warm white	3000 K	5,860 lm
911401747543	BVP353 36LED 40K 220V L35 45 DMX	840 neutral white	4000 K	6,540 lm
911401747553	BVP353 36LED RGB 220V L35 45 DMX	RGB	-	3,455 lm
911401747563	BVP353 36LED RGBWW 220V L35 45 DMX	RGBW	-	3,825 lm
911401747573	BVP353 36LED RGBNW 220V L35 45 DMX	RGBW	-	3,995 lm
911401746503	BVP353 24LED 27K 220V L24 10	827 warm white	2700 K	3,615 lm
911401746513	BVP353 24LED 30K 220V L24 10	830 warm white	3000 K	3,770 lm

Order Code	Full Product Name	Light source	Correlated Color	
		color	Temperature (Nom)	Luminous Flux
911401746523	BVP353 24LED 40K 220V L24 10	840 neutral white	4000 K	4,205 lm
911401746533	BVP353 24LED 27K 220V L24 10 DMX	827 warm white	2700 K	3,465 lm
911401746543	BVP353 24LED 30K 220V L24 10 DMX	830 warm white	3000 K	3,615 lm
911401746553	BVP353 24LED 40K 220V L24 10 DMX	840 neutral white	4000 K	4,035 lm
911401746563	BVP353 24LED RGB 220V L24 10 DMX	RGB	-	2,085 lm
911401746573	BVP353 24LED RGBWW 220V L24 10 DMX	RGBW	-	2,350 lm
911401746583	BVP353 24LED RGBNW 220V L24 10 DMX	RGBW	-	2,450 lm
911401746593	BVP353 24LED 27K 220V L24 15	827 warm white	2700 K	3,795 lm
911401746603	BVP353 24LED 30K 220V L24 15	830 warm white	3000 K	3,955 lm
911401746613	BVP353 24LED 40K 220V L24 15	840 neutral white	4000 K	4,415 lm
911401746623	BVP353 24LED 27K 220V L24 15 DMX	827 warm white	2700 K	3,640 lm
911401746633	BVP353 24LED 30K 220V L24 15 DMX	830 warm white	3000 K	3,800 lm
911401746643	BVP353 24LED 40K 220V L24 15 DMX	840 neutral white	4000 K	4,235 lm
911401746653	BVP353 24LED RGB 220V L24 15 DMX	RGB	-	2,190 lm
911401746663	BVP353 24LED RGBWW 220V L24 15 DMX	RGBW	-	2,465 lm
911401746673	BVP353 24LED RGBNW 220V L24 15 DMX	RGBW	-	2,575 lm
911401746683	BVP353 24LED 27K 220V L24 30	827 warm white	2700 K	3,930 lm
911401746693	BVP353 24LED 30K 220V L24 30	830 warm white	3000 K	4,100 lm
911401746703	BVP353 24LED 40K 220V L24 30	840 neutral white	4000 K	4,575 lm
911401746713	BVP353 24LED 27K 220V L24 30 DMX	827 warm white	2700 K	3,770 lm
911401746723	BVP353 24LED 30K 220V L24 30 DMX	830 warm white	3000 K	3,935 lm
911401746733	BVP353 24LED 40K 220V L24 30 DMX	840 neutral white	4000 K	4,390 lm
911401746743	BVP353 24LED RGB 220V L24 30 DMX	RGB	-	2,270 lm
911401746753	BVP353 24LED RGBWW 220V L24 30 DMX	RGBW	-	2,555 lm
911401746763	BVP353 24LED RGBNW 220V L24 30 DMX	RGBW	-	2,665 lm
911401746773	BVP353 24LED 27K 220V L24 45	827 warm white	2700 K	3,795 lm
911401746783	BVP353 24LED 30K 220V L24 45	830 warm white	3000 K	3,955 lm
911401746793	BVP353 24LED 40K 220V L24 45	840 neutral white	4000 K	4,415 lm
911401746803	BVP353 24LED 27K 220V L24 45 DMX	827 warm white	2700 K	3,640 lm
911401746813	BVP353 24LED 30K 220V L24 45 DMX	830 warm white	3000 K	3,800 lm
911401746823	BVP353 24LED 40K 220V L24 45 DMX	840 neutral white	4000 K	4,235 lm
911401746833	BVP353 24LED RGB 220V L24 45 DMX	RGB	-	2,190 lm
911401746843	BVP353 24LED RGBWW 220V L24 45 DMX	RGBW	-	2,465 lm
911401746853	BVP353 24LED RGBNW 220V L24 45 DMX	RGBW	-	2,575 lm
911401747943	BVP353 60LED 27K 220V L50 10	827 warm white	2700 K	9,150 lm
911401747953	BVP353 60LED 30K 220V L50 10	830 warm white	3000 K	9,540 lm
911401747963	BVP353 60LED 40K 220V L50 10	840 neutral white	4000 K	10,645 lm
911401747973	BVP353 60LED 27K 220V L50 10 DMX	827 warm white	2700 K	8,805 lm
911401747983	BVP353 60LED 30K 220V L50 10 DMX	830 warm white	3000 K	9,185 lm
911401747993	BVP353 60LED 40K 220V L50 10 DMX	840 neutral white	4000 K	10,250 lm
911401748003	BVP353 60LED RGB 220V L50 10 DMX	RGB	-	5,215 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401748013	BVP353 60LED RGBWW 220V L50 10 DMX	RGBW	-	5,995 lm
911401748023	BVP353 60LED RGBNW 220V L50 10 DMX	RGBW	-	6,260 lm
911401748033	BVP353 60LED 27K 220V L50 15	827 warm white	2700 K	9,605 lm
911401748043	BVP353 60LED 30K 220V L50 15	830 warm white	3000 K	10,020 lm
911401748053	BVP353 60LED 40K 220V L50 15	840 neutral white	4000 K	11,180 lm
911401748063	BVP353 60LED 27K 220V L50 15 DMX	827 warm white	2700 K	9,245 lm
911401748073	BVP353 60LED 30K 220V L50 15 DMX	830 warm white	3000 K	9,645 lm
911401748083	BVP353 60LED 40K 220V L50 15 DMX	840 neutral white	4000 K	10,760 lm
911401748093	BVP353 60LED RGB 220V L50 15 DMX	RGB	-	5,480 lm
911401748103	BVP353 60LED RGBWW 220V L50 15 DMX	RGBW	-	6,295 lm
911401748113	BVP353 60LED RGBNW 220V L50 15 DMX	RGBW	-	6,575 lm
911401748123	BVP353 60LED 27K 220V L50 30	827 warm white	2700 K	9,950 lm
911401748133	BVP353 60LED 30K 220V L50 30	830 warm white	3000 K	10,380 lm
911401748143	BVP353 60LED 40K 220V L50 30	840 neutral white	4000 K	11,580 lm
911401748153	BVP353 60LED 27K 220V L50 30 DMX	827 warm white	2700 K	9,575 lm
911401748163	BVP353 60LED 30K 220V L50 30 DMX	830 warm white	3000 K	9,990 lm
911401748173	BVP353 60LED 40K 220V L50 30 DMX	840 neutral white	4000 K	11,145 lm
911401748183	BVP353 60LED RGB 220V L50 30 DMX	RGB	-	5,675 lm
911401748193	BVP353 60LED RGBWW 220V L50 30 DMX	RGBW	-	6,520 lm
911401748203	BVP353 60LED RGBNW 220V L50 30 DMX	RGBW	-	6,810 lm
911401748213	BVP353 60LED 27K 220V L50 45	827 warm white	2700 K	9,605 lm
911401748223	BVP353 60LED 30K 220V L50 45	830 warm white	3000 K	10,020 lm
911401748233	BVP353 60LED 40K 220V L50 45	840 neutral white	4000 K	11,180 lm
911401748243	BVP353 60LED 27K 220V L50 45 DMX	827 warm white	2700 K	9,245 lm
911401748253	BVP353 60LED 30K 220V L50 45 DMX	830 warm white	3000 K	9,645 lm
911401748263	BVP353 60LED 40K 220V L50 45 DMX	840 neutral white	4000 K	10,760 lm
911401748273	BVP353 60LED RGB 220V L50 45 DMX	RGB	-	5,480 lm
911401748283	BVP353 60LED RGBWW 220V L50 45 DMX	RGBW	-	6,295 lm
911401748293	BVP353 60LED RGBNW 220V L50 45 DMX	RGBW	-	6,575 lm
911401745783	BVP353 16LED 27K 220V L18 10	827 warm white	2700 K	2,755 lm
911401745793	BVP353 16LED 30K 220V L18 10	830 warm white	3000 K	2,875 lm
911401745803	BVP353 16LED 40K 220V L18 10	840 neutral white	4000 K	3,205 lm
911401745813	BVP353 16LED 27K 220V L18 10 DMX	827 warm white	2700 K	2,060 lm
911401745823	BVP353 16LED 30K 220V L18 10 DMX	830 warm white	3000 K	2,145 lm
911401745833	BVP353 16LED 40K 220V L18 10 DMX	840 neutral white	4000 K	2,395 lm
911401745843	BVP353 15LED RGB 220V L18 10 DMX	RGB	-	1,200 lm
911401745853	BVP353 16LED RGBWW 220V L18 10 DMX	RGBW	-	1,425 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401745863	BVP353 16LED RGBNW 220V L18 10 DMX	RGBW	-	1,490 lm
911401745873	BVP353 16LED 27K 220V L18 15	827 warm white	2700 K	2,895 lm
911401745883	BVP353 16LED 30K 220V L18 15	830 warm white	3000 K	3,020 lm
911401745893	BVP353 16LED 40K 220V L18 15	840 neutral white	4000 K	3,365 lm
911401745903	BVP353 16LED 27K 220V L18 15 DMX	827 warm white	2700 K	2,160 lm
911401745913	BVP353 16LED 30K 220V L18 15 DMX	830 warm white	3000 K	2,255 lm
911401745923	BVP353 16LED 40K 220V L18 15 DMX	840 neutral white	4000 K	2,515 lm
911401745933	BVP353 15LED RGB 220V L18 15 DMX	RGB	-	1,260 lm
911401745943	BVP353 16LED RGBWW 220V L18 15 DMX	RGBW	-	1,500 lm
911401745953	BVP353 16LED RGBNW 220V L18 15 DMX	RGBW	-	1,565 lm
911401745963	BVP353 16LED 27K 220V L18 30	827 warm white	2700 K	2,995 lm
911401745973	BVP353 16LED 30K 220V L18 30	830 warm white	3000 K	3,125 lm
911401745983	BVP353 16LED 40K 220V L18 30	840 neutral white	4000 K	3,490 lm
911401745993	BVP353 16LED 27K 220V L18 30 DMX	827 warm white	2700 K	2,240 lm
911401746003	BVP353 16LED 30K 220V L18 30 DMX	830 warm white	3000 K	2,335 lm
911401746013	BVP353 16LED 40K 220V L18 30 DMX	840 neutral white	4000 K	2,605 lm
911401746023	BVP353 15LED RGB 220V L18 30 DMX	RGB	-	1,305 lm
911401746033	BVP353 16LED RGBWW 220V L18 30 DMX	RGBW	-	1,550 lm
911401746043	BVP353 16LED RGBNW 220V L18 30 DMX	RGBW	-	1,620 lm
911401746053	BVP353 16LED 27K 220V L18 45	827 warm white	2700 K	2,895 lm
911401746063	BVP353 16LED 30K 220V L18 45	830 warm white	3000 K	3,020 lm
911401746073	BVP353 16LED 40K 220V L18 45	840 neutral white	4000 K	3,365 lm
911401746083	BVP353 16LED 27K 220V L18 45 DMX	827 warm white	2700 K	2,160 lm
911401746093	BVP353 16LED 30K 220V L18 45 DMX	830 warm white	3000 K	2,255 lm
911401746103	BVP353 16LED 40K 220V L18 45 DMX	840 neutral white	4000 K	2,515 lm
911401746113	BVP353 15LED RGB 220V L18 45 DMX	RGB	-	1,260 lm
911401746123	BVP353 16LED RGBWW 220V L18 45 DMX	RGBW	-	1,500 lm
911401746133	BVP353 16LED RGBNW 220V L18 45 DMX	RGBW	-	1,565 lm
911401749743	BVP355 216LED 27K 220V L57 10	827 warm white	2700 K	34,145 lm
911401749753	BVP355 216LED 30K 220V L57 10	830 warm white	3000 K	35,615 lm
911401749763	BVP355 216LED 40K 220V L57 10	840 neutral white	4000 K	39,740 lm
911401749773	BVP355 216LED 27K 220V L57 10 DMX	827 warm white	2700 K	32,535 lm
911401749783	BVP355 216LED 30K 220V L57 10 DMX	830 warm white	3000 K	33,935 lm
911401749793	BVP355 216LED 40K 220V L57 10 DMX	840 neutral white	4000 K	37,860 lm
911401749803	BVP355 216LED RGB 220V L57 10 DMX	RGB	-	20,115 lm
911401749813	BVP355 216LED RGBWW 220V L57 10 DMX	RGBW	-	21,590 lm
911401749823	BVP355 216LED RGBNW 220V L57 10 DMX	RGBW	-	22,550 lm
911401749833	BVP355 216LED 27K 220V L57 15	827 warm white	2700 K	35,850 lm
911401749843	BVP355 216LED 30K 220V L57 15	830 warm white	3000 K	37,400 lm
911401749853	BVP355 216LED 40K 220V L57 15	840 neutral white	4000 K	41,725 lm
911401749863	BVP355 216LED 27K 220V L57 15 DMX	827 warm white	2700 K	34,160 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401749873	BVP355 216LED 30K 220V L57 15 DMX	830 warm white	3000 K	35,635 lm
911401749883	BVP355 216LED 40K 220V L57 15 DMX	840 neutral white	4000 K	39,755 lm
911401749893	BVP355 216LED RGB 220V L57 15 DMX	RGB	-	21,120 lm
911401749903	BVP355 216LED RGBWW 220V L57 15 DMX	RGBW	-	22,670 lm
911401749913	BVP355 216LED RGBNW 220V L57 15 DMX	RGBW	-	23,675 lm
911401749923	BVP355 216LED 27K 220V L57 30	827 warm white	2700 K	37,135 lm
911401749933	BVP355 216LED 30K 220V L57 30	830 warm white	3000 K	38,735 lm
911401749943	BVP355 216LED 40K 220V L57 30	840 neutral white	4000 K	43,215 lm
911401749953	BVP355 216LED 27K 220V L57 30 DMX	827 warm white	2700 K	35,380 lm
911401749963	BVP355 216LED 30K 220V L57 30 DMX	830 warm white	3000 K	36,905 lm
911401749973	BVP355 216LED 40K 220V L57 30 DMX	840 neutral white	4000 K	41,175 lm
911401749983	BVP355 216LED RGB 220V L57 30 DMX	RGB	-	21,875 lm
911401749993	BVP355 216LED RGBWW 220V L57 30 DMX	RGBW	-	23,480 lm
911401750003	BVP355 216LED RGBNW 220V L57 30 DMX	RGBW	-	24,520 lm
911401750013	BVP355 216LED 27K 220V L57 45	827 warm white	2700 K	35,850 lm
911401750023	BVP355 216LED 30K 220V L57 45	830 warm white	3000 K	37,400 lm
911401750033	BVP355 216LED 40K 220V L57 45	840 neutral white	4000 K	41,725 lm
911401750043	BVP355 216LED 27K 220V L57 45 DMX	827 warm white	2700 K	34,160 lm
911401750053	BVP355 216LED 30K 220V L57 45 DMX	830 warm white	3000 K	35,635 lm
911401750063	BVP355 216LED 40K 220V L57 45 DMX	840 neutral white	4000 K	39,755 lm
911401750073	BVP355 216LED RGB 220V L57 45 DMX	RGB	-	21,120 lm
911401750083	BVP355 216LED RGBWW 220V L57 45 DMX	RGBW	-	22,670 lm
911401750093	BVP355 216LED RGBNW 220V L57 45 DMX	RGBW	-	23,675 lm
911401750103	BVP355 180LED 27K 220V L50 10	827 warm white	2700 K	27,450 lm
911401750113	BVP355 180LED 30K 220V L50 10	830 warm white	3000 K	28,630 lm
911401750123	BVP355 180LED 40K 220V L50 10	840 neutral white	4000 K	31,945 lm
911401750133	BVP355 180LED 27K 220V L50 10 DMX	827 warm white	2700 K	26,425 lm
911401750143	BVP355 180LED 30K 220V L50 10 DMX	830 warm white	3000 K	27,565 lm
911401750153	BVP355 180LED 40K 220V L50 10 DMX	840 neutral white	4000 K	30,750 lm
911401750163	BVP355 180LED RGB 220V L50 10 DMX	RGB	-	15,655 lm
911401750173	BVP355 180LED RGBWW 220V L50 10 DMX	RGBW	-	17,990 lm
911401750183	BVP355 180LED RGBNW 220V L50 10 DMX	RGBW	-	18,790 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401750193	BVP355 180LED 27K 220V L50 15	827 warm white	2700 K	28,820 lm
911401750203	BVP355 180LED 30K 220V L50 15	830 warm white	3000 K	30,065 lm
911401750213	BVP355 180LED 40K 220V L50 15	840 neutral white	4000 K	33,540 lm
911401750223	BVP355 180LED 27K 220V L50 15 DMX	827 warm white	2700 K	27,745 lm
911401750233	BVP355 180LED 30K 220V L50 15 DMX	830 warm white	3000 K	28,940 lm
911401750243	BVP355 180LED 40K 220V L50 15 DMX	840 neutral white	4000 K	32,290 lm
911401750253	BVP355 180LED RGB 220V L50 15 DMX	RGB	-	16,440 lm
911401750263	BVP355 180LED RGBWW 220V L50 15 DMX	RGBW	-	18,890 lm
911401750273	BVP355 180LED RGBNW 220V L50 15 DMX	RGBW	-	19,730 lm
911401750283	BVP355 180LED 27K 220V L50 30	827 warm white	2700 K	29,850 lm
911401750293	BVP355 180LED 30K 220V L50 30	830 warm white	3000 K	31,140 lm
911401750303	BVP355 180LED 40K 220V L50 30	840 neutral white	4000 K	34,740 lm
911401750313	BVP355 180LED 27K 220V L50 30 DMX	827 warm white	2700 K	28,735 lm
911401750323	BVP355 180LED 30K 220V L50 30 DMX	830 warm white	3000 K	29,975 lm
911401750333	BVP355 180LED 40K 220V L50 30 DMX	840 neutral white	4000 K	33,445 lm
911401750343	BVP355 180LED RGB 220V L50 30 DMX	RGB	-	17,025 lm
911401750353	BVP355 180LED RGBWW 220V L50 30 DMX	RGBW	-	19,565 lm
911401750363	BVP355 180LED RGBNW 220V L50 30 DMX	RGBW	-	20,435 lm
911401750373	BVP355 180LED 27K 220V L50 45	827 warm white	2700 K	28,820 lm
911401750383	BVP355 180LED 30K 220V L50 45	830 warm white	3000 K	30,065 lm
911401750393	BVP355 180LED 40K 220V L50 45	840 neutral white	4000 K	33,540 lm
911401750403	BVP355 180LED 27K 220V L50 45 DMX	827 warm white	2700 K	27,745 lm
911401750413	BVP355 180LED 30K 220V L50 45 DMX	830 warm white	3000 K	28,940 lm
911401750423	BVP355 180LED 40K 220V L50 45 DMX	840 neutral white	4000 K	32,290 lm
911401750433	BVP355 180LED RGB 220V L50 45 DMX	RGB	-	16,440 lm
911401750443	BVP355 180LED RGBWW 220V L50 45 DMX	RGBW	-	18,890 lm
911401750453	BVP355 180LED RGBNW 220V L50 45 DMX	RGBW	-	19,730 lm
911401747583	BVP353 48LED 27K 220V L40 10	827 warm white	2700 K	7,440 lm
911401747593	BVP353 48LED 30K 220V L40 10	830 warm white	3000 K	7,760 lm
911401747603	BVP353 48LED 40K 220V L40 10	840 neutral white	4000 K	8,655 lm
911401747613	BVP353 48LED 27K 220V L40 10 DMX	827 warm white	2700 K	6,860 lm
911401747623	BVP353 48LED 30K 220V L40 10 DMX	830 warm white	3000 K	7,155 lm
911401747633	BVP353 48LED 40K 220V L40 10 DMX	840 neutral white	4000 K	7,985 lm
911401747643	BVP353 48LED RGB 220V L40 10 DMX	RGB	-	3,830 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401747653	BVP353 48LED RGBWW 220V L40 10 DMX	RGBW	-	5,250 lm
911401747663	BVP353 48LED RGBNW 220V L40 10 DMX	RGBW	-	5,485 lm
911401747673	BVP353 48LED 27K 220V L40 15	827 warm white	2700 K	7,810 lm
911401747683	BVP353 48LED 30K 220V L40 15	830 warm white	3000 K	8,145 lm
911401747693	BVP353 48LED 40K 220V L40 15	840 neutral white	4000 K	9,090 lm
911401747703	BVP353 48LED 27K 220V L40 15 DMX	827 warm white	2700 K	7,205 lm
911401747713	BVP353 48LED 30K 220V L40 15 DMX	830 warm white	3000 K	7,515 lm
911401747723	BVP353 48LED 40K 220V L40 15 DMX	840 neutral white	4000 K	8,385 lm
911401747733	BVP353 48LED RGB 220V L40 15 DMX	RGB	-	4,020 lm
911401747743	BVP353 48LED RGBWW 220V L40 15 DMX	RGBW	-	5,515 lm
911401747753	BVP353 48LED RGBNW 220V L40 15 DMX	RGBW	-	5,760 lm
911401747763	BVP353 48LED 27K 220V L40 30	827 warm white	2700 K	8,090 lm
911401747773	BVP353 48LED 30K 220V L40 30	830 warm white	3000 K	8,440 lm
911401747783	BVP353 48LED 40K 220V L40 30	840 neutral white	4000 K	9,415 lm
911401747793	BVP353 48LED 27K 220V L40 30 DMX	827 warm white	2700 K	7,460 lm
911401747803	BVP353 48LED 30K 220V L40 30 DMX	830 warm white	3000 K	7,785 lm
911401747813	BVP353 48LED 40K 220V L40 30 DMX	840 neutral white	4000 K	8,685 lm
911401747823	BVP353 48LED RGB 220V L40 30 DMX	RGB	-	4,165 lm
911401747833	BVP353 48LED RGBWW 220V L40 30 DMX	RGBW	-	5,710 lm
911401747843	BVP353 48LED RGBNW 220V L40 30 DMX	RGBW	-	5,965 lm
911401747853	BVP353 48LED 27K 220V L40 45	827 warm white	2700 K	7,810 lm
911401747863	BVP353 48LED 30K 220V L40 45	830 warm white	3000 K	8,145 lm
911401747873	BVP353 48LED 40K 220V L40 45	840 neutral white	4000 K	9,090 lm
911401747883	BVP353 48LED 27K 220V L40 45 DMX	827 warm white	2700 K	7,205 lm
911401747893	BVP353 48LED 30K 220V L40 45 DMX	830 warm white	3000 K	7,515 lm
911401747903	BVP353 48LED 40K 220V L40 45 DMX	840 neutral white	4000 K	8,385 lm
911401747913	BVP353 48LED RGB 220V L40 45 DMX	RGB	-	4,020 lm
911401747923	BVP353 48LED RGBWW 220V L40 45 DMX	RGBW	-	5,515 lm
911401747933	BVP353 48LED RGBNW 220V L40 45 DMX	RGBW	-	5,760 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401746863	BVP353 30LED 27K 220V L30 10	60 W	911401746933	BVP353 32LED RGBWW 220V L30 10 DMX	60 W
911401746873	BVP353 30LED 30K 220V L30 10	60 W	911401746943	BVP353 32LED RGBNW 220V L30 10 DMX	60 W
911401746883	BVP353 30LED 40K 220V L30 10	60 W	911401746953	BVP353 30LED 27K 220V L30 15	60 W
911401746893	BVP353 30LED 27K 220V L30 10 DMX	60 W	911401746963	BVP353 30LED 30K 220V L30 15	60 W
911401746903	BVP353 30LED 30K 220V L30 10 DMX	60 W	911401746973	BVP353 30LED 40K 220V L30 15	60 W
911401746913	BVP353 30LED 40K 220V L30 10 DMX	60 W	911401746983	BVP353 30LED 27K 220V L30 15 DMX	60 W
911401746923	BVP353 30LED RGB 220V L30 10 DMX	60 W	911401746993	BVP353 30LED 30K 220V L30 15 DMX	60 W

Order Code	Full Product Name	Power Consumption
911401747003	BVP353 30LED 40K 220V L30 15 DMX	60 W
911401747013	BVP353 30LED RGB 220V L30 15 DMX	60 W
911401747023	BVP353 32LED RGBWW 220V L30 15 DMX	60 W
911401747033	BVP353 32LED RGBNW 220V L30 15 DMX	60 W
911401747043	BVP353 30LED 27K 220V L30 30	60 W
911401747053	BVP353 30LED 30K 220V L30 30	60 W
911401747063	BVP353 30LED 40K 220V L30 30	60 W
911401747073	BVP353 30LED 27K 220V L30 30 DMX	60 W
911401747083	BVP353 30LED 30K 220V L30 30 DMX	60 W
911401747093	BVP353 30LED 40K 220V L30 30 DMX	60 W
911401747103	BVP353 30LED RGB 220V L30 30 DMX	60 W
911401747113	BVP353 32LED RGBWW 220V L30 30 DMX	60 W
911401747123	BVP353 32LED RGBNW 220V L30 30 DMX	60 W
911401747133	BVP353 30LED 27K 220V L30 45	60 W
911401747143	BVP353 30LED 30K 220V L30 45	60 W
911401747153	BVP353 30LED 40K 220V L30 45	60 W
911401747163	BVP353 30LED 27K 220V L30 45 DMX	60 W
911401747173	BVP353 30LED 30K 220V L30 45 DMX	60 W
911401747183	BVP353 30LED 40K 220V L30 45 DMX	60 W
911401747193	BVP353 30LED RGB 220V L30 45 DMX	60 W
911401747203	BVP353 32LED RGBWW 220V L30 45 DMX	60 W
911401747213	BVP353 32LED RGBNW 220V L30 45 DMX	60 W
911401748663	BVP354 96LED 27K 220V L40 10	200 W
911401748673	BVP354 96LED 30K 220V L40 10	200 W
911401748683	BVP354 96LED 40K 220V L40 10	200 W
911401748693	BVP354 96LED 27K 220V L40 10 DMX	200 W
911401748703	BVP354 96LED 30K 220V L40 10 DMX	200 W
911401748713	BVP354 96LED 40K 220V L40 10 DMX	200 W
911401748723	BVP354 96LED RGB 220V L40 10 DMX	200 W
911401748733	BVP354 96LED RGBWW 220V L40 10 DMX	200 W
911401748743	BVP354 96LED RGBNW 220V L40 10 DMX	200 W
911401748753	BVP354 96LED 27K 220V L40 15	200 W
911401748763	BVP354 96LED 30K 220V L40 15	200 W
911401748773	BVP354 96LED 40K 220V L40 15	200 W
911401748783	BVP354 96LED 27K 220V L40 15 DMX	200 W
911401748793	BVP354 96LED 30K 220V L40 15 DMX	200 W
911401748803	BVP354 96LED 40K 220V L40 15 DMX	200 W
911401748813	BVP354 96LED RGB 220V L40 15 DMX	200 W
911401748823	BVP354 96LED RGBWW 220V L40 15 DMX	200 W
911401748833	BVP354 96LED RGBNW 220V L40 15 DMX	200 W
911401748843	BVP354 96LED 27K 220V L40 30	200 W
911401748853	BVP354 96LED 30K 220V L40 30	200 W
911401748863	BVP354 96LED 40K 220V L40 30	200 W
911401748873	BVP354 96LED 27K 220V L40 30 DMX	200 W
911401748883	BVP354 96LED 30K 220V L40 30 DMX	200 W
911401748893	BVP354 96LED 40K 220V L40 30 DMX	200 W
911401748903	BVP354 96LED RGB 220V L40 30 DMX	200 W
911401748913	BVP354 96LED RGBWW 220V L40 30 DMX	200 W
911401748923	BVP354 96LED RGBNW 220V L40 30 DMX	200 W
911401748933	BVP354 96LED 27K 220V L40 45	200 W
911401748943	BVP354 96LED 30K 220V L40 45	200 W
911401748953	BVP354 96LED 40K 220V L40 45	200 W

Order Code	Full Product Name	Power Consumption
911401748963	BVP354 96LED 27K 220V L40 45 DMX	200 W
911401748973	BVP354 96LED 30K 220V L40 45 DMX	200 W
911401748983	BVP354 96LED 40K 220V L40 45 DMX	200 W
911401748993	BVP354 96LED RGB 220V L40 45 DMX	200 W
911401749003	BVP354 96LED RGBWW 220V L40 45 DMX	200 W
911401749013	BVP354 96LED RGBNW 220V L40 45 DMX	200 W
911401749023	BVP354 120LED 27K 220V L50 10	240 W
911401749033	BVP354 120LED 30K 220V L50 10	240 W
911401749043	BVP354 120LED 40K 220V L50 10	240 W
911401749053	BVP354 120LED 27K 220V L50 10 DMX	240 W
911401749063	BVP354 120LED 30K 220V L50 10 DMX	240 W
911401749073	BVP354 120LED 40K 220V L50 10 DMX	240 W
911401749083	BVP354 120LED RGB 220V L50 10 DMX	240 W
911401749093	BVP354 120LED RGBWW 220V L50 10 DMX	240 W
911401749103	BVP354 120LED RGBNW 220V L50 10 DMX	240 W
911401749113	BVP354 120LED 27K 220V L50 15	240 W
911401749123	BVP354 120LED 30K 220V L50 15	240 W
911401749133	BVP354 120LED 40K 220V L50 15	240 W
911401749143	BVP354 120LED 27K 220V L50 15 DMX	240 W
911401749153	BVP354 120LED 30K 220V L50 15 DMX	240 W
911401749163	BVP354 120LED 40K 220V L50 15 DMX	240 W
911401749173	BVP354 120LED RGB 220V L50 15 DMX	240 W
911401749183	BVP354 120LED RGBWW 220V L50 15 DMX	240 W
911401749193	BVP354 120LED RGBNW 220V L50 15 DMX	240 W
911401749203	BVP354 120LED 27K 220V L50 30	240 W
911401749213	BVP354 120LED 30K 220V L50 30	240 W
911401749223	BVP354 120LED 40K 220V L50 30	240 W
911401749233	BVP354 120LED 27K 220V L50 30 DMX	240 W
911401749243	BVP354 120LED 30K 220V L50 30 DMX	240 W
911401749253	BVP354 120LED 40K 220V L50 30 DMX	240 W
911401749263	BVP354 120LED RGB 220V L50 30 DMX	240 W
911401749273	BVP354 120LED RGBWW 220V L50 30 DMX	240 W
911401749283	BVP354 120LED RGBNW 220V L50 30 DMX	240 W
911401749293	BVP354 120LED 27K 220V L50 45	240 W
911401749303	BVP354 120LED 30K 220V L50 45	240 W
911401749313	BVP354 120LED 40K 220V L50 45	240 W
911401749323	BVP354 120LED 27K 220V L50 45 DMX	240 W
911401749333	BVP354 120LED 30K 220V L50 45 DMX	240 W
911401749343	BVP354 120LED 40K 220V L50 45 DMX	240 W
911401749353	BVP354 120LED RGB 220V L50 45 DMX	240 W
911401749363	BVP354 120LED RGBWW 220V L50 45 DMX	240 W
911401749373	BVP354 120LED RGBNW 220V L50 45 DMX	240 W
911401749383	BVP354 144LED 27K 220V L57 10	300 W
911401749393	BVP354 144LED 30K 220V L57 10	300 W
911401749403	BVP354 144LED 40K 220V L57 10	300 W
911401749413	BVP354 144LED 27K 220V L57 10 DMX	300 W
911401749423	BVP354 144LED 30K 220V L57 10 DMX	300 W
911401749433	BVP354 144LED 40K 220V L57 10 DMX	300 W
911401749443	BVP354 144LED RGB 220V L57 10 DMX	300 W
911401749453	BVP354 144LED RGBWW 220V L57 10 DMX	300 W
911401749463	BVP354 144LED RGBNW 220V L57 10 DMX	300 W
911401749473	BVP354 144LED 27K 220V L57 15	300 W

Order Code	Full Product Name	Power Consumption
911401749483	BVP354 144LED 30K 220V L57 15	300 W
911401749493	BVP354 144LED 40K 220V L57 15	300 W
911401749503	BVP354 144LED 27K 220V L57 15 DMX	300 W
911401749513	BVP354 144LED 30K 220V L57 15 DMX	300 W
911401749523	BVP354 144LED 40K 220V L57 15 DMX	300 W
911401749533	BVP354 144LED RGB 220V L57 15 DMX	300 W
911401749543	BVP354 144LED RGBWW 220V L57 15 DMX	300 W
911401749553	BVP354 144LED RGBNW 220V L57 15 DMX	300 W
911401749563	BVP354 144LED 27K 220V L57 30	300 W
911401749573	BVP354 144LED 30K 220V L57 30	300 W
911401749583	BVP354 144LED 40K 220V L57 30	300 W
911401749593	BVP354 144LED 27K 220V L57 30 DMX	300 W
911401749603	BVP354 144LED 30K 220V L57 30 DMX	300 W
911401749613	BVP354 144LED 40K 220V L57 30 DMX	300 W
911401749623	BVP354 144LED RGB 220V L57 30 DMX	300 W
911401749633	BVP354 144LED RGBWW 220V L57 30 DMX	300 W
911401749643	BVP354 144LED RGBNW 220V L57 30 DMX	300 W
911401749653	BVP354 144LED 27K 220V L57 45	300 W
911401749663	BVP354 144LED 30K 220V L57 45	300 W
911401749673	BVP354 144LED 40K 220V L57 45	300 W
911401749683	BVP354 144LED 27K 220V L57 45 DMX	300 W
911401749693	BVP354 144LED 30K 220V L57 45 DMX	300 W
911401749703	BVP354 144LED 40K 220V L57 45 DMX	300 W
911401749713	BVP354 144LED RGB 220V L57 45 DMX	300 W
911401749723	BVP354 144LED RGBWW 220V L57 45 DMX	300 W
911401749733	BVP354 144LED RGBNW 220V L57 45 DMX	300 W
911401748303	BVP353 72LED 27K 220V L57 10	150 W
911401748313	BVP353 72LED 30K 220V L57 10	150 W
911401748323	BVP353 72LED 40K 220V L57 10	150 W
911401748333	BVP353 72LED 27K 220V L57 10 DMX	150 W
911401748343	BVP353 72LED 30K 220V L57 10 DMX	150 W
911401748353	BVP353 72LED 40K 220V L57 10 DMX	150 W
911401748363	BVP353 72LED RGB 220V L57 10 DMX	150 W
911401748373	BVP353 72LED RGBWW 220V L57 10 DMX	150 W
911401748383	BVP353 72LED RGBNW 220V L57 10 DMX	150 W
911401748393	BVP353 72LED 27K 220V L57 15	150 W
911401748403	BVP353 72LED 30K 220V L57 15	150 W
911401748413	BVP353 72LED 40K 220V L57 15	150 W
911401748423	BVP353 72LED 27K 220V L57 15 DMX	150 W
911401748433	BVP353 72LED 30K 220V L57 15 DMX	150 W
911401748443	BVP353 72LED 40K 220V L57 15 DMX	150 W
911401748453	BVP353 72LED RGB 220V L57 15 DMX	150 W
911401748463	BVP353 72LED RGBWW 220V L57 15 DMX	150 W
911401748473	BVP353 72LED RGBNW 220V L57 15 DMX	150 W
911401748483	BVP353 72LED 27K 220V L57 30	150 W
911401748493	BVP353 72LED 30K 220V L57 30	150 W
911401748503	BVP353 72LED 40K 220V L57 30	150 W
911401748513	BVP353 72LED 27K 220V L57 30 DMX	150 W
911401748523	BVP353 72LED 30K 220V L57 30 DMX	150 W
911401748533	BVP353 72LED 40K 220V L57 30 DMX	150 W
911401748543	BVP353 72LED RGB 220V L57 30 DMX	150 W
911401748553	BVP353 72LED RGBWW 220V L57 30 DMX	150 W

Order Code	Full Product Name	Power Consumption
911401748563	BVP353 72LED RGBNW 220V L57 30 DMX	150 W
911401748573	BVP353 72LED 27K 220V L57 45	150 W
911401748583	BVP353 72LED 30K 220V L57 45	150 W
911401748593	BVP353 72LED 40K 220V L57 45	150 W
911401748603	BVP353 72LED 27K 220V L57 45 DMX	150 W
911401748613	BVP353 72LED 30K 220V L57 45 DMX	150 W
911401748623	BVP353 72LED 40K 220V L57 45 DMX	150 W
911401748633	BVP353 72LED RGB 220V L57 45 DMX	150 W
911401748643	BVP353 72LED RGBWW 220V L57 45 DMX	150 W
911401748653	BVP353 72LED RGBNW 220V L57 45 DMX	150 W
911401746143	BVP353 18LED 27K 220V L21 10	40 W
911401746153	BVP353 18LED 30K 220V L21 10	40 W
911401746163	BVP353 18LED 40K 220V L21 10	40 W
911401746173	BVP353 18LED 27K 220V L21 10 DMX	40 W
911401746183	BVP353 18LED 30K 220V L21 10 DMX	40 W
911401746193	BVP353 18LED 40K 220V L21 10 DMX	40 W
911401746203	BVP353 18LED RGB 220V L21 10 DMX	40 W
911401746213	BVP353 20LED RGBWW 220V L21 10 DMX	40 W
911401746223	BVP353 20LED RGBNW 220V L21 10 DMX	40 W
911401746233	BVP353 18LED 27K 220V L21 15	40 W
911401746243	BVP353 18LED 30K 220V L21 15	40 W
911401746253	BVP353 18LED 40K 220V L21 15	40 W
911401746263	BVP353 18LED 27K 220V L21 15 DMX	40 W
911401746273	BVP353 18LED 30K 220V L21 15 DMX	40 W
911401746283	BVP353 18LED 40K 220V L21 15 DMX	40 W
911401746293	BVP353 18LED RGB 220V L21 15 DMX	40 W
911401746303	BVP353 20LED RGBWW 220V L21 15 DMX	40 W
911401746313	BVP353 20LED RGBNW 220V L21 15 DMX	40 W
911401746323	BVP353 18LED 27K 220V L21 30	40 W
911401746333	BVP353 18LED 30K 220V L21 30	40 W
911401746343	BVP353 18LED 40K 220V L21 30	40 W
911401746353	BVP353 18LED 27K 220V L21 30 DMX	40 W
911401746363	BVP353 18LED 30K 220V L21 30 DMX	40 W
911401746373	BVP353 18LED 40K 220V L21 30 DMX	40 W
911401746383	BVP353 18LED RGB 220V L21 30 DMX	40 W
911401746393	BVP353 20LED RGBWW 220V L21 30 DMX	40 W
911401746403	BVP353 20LED RGBNW 220V L21 30 DMX	40 W
911401746413	BVP353 18LED 27K 220V L21 45	40 W
911401746423	BVP353 18LED 30K 220V L21 45	40 W
911401746433	BVP353 18LED 40K 220V L21 45	40 W
911401746443	BVP353 18LED 27K 220V L21 45 DMX	40 W
911401746453	BVP353 18LED 30K 220V L21 45 DMX	40 W
911401746463	BVP353 18LED 40K 220V L21 45 DMX	40 W
911401746473	BVP353 18LED RGB 220V L21 45 DMX	40 W
911401746483	BVP353 20LED RGBWW 220V L21 45 DMX	40 W
911401746493	BVP353 20LED RGBNW 220V L21 45 DMX	40 W
911401745423	BVP353 12LED 27K 220V L15 10	24 W
911401745433	BVP353 12LED 30K 220V L15 10	24 W
911401745443	BVP353 12LED 40K 220V L15 10	24 W
911401745453	BVP353 12LED 27K 220V L15 10 DMX	24 W
911401745463	BVP353 12LED 30K 220V L15 10 DMX	24 W
911401745473	BVP353 12LED 40K 220V L15 10 DMX	24 W

Order Code	Full Product Name	Power Consumption
911401745483	BVP353 12LED RGB 220V L15 10 DMX	24 W
911401745493	BVP353 12LED RGBWW 220V L15 10 DMX	24 W
911401745503	BVP353 12LED RGBNW 220V L15 10 DMX	24 W
911401745513	BVP353 12LED 27K 220V L15 15	24 W
911401745523	BVP353 12LED 30K 220V L15 15	24 W
911401745533	BVP353 12LED 40K 220V L15 15	24 W
911401745543	BVP353 12LED 27K 220V L15 15 DMX	24 W
911401745553	BVP353 12LED 30K 220V L15 15 DMX	24 W
911401745563	BVP353 12LED 40K 220V L15 15 DMX	24 W
911401745573	BVP353 12LED RGB 220V L15 15 DMX	24 W
911401745583	BVP353 12LED RGBWW 220V L15 15 DMX	24 W
911401745593	BVP353 12LED RGBNW 220V L15 15 DMX	24 W
911401745603	BVP353 12LED 27K 220V L15 30	24 W
911401745613	BVP353 12LED 30K 220V L15 30	24 W
911401745623	BVP353 12LED 40K 220V L15 30	24 W
911401745633	BVP353 12LED 27K 220V L15 30 DMX	24 W
911401745643	BVP353 12LED 30K 220V L15 30 DMX	24 W
911401745653	BVP353 12LED 40K 220V L15 30 DMX	24 W
911401745663	BVP353 12LED RGB 220V L15 30 DMX	24 W
911401745673	BVP353 12LED RGBWW 220V L15 30 DMX	24 W
911401745683	BVP353 12LED RGBNW 220V L15 30 DMX	24 W
911401745693	BVP353 12LED 27K 220V L15 45	24 W
911401745703	BVP353 12LED 30K 220V L15 45	24 W
911401745713	BVP353 12LED 40K 220V L15 45	24 W
911401745723	BVP353 12LED 27K 220V L15 45 DMX	24 W
911401745733	BVP353 12LED 30K 220V L15 45 DMX	24 W
911401745743	BVP353 12LED 40K 220V L15 45 DMX	24 W
911401745753	BVP353 12LED RGB 220V L15 45 DMX	24 W
911401745763	BVP353 12LED RGBWW 220V L15 45 DMX	24 W
911401745773	BVP353 12LED RGBNW 220V L15 45 DMX	24 W
911401747223	BVP353 36LED 27K 220V L35 10	80 W
911401747233	BVP353 36LED 30K 220V L35 10	80 W
911401747243	BVP353 36LED 40K 220V L35 10	80 W
911401747253	BVP353 36LED 27K 220V L35 10 DMX	80 W
911401747263	BVP353 36LED 30K 220V L35 10 DMX	80 W
911401747273	BVP353 36LED 40K 220V L35 10 DMX	80 W
911401747283	BVP353 36LED RGB 220V L35 10 DMX	80 W
911401747293	BVP353 36LED RGBWW 220V L35 10 DMX	80 W
911401747303	BVP353 36LED RGBNW 220V L35 10 DMX	80 W
911401747313	BVP353 36LED 27K 220V L35 15	80 W
911401747323	BVP353 36LED 30K 220V L35 15	80 W
911401747333	BVP353 36LED 40K 220V L35 15	80 W
911401747343	BVP353 36LED 27K 220V L35 15 DMX	80 W
911401747353	BVP353 36LED 30K 220V L35 15 DMX	80 W
911401747363	BVP353 36LED 40K 220V L35 15 DMX	80 W
911401747373	BVP353 36LED RGB 220V L35 15 DMX	80 W
911401747383	BVP353 36LED RGBWW 220V L35 15 DMX	80 W
911401747393	BVP353 36LED RGBNW 220V L35 15 DMX	80 W
911401747403	BVP353 36LED 27K 220V L35 30	80 W
911401747413	BVP353 36LED 30K 220V L35 30	80 W
911401747423	BVP353 36LED 40K 220V L35 30	80 W
911401747433	BVP353 36LED 27K 220V L35 30 DMX	80 W

Order Code	Full Product Name	Power Consumption
911401747443	BVP353 36LED 30K 220V L35 30 DMX	80 W
911401747453	BVP353 36LED 40K 220V L35 30 DMX	80 W
911401747463	BVP353 36LED RGB 220V L35 30 DMX	80 W
911401747473	BVP353 36LED RGBWW 220V L35 30 DMX	80 W
911401747483	BVP353 36LED RGBNW 220V L35 30 DMX	80 W
911401747493	BVP353 36LED 27K 220V L35 45	80 W
911401747503	BVP353 36LED 30K 220V L35 45	80 W
911401747513	BVP353 36LED 40K 220V L35 45	80 W
911401747523	BVP353 36LED 27K 220V L35 45 DMX	80 W
911401747533	BVP353 36LED 30K 220V L35 45 DMX	80 W
911401747543	BVP353 36LED 40K 220V L35 45 DMX	80 W
911401747553	BVP353 36LED RGB 220V L35 45 DMX	80 W
911401747563	BVP353 36LED RGBWW 220V L35 45 DMX	80 W
911401747573	BVP353 36LED RGBNW 220V L35 45 DMX	80 W
911401746503	BVP353 24LED 27K 220V L24 10	50 W
911401746513	BVP353 24LED 30K 220V L24 10	50 W
911401746523	BVP353 24LED 40K 220V L24 10	50 W
911401746533	BVP353 24LED 27K 220V L24 10 DMX	50 W
911401746543	BVP353 24LED 30K 220V L24 10 DMX	50 W
911401746553	BVP353 24LED 40K 220V L24 10 DMX	50 W
911401746563	BVP353 24LED RGB 220V L24 10 DMX	50 W
911401746573	BVP353 24LED RGBWW 220V L24 10 DMX	50 W
911401746583	BVP353 24LED RGBNW 220V L24 10 DMX	50 W
911401746593	BVP353 24LED 27K 220V L24 15	50 W
911401746603	BVP353 24LED 30K 220V L24 15	50 W
911401746613	BVP353 24LED 40K 220V L24 15	50 W
911401746623	BVP353 24LED 27K 220V L24 15 DMX	50 W
911401746633	BVP353 24LED 30K 220V L24 15 DMX	50 W
911401746643	BVP353 24LED 40K 220V L24 15 DMX	50 W
911401746653	BVP353 24LED RGB 220V L24 15 DMX	50 W
911401746663	BVP353 24LED RGBWW 220V L24 15 DMX	50 W
911401746673	BVP353 24LED RGBNW 220V L24 15 DMX	50 W
911401746683	BVP353 24LED 27K 220V L24 30	50 W
911401746693	BVP353 24LED 30K 220V L24 30	50 W
911401746703	BVP353 24LED 40K 220V L24 30	50 W
911401746713	BVP353 24LED 27K 220V L24 30 DMX	50 W
911401746723	BVP353 24LED 30K 220V L24 30 DMX	50 W
911401746733	BVP353 24LED 40K 220V L24 30 DMX	50 W
911401746743	BVP353 24LED RGB 220V L24 30 DMX	50 W
911401746753	BVP353 24LED RGBWW 220V L24 30 DMX	50 W
911401746763	BVP353 24LED RGBNW 220V L24 30 DMX	50 W
911401746773	BVP353 24LED 27K 220V L24 45	50 W
911401746783	BVP353 24LED 30K 220V L24 45	50 W
911401746793	BVP353 24LED 40K 220V L24 45	50 W
911401746803	BVP353 24LED 27K 220V L24 45 DMX	50 W
911401746813	BVP353 24LED 30K 220V L24 45 DMX	50 W
911401746823	BVP353 24LED 40K 220V L24 45 DMX	50 W
911401746833	BVP353 24LED RGB 220V L24 45 DMX	50 W
911401746843	BVP353 24LED RGBWW 220V L24 45 DMX	50 W
911401746853	BVP353 24LED RGBNW 220V L24 45 DMX	50 W
911401747943	BVP353 60LED 27K 220V L50 10	120 W
911401747953	BVP353 60LED 30K 220V L50 10	120 W

Order Code	Full Product Name	Power Consumption
911401747963	BVP353 60LED 40K 220V L50 10	120 W
911401747973	BVP353 60LED 27K 220V L50 10 DMX	120 W
911401747983	BVP353 60LED 30K 220V L50 10 DMX	120 W
911401747993	BVP353 60LED 40K 220V L50 10 DMX	120 W
911401748003	BVP353 60LED RGB 220V L50 10 DMX	120 W
911401748013	BVP353 60LED RGBWW 220V L50 10 DMX	120 W
911401748023	BVP353 60LED RGBNW 220V L50 10 DMX	120 W
911401748033	BVP353 60LED 27K 220V L50 15	120 W
911401748043	BVP353 60LED 30K 220V L50 15	120 W
911401748053	BVP353 60LED 40K 220V L50 15	120 W
911401748063	BVP353 60LED 27K 220V L50 15 DMX	120 W
911401748073	BVP353 60LED 30K 220V L50 15 DMX	120 W
911401748083	BVP353 60LED 40K 220V L50 15 DMX	120 W
911401748093	BVP353 60LED RGB 220V L50 15 DMX	120 W
911401748103	BVP353 60LED RGBWW 220V L50 15 DMX	120 W
911401748113	BVP353 60LED RGBNW 220V L50 15 DMX	120 W
911401748123	BVP353 60LED 27K 220V L50 30	120 W
911401748133	BVP353 60LED 30K 220V L50 30	120 W
911401748143	BVP353 60LED 40K 220V L50 30	120 W
911401748153	BVP353 60LED 27K 220V L50 30 DMX	120 W
911401748163	BVP353 60LED 30K 220V L50 30 DMX	120 W
911401748173	BVP353 60LED 40K 220V L50 30 DMX	120 W
911401748183	BVP353 60LED RGB 220V L50 30 DMX	120 W
911401748193	BVP353 60LED RGBWW 220V L50 30 DMX	120 W
911401748203	BVP353 60LED RGBNW 220V L50 30 DMX	120 W
911401748213	BVP353 60LED 27K 220V L50 45	120 W
911401748223	BVP353 60LED 30K 220V L50 45	120 W
911401748233	BVP353 60LED 40K 220V L50 45	120 W
911401748243	BVP353 60LED 27K 220V L50 45 DMX	120 W
911401748253	BVP353 60LED 30K 220V L50 45 DMX	120 W
911401748263	BVP353 60LED 40K 220V L50 45 DMX	120 W
911401748273	BVP353 60LED RGB 220V L50 45 DMX	120 W
911401748283	BVP353 60LED RGBWW 220V L50 45 DMX	120 W
911401748293	BVP353 60LED RGBNW 220V L50 45 DMX	120 W
911401745783	BVP353 16LED 27K 220V L18 10	30 W
911401745793	BVP353 16LED 30K 220V L18 10	30 W
911401745803	BVP353 16LED 40K 220V L18 10	30 W
911401745813	BVP353 16LED 27K 220V L18 10 DMX	30 W
911401745823	BVP353 16LED 30K 220V L18 10 DMX	30 W
911401745833	BVP353 16LED 40K 220V L18 10 DMX	30 W
911401745843	BVP353 15LED RGB 220V L18 10 DMX	30 W
911401745853	BVP353 16LED RGBWW 220V L18 10 DMX	30 W
911401745863	BVP353 16LED RGBNW 220V L18 10 DMX	30 W
911401745873	BVP353 16LED 27K 220V L18 15	30 W
911401745883	BVP353 16LED 30K 220V L18 15	30 W
911401745893	BVP353 16LED 40K 220V L18 15	30 W
911401745903	BVP353 16LED 27K 220V L18 15 DMX	30 W
911401745913	BVP353 16LED 30K 220V L18 15 DMX	30 W
911401745923	BVP353 16LED 40K 220V L18 15 DMX	30 W
911401745933	BVP353 15LED RGB 220V L18 15 DMX	30 W
911401745943	BVP353 16LED RGBWW 220V L18 15 DMX	30 W
911401745953	BVP353 16LED RGBNW 220V L18 15 DMX	30 W

Order Code	Full Product Name	Power Consumption
911401745963	BVP353 16LED 27K 220V L18 30	30 W
911401745973	BVP353 16LED 30K 220V L18 30	30 W
911401745983	BVP353 16LED 40K 220V L18 30	30 W
911401745993	BVP353 16LED 27K 220V L18 30 DMX	30 W
911401746003	BVP353 16LED 30K 220V L18 30 DMX	30 W
911401746013	BVP353 16LED 40K 220V L18 30 DMX	30 W
911401746023	BVP353 15LED RGB 220V L18 30 DMX	30 W
911401746033	BVP353 16LED RGBWW 220V L18 30 DMX	30 W
911401746043	BVP353 16LED RGBNW 220V L18 30 DMX	30 W
911401746053	BVP353 16LED 27K 220V L18 45	30 W
911401746063	BVP353 16LED 30K 220V L18 45	30 W
911401746073	BVP353 16LED 40K 220V L18 45	30 W
911401746083	BVP353 16LED 27K 220V L18 45 DMX	30 W
911401746093	BVP353 16LED 30K 220V L18 45 DMX	30 W
911401746103	BVP353 16LED 40K 220V L18 45 DMX	30 W
911401746113	BVP353 15LED RGB 220V L18 45 DMX	30 W
911401746123	BVP353 16LED RGBWW 220V L18 45 DMX	30 W
911401746133	BVP353 16LED RGBNW 220V L18 45 DMX	30 W
911401749743	BVP355 216LED 27K 220V L57 10	450 W
911401749753	BVP355 216LED 30K 220V L57 10	450 W
911401749763	BVP355 216LED 40K 220V L57 10	450 W
911401749773	BVP355 216LED 27K 220V L57 10 DMX	450 W
911401749783	BVP355 216LED 30K 220V L57 10 DMX	450 W
911401749793	BVP355 216LED 40K 220V L57 10 DMX	450 W
911401749803	BVP355 216LED RGB 220V L57 10 DMX	450 W
911401749813	BVP355 216LED RGBWW 220V L57 10 DMX	450 W
911401749823	BVP355 216LED RGBNW 220V L57 10 DMX	450 W
911401749833	BVP355 216LED 27K 220V L57 15	450 W
911401749843	BVP355 216LED 30K 220V L57 15	450 W
911401749853	BVP355 216LED 40K 220V L57 15	450 W
911401749863	BVP355 216LED 27K 220V L57 15 DMX	450 W
911401749873	BVP355 216LED 30K 220V L57 15 DMX	450 W
911401749883	BVP355 216LED 40K 220V L57 15 DMX	450 W
911401749893	BVP355 216LED RGB 220V L57 15 DMX	450 W
911401749903	BVP355 216LED RGBWW 220V L57 15 DMX	450 W
911401749913	BVP355 216LED RGBNW 220V L57 15 DMX	450 W
911401749923	BVP355 216LED 27K 220V L57 30	450 W
911401749933	BVP355 216LED 30K 220V L57 30	450 W
911401749943	BVP355 216LED 40K 220V L57 30	450 W
911401749953	BVP355 216LED 27K 220V L57 30 DMX	450 W
911401749963	BVP355 216LED 30K 220V L57 30 DMX	450 W
911401749973	BVP355 216LED 40K 220V L57 30 DMX	450 W
911401749983	BVP355 216LED RGB 220V L57 30 DMX	450 W
911401749993	BVP355 216LED RGBWW 220V L57 30 DMX	450 W
911401750003	BVP355 216LED RGBNW 220V L57 30 DMX	450 W
911401750013	BVP355 216LED 27K 220V L57 45	450 W
911401750023	BVP355 216LED 30K 220V L57 45	450 W
911401750033	BVP355 216LED 40K 220V L57 45	450 W
911401750043	BVP355 216LED 27K 220V L57 45 DMX	450 W
911401750053	BVP355 216LED 30K 220V L57 45 DMX	450 W
911401750063	BVP355 216LED 40K 220V L57 45 DMX	450 W
911401750073	BVP355 216LED RGB 220V L57 45 DMX	450 W

Order Code	Full Product Name	Power Consumption
911401750083	BVP355 216LED RGBWW 220V L57 45 DMX	450 W
911401750093	BVP355 216LED RGBNW 220V L57 45 DMX	450 W
911401750103	BVP355 180LED 27K 220V L50 10	360 W
911401750113	BVP355 180LED 30K 220V L50 10	360 W
911401750123	BVP355 180LED 40K 220V L50 10	360 W
911401750133	BVP355 180LED 27K 220V L50 10 DMX	360 W
911401750143	BVP355 180LED 30K 220V L50 10 DMX	360 W
911401750153	BVP355 180LED 40K 220V L50 10 DMX	360 W
911401750163	BVP355 180LED RGB 220V L50 10 DMX	360 W
911401750173	BVP355 180LED RGBWW 220V L50 10 DMX	360 W
911401750183	BVP355 180LED RGBNW 220V L50 10 DMX	360 W
911401750193	BVP355 180LED 27K 220V L50 15	360 W
911401750203	BVP355 180LED 30K 220V L50 15	360 W
911401750213	BVP355 180LED 40K 220V L50 15	360 W
911401750223	BVP355 180LED 27K 220V L50 15 DMX	360 W
911401750233	BVP355 180LED 30K 220V L50 15 DMX	360 W
911401750243	BVP355 180LED 40K 220V L50 15 DMX	360 W
911401750253	BVP355 180LED RGB 220V L50 15 DMX	360 W
911401750263	BVP355 180LED RGBWW 220V L50 15 DMX	360 W
911401750273	BVP355 180LED RGBNW 220V L50 15 DMX	360 W
911401750283	BVP355 180LED 27K 220V L50 30	360 W
911401750293	BVP355 180LED 30K 220V L50 30	360 W
911401750303	BVP355 180LED 40K 220V L50 30	360 W
911401750313	BVP355 180LED 27K 220V L50 30 DMX	360 W
911401750323	BVP355 180LED 30K 220V L50 30 DMX	360 W
911401750333	BVP355 180LED 40K 220V L50 30 DMX	360 W
911401750343	BVP355 180LED RGB 220V L50 30 DMX	360 W
911401750353	BVP355 180LED RGBWW 220V L50 30 DMX	360 W
911401750363	BVP355 180LED RGBNW 220V L50 30 DMX	360 W
911401750373	BVP355 180LED 27K 220V L50 45	360 W
911401750383	BVP355 180LED 30K 220V L50 45	360 W
911401750393	BVP355 180LED 40K 220V L50 45	360 W
911401750403	BVP355 180LED 27K 220V L50 45 DMX	360 W
911401750413	BVP355 180LED 30K 220V L50 45 DMX	360 W
911401750423	BVP355 180LED 40K 220V L50 45 DMX	360 W
911401750433	BVP355 180LED RGB 220V L50 45 DMX	360 W
911401750443	BVP355 180LED RGBWW 220V L50 45 DMX	360 W

Order Code	Full Product Name	Power Consumption
911401750453	BVP355 180LED RGBNW 220V L50 45 DMX	360 W
911401747583	BVP353 48LED 27K 220V L40 10	100 W
911401747593	BVP353 48LED 30K 220V L40 10	100 W
911401747603	BVP353 48LED 40K 220V L40 10	100 W
911401747613	BVP353 48LED 27K 220V L40 10 DMX	100 W
911401747623	BVP353 48LED 30K 220V L40 10 DMX	100 W
911401747633	BVP353 48LED 40K 220V L40 10 DMX	100 W
911401747643	BVP353 48LED RGB 220V L40 10 DMX	100 W
911401747653	BVP353 48LED RGBWW 220V L40 10 DMX	100 W
911401747663	BVP353 48LED RGBNW 220V L40 10 DMX	100 W
911401747673	BVP353 48LED 27K 220V L40 15	100 W
911401747683	BVP353 48LED 30K 220V L40 15	100 W
911401747693	BVP353 48LED 40K 220V L40 15	100 W
911401747703	BVP353 48LED 27K 220V L40 15 DMX	100 W
911401747713	BVP353 48LED 30K 220V L40 15 DMX	100 W
911401747723	BVP353 48LED 40K 220V L40 15 DMX	100 W
911401747733	BVP353 48LED RGB 220V L40 15 DMX	100 W
911401747743	BVP353 48LED RGBWW 220V L40 15 DMX	100 W
911401747753	BVP353 48LED RGBNW 220V L40 15 DMX	100 W
911401747763	BVP353 48LED 27K 220V L40 30	100 W
911401747773	BVP353 48LED 30K 220V L40 30	100 W
911401747783	BVP353 48LED 40K 220V L40 30	100 W
911401747793	BVP353 48LED 27K 220V L40 30 DMX	100 W
911401747803	BVP353 48LED 30K 220V L40 30 DMX	100 W
911401747813	BVP353 48LED 40K 220V L40 30 DMX	100 W
911401747823	BVP353 48LED RGB 220V L40 30 DMX	100 W
911401747833	BVP353 48LED RGBWW 220V L40 30 DMX	100 W
911401747843	BVP353 48LED RGBNW 220V L40 30 DMX	100 W
911401747853	BVP353 48LED 27K 220V L40 45	100 W
911401747863	BVP353 48LED 30K 220V L40 45	100 W
911401747873	BVP353 48LED 40K 220V L40 45	100 W
911401747883	BVP353 48LED 27K 220V L40 45 DMX	100 W
911401747893	BVP353 48LED 30K 220V L40 45 DMX	100 W
911401747903	BVP353 48LED 40K 220V L40 45 DMX	100 W
911401747913	BVP353 48LED RGB 220V L40 45 DMX	100 W
911401747923	BVP353 48LED RGBWW 220V L40 45 DMX	100 W
911401747933	BVP353 48LED RGBNW 220V L40 45 DMX	100 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401746863	BVP353 30LED 27K 220V L30 10	No
911401746873	BVP353 30LED 30K 220V L30 10	No
911401746883	BVP353 30LED 40K 220V L30 10	No
911401746893	BVP353 30LED 27K 220V L30 10 DMX	Yes
911401746903	BVP353 30LED 30K 220V L30 10 DMX	Yes
911401746913	BVP353 30LED 40K 220V L30 10 DMX	Yes
911401746923	BVP353 30LED RGB 220V L30 10 DMX	Yes
911401746933	BVP353 32LED RGBWW 220V L30 10 DMX	Yes
911401746943	BVP353 32LED RGBNW 220V L30 10 DMX	Yes
911401746953	BVP353 30LED 27K 220V L30 15	No
911401746963	BVP353 30LED 30K 220V L30 15	No

Order Code	Full Product Name	Dimmable
911401746973	BVP353 30LED 40K 220V L30 15	No
911401746983	BVP353 30LED 27K 220V L30 15 DMX	Yes
911401746993	BVP353 30LED 30K 220V L30 15 DMX	Yes
911401747003	BVP353 30LED 40K 220V L30 15 DMX	Yes
911401747013	BVP353 30LED RGB 220V L30 15 DMX	Yes
911401747023	BVP353 32LED RGBWW 220V L30 15 DMX	Yes
911401747033	BVP353 32LED RGBNW 220V L30 15 DMX	Yes
911401747043	BVP353 30LED 27K 220V L30 30	No
911401747053	BVP353 30LED 30K 220V L30 30	No
911401747063	BVP353 30LED 40K 220V L30 30	No
911401747073	BVP353 30LED 27K 220V L30 30 DMX	Yes

Order Code	Full Product Name	Dimmable
911401747083	BVP353 30LED 30K 220V L30 30 DMX	Yes
911401747093	BVP353 30LED 40K 220V L30 30 DMX	Yes
911401747103	BVP353 30LED RGB 220V L30 30 DMX	Yes
911401747113	BVP353 32LED RGBWW 220V L30 30 DMX	Yes
911401747123	BVP353 32LED RGBNW 220V L30 30 DMX	Yes
911401747133	BVP353 30LED 27K 220V L30 45	No
911401747143	BVP353 30LED 30K 220V L30 45	No
911401747153	BVP353 30LED 40K 220V L30 45	No
911401747163	BVP353 30LED 27K 220V L30 45 DMX	Yes
911401747173	BVP353 30LED 30K 220V L30 45 DMX	Yes
911401747183	BVP353 30LED 40K 220V L30 45 DMX	Yes
911401747193	BVP353 30LED RGB 220V L30 45 DMX	Yes
911401747203	BVP353 32LED RGBWW 220V L30 45 DMX	Yes
911401747213	BVP353 32LED RGBNW 220V L30 45 DMX	Yes
911401748663	BVP354 96LED 27K 220V L40 10	No
911401748673	BVP354 96LED 30K 220V L40 10	No
911401748683	BVP354 96LED 40K 220V L40 10	No
911401748693	BVP354 96LED 27K 220V L40 10 DMX	Yes
911401748703	BVP354 96LED 30K 220V L40 10 DMX	Yes
911401748713	BVP354 96LED 40K 220V L40 10 DMX	Yes
911401748723	BVP354 96LED RGB 220V L40 10 DMX	Yes
911401748733	BVP354 96LED RGBWW 220V L40 10 DMX	Yes
911401748743	BVP354 96LED RGBNW 220V L40 10 DMX	Yes
911401748753	BVP354 96LED 27K 220V L40 15	No
911401748763	BVP354 96LED 30K 220V L40 15	No
911401748773	BVP354 96LED 40K 220V L40 15	No
911401748783	BVP354 96LED 27K 220V L40 15 DMX	Yes
911401748793	BVP354 96LED 30K 220V L40 15 DMX	Yes
911401748803	BVP354 96LED 40K 220V L40 15 DMX	Yes
911401748813	BVP354 96LED RGB 220V L40 15 DMX	Yes
911401748823	BVP354 96LED RGBWW 220V L40 15 DMX	Yes
911401748833	BVP354 96LED RGBNW 220V L40 15 DMX	Yes
911401748843	BVP354 96LED 27K 220V L40 30	No
911401748853	BVP354 96LED 30K 220V L40 30	No
911401748863	BVP354 96LED 40K 220V L40 30	No
911401748873	BVP354 96LED 27K 220V L40 30 DMX	Yes
911401748883	BVP354 96LED 30K 220V L40 30 DMX	Yes
911401748893	BVP354 96LED 40K 220V L40 30 DMX	Yes
911401748903	BVP354 96LED RGB 220V L40 30 DMX	Yes
911401748913	BVP354 96LED RGBWW 220V L40 30 DMX	Yes
911401748923	BVP354 96LED RGBNW 220V L40 30 DMX	Yes
911401748933	BVP354 96LED 27K 220V L40 45	No
911401748943	BVP354 96LED 30K 220V L40 45	No
911401748953	BVP354 96LED 40K 220V L40 45	No
911401748963	BVP354 96LED 27K 220V L40 45 DMX	Yes
911401748973	BVP354 96LED 30K 220V L40 45 DMX	Yes
911401748983	BVP354 96LED 40K 220V L40 45 DMX	Yes
911401748993	BVP354 96LED RGB 220V L40 45 DMX	Yes
911401749003	BVP354 96LED RGBWW 220V L40 45 DMX	Yes
911401749013	BVP354 96LED RGBNW 220V L40 45 DMX	Yes
911401749023	BVP354 120LED 27K 220V L50 10	No
911401749033	BVP354 120LED 30K 220V L50 10	No

Order Code	Full Product Name	Dimmable
911401749043	BVP354 120LED 40K 220V L50 10	No
911401749053	BVP354 120LED 27K 220V L50 10 DMX	Yes
911401749063	BVP354 120LED 30K 220V L50 10 DMX	Yes
911401749073	BVP354 120LED 40K 220V L50 10 DMX	Yes
911401749083	BVP354 120LED RGB 220V L50 10 DMX	Yes
911401749093	BVP354 120LED RGBWW 220V L50 10 DMX	Yes
911401749103	BVP354 120LED RGBNW 220V L50 10 DMX	Yes
911401749113	BVP354 120LED 27K 220V L50 15	No
911401749123	BVP354 120LED 30K 220V L50 15	No
911401749133	BVP354 120LED 40K 220V L50 15	No
911401749143	BVP354 120LED 27K 220V L50 15 DMX	Yes
911401749153	BVP354 120LED 30K 220V L50 15 DMX	Yes
911401749163	BVP354 120LED 40K 220V L50 15 DMX	Yes
911401749173	BVP354 120LED RGB 220V L50 15 DMX	Yes
911401749183	BVP354 120LED RGBWW 220V L50 15 DMX	Yes
911401749193	BVP354 120LED RGBNW 220V L50 15 DMX	Yes
911401749203	BVP354 120LED 27K 220V L50 30	No
911401749213	BVP354 120LED 30K 220V L50 30	No
911401749223	BVP354 120LED 40K 220V L50 30	No
911401749233	BVP354 120LED 27K 220V L50 30 DMX	Yes
911401749243	BVP354 120LED 30K 220V L50 30 DMX	Yes
911401749253	BVP354 120LED 40K 220V L50 30 DMX	Yes
911401749263	BVP354 120LED RGB 220V L50 30 DMX	Yes
911401749273	BVP354 120LED RGBWW 220V L50 30 DMX	Yes
911401749283	BVP354 120LED RGBNW 220V L50 30 DMX	Yes
911401749293	BVP354 120LED 27K 220V L50 45	No
911401749303	BVP354 120LED 30K 220V L50 45	No
911401749313	BVP354 120LED 40K 220V L50 45	No
911401749323	BVP354 120LED 27K 220V L50 45 DMX	Yes
911401749333	BVP354 120LED 30K 220V L50 45 DMX	Yes
911401749343	BVP354 120LED 40K 220V L50 45 DMX	Yes
911401749353	BVP354 120LED RGB 220V L50 45 DMX	Yes
911401749363	BVP354 120LED RGBWW 220V L50 45 DMX	Yes
911401749373	BVP354 120LED RGBNW 220V L50 45 DMX	Yes
911401749383	BVP354 144LED 27K 220V L57 10	No
911401749393	BVP354 144LED 30K 220V L57 10	No
911401749403	BVP354 144LED 40K 220V L57 10	No
911401749413	BVP354 144LED 27K 220V L57 10 DMX	Yes
911401749423	BVP354 144LED 30K 220V L57 10 DMX	Yes
911401749433	BVP354 144LED 40K 220V L57 10 DMX	Yes
911401749443	BVP354 144LED RGB 220V L57 10 DMX	Yes
911401749453	BVP354 144LED RGBWW 220V L57 10 DMX	Yes
911401749463	BVP354 144LED RGBNW 220V L57 10 DMX	Yes
911401749473	BVP354 144LED 27K 220V L57 15	No
911401749483	BVP354 144LED 30K 220V L57 15	No
911401749493	BVP354 144LED 40K 220V L57 15	No
911401749503	BVP354 144LED 27K 220V L57 15 DMX	Yes
911401749513	BVP354 144LED 30K 220V L57 15 DMX	Yes
911401749523	BVP354 144LED 40K 220V L57 15 DMX	Yes
911401749533	BVP354 144LED RGB 220V L57 15 DMX	Yes
911401749543	BVP354 144LED RGBWW 220V L57 15 DMX	Yes
911401749553	BVP354 144LED RGBNW 220V L57 15 DMX	Yes

Order Code	Full Product Name	Dimmable
911401749563	BVP354 144LED 27K 220V L57 30	No
911401749573	BVP354 144LED 30K 220V L57 30	No
911401749583	BVP354 144LED 40K 220V L57 30	No
911401749593	BVP354 144LED 27K 220V L57 30 DMX	Yes
911401749603	BVP354 144LED 30K 220V L57 30 DMX	Yes
911401749613	BVP354 144LED 40K 220V L57 30 DMX	Yes
911401749623	BVP354 144LED RGB 220V L57 30 DMX	Yes
911401749633	BVP354 144LED RGBWW 220V L57 30 DMX	Yes
911401749643	BVP354 144LED RGBNW 220V L57 30 DMX	Yes
911401749653	BVP354 144LED 27K 220V L57 45	No
911401749663	BVP354 144LED 30K 220V L57 45	No
911401749673	BVP354 144LED 40K 220V L57 45	No
911401749683	BVP354 144LED 27K 220V L57 45 DMX	Yes
911401749693	BVP354 144LED 30K 220V L57 45 DMX	Yes
911401749703	BVP354 144LED 40K 220V L57 45 DMX	Yes
911401749713	BVP354 144LED RGB 220V L57 45 DMX	Yes
911401749723	BVP354 144LED RGBWW 220V L57 45 DMX	Yes
911401749733	BVP354 144LED RGBNW 220V L57 45 DMX	Yes
911401748303	BVP353 72LED 27K 220V L57 10	No
911401748313	BVP353 72LED 30K 220V L57 10	No
911401748323	BVP353 72LED 40K 220V L57 10	No
911401748333	BVP353 72LED 27K 220V L57 10 DMX	Yes
911401748343	BVP353 72LED 30K 220V L57 10 DMX	Yes
911401748353	BVP353 72LED 40K 220V L57 10 DMX	Yes
911401748363	BVP353 72LED RGB 220V L57 10 DMX	Yes
911401748373	BVP353 72LED RGBWW 220V L57 10 DMX	Yes
911401748383	BVP353 72LED RGBNW 220V L57 10 DMX	Yes
911401748393	BVP353 72LED 27K 220V L57 15	No
911401748403	BVP353 72LED 30K 220V L57 15	No
911401748413	BVP353 72LED 40K 220V L57 15	No
911401748423	BVP353 72LED 27K 220V L57 15 DMX	Yes
911401748433	BVP353 72LED 30K 220V L57 15 DMX	Yes
911401748443	BVP353 72LED 40K 220V L57 15 DMX	Yes
911401748453	BVP353 72LED RGB 220V L57 15 DMX	Yes
911401748463	BVP353 72LED RGBWW 220V L57 15 DMX	Yes
911401748473	BVP353 72LED RGBNW 220V L57 15 DMX	Yes
911401748483	BVP353 72LED 27K 220V L57 30	No
911401748493	BVP353 72LED 30K 220V L57 30	No
911401748503	BVP353 72LED 40K 220V L57 30	No
911401748513	BVP353 72LED 27K 220V L57 30 DMX	Yes
911401748523	BVP353 72LED 30K 220V L57 30 DMX	Yes
911401748533	BVP353 72LED 40K 220V L57 30 DMX	Yes
911401748543	BVP353 72LED RGB 220V L57 30 DMX	Yes
911401748553	BVP353 72LED RGBWW 220V L57 30 DMX	Yes
911401748563	BVP353 72LED RGBNW 220V L57 30 DMX	Yes
911401748573	BVP353 72LED 27K 220V L57 45	No
911401748583	BVP353 72LED 30K 220V L57 45	No
911401748593	BVP353 72LED 40K 220V L57 45	No
911401748603	BVP353 72LED 27K 220V L57 45 DMX	Yes
911401748613	BVP353 72LED 30K 220V L57 45 DMX	Yes
911401748623	BVP353 72LED 40K 220V L57 45 DMX	Yes
911401748633	BVP353 72LED RGB 220V L57 45 DMX	Yes

Order Code	Full Product Name	Dimmable
911401748643	BVP353 72LED RGBWW 220V L57 45 DMX	Yes
911401748653	BVP353 72LED RGBNW 220V L57 45 DMX	Yes
911401746143	BVP353 18LED 27K 220V L21 10	No
911401746153	BVP353 18LED 30K 220V L21 10	No
911401746163	BVP353 18LED 40K 220V L21 10	No
911401746173	BVP353 18LED 27K 220V L21 10 DMX	Yes
911401746183	BVP353 18LED 30K 220V L21 10 DMX	Yes
911401746193	BVP353 18LED 40K 220V L21 10 DMX	Yes
911401746203	BVP353 18LED RGB 220V L21 10 DMX	Yes
911401746213	BVP353 20LED RGBWW 220V L21 10 DMX	Yes
911401746223	BVP353 20LED RGBNW 220V L21 10 DMX	Yes
911401746233	BVP353 18LED 27K 220V L21 15	No
911401746243	BVP353 18LED 30K 220V L21 15	No
911401746253	BVP353 18LED 40K 220V L21 15	No
911401746263	BVP353 18LED 27K 220V L21 15 DMX	Yes
911401746273	BVP353 18LED 30K 220V L21 15 DMX	Yes
911401746283	BVP353 18LED 40K 220V L21 15 DMX	Yes
911401746293	BVP353 18LED RGB 220V L21 15 DMX	Yes
911401746303	BVP353 20LED RGBWW 220V L21 15 DMX	Yes
911401746313	BVP353 20LED RGBNW 220V L21 15 DMX	Yes
911401746323	BVP353 18LED 27K 220V L21 30	No
911401746333	BVP353 18LED 30K 220V L21 30	No
911401746343	BVP353 18LED 40K 220V L21 30	No
911401746353	BVP353 18LED 27K 220V L21 30 DMX	Yes
911401746363	BVP353 18LED 30K 220V L21 30 DMX	Yes
911401746373	BVP353 18LED 40K 220V L21 30 DMX	Yes
911401746383	BVP353 18LED RGB 220V L21 30 DMX	Yes
911401746393	BVP353 20LED RGBWW 220V L21 30 DMX	Yes
911401746403	BVP353 20LED RGBNW 220V L21 30 DMX	Yes
911401746413	BVP353 18LED 27K 220V L21 45	No
911401746423	BVP353 18LED 30K 220V L21 45	No
911401746433	BVP353 18LED 40K 220V L21 45	No
911401746443	BVP353 18LED 27K 220V L21 45 DMX	Yes
911401746453	BVP353 18LED 30K 220V L21 45 DMX	Yes
911401746463	BVP353 18LED 40K 220V L21 45 DMX	Yes
911401746473	BVP353 18LED RGB 220V L21 45 DMX	Yes
911401746483	BVP353 20LED RGBWW 220V L21 45 DMX	Yes
911401746493	BVP353 20LED RGBNW 220V L21 45 DMX	Yes
911401745423	BVP353 12LED 27K 220V L15 10	No
911401745433	BVP353 12LED 30K 220V L15 10	No
911401745443	BVP353 12LED 40K 220V L15 10	No
911401745453	BVP353 12LED 27K 220V L15 10 DMX	Yes
911401745463	BVP353 12LED 30K 220V L15 10 DMX	Yes
911401745473	BVP353 12LED 40K 220V L15 10 DMX	Yes
911401745483	BVP353 12LED RGB 220V L15 10 DMX	Yes
911401745493	BVP353 12LED RGBWW 220V L15 10 DMX	Yes
911401745503	BVP353 12LED RGBNW 220V L15 10 DMX	Yes
911401745513	BVP353 12LED 27K 220V L15 15	No
911401745523	BVP353 12LED 30K 220V L15 15	No
911401745533	BVP353 12LED 40K 220V L15 15	No
911401745543	BVP353 12LED 27K 220V L15 15 DMX	Yes
911401745553	BVP353 12LED 30K 220V L15 15 DMX	Yes

Order Code	Full Product Name	Dimmable
911401745563	BVP353 12LED 40K 220V L15 15 DMX	Yes
911401745573	BVP353 12LED RGB 220V L15 15 DMX	Yes
911401745583	BVP353 12LED RGBWW 220V L15 15 DMX	Yes
911401745593	BVP353 12LED RGBNW 220V L15 15 DMX	Yes
911401745603	BVP353 12LED 27K 220V L15 30	No
911401745613	BVP353 12LED 30K 220V L15 30	No
911401745623	BVP353 12LED 40K 220V L15 30	No
911401745633	BVP353 12LED 27K 220V L15 30 DMX	Yes
911401745643	BVP353 12LED 30K 220V L15 30 DMX	Yes
911401745653	BVP353 12LED 40K 220V L15 30 DMX	Yes
911401745663	BVP353 12LED RGB 220V L15 30 DMX	Yes
911401745673	BVP353 12LED RGBWW 220V L15 30 DMX	Yes
911401745683	BVP353 12LED RGBNW 220V L15 30 DMX	Yes
911401745693	BVP353 12LED 27K 220V L15 45	No
911401745703	BVP353 12LED 30K 220V L15 45	No
911401745713	BVP353 12LED 40K 220V L15 45	No
911401745723	BVP353 12LED 27K 220V L15 45 DMX	Yes
911401745733	BVP353 12LED 30K 220V L15 45 DMX	Yes
911401745743	BVP353 12LED 40K 220V L15 45 DMX	Yes
911401745753	BVP353 12LED RGB 220V L15 45 DMX	Yes
911401745763	BVP353 12LED RGBWW 220V L15 45 DMX	Yes
911401745773	BVP353 12LED RGBNW 220V L15 45 DMX	Yes
911401747223	BVP353 36LED 27K 220V L35 10	No
911401747233	BVP353 36LED 30K 220V L35 10	No
911401747243	BVP353 36LED 40K 220V L35 10	No
911401747253	BVP353 36LED 27K 220V L35 10 DMX	Yes
911401747263	BVP353 36LED 30K 220V L35 10 DMX	Yes
911401747273	BVP353 36LED 40K 220V L35 10 DMX	Yes
911401747283	BVP353 36LED RGB 220V L35 10 DMX	Yes
911401747293	BVP353 36LED RGBWW 220V L35 10 DMX	Yes
911401747303	BVP353 36LED RGBNW 220V L35 10 DMX	Yes
911401747313	BVP353 36LED 27K 220V L35 15	No
911401747323	BVP353 36LED 30K 220V L35 15	No
911401747333	BVP353 36LED 40K 220V L35 15	No
911401747343	BVP353 36LED 27K 220V L35 15 DMX	Yes
911401747353	BVP353 36LED 30K 220V L35 15 DMX	Yes
911401747363	BVP353 36LED 40K 220V L35 15 DMX	Yes
911401747373	BVP353 36LED RGB 220V L35 15 DMX	Yes
911401747383	BVP353 36LED RGBWW 220V L35 15 DMX	Yes
911401747393	BVP353 36LED RGBNW 220V L35 15 DMX	Yes
911401747403	BVP353 36LED 27K 220V L35 30	No
911401747413	BVP353 36LED 30K 220V L35 30	No
911401747423	BVP353 36LED 40K 220V L35 30	No
911401747433	BVP353 36LED 27K 220V L35 30 DMX	Yes
911401747443	BVP353 36LED 30K 220V L35 30 DMX	Yes
911401747453	BVP353 36LED 40K 220V L35 30 DMX	Yes
911401747463	BVP353 36LED RGB 220V L35 30 DMX	Yes
911401747473	BVP353 36LED RGBWW 220V L35 30 DMX	Yes
911401747483	BVP353 36LED RGBNW 220V L35 30 DMX	Yes
911401747493	BVP353 36LED 27K 220V L35 45	No
911401747503	BVP353 36LED 30K 220V L35 45	No
911401747513	BVP353 36LED 40K 220V L35 45	No

Order Code	Full Product Name	Dimmable
911401747523	BVP353 36LED 27K 220V L35 45 DMX	Yes
911401747533	BVP353 36LED 30K 220V L35 45 DMX	Yes
911401747543	BVP353 36LED 40K 220V L35 45 DMX	Yes
911401747553	BVP353 36LED RGB 220V L35 45 DMX	Yes
911401747563	BVP353 36LED RGBWW 220V L35 45 DMX	Yes
911401747573	BVP353 36LED RGBNW 220V L35 45 DMX	Yes
911401746503	BVP353 24LED 27K 220V L24 10	No
911401746513	BVP353 24LED 30K 220V L24 10	No
911401746523	BVP353 24LED 40K 220V L24 10	No
911401746533	BVP353 24LED 27K 220V L24 10 DMX	Yes
911401746543	BVP353 24LED 30K 220V L24 10 DMX	Yes
911401746553	BVP353 24LED 40K 220V L24 10 DMX	Yes
911401746563	BVP353 24LED RGB 220V L24 10 DMX	Yes
911401746573	BVP353 24LED RGBWW 220V L24 10 DMX	Yes
911401746583	BVP353 24LED RGBNW 220V L24 10 DMX	Yes
911401746593	BVP353 24LED 27K 220V L24 15	No
911401746603	BVP353 24LED 30K 220V L24 15	No
911401746613	BVP353 24LED 40K 220V L24 15	No
911401746623	BVP353 24LED 27K 220V L24 15 DMX	Yes
911401746633	BVP353 24LED 30K 220V L24 15 DMX	Yes
911401746643	BVP353 24LED 40K 220V L24 15 DMX	Yes
911401746653	BVP353 24LED RGB 220V L24 15 DMX	Yes
911401746663	BVP353 24LED RGBWW 220V L24 15 DMX	Yes
911401746673	BVP353 24LED RGBNW 220V L24 15 DMX	Yes
911401746683	BVP353 24LED 27K 220V L24 30	No
911401746693	BVP353 24LED 30K 220V L24 30	No
911401746703	BVP353 24LED 40K 220V L24 30	No
911401746713	BVP353 24LED 27K 220V L24 30 DMX	Yes
911401746723	BVP353 24LED 30K 220V L24 30 DMX	Yes
911401746733	BVP353 24LED 40K 220V L24 30 DMX	Yes
911401746743	BVP353 24LED RGB 220V L24 30 DMX	Yes
911401746753	BVP353 24LED RGBWW 220V L24 30 DMX	Yes
911401746763	BVP353 24LED RGBNW 220V L24 30 DMX	Yes
911401746773	BVP353 24LED 27K 220V L24 45	No
911401746783	BVP353 24LED 30K 220V L24 45	No
911401746793	BVP353 24LED 40K 220V L24 45	No
911401746803	BVP353 24LED 27K 220V L24 45 DMX	Yes
911401746813	BVP353 24LED 30K 220V L24 45 DMX	Yes
911401746823	BVP353 24LED 40K 220V L24 45 DMX	Yes
911401746833	BVP353 24LED RGB 220V L24 45 DMX	Yes
911401746843	BVP353 24LED RGBWW 220V L24 45 DMX	Yes
911401746853	BVP353 24LED RGBNW 220V L24 45 DMX	Yes
911401747943	BVP353 60LED 27K 220V L50 10	No
911401747953	BVP353 60LED 30K 220V L50 10	No
911401747963	BVP353 60LED 40K 220V L50 10	No
911401747973	BVP353 60LED 27K 220V L50 10 DMX	Yes
911401747983	BVP353 60LED 30K 220V L50 10 DMX	Yes
911401747993	BVP353 60LED 40K 220V L50 10 DMX	Yes
911401748003	BVP353 60LED RGB 220V L50 10 DMX	Yes
911401748013	BVP353 60LED RGBWW 220V L50 10 DMX	Yes
911401748023	BVP353 60LED RGBNW 220V L50 10 DMX	Yes
911401748033	BVP353 60LED 27K 220V L50 15	No

Order Code	Full Product Name	Dimmable
911401748043	BVP353 60LED 30K 220V L50 15	No
911401748053	BVP353 60LED 40K 220V L50 15	No
911401748063	BVP353 60LED 27K 220V L50 15 DMX	Yes
911401748073	BVP353 60LED 30K 220V L50 15 DMX	Yes
911401748083	BVP353 60LED 40K 220V L50 15 DMX	Yes
911401748093	BVP353 60LED RGB 220V L50 15 DMX	Yes
911401748103	BVP353 60LED RGBWW 220V L50 15 DMX	Yes
911401748113	BVP353 60LED RGBNW 220V L50 15 DMX	Yes
911401748123	BVP353 60LED 27K 220V L50 30	No
911401748133	BVP353 60LED 30K 220V L50 30	No
911401748143	BVP353 60LED 40K 220V L50 30	No
911401748153	BVP353 60LED 27K 220V L50 30 DMX	Yes
911401748163	BVP353 60LED 30K 220V L50 30 DMX	Yes
911401748173	BVP353 60LED 40K 220V L50 30 DMX	Yes
911401748183	BVP353 60LED RGB 220V L50 30 DMX	Yes
911401748193	BVP353 60LED RGBWW 220V L50 30 DMX	Yes
911401748203	BVP353 60LED RGBNW 220V L50 30 DMX	Yes
911401748213	BVP353 60LED 27K 220V L50 45	No
911401748223	BVP353 60LED 30K 220V L50 45	No
911401748233	BVP353 60LED 40K 220V L50 45	No
911401748243	BVP353 60LED 27K 220V L50 45 DMX	Yes
911401748253	BVP353 60LED 30K 220V L50 45 DMX	Yes
911401748263	BVP353 60LED 40K 220V L50 45 DMX	Yes
911401748273	BVP353 60LED RGB 220V L50 45 DMX	Yes
911401748283	BVP353 60LED RGBWW 220V L50 45 DMX	Yes
911401748293	BVP353 60LED RGBNW 220V L50 45 DMX	Yes
911401745783	BVP353 16LED 27K 220V L18 10	No
911401745793	BVP353 16LED 30K 220V L18 10	No
911401745803	BVP353 16LED 40K 220V L18 10	No
911401745813	BVP353 16LED 27K 220V L18 10 DMX	Yes
911401745823	BVP353 16LED 30K 220V L18 10 DMX	Yes
911401745833	BVP353 16LED 40K 220V L18 10 DMX	Yes
911401745843	BVP353 15LED RGB 220V L18 10 DMX	Yes
911401745853	BVP353 16LED RGBWW 220V L18 10 DMX	Yes
911401745863	BVP353 16LED RGBNW 220V L18 10 DMX	Yes
911401745873	BVP353 16LED 27K 220V L18 15	No
911401745883	BVP353 16LED 30K 220V L18 15	No
911401745893	BVP353 16LED 40K 220V L18 15	No
911401745903	BVP353 16LED 27K 220V L18 15 DMX	Yes
911401745913	BVP353 16LED 30K 220V L18 15 DMX	Yes
911401745923	BVP353 16LED 40K 220V L18 15 DMX	Yes
911401745933	BVP353 15LED RGB 220V L18 15 DMX	Yes
911401745943	BVP353 16LED RGBWW 220V L18 15 DMX	Yes
911401745953	BVP353 16LED RGBNW 220V L18 15 DMX	Yes
911401745963	BVP353 16LED 27K 220V L18 30	No
911401745973	BVP353 16LED 30K 220V L18 30	No
911401745983	BVP353 16LED 40K 220V L18 30	No
911401745993	BVP353 16LED 27K 220V L18 30 DMX	Yes
911401746003	BVP353 16LED 30K 220V L18 30 DMX	Yes
911401746013	BVP353 16LED 40K 220V L18 30 DMX	Yes
911401746023	BVP353 15LED RGB 220V L18 30 DMX	Yes
911401746033	BVP353 16LED RGBWW 220V L18 30 DMX	Yes

Order Code	Full Product Name	Dimmable
911401746043	BVP353 16LED RGBNW 220V L18 30 DMX	Yes
911401746053	BVP353 16LED 27K 220V L18 45	No
911401746063	BVP353 16LED 30K 220V L18 45	No
911401746073	BVP353 16LED 40K 220V L18 45	No
911401746083	BVP353 16LED 27K 220V L18 45 DMX	Yes
911401746093	BVP353 16LED 30K 220V L18 45 DMX	Yes
911401746103	BVP353 16LED 40K 220V L18 45 DMX	Yes
911401746113	BVP353 15LED RGB 220V L18 45 DMX	Yes
911401746123	BVP353 16LED RGBWW 220V L18 45 DMX	Yes
911401746133	BVP353 16LED RGBNW 220V L18 45 DMX	Yes
911401749743	BVP355 216LED 27K 220V L57 10	No
911401749753	BVP355 216LED 30K 220V L57 10	No
911401749763	BVP355 216LED 40K 220V L57 10	No
911401749773	BVP355 216LED 27K 220V L57 10 DMX	Yes
911401749783	BVP355 216LED 30K 220V L57 10 DMX	Yes
911401749793	BVP355 216LED 40K 220V L57 10 DMX	Yes
911401749803	BVP355 216LED RGB 220V L57 10 DMX	Yes
911401749813	BVP355 216LED RGBWW 220V L57 10 DMX	Yes
911401749823	BVP355 216LED RGBNW 220V L57 10 DMX	Yes
911401749833	BVP355 216LED 27K 220V L57 15	No
911401749843	BVP355 216LED 30K 220V L57 15	No
911401749853	BVP355 216LED 40K 220V L57 15	No
911401749863	BVP355 216LED 27K 220V L57 15 DMX	Yes
911401749873	BVP355 216LED 30K 220V L57 15 DMX	Yes
911401749883	BVP355 216LED 40K 220V L57 15 DMX	Yes
911401749893	BVP355 216LED RGB 220V L57 15 DMX	Yes
911401749903	BVP355 216LED RGBWW 220V L57 15 DMX	Yes
911401749913	BVP355 216LED RGBNW 220V L57 15 DMX	Yes
911401749923	BVP355 216LED 27K 220V L57 30	No
911401749933	BVP355 216LED 30K 220V L57 30	No
911401749943	BVP355 216LED 40K 220V L57 30	No
911401749953	BVP355 216LED 27K 220V L57 30 DMX	Yes
911401749963	BVP355 216LED 30K 220V L57 30 DMX	Yes
911401749973	BVP355 216LED 40K 220V L57 30 DMX	Yes
911401749983	BVP355 216LED RGB 220V L57 30 DMX	Yes
911401749993	BVP355 216LED RGBWW 220V L57 30 DMX	Yes
911401750003	BVP355 216LED RGBNW 220V L57 30 DMX	Yes
911401750013	BVP355 216LED 27K 220V L57 45	No
911401750023	BVP355 216LED 30K 220V L57 45	No
911401750033	BVP355 216LED 40K 220V L57 45	No
911401750043	BVP355 216LED 27K 220V L57 45 DMX	Yes
911401750053	BVP355 216LED 30K 220V L57 45 DMX	Yes
911401750063	BVP355 216LED 40K 220V L57 45 DMX	Yes
911401750073	BVP355 216LED RGB 220V L57 45 DMX	Yes
911401750083	BVP355 216LED RGBWW 220V L57 45 DMX	Yes
911401750093	BVP355 216LED RGBNW 220V L57 45 DMX	Yes
911401750103	BVP355 180LED 27K 220V L50 10	No
911401750113	BVP355 180LED 30K 220V L50 10	No
911401750123	BVP355 180LED 40K 220V L50 10	No
911401750133	BVP355 180LED 27K 220V L50 10 DMX	Yes
911401750143	BVP355 180LED 30K 220V L50 10 DMX	Yes
911401750153	BVP355 180LED 40K 220V L50 10 DMX	Yes

Order Code	Full Product Name	Dimmable
911401750163	BVP355 180LED RGB 220V L50 10 DMX	Yes
911401750173	BVP355 180LED RGBWW 220V L50 10 DMX	Yes
911401750183	BVP355 180LED RGBNW 220V L50 10 DMX	Yes
911401750193	BVP355 180LED 27K 220V L50 15	No
911401750203	BVP355 180LED 30K 220V L50 15	No
911401750213	BVP355 180LED 40K 220V L50 15	No
911401750223	BVP355 180LED 27K 220V L50 15 DMX	Yes
911401750233	BVP355 180LED 30K 220V L50 15 DMX	Yes
911401750243	BVP355 180LED 40K 220V L50 15 DMX	Yes
911401750253	BVP355 180LED RGB 220V L50 15 DMX	Yes
911401750263	BVP355 180LED RGBWW 220V L50 15 DMX	Yes
911401750273	BVP355 180LED RGBNW 220V L50 15 DMX	Yes
911401750283	BVP355 180LED 27K 220V L50 30	No
911401750293	BVP355 180LED 30K 220V L50 30	No
911401750303	BVP355 180LED 40K 220V L50 30	No
911401750313	BVP355 180LED 27K 220V L50 30 DMX	Yes
911401750323	BVP355 180LED 30K 220V L50 30 DMX	Yes
911401750333	BVP355 180LED 40K 220V L50 30 DMX	Yes
911401750343	BVP355 180LED RGB 220V L50 30 DMX	Yes
911401750353	BVP355 180LED RGBWW 220V L50 30 DMX	Yes
911401750363	BVP355 180LED RGBNW 220V L50 30 DMX	Yes
911401750373	BVP355 180LED 27K 220V L50 45	No
911401750383	BVP355 180LED 30K 220V L50 45	No
911401750393	BVP355 180LED 40K 220V L50 45	No
911401750403	BVP355 180LED 27K 220V L50 45 DMX	Yes
911401750413	BVP355 180LED 30K 220V L50 45 DMX	Yes
911401750423	BVP355 180LED 40K 220V L50 45 DMX	Yes
911401750433	BVP355 180LED RGB 220V L50 45 DMX	Yes
911401750443	BVP355 180LED RGBWW 220V L50 45 DMX	Yes
911401750453	BVP355 180LED RGBNW 220V L50 45 DMX	Yes
911401747583	BVP353 48LED 27K 220V L40 10	No
911401747593	BVP353 48LED 30K 220V L40 10	No
911401747603	BVP353 48LED 40K 220V L40 10	No

Order Code	Full Product Name	Dimmable
911401747613	BVP353 48LED 27K 220V L40 10 DMX	Yes
911401747623	BVP353 48LED 30K 220V L40 10 DMX	Yes
911401747633	BVP353 48LED 40K 220V L40 10 DMX	Yes
911401747643	BVP353 48LED RGB 220V L40 10 DMX	Yes
911401747653	BVP353 48LED RGBWW 220V L40 10 DMX	Yes
911401747663	BVP353 48LED RGBNW 220V L40 10 DMX	Yes
911401747673	BVP353 48LED 27K 220V L40 15	No
911401747683	BVP353 48LED 30K 220V L40 15	No
911401747693	BVP353 48LED 40K 220V L40 15	No
911401747703	BVP353 48LED 27K 220V L40 15 DMX	Yes
911401747713	BVP353 48LED 30K 220V L40 15 DMX	Yes
911401747723	BVP353 48LED 40K 220V L40 15 DMX	Yes
911401747733	BVP353 48LED RGB 220V L40 15 DMX	Yes
911401747743	BVP353 48LED RGBWW 220V L40 15 DMX	Yes
911401747753	BVP353 48LED RGBNW 220V L40 15 DMX	Yes
911401747763	BVP353 48LED 27K 220V L40 30	No
911401747773	BVP353 48LED 30K 220V L40 30	No
911401747783	BVP353 48LED 40K 220V L40 30	No
911401747793	BVP353 48LED 27K 220V L40 30 DMX	Yes
911401747803	BVP353 48LED 30K 220V L40 30 DMX	Yes
911401747813	BVP353 48LED 40K 220V L40 30 DMX	Yes
911401747823	BVP353 48LED RGB 220V L40 30 DMX	Yes
911401747833	BVP353 48LED RGBWW 220V L40 30 DMX	Yes
911401747843	BVP353 48LED RGBNW 220V L40 30 DMX	Yes
911401747853	BVP353 48LED 27K 220V L40 45	No
911401747863	BVP353 48LED 30K 220V L40 45	No
911401747873	BVP353 48LED 40K 220V L40 45	No
911401747883	BVP353 48LED 27K 220V L40 45 DMX	Yes
911401747893	BVP353 48LED 30K 220V L40 45 DMX	Yes
911401747903	BVP353 48LED 40K 220V L40 45 DMX	Yes
911401747913	BVP353 48LED RGB 220V L40 45 DMX	Yes
911401747923	BVP353 48LED RGBWW 220V L40 45 DMX	Yes
911401747933	BVP353 48LED RGBNW 220V L40 45 DMX	Yes

