



Philips UniFlood M gen2: A high power floodlight with true modularity

UniFlood M G2

The Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor floodlighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colours, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Features

- Standard: RGBW, RGB, 2,700 K, 3,000 K and 4,000 K
- Optional 5,000 K, monochromatic colours and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

UniFlood M G2

Application

- Bridges, Monuments, Facades
- Parks and squares
- Landscape

Warnings and Safety





- For outdoor use only.

Versions




UniFlood M Gen2

Dimensional drawing



Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Colour rendering index (CRI)	>80
Mechanical and Housing	
Optical cover type	Clear glass
Housing Colour	Dark grey
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

Light Technical

		Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92608099	BVP353 30LED 30K 220V L30 10	830 warm white	3000 K	4,710 lm
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	RGBW	-	2,855 lm
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	RGBW	-	2,985 lm
92618999	BVP353 30LED 40K 220V L30 15	840 neutral white	4000 K	5,520 lm
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	RGBW	-	3,130 lm
92626499	BVP353 30LED 30K 220V L30 30	830 warm white	3000 K	5,125 lm
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	RGBW	-	3,105 lm
92635699	BVP353 30LED 30K 220V L30 45	830 warm white	3000 K	4,945 lm
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	RGBW	-	3,130 lm
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	RGBW	-	10,505 lm
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	RGBW	-	10,975 lm
92806000	BVP354 96LED 30K 220V L40 30	830 warm white	3000 K	18,005 lm
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	RGBW	-	11,425 lm
92815200	BVP354 96LED 30K 220V L40 45	830 warm white	3000 K	17,385 lm
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	RGBW	-	11,520 lm
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	RGBW	-	10,720 lm
92833600	BVP354 120LED 30K 220V L50 15	830 warm white	3000 K	19,795 lm
92843500	BVP354 120LED 40K 220V L50 30	840 neutral white	4000 K	22,875 lm
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	RGBW	-	12,170 lm
92851000	BVP354 120LED 30K 220V L50 45	830 warm white	3000 K	19,795 lm
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	RGBW	-	11,255 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	RGBW	-	11,750 lm
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	RGBW	-	14,395 lm
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	RGBW	-	15,030 lm
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	RGBW	-	15,785 lm
92878700	BVP354 144LED 30K 220V L57 30	830 warm white	3000 K	25,820 lm
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	RGBW	-	16,345 lm
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	RGBW	-	15,115 lm
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	RGBW	-	15,785 lm
92752099	BVP353 72LED 30K 220V L57 10	830 warm white	3000 K	11,870 lm
92753799	BVP353 72LED 40K 220V L57 10	840 neutral white	4000 K	13,245 lm
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	RGBW	-	7,195 lm
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	RGBW	-	7,515 lm
92762999	BVP353 72LED 40K 220V L57 15	840 neutral white	4000 K	13,905 lm
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	RGBW	-	7,555 lm
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	RGBW	-	7,890 lm
92771199	BVP353 72LED 40K 220V L57 30	840 neutral white	4000 K	14,405 lm
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	RGBW	-	7,825 lm
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	RGBW	-	8,170 lm
92779799	BVP353 72LED 30K 220V L57 45	830 warm white	3000 K	12,465 lm
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	RGBW	-	7,555 lm
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	RGBW	-	7,890 lm
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	RGBW	-	1,945 lm
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	RGBW	-	2,040 lm
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	RGBW	-	2,115 lm
92464299	BVP353 12LED 30K 220V L15 10	830 warm white	3000 K	1,835 lm
92465999	BVP353 12LED 40K 220V L15 10	840 neutral white	4000 K	2,050 lm
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	RGBW	-	1,175 lm
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	RGBW	-	1,225 lm
92474199	BVP353 12LED 40K 220V L15 15	840 neutral white	4000 K	2,150 lm
92479699	BVP353 12LED RGBWW 220V L15 15 DMX	RGBW	-	1,230 lm
92482699	BVP353 12LED 30K 220V L15 30	830 warm white	3000 K	1,995 lm
92483399	BVP353 12LED 40K 220V L15 30	840 neutral white	4000 K	2,225 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92492599	BVP353 12LED 40K 220V L15 45	840 neutral white	4000 K	2,150 lm
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	RGBW	-	1,230 lm
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	RGBW	-	1,285 lm
92644899	BVP353 36LED 30K 220V L35 10	830 warm white	3000 K	6,205 lm
92645599	BVP353 36LED 40K 220V L35 10	840 neutral white	4000 K	6,925 lm
92654799	BVP353 36LED 40K 220V L35 15	840 neutral white	4000 K	7,270 lm
92663999	BVP353 36LED 40K 220V L35 30	840 neutral white	4000 K	7,530 lm
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	RGBW	-	3,995 lm
92572499	BVP353 24LED 30K 220V L24 10	830 warm white	3000 K	3,770 lm
92573199	BVP353 24LED 40K 220V L24 10	840 neutral white	4000 K	4,205 lm
92581699	BVP353 24LED 30K 220V L24 15	830 warm white	3000 K	3,955 lm
92582399	BVP353 24LED 40K 220V L24 15	840 neutral white	4000 K	4,415 lm
92590899	BVP353 24LED 30K 220V L24 30	830 warm white	3000 K	4,100 lm
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	RGBW	-	2,555 lm
92599199	BVP353 24LED 30K 220V L24 45	830 warm white	3000 K	3,955 lm
92600499	BVP353 24LED 40K 220V L24 45	840 neutral white	4000 K	4,415 lm
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	RGBW	-	6,575 lm
92734699	BVP353 60LED 30K 220V L50 30	830 warm white	3000 K	10,380 lm
92735399	BVP353 60LED 40K 220V L50 30	840 neutral white	4000 K	11,580 lm
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	RGBW	-	6,810 lm
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	RGBW	-	6,295 lm
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	RGBW	-	6,575 lm
92509099	BVP353 16LED 30K 220V L18 15	830 warm white	3000 K	3,020 lm
92510699	BVP353 16LED 40K 220V L18 15	840 neutral white	4000 K	3,365 lm
92518299	BVP353 16LED 30K 220V L18 30	830 warm white	3000 K	3,125 lm
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	RGBW	-	1,565 lm
92897800	BVP355 216LED 40K 220V L57 10	840 neutral white	4000 K	39,740 lm
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	RGBW	-	21,590 lm
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	RGBW	-	23,675 lm
92923400	BVP355 216LED 30K 220V L57 45	830 warm white	3000 K	37,400 lm
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	RGBW	-	23,675 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92933300	BVP355 180LED 40K 220V L50 10	840 neutral white	4000 K	31,945 lm
92942500	BVP355 180LED 40K 220V L50 15	840 neutral white	4000 K	33,540 lm
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	RGBW	-	20,435 lm
92960900	BVP355 180LED 40K 220V L50 45	840 neutral white	4000 K	33,540 lm
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	RGBW	-	5,250 lm
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	RGBW	-	5,485 lm
92690599	BVP353 48LED 40K 220V L40 15	840 neutral white	4000 K	9,090 lm
92699899	BVP353 48LED 40K 220V L40 30	840 neutral white	4000 K	9,415 lm
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	RGBW	-	5,965 lm
92708799	BVP353 48LED 40K 220V L40 45	840 neutral white	4000 K	9,090 lm
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	RGBW	-	5,760 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
92608099	BVP353 30LED 30K 220V L30 10	60 W	92878700	BVP354 144LED 30K 220V L57 30	300 W
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	60 W	92885500	BVP354 144LED RGBNW 220V L57 30 DMX	300 W
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	60 W	92893000	BVP354 144LED RGBWW 220V L57 45 DMX	300 W
92618999	BVP353 30LED 40K 220V L30 15	60 W	92894700	BVP354 144LED RGBNW 220V L57 45 DMX	300 W
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	60 W	92752099	BVP353 72LED 30K 220V L57 10	150 W
92626499	BVP353 30LED 30K 220V L30 30	60 W	92753799	BVP353 72LED 40K 220V L57 10	150 W
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	60 W	92758299	BVP353 72LED RGBWW 220V L57 10 DMX	150 W
92635699	BVP353 30LED 30K 220V L30 45	60 W	92759999	BVP353 72LED RGBNW 220V L57 10 DMX	150 W
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	60 W	92762999	BVP353 72LED 40K 220V L57 15	150 W
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	200 W	92767499	BVP353 72LED RGBWW 220V L57 15 DMX	150 W
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	200 W	92768199	BVP353 72LED RGBNW 220V L57 15 DMX	150 W
92806000	BVP354 96LED 30K 220V L40 30	200 W	92771199	BVP353 72LED 40K 220V L57 30	150 W
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	200 W	92776699	BVP353 72LED RGBWW 220V L57 30 DMX	150 W
92815200	BVP354 96LED 30K 220V L40 45	200 W	92777399	BVP353 72LED RGBNW 220V L57 30 DMX	150 W
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	200 W	92779799	BVP353 72LED 30K 220V L57 45	150 W
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	240 W	92785899	BVP353 72LED RGBWW 220V L57 45 DMX	150 W
92833600	BVP354 120LED 30K 220V L50 15	240 W	92786599	BVP353 72LED RGBNW 220V L57 45 DMX	150 W
92843500	BVP354 120LED 40K 220V L50 30	240 W	92543499	BVP353 20LED RGBNW 220V L21 10 DMX	40 W
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	240 W	92552699	BVP353 20LED RGBNW 220V L21 15 DMX	40 W
92851000	BVP354 120LED 30K 220V L50 45	240 W	92561899	BVP353 20LED RGBNW 220V L21 30 DMX	40 W
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	240 W	92464299	BVP353 12LED 30K 220V L15 10	24 W
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	240 W	92465999	BVP353 12LED 40K 220V L15 10	24 W
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	300 W	92470399	BVP353 12LED RGBWW 220V L15 10 DMX	24 W
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	300 W	92471099	BVP353 12LED RGBNW 220V L15 10 DMX	24 W
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	300 W	92474199	BVP353 12LED 40K 220V L15 15	24 W

UniFlood M G2

Order Code	Full Product Name	Power Consumption
92479699	BVP353 12LED RGBWW 220V L15 15 DMX	24 W
92482699	BVP353 12LED 30K 220V L15 30	24 W
92483399	BVP353 12LED 40K 220V L15 30	24 W
92492599	BVP353 12LED 40K 220V L15 45	24 W
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	24 W
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	24 W
92644899	BVP353 36LED 30K 220V L35 10	80 W
92645599	BVP353 36LED 40K 220V L35 10	80 W
92654799	BVP353 36LED 40K 220V L35 15	80 W
92663999	BVP353 36LED 40K 220V L35 30	80 W
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	80 W
92572499	BVP353 24LED 30K 220V L24 10	50 W
92573199	BVP353 24LED 40K 220V L24 10	50 W
92581699	BVP353 24LED 30K 220V L24 15	50 W
92582399	BVP353 24LED 40K 220V L24 15	50 W
92590899	BVP353 24LED 30K 220V L24 30	50 W
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	50 W
92599199	BVP353 24LED 30K 220V L24 45	50 W
92600499	BVP353 24LED 40K 220V L24 45	50 W
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	120 W
92734699	BVP353 60LED 30K 220V L50 30	120 W
92735399	BVP353 60LED 40K 220V L50 30	120 W
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	120 W

Order Code	Full Product Name	Power Consumption
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	120 W
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	120 W
92509099	BVP353 16LED 30K 220V L18 15	30 W
92510699	BVP353 16LED 40K 220V L18 15	30 W
92518299	BVP353 16LED 30K 220V L18 30	30 W
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	30 W
92897800	BVP355 216LED 40K 220V L57 10	450 W
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	450 W
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	450 W
92923400	BVP355 216LED 30K 220V L57 45	450 W
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	450 W
92933300	BVP355 180LED 40K 220V L50 10	360 W
92942500	BVP355 180LED 40K 220V L50 15	360 W
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	360 W
92960900	BVP355 180LED 40K 220V L50 45	360 W
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	100 W
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	100 W
92690599	BVP353 48LED 40K 220V L40 15	100 W
92699899	BVP353 48LED 40K 220V L40 30	100 W
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	100 W
92708799	BVP353 48LED 40K 220V L40 45	100 W
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	100 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
92608099	BVP353 30LED 30K 220V L30 10	No
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	Yes
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	Yes
92618999	BVP353 30LED 40K 220V L30 15	No
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	Yes
92626499	BVP353 30LED 30K 220V L30 30	No
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	Yes
92635699	BVP353 30LED 30K 220V L30 45	No
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	Yes
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	Yes
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	Yes
92806000	BVP354 96LED 30K 220V L40 30	No
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	Yes
92815200	BVP354 96LED 30K 220V L40 45	No
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	Yes
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	Yes
92833600	BVP354 120LED 30K 220V L50 15	No
92843500	BVP354 120LED 40K 220V L50 30	No
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	Yes
92851000	BVP354 120LED 30K 220V L50 45	No
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	Yes
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	Yes
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	Yes
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	Yes
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	Yes

Order Code	Full Product Name	Dimmable
92878700	BVP354 144LED 30K 220V L57 30	No
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	Yes
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	Yes
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	Yes
92752099	BVP353 72LED 30K 220V L57 10	No
92753799	BVP353 72LED 40K 220V L57 10	No
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	Yes
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	Yes
92762999	BVP353 72LED 40K 220V L57 15	No
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	Yes
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	Yes
92771199	BVP353 72LED 40K 220V L57 30	No
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	Yes
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	Yes
92779799	BVP353 72LED 30K 220V L57 45	No
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	Yes
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	Yes
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	Yes
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	Yes
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	Yes
92464299	BVP353 12LED 30K 220V L15 10	No
92465999	BVP353 12LED 40K 220V L15 10	No
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	Yes
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	Yes
92474199	BVP353 12LED 40K 220V L15 15	No

UniFlood M G2

Order Code	Full Product Name	Dimmable
92479699	BVP353 12LED RGBWW 220V L15 15 DMX	Yes
92482699	BVP353 12LED 30K 220V L15 30	No
92483399	BVP353 12LED 40K 220V L15 30	No
92492599	BVP353 12LED 40K 220V L15 45	No
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	Yes
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	Yes
92644899	BVP353 36LED 30K 220V L35 10	No
92645599	BVP353 36LED 40K 220V L35 10	No
92654799	BVP353 36LED 40K 220V L35 15	No
92663999	BVP353 36LED 40K 220V L35 30	No
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	Yes
92572499	BVP353 24LED 30K 220V L24 10	No
92573199	BVP353 24LED 40K 220V L24 10	No
92581699	BVP353 24LED 30K 220V L24 15	No
92582399	BVP353 24LED 40K 220V L24 15	No
92590899	BVP353 24LED 30K 220V L24 30	No
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	Yes
92599199	BVP353 24LED 30K 220V L24 45	No
92600499	BVP353 24LED 40K 220V L24 45	No
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	Yes
92734699	BVP353 60LED 30K 220V L50 30	No
92735399	BVP353 60LED 40K 220V L50 30	No
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	Yes

Order Code	Full Product Name	Dimmable
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	Yes
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	Yes
92509099	BVP353 16LED 30K 220V L18 15	No
92510699	BVP353 16LED 40K 220V L18 15	No
92518299	BVP353 16LED 30K 220V L18 30	No
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	Yes
92897800	BVP355 216LED 40K 220V L57 10	No
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	Yes
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	Yes
92923400	BVP355 216LED 30K 220V L57 45	No
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	Yes
92933300	BVP355 180LED 40K 220V L50 10	No
92942500	BVP355 180LED 40K 220V L50 15	No
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	Yes
92960900	BVP355 180LED 40K 220V L50 45	No
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	Yes
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	Yes
92690599	BVP353 48LED 40K 220V L40 15	No
92699899	BVP353 48LED 40K 220V L40 30	No
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	Yes
92708799	BVP353 48LED 40K 220V L40 45	No
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	Yes

