



Philips UniFlood M gen2: A high power floodlight with true modularity

UniFlood M G2

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

UniFlood M G2


Application

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape


Warnings and Safety

- For outdoor use only.


Versions



Dimensional drawing



Dimensional drawing



General Information

Driver included	Yes
-----------------	-----

Light Technical

Color rendering index (CRI)	>80
-----------------------------	-----

Mechanical and Housing

Optical cover type	Clear glass
--------------------	-------------

Housing Color	Dark gray
---------------	-----------

Mech. impact protection code	IK06
------------------------------	------

Ingress protection code	IP66
-------------------------	------

Approval and Application

CE mark	Yes
---------	-----

Flammability mark	For mounting on normally flammable surfaces
-------------------	---

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401746943	BVP353 32LED RGBNW 220V L30 10 DMX	RGBW	-	2,985 lm
911401748743	BVP354 96LED RGBNW 220V L40 10 DMX	RGBW	-	10,975 lm
911401749013	BVP354 96LED RGBNW 220V L40 45 DMX	RGBW	-	11,520 lm
911401749153	BVP354 120LED 30K 220V L50 15 DMX	830 warm white	3000 K	18,485 lm
911401749213	BVP354 120LED 30K 220V L50 30 DMX	830 warm white	3000 K	20,500 lm
911401749223	BVP354 120LED 40K 220V L50 30 DMX	840 neutral white	4000 K	22,875 lm
911401749303	BVP354 120LED 30K 220V L50 45 DMX	830 warm white	3000 K	19,795 lm
911401749313	BVP354 120LED 40K 220V L50 45 DMX	840 neutral white	4000 K	22,085 lm
911401749463	BVP354 144LED RGBNW 220V L57 10 DMX	RGBW	-	15,030 lm
911401750023	BVP355 216LED 30K 220V L57 45 DMX	830 warm white	3000 K	37,400 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401746943	BVP353 32LED RGBNW 220V L30 10 DMX	60 W
911401748743	BVP354 96LED RGBNW 220V L40 10 DMX	200 W
911401749013	BVP354 96LED RGBNW 220V L40 45 DMX	200 W
911401749153	BVP354 120LED 30K 220V L50 15 DMX	240 W
911401749213	BVP354 120LED 30K 220V L50 30 DMX	240 W

Order Code	Full Product Name	Power Consumption
911401749223	BVP354 120LED 40K 220V L50 30 DMX	240 W
911401749303	BVP354 120LED 30K 220V L50 45 DMX	240 W
911401749313	BVP354 120LED 40K 220V L50 45 DMX	240 W
911401749463	BVP354 144LED RGBNW 220V L57 10 DMX	300 W
911401750023	BVP355 216LED 30K 220V L57 45 DMX	450 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401746943	BVP353 32LED RGBNW 220V L30 10 DMX	Yes
911401748743	BVP354 96LED RGBNW 220V L40 10 DMX	Yes
911401749013	BVP354 96LED RGBNW 220V L40 45 DMX	Yes
911401749153	BVP354 120LED 30K 220V L50 15 DMX	Yes
911401749213	BVP354 120LED 30K 220V L50 30 DMX	No

Order Code	Full Product Name	Dimmable
911401749223	BVP354 120LED 40K 220V L50 30 DMX	No
911401749303	BVP354 120LED 30K 220V L50 45 DMX	No
911401749313	BVP354 120LED 40K 220V L50 45 DMX	No
911401749463	BVP354 144LED RGBNW 220V L57 10 DMX	Yes
911401750023	BVP355 216LED 30K 220V L57 45 DMX	No

