



Architectural LED floodlight for fixed or dynamic lighting

UniFlood C Pro

Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, while the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-story exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colors, multiple spread lenses and a DMX512/RDM control option.

Benefits

- Available in white, monochromatic colors, RGB, RGBW and tunable white
- Wide range of beam angles from Narrow Spot to Wide Flood
- Available in DMX512/RDM control interface option

Features

- Robust design, IP66 rated for outdoor use
- Optical distributions: 3.5°, 10°, 15°, 30°, 45° and 60°
- Adjustable ±90° tilting angle
- Through wiring for DMX signal via dedicated cables with IP67 connectors

UniFlood C Pro


Application

- Bridges, Monuments, Façades
- Landscape
- Parks and Plazas

Warnings and Safety

- For outdoor use only

Dimensional drawing



General Information	
Driver included	Yes
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401773603	BVP371 12LED 27K 220V 10 24W HE	827 warm white	2700 K	>80	1,570 lm
911401773613	BVP371 12LED 27K 220V 10 DMX 24W HE	827 warm white	2700 K	>80	1,440 lm
911401773623	BVP371 12LED 27K 220V 15 24W HE	827 warm white	2700 K	>80	1,635 lm
911401773633	BVP371 12LED 27K 220V 15 DMX 24W HE	827 warm white	2700 K	>80	1,500 lm
911401773643	BVP371 12LED 27K 220V 30 24W HE	827 warm white	2700 K	>80	1,855 lm
911401773653	BVP371 12LED 27K 220V 30 DMX 24W HE	827 warm white	2700 K	>80	1,705 lm
911401773663	BVP371 12LED 27K 220V 45 24W HE	827 warm white	2700 K	>80	1,390 lm
911401773673	BVP371 12LED 27K 220V 45 DMX 24W HE	827 warm white	2700 K	>80	1,280 lm
911401773683	BVP371 12LED 27K 220V 60 24W HE	827 warm white	2700 K	>80	1,345 lm
911401773693	BVP371 12LED 27K 220V 60 DMX 24W HE	827 warm white	2700 K	>80	1,235 lm
911401773703	BVP371 12LED 30K 220V 10 24W HE	830 warm white	3000 K	>80	1,635 lm
911401773713	BVP371 12LED 30K 220V 10 DMX 24W HE	830 warm white	3000 K	>80	1,505 lm
911401773723	BVP371 12LED 30K 220V 15 24W HE	830 warm white	3000 K	>80	1,705 lm
911401773733	BVP371 12LED 30K 220V 15 DMX 24W HE	830 warm white	3000 K	>80	1,565 lm
911401773743	BVP371 12LED 30K 220V 30 24W HE	830 warm white	3000 K	>80	1,935 lm
911401773753	BVP371 12LED 30K 220V 30 DMX 24W HE	830 warm white	3000 K	>80	1,780 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401773763	BVP371 12LED 30K 220V 45 24W HE	830 warm white	3000 K	>80	1,450 lm
911401773773	BVP371 12LED 30K 220V 45 DMX 24W HE	830 warm white	3000 K	>80	1,335 lm
911401773783	BVP371 12LED 30K 220V 60 24W HE	830 warm white	3000 K	>80	1,405 lm
911401773793	BVP371 12LED 30K 220V 60 DMX 24W HE	830 warm white	3000 K	>80	1,290 lm
911401773803	BVP371 12LED 40K 220V 10 24W HE	840 neutral white	4000 K	>80	1,825 lm
911401773813	BVP371 12LED 40K 220V 10 DMX 24W HE	840 neutral white	4000 K	>80	1,675 lm
911401773823	BVP371 12LED 40K 220V 15 24W HE	840 neutral white	4000 K	>80	1,905 lm
911401773833	BVP371 12LED 40K 220V 15 DMX 24W HE	840 neutral white	4000 K	>80	1,750 lm
911401773843	BVP371 12LED 40K 220V 30 24W HE	840 neutral white	4000 K	>80	2,160 lm
911401773853	BVP371 12LED 40K 220V 30 DMX 24W HE	840 neutral white	4000 K	>80	1,985 lm
911401773863	BVP371 12LED 40K 220V 45 24W HE	840 neutral white	4000 K	>80	1,620 lm
911401773873	BVP371 12LED 40K 220V 45 DMX 24W HE	840 neutral white	4000 K	>80	1,485 lm
911401773883	BVP371 12LED 40K 220V 60 24W HE	840 neutral white	4000 K	>80	1,570 lm
911401773893	BVP371 12LED 40K 220V 60 DMX 24W HE	840 neutral white	4000 K	>80	1,440 lm
911401773903	BVP371 12LED RGB 220V 10 DMX 24W HE	RGB	-	N.A.	880 lm
911401773913	BVP371 12LED RGB 220V 15 DMX 24W HE	RGB	-	N.A.	920 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401773923	BVP371 12LED RGB 220V 30 DMX 24W HE	RGB	-	N.A.	1,040 lm
911401773933	BVP371 12LED RGB 220V 45 DMX 24W HE	RGB	-	N.A.	780 lm
911401773943	BVP371 12LED RGB 220V 60 DMX 24W HE	RGB	-	N.A.	755 lm
911401773953	BVP371 12LED RGBNW 220V 10 DMX 24W HE	RGBW	-	N.A.	1,090 lm
911401773963	BVP371 12LED RGBNW 220V 15 DMX 24W HE	RGBW	-	N.A.	1,140 lm
911401773973	BVP371 12LED RGBNW 220V 30 DMX 24W HE	RGBW	-	N.A.	1,290 lm
911401773983	BVP371 12LED RGBNW 220V 45 DMX 24W HE	RGBW	-	N.A.	970 lm
911401773993	BVP371 12LED RGBNW 220V 60 DMX 24W HE	RGBW	-	N.A.	940 lm
911401774003	BVP371 12LED RGBWW 220V 10 DMX 24W HE	RGBW	-	N.A.	1,045 lm
911401774013	BVP371 12LED RGBWW 220V 15 DMX 24W HE	RGBW	-	N.A.	1,090 lm
911401774023	BVP371 12LED RGBWW 220V 30 DMX 24W HE	RGBW	-	N.A.	1,235 lm
911401774033	BVP371 12LED RGBWW 220V 45 DMX 24W HE	RGBW	-	N.A.	925 lm
911401774043	BVP371 12LED RGBWW 220V 60 DMX 24W HE	RGBW	-	N.A.	900 lm
911401774053	BVP372 15LED RGB 220V 10 DMX 40W HP	RGB	-	N.A.	1,295 lm
911401774063	BVP372 15LED RGB 220V 15 DMX 40W HP	RGB	-	N.A.	1,350 lm
911401774073	BVP372 15LED RGB 220V 30 DMX 40W HP	RGB	-	N.A.	1,530 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401774083	BVP372 15LED RGB 220V 45 DMX 40W HP	RGB	-	N.A.	1,150 lm
911401774093	BVP372 15LED RGB 220V 60 DMX 40W HP	RGB	-	N.A.	1,110 lm
911401774103	BVP372 16LED 27K 220V 10 40W HP	827 warm white	2700 K	>80	2,465 lm
911401774113	BVP372 16LED 27K 220V 10 DMX 40W HP	827 warm white	2700 K	>80	2,240 lm
911401774123	BVP372 16LED 27K 220V 15 40W HP	827 warm white	2700 K	>80	2,570 lm
911401774133	BVP372 16LED 27K 220V 15 DMX 40W HP	827 warm white	2700 K	>80	2,335 lm
911401774143	BVP372 16LED 27K 220V 30 40W HP	827 warm white	2700 K	>80	2,915 lm
911401774153	BVP372 16LED 27K 220V 30 DMX 40W HP	827 warm white	2700 K	>80	2,650 lm
911401774163	BVP372 16LED 27K 220V 45 40W HP	827 warm white	2700 K	>80	2,185 lm
911401774173	BVP372 16LED 27K 220V 45 DMX 40W HP	827 warm white	2700 K	>80	1,990 lm
911401774183	BVP372 16LED 27K 220V 60 40W HP	827 warm white	2700 K	>80	2,115 lm
911401774193	BVP372 16LED 27K 220V 60 DMX 40W HP	827 warm white	2700 K	>80	1,925 lm
911401774203	BVP372 16LED 30K 220V 10 40W HP	830 warm white	3000 K	>80	2,570 lm
911401774213	BVP372 16LED 30K 220V 10 DMX 40W HP	830 warm white	3000 K	>80	2,340 lm
911401774223	BVP372 16LED 30K 220V 15 40W HP	830 warm white	3000 K	>80	2,680 lm
911401774233	BVP372 16LED 30K 220V 15 DMX 40W HP	830 warm white	3000 K	>80	2,435 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401774243	BVP372 16LED 30K 220V 30 40W HP	830 warm white	3000 K	>80	3,040 lm
911401774253	BVP372 16LED 30K 220V 30 DMX 40W HP	830 warm white	3000 K	>80	2,765 lm
911401774263	BVP372 16LED 30K 220V 45 40W HP	830 warm white	3000 K	>80	2,280 lm
911401774273	BVP372 16LED 30K 220V 45 DMX 40W HP	830 warm white	3000 K	>80	2,075 lm
911401774283	BVP372 16LED 30K 220V 60 40W HP	830 warm white	3000 K	>80	2,210 lm
911401774293	BVP372 16LED 30K 220V 60 DMX 40W HP	830 warm white	3000 K	>80	2,010 lm
911401774303	BVP372 16LED 40K 220V 10 40W HP	840 neutral white	4000 K	>80	2,870 lm
911401774313	BVP372 16LED 40K 220V 10 DMX 40W HP	840 neutral white	4000 K	>80	2,610 lm
911401774323	BVP372 16LED 40K 220V 15 40W HP	840 neutral white	4000 K	>80	2,990 lm
911401774333	BVP372 16LED 40K 220V 15 DMX 40W HP	840 neutral white	4000 K	>80	2,720 lm
911401774343	BVP372 16LED 40K 220V 30 40W HP	840 neutral white	4000 K	>80	3,395 lm
911401774353	BVP372 16LED 40K 220V 30 DMX 40W HP	840 neutral white	4000 K	>80	3,085 lm
911401774363	BVP372 16LED 40K 220V 45 40W HP	840 neutral white	4000 K	>80	2,545 lm
911401774373	BVP372 16LED 40K 220V 45 DMX 40W HP	840 neutral white	4000 K	>80	2,315 lm
911401774383	BVP372 16LED 40K 220V 60 40W HP	840 neutral white	4000 K	>80	2,465 lm
911401774393	BVP372 16LED 40K 220V 60 DMX 40W HP	840 neutral white	4000 K	>80	2,240 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401774403	BVP372 16LED RGBW 220V 10 DMX 40W HP	RGBW	-	N.A.	1,580 lm
911401774413	BVP372 16LED RGBW 220V 15 DMX 40W HP	RGBW	-	N.A.	1,650 lm
911401774423	BVP372 16LED RGBW 220V 30 DMX 40W HP	RGBW	-	N.A.	1,870 lm
911401774433	BVP372 16LED RGBW 220V 45 DMX 40W HP	RGBW	-	N.A.	1,400 lm
911401774443	BVP372 16LED RGBW 220V 60 DMX 40W HP	RGBW	-	N.A.	1,360 lm
911401774453	BVP372 16LED RGBWW 220V 10 DMX 40W HP	RGBW	-	N.A.	1,515 lm
911401774463	BVP372 16LED RGBWW 220V 15 DMX 40W HP	RGBW	-	N.A.	1,575 lm
911401774473	BVP372 16LED RGBWW 220V 30 DMX 40W HP	RGBW	-	N.A.	1,790 lm
911401774483	BVP372 16LED RGBWW 220V 45 DMX 40W HP	RGBW	-	N.A.	1,340 lm
911401774493	BVP372 16LED RGBWW 220V 60 DMX 40W HP	RGBW	-	N.A.	1,300 lm
911401774503	BVP372 18LED 27K 220V 10 50W HP	827 warm white	2700 K	>80	2,945 lm
911401774513	BVP372 18LED 27K 220V 10 DMX 50W HP	827 warm white	2700 K	>80	2,745 lm
911401774523	BVP372 18LED 27K 220V 15 50W HP	827 warm white	2700 K	>80	3,070 lm
911401774533	BVP372 18LED 27K 220V 15 DMX 50W HP	827 warm white	2700 K	>80	2,860 lm
911401774543	BVP372 18LED 27K 220V 30 50W HP	827 warm white	2700 K	>80	3,485 lm
911401774553	BVP372 18LED 27K 220V 30 DMX 50W HP	827 warm white	2700 K	>80	3,250 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401774563	BVP372 18LED 27K 220V 45 50W HP	827 warm white	2700 K	>80	2,615 lm
911401774573	BVP372 18LED 27K 220V 45 DMX 50W HP	827 warm white	2700 K	>80	2,435 lm
911401774583	BVP372 18LED 27K 220V 60 50W HP	827 warm white	2700 K	>80	2,530 lm
911401774593	BVP372 18LED 27K 220V 60 DMX 50W HP	827 warm white	2700 K	>80	2,360 lm
911401774603	BVP372 18LED 30K 220V 10 50W HP	830 warm white	3000 K	>80	3,070 lm
911401774613	BVP372 18LED 30K 220V 10 DMX 50W HP	830 warm white	3000 K	>80	2,865 lm
911401774623	BVP372 18LED 30K 220V 15 50W HP	830 warm white	3000 K	>80	3,200 lm
911401774633	BVP372 18LED 30K 220V 15 DMX 50W HP	830 warm white	3000 K	>80	2,985 lm
911401774643	BVP372 18LED 30K 220V 30 50W HP	830 warm white	3000 K	>80	3,635 lm
911401774653	BVP372 18LED 30K 220V 30 DMX 50W HP	830 warm white	3000 K	>80	3,390 lm
911401774663	BVP372 18LED 30K 220V 45 50W HP	830 warm white	3000 K	>80	2,725 lm
911401774673	BVP372 18LED 30K 220V 45 DMX 50W HP	830 warm white	3000 K	>80	2,540 lm
911401774683	BVP372 18LED 30K 220V 60 50W HP	830 warm white	3000 K	>80	2,640 lm
911401774693	BVP372 18LED 30K 220V 60 DMX 50W HP	830 warm white	3000 K	>80	2,460 lm
911401774703	BVP372 18LED 40K 220V 10 50W HP	840 neutral white	4000 K	>80	3,430 lm
911401774713	BVP372 18LED 40K 220V 10 DMX 50W HP	840 neutral white	4000 K	>80	3,195 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401774723	BVP372 18LED 40K 220V 15 50W HP	840 neutral white	4000 K	>80	3,575 lm
911401774733	BVP372 18LED 40K 220V 15 DMX 50W HP	840 neutral white	4000 K	>80	3,330 lm
911401774743	BVP372 18LED 40K 220V 30 50W HP	840 neutral white	4000 K	>80	4,055 lm
911401774753	BVP372 18LED 40K 220V 30 DMX 50W HP	840 neutral white	4000 K	>80	3,780 lm
911401774763	BVP372 18LED 40K 220V 45 50W HP	840 neutral white	4000 K	>80	3,040 lm
911401774773	BVP372 18LED 40K 220V 45 DMX 50W HP	840 neutral white	4000 K	>80	2,835 lm
911401774783	BVP372 18LED 40K 220V 60 50W HP	840 neutral white	4000 K	>80	2,945 lm
911401774793	BVP372 18LED 40K 220V 60 DMX 50W HP	840 neutral white	4000 K	>80	2,745 lm
911401774803	BVP372 18LED RGB 220V 10 DMX 50W HP	RGB	-	N.A.	1,570 lm
911401774813	BVP372 18LED RGB 220V 15 DMX 50W HP	RGB	-	N.A.	1,635 lm
911401774823	BVP372 18LED RGB 220V 30 DMX 50W HP	RGB	-	N.A.	1,855 lm
911401774833	BVP372 18LED RGB 220V 45 DMX 50W HP	RGB	-	N.A.	1,390 lm
911401774843	BVP372 18LED RGB 220V 60 DMX 50W HP	RGB	-	N.A.	1,345 lm
911401774853	BVP372 20LED RGBNW 220V 10 DMX 50W HP	RGBW	-	N.A.	2,140 lm
911401774863	BVP372 20LED RGBNW 220V 15 DMX 50W HP	RGBW	-	N.A.	2,230 lm
911401774873	BVP372 20LED RGBNW 220V 30 DMX 50W HP	RGBW	-	N.A.	2,530 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401774883	BVP372 20LED RGBNW 220V 45 DMX 50W HP	RGBW	-	N.A.	1,895 lm
911401774893	BVP372 20LED RGBNW 220V 60 DMX 50W HP	RGBW	-	N.A.	1,835 lm
911401774903	BVP372 20LED RGBWW 220V 10 DMX 50W HP	RGBW	-	N.A.	2,045 lm
911401774913	BVP372 20LED RGBWW 220V 15 DMX 50W HP	RGBW	-	N.A.	2,130 lm
911401774923	BVP372 20LED RGBWW 220V 30 DMX 50W HP	RGBW	-	N.A.	2,420 lm
911401774933	BVP372 20LED RGBWW 220V 45 DMX 50W HP	RGBW	-	N.A.	1,815 lm
911401774943	BVP372 20LED RGBWW 220V 60 DMX 50W HP	RGBW	-	N.A.	1,755 lm
911401774953	BVP373 30LED 27K 220V 10 80W HP	827 warm white	2700 K	>80	4,945 lm
911401774963	BVP373 30LED 27K 220V 10 DMX 80W HP	827 warm white	2700 K	>80	4,640 lm
911401774973	BVP373 30LED 27K 220V 15 80W HP	827 warm white	2700 K	>80	5,155 lm
911401774983	BVP373 30LED 27K 220V 15 DMX 80W HP	827 warm white	2700 K	>80	4,835 lm
911401774993	BVP373 30LED 27K 220V 30 80W HP	827 warm white	2700 K	>80	5,850 lm
911401775003	BVP373 30LED 27K 220V 30 DMX 80W HP	827 warm white	2700 K	>80	5,490 lm
911401775013	BVP373 30LED 27K 220V 45 80W HP	827 warm white	2700 K	>80	4,385 lm
911401775023	BVP373 30LED 27K 220V 45 DMX 80W HP	827 warm white	2700 K	>80	4,115 lm
911401775033	BVP373 30LED 27K 220V 60 80W HP	827 warm white	2700 K	>80	4,250 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401775043	BVP373 30LED 27K 220V 60 DMX 80W HP	827 warm white	2700 K	>80	3,985 lm
911401775053	BVP373 30LED 30K 220V 10 80W HP	830 warm white	3000 K	>80	5,160 lm
911401775063	BVP373 30LED 30K 220V 10 DMX 80W HP	830 warm white	3000 K	>80	4,840 lm
911401775073	BVP373 30LED 30K 220V 15 80W HP	830 warm white	3000 K	>80	5,375 lm
911401775083	BVP373 30LED 30K 220V 15 DMX 80W HP	830 warm white	3000 K	>80	5,045 lm
911401775093	BVP373 30LED 30K 220V 30 80W HP	830 warm white	3000 K	>80	6,100 lm
911401775103	BVP373 30LED 30K 220V 30 DMX 80W HP	830 warm white	3000 K	>80	5,725 lm
911401775113	BVP373 30LED 30K 220V 45 80W HP	830 warm white	3000 K	>80	4,575 lm
911401775123	BVP373 30LED 30K 220V 45 DMX 80W HP	830 warm white	3000 K	>80	4,295 lm
911401775133	BVP373 30LED 30K 220V 60 80W HP	830 warm white	3000 K	>80	4,430 lm
911401775143	BVP373 30LED 30K 220V 60 DMX 80W HP	830 warm white	3000 K	>80	4,155 lm
911401775153	BVP373 30LED 40K 220V 10 80W HP	840 neutral white	4000 K	>80	5,755 lm
911401775163	BVP373 30LED 40K 220V 10 DMX 80W HP	840 neutral white	4000 K	>80	5,400 lm
911401775173	BVP373 30LED 40K 220V 15 80W HP	840 neutral white	4000 K	>80	6,000 lm
911401775183	BVP373 30LED 40K 220V 15 DMX 80W HP	840 neutral white	4000 K	>80	5,625 lm
911401775193	BVP373 30LED 40K 220V 30 80W HP	840 neutral white	4000 K	>80	6,810 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401775203	BVP373 30LED	840	4000 K	>80	6,385 lm
	40K 220V 30	neutral			
	DMX 80W HP	white			
911401775213	BVP373 30LED	840	4000 K	>80	5,105 lm
	40K 220V 45	neutral			
	80W HP	white			
911401775223	BVP373 30LED	840	4000 K	>80	4,790 lm
	40K 220V 45	neutral			
	DMX 80W HP	white			
911401775233	BVP373 30LED	840	4000 K	>80	4,945 lm
	40K 220V 60	neutral			
	80W HP	white			
911401775243	BVP373 30LED	840	4000 K	>80	4,640 lm
	40K 220V 60	neutral			
	DMX 80W HP	white			
911401775253	BVP373 30LED	RGB	-	N.A.	2,695 lm
	RGB 220V 10				
	DMX 80W HP				
911401775263	BVP373 30LED	RGB	-	N.A.	2,810 lm
	RGB 220V 15				
	DMX 80W HP				
911401775273	BVP373 30LED	RGB	-	N.A.	3,190 lm
	RGB 220V 30				
	DMX 80W HP				
911401775283	BVP373 30LED	RGB	-	N.A.	2,390 lm
	RGB 220V 45				
	DMX 80W HP				
911401775293	BVP373 30LED	RGB	-	N.A.	2,315 lm
	RGB 220V 60				
	DMX 80W HP				
911401775303	BVP373 32LED	RGBW	-	N.A.	3,520 lm
	RGBNW 220V 10				
	DMX 80W HP				
911401775313	BVP373 32LED	RGBW	-	N.A.	3,670 lm
	RGBNW 220V 15				
	DMX 80W HP				
911401775323	BVP373 32LED	RGBW	-	N.A.	4,170 lm
	RGBNW 220V 30				
	DMX 80W HP				
911401775333	BVP373 32LED	RGBW	-	N.A.	3,125 lm
	RGBNW 220V 45				
	DMX 80W HP				
911401775343	BVP373 32LED	RGBW	-	N.A.	3,025 lm
	RGBNW 220V 60				
	DMX 80W HP				
911401775353	BVP373 32LED	RGBW	-	N.A.	3,370 lm
	RGBWW 220V 10				
	DMX 80W HP				

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401775363	BVP373 32LED	RGBW	-	N.A.	3,515 lm
	RGBWW 220V 15				
	DMX 80W HP				
911401775373	BVP373 32LED	RGBW	-	N.A.	3,990 lm
	RGBWW 220V 30				
	DMX 80W HP				
911401775383	BVP373 32LED	RGBW	-	N.A.	2,990 lm
	RGBWW 220V 45				
	DMX 80W HP				
911401775393	BVP373 32LED	RGBW	-	N.A.	2,895 lm
	RGBWW 220V 60				
	DMX 80W HP				
911401775403	BVP373 36LED	827 warm	2700 K	>80	6,175 lm
	27K 220V 10	white			
	100W HP				
911401775413	BVP373 36LED	827 warm	2700 K	>80	5,720 lm
	27K 220V 10 DMX	white			
	100W HP				
911401775423	BVP373 36LED	827 warm	2700 K	>80	6,440 lm
	27K 220V 15	white			
	100W HP				
911401775433	BVP373 36LED	827 warm	2700 K	>80	5,965 lm
	27K 220V 15 DMX	white			
	100W HP				
911401775443	BVP373 36LED	827 warm	2700 K	>80	7,310 lm
	27K 220V 30	white			
	100W HP				
911401775453	BVP373 36LED	827 warm	2700 K	>80	6,770 lm
	27K 220V 30 DMX	white			
	100W HP				
911401775463	BVP373 36LED	827 warm	2700 K	>80	5,480 lm
	27K 220V 45	white			
	100W HP				
911401775473	BVP373 36LED	827 warm	2700 K	>80	5,075 lm
	27K 220V 45 DMX	white			
	100W HP				
911401775483	BVP373 36LED	827 warm	2700 K	>80	5,305 lm
	27K 220V 60	white			
	100W HP				
911401775493	BVP373 36LED	827 warm	2700 K	>80	4,915 lm
	27K 220V 60	white			
	DMX 100W HP				
911401775503	BVP373 36LED	830 warm	3000 K	>80	6,445 lm
	30K 220V 10	white			
	100W HP				
911401775513	BVP373 36LED	830 warm	3000 K	>80	5,970 lm
	30K 220V 10 DMX	white			
	100W HP				

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401775523	BVP373 36LED 30K 220V 15 100W HP	830 warm white	3000 K	>80	6,715 lm
911401775533	BVP373 36LED 30K 220V 15 DMX 100W HP	830 warm white	3000 K	>80	6,220 lm
911401775543	BVP373 36LED 30K 220V 30 100W HP	830 warm white	3000 K	>80	7,625 lm
911401775553	BVP373 36LED 30K 220V 30 DMX 100W HP	830 warm white	3000 K	>80	7,060 lm
911401775563	BVP373 36LED 30K 220V 45 100W HP	830 warm white	3000 K	>80	5,715 lm
911401775573	BVP373 36LED 30K 220V 45 DMX 100W HP	830 warm white	3000 K	>80	5,295 lm
911401775583	BVP373 36LED 30K 220V 60 100W HP	830 warm white	3000 K	>80	5,535 lm
911401775593	BVP373 36LED 30K 220V 60 DMX 100W HP	830 warm white	3000 K	>80	5,125 lm
911401775603	BVP373 36LED 40K 220V 10 100W HP	840 neutral white	4000 K	>80	7,190 lm
911401775613	BVP373 36LED 40K 220V 10 DMX 100W HP	840 neutral white	4000 K	>80	6,660 lm
911401775623	BVP373 36LED 40K 220V 15 100W HP	840 neutral white	4000 K	>80	7,495 lm
911401775633	BVP373 36LED 40K 220V 15 DMX 100W HP	840 neutral white	4000 K	>80	6,940 lm
911401775643	BVP373 36LED 40K 220V 30 100W HP	840 neutral white	4000 K	>80	8,505 lm
911401775653	BVP373 36LED 40K 220V 30 DMX 100W HP	840 neutral white	4000 K	>80	7,880 lm
911401775663	BVP373 36LED 40K 220V 45 100W HP	840 neutral white	4000 K	>80	6,380 lm
911401775673	BVP373 36LED 40K 220V 45 DMX 100W HP	840 neutral white	4000 K	>80	5,910 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401775683	BVP373 36LED 40K 220V 60 100W HP	840 neutral white	4000 K	>80	6,175 lm
911401775693	BVP373 36LED 40K 220V 60 DMX 100W HP	840 neutral white	4000 K	>80	5,720 lm
911401775703	BVP373 36LED RGB 220V 10 DMX 100W HP	RGB	-	N.A.	3,300 lm
911401775713	BVP373 36LED RGB 220V 15 DMX 100W HP	RGB	-	N.A.	3,440 lm
911401775723	BVP373 36LED RGB 220V 30 DMX 100W HP	RGB	-	N.A.	3,905 lm
911401775733	BVP373 36LED RGB 220V 45 DMX 100W HP	RGB	-	N.A.	2,930 lm
911401775743	BVP373 36LED RGB 220V 60 DMX 100W HP	RGB	-	N.A.	2,835 lm
911401775753	BVP373 36LED RGBW 220V 10 DMX 100W HP	RGBW	-	N.A.	4,175 lm
911401775763	BVP373 36LED RGBW 220V 15 DMX 100W HP	RGBW	-	N.A.	4,355 lm
911401775773	BVP373 36LED RGBW 220V 30 DMX 100W HP	RGBW	-	N.A.	4,945 lm
911401775783	BVP373 36LED RGBW 220V 45 DMX 100W HP	RGBW	-	N.A.	3,705 lm
911401775793	BVP373 36LED RGBW 220V 60 DMX 100W HP	RGBW	-	N.A.	3,590 lm
911401775803	BVP373 36LED RGBWW 220V 10 DMX 100W HP	RGBW	-	N.A.	3,995 lm
911401775813	BVP373 36LED RGBWW 220V 15 DMX 100W HP	RGBW	-	N.A.	4,165 lm
911401775823	BVP373 36LED RGBWW 220V 30 DMX 100W HP	RGBW	-	N.A.	4,730 lm
911401775833	BVP373 36LED RGBWW 220V 45 DMX 100W HP	RGBW	-	N.A.	3,545 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401775843	BVP373 36LED RGBWW 220V 60 DMX 100W HP	RGBW	-	N.A.	3,435 lm
911401775853	BVP374 48LED 27K 220V 10 120W HP	827 warm white	2700 K	>80	7,540 lm
911401775863	BVP374 48LED 27K 220V 10 DMX 120W HP	827 warm white	2700 K	>80	7,040 lm
911401775873	BVP374 48LED 27K 220V 15 120W HP	827 warm white	2700 K	>80	7,855 lm
911401775883	BVP374 48LED 27K 220V 15 DMX 120W HP	827 warm white	2700 K	>80	7,340 lm
911401775893	BVP374 48LED 27K 220V 30 120W HP	827 warm white	2700 K	>80	8,920 lm
911401775903	BVP374 48LED 27K 220V 30 DMX 120W HP	827 warm white	2700 K	>80	8,330 lm
911401775913	BVP374 48LED 27K 220V 45 120W HP	827 warm white	2700 K	>80	6,690 lm
911401775923	BVP374 48LED 27K 220V 45 DMX 120W HP	827 warm white	2700 K	>80	6,245 lm
911401775933	BVP374 48LED 27K 220V 60 120W HP	827 warm white	2700 K	>80	6,475 lm
911401775943	BVP374 48LED 27K 220V 60 DMX 120W HP	827 warm white	2700 K	>80	6,050 lm
911401775953	BVP374 48LED 30K 220V 10 120W HP	830 warm white	3000 K	>80	7,865 lm
911401775963	BVP374 48LED 30K 220V 10 DMX 120W HP	830 warm white	3000 K	>80	7,345 lm
911401775973	BVP374 48LED 30K 220V 15 120W HP	830 warm white	3000 K	>80	8,195 lm
911401775983	BVP374 48LED 30K 220V 15 DMX 120W HP	830 warm white	3000 K	>80	7,655 lm
911401775993	BVP374 48LED 30K 220V 30 120W HP	830 warm white	3000 K	>80	9,305 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401776003	BVP374 48LED 30K 220V 30 DMX 120W HP	830 warm white	3000 K	>80	8,690 lm
911401776013	BVP374 48LED 30K 220V 45 120W HP	830 warm white	3000 K	>80	6,975 lm
911401776023	BVP374 48LED 30K 220V 45 DMX 120W HP	830 warm white	3000 K	>80	6,515 lm
911401776033	BVP374 48LED 30K 220V 60 120W HP	830 warm white	3000 K	>80	6,755 lm
911401776043	BVP374 48LED 30K 220V 60 DMX 120W HP	830 warm white	3000 K	>80	6,310 lm
911401776053	BVP374 48LED 40K 220V 10 120W HP	840 neutral white	4000 K	>80	8,775 lm
911401776063	BVP374 48LED 40K 220V 10 DMX 120W HP	840 neutral white	4000 K	>80	8,195 lm
911401776073	BVP374 48LED 40K 220V 15 120W HP	840 neutral white	4000 K	>80	9,145 lm
911401776083	BVP374 48LED 40K 220V 15 DMX 120W HP	840 neutral white	4000 K	>80	8,540 lm
911401776093	BVP374 48LED 40K 220V 30 120W HP	840 neutral white	4000 K	>80	10,380 lm
911401776103	BVP374 48LED 40K 220V 30 DMX 120W HP	840 neutral white	4000 K	>80	9,695 lm
911401776113	BVP374 48LED 40K 220V 45 120W HP	840 neutral white	4000 K	>80	7,785 lm
911401776123	BVP374 48LED 40K 220V 45 DMX 120W HP	840 neutral white	4000 K	>80	7,270 lm
911401776133	BVP374 48LED 40K 220V 60 120W HP	840 neutral white	4000 K	>80	7,535 lm
911401776143	BVP374 48LED 40K 220V 60 DMX 120W HP	840 neutral white	4000 K	>80	7,040 lm
911401776153	BVP374 48LED RGB 220V 10 DMX 120W HP	RGB	-	N.A.	4,035 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401776163	BVP374 48LED RGB 220V 15 DMX 120W HP	RGB	-	N.A.	4,205 lm
911401776173	BVP374 48LED RGB 220V 30 DMX 120W HP	RGB	-	N.A.	4,775 lm
911401776183	BVP374 48LED RGB 220V 45 DMX 120W HP	RGB	-	N.A.	3,580 lm
911401776193	BVP374 48LED RGB 220V 60 DMX 120W HP	RGB	-	N.A.	3,465 lm
911401776203	BVP374 48LED RGBW 220V 10 DMX 120W HP	RGBW	-	N.A.	5,165 lm
911401776213	BVP374 48LED RGBW 220V 15 DMX 120W HP	RGBW	-	N.A.	5,380 lm
911401776223	BVP374 48LED RGBW 220V 30 DMX 120W HP	RGBW	-	N.A.	6,110 lm
911401776233	BVP374 48LED RGBW 220V 45 DMX 120W HP	RGBW	-	N.A.	4,580 lm
911401776243	BVP374 48LED RGBW 220V 60 DMX 120W HP	RGBW	-	N.A.	4,435 lm
911401776253	BVP374 48LED RGBW 220V 10 DMX 120W HP	RGBW	-	N.A.	4,940 lm
911401776263	BVP374 48LED RGBW 220V 15 DMX 120W HP	RGBW	-	N.A.	5,150 lm
911401776273	BVP374 48LED RGBW 220V 30 DMX 120W HP	RGBW	-	N.A.	5,845 lm
911401776283	BVP374 48LED RGBW 220V 45 DMX 120W HP	RGBW	-	N.A.	4,385 lm
911401776293	BVP374 48LED RGBW 220V 60 DMX 120W HP	RGBW	-	N.A.	4,245 lm
911401776303	BVP374 60LED 27K 220V 10 150W HP	827 warm white	2700 K	>80	9,425 lm
911401776313	BVP374 60LED 27K 220V 10 DMX 150W HP	827 warm white	2700 K	>80	9,065 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401776323	BVP374 60LED 27K 220V 15 150W HP	827 warm white	2700 K	>80	9,820 lm
911401776333	BVP374 60LED 27K 220V 15 DMX 150W HP	827 warm white	2700 K	>80	9,450 lm
911401776343	BVP374 60LED 27K 220V 30 150W HP	827 warm white	2700 K	>80	11,150 lm
911401776353	BVP374 60LED 27K 220V 30 DMX 150W HP	827 warm white	2700 K	>80	10,725 lm
911401776363	BVP374 60LED 27K 220V 45 150W HP	827 warm white	2700 K	>80	8,360 lm
911401776373	BVP374 60LED 27K 220V 45 DMX 150W HP	827 warm white	2700 K	>80	8,045 lm
911401776383	BVP374 60LED 27K 220V 60 150W HP	827 warm white	2700 K	>80	8,095 lm
911401776393	BVP374 60LED 27K 220V 60 DMX 150W HP	827 warm white	2700 K	>80	7,790 lm
911401776403	BVP374 60LED 30K 220V 10 150W HP	830 warm white	3000 K	>80	9,830 lm
911401776413	BVP374 60LED 30K 220V 10 DMX 150W HP	830 warm white	3000 K	>80	9,455 lm
911401776423	BVP374 60LED 30K 220V 15 150W HP	830 warm white	3000 K	>80	10,245 lm
911401776433	BVP374 60LED 30K 220V 15 DMX 150W HP	830 warm white	3000 K	>80	9,855 lm
911401776443	BVP374 60LED 30K 220V 30 150W HP	830 warm white	3000 K	>80	11,630 lm
911401776453	BVP374 60LED 30K 220V 30 DMX 150W HP	830 warm white	3000 K	>80	11,190 lm
911401776463	BVP374 60LED 30K 220V 45 150W HP	830 warm white	3000 K	>80	8,720 lm
911401776473	BVP374 60LED 30K 220V 45 DMX 150W HP	830 warm white	3000 K	>80	8,390 lm

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401776483	BVP374 60LED 30K 220V 60 150W HP	830 warm white	3000 K	>80	8,445 lm
911401776493	BVP374 60LED 30K 220V 60 DMX 150W HP	830 warm white	3000 K	>80	8,125 lm
911401776503	BVP374 60LED 40K 220V 10 150W HP	840 neutral white	4000 K	>80	10,965 lm
911401776513	BVP374 60LED 40K 220V 10 DMX 150W HP	840 neutral white	4000 K	>80	10,550 lm
911401776523	BVP374 60LED 40K 220V 15 150W HP	840 neutral white	4000 K	>80	11,430 lm
911401776533	BVP374 60LED 40K 220V 15 DMX 150W HP	840 neutral white	4000 K	>80	10,995 lm
911401776543	BVP374 60LED 40K 220V 30 150W HP	840 neutral white	4000 K	>80	12,975 lm
911401776553	BVP374 60LED 40K 220V 30 DMX 150W HP	840 neutral white	4000 K	>80	12,485 lm
911401776563	BVP374 60LED 40K 220V 45 150W HP	840 neutral white	4000 K	>80	9,730 lm
911401776573	BVP374 60LED 40K 220V 45 DMX 150W HP	840 neutral white	4000 K	>80	9,360 lm
911401776583	BVP374 60LED 40K 220V 60 150W HP	840 neutral white	4000 K	>80	9,420 lm
911401776593	BVP374 60LED 40K 220V 60 DMX 150W HP	840 neutral white	4000 K	>80	9,065 lm
911401776603	BVP374 60LED RGB 220V 10 DMX 150W HP	RGB	-	N.A.	5,185 lm
911401776613	BVP374 60LED RGB 220V 15 DMX 150W HP	RGB	-	N.A.	5,405 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401773603	BVP371 12LED 27K 220V 10 24W HE	24 W
911401773613	BVP371 12LED 27K 220V 10 DMX 24W HE	24 W
911401773623	BVP371 12LED 27K 220V 15 24W HE	24 W

Order Code	Full Product Name	Light source color	Correlated Color	Color rendering index	Luminous Flux
			Temperature (Nom)	(CRI)	
911401776623	BVP374 60LED RGB 220V 30 DMX 150W HP	RGB	-	N.A.	6,135 lm
911401776633	BVP374 60LED RGB 220V 45 DMX 150W HP	RGB	-	N.A.	4,600 lm
911401776643	BVP374 60LED RGB 220V 60 DMX 150W HP	RGB	-	N.A.	4,455 lm
911401776653	BVP374 60LED RGBW 220V 10 DMX 150W HP	RGBW	-	N.A.	6,635 lm
911401776663	BVP374 60LED RGBW 220V 15 DMX 150W HP	RGBW	-	N.A.	6,920 lm
911401776673	BVP374 60LED RGBW 220V 30 DMX 150W HP	RGBW	-	N.A.	7,855 lm
911401776683	BVP374 60LED RGBW 220V 45 DMX 150W HP	RGBW	-	N.A.	5,890 lm
911401776693	BVP374 60LED RGBW 220V 60 DMX 150W HP	RGBW	-	N.A.	5,700 lm
911401776703	BVP374 60LED RGBWW 220V 10 DMX 150W HP	RGBW	-	N.A.	6,370 lm
911401776713	BVP374 60LED RGBWW 220V 15 DMX 150W HP	RGBW	-	N.A.	6,640 lm
911401776723	BVP374 60LED RGBWW 220V 30 DMX 150W HP	RGBW	-	N.A.	7,535 lm
911401776733	BVP374 60LED RGBWW 220V 45 DMX 150W HP	RGBW	-	N.A.	5,650 lm
911401776743	BVP374 60LED RGBWW 220V 60 DMX 150W HP	RGBW	-	N.A.	5,470 lm

Order Code	Full Product Name	Power Consumption
911401773663	BVP371 12LED 27K 220V 45 24W HE	24 W
911401773673	BVP371 12LED 27K 220V 45 DMX 24W HE	24 W
911401773683	BVP371 12LED 27K 220V 60 24W HE	24 W
911401773693	BVP371 12LED 27K 220V 60 DMX 24W HE	24 W
911401773703	BVP371 12LED 30K 220V 10 24W HE	24 W
911401773713	BVP371 12LED 30K 220V 10 DMX 24W HE	24 W
911401773723	BVP371 12LED 30K 220V 15 24W HE	24 W
911401773733	BVP371 12LED 30K 220V 15 DMX 24W HE	24 W
911401773743	BVP371 12LED 30K 220V 30 24W HE	24 W
911401773753	BVP371 12LED 30K 220V 30 DMX 24W HE	24 W
911401773763	BVP371 12LED 30K 220V 45 24W HE	24 W
911401773773	BVP371 12LED 30K 220V 45 DMX 24W HE	24 W
911401773783	BVP371 12LED 30K 220V 60 24W HE	24 W
911401773793	BVP371 12LED 30K 220V 60 DMX 24W HE	24 W
911401773803	BVP371 12LED 40K 220V 10 24W HE	24 W
911401773813	BVP371 12LED 40K 220V 10 DMX 24W HE	24 W
911401773823	BVP371 12LED 40K 220V 15 24W HE	24 W
911401773833	BVP371 12LED 40K 220V 15 DMX 24W HE	24 W
911401773843	BVP371 12LED 40K 220V 30 24W HE	24 W
911401773853	BVP371 12LED 40K 220V 30 DMX 24W HE	24 W
911401773863	BVP371 12LED 40K 220V 45 24W HE	24 W
911401773873	BVP371 12LED 40K 220V 45 DMX 24W HE	24 W
911401773883	BVP371 12LED 40K 220V 60 24W HE	24 W
911401773893	BVP371 12LED 40K 220V 60 DMX 24W HE	24 W
911401773903	BVP371 12LED RGB 220V 10 DMX 24W HE	24 W
911401773913	BVP371 12LED RGB 220V 15 DMX 24W HE	24 W
911401773923	BVP371 12LED RGB 220V 30 DMX 24W HE	24 W
911401773933	BVP371 12LED RGB 220V 45 DMX 24W HE	24 W
911401773943	BVP371 12LED RGB 220V 60 DMX 24W HE	24 W
911401773953	BVP371 12LED RGBNW 220V 10 DMX 24W HE	24 W
911401773963	BVP371 12LED RGBNW 220V 15 DMX 24W HE	24 W
911401773973	BVP371 12LED RGBNW 220V 30 DMX 24W HE	24 W
911401773983	BVP371 12LED RGBNW 220V 45 DMX 24W HE	24 W
911401773993	BVP371 12LED RGBNW 220V 60 DMX 24W HE	24 W
911401774003	BVP371 12LED RGBWW 220V 10 DMX 24W HE	24 W
911401774013	BVP371 12LED RGBWW 220V 15 DMX 24W HE	24 W
911401774023	BVP371 12LED RGBWW 220V 30 DMX 24W HE	24 W
911401774033	BVP371 12LED RGBWW 220V 45 DMX 24W HE	24 W
911401774043	BVP371 12LED RGBWW 220V 60 DMX 24W HE	24 W
911401774053	BVP372 15LED RGB 220V 10 DMX 40W HP	40 W
911401774063	BVP372 15LED RGB 220V 15 DMX 40W HP	40 W
911401774073	BVP372 15LED RGB 220V 30 DMX 40W HP	40 W
911401774083	BVP372 15LED RGB 220V 45 DMX 40W HP	40 W
911401774093	BVP372 15LED RGB 220V 60 DMX 40W HP	40 W
911401774103	BVP372 16LED 27K 220V 10 40W HP	40 W
911401774113	BVP372 16LED 27K 220V 10 DMX 40W HP	40 W
911401774123	BVP372 16LED 27K 220V 15 40W HP	40 W
911401774133	BVP372 16LED 27K 220V 15 DMX 40W HP	40 W
911401774143	BVP372 16LED 27K 220V 30 40W HP	40 W
911401774153	BVP372 16LED 27K 220V 30 DMX 40W HP	40 W
911401774163	BVP372 16LED 27K 220V 45 40W HP	40 W
911401774173	BVP372 16LED 27K 220V 45 DMX 40W HP	40 W

Order Code	Full Product Name	Power Consumption
911401774183	BVP372 16LED 27K 220V 60 40W HP	40 W
911401774193	BVP372 16LED 27K 220V 60 DMX 40W HP	40 W
911401774203	BVP372 16LED 30K 220V 10 40W HP	40 W
911401774213	BVP372 16LED 30K 220V 10 DMX 40W HP	40 W
911401774223	BVP372 16LED 30K 220V 15 40W HP	40 W
911401774233	BVP372 16LED 30K 220V 15 DMX 40W HP	40 W
911401774243	BVP372 16LED 30K 220V 30 40W HP	40 W
911401774253	BVP372 16LED 30K 220V 30 DMX 40W HP	40 W
911401774263	BVP372 16LED 30K 220V 45 40W HP	40 W
911401774273	BVP372 16LED 30K 220V 45 DMX 40W HP	40 W
911401774283	BVP372 16LED 30K 220V 60 40W HP	40 W
911401774293	BVP372 16LED 30K 220V 60 DMX 40W HP	40 W
911401774303	BVP372 16LED 40K 220V 10 40W HP	40 W
911401774313	BVP372 16LED 40K 220V 10 DMX 40W HP	40 W
911401774323	BVP372 16LED 40K 220V 15 40W HP	40 W
911401774333	BVP372 16LED 40K 220V 15 DMX 40W HP	40 W
911401774343	BVP372 16LED 40K 220V 30 40W HP	40 W
911401774353	BVP372 16LED 40K 220V 30 DMX 40W HP	40 W
911401774363	BVP372 16LED 40K 220V 45 40W HP	40 W
911401774373	BVP372 16LED 40K 220V 45 DMX 40W HP	40 W
911401774383	BVP372 16LED 40K 220V 60 40W HP	40 W
911401774393	BVP372 16LED 40K 220V 60 DMX 40W HP	40 W
911401774403	BVP372 16LED RGBNW 220V 10 DMX 40W HP	40 W
911401774413	BVP372 16LED RGBNW 220V 15 DMX 40W HP	40 W
911401774423	BVP372 16LED RGBNW 220V 30 DMX 40W HP	40 W
911401774433	BVP372 16LED RGBNW 220V 45 DMX 40W HP	40 W
911401774443	BVP372 16LED RGBNW 220V 60 DMX 40W HP	40 W
911401774453	BVP372 16LED RGBWW 220V 10 DMX 40W HP	40 W
911401774463	BVP372 16LED RGBWW 220V 15 DMX 40W HP	40 W
911401774473	BVP372 16LED RGBWW 220V 30 DMX 40W HP	40 W
911401774483	BVP372 16LED RGBWW 220V 45 DMX 40W HP	40 W
911401774493	BVP372 16LED RGBWW 220V 60 DMX 40W HP	40 W
911401774503	BVP372 18LED 27K 220V 10 50W HP	50 W
911401774513	BVP372 18LED 27K 220V 10 DMX 50W HP	50 W
911401774523	BVP372 18LED 27K 220V 15 50W HP	50 W
911401774533	BVP372 18LED 27K 220V 15 DMX 50W HP	50 W
911401774543	BVP372 18LED 27K 220V 30 50W HP	50 W
911401774553	BVP372 18LED 27K 220V 30 DMX 50W HP	50 W
911401774563	BVP372 18LED 27K 220V 45 50W HP	50 W
911401774573	BVP372 18LED 27K 220V 45 DMX 50W HP	50 W
911401774583	BVP372 18LED 27K 220V 60 50W HP	50 W
911401774593	BVP372 18LED 27K 220V 60 DMX 50W HP	50 W
911401774603	BVP372 18LED 30K 220V 10 50W HP	50 W
911401774613	BVP372 18LED 30K 220V 10 DMX 50W HP	50 W
911401774623	BVP372 18LED 30K 220V 15 50W HP	50 W
911401774633	BVP372 18LED 30K 220V 15 DMX 50W HP	50 W
911401774643	BVP372 18LED 30K 220V 30 50W HP	50 W
911401774653	BVP372 18LED 30K 220V 30 DMX 50W HP	50 W
911401774663	BVP372 18LED 30K 220V 45 50W HP	50 W
911401774673	BVP372 18LED 30K 220V 45 DMX 50W HP	50 W
911401774683	BVP372 18LED 30K 220V 60 50W HP	50 W
911401774693	BVP372 18LED 30K 220V 60 DMX 50W HP	50 W

Order Code	Full Product Name	Power Consumption
911401774703	BVP372 18LED 40K 220V 10 50W HP	50 W
911401774713	BVP372 18LED 40K 220V 10 DMX 50W HP	50 W
911401774723	BVP372 18LED 40K 220V 15 50W HP	50 W
911401774733	BVP372 18LED 40K 220V 15 DMX 50W HP	50 W
911401774743	BVP372 18LED 40K 220V 30 50W HP	50 W
911401774753	BVP372 18LED 40K 220V 30 DMX 50W HP	50 W
911401774763	BVP372 18LED 40K 220V 45 50W HP	50 W
911401774773	BVP372 18LED 40K 220V 45 DMX 50W HP	50 W
911401774783	BVP372 18LED 40K 220V 60 50W HP	50 W
911401774793	BVP372 18LED 40K 220V 60 DMX 50W HP	50 W
911401774803	BVP372 18LED RGB 220V 10 DMX 50W HP	50 W
911401774813	BVP372 18LED RGB 220V 15 DMX 50W HP	50 W
911401774823	BVP372 18LED RGB 220V 30 DMX 50W HP	50 W
911401774833	BVP372 18LED RGB 220V 45 DMX 50W HP	50 W
911401774843	BVP372 18LED RGB 220V 60 DMX 50W HP	50 W
911401774853	BVP372 20LED RGBNW 220V 10 DMX 50W HP	50 W
911401774863	BVP372 20LED RGBNW 220V 15 DMX 50W HP	50 W
911401774873	BVP372 20LED RGBNW 220V 30 DMX 50W HP	50 W
911401774883	BVP372 20LED RGBNW 220V 45 DMX 50W HP	50 W
911401774893	BVP372 20LED RGBNW 220V 60 DMX 50W HP	50 W
911401774903	BVP372 20LED RGBWW 220V 10 DMX 50W HP	50 W
911401774913	BVP372 20LED RGBWW 220V 15 DMX 50W HP	50 W
911401774923	BVP372 20LED RGBWW 220V 30 DMX 50W HP	50 W
911401774933	BVP372 20LED RGBWW 220V 45 DMX 50W HP	50 W
911401774943	BVP372 20LED RGBWW 220V 60 DMX 50W HP	50 W
911401774953	BVP373 30LED 27K 220V 10 80W HP	80 W
911401774963	BVP373 30LED 27K 220V 10 DMX 80W HP	80 W
911401774973	BVP373 30LED 27K 220V 15 80W HP	80 W
911401774983	BVP373 30LED 27K 220V 15 DMX 80W HP	80 W
911401774993	BVP373 30LED 27K 220V 30 80W HP	80 W
911401775003	BVP373 30LED 27K 220V 30 DMX 80W HP	80 W
911401775013	BVP373 30LED 27K 220V 45 80W HP	80 W
911401775023	BVP373 30LED 27K 220V 45 DMX 80W HP	80 W
911401775033	BVP373 30LED 27K 220V 60 80W HP	80 W
911401775043	BVP373 30LED 27K 220V 60 DMX 80W HP	80 W
911401775053	BVP373 30LED 30K 220V 10 80W HP	80 W
911401775063	BVP373 30LED 30K 220V 10 DMX 80W HP	80 W
911401775073	BVP373 30LED 30K 220V 15 80W HP	80 W
911401775083	BVP373 30LED 30K 220V 15 DMX 80W HP	80 W
911401775093	BVP373 30LED 30K 220V 30 80W HP	80 W
911401775103	BVP373 30LED 30K 220V 30 DMX 80W HP	80 W
911401775113	BVP373 30LED 30K 220V 45 80W HP	80 W
911401775123	BVP373 30LED 30K 220V 45 DMX 80W HP	80 W
911401775133	BVP373 30LED 30K 220V 60 80W HP	80 W
911401775143	BVP373 30LED 30K 220V 60 DMX 80W HP	80 W
911401775153	BVP373 30LED 40K 220V 10 80W HP	80 W
911401775163	BVP373 30LED 40K 220V 10 DMX 80W HP	80 W
911401775173	BVP373 30LED 40K 220V 15 80W HP	80 W
911401775183	BVP373 30LED 40K 220V 15 DMX 80W HP	80 W
911401775193	BVP373 30LED 40K 220V 30 80W HP	80 W
911401775203	BVP373 30LED 40K 220V 30 DMX 80W HP	80 W
911401775213	BVP373 30LED 40K 220V 45 80W HP	80 W

Order Code	Full Product Name	Power Consumption
911401775223	BVP373 30LED 40K 220V 45 DMX 80W HP	80 W
911401775233	BVP373 30LED 40K 220V 60 80W HP	80 W
911401775243	BVP373 30LED 40K 220V 60 DMX 80W HP	80 W
911401775253	BVP373 30LED RGB 220V 10 DMX 80W HP	80 W
911401775263	BVP373 30LED RGB 220V 15 DMX 80W HP	80 W
911401775273	BVP373 30LED RGB 220V 30 DMX 80W HP	80 W
911401775283	BVP373 30LED RGB 220V 45 DMX 80W HP	80 W
911401775293	BVP373 30LED RGB 220V 60 DMX 80W HP	80 W
911401775303	BVP373 32LED RGBNW 220V 10 DMX 80W HP	80 W
911401775313	BVP373 32LED RGBNW 220V 15 DMX 80W HP	80 W
911401775323	BVP373 32LED RGBNW 220V 30 DMX 80W HP	80 W
911401775333	BVP373 32LED RGBNW 220V 45 DMX 80W HP	80 W
911401775343	BVP373 32LED RGBNW 220V 60 DMX 80W HP	80 W
911401775353	BVP373 32LED RGBWW 220V 10 DMX 80W HP	80 W
911401775363	BVP373 32LED RGBWW 220V 15 DMX 80W HP	80 W
911401775373	BVP373 32LED RGBWW 220V 30 DMX 80W HP	80 W
911401775383	BVP373 32LED RGBWW 220V 45 DMX 80W HP	80 W
911401775393	BVP373 32LED RGBWW 220V 60 DMX 80W HP	80 W
911401775403	BVP373 36LED 27K 220V 10 100W HP	100 W
911401775413	BVP373 36LED 27K 220V 10 DMX 100W HP	100 W
911401775423	BVP373 36LED 27K 220V 15 100W HP	100 W
911401775433	BVP373 36LED 27K 220V 15 DMX 100W HP	100 W
911401775443	BVP373 36LED 27K 220V 30 100W HP	100 W
911401775453	BVP373 36LED 27K 220V 30 DMX 100W HP	100 W
911401775463	BVP373 36LED 27K 220V 45 100W HP	100 W
911401775473	BVP373 36LED 27K 220V 45 DMX 100W HP	100 W
911401775483	BVP373 36LED 27K 220V 60 100W HP	100 W
911401775493	BVP373 36LED 27K 220V 60 DMX 100W HP	100 W
911401775503	BVP373 36LED 30K 220V 10 100W HP	100 W
911401775513	BVP373 36LED 30K 220V 10 DMX 100W HP	100 W
911401775523	BVP373 36LED 30K 220V 15 100W HP	100 W
911401775533	BVP373 36LED 30K 220V 15 DMX 100W HP	100 W
911401775543	BVP373 36LED 30K 220V 30 100W HP	100 W
911401775553	BVP373 36LED 30K 220V 30 DMX 100W HP	100 W
911401775563	BVP373 36LED 30K 220V 45 100W HP	100 W
911401775573	BVP373 36LED 30K 220V 45 DMX 100W HP	100 W
911401775583	BVP373 36LED 30K 220V 60 100W HP	100 W
911401775593	BVP373 36LED 30K 220V 60 DMX 100W HP	100 W
911401775603	BVP373 36LED 40K 220V 10 100W HP	100 W
911401775613	BVP373 36LED 40K 220V 10 DMX 100W HP	100 W
911401775623	BVP373 36LED 40K 220V 15 100W HP	100 W
911401775633	BVP373 36LED 40K 220V 15 DMX 100W HP	100 W
911401775643	BVP373 36LED 40K 220V 30 100W HP	100 W
911401775653	BVP373 36LED 40K 220V 30 DMX 100W HP	100 W
911401775663	BVP373 36LED 40K 220V 45 100W HP	100 W
911401775673	BVP373 36LED 40K 220V 45 DMX 100W HP	100 W
911401775683	BVP373 36LED 40K 220V 60 100W HP	100 W
911401775693	BVP373 36LED 40K 220V 60 DMX 100W HP	100 W
911401775703	BVP373 36LED RGB 220V 10 DMX 100W HP	100 W
911401775713	BVP373 36LED RGB 220V 15 DMX 100W HP	100 W
911401775723	BVP373 36LED RGB 220V 30 DMX 100W HP	100 W
911401775733	BVP373 36LED RGB 220V 45 DMX 100W HP	100 W

Order Code	Full Product Name	Power Consumption
911401775743	BVP373 36LED RGB 220V 60 DMX 100W HP	100 W
911401775753	BVP373 36LED RGBNW 220V 10 DMX 100W HP	100 W
911401775763	BVP373 36LED RGBNW 220V 15 DMX 100W HP	100 W
911401775773	BVP373 36LED RGBNW 220V 30 DMX 100W HP	100 W
911401775783	BVP373 36LED RGBNW 220V 45 DMX 100W HP	100 W
911401775793	BVP373 36LED RGBNW 220V 60 DMX 100W HP	100 W
911401775803	BVP373 36LED RGBWW 220V 10 DMX 100W HP	100 W
911401775813	BVP373 36LED RGBWW 220V 15 DMX 100W HP	100 W
911401775823	BVP373 36LED RGBWW 220V 30 DMX 100W HP	100 W
911401775833	BVP373 36LED RGBWW 220V 45 DMX 100W HP	100 W
911401775843	BVP373 36LED RGBWW 220V 60 DMX 100W HP	100 W
911401775853	BVP374 48LED 27K 220V 10 120W HP	120 W
911401775863	BVP374 48LED 27K 220V 10 DMX 120W HP	120 W
911401775873	BVP374 48LED 27K 220V 15 120W HP	120 W
911401775883	BVP374 48LED 27K 220V 15 DMX 120W HP	120 W
911401775893	BVP374 48LED 27K 220V 30 120W HP	120 W
911401775903	BVP374 48LED 27K 220V 30 DMX 120W HP	120 W
911401775913	BVP374 48LED 27K 220V 45 120W HP	120 W
911401775923	BVP374 48LED 27K 220V 45 DMX 120W HP	120 W
911401775933	BVP374 48LED 27K 220V 60 120W HP	120 W
911401775943	BVP374 48LED 27K 220V 60 DMX 120W HP	120 W
911401775953	BVP374 48LED 30K 220V 10 120W HP	120 W
911401775963	BVP374 48LED 30K 220V 10 DMX 120W HP	120 W
911401775973	BVP374 48LED 30K 220V 15 120W HP	120 W
911401775983	BVP374 48LED 30K 220V 15 DMX 120W HP	120 W
911401775993	BVP374 48LED 30K 220V 30 120W HP	120 W
911401776003	BVP374 48LED 30K 220V 30 DMX 120W HP	120 W
911401776013	BVP374 48LED 30K 220V 45 120W HP	120 W
911401776023	BVP374 48LED 30K 220V 45 DMX 120W HP	120 W
911401776033	BVP374 48LED 30K 220V 60 120W HP	120 W
911401776043	BVP374 48LED 30K 220V 60 DMX 120W HP	120 W
911401776053	BVP374 48LED 40K 220V 10 120W HP	120 W
911401776063	BVP374 48LED 40K 220V 10 DMX 120W HP	120 W
911401776073	BVP374 48LED 40K 220V 15 120W HP	120 W
911401776083	BVP374 48LED 40K 220V 15 DMX 120W HP	120 W
911401776093	BVP374 48LED 40K 220V 30 120W HP	120 W
911401776103	BVP374 48LED 40K 220V 30 DMX 120W HP	120 W
911401776113	BVP374 48LED 40K 220V 45 120W HP	120 W
911401776123	BVP374 48LED 40K 220V 45 DMX 120W HP	120 W
911401776133	BVP374 48LED 40K 220V 60 120W HP	120 W
911401776143	BVP374 48LED 40K 220V 60 DMX 120W HP	120 W
911401776153	BVP374 48LED RGB 220V 10 DMX 120W HP	120 W
911401776163	BVP374 48LED RGB 220V 15 DMX 120W HP	120 W
911401776173	BVP374 48LED RGB 220V 30 DMX 120W HP	120 W
911401776183	BVP374 48LED RGB 220V 45 DMX 120W HP	120 W
911401776193	BVP374 48LED RGB 220V 60 DMX 120W HP	120 W
911401776203	BVP374 48LED RGBNW 220V 10 DMX 120W HP	120 W
911401776213	BVP374 48LED RGBNW 220V 15 DMX 120W HP	120 W
911401776223	BVP374 48LED RGBNW 220V 30 DMX 120W HP	120 W
911401776233	BVP374 48LED RGBNW 220V 45 DMX 120W HP	120 W
911401776243	BVP374 48LED RGBNW 220V 60 DMX 120W HP	120 W

Order Code	Full Product Name	Power Consumption
911401776253	BVP374 48LED RGBWW 220V 10 DMX 120W HP	120 W
911401776263	BVP374 48LED RGBWW 220V 15 DMX 120W HP	120 W
911401776273	BVP374 48LED RGBWW 220V 30 DMX 120W HP	120 W
911401776283	BVP374 48LED RGBWW 220V 45 DMX 120W HP	120 W
911401776293	BVP374 48LED RGBWW 220V 60 DMX 120W HP	120 W
911401776303	BVP374 60LED 27K 220V 10 150W HP	150 W
911401776313	BVP374 60LED 27K 220V 10 DMX 150W HP	150 W
911401776323	BVP374 60LED 27K 220V 15 150W HP	150 W
911401776333	BVP374 60LED 27K 220V 15 DMX 150W HP	150 W
911401776343	BVP374 60LED 27K 220V 30 150W HP	150 W
911401776353	BVP374 60LED 27K 220V 30 DMX 150W HP	150 W
911401776363	BVP374 60LED 27K 220V 45 150W HP	150 W
911401776373	BVP374 60LED 27K 220V 45 DMX 150W HP	150 W
911401776383	BVP374 60LED 27K 220V 60 150W HP	150 W
911401776393	BVP374 60LED 27K 220V 60 DMX 150W HP	150 W
911401776403	BVP374 60LED 30K 220V 10 150W HP	150 W
911401776413	BVP374 60LED 30K 220V 10 DMX 150W HP	150 W
911401776423	BVP374 60LED 30K 220V 15 150W HP	150 W
911401776433	BVP374 60LED 30K 220V 15 DMX 150W HP	150 W
911401776443	BVP374 60LED 30K 220V 30 150W HP	150 W
911401776453	BVP374 60LED 30K 220V 30 DMX 150W HP	150 W
911401776463	BVP374 60LED 30K 220V 45 150W HP	150 W
911401776473	BVP374 60LED 30K 220V 45 DMX 150W HP	150 W
911401776483	BVP374 60LED 30K 220V 60 150W HP	150 W
911401776493	BVP374 60LED 30K 220V 60 DMX 150W HP	150 W
911401776503	BVP374 60LED 40K 220V 10 150W HP	150 W
911401776513	BVP374 60LED 40K 220V 10 DMX 150W HP	150 W
911401776523	BVP374 60LED 40K 220V 15 150W HP	150 W
911401776533	BVP374 60LED 40K 220V 15 DMX 150W HP	150 W
911401776543	BVP374 60LED 40K 220V 30 150W HP	150 W
911401776553	BVP374 60LED 40K 220V 30 DMX 150W HP	150 W
911401776563	BVP374 60LED 40K 220V 45 150W HP	150 W
911401776573	BVP374 60LED 40K 220V 45 DMX 150W HP	150 W
911401776583	BVP374 60LED 40K 220V 60 150W HP	150 W
911401776593	BVP374 60LED 40K 220V 60 DMX 150W HP	150 W
911401776603	BVP374 60LED RGB 220V 10 DMX 150W HP	150 W
911401776613	BVP374 60LED RGB 220V 15 DMX 150W HP	150 W
911401776623	BVP374 60LED RGB 220V 30 DMX 150W HP	150 W
911401776633	BVP374 60LED RGB 220V 45 DMX 150W HP	150 W
911401776643	BVP374 60LED RGB 220V 60 DMX 150W HP	150 W
911401776653	BVP374 60LED RGBNW 220V 10 DMX 150W HP	150 W
911401776663	BVP374 60LED RGBNW 220V 15 DMX 150W HP	150 W
911401776673	BVP374 60LED RGBNW 220V 30 DMX 150W HP	150 W
911401776683	BVP374 60LED RGBNW 220V 45 DMX 150W HP	150 W
911401776693	BVP374 60LED RGBNW 220V 60 DMX 150W HP	150 W
911401776703	BVP374 60LED RGBWW 220V 10 DMX 150W HP	150 W
911401776713	BVP374 60LED RGBWW 220V 15 DMX 150W HP	150 W
911401776723	BVP374 60LED RGBWW 220V 30 DMX 150W HP	150 W
911401776733	BVP374 60LED RGBWW 220V 45 DMX 150W HP	150 W
911401776743	BVP374 60LED RGBWW 220V 60 DMX 150W HP	150 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401773603	BVP371 12LED 27K 220V 10 24W HE	No
911401773613	BVP371 12LED 27K 220V 10 DMX 24W HE	Yes
911401773623	BVP371 12LED 27K 220V 15 24W HE	No
911401773633	BVP371 12LED 27K 220V 15 DMX 24W HE	Yes
911401773643	BVP371 12LED 27K 220V 30 24W HE	No
911401773653	BVP371 12LED 27K 220V 30 DMX 24W HE	Yes
911401773663	BVP371 12LED 27K 220V 45 24W HE	No
911401773673	BVP371 12LED 27K 220V 45 DMX 24W HE	Yes
911401773683	BVP371 12LED 27K 220V 60 24W HE	No
911401773693	BVP371 12LED 27K 220V 60 DMX 24W HE	Yes
911401773703	BVP371 12LED 30K 220V 10 24W HE	No
911401773713	BVP371 12LED 30K 220V 10 DMX 24W HE	Yes
911401773723	BVP371 12LED 30K 220V 15 24W HE	No
911401773733	BVP371 12LED 30K 220V 15 DMX 24W HE	Yes
911401773743	BVP371 12LED 30K 220V 30 24W HE	No
911401773753	BVP371 12LED 30K 220V 30 DMX 24W HE	Yes
911401773763	BVP371 12LED 30K 220V 45 24W HE	No
911401773773	BVP371 12LED 30K 220V 45 DMX 24W HE	Yes
911401773783	BVP371 12LED 30K 220V 60 24W HE	No
911401773793	BVP371 12LED 30K 220V 60 DMX 24W HE	Yes
911401773803	BVP371 12LED 40K 220V 10 24W HE	No
911401773813	BVP371 12LED 40K 220V 10 DMX 24W HE	Yes
911401773823	BVP371 12LED 40K 220V 15 24W HE	No
911401773833	BVP371 12LED 40K 220V 15 DMX 24W HE	Yes
911401773843	BVP371 12LED 40K 220V 30 24W HE	No
911401773853	BVP371 12LED 40K 220V 30 DMX 24W HE	Yes
911401773863	BVP371 12LED 40K 220V 45 24W HE	No
911401773873	BVP371 12LED 40K 220V 45 DMX 24W HE	Yes
911401773883	BVP371 12LED 40K 220V 60 24W HE	No
911401773893	BVP371 12LED 40K 220V 60 DMX 24W HE	Yes
911401773903	BVP371 12LED RGB 220V 10 DMX 24W HE	Yes
911401773913	BVP371 12LED RGB 220V 15 DMX 24W HE	Yes
911401773923	BVP371 12LED RGB 220V 30 DMX 24W HE	Yes
911401773933	BVP371 12LED RGB 220V 45 DMX 24W HE	Yes
911401773943	BVP371 12LED RGB 220V 60 DMX 24W HE	Yes
911401773953	BVP371 12LED RGBNW 220V 10 DMX 24W HE	Yes
911401773963	BVP371 12LED RGBNW 220V 15 DMX 24W HE	Yes
911401773973	BVP371 12LED RGBNW 220V 30 DMX 24W HE	Yes
911401773983	BVP371 12LED RGBNW 220V 45 DMX 24W HE	Yes
911401773993	BVP371 12LED RGBNW 220V 60 DMX 24W HE	Yes
911401774003	BVP371 12LED RGBWW 220V 10 DMX 24W HE	Yes
911401774013	BVP371 12LED RGBWW 220V 15 DMX 24W HE	Yes
911401774023	BVP371 12LED RGBWW 220V 30 DMX 24W HE	Yes
911401774033	BVP371 12LED RGBWW 220V 45 DMX 24W HE	Yes
911401774043	BVP371 12LED RGBWW 220V 60 DMX 24W HE	Yes
911401774053	BVP372 15LED RGB 220V 10 DMX 40W HP	Yes
911401774063	BVP372 15LED RGB 220V 15 DMX 40W HP	Yes
911401774073	BVP372 15LED RGB 220V 30 DMX 40W HP	Yes
911401774083	BVP372 15LED RGB 220V 45 DMX 40W HP	Yes
911401774093	BVP372 15LED RGB 220V 60 DMX 40W HP	Yes
911401774103	BVP372 16LED 27K 220V 10 40W HP	No
911401774113	BVP372 16LED 27K 220V 10 DMX 40W HP	Yes

Order Code	Full Product Name	Dimmable
911401774123	BVP372 16LED 27K 220V 15 40W HP	No
911401774133	BVP372 16LED 27K 220V 15 DMX 40W HP	Yes
911401774143	BVP372 16LED 27K 220V 30 40W HP	No
911401774153	BVP372 16LED 27K 220V 30 DMX 40W HP	Yes
911401774163	BVP372 16LED 27K 220V 45 40W HP	No
911401774173	BVP372 16LED 27K 220V 45 DMX 40W HP	Yes
911401774183	BVP372 16LED 27K 220V 60 40W HP	No
911401774193	BVP372 16LED 27K 220V 60 DMX 40W HP	Yes
911401774203	BVP372 16LED 30K 220V 10 40W HP	No
911401774213	BVP372 16LED 30K 220V 10 DMX 40W HP	Yes
911401774223	BVP372 16LED 30K 220V 15 40W HP	No
911401774233	BVP372 16LED 30K 220V 15 DMX 40W HP	Yes
911401774243	BVP372 16LED 30K 220V 30 40W HP	No
911401774253	BVP372 16LED 30K 220V 30 DMX 40W HP	Yes
911401774263	BVP372 16LED 30K 220V 45 40W HP	No
911401774273	BVP372 16LED 30K 220V 45 DMX 40W HP	Yes
911401774283	BVP372 16LED 30K 220V 60 40W HP	No
911401774293	BVP372 16LED 30K 220V 60 DMX 40W HP	Yes
911401774303	BVP372 16LED 40K 220V 10 40W HP	No
911401774313	BVP372 16LED 40K 220V 10 DMX 40W HP	Yes
911401774323	BVP372 16LED 40K 220V 15 40W HP	No
911401774333	BVP372 16LED 40K 220V 15 DMX 40W HP	Yes
911401774343	BVP372 16LED 40K 220V 30 40W HP	No
911401774353	BVP372 16LED 40K 220V 30 DMX 40W HP	Yes
911401774363	BVP372 16LED 40K 220V 45 40W HP	No
911401774373	BVP372 16LED 40K 220V 45 DMX 40W HP	Yes
911401774383	BVP372 16LED 40K 220V 60 40W HP	No
911401774393	BVP372 16LED 40K 220V 60 DMX 40W HP	Yes
911401774403	BVP372 16LED RGBNW 220V 10 DMX 40W HP	Yes
911401774413	BVP372 16LED RGBNW 220V 15 DMX 40W HP	Yes
911401774423	BVP372 16LED RGBNW 220V 30 DMX 40W HP	Yes
911401774433	BVP372 16LED RGBNW 220V 45 DMX 40W HP	Yes
911401774443	BVP372 16LED RGBNW 220V 60 DMX 40W HP	Yes
911401774453	BVP372 16LED RGBWW 220V 10 DMX 40W HP	Yes
911401774463	BVP372 16LED RGBWW 220V 15 DMX 40W HP	Yes
911401774473	BVP372 16LED RGBWW 220V 30 DMX 40W HP	Yes
911401774483	BVP372 16LED RGBWW 220V 45 DMX 40W HP	Yes
911401774493	BVP372 16LED RGBWW 220V 60 DMX 40W HP	Yes
911401774503	BVP372 18LED 27K 220V 10 50W HP	No
911401774513	BVP372 18LED 27K 220V 10 DMX 50W HP	Yes
911401774523	BVP372 18LED 27K 220V 15 50W HP	No
911401774533	BVP372 18LED 27K 220V 15 DMX 50W HP	Yes
911401774543	BVP372 18LED 27K 220V 30 50W HP	No
911401774553	BVP372 18LED 27K 220V 30 DMX 50W HP	Yes
911401774563	BVP372 18LED 27K 220V 45 50W HP	No
911401774573	BVP372 18LED 27K 220V 45 DMX 50W HP	Yes
911401774583	BVP372 18LED 27K 220V 60 50W HP	No
911401774593	BVP372 18LED 27K 220V 60 DMX 50W HP	Yes
911401774603	BVP372 18LED 30K 220V 10 50W HP	No
911401774613	BVP372 18LED 30K 220V 10 DMX 50W HP	Yes
911401774623	BVP372 18LED 30K 220V 15 50W HP	No
911401774633	BVP372 18LED 30K 220V 15 DMX 50W HP	Yes

Order Code	Full Product Name	Dimmable
911401774643	BVP372 18LED 30K 220V 30 50W HP	No
911401774653	BVP372 18LED 30K 220V 30 DMX 50W HP	Yes
911401774663	BVP372 18LED 30K 220V 45 50W HP	No
911401774673	BVP372 18LED 30K 220V 45 DMX 50W HP	Yes
911401774683	BVP372 18LED 30K 220V 60 50W HP	No
911401774693	BVP372 18LED 30K 220V 60 DMX 50W HP	Yes
911401774703	BVP372 18LED 40K 220V 10 50W HP	No
911401774713	BVP372 18LED 40K 220V 10 DMX 50W HP	Yes
911401774723	BVP372 18LED 40K 220V 15 50W HP	No
911401774733	BVP372 18LED 40K 220V 15 DMX 50W HP	Yes
911401774743	BVP372 18LED 40K 220V 30 50W HP	No
911401774753	BVP372 18LED 40K 220V 30 DMX 50W HP	Yes
911401774763	BVP372 18LED 40K 220V 45 50W HP	No
911401774773	BVP372 18LED 40K 220V 45 DMX 50W HP	Yes
911401774783	BVP372 18LED 40K 220V 60 50W HP	No
911401774793	BVP372 18LED 40K 220V 60 DMX 50W HP	Yes
911401774803	BVP372 18LED RGB 220V 10 DMX 50W HP	Yes
911401774813	BVP372 18LED RGB 220V 15 DMX 50W HP	Yes
911401774823	BVP372 18LED RGB 220V 30 DMX 50W HP	Yes
911401774833	BVP372 18LED RGB 220V 45 DMX 50W HP	Yes
911401774843	BVP372 18LED RGB 220V 60 DMX 50W HP	Yes
911401774853	BVP372 20LED RGBNW 220V 10 DMX 50W HP	Yes
911401774863	BVP372 20LED RGBNW 220V 15 DMX 50W HP	Yes
911401774873	BVP372 20LED RGBNW 220V 30 DMX 50W HP	Yes
911401774883	BVP372 20LED RGBNW 220V 45 DMX 50W HP	Yes
911401774893	BVP372 20LED RGBNW 220V 60 DMX 50W HP	Yes
911401774903	BVP372 20LED RGBWW 220V 10 DMX 50W HP	Yes
911401774913	BVP372 20LED RGBWW 220V 15 DMX 50W HP	Yes
911401774923	BVP372 20LED RGBWW 220V 30 DMX 50W HP	Yes
911401774933	BVP372 20LED RGBWW 220V 45 DMX 50W HP	Yes
911401774943	BVP372 20LED RGBWW 220V 60 DMX 50W HP	Yes
911401774953	BVP373 30LED 27K 220V 10 80W HP	No
911401774963	BVP373 30LED 27K 220V 10 DMX 80W HP	Yes
911401774973	BVP373 30LED 27K 220V 15 80W HP	No
911401774983	BVP373 30LED 27K 220V 15 DMX 80W HP	Yes
911401774993	BVP373 30LED 27K 220V 30 80W HP	No
911401775003	BVP373 30LED 27K 220V 30 DMX 80W HP	Yes
911401775013	BVP373 30LED 27K 220V 45 80W HP	No
911401775023	BVP373 30LED 27K 220V 45 DMX 80W HP	Yes
911401775033	BVP373 30LED 27K 220V 60 80W HP	No
911401775043	BVP373 30LED 27K 220V 60 DMX 80W HP	Yes
911401775053	BVP373 30LED 30K 220V 10 80W HP	No
911401775063	BVP373 30LED 30K 220V 10 DMX 80W HP	Yes
911401775073	BVP373 30LED 30K 220V 15 80W HP	No
911401775083	BVP373 30LED 30K 220V 15 DMX 80W HP	Yes
911401775093	BVP373 30LED 30K 220V 30 80W HP	No
911401775103	BVP373 30LED 30K 220V 30 DMX 80W HP	Yes
911401775113	BVP373 30LED 30K 220V 45 80W HP	No
911401775123	BVP373 30LED 30K 220V 45 DMX 80W HP	Yes
911401775133	BVP373 30LED 30K 220V 60 80W HP	No
911401775143	BVP373 30LED 30K 220V 60 DMX 80W HP	Yes
911401775153	BVP373 30LED 40K 220V 10 80W HP	No

Order Code	Full Product Name	Dimmable
911401775163	BVP373 30LED 40K 220V 10 DMX 80W HP	Yes
911401775173	BVP373 30LED 40K 220V 15 80W HP	No
911401775183	BVP373 30LED 40K 220V 15 DMX 80W HP	Yes
911401775193	BVP373 30LED 40K 220V 30 80W HP	No
911401775203	BVP373 30LED 40K 220V 30 DMX 80W HP	Yes
911401775213	BVP373 30LED 40K 220V 45 80W HP	No
911401775223	BVP373 30LED 40K 220V 45 DMX 80W HP	Yes
911401775233	BVP373 30LED 40K 220V 60 80W HP	No
911401775243	BVP373 30LED 40K 220V 60 DMX 80W HP	Yes
911401775253	BVP373 30LED RGB 220V 10 DMX 80W HP	Yes
911401775263	BVP373 30LED RGB 220V 15 DMX 80W HP	Yes
911401775273	BVP373 30LED RGB 220V 30 DMX 80W HP	Yes
911401775283	BVP373 30LED RGB 220V 45 DMX 80W HP	Yes
911401775293	BVP373 30LED RGB 220V 60 DMX 80W HP	Yes
911401775303	BVP373 32LED RGBNW 220V 10 DMX 80W HP	Yes
911401775313	BVP373 32LED RGBNW 220V 15 DMX 80W HP	Yes
911401775323	BVP373 32LED RGBNW 220V 30 DMX 80W HP	Yes
911401775333	BVP373 32LED RGBNW 220V 45 DMX 80W HP	Yes
911401775343	BVP373 32LED RGBNW 220V 60 DMX 80W HP	Yes
911401775353	BVP373 32LED RGBWW 220V 10 DMX 80W HP	Yes
911401775363	BVP373 32LED RGBWW 220V 15 DMX 80W HP	Yes
911401775373	BVP373 32LED RGBWW 220V 30 DMX 80W HP	Yes
911401775383	BVP373 32LED RGBWW 220V 45 DMX 80W HP	Yes
911401775393	BVP373 32LED RGBWW 220V 60 DMX 80W HP	Yes
911401775403	BVP373 36LED 27K 220V 10 100W HP	No
911401775413	BVP373 36LED 27K 220V 10 DMX 100W HP	Yes
911401775423	BVP373 36LED 27K 220V 15 100W HP	No
911401775433	BVP373 36LED 27K 220V 15 DMX 100W HP	Yes
911401775443	BVP373 36LED 27K 220V 30 100W HP	No
911401775453	BVP373 36LED 27K 220V 30 DMX 100W HP	Yes
911401775463	BVP373 36LED 27K 220V 45 100W HP	No
911401775473	BVP373 36LED 27K 220V 45 DMX 100W HP	Yes
911401775483	BVP373 36LED 27K 220V 60 100W HP	No
911401775493	BVP373 36LED 27K 220V 60 DMX 100W HP	Yes
911401775503	BVP373 36LED 30K 220V 10 100W HP	No
911401775513	BVP373 36LED 30K 220V 10 DMX 100W HP	Yes
911401775523	BVP373 36LED 30K 220V 15 100W HP	No
911401775533	BVP373 36LED 30K 220V 15 DMX 100W HP	Yes
911401775543	BVP373 36LED 30K 220V 30 100W HP	No
911401775553	BVP373 36LED 30K 220V 30 DMX 100W HP	Yes
911401775563	BVP373 36LED 30K 220V 45 100W HP	No
911401775573	BVP373 36LED 30K 220V 45 DMX 100W HP	Yes
911401775583	BVP373 36LED 30K 220V 60 100W HP	No
911401775593	BVP373 36LED 30K 220V 60 DMX 100W HP	Yes
911401775603	BVP373 36LED 40K 220V 10 100W HP	No
911401775613	BVP373 36LED 40K 220V 10 DMX 100W HP	Yes
911401775623	BVP373 36LED 40K 220V 15 100W HP	No
911401775633	BVP373 36LED 40K 220V 15 DMX 100W HP	Yes
911401775643	BVP373 36LED 40K 220V 30 100W HP	No
911401775653	BVP373 36LED 40K 220V 30 DMX 100W HP	Yes
911401775663	BVP373 36LED 40K 220V 45 100W HP	No
911401775673	BVP373 36LED 40K 220V 45 DMX 100W HP	Yes

Order Code	Full Product Name	Dimmable
911401775683	BVP373 36LED 40K 220V 60 100W HP	No
911401775693	BVP373 36LED 40K 220V 60 DMX 100W HP	Yes
911401775703	BVP373 36LED RGB 220V 10 DMX 100W HP	Yes
911401775713	BVP373 36LED RGB 220V 15 DMX 100W HP	Yes
911401775723	BVP373 36LED RGB 220V 30 DMX 100W HP	Yes
911401775733	BVP373 36LED RGB 220V 45 DMX 100W HP	Yes
911401775743	BVP373 36LED RGB 220V 60 DMX 100W HP	Yes
911401775753	BVP373 36LED RGBNW 220V 10 DMX 100W HP	Yes
911401775763	BVP373 36LED RGBNW 220V 15 DMX 100W HP	Yes
911401775773	BVP373 36LED RGBNW 220V 30 DMX 100W HP	Yes
911401775783	BVP373 36LED RGBNW 220V 45 DMX 100W HP	Yes
911401775793	BVP373 36LED RGBNW 220V 60 DMX 100W HP	Yes
911401775803	BVP373 36LED RGBWW 220V 10 DMX 100W HP	Yes
911401775813	BVP373 36LED RGBWW 220V 15 DMX 100W HP	Yes
911401775823	BVP373 36LED RGBWW 220V 30 DMX 100W HP	Yes
911401775833	BVP373 36LED RGBWW 220V 45 DMX 100W HP	Yes
911401775843	BVP373 36LED RGBWW 220V 60 DMX 100W HP	Yes
911401775853	BVP374 48LED 27K 220V 10 120W HP	No
911401775863	BVP374 48LED 27K 220V 10 DMX 120W HP	Yes
911401775873	BVP374 48LED 27K 220V 15 120W HP	No
911401775883	BVP374 48LED 27K 220V 15 DMX 120W HP	Yes
911401775893	BVP374 48LED 27K 220V 30 120W HP	No
911401775903	BVP374 48LED 27K 220V 30 DMX 120W HP	Yes
911401775913	BVP374 48LED 27K 220V 45 120W HP	No
911401775923	BVP374 48LED 27K 220V 45 DMX 120W HP	Yes
911401775933	BVP374 48LED 27K 220V 60 120W HP	No
911401775943	BVP374 48LED 27K 220V 60 DMX 120W HP	Yes
911401775953	BVP374 48LED 30K 220V 10 120W HP	No
911401775963	BVP374 48LED 30K 220V 10 DMX 120W HP	Yes
911401775973	BVP374 48LED 30K 220V 15 120W HP	No
911401775983	BVP374 48LED 30K 220V 15 DMX 120W HP	Yes
911401775993	BVP374 48LED 30K 220V 30 120W HP	No
911401776003	BVP374 48LED 30K 220V 30 DMX 120W HP	Yes
911401776013	BVP374 48LED 30K 220V 45 120W HP	No
911401776023	BVP374 48LED 30K 220V 45 DMX 120W HP	Yes
911401776033	BVP374 48LED 30K 220V 60 120W HP	No
911401776043	BVP374 48LED 30K 220V 60 DMX 120W HP	Yes
911401776053	BVP374 48LED 40K 220V 10 120W HP	No
911401776063	BVP374 48LED 40K 220V 10 DMX 120W HP	Yes
911401776073	BVP374 48LED 40K 220V 15 120W HP	No
911401776083	BVP374 48LED 40K 220V 15 DMX 120W HP	Yes
911401776093	BVP374 48LED 40K 220V 30 120W HP	No
911401776103	BVP374 48LED 40K 220V 30 DMX 120W HP	Yes
911401776113	BVP374 48LED 40K 220V 45 120W HP	No
911401776123	BVP374 48LED 40K 220V 45 DMX 120W HP	Yes
911401776133	BVP374 48LED 40K 220V 60 120W HP	No
911401776143	BVP374 48LED 40K 220V 60 DMX 120W HP	Yes
911401776153	BVP374 48LED RGB 220V 10 DMX 120W HP	Yes
911401776163	BVP374 48LED RGB 220V 15 DMX 120W HP	Yes
911401776173	BVP374 48LED RGB 220V 30 DMX 120W HP	Yes
911401776183	BVP374 48LED RGB 220V 45 DMX 120W HP	Yes
911401776193	BVP374 48LED RGB 220V 60 DMX 120W HP	Yes

Order Code	Full Product Name	Dimmable
911401776203	BVP374 48LED RGBNW 220V 10 DMX 120W HP	Yes
911401776213	BVP374 48LED RGBNW 220V 15 DMX 120W HP	Yes
911401776223	BVP374 48LED RGBNW 220V 30 DMX 120W HP	Yes
911401776233	BVP374 48LED RGBNW 220V 45 DMX 120W HP	Yes
911401776243	BVP374 48LED RGBNW 220V 60 DMX 120W HP	Yes
911401776253	BVP374 48LED RGBWW 220V 10 DMX 120W HP	Yes
911401776263	BVP374 48LED RGBWW 220V 15 DMX 120W HP	Yes
911401776273	BVP374 48LED RGBWW 220V 30 DMX 120W HP	Yes
911401776283	BVP374 48LED RGBWW 220V 45 DMX 120W HP	Yes
911401776293	BVP374 48LED RGBWW 220V 60 DMX 120W HP	Yes
911401776303	BVP374 60LED 27K 220V 10 150W HP	No
911401776313	BVP374 60LED 27K 220V 10 DMX 150W HP	Yes
911401776323	BVP374 60LED 27K 220V 15 150W HP	No
911401776333	BVP374 60LED 27K 220V 15 DMX 150W HP	Yes
911401776343	BVP374 60LED 27K 220V 30 150W HP	No
911401776353	BVP374 60LED 27K 220V 30 DMX 150W HP	Yes
911401776363	BVP374 60LED 27K 220V 45 150W HP	No
911401776373	BVP374 60LED 27K 220V 45 DMX 150W HP	Yes
911401776383	BVP374 60LED 27K 220V 60 150W HP	No
911401776393	BVP374 60LED 27K 220V 60 DMX 150W HP	Yes
911401776403	BVP374 60LED 30K 220V 10 150W HP	No
911401776413	BVP374 60LED 30K 220V 10 DMX 150W HP	Yes
911401776423	BVP374 60LED 30K 220V 15 150W HP	No
911401776433	BVP374 60LED 30K 220V 15 DMX 150W HP	Yes
911401776443	BVP374 60LED 30K 220V 30 150W HP	No
911401776453	BVP374 60LED 30K 220V 30 DMX 150W HP	Yes
911401776463	BVP374 60LED 30K 220V 45 150W HP	No
911401776473	BVP374 60LED 30K 220V 45 DMX 150W HP	Yes
911401776483	BVP374 60LED 30K 220V 60 150W HP	No
911401776493	BVP374 60LED 30K 220V 60 DMX 150W HP	Yes
911401776503	BVP374 60LED 40K 220V 10 150W HP	No
911401776513	BVP374 60LED 40K 220V 10 DMX 150W HP	Yes
911401776523	BVP374 60LED 40K 220V 15 150W HP	No
911401776533	BVP374 60LED 40K 220V 15 DMX 150W HP	Yes
911401776543	BVP374 60LED 40K 220V 30 150W HP	No
911401776553	BVP374 60LED 40K 220V 30 DMX 150W HP	Yes
911401776563	BVP374 60LED 40K 220V 45 150W HP	No
911401776573	BVP374 60LED 40K 220V 45 DMX 150W HP	Yes
911401776583	BVP374 60LED 40K 220V 60 150W HP	No
911401776593	BVP374 60LED 40K 220V 60 DMX 150W HP	Yes
911401776603	BVP374 60LED RGB 220V 10 DMX 150W HP	Yes
911401776613	BVP374 60LED RGB 220V 15 DMX 150W HP	Yes
911401776623	BVP374 60LED RGB 220V 30 DMX 150W HP	Yes
911401776633	BVP374 60LED RGB 220V 45 DMX 150W HP	Yes
911401776643	BVP374 60LED RGB 220V 60 DMX 150W HP	Yes
911401776653	BVP374 60LED RGBNW 220V 10 DMX 150W HP	Yes
911401776663	BVP374 60LED RGBNW 220V 15 DMX 150W HP	Yes
911401776673	BVP374 60LED RGBNW 220V 30 DMX 150W HP	Yes
911401776683	BVP374 60LED RGBNW 220V 45 DMX 150W HP	Yes
911401776693	BVP374 60LED RGBNW 220V 60 DMX 150W HP	Yes
911401776703	BVP374 60LED RGBWW 220V 10 DMX 150W HP	Yes
911401776713	BVP374 60LED RGBWW 220V 15 DMX 150W HP	Yes

UniFlood C Pro

Order Code	Full Product Name	Dimmable
911401776723	BVP374 60LED RGBWW 220V 30 DMX 150W HP	Yes
911401776733	BVP374 60LED RGBWW 220V 45 DMX 150W HP	Yes

Order Code	Full Product Name	Dimmable
911401776743	BVP374 60LED RGBWW 220V 60 DMX 150W HP	Yes

