



GameVision : the 1:1 retrofit of conventional floodlights for recreational sports.

GameVision

GameVision is a simple, easy to choose led floodlight to replace conventional installations in municipal football stadiums, hockey fields... Its specific hooded shape design ensures a limited perception of light outside the field of play, hence a better comfort for people living nearby, but also favors dark skies. The light distribution is maintained all along the product lifetime as the reflector inside is protected against pollution and corrosion.

Benefits

- 1:1 retrofit of conventional floodlights in recreational sports
- Easy to choose
- Low glare perception
- Favors dark skies

Features

- 1 "do-it-all" light distribution
- 2 levels of light output
- Weight and SCx similar to OptiVision HID (MVP507)
- Low to 0 tilt angle in application


Application

- Arena and Sports

Versions











BVP440 GameVision HGB with louvre PP



BVP440 GameVision BV with louvre PP

Dimensional drawing



Product details



BVP440 GameVision tilt aiming DP

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Luminaire light beam spread	-
Color rendering index (CRI)	70
Optic type outdoor	Asymmetrical
Upward light output ratio	0
Operating and Electrical	
Surge Protection (Common/ Differential)	Surge protection level until 10 kV differential mode and 10 kV common mode
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Aluminum
Mech. impact protection code	IK08
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	10°
Approval and Application	
CE mark	Yes
Flammability mark	-
Product Data	
Product family code	BVP440

General Information

Order Code	Full Product Name	Lamp family code	Service tag
912300060576	BVP440 LED1650/757 DW HGB FG PSD ALU D9	LED1650	-
912300060577	BVP440 LED1150/757 DW HGB FG PSD ALU D9	LED1300	-
912300060578	BVP440 LED1650/757 DW HGB L FG PSD ALU	LED1650	-
912300060579	BVP440 LED1150/757 DW HGB L FG PSD ALU	LED1300	-
912300060574	BVP440 LED1650/757 DW BV L FG PSD ALU D9	LED1650	Yes
912300060575	BVP440 LED1150/757 DW BV L FG PSD ALU D9	LED1300	Yes
912300060572	BVP440 LED1650/757 DW BV FG PSD ALU D9	LED1650	Yes
912300060573	BVP440 LED1150/757 DW BV FG PSD ALU D9	LED1300	Yes
912300060749	BVP440 LED1565/730 DW BV GCA PSM ALU D28	LED1650	-
912300060750	BVP440 LED1565/730 DW BV GCA PSU ALU	LED1650	-
912300060751	BVP440 LED1650/740 DW BV GCA PSM ALU D28	LED1650	-
912300060752	BVP440 LED1650/740 DW BV GCA PSU ALU	LED1650	-

Light Technical

Order Code	Full Product Name	Light	Correlated	Luminous
		source color	Color Temperature (Nom)	
912300060576	BVP440 LED1650/757 DW HGB FG PSD ALU D9	757 cool white	5700 K	142,972 lm
912300060577	BVP440 LED1150/757 DW HGB FG PSD ALU D9	757 cool white	5700 K	110,769 lm
912300060578	BVP440 LED1650/757 DW HGB L FG PSD ALU	757 cool white	5700 K	140,661 lm
912300060579	BVP440 LED1150/757 DW HGB L FG PSD ALU	757 cool white	5700 K	108,978 lm
912300060574	BVP440 LED1650/757 DW BV L FG PSD ALU D9	757 cool white	5700 K	140,661 lm
912300060575	BVP440 LED1150/757 DW BV L FG PSD ALU D9	757 cool white	5700 K	108,978 lm
912300060572	BVP440 LED1650/757 DW BV FG PSD ALU D9	757 cool white	5700 K	142,972 lm

Order Code	Full Product Name	Light	Correlated	Luminous
		source color	Color Temperature (Nom)	
912300060573	BVP440 LED1150/757 DW BV FG PSD ALU D9	757 cool white	5700 K	110,769 lm
912300060749	BVP440 LED1565/730 DW BV GCA PSM ALU D28	730 warm white	3000 K	138,711 lm
912300060750	BVP440 LED1565/730 DW BV GCA PSU ALU	730 warm white	3000 K	138,711 lm
912300060751	BVP440 LED1650/740 DW BV GCA PSM ALU D28	740 neutral white	4000 K	145,004 lm
912300060752	BVP440 LED1650/740 DW BV GCA PSU ALU	740 neutral white	4000 K	145,004 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
912300060576	BVP440 LED1650/757 DW HGB FG PSD ALU D9	1,000 W
912300060577	BVP440 LED1150/757 DW HGB FG PSD ALU D9	736 W
912300060578	BVP440 LED1650/757 DW HGB L FG PSD ALU	1,000 W
912300060579	BVP440 LED1150/757 DW HGB L FG PSD ALU	736 W
912300060574	BVP440 LED1650/757 DW BV L FG PSD ALU D9	1,000 W
912300060575	BVP440 LED1150/757 DW BV L FG PSD ALU D9	736 W


Order Code	Full Product Name	Power Consumption
912300060572	BVP440 LED1650/757 DW BV FG PSD ALU D9	1,000 W
912300060573	BVP440 LED1150/757 DW BV FG PSD ALU D9	736 W
912300060749	BVP440 LED1565/730 DW BV GCA PSM ALU D28	985 W
912300060750	BVP440 LED1565/730 DW BV GCA PSU ALU	985 W
912300060751	BVP440 LED1650/740 DW BV GCA PSM ALU D28	1,000 W
912300060752	BVP440 LED1650/740 DW BV GCA PSU ALU	1,000 W

Controls and Dimming


Order Code	Full Product Name	Dimmable
912300060576	BVP440 LED1650/757 DW HGB FG PSD ALU D9	Yes
912300060577	BVP440 LED1150/757 DW HGB FG PSD ALU D9	Yes
912300060578	BVP440 LED1650/757 DW HGB L FG PSD ALU	Yes
912300060579	BVP440 LED1150/757 DW HGB L FG PSD ALU	Yes
912300060574	BVP440 LED1650/757 DW BV L FG PSD ALU D9	Yes
912300060575	BVP440 LED1150/757 DW BV L FG PSD ALU D9	Yes

Order Code	Full Product Name	Dimmable
912300060572	BVP440 LED1650/757 DW BV FG PSD ALU D9	Yes
912300060573	BVP440 LED1150/757 DW BV FG PSD ALU D9	Yes
912300060749	BVP440 LED1565/730 DW BV GCA PSM ALU D28	Yes
912300060750	BVP440 LED1565/730 DW BV GCA PSU ALU	No
912300060751	BVP440 LED1650/740 DW BV GCA PSM ALU D28	Yes
912300060752	BVP440 LED1650/740 DW BV GCA PSU ALU	No


Polar Wide Diagrams




Polar Normal (separate) - BVP440I - 912300060576




Polar Normal (separate) - BVP440I - 912300060578




Polar Normal (separate) - BVP440I - 912300060579



Polar Normal (separate) - BVP440I - 912300060577




Polar Normal (separate) - BVP440I - 912300060572




Polar Normal (separate) - BVP440I - 912300060574


Polar Wide Diagrams




Polar Normal (separate) - BVP440I - 912300060575




Polar Normal (separate) - BVP440I - 912300060573




Polar Normal (separate) - BVP440I - 912300060749



Polar Normal (separate) - BVP440I - 912300060752



Polar Normal (separate) - BVP440I - 912300060750



Polar Normal (separate) - BVP440I - 912300060751

