



Versatile floodlight to illuminate your areas

The ActiStar Large represents a new era in large-area and recreational sports lighting, engineered to deliver superior performance, efficiency, and connectivity. This comprehensive solution is designed to meet the demands of both simple and highly complex applications. Uncompromising Performance & Quality – Delivers exceptional light quality, uniformity, and visual comfort, ensuring safety and meeting the highest lighting performance standards with a long operational lifespan. Advanced Control & Connectivity–Features an integrated DALI driver box for seamless connectivity to building management systems. Its D4i standard compliance ensures readiness for advanced wireless control and IoT integration. Superior Energy Efficiency – The combination of high-efficacy LEDs and intelligent control capabilities leads to significant reductions in energy consumption and operational costs. Precision Optical Engineering – Equipped with a premium beam control system that maximizes light on the target area (higher lux levels and uniformity) while drastically reducing spill light

and sky glow pollution for minimal environmental impact. Optimized for Versatile Applications – The robust, single-piece pressure die-cast aluminum housing is engineered for durability and features flexible bonding fins to minimize wind load, making it ideal for sports venues and other demanding installations. Modular & Scalable Design – Available in versatile configurations—hosting 1, 2, or 3 LED modules—to provide the exact luminous flux and coverage required for any project scale.

Benefits

- High system lumen package up to 249,500 lumens at color rendering index (CRI70) at high system efficacy reduces the number of fixtures and therefore lowers TCO per area.
- The light weight (3Kg by 12% reduced compared to typical floodlight) and compact size will result in convenience of installation, lower structural load cost and lower wind loading pressure (SCx).
- Innovative beam control system – proven optics in ArenaVision and specialized designed visors, ensuring arena lighting fully complying with global sports lighting standards and reducing the spill light (20% cut) towards neighbor environment.
- Versatile mounting system with horizontally rotatable ($\pm 75^\circ$) bracket will enable installation with less constraints physically and easy aiming for optimal field illumination.
- Beam easy tracking system (color coded cap) give more convenience on maintenance to track and identify optics of each lighting fixture.
- All-in-one driver of the luminaire integrate DMX/ RDM, complying to DALI and D4i which are compatible with Interact system to control lighting points, set operation scheme and asset-management.

Applications

- Recreational sports lighting – Football, Hockey, Basketball, Golf, Tennis, etc
- Apron lighting – Airports, Parking and Industrial areas
- Logistics areas – Ports and container yards, construction sites

Features

- System lumen output (CRI70) up to 249,500lm and 233,200lm (without visor)
- Specialized designed visor to cut spill light
- Color caps for easy identification of optic type at installation site
- Both symmetric and asymmetric optics for better lighting performance given far distance light distribution and reduce quantity on project
- PC and glass front face cover optional
- Horizontally rotatable ($\pm 75^\circ$) U bracket for easing aiming and commissioning
- Breather on each LED module and 3-in-1 seamless cable for wiring, bird-proof conduit
- Unique adjustable module design to lower wind loading pressure (SCx)
- Not suitable for industry area where chemical stuff exists. Application in corrosion environment like swimming pool, coastline outdoors, please consult local sales team for special painting before order. Product has be installed on fixed objects.


Versions



ActiStar sports area



ActiStar sports area




ActiStar sports area




ActiStar sports area


Dimensional drawing




BVP582 LED1335/757 900W A35NB R5BV




BVP583 LED2332/757 1800W A35NB V1R5HB




BVP581 LED777/757 600W A35NB V1R5BV



BVP582 LED1663/757 1200W A35NB R5HB VP



BVP583 LED2088/757 1800W A65VWB R35BV



BVP581 LED832/757 600W A35NB R5HB

Product details



ActiStar sports area



ActiStar sports area



ActiStar sports area



ActiStar sports area



ActiStar sports area



ActiStar sports area

General Information

Number of gear units	1 unit
Driver included	Yes

Light Technical

Correlated Color Temperature (Nom)	5700 K
Color rendering index (CRI)	70
Light source color	757 cool white

Controls and Dimming

Dimmable	DALI
----------	------

Mechanical and Housing

Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Optical cover type	Polycarbonate

Approval and Application

Flammability mark	-
CE mark	Yes

Light Technical

Order Code	Full Product Name	Luminous Flux
911401602510	BVP583 LED2059/757 1400W A35NB R5BV	205,900 lm
911401602610	BVP583 LED2175/757 1500W A35NB R5BV	217,500 lm
911401602710	BVP583 LED2291/757 1600W A35NB R5BV	229,100 lm
911401602810	BVP583 LED2495/757 1800W A35MB R5BV	249,500 lm
911401602910	BVP583 LED2467/757 1800W A35WB R5BV	246,700 lm
911401603010	BVP583 LED2467/757 1800W A35VWB R5BV	246,700 lm
911401603710	BVP583 LED2014/757 1400W A45NB R15BV	201,400 lm
911401603810	BVP583 LED2127/757 1500W A45NB R15BV	212,700 lm
911401603910	BVP583 LED2241/757 1600W A45NB R15BV	224,100 lm
911401604010	BVP583 LED2440/757 1800W A45NB R15BV	244,000 lm
911401604110	BVP583 LED2413/757 1800W A45MB R15BV	241,300 lm
911401604210	BVP583 LED2413/757 1800W A45WB R15BV	241,300 lm
911401604310	BVP583 LED2386/757 1800W A45VWB R15BV	238,600 lm
911401605010	BVP583 LED2014/757 1400W A55NB R25BV	201,400 lm
911401605110	BVP583 LED2127/757 1500W A55NB R25BV	212,700 lm
911401605210	BVP583 LED2241/757 1600W A55NB R25BV	224,100 lm
911401605310	BVP583 LED2440/757 1800W A55NB R25BV	244,000 lm
911401605410	BVP583 LED2413/757 1800W A55MB R25BV	241,300 lm
911401605510	BVP583 LED2413/757 1800W A55WB R25BV	241,300 lm
911401605610	BVP583 LED2386/757 1800W A55VWB R25BV	238,600 lm
911401606310	BVP583 LED1857/757 1400W A65NB R35BV	185,700 lm
911401606410	BVP583 LED1962/757 1500W A65NB R35BV	196,200 lm
911401606510	BVP583 LED2067/757 1600W A65NB R35BV	206,700 lm
911401606610	BVP583 LED2251/757 1800W A65NB R35BV	225,100 lm
911401606710	BVP583 LED2223/757 1800W A65MB R35BV	222,300 lm
911401606810	BVP583 LED2223/757 1800W A65WB R35BV	222,300 lm
911401606910	BVP583 LED2088/757 1800W A65VWB R35BV	208,800 lm
911401608010	BVP583 LED1924/757 1400W A35NB V1R5BV	192,400 lm
911401608110	BVP583 LED2033/757 1500W A35NB V1R5BV	203,300 lm
911401608210	BVP583 LED2332/757 1800W A35NB V1R5BV	233,200 lm
911401608310	BVP583 LED2332/757 1800W A35MB V1R5BV	233,200 lm
911401608410	BVP583 LED2332/757 1800W A35WB V1R5BV	233,200 lm
911401608510	BVP583 LED2305/757 1800W A35VWB V1R5BV	230,500 lm
911401609210	BVP583 LED1723/757 1400W A45NB V2R15BV	172,300 lm
911401609310	BVP583 LED1820/757 1500W A45NB V2R15BV	182,000 lm
911401609410	BVP583 LED1917/757 1600W A45NB V2R15BV	191,700 lm
911401609510	BVP583 LED2088/757 1800W A45NB V2R15BV	208,800 lm

Order Code	Full Product Name	Luminous Flux
911401609610	BVP583 LED2088/757 1800W A45MB V2R15BV	208,800 lm
911401609710	BVP583 LED2088/757 1800W A45WB V2R15BV	208,800 lm
911401609810	BVP583 LED2007/757 1800W A45VWB V2R15BV	200,700 lm
911401610510	BVP583 LED1723/757 1400W A55NB V2R25BV	172,300 lm
911401610610	BVP583 LED1820/757 1500W A55NB V2R25BV	182,000 lm
911401610710	BVP583 LED1917/757 1600W A55NB V2R25BV	191,700 lm
911401610810	BVP583 LED2088/757 1800W A55NB V2R25BV	208,800 lm
911401610910	BVP583 LED2088/757 1800W A55MB V2R25BV	208,800 lm
911401611010	BVP583 LED2088/757 1800W A55WB V2R25BV	208,800 lm
911401611110	BVP583 LED2007/757 1800W A55VWB V2R25BV	200,700 lm
911401611810	BVP583 LED1723/757 1400W A65NB V2R35BV	172,300 lm
911401611910	BVP583 LED1820/757 1500W A65NB V2R35BV	182,000 lm
911401612010	BVP583 LED1917/757 1600W A65NB V2R35BV	191,700 lm
911401612110	BVP583 LED2088/757 1800W A65NB V2R35BV	208,800 lm
911401612210	BVP583 LED2061/757 1800W A65MB V2R35BV	206,100 lm
911401612310	BVP583 LED2061/757 1800W A65WB V2R35BV	206,100 lm
911401612410	BVP583 LED1952/757 1800W A65VWB V2R35BV	195,200 lm
911401612710	BVP583 LED2495/757 1800W A35NB R5HB	249,500 lm
911401613010	BVP583 LED2332/757 1800W A35NB V1R5HB	233,200 lm
911401695909	BVP583 LED2495/757 1800W A35NB R5BV	249,500 lm
911401696009	BVP583 LED2141/757 1600W A35NB V1R5BV	214,100 lm
911401602110	BVP582 LED1335/757 900W A35NB R5BV	133,500 lm
911401602210	BVP582 LED1456/757 1000W A35NB R5BV	145,600 lm
911401602310	BVP582 LED1645/757 1200W A35WB R5BV	164,500 lm
911401602410	BVP582 LED1645/757 1200W A35VWB R5BV	164,500 lm
911401603110	BVP582 LED1306/757 900W A45NB R15BV	130,600 lm
911401603210	BVP582 LED1424/757 1000W A45NB R15BV	142,400 lm
911401603310	BVP582 LED1627/757 1200W A45NB R15BV	162,700 lm
911401603410	BVP582 LED1609/757 1200W A45MB R15BV	160,900 lm
911401603510	BVP582 LED1609/757 1200W A45WB R15BV	160,900 lm
911401603610	BVP582 LED1591/757 1200W A45VWB R15BV	159,100 lm
911401604410	BVP582 LED1306/757 900W A55NB R25BV	130,600 lm
911401604510	BVP582 LED1424/757 1000W A55NB R25BV	142,400 lm
911401604610	BVP582 LED1627/757 1200W A55NB R25BV	162,700 lm
911401604710	BVP582 LED1609/757 1200W A55MB R25BV	160,900 lm
911401604810	BVP582 LED1609/757 1200W A55WB R25BV	160,900 lm
911401604910	BVP582 LED1591/757 1200W A55VWB R25BV	159,100 lm
911401605710	BVP582 LED1205/757 900W A65NB R35BV	120,500 lm
911401605810	BVP582 LED1314/757 1000W A65NB R35BV	131,400 lm
911401605910	BVP582 LED1500/757 1200W A65NB R35BV	150,000 lm

Order Code	Full Product Name	Luminous Flux
911401606010	BVP582 LED1482/757 1200W A65MB R35BV	148,200 lm
911401606110	BVP582 LED1482/757 1200W A65WB R35BV	148,200 lm
911401606210	BVP582 LED1392/757 1200W A65VWB R35BV	139,200 lm
911401607410	BVP582 LED1248/757 900W A35NB V1R5BV	124,800 lm
911401607510	BVP582 LED1361/757 1000W A35NB V1R5BV	136,100 lm
911401607610	BVP582 LED1555/757 1200W A35NB V1R5BV	155,500 lm
911401607710	BVP582 LED1555/757 1200W A35MB V1R5BV	155,500 lm
911401607810	BVP582 LED1555/757 1200W A35WB V1R5BV	155,500 lm
911401607910	BVP582 LED1537/757 1200W A35VWB V1R5BV	153,700 lm
911401608610	BVP582 LED1118/757 900W A45NB V2R15BV	111,800 lm
911401608710	BVP582 LED1219/757 1000W A45NB V2R15BV	121,900 lm
911401608810	BVP582 LED1392/757 1200W A45NB V2R15BV	139,200 lm
911401608910	BVP582 LED1392/757 1200W A45MB V2R15BV	139,200 lm
911401609010	BVP582 LED1392/757 1200W A45WB V2R15BV	139,200 lm
911401609110	BVP582 LED1338/757 1200W A45VWB V2R15BV	133,800 lm
911401609910	BVP582 LED1118/757 900W A55NB V2R25BV	111,800 lm
911401610010	BVP582 LED1219/757 1000W A55NB V2R25BV	121,900 lm
911401610110	BVP582 LED1392/757 1200W A55NB V2R25BV	139,200 lm
911401610210	BVP582 LED1392/757 1200W A55MB V2R25BV	139,200 lm
911401610310	BVP582 LED1392/757 1200W A55WB V2R25BV	139,200 lm
911401610410	BVP582 LED1338/757 1200W A55VWB V2R25BV	133,800 lm
911401611210	BVP582 LED1118/757 900W A65NB V2R35BV	111,800 lm
911401611310	BVP582 LED1219/757 1000W A65NB V2R35BV	121,900 lm
911401611410	BVP582 LED1392/757 1200W A65NB V2R35BV	139,200 lm
911401611510	BVP582 LED1374/757 1200W A65MB V2R35BV	137,400 lm
911401611610	BVP582 LED1374/757 1200W A65WB V2R35BV	137,400 lm
911401611710	BVP582 LED1302/757 1200W A65VWB V2R35BV	130,200 lm
911401612610	BVP582 LED1663/757 1200W A35NB R5HB	166,300 lm
911401612910	BVP582 LED1555/757 1200W A35NB V1R5HB	155,500 lm
911401613210	BVP582 LED1663/757 1200W A35NB R5HB VP	166,300 lm
911401695709	BVP582 LED1663/757 1200W A35NB R5BV	166,300 lm
911401695809	BVP582 LED1663/757 1200W A35MB R5BV	166,300 lm
911401601710	BVP581 LED832/757 600W A35NB R5BV	83,200 lm
911401601810	BVP581 LED832/757 600W A35MB R5BV	83,200 lm
911401601910	BVP581 LED822/757 600W A35WB R5BV	82,200 lm
911401602010	BVP581 LED822/757 600W A35VWB R5BV	82,200 lm
911401607010	BVP581 LED777/757 600W A35NB V1R5BV	77,700 lm
911401607110	BVP581 LED777/757 600W A35MB V1R5BV	77,700 lm
911401607210	BVP581 LED777/757 600W A35WB V1R5BV	77,700 lm
911401607310	BVP581 LED768/757 600W A35VWB V1R5BV	76,800 lm

Order Code	Full Product Name	Luminous Flux
911401612510	BVP581 LED832/757 600W A35NB R5HB	83,200 lm
911401612810	BVP581 LED777/757 600W A35NB V1R5HB	77,700 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401602510	BVP583 LED2059/757 1400W A35NB R5BV	1,400 W
911401602610	BVP583 LED2175/757 1500W A35NB R5BV	1,500 W
911401602710	BVP583 LED2291/757 1600W A35NB R5BV	1,600 W
911401602810	BVP583 LED2495/757 1800W A35MB R5BV	1,800 W
911401602910	BVP583 LED2467/757 1800W A35WB R5BV	1,800 W
911401603010	BVP583 LED2467/757 1800W A35VWB R5BV	1,800 W
911401603710	BVP583 LED2014/757 1400W A45NB R15BV	1,400 W
911401603810	BVP583 LED2127/757 1500W A45NB R15BV	1,500 W
911401603910	BVP583 LED2241/757 1600W A45NB R15BV	1,600 W
911401604010	BVP583 LED2440/757 1800W A45NB R15BV	1,800 W
911401604110	BVP583 LED2413/757 1800W A45MB R15BV	1,800 W
911401604210	BVP583 LED2413/757 1800W A45WB R15BV	1,800 W
911401604310	BVP583 LED2386/757 1800W A45VWB R15BV	1,800 W
911401605010	BVP583 LED2014/757 1400W A55NB R25BV	1,400 W
911401605110	BVP583 LED2127/757 1500W A55NB R25BV	1,500 W
911401605210	BVP583 LED2241/757 1600W A55NB R25BV	1,600 W
911401605310	BVP583 LED2440/757 1800W A55NB R25BV	1,800 W
911401605410	BVP583 LED2413/757 1800W A55MB R25BV	1,800 W
911401605510	BVP583 LED2413/757 1800W A55WB R25BV	1,800 W
911401605610	BVP583 LED2386/757 1800W A55VWB R25BV	1,800 W
911401606310	BVP583 LED1857/757 1400W A65NB R35BV	1,400 W
911401606410	BVP583 LED1962/757 1500W A65NB R35BV	1,500 W
911401606510	BVP583 LED2067/757 1600W A65NB R35BV	1,600 W
911401606610	BVP583 LED2251/757 1800W A65NB R35BV	1,800 W
911401606710	BVP583 LED2223/757 1800W A65MB R35BV	1,800 W
911401606810	BVP583 LED2223/757 1800W A65WB R35BV	1,800 W
911401606910	BVP583 LED2088/757 1800W A65VWB R35BV	1,800 W
911401608010	BVP583 LED1924/757 1400W A35NB V1R5BV	1,400 W
911401608110	BVP583 LED2033/757 1500W A35NB V1R5BV	1,500 W
911401608210	BVP583 LED2332/757 1800W A35NB V1R5BV	1,800 W
911401608310	BVP583 LED2332/757 1800W A35MB V1R5BV	1,800 W
911401608410	BVP583 LED2332/757 1800W A35WB V1R5BV	1,800 W
911401608510	BVP583 LED2305/757 1800W A35VWB V1R5BV	1,800 W

Order Code	Full Product Name	Power Consumption
911401609210	BVP583 LED1723/757 1400W A45NB V2R15BV	1,400 W
911401609310	BVP583 LED1820/757 1500W A45NB V2R15BV	1,500 W
911401609410	BVP583 LED1917/757 1600W A45NB V2R15BV	1,600 W
911401609510	BVP583 LED2088/757 1800W A45NB V2R15BV	1,800 W
911401609610	BVP583 LED2088/757 1800W A45MB V2R15BV	1,800 W
911401609710	BVP583 LED2088/757 1800W A45WB V2R15BV	1,800 W
911401609810	BVP583 LED2007/757 1800W A45VWB V2R15BV	1,800 W
911401610510	BVP583 LED1723/757 1400W A55NB V2R25BV	1,400 W
911401610610	BVP583 LED1820/757 1500W A55NB V2R25BV	1,500 W
911401610710	BVP583 LED1917/757 1600W A55NB V2R25BV	1,600 W
911401610810	BVP583 LED2088/757 1800W A55NB V2R25BV	1,800 W
911401610910	BVP583 LED2088/757 1800W A55MB V2R25BV	1,800 W
911401611010	BVP583 LED2088/757 1800W A55WB V2R25BV	1,800 W
911401611110	BVP583 LED2007/757 1800W A55VWB V2R25BV	1,800 W
911401611810	BVP583 LED1723/757 1400W A65NB V2R35BV	1,400 W
911401611910	BVP583 LED1820/757 1500W A65NB V2R35BV	1,500 W
911401612010	BVP583 LED1917/757 1600W A65NB V2R35BV	1,600 W
911401612110	BVP583 LED2088/757 1800W A65NB V2R35BV	1,800 W
911401612210	BVP583 LED2061/757 1800W A65MB V2R35BV	1,800 W
911401612310	BVP583 LED2061/757 1800W A65WB V2R35BV	1,800 W
911401612410	BVP583 LED1952/757 1800W A65VWB V2R35BV	1,800 W
911401612710	BVP583 LED2495/757 1800W A35NB R5HB	1,800 W
911401613010	BVP583 LED2332/757 1800W A35NB V1R5HB	1,800 W
911401695909	BVP583 LED2495/757 1800W A35NB R5BV	1,800 W
911401696009	BVP583 LED2141/757 1600W A35NB V1R5BV	1,600 W
911401602110	BVP582 LED1335/757 900W A35NB R5BV	900 W
911401602210	BVP582 LED1456/757 1000W A35NB R5BV	1,000 W
911401602310	BVP582 LED1645/757 1200W A35WB R5BV	1,200 W
911401602410	BVP582 LED1645/757 1200W A35VWB R5BV	1,200 W
911401603110	BVP582 LED1306/757 900W A45NB R15BV	900 W
911401603210	BVP582 LED1424/757 1000W A45NB R15BV	1,000 W
911401603310	BVP582 LED1627/757 1200W A45NB R15BV	1,200 W
911401603410	BVP582 LED1609/757 1200W A45MB R15BV	1,200 W
911401603510	BVP582 LED1609/757 1200W A45WB R15BV	1,200 W
911401603610	BVP582 LED1591/757 1200W A45VWB R15BV	1,200 W
911401604410	BVP582 LED1306/757 900W A55NB R25BV	900 W
911401604510	BVP582 LED1424/757 1000W A55NB R25BV	1,000 W
911401604610	BVP582 LED1627/757 1200W A55NB R25BV	1,200 W
911401604710	BVP582 LED1609/757 1200W A55MB R25BV	1,200 W
911401604810	BVP582 LED1609/757 1200W A55WB R25BV	1,200 W

Order Code	Full Product Name	Power Consumption
911401604910	BVP582 LED1591/757 1200W A55VWB R25BV	1,200 W
911401605710	BVP582 LED1205/757 900W A65NB R35BV	900 W
911401605810	BVP582 LED1314/757 1000W A65NB R35BV	1,000 W
911401605910	BVP582 LED1500/757 1200W A65NB R35BV	1,200 W
911401606010	BVP582 LED1482/757 1200W A65MB R35BV	1,200 W
911401606110	BVP582 LED1482/757 1200W A65WB R35BV	1,200 W
911401606210	BVP582 LED1392/757 1200W A65VWB R35BV	1,200 W
911401607410	BVP582 LED1248/757 900W A35NB V1R5BV	900 W
911401607510	BVP582 LED1361/757 1000W A35NB V1R5BV	1,000 W
911401607610	BVP582 LED1555/757 1200W A35NB V1R5BV	1,200 W
911401607710	BVP582 LED1555/757 1200W A35MB V1R5BV	1,200 W
911401607810	BVP582 LED1555/757 1200W A35WB V1R5BV	1,200 W
911401607910	BVP582 LED1537/757 1200W A35VWB V1R5BV	1,200 W
911401608610	BVP582 LED1118/757 900W A45NB V2R15BV	900 W
911401608710	BVP582 LED1219/757 1000W A45NB V2R15BV	1,000 W
911401608810	BVP582 LED1392/757 1200W A45NB V2R15BV	1,200 W
911401608910	BVP582 LED1392/757 1200W A45MB V2R15BV	1,200 W
911401609010	BVP582 LED1392/757 1200W A45WB V2R15BV	1,200 W
911401609110	BVP582 LED1338/757 1200W A45VWB V2R15BV	1,200 W
911401609910	BVP582 LED1118/757 900W A55NB V2R25BV	900 W
911401610010	BVP582 LED1219/757 1000W A55NB V2R25BV	1,000 W
911401610110	BVP582 LED1392/757 1200W A55NB V2R25BV	1,200 W
911401610210	BVP582 LED1392/757 1200W A55MB V2R25BV	1,200 W
911401610310	BVP582 LED1392/757 1200W A55WB V2R25BV	1,200 W
911401610410	BVP582 LED1338/757 1200W A55VWB V2R25BV	1,200 W
911401611210	BVP582 LED1118/757 900W A65NB V2R35BV	900 W
911401611310	BVP582 LED1219/757 1000W A65NB V2R35BV	1,000 W
911401611410	BVP582 LED1392/757 1200W A65NB V2R35BV	1,200 W
911401611510	BVP582 LED1374/757 1200W A65MB V2R35BV	1,200 W
911401611610	BVP582 LED1374/757 1200W A65WB V2R35BV	1,200 W
911401611710	BVP582 LED1302/757 1200W A65VWB V2R35BV	1,200 W
911401612610	BVP582 LED1663/757 1200W A35NB R5HB	1,200 W
911401612910	BVP582 LED1555/757 1200W A35NB V1R5HB	1,200 W
911401613210	BVP582 LED1663/757 1200W A35NB R5HB VP	1,200 W
911401695709	BVP582 LED1663/757 1200W A35NB R5BV	1,200 W
911401695809	BVP582 LED1663/757 1200W A35MB R5BV	1,200 W
911401601710	BVP581 LED832/757 600W A35NB R5BV	600 W
911401601810	BVP581 LED832/757 600W A35MB R5BV	600 W
911401601910	BVP581 LED822/757 600W A35WB R5BV	600 W
911401602010	BVP581 LED822/757 600W A35VWB R5BV	600 W

Order Code	Full Product Name	Power Consumption
911401607010	BVP581 LED777/757 600W A35NB V1R5BV	600 W
911401607110	BVP581 LED777/757 600W A35MB V1R5BV	600 W
911401607210	BVP581 LED777/757 600W A35WB V1R5BV	600 W
911401607310	BVP581 LED768/757 600W A35VWB V1R5BV	600 W
911401612510	BVP581 LED832/757 600W A35NB R5HB	600 W
911401612810	BVP581 LED777/757 600W A35NB V1R5HB	600 W