



Philips GreenPerform Canopy Mini500 Gen4: A high- performance, versatile, energy- saving LED

GreenPerform Canopy Mini500 G4

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

Benefits

- Excellent energy savings
- Long-term quality and reliability
- Choice of optics
- Flexible installation options
- Range of control and connectivity platforms

GreenPerform Canopy Mini500 G4

Features

- Up to 160 lm/W system efficacy
- 60,000 hours lifetime @Ta 35°C
- Outdoor and edge area (Asymmetry WB), general area (WB), emphasizing and limited area (NB)
- Recessed (BBP), Surface & frame (BCP), Pole (BGP)
- DALI control, GU5.3 for emergency lighting, EcoSet sensor

Application



- Petrol and Convenience
- Parking Garages
- Food Processing

Specifications

Mounting type	Recessed
	Surface
	Pole
Operating Temperature range	- 40 to +50 °C
Light Source	LED
Mains Voltage	2320-240V / 50-60Hz
Mains connection	Flying cable
Mechanical Accessories	Clamp
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
Control system input	DALI
Material	Housing: die-cast aluminium
Main color of the luminaire	RAL9003
Flicker / Pst / SVM	<3.2% / 0.5 / 0.4
Luminous flux	8.5klm - 18klm
Power consumption	53W - 128W
Luminaire efficacy	Up to 160lm/W
Correlated color temperature - CCT	4000K 6000K


Color Rendering index - 80	
CRI	
Beam angle	S-WB: 115°
	S-MB: 90°
	A-WB: 110°*80°
Optical cover/lens	Lens: PC
material	Cover: Glass
Optical cover/lens	Clear
finish	
Protection Class	Class I
IEC61140	
Mechanical impact	IK07
protection	
Ingress protection	IP65
Driver replaceable	Yes
Installation	Recessed
	Surface
	Pole

Dimensional drawing



GreenPerform Canopy Mini500 G4

Dimensional drawing



GreenPerform Canopy Mini500 G4

General Information	
Gear	-
Service tag	Yes
Operating and Electrical	
Protection class IEC	Safety class I
Mechanical and Housing	
Ingress protection code	IP65
Approval and Application	
ENEC mark	-
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Driver included	Number of gear units
911401502742	BCP500 G4 LED85/NW PSU S-WB	-	-
911401502842	BCP500 G4 LED85/NW PSU S-MB	-	-
911401502942	BCP500 G4 LED85/NW PSU A-WB	-	-
911401503042	BCP500 G4 LED85/CW PSU S-WB	-	-
911401503142	BCP500 G4 LED85/CW PSU S-MB	-	-
911401503242	BCP500 G4 LED85/CW PSU A-WB	-	-
911401503342	BCP500 G4 LED125/NW PSU S-WB	-	-
911401503442	BCP500 G4 LED125/NW PSU S-MB	-	-
911401503542	BCP500 G4 LED125/NW PSU A-WB	-	-
911401503642	BCP500 G4 LED125/CW PSU S-WB	-	-
911401503742	BCP500 G4 LED125/CW PSU S-MB	-	-
911401503842	BCP500 G4 LED125/CW PSU A-WB	-	-
911401503942	BCP500 G4 LED140/NW PSU S-WB	-	-
911401504042	BCP500 G4 LED140/NW PSU S-MB	-	-
911401504142	BCP500 G4 LED140/NW PSU A-WB	-	-
911401504242	BCP500 G4 LED140/CW PSU S-WB	-	-
911401504342	BCP500 G4 LED140/CW PSU S-MB	-	-
911401504442	BCP500 G4 LED140/CW PSU A-WB	-	-
911401504542	BCP500 G4 LED180/NW PSU S-WB	-	-
911401504642	BCP500 G4 LED180/NW PSU S-MB	-	-
911401504742	BCP500 G4 LED180/NW PSU A-WB	-	-
911401504842	BCP500 G4 LED180/CW PSU S-WB	-	-
911401504942	BCP500 G4 LED180/CW PSU S-MB	-	-
911401505042	BCP500 G4 LED180/CW PSU A-WB	-	-
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	-	-
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	-	-
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	-	-
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	-	-
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	-	-
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	-	-
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	-	-
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	-	-
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	-	-

Order Code	Full Product Name	Driver included	Number of gear units
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	-	-
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	-	-
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	-	-
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	-	-
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	-	-
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	-	-
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	-	-
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	-	-
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	-	-
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	-	-
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	-	-
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	-	-
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	-	-
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	-	-
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	-	-
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	-	-
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	-	-
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	-	-
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	-	-
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	-	-
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	-	-
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	-	-
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	-	-
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	-	-
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	-	-
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	-	-
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	-	-
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	-	-
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	-	-
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	-	-
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	-	-
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	-	-
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	-	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Driver included	Number of gear units
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	-	-
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	-	-
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	-	-
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	-	-
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	-	-
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	-	-
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	-	-
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	-	-
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	-	-
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	-	-
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	-	-
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	-	-
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	-	-
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	-	-
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	-	-
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	-	-
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	-	-
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	-	-
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	-	-
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	-	-
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	-	-
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	-	-
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	-	-
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	-	-
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	-	-
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	-	-
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	-	-
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	-	-
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	-	-
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	-	-
911401512342	BGP500 G4 LED85/NW PSU A-WB	-	-
911401512442	BGP500 G4 LED85/CW PSU A-WB	-	-
911401512542	BGP500 G4 LED125/NW PSU A-WB	-	-
911401512642	BGP500 G4 LED125/CW PSU A-WB	-	-
911401512742	BGP500 G4 LED140/NW PSU A-WB	-	-
911401512842	BGP500 G4 LED140/CW PSU A-WB	-	-
911401512942	BGP500 G4 LED180/NW PSU A-WB	-	-
911401513042	BGP500 G4 LED180/CW PSU A-WB	-	-
911401562142	BBP500 G4 LED125/NW L1S H S-WB	Yes	1 unit
911401562242	BBP500 G4 LED125/NW L1S H S-MB	Yes	1 unit
911401562342	BBP500 G4 LED125/NW L1S H A-WB	Yes	1 unit
911401562442	BBP500 G4 LED125/CW L1S H S-WB	Yes	1 unit
911401562542	BBP500 G4 LED125/CW L1S H S-MB	Yes	1 unit
911401562642	BBP500 G4 LED125/CW L1S H A-WB	Yes	1 unit
911401562742	BBP500 G4 LED140/NW L1S H S-WB	Yes	1 unit
911401562842	BBP500 G4 LED140/NW L1S H S-MB	Yes	1 unit
911401562942	BBP500 G4 LED140/NW L1S H A-WB	Yes	1 unit
911401563042	BBP500 G4 LED140/CW L1S H S-WB	Yes	1 unit
911401563142	BBP500 G4 LED140/CW L1S H S-MB	Yes	1 unit
911401563242	BBP500 G4 LED140/CW L1S H A-WB	Yes	1 unit
911401563342	BBP500 G4 LED180/NW L1S H S-WB	Yes	1 unit

Order Code	Full Product Name	Driver included	Number of gear units
911401563442	BBP500 G4 LED180/NW L1S H S-MB	Yes	1 unit
911401563542	BBP500 G4 LED180/NW L1S H A-WB	Yes	1 unit
911401563642	BBP500 G4 LED180/CW L1S H S-WB	Yes	1 unit
911401563742	BBP500 G4 LED180/CW L1S H S-MB	Yes	1 unit
911401563842	BBP500 G4 LED180/CW L1S H A-WB	Yes	1 unit
911401563942	BCP500 G4 LED125/NW L1S H S-WB	Yes	1 unit
911401564042	BCP500 G4 LED125/NW L1S H S-MB	Yes	1 unit
911401564142	BCP500 G4 LED125/NW L1S H A-WB	Yes	1 unit
911401564242	BCP500 G4 LED125/CW L1S H S-WB	Yes	1 unit
911401564342	BCP500 G4 LED125/CW L1S H S-MB	Yes	1 unit
911401564442	BCP500 G4 LED125/CW L1S H A-WB	Yes	1 unit
911401564542	BCP500 G4 LED140/NW L1S H S-WB	Yes	1 unit
911401564642	BCP500 G4 LED140/NW L1S H S-MB	Yes	1 unit
911401564742	BCP500 G4 LED140/NW L1S H A-WB	Yes	1 unit
911401564842	BCP500 G4 LED140/CW L1S H S-WB	Yes	1 unit
911401564942	BCP500 G4 LED140/CW L1S H S-MB	Yes	1 unit
911401565042	BCP500 G4 LED140/CW L1S H A-WB	Yes	1 unit
911401565142	BCP500 G4 LED180/NW L1S H S-WB	Yes	1 unit
911401565242	BCP500 G4 LED180/NW L1S H S-MB	Yes	1 unit
911401565342	BCP500 G4 LED180/NW L1S H A-WB	Yes	1 unit
911401565442	BCP500 G4 LED180/CW L1S H S-WB	Yes	1 unit
911401565542	BCP500 G4 LED180/CW L1S H S-MB	Yes	1 unit
911401565642	BCP500 G4 LED180/CW L1S H A-WB	Yes	1 unit
911401505142	BCP500 G4 LED85/NW PSD S-WB	-	-
911401505242	BCP500 G4 LED85/NW PSD S-MB	-	-
911401505342	BCP500 G4 LED85/NW PSD A-WB	-	-
911401505442	BCP500 G4 LED85/CW PSD S-WB	-	-
911401505542	BCP500 G4 LED85/CW PSD S-MB	-	-
911401505642	BCP500 G4 LED85/CW PSD A-WB	-	-
911401505742	BCP500 G4 LED125/NW PSD S-WB	-	-
911401505842	BCP500 G4 LED125/NW PSD S-MB	-	-
911401505942	BCP500 G4 LED125/NW PSD A-WB	-	-
911401506042	BCP500 G4 LED125/CW PSD S-WB	-	-
911401506142	BCP500 G4 LED125/CW PSD S-MB	-	-
911401506242	BCP500 G4 LED125/CW PSD A-WB	-	-
911401506342	BCP500 G4 LED140/NW PSD S-WB	-	-
911401506442	BCP500 G4 LED140/NW PSD S-MB	-	-
911401506542	BCP500 G4 LED140/NW PSD A-WB	-	-
911401506642	BCP500 G4 LED140/CW PSD S-WB	-	-
911401506742	BCP500 G4 LED140/CW PSD S-MB	-	-
911401506842	BCP500 G4 LED140/CW PSD A-WB	-	-
911401506942	BCP500 G4 LED180/NW PSD S-WB	-	-
911401507042	BCP500 G4 LED180/NW PSD S-MB	-	-
911401507142	BCP500 G4 LED180/NW PSD A-WB	-	-
911401507242	BCP500 G4 LED180/CW PSD S-WB	-	-
911401507342	BCP500 G4 LED180/CW PSD S-MB	-	-
911401507442	BCP500 G4 LED180/CW PSD A-WB	-	-
911401638109	BCP500 G4 LED100/850 PSU S-MB JP	Yes	1 unit
911401638209	BCP500 G4 LED190/850 PSU S-MB JP	Yes	1 unit
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	-	-
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	-	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Driver included	Number of gear units
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	-	-
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	-	-
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	-	-
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	-	-
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	-	-
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	-	-
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	-	-
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	-	-
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	-	-
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	-	-
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	-	-
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	-	-
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	-	-
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	-	-
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	-	-
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	-	-
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	-	-
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	-	-
911401502342	BBP500 G4 LED180/NW PSU A-WB PC	-	-
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	-	-
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	-	-
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	-	-
911401593132	BBP500 G4 LED85/NW PSU S-WB	-	-
911401593232	BBP500 G4 LED85/NW PSU S-MB	-	-
911401593332	BBP500 G4 LED85/NW PSU A-WB	-	-
911401593432	BBP500 G4 LED85/CW PSU S-WB	-	-
911401593532	BBP500 G4 LED85/CW PSU S-MB	-	-
911401593632	BBP500 G4 LED85/CW PSU A-WB	-	-
911401593732	BBP500 G4 LED125/NW PSU S-WB	-	-
911401593832	BBP500 G4 LED125/NW PSU S-MB	-	-
911401593932	BBP500 G4 LED125/NW PSU A-WB	-	-
911401594032	BBP500 G4 LED125/CW PSU S-WB	-	-
911401594132	BBP500 G4 LED125/CW PSU S-MB	-	-
911401594232	BBP500 G4 LED125/CW PSU A-WB	-	-
911401594332	BBP500 G4 LED140/NW PSU S-WB	-	-

Order Code	Full Product Name	Driver included	Number of gear units
911401594432	BBP500 G4 LED140/NW PSU S-MB	-	-
911401594532	BBP500 G4 LED140/NW PSU A-WB	-	-
911401594632	BBP500 G4 LED140/CW PSU S-WB	-	-
911401594732	BBP500 G4 LED140/CW PSU S-MB	-	-
911401594832	BBP500 G4 LED140/CW PSU A-WB	-	-
911401594932	BBP500 G4 LED180/NW PSU S-WB	-	-
911401595032	BBP500 G4 LED180/NW PSU S-MB	-	-
911401595132	BBP500 G4 LED180/NW PSU A-WB	-	-
911401595232	BBP500 G4 LED180/CW PSU S-WB	-	-
911401595332	BBP500 G4 LED180/CW PSU S-MB	-	-
911401595432	BBP500 G4 LED180/CW PSU A-WB	-	-
911401595532	BBP500 G4 LED85/NW PSD S-WB	-	-
911401595632	BBP500 G4 LED85/NW PSD S-MB	-	-
911401595732	BBP500 G4 LED85/NW PSD A-WB	-	-
911401595832	BBP500 G4 LED85/CW PSD S-WB	-	-
911401595932	BBP500 G4 LED85/CW PSD S-MB	-	-
911401596032	BBP500 G4 LED85/CW PSD A-WB	-	-
911401596132	BBP500 G4 LED125/NW PSD S-WB	-	-
911401596232	BBP500 G4 LED125/NW PSD S-MB	-	-
911401596332	BBP500 G4 LED125/NW PSD A-WB	-	-
911401596432	BBP500 G4 LED125/CW PSD S-WB	-	-
911401596532	BBP500 G4 LED125/CW PSD S-MB	-	-
911401596632	BBP500 G4 LED125/CW PSD A-WB	-	-
911401596732	BBP500 G4 LED140/NW PSD S-WB	-	-
911401596832	BBP500 G4 LED140/NW PSD S-MB	-	-
911401596932	BBP500 G4 LED140/NW PSD A-WB	-	-
911401597032	BBP500 G4 LED140/CW PSD S-WB	-	-
911401597132	BBP500 G4 LED140/CW PSD S-MB	-	-
911401597232	BBP500 G4 LED140/CW PSD A-WB	-	-
911401597332	BBP500 G4 LED180/NW PSD S-WB	-	-
911401597432	BBP500 G4 LED180/NW PSD S-MB	-	-
911401597532	BBP500 G4 LED180/NW PSD A-WB	-	-
911401597632	BBP500 G4 LED180/CW PSD S-WB	-	-
911401597732	BBP500 G4 LED180/CW PSD S-MB	-	-
911401597832	BBP500 G4 LED180/CW PSD A-WB	-	-

Light Technical

Order Code	Full Product Name	Beam angle		Color rendering index (CRI)	Luminous Efficacy (rated)		Number of	
		of light source	Correlated Color Temperature (Nom)		(Nom)	Luminous Flux	light sources	Optic type
911401502742	BCP500 G4 LED85/NW PSU S-WB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401502842	BCP500 G4 LED85/NW PSU S-MB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401502942	BCP500 G4 LED85/NW PSU A-WB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401503042	BCP500 G4 LED85/CW PSU S-WB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401503142	BCP500 G4 LED85/CW PSU S-MB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401503242	BCP500 G4 LED85/CW PSU A-WB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401503342	BCP500 G4 LED125/NW PSU S-WB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401503442	BCP500 G4 LED125/NW PSU S-MB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401503542	BCP500 G4 LED125/NW PSU A-WB	-	4000 K	>80	159 lm/W	12,638 lm	-	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Beam angle		Color rendering index (CRI)	Luminous Efficacy (rated)		Number of	
		of light source	Correlated Color Temperature (Nom)		(Nom)	Luminous Flux	light sources	Optic type
911401503642	BCP500 G4 LED125/CW PSU S-WB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401503742	BCP500 G4 LED125/CW PSU S-MB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401503842	BCP500 G4 LED125/CW PSU A-WB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401503942	BCP500 G4 LED140/NW PSU S-WB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401504042	BCP500 G4 LED140/NW PSU S-MB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401504142	BCP500 G4 LED140/NW PSU A-WB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401504242	BCP500 G4 LED140/CW PSU S-WB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401504342	BCP500 G4 LED140/CW PSU S-MB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401504442	BCP500 G4 LED140/CW PSU A-WB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401504542	BCP500 G4 LED180/NW PSU S-WB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401504642	BCP500 G4 LED180/NW PSU S-MB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401504742	BCP500 G4 LED180/NW PSU A-WB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401504842	BCP500 G4 LED180/CW PSU S-WB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401504942	BCP500 G4 LED180/CW PSU S-MB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401505042	BCP500 G4 LED180/CW PSU A-WB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	-	4000 K	>80	157 lm/W	8,313 lm	-	-
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	-	4000 K	>80	157 lm/W	8,313 lm	-	-
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	-	4000 K	>80	157 lm/W	8,313 lm	-	-
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	-	6500 K	>80	157 lm/W	8,313 lm	-	-
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	-	6500 K	>80	157 lm/W	8,313 lm	-	-
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	-	6500 K	>80	157 lm/W	8,313 lm	-	-
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	-	4000 K	>80	156 lm/W	12,366 lm	-	-
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	-	4000 K	>80	156 lm/W	12,366 lm	-	-
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	-	4000 K	>80	156 lm/W	12,366 lm	-	-
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	-	6500 K	>80	156 lm/W	12,366 lm	-	-
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	-	6500 K	>80	156 lm/W	12,366 lm	-	-
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	-	6500 K	>80	156 lm/W	12,366 lm	-	-
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	-	4000 K	>80	152 lm/W	13,777 lm	-	-
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	-	4000 K	>80	152 lm/W	13,777 lm	-	-
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	-	4000 K	>80	152 lm/W	13,777 lm	-	-
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	-	6500 K	>80	152 lm/W	13,777 lm	-	-
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	-	6500 K	>80	152 lm/W	13,777 lm	-	-
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	-	6500 K	>80	152 lm/W	13,777 lm	-	-
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	-	4000 K	>80	145 lm/W	17,677 lm	-	-
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	-	4000 K	>80	145 lm/W	17,677 lm	-	-
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	-	4000 K	>80	145 lm/W	17,677 lm	-	-
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	-	6500 K	>80	145 lm/W	17,677 lm	-	-
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	-	6500 K	>80	145 lm/W	17,677 lm	-	-
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	-	6500 K	>80	145 lm/W	17,677 lm	-	-
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	-	6500 K	>80	159 lm/W	12,638 lm	-	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Beam angle	Correlated Color Temperature (Nom)	Color	Luminous Efficacy (rated)		Number of	
		of light source		rendering index (CRI)	(Nom)	Luminous Flux	light sources	Optic type
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401512342	BGP500 G4 LED85/NW PSU A-WB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401512442	BGP500 G4 LED85/CW PSU A-WB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401512542	BGP500 G4 LED125/NW PSU A-WB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401512642	BGP500 G4 LED125/CW PSU A-WB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401512742	BGP500 G4 LED140/NW PSU A-WB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401512842	BGP500 G4 LED140/CW PSU A-WB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401512942	BGP500 G4 LED180/NW PSU A-WB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401513042	BGP500 G4 LED180/CW PSU A-WB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401562142	BBP500 G4 LED125/NW L1S H S-WB	120 degree(s)	4000 K	80	153 lm/W	12,869 lm	220	Symmetric al
911401562242	BBP500 G4 LED125/NW L1S H S-MB	120 degree(s)	4000 K	80	153 lm/W	12,869 lm	220	Symmetric al

GreenPerform Canopy Mini500 G4

		Beam angle	Color					
		of light	Correlated Color	rendering	Luminous Efficacy (rated)		Number of	
Order Code	Full Product Name	source	Temperature (Nom)	index (CRI)	(Nom)	Luminous Flux	light sources	Optic type
911401562342	BBP500 G4 LED125/NW L1S H A-WB	120 degree(s)	4000 K	80	153 lm/W	12,869 lm	220	Assymetric Beam angle
911401562442	BBP500 G4 LED125/CW L1S H S-WB	120 degree(s)	6500 K	80	153 lm/W	12,869 lm	220	Symmetrical
911401562542	BBP500 G4 LED125/CW L1S H S-MB	120 degree(s)	6500 K	80	153 lm/W	12,869 lm	220	Symmetrical
911401562642	BBP500 G4 LED125/CW L1S H A-WB	120 degree(s)	6500 K	80	153 lm/W	12,869 lm	220	Assymetric Beam angle
911401562742	BBP500 G4 LED140/NW L1S H S-WB	120 degree(s)	4000 K	80	151 lm/W	14,056 lm	220	Symmetrical
911401562842	BBP500 G4 LED140/NW L1S H S-MB	120 degree(s)	4000 K	80	151 lm/W	14,056 lm	220	Symmetrical
911401562942	BBP500 G4 LED140/NW L1S H A-WB	120 degree(s)	4000 K	80	151 lm/W	14,056 lm	220	Assymetric Beam angle
911401563042	BBP500 G4 LED140/CW L1S H S-WB	120 degree(s)	6500 K	80	151 lm/W	14,056 lm	220	Symmetrical
911401563142	BBP500 G4 LED140/CW L1S H S-MB	120 degree(s)	6500 K	80	151 lm/W	14,056 lm	220	Symmetrical
911401563242	BBP500 G4 LED140/CW L1S H A-WB	120 degree(s)	6500 K	80	151 lm/W	14,056 lm	220	Assymetric Beam angle
911401563342	BBP500 G4 LED180/NW L1S H S-WB	120 degree(s)	4000 K	80	142 lm/W	18,394 lm	220	Symmetrical
911401563442	BBP500 G4 LED180/NW L1S H S-MB	120 degree(s)	4000 K	80	142 lm/W	18,394 lm	220	Symmetrical
911401563542	BBP500 G4 LED180/NW L1S H A-WB	120 degree(s)	4000 K	80	142 lm/W	18,394 lm	220	Assymetric Beam angle
911401563642	BBP500 G4 LED180/CW L1S H S-WB	120 degree(s)	6500 K	80	142 lm/W	18,394 lm	220	Symmetrical
911401563742	BBP500 G4 LED180/CW L1S H S-MB	120 degree(s)	6500 K	80	142 lm/W	18,394 lm	220	Symmetrical
911401563842	BBP500 G4 LED180/CW L1S H A-WB	120 degree(s)	6500 K	80	142 lm/W	18,394 lm	220	Assymetric Beam angle
911401563942	BCP500 G4 LED125/NW L1S H S-WB	120 degree(s)	4000 K	80	153 lm/W	12,869 lm	220	Symmetrical
911401564042	BCP500 G4 LED125/NW L1S H S-MB	120 degree(s)	4000 K	80	153 lm/W	12,869 lm	220	Symmetrical
911401564142	BCP500 G4 LED125/NW L1S H A-WB	120 degree(s)	4000 K	80	153 lm/W	12,869 lm	220	Assymetric Beam angle
911401564242	BCP500 G4 LED125/CW L1S H S-WB	120 degree(s)	6500 K	80	153 lm/W	12,869 lm	220	Symmetrical
911401564342	BCP500 G4 LED125/CW L1S H S-MB	120 degree(s)	6500 K	80	153 lm/W	12,869 lm	220	Symmetrical

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Beam angle	Correlated Color	Color	Luminous Efficacy (rated)	Number of		
		of light		rendering				
		source	Temperature (Nom)	index (CRI)	(Nom)			
911401564442	BCP500 G4 LED125/CW L1S H A-WB	120 degree(s)	6500 K	80	153 lm/W	12,869 lm	220	Assymetric Beam angle
911401564542	BCP500 G4 LED140/NW L1S H S-WB	120 degree(s)	4000 K	80	151 lm/W	14,056 lm	220	Symmetrical
911401564642	BCP500 G4 LED140/NW L1S H S-MB	120 degree(s)	4000 K	80	151 lm/W	14,056 lm	220	Symmetrical
911401564742	BCP500 G4 LED140/NW L1S H A-WB	120 degree(s)	4000 K	80	151 lm/W	14,056 lm	220	Assymetric Beam angle
911401564842	BCP500 G4 LED140/CW L1S H S-WB	120 degree(s)	6500 K	80	151 lm/W	14,056 lm	220	Symmetrical
911401564942	BCP500 G4 LED140/CW L1S H S-MB	120 degree(s)	6500 K	80	151 lm/W	14,056 lm	220	Symmetrical
911401565042	BCP500 G4 LED140/CW L1S H A-WB	120 degree(s)	6500 K	80	151 lm/W	14,056 lm	220	Assymetric Beam angle
911401565142	BCP500 G4 LED180/NW L1S H S-WB	120 degree(s)	4000 K	80	142 lm/W	18,394 lm	220	Symmetrical
911401565242	BCP500 G4 LED180/NW L1S H S-MB	120 degree(s)	4000 K	80	142 lm/W	18,394 lm	220	Symmetrical
911401565342	BCP500 G4 LED180/NW L1S H A-WB	120 degree(s)	4000 K	80	142 lm/W	18,394 lm	220	Assymetric Beam angle
911401565442	BCP500 G4 LED180/CW L1S H S-WB	120 degree(s)	6500 K	80	142 lm/W	18,394 lm	220	Symmetrical
911401565542	BCP500 G4 LED180/CW L1S H S-MB	120 degree(s)	6500 K	80	142 lm/W	18,394 lm	220	Symmetrical
911401565642	BCP500 G4 LED180/CW L1S H A-WB	120 degree(s)	6500 K	80	142 lm/W	18,394 lm	220	Assymetric Beam angle
911401505142	BCP500 G4 LED85/NW PSD S-WB	-	4000 K	>80	147 lm/W	8,496 lm	-	-
911401505242	BCP500 G4 LED85/NW PSD S-MB	-	4000 K	>80	147 lm/W	8,496 lm	-	-
911401505342	BCP500 G4 LED85/NW PSD A-WB	-	4000 K	>80	147 lm/W	8,496 lm	-	-
911401505442	BCP500 G4 LED85/CW PSD S-WB	-	6500 K	>80	147 lm/W	8,496 lm	-	-
911401505542	BCP500 G4 LED85/CW PSD S-MB	-	6500 K	>80	147 lm/W	8,496 lm	-	-
911401505642	BCP500 G4 LED85/CW PSD A-WB	-	6500 K	>80	147 lm/W	8,496 lm	-	-
911401505742	BCP500 G4 LED125/NW PSD S-WB	-	4000 K	>80	149 lm/W	12,638 lm	-	-
911401505842	BCP500 G4 LED125/NW PSD S-MB	-	4000 K	>80	149 lm/W	12,638 lm	-	-
911401505942	BCP500 G4 LED125/NW PSD A-WB	-	4000 K	>80	149 lm/W	12,638 lm	-	-
911401506042	BCP500 G4 LED125/CW PSD S-WB	-	6500 K	>80	149 lm/W	12,638 lm	-	-
911401506142	BCP500 G4 LED125/CW PSD S-MB	-	6500 K	>80	149 lm/W	12,638 lm	-	-
911401506242	BCP500 G4 LED125/CW PSD A-WB	-	6500 K	>80	149 lm/W	12,638 lm	-	-
911401506342	BCP500 G4 LED140/NW PSD S-WB	-	4000 K	>80	147 lm/W	14,079 lm	-	-
911401506442	BCP500 G4 LED140/NW PSD S-MB	-	4000 K	>80	147 lm/W	14,079 lm	-	-
911401506542	BCP500 G4 LED140/NW PSD A-WB	-	4000 K	>80	147 lm/W	14,079 lm	-	-
911401506642	BCP500 G4 LED140/CW PSD S-WB	-	6500 K	>80	147 lm/W	14,079 lm	-	-
911401506742	BCP500 G4 LED140/CW PSD S-MB	-	6500 K	>80	147 lm/W	14,079 lm	-	-
911401506842	BCP500 G4 LED140/CW PSD A-WB	-	6500 K	>80	147 lm/W	14,079 lm	-	-
911401506942	BCP500 G4 LED180/NW PSD S-WB	-	4000 K	>80	142 lm/W	18,066 lm	-	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Beam angle	Correlated Color	Color	Luminous Efficacy (rated)		Number of	
		of light source	Temperature (Nom)	rendering index (CRI)	(Nom)	Luminous Flux	light sources	Optic type
911401507042	BCP500 G4 LED180/NW PSD S-MB	-	4000 K	>80	142 lm/W	18,066 lm	-	-
911401507142	BCP500 G4 LED180/NW PSD A-WB	-	4000 K	>80	142 lm/W	18,066 lm	-	-
911401507242	BCP500 G4 LED180/CW PSD S-WB	-	6500 K	>80	142 lm/W	18,066 lm	-	-
911401507342	BCP500 G4 LED180/CW PSD S-MB	-	6500 K	>80	142 lm/W	18,066 lm	-	-
911401507442	BCP500 G4 LED180/CW PSD A-WB	-	6500 K	>80	142 lm/W	18,066 lm	-	-
911401638109	BCP500 G4 LED100/850 PSU S-MB JP	92 degree(s)	5000 K	80	159 lm/W	10,000 lm	152	Symmetrical
911401638209	BCP500 G4 LED190/850 PSU S-MB JP	92 degree(s)	5000 K	80	160 lm/W	19,000 lm	304	Symmetrical
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	-	4000 K	>80	157 lm/W	8,313 lm	-	-
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	-	4000 K	>80	157 lm/W	8,313 lm	-	-
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	-	4000 K	>80	157 lm/W	8,313 lm	-	-
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	-	6500 K	>80	157 lm/W	8,313 lm	-	-
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	-	6500 K	>80	157 lm/W	8,313 lm	-	-
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	-	6500 K	>80	157 lm/W	8,313 lm	-	-
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	-	4000 K	>80	156 lm/W	12,366 lm	-	-
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	-	4000 K	>80	156 lm/W	12,366 lm	-	-
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	-	4000 K	>80	156 lm/W	12,366 lm	-	-
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	-	6500 K	>80	156 lm/W	12,366 lm	-	-
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	-	6500 K	>80	156 lm/W	12,366 lm	-	-
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	-	6500 K	>80	156 lm/W	12,366 lm	-	-
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	-	4000 K	>80	152 lm/W	13,777 lm	-	-
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	-	4000 K	>80	152 lm/W	13,777 lm	-	-
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	-	4000 K	>80	152 lm/W	13,777 lm	-	-
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	-	6500 K	>80	152 lm/W	13,777 lm	-	-
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	-	6500 K	>80	152 lm/W	13,777 lm	-	-
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	-	6500 K	>80	152 lm/W	13,777 lm	-	-
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	-	4000 K	>80	145 lm/W	17,677 lm	-	-
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	-	4000 K	>80	145 lm/W	17,677 lm	-	-
911401502342	BBP500 G4 LED180/NW PSU A-WB PC	-	4000 K	>80	145 lm/W	17,677 lm	-	-
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	-	6500 K	>80	145 lm/W	17,677 lm	-	-
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	-	6500 K	>80	145 lm/W	17,677 lm	-	-
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	-	6500 K	>80	145 lm/W	17,677 lm	-	-
911401593132	BBP500 G4 LED85/NW PSU S-WB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401593232	BBP500 G4 LED85/NW PSU S-MB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401593332	BBP500 G4 LED85/NW PSU A-WB	-	4000 K	>80	160 lm/W	8,496 lm	-	-
911401593432	BBP500 G4 LED85/CW PSU S-WB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401593532	BBP500 G4 LED85/CW PSU S-MB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401593632	BBP500 G4 LED85/CW PSU A-WB	-	6500 K	>80	160 lm/W	8,496 lm	-	-
911401593732	BBP500 G4 LED125/NW PSU S-WB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401593832	BBP500 G4 LED125/NW PSU S-MB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401593932	BBP500 G4 LED125/NW PSU A-WB	-	4000 K	>80	159 lm/W	12,638 lm	-	-
911401594032	BBP500 G4 LED125/CW PSU S-WB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401594132	BBP500 G4 LED125/CW PSU S-MB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401594232	BBP500 G4 LED125/CW PSU A-WB	-	6500 K	>80	159 lm/W	12,638 lm	-	-
911401594332	BBP500 G4 LED140/NW PSU S-WB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401594432	BBP500 G4 LED140/NW PSU S-MB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401594532	BBP500 G4 LED140/NW PSU A-WB	-	4000 K	>80	155 lm/W	14,079 lm	-	-
911401594632	BBP500 G4 LED140/CW PSU S-WB	-	6500 K	>80	155 lm/W	14,079 lm	-	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Beam angle		Color rendering index (CRI)	Luminous Efficacy (rated)	Number of		
		of light source	Correlated Color Temperature (Nom)			Luminous Flux	light sources	Optic type
911401594732	BBP500 G4 LED140/CW PSU S-MB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401594832	BBP500 G4 LED140/CW PSU A-WB	-	6500 K	>80	155 lm/W	14,079 lm	-	-
911401594932	BBP500 G4 LED180/NW PSU S-WB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401595032	BBP500 G4 LED180/NW PSU S-MB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401595132	BBP500 G4 LED180/NW PSU A-WB	-	4000 K	>80	148 lm/W	18,066 lm	-	-
911401595232	BBP500 G4 LED180/CW PSU S-WB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401595332	BBP500 G4 LED180/CW PSU S-MB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401595432	BBP500 G4 LED180/CW PSU A-WB	-	6500 K	>80	148 lm/W	18,066 lm	-	-
911401595532	BBP500 G4 LED85/NW PSD S-WB	-	4000 K	>80	147 lm/W	8,496 lm	-	-
911401595632	BBP500 G4 LED85/NW PSD S-MB	-	4000 K	>80	147 lm/W	8,496 lm	-	-
911401595732	BBP500 G4 LED85/NW PSD A-WB	-	4000 K	>80	147 lm/W	8,496 lm	-	-
911401595832	BBP500 G4 LED85/CW PSD S-WB	-	6500 K	>80	147 lm/W	8,496 lm	-	-
911401595932	BBP500 G4 LED85/CW PSD S-MB	-	6500 K	>80	147 lm/W	8,496 lm	-	-
911401596032	BBP500 G4 LED85/CW PSD A-WB	-	6500 K	>80	147 lm/W	8,496 lm	-	-
911401596132	BBP500 G4 LED125/NW PSD S-WB	-	4000 K	>80	149 lm/W	12,638 lm	-	-
911401596232	BBP500 G4 LED125/NW PSD S-MB	-	4000 K	>80	149 lm/W	12,638 lm	-	-
911401596332	BBP500 G4 LED125/NW PSD A-WB	-	4000 K	>80	149 lm/W	12,638 lm	-	-
911401596432	BBP500 G4 LED125/CW PSD S-WB	-	6500 K	>80	149 lm/W	12,638 lm	-	-
911401596532	BBP500 G4 LED125/CW PSD S-MB	-	6500 K	>80	149 lm/W	12,638 lm	-	-
911401596632	BBP500 G4 LED125/CW PSD A-WB	-	6500 K	>80	149 lm/W	12,638 lm	-	-
911401596732	BBP500 G4 LED140/NW PSD S-WB	-	4000 K	>80	147 lm/W	14,079 lm	-	-
911401596832	BBP500 G4 LED140/NW PSD S-MB	-	4000 K	>80	147 lm/W	14,079 lm	-	-
911401596932	BBP500 G4 LED140/NW PSD A-WB	-	4000 K	>80	147 lm/W	14,079 lm	-	-
911401597032	BBP500 G4 LED140/CW PSD S-WB	-	6500 K	>80	147 lm/W	14,079 lm	-	-
911401597132	BBP500 G4 LED140/CW PSD S-MB	-	6500 K	>80	147 lm/W	14,079 lm	-	-
911401597232	BBP500 G4 LED140/CW PSD A-WB	-	6500 K	>80	147 lm/W	14,079 lm	-	-
911401597332	BBP500 G4 LED180/NW PSD S-WB	-	4000 K	>80	142 lm/W	18,066 lm	-	-
911401597432	BBP500 G4 LED180/NW PSD S-MB	-	4000 K	>80	142 lm/W	18,066 lm	-	-
911401597532	BBP500 G4 LED180/NW PSD A-WB	-	4000 K	>80	142 lm/W	18,066 lm	-	-
911401597632	BBP500 G4 LED180/CW PSD S-WB	-	6500 K	>80	142 lm/W	18,066 lm	-	-
911401597732	BBP500 G4 LED180/CW PSD S-MB	-	6500 K	>80	142 lm/W	18,066 lm	-	-
911401597832	BBP500 G4 LED180/CW PSD A-WB	-	6500 K	>80	142 lm/W	18,066 lm	-	-

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401502742	BCP500 G4 LED85/NW PSU S-WB	220-240 V	50 to 60 Hz	53 W	-
911401502842	BCP500 G4 LED85/NW PSU S-MB	220-240 V	50 to 60 Hz	53 W	-
911401502942	BCP500 G4 LED85/NW PSU A-WB	220-240 V	50 to 60 Hz	53 W	-

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401503042	BCP500 G4 LED85/CW PSU S-WB	220-240 V	50 to 60 Hz	53 W	-
911401503142	BCP500 G4 LED85/CW PSU S-MB	220-240 V	50 to 60 Hz	53 W	-
911401503242	BCP500 G4 LED85/CW PSU A-WB	220-240 V	50 to 60 Hz	53 W	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401503342	BCP500 G4 LED125/NW PSU S-WB	220-240 V	50 to 60 Hz	79 W	-
911401503442	BCP500 G4 LED125/NW PSU S-MB	220-240 V	50 to 60 Hz	79 W	-
911401503542	BCP500 G4 LED125/NW PSU A-WB	220-240 V	50 to 60 Hz	79 W	-
911401503642	BCP500 G4 LED125/CW PSU S-WB	220-240 V	50 to 60 Hz	79 W	-
911401503742	BCP500 G4 LED125/CW PSU S-MB	220-240 V	50 to 60 Hz	79 W	-
911401503842	BCP500 G4 LED125/CW PSU A-WB	220-240 V	50 to 60 Hz	79 W	-
911401503942	BCP500 G4 LED140/NW PSU S-WB	220-240 V	50 to 60 Hz	91 W	-
911401504042	BCP500 G4 LED140/NW PSU S-MB	220-240 V	50 to 60 Hz	91 W	-
911401504142	BCP500 G4 LED140/NW PSU A-WB	220-240 V	50 to 60 Hz	91 W	-
911401504242	BCP500 G4 LED140/CW PSU S-WB	220-240 V	50 to 60 Hz	91 W	-
911401504342	BCP500 G4 LED140/CW PSU S-MB	220-240 V	50 to 60 Hz	91 W	-
911401504442	BCP500 G4 LED140/CW PSU A-WB	220-240 V	50 to 60 Hz	91 W	-
911401504542	BCP500 G4 LED180/NW PSU S-WB	220-240 V	50 to 60 Hz	122 W	-
911401504642	BCP500 G4 LED180/NW PSU S-MB	220-240 V	50 to 60 Hz	122 W	-
911401504742	BCP500 G4 LED180/NW PSU A-WB	220-240 V	50 to 60 Hz	122 W	-
911401504842	BCP500 G4 LED180/CW PSU S-WB	220-240 V	50 to 60 Hz	122 W	-

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401504942	BCP500 G4 LED180/CW PSU S-MB	220-240 V	50 to 60 Hz	122 W	-
911401505042	BCP500 G4 LED180/CW PSU A-WB	220-240 V	50 to 60 Hz	122 W	-
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	220-240 V	50 to 60 Hz	53 W	-
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	220-240 V	50 to 60 Hz	53 W	-
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	220-240 V	50 to 60 Hz	53 W	-
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	220-240 V	50 to 60 Hz	53 W	-
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	220-240 V	50 to 60 Hz	53 W	-
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	220-240 V	50 to 60 Hz	53 W	-
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	220-240 V	50 to 60 Hz	79 W	-
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	220-240 V	50 to 60 Hz	79 W	-
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	220-240 V	50 to 60 Hz	79 W	-
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	220-240 V	50 to 60 Hz	79 W	-
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	220-240 V	50 to 60 Hz	79 W	-
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	220-240 V	50 to 60 Hz	79 W	-
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	220-240 V	50 to 60 Hz	91 W	-
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	220-240 V	50 to 60 Hz	91 W	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	220-240 V	50 to 60 Hz	91 W	-
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	220-240 V	50 to 60 Hz	91 W	-
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	220-240 V	50 to 60 Hz	91 W	-
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	220-240 V	50 to 60 Hz	91 W	-
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	220-240 V	50 to 60 Hz	122 W	-
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	220-240 V	50 to 60 Hz	122 W	-
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	220-240 V	50 to 60 Hz	122 W	-
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	220-240 V	50 to 60 Hz	122 W	-
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	220-240 V	50 to 60 Hz	122 W	-
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	220-240 V	50 to 60 Hz	122 W	-
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	220-240 V	50 to 60 Hz	53 W	-
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	220-240 V	50 to 60 Hz	53 W	-
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	220-240 V	50 to 60 Hz	53 W	-
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	220-240 V	50 to 60 Hz	53 W	-
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	220-240 V	50 to 60 Hz	53 W	-
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	220-240 V	50 to 60 Hz	53 W	-

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	220-240 V	50 to 60 Hz	79 W	-
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	220-240 V	50 to 60 Hz	79 W	-
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	220-240 V	50 to 60 Hz	79 W	-
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	220-240 V	50 to 60 Hz	79 W	-
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	220-240 V	50 to 60 Hz	79 W	-
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	220-240 V	50 to 60 Hz	79 W	-
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	220-240 V	50 to 60 Hz	91 W	-
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	220-240 V	50 to 60 Hz	91 W	-
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	220-240 V	50 to 60 Hz	91 W	-
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	220-240 V	50 to 60 Hz	91 W	-
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	220-240 V	50 to 60 Hz	91 W	-
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	220-240 V	50 to 60 Hz	91 W	-
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	220-240 V	50 to 60 Hz	122 W	-
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	220-240 V	50 to 60 Hz	122 W	-
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	220-240 V	50 to 60 Hz	122 W	-
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	220-240 V	50 to 60 Hz	122 W	-

GreenPerform Canopy Mini500 G4

					Suitable for random switching
Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	220-240 V	50 to 60 Hz	122 W	-
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	220-240 V	50 to 60 Hz	122 W	-
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	220-240 V	50 to 60 Hz	122 W	-
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	220-240 V	50 to 60 Hz	122 W	-
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	220-240 V	50 to 60 Hz	122 W	-
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	220-240 V	50 to 60 Hz	53 W	-
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	220-240 V	50 to 60 Hz	53 W	-
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	220-240 V	50 to 60 Hz	53 W	-
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	220-240 V	50 to 60 Hz	53 W	-
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	220-240 V	50 to 60 Hz	53 W	-
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	220-240 V	50 to 60 Hz	53 W	-
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	220-240 V	50 to 60 Hz	79 W	-
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	220-240 V	50 to 60 Hz	79 W	-
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	220-240 V	50 to 60 Hz	79 W	-
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	220-240 V	50 to 60 Hz	79 W	-
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	220-240 V	50 to 60 Hz	79 W	-

					Suitable for random switching
Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	220-240 V	50 to 60 Hz	79 W	-
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	220-240 V	50 to 60 Hz	91 W	-
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	220-240 V	50 to 60 Hz	91 W	-
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	220-240 V	50 to 60 Hz	91 W	-
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	220-240 V	50 to 60 Hz	91 W	-
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	220-240 V	50 to 60 Hz	91 W	-
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	220-240 V	50 to 60 Hz	91 W	-
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	220-240 V	50 to 60 Hz	122 W	-
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	220-240 V	50 to 60 Hz	122 W	-
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	220-240 V	50 to 60 Hz	122 W	-
911401512342	BGP500 G4 LED85/NW PSU A-WB	220-240 V	50 to 60 Hz	53 W	-
911401512442	BGP500 G4 LED85/CW PSU A-WB	220-240 V	50 to 60 Hz	53 W	-
911401512542	BGP500 G4 LED125/NW PSU A-WB	220-240 V	50 to 60 Hz	79 W	-
911401512642	BGP500 G4 LED125/CW PSU A-WB	220-240 V	50 to 60 Hz	79 W	-
911401512742	BGP500 G4 LED140/NW PSU A-WB	220-240 V	50 to 60 Hz	91 W	-
911401512842	BGP500 G4 LED140/CW PSU A-WB	220-240 V	50 to 60 Hz	91 W	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401512942	BGP500 G4 LED180/NW PSU A-WB	220-240 V	50 to 60 Hz	122 W	-
911401513042	BGP500 G4 LED180/CW PSU A-WB	220-240 V	50 to 60 Hz	122 W	-
911401562142	BBP500 G4 LED125/NW L1S H S-WB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401562242	BBP500 G4 LED125/NW L1S H S-MB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401562342	BBP500 G4 LED125/NW L1S H A-WB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401562442	BBP500 G4 LED125/CW L1S H S-WB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401562542	BBP500 G4 LED125/CW L1S H S-MB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401562642	BBP500 G4 LED125/CW L1S H A-WB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401562742	BBP500 G4 LED140/NW L1S H S-WB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401562842	BBP500 G4 LED140/NW L1S H S-MB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401562942	BBP500 G4 LED140/NW L1S H A-WB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401563042	BBP500 G4 LED140/CW L1S H S-WB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401563142	BBP500 G4 LED140/CW L1S H S-MB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401563242	BBP500 G4 LED140/CW L1S H A-WB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401563342	BBP500 G4 LED180/NW L1S H S-WB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)
911401563442	BBP500 G4 LED180/NW L1S H S-MB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)
911401563542	BBP500 G4 LED180/NW L1S H A-WB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401563642	BBP500 G4 LED180/CW L1S H S-WB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)
911401563742	BBP500 G4 LED180/CW L1S H S-MB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)
911401563842	BBP500 G4 LED180/CW L1S H A-WB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)
911401563942	BCP500 G4 LED125/NW L1S H S-WB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401564042	BCP500 G4 LED125/NW L1S H S-MB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401564142	BCP500 G4 LED125/NW L1S H A-WB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401564242	BCP500 G4 LED125/CW L1S H S-WB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401564342	BCP500 G4 LED125/CW L1S H S-MB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401564442	BCP500 G4 LED125/CW L1S H A-WB	222 to 240 V	50 or 60 Hz	84 W	Yes (relates to presence/movement detection)
911401564542	BCP500 G4 LED140/NW L1S H S-WB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401564642	BCP500 G4 LED140/NW L1S H S-MB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401564742	BCP500 G4 LED140/NW L1S H A-WB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401564842	BCP500 G4 LED140/CW L1S H S-WB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401564942	BCP500 G4 LED140/CW L1S H S-MB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401565042	BCP500 G4 LED140/CW L1S H A-WB	222 to 240 V	50 or 60 Hz	93 W	Yes (relates to presence/movement detection)
911401565142	BCP500 G4 LED180/NW L1S H S-WB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401565242	BCP500 G4 LED180/NW L1S H S-MB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)
911401565342	BCP500 G4 LED180/NW L1S H A-WB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)
911401565442	BCP500 G4 LED180/CW L1S H S-WB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)
911401565542	BCP500 G4 LED180/CW L1S H S-MB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)
911401565642	BCP500 G4 LED180/CW L1S H A-WB	222 to 240 V	50 or 60 Hz	130 W	Yes (relates to presence/movement detection)
911401505142	BCP500 G4 LED85/NW PSD S-WB	220-240 V	50 to 60 Hz	58 W	-
911401505242	BCP500 G4 LED85/NW PSD S-MB	220-240 V	50 to 60 Hz	58 W	-
911401505342	BCP500 G4 LED85/NW PSD A-WB	220-240 V	50 to 60 Hz	58 W	-
911401505442	BCP500 G4 LED85/CW PSD S-WB	220-240 V	50 to 60 Hz	58 W	-
911401505542	BCP500 G4 LED85/CW PSD S-MB	220-240 V	50 to 60 Hz	58 W	-
911401505642	BCP500 G4 LED85/CW PSD A-WB	220-240 V	50 to 60 Hz	58 W	-

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401505742	BCP500 G4 LED125/NW PSD S-WB	220-240 V	50 to 60 Hz	85 W	-
911401505842	BCP500 G4 LED125/NW PSD S-MB	220-240 V	50 to 60 Hz	85 W	-
911401505942	BCP500 G4 LED125/NW PSD A-WB	220-240 V	50 to 60 Hz	85 W	-
911401506042	BCP500 G4 LED125/CW PSD S-WB	220-240 V	50 to 60 Hz	85 W	-
911401506142	BCP500 G4 LED125/CW PSD S-MB	220-240 V	50 to 60 Hz	85 W	-
911401506242	BCP500 G4 LED125/CW PSD A-WB	220-240 V	50 to 60 Hz	85 W	-
911401506342	BCP500 G4 LED140/NW PSD S-WB	220-240 V	50 to 60 Hz	96 W	-
911401506442	BCP500 G4 LED140/NW PSD S-MB	220-240 V	50 to 60 Hz	96 W	-
911401506542	BCP500 G4 LED140/NW PSD A-WB	220-240 V	50 to 60 Hz	96 W	-
911401506642	BCP500 G4 LED140/CW PSD S-WB	220-240 V	50 to 60 Hz	96 W	-
911401506742	BCP500 G4 LED140/CW PSD S-MB	220-240 V	50 to 60 Hz	96 W	-
911401506842	BCP500 G4 LED140/CW PSD A-WB	220-240 V	50 to 60 Hz	96 W	-
911401506942	BCP500 G4 LED180/NW PSD S-WB	220-240 V	50 to 60 Hz	128 W	-
911401507042	BCP500 G4 LED180/NW PSD S-MB	220-240 V	50 to 60 Hz	128 W	-
911401507142	BCP500 G4 LED180/NW PSD A-WB	220-240 V	50 to 60 Hz	128 W	-
911401507242	BCP500 G4 LED180/CW PSD S-WB	220-240 V	50 to 60 Hz	128 W	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401507342	BCP500 G4 LED180/CW PSD S-MB	220-240 V	50 to 60 Hz	128 W	-
911401507442	BCP500 G4 LED180/CW PSD A-WB	220-240 V	50 to 60 Hz	128 W	-
911401638109	BCP500 G4 LED100/850 PSU S-MB JP	200 to 240 V	50 or 60 Hz	63 W	Yes
911401638209	BCP500 G4 LED190/850 PSU S-MB JP	200 to 240 V	50 or 60 Hz	119 W	Yes
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	220-240 V	50 to 60 Hz	53 W	-
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	220-240 V	50 to 60 Hz	53 W	-
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	220-240 V	50 to 60 Hz	53 W	-
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	220-240 V	50 to 60 Hz	53 W	-
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	220-240 V	50 to 60 Hz	53 W	-
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	220-240 V	50 to 60 Hz	53 W	-
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	220-240 V	50 to 60 Hz	79 W	-
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	220-240 V	50 to 60 Hz	79 W	-
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	220-240 V	50 to 60 Hz	79 W	-
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	220-240 V	50 to 60 Hz	79 W	-
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	220-240 V	50 to 60 Hz	79 W	-
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	220-240 V	50 to 60 Hz	79 W	-

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	Suitable for random switching
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	220-240 V	50 to 60 Hz	91 W	-
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	220-240 V	50 to 60 Hz	91 W	-
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	220-240 V	50 to 60 Hz	91 W	-
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	220-240 V	50 to 60 Hz	91 W	-
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	220-240 V	50 to 60 Hz	91 W	-
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	220-240 V	50 to 60 Hz	91 W	-
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	220-240 V	50 to 60 Hz	122 W	-
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	220-240 V	50 to 60 Hz	122 W	-
911401502342	BBP500 G4 LED180/NW PSU A-WB PC	220-240 V	50 to 60 Hz	122 W	-
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	220-240 V	50 to 60 Hz	122 W	-
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	220-240 V	50 to 60 Hz	122 W	-
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	220-240 V	50 to 60 Hz	122 W	-
911401593132	BBP500 G4 LED85/NW PSU S-WB	220-240 V	50 to 60 Hz	53 W	-
911401593232	BBP500 G4 LED85/NW PSU S-MB	220-240 V	50 to 60 Hz	53 W	-
911401593332	BBP500 G4 LED85/NW PSU A-WB	220-240 V	50 to 60 Hz	53 W	-
911401593432	BBP500 G4 LED85/CW PSU S-WB	220-240 V	50 to 60 Hz	53 W	-

GreenPerform Canopy Mini500 G4

					Suitable for random switching
Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	
911401593532	BBP500 G4 LED85/CW PSU S-MB	220-240 V	50 to 60 Hz	53 W	-
911401593632	BBP500 G4 LED85/CW PSU A-WB	220-240 V	50 to 60 Hz	53 W	-
911401593732	BBP500 G4 LED125/NW PSU S-WB	220-240 V	50 to 60 Hz	79 W	-
911401593832	BBP500 G4 LED125/NW PSU S-MB	220-240 V	50 to 60 Hz	79 W	-
911401593932	BBP500 G4 LED125/NW PSU A-WB	220-240 V	50 to 60 Hz	79 W	-
911401594032	BBP500 G4 LED125/CW PSU S-WB	220-240 V	50 to 60 Hz	79 W	-
911401594132	BBP500 G4 LED125/CW PSU S-MB	220-240 V	50 to 60 Hz	79 W	-
911401594232	BBP500 G4 LED125/CW PSU A-WB	220-240 V	50 to 60 Hz	79 W	-
911401594332	BBP500 G4 LED140/NW PSU S-WB	220-240 V	50 to 60 Hz	91 W	-
911401594432	BBP500 G4 LED140/NW PSU S-MB	220-240 V	50 to 60 Hz	91 W	-
911401594532	BBP500 G4 LED140/NW PSU A-WB	220-240 V	50 to 60 Hz	91 W	-
911401594632	BBP500 G4 LED140/CW PSU S-WB	220-240 V	50 to 60 Hz	91 W	-
911401594732	BBP500 G4 LED140/CW PSU S-MB	220-240 V	50 to 60 Hz	91 W	-
911401594832	BBP500 G4 LED140/CW PSU A-WB	220-240 V	50 to 60 Hz	91 W	-
911401594932	BBP500 G4 LED180/NW PSU S-WB	220-240 V	50 to 60 Hz	122 W	-
911401595032	BBP500 G4 LED180/NW PSU S-MB	220-240 V	50 to 60 Hz	122 W	-

					Suitable for random switching
Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption	
911401595132	BBP500 G4 LED180/NW PSU A-WB	220-240 V	50 to 60 Hz	122 W	-
911401595232	BBP500 G4 LED180/CW PSU S-WB	220-240 V	50 to 60 Hz	122 W	-
911401595332	BBP500 G4 LED180/CW PSU S-MB	220-240 V	50 to 60 Hz	122 W	-
911401595432	BBP500 G4 LED180/CW PSU A-WB	220-240 V	50 to 60 Hz	122 W	-
911401595532	BBP500 G4 LED85/NW PSD S-WB	220-240 V	50 to 60 Hz	58 W	-
911401595632	BBP500 G4 LED85/NW PSD S-MB	220-240 V	50 to 60 Hz	58 W	-
911401595732	BBP500 G4 LED85/NW PSD A-WB	220-240 V	50 to 60 Hz	58 W	-
911401595832	BBP500 G4 LED85/CW PSD S-WB	220-240 V	50 to 60 Hz	58 W	-
911401595932	BBP500 G4 LED85/CW PSD S-MB	220-240 V	50 to 60 Hz	58 W	-
911401596032	BBP500 G4 LED85/CW PSD A-WB	220-240 V	50 to 60 Hz	58 W	-
911401596132	BBP500 G4 LED125/NW PSD S-WB	220-240 V	50 to 60 Hz	85 W	-
911401596232	BBP500 G4 LED125/NW PSD S-MB	220-240 V	50 to 60 Hz	85 W	-
911401596332	BBP500 G4 LED125/NW PSD A-WB	220-240 V	50 to 60 Hz	85 W	-
911401596432	BBP500 G4 LED125/CW PSD S-WB	220-240 V	50 to 60 Hz	85 W	-
911401596532	BBP500 G4 LED125/CW PSD S-MB	220-240 V	50 to 60 Hz	85 W	-
911401596632	BBP500 G4 LED125/CW PSD A-WB	220-240 V	50 to 60 Hz	85 W	-

GreenPerform Canopy Mini500 G4

	Full Product	Input	Line	Power	Suitable for random switching
Order Code	Name	Voltage	Frequency	Consumption	
911401596732	BBP500 G4 LED140/NW PSD S-WB	220-240 V	50 to 60 Hz	96 W	-
911401596832	BBP500 G4 LED140/NW PSD S-MB	220-240 V	50 to 60 Hz	96 W	-
911401596932	BBP500 G4 LED140/NW PSD A-WB	220-240 V	50 to 60 Hz	96 W	-
911401597032	BBP500 G4 LED140/CW PSD S-WB	220-240 V	50 to 60 Hz	96 W	-
911401597132	BBP500 G4 LED140/CW PSD S-MB	220-240 V	50 to 60 Hz	96 W	-
911401597232	BBP500 G4 LED140/CW PSD A-WB	220-240 V	50 to 60 Hz	96 W	-

	Full Product	Input	Line	Power	Suitable for random switching
Order Code	Name	Voltage	Frequency	Consumption	
911401597332	BBP500 G4 LED180/NW PSD S-WB	220-240 V	50 to 60 Hz	128 W	-
911401597432	BBP500 G4 LED180/NW PSD S-MB	220-240 V	50 to 60 Hz	128 W	-
911401597532	BBP500 G4 LED180/NW PSD A-WB	220-240 V	50 to 60 Hz	128 W	-
911401597632	BBP500 G4 LED180/CW PSD S-WB	220-240 V	50 to 60 Hz	128 W	-
911401597732	BBP500 G4 LED180/CW PSD S-MB	220-240 V	50 to 60 Hz	128 W	-
911401597832	BBP500 G4 LED180/CW PSD A-WB	220-240 V	50 to 60 Hz	128 W	-

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401502742	BCP500 G4 LED85/NW PSU S-WB	No	-
911401502842	BCP500 G4 LED85/NW PSU S-MB	No	-
911401502942	BCP500 G4 LED85/NW PSU A-WB	No	-
911401503042	BCP500 G4 LED85/CW PSU S-WB	No	-
911401503142	BCP500 G4 LED85/CW PSU S-MB	No	-
911401503242	BCP500 G4 LED85/CW PSU A-WB	No	-
911401503342	BCP500 G4 LED125/NW PSU S-WB	No	-
911401503442	BCP500 G4 LED125/NW PSU S-MB	No	-
911401503542	BCP500 G4 LED125/NW PSU A-WB	No	-
911401503642	BCP500 G4 LED125/CW PSU S-WB	No	-
911401503742	BCP500 G4 LED125/CW PSU S-MB	No	-
911401503842	BCP500 G4 LED125/CW PSU A-WB	No	-
911401503942	BCP500 G4 LED140/NW PSU S-WB	No	-
911401504042	BCP500 G4 LED140/NW PSU S-MB	No	-
911401504142	BCP500 G4 LED140/NW PSU A-WB	No	-
911401504242	BCP500 G4 LED140/CW PSU S-WB	No	-
911401504342	BCP500 G4 LED140/CW PSU S-MB	No	-
911401504442	BCP500 G4 LED140/CW PSU A-WB	No	-
911401504542	BCP500 G4 LED180/NW PSU S-WB	No	-
911401504642	BCP500 G4 LED180/NW PSU S-MB	No	-
911401504742	BCP500 G4 LED180/NW PSU A-WB	No	-
911401504842	BCP500 G4 LED180/CW PSU S-WB	No	-
911401504942	BCP500 G4 LED180/CW PSU S-MB	No	-
911401505042	BCP500 G4 LED180/CW PSU A-WB	No	-
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	No	-
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	No	-
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	No	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	No	-
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	No	-
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	No	-
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	No	-
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	No	-
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	No	-
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	No	-
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	No	-
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	No	-
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	No	-
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	No	-
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	No	-
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	No	-
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	No	-
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	No	-
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	No	-
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	No	-
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	No	-
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	No	-
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	No	-
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	No	-
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	No	-
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	No	-
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	No	-
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	No	-
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	No	-
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	No	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Dimmable	Maximum dim level
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	No	-
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	No	-
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	No	-
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	No	-
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	No	-
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	No	-
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	No	-
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	No	-
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	No	-
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	No	-
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	No	-
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	No	-
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	No	-
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	No	-
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	No	-
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	No	-
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	No	-
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	No	-
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	No	-
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	No	-
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	No	-
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	No	-
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	No	-
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	No	-
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	No	-
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	No	-
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	No	-
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	No	-
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	No	-
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	No	-
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	No	-
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	No	-
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	No	-
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	No	-
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	No	-
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	No	-
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	No	-
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	No	-
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	No	-
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	No	-
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	No	-
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	No	-
911401512342	BGP500 G4 LED85/NW PSU A-WB	No	-
911401512442	BGP500 G4 LED85/CW PSU A-WB	No	-
911401512542	BGP500 G4 LED125/NW PSU A-WB	No	-
911401512642	BGP500 G4 LED125/CW PSU A-WB	No	-
911401512742	BGP500 G4 LED140/NW PSU A-WB	No	-
911401512842	BGP500 G4 LED140/CW PSU A-WB	No	-
911401512942	BGP500 G4 LED180/NW PSU A-WB	No	-
911401513042	BGP500 G4 LED180/CW PSU A-WB	No	-
911401562142	BBP500 G4 LED125/NW L1S H S-WB	Yes	50%
911401562242	BBP500 G4 LED125/NW L1S H S-MB	Yes	50%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401562342	BBP500 G4 LED125/NW L1S H A-WB	Yes	50%
911401562442	BBP500 G4 LED125/CW L1S H S-WB	Yes	50%
911401562542	BBP500 G4 LED125/CW L1S H S-MB	Yes	50%
911401562642	BBP500 G4 LED125/CW L1S H A-WB	Yes	50%
911401562742	BBP500 G4 LED140/NW L1S H S-WB	Yes	50%
911401562842	BBP500 G4 LED140/NW L1S H S-MB	Yes	50%
911401562942	BBP500 G4 LED140/NW L1S H A-WB	Yes	50%
911401563042	BBP500 G4 LED140/CW L1S H S-WB	Yes	50%
911401563142	BBP500 G4 LED140/CW L1S H S-MB	Yes	50%
911401563242	BBP500 G4 LED140/CW L1S H A-WB	Yes	50%
911401563342	BBP500 G4 LED180/NW L1S H S-WB	Yes	50%
911401563442	BBP500 G4 LED180/NW L1S H S-MB	Yes	50%
911401563542	BBP500 G4 LED180/NW L1S H A-WB	Yes	50%
911401563642	BBP500 G4 LED180/CW L1S H S-WB	Yes	50%
911401563742	BBP500 G4 LED180/CW L1S H S-MB	Yes	50%
911401563842	BBP500 G4 LED180/CW L1S H A-WB	Yes	50%
911401563942	BCP500 G4 LED125/NW L1S H S-WB	Yes	50%
911401564042	BCP500 G4 LED125/NW L1S H S-MB	Yes	50%
911401564142	BCP500 G4 LED125/NW L1S H A-WB	Yes	50%
911401564242	BCP500 G4 LED125/CW L1S H S-WB	Yes	50%
911401564342	BCP500 G4 LED125/CW L1S H S-MB	Yes	50%
911401564442	BCP500 G4 LED125/CW L1S H A-WB	Yes	50%
911401564542	BCP500 G4 LED140/NW L1S H S-WB	Yes	50%
911401564642	BCP500 G4 LED140/NW L1S H S-MB	Yes	50%
911401564742	BCP500 G4 LED140/NW L1S H A-WB	Yes	50%
911401564842	BCP500 G4 LED140/CW L1S H S-WB	Yes	50%
911401564942	BCP500 G4 LED140/CW L1S H S-MB	Yes	50%
911401565042	BCP500 G4 LED140/CW L1S H A-WB	Yes	50%
911401565142	BCP500 G4 LED180/NW L1S H S-WB	Yes	50%
911401565242	BCP500 G4 LED180/NW L1S H S-MB	Yes	50%
911401565342	BCP500 G4 LED180/NW L1S H A-WB	Yes	50%
911401565442	BCP500 G4 LED180/CW L1S H S-WB	Yes	50%
911401565542	BCP500 G4 LED180/CW L1S H S-MB	Yes	50%
911401565642	BCP500 G4 LED180/CW L1S H A-WB	Yes	50%
911401505142	BCP500 G4 LED85/NW PSD S-WB	DALI	-
911401505242	BCP500 G4 LED85/NW PSD S-MB	DALI	-
911401505342	BCP500 G4 LED85/NW PSD A-WB	DALI	-
911401505442	BCP500 G4 LED85/CW PSD S-WB	DALI	-
911401505542	BCP500 G4 LED85/CW PSD S-MB	DALI	-
911401505642	BCP500 G4 LED85/CW PSD A-WB	DALI	-
911401505742	BCP500 G4 LED125/NW PSD S-WB	DALI	-
911401505842	BCP500 G4 LED125/NW PSD S-MB	DALI	-
911401505942	BCP500 G4 LED125/NW PSD A-WB	DALI	-
911401506042	BCP500 G4 LED125/CW PSD S-WB	DALI	-
911401506142	BCP500 G4 LED125/CW PSD S-MB	DALI	-
911401506242	BCP500 G4 LED125/CW PSD A-WB	DALI	-
911401506342	BCP500 G4 LED140/NW PSD S-WB	DALI	-
911401506442	BCP500 G4 LED140/NW PSD S-MB	DALI	-
911401506542	BCP500 G4 LED140/NW PSD A-WB	DALI	-
911401506642	BCP500 G4 LED140/CW PSD S-WB	DALI	-
911401506742	BCP500 G4 LED140/CW PSD S-MB	DALI	-
911401506842	BCP500 G4 LED140/CW PSD A-WB	DALI	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Dimmable	Maximum dim level
911401506942	BCP500 G4 LED180/NW PSD S-WB	DALI	-
911401507042	BCP500 G4 LED180/NW PSD S-MB	DALI	-
911401507142	BCP500 G4 LED180/NW PSD A-WB	DALI	-
911401507242	BCP500 G4 LED180/CW PSD S-WB	DALI	-
911401507342	BCP500 G4 LED180/CW PSD S-MB	DALI	-
911401507442	BCP500 G4 LED180/CW PSD A-WB	DALI	-
911401638109	BCP500 G4 LED100/850 PSU S-MB JP	No	Not applicable
911401638209	BCP500 G4 LED190/850 PSU S-MB JP	No	Not applicable
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	No	-
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	No	-
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	No	-
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	No	-
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	No	-
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	No	-
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	No	-
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	No	-
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	No	-
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	No	-
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	No	-
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	No	-
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	No	-
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	No	-
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	No	-
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	No	-
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	No	-
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	No	-
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	No	-
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	No	-
911401502342	BBP500 G4 LED180/NW PSU A-WB PC	No	-
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	No	-
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	No	-
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	No	-
911401593132	BBP500 G4 LED85/NW PSU S-WB	No	-
911401593232	BBP500 G4 LED85/NW PSU S-MB	No	-
911401593332	BBP500 G4 LED85/NW PSU A-WB	No	-
911401593432	BBP500 G4 LED85/CW PSU S-WB	No	-
911401593532	BBP500 G4 LED85/CW PSU S-MB	No	-
911401593632	BBP500 G4 LED85/CW PSU A-WB	No	-
911401593732	BBP500 G4 LED125/NW PSU S-WB	No	-
911401593832	BBP500 G4 LED125/NW PSU S-MB	No	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401593932	BBP500 G4 LED125/NW PSU A-WB	No	-
911401594032	BBP500 G4 LED125/CW PSU S-WB	No	-
911401594132	BBP500 G4 LED125/CW PSU S-MB	No	-
911401594232	BBP500 G4 LED125/CW PSU A-WB	No	-
911401594332	BBP500 G4 LED140/NW PSU S-WB	No	-
911401594432	BBP500 G4 LED140/NW PSU S-MB	No	-
911401594532	BBP500 G4 LED140/NW PSU A-WB	No	-
911401594632	BBP500 G4 LED140/CW PSU S-WB	No	-
911401594732	BBP500 G4 LED140/CW PSU S-MB	No	-
911401594832	BBP500 G4 LED140/CW PSU A-WB	No	-
911401594932	BBP500 G4 LED180/NW PSU S-WB	No	-
911401595032	BBP500 G4 LED180/NW PSU S-MB	No	-
911401595132	BBP500 G4 LED180/NW PSU A-WB	No	-
911401595232	BBP500 G4 LED180/CW PSU S-WB	No	-
911401595332	BBP500 G4 LED180/CW PSU S-MB	No	-
911401595432	BBP500 G4 LED180/CW PSU A-WB	No	-
911401595532	BBP500 G4 LED85/NW PSD S-WB	DALI	-
911401595632	BBP500 G4 LED85/NW PSD S-MB	DALI	-
911401595732	BBP500 G4 LED85/NW PSD A-WB	DALI	-
911401595832	BBP500 G4 LED85/CW PSD S-WB	DALI	-
911401595932	BBP500 G4 LED85/CW PSD S-MB	DALI	-
911401596032	BBP500 G4 LED85/CW PSD A-WB	DALI	-
911401596132	BBP500 G4 LED125/NW PSD S-WB	DALI	-
911401596232	BBP500 G4 LED125/NW PSD S-MB	DALI	-
911401596332	BBP500 G4 LED125/NW PSD A-WB	DALI	-
911401596432	BBP500 G4 LED125/CW PSD S-WB	DALI	-
911401596532	BBP500 G4 LED125/CW PSD S-MB	DALI	-
911401596632	BBP500 G4 LED125/CW PSD A-WB	DALI	-
911401596732	BBP500 G4 LED140/NW PSD S-WB	DALI	-
911401596832	BBP500 G4 LED140/NW PSD S-MB	DALI	-
911401596932	BBP500 G4 LED140/NW PSD A-WB	DALI	-
911401597032	BBP500 G4 LED140/CW PSD S-WB	DALI	-
911401597132	BBP500 G4 LED140/CW PSD S-MB	DALI	-
911401597232	BBP500 G4 LED140/CW PSD A-WB	DALI	-
911401597332	BBP500 G4 LED180/NW PSD S-WB	DALI	-
911401597432	BBP500 G4 LED180/NW PSD S-MB	DALI	-
911401597532	BBP500 G4 LED180/NW PSD A-WB	DALI	-
911401597632	BBP500 G4 LED180/CW PSD S-WB	DALI	-
911401597732	BBP500 G4 LED180/CW PSD S-MB	DALI	-
911401597832	BBP500 G4 LED180/CW PSD A-WB	DALI	-

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing	Mech. impact protection
			Color	code
911401502742	BCP500 G4 LED85/NW PSU S-WB	Clear glass	White	IK07
911401502842	BCP500 G4 LED85/NW PSU S-MB	Clear glass	White	IK07

Order Code	Full Product Name	Optical cover type	Housing	Mech. impact protection
			Color	code
911401502942	BCP500 G4 LED85/NW PSU A-WB	Clear glass	White	IK07
911401503042	BCP500 G4 LED85/CW PSU S-WB	Clear glass	White	IK07

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401503142	BCP500 G4 LED85/CW PSU S-MB	Clear glass	White	IK07
911401503242	BCP500 G4 LED85/CW PSU A-WB	Clear glass	White	IK07
911401503342	BCP500 G4 LED125/NW PSU S-WB	Clear glass	White	IK07
911401503442	BCP500 G4 LED125/NW PSU S-MB	Clear glass	White	IK07
911401503542	BCP500 G4 LED125/NW PSU A-WB	Clear glass	White	IK07
911401503642	BCP500 G4 LED125/CW PSU S-WB	Clear glass	White	IK07
911401503742	BCP500 G4 LED125/CW PSU S-MB	Clear glass	White	IK07
911401503842	BCP500 G4 LED125/CW PSU A-WB	Clear glass	White	IK07
911401503942	BCP500 G4 LED140/NW PSU S-WB	Clear glass	White	IK07
911401504042	BCP500 G4 LED140/NW PSU S-MB	Clear glass	White	IK07
911401504142	BCP500 G4 LED140/NW PSU A-WB	Clear glass	White	IK07
911401504242	BCP500 G4 LED140/CW PSU S-WB	Clear glass	White	IK07
911401504342	BCP500 G4 LED140/CW PSU S-MB	Clear glass	White	IK07
911401504442	BCP500 G4 LED140/CW PSU A-WB	Clear glass	White	IK07
911401504542	BCP500 G4 LED180/NW PSU S-WB	Clear glass	White	IK07
911401504642	BCP500 G4 LED180/NW PSU S-MB	Clear glass	White	IK07
911401504742	BCP500 G4 LED180/NW PSU A-WB	Clear glass	White	IK07
911401504842	BCP500 G4 LED180/CW PSU S-WB	Clear glass	White	IK07
911401504942	BCP500 G4 LED180/CW PSU S-MB	Clear glass	White	IK07
911401505042	BCP500 G4 LED180/CW PSU A-WB	Clear glass	White	IK07
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	Polycarbonate	White	IK08
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	Polycarbonate	White	IK08
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	Polycarbonate	White	IK08
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	Polycarbonate	White	IK08

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	Polycarbonate	White	IK08
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	Polycarbonate	White	IK08
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	Polycarbonate	White	IK08
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	Polycarbonate	White	IK08
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	Polycarbonate	White	IK08
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	Polycarbonate	White	IK08
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	Polycarbonate	White	IK08
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	Polycarbonate	White	IK08
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	Polycarbonate	White	IK08
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	Polycarbonate	White	IK08
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	Polycarbonate	White	IK08
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	Polycarbonate	White	IK08
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	Polycarbonate	White	IK08
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	Polycarbonate	White	IK08
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	Polycarbonate	White	IK08
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	Polycarbonate	White	IK08
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	Polycarbonate	White	IK08
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	Polycarbonate	White	IK08
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	Polycarbonate	White	IK08
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	Polycarbonate	White	IK08
9114015107542	BCP500 G4 LED85/NW GU5.3 S-WB	Clear glass	White	IK07
9114015107642	BCP500 G4 LED85/NW GU5.3 S-MB	Clear glass	White	IK07
9114015107742	BCP500 G4 LED85/NW GU5.3 A-WB	Clear glass	White	IK07
9114015107842	BCP500 G4 LED85/CW GU5.3 S-WB	Clear glass	White	IK07

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	Clear glass	White	IK07
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	Clear glass	White	IK07
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	Clear glass	White	IK07
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	Clear glass	White	IK07
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	Clear glass	White	IK07
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	Clear glass	White	IK07
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	Clear glass	White	IK07
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	Clear glass	White	IK07
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	Clear glass	White	IK07
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	Clear glass	White	IK07
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	Clear glass	White	IK07
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	Clear glass	White	IK07
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	Clear glass	White	IK07
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	Clear glass	White	IK07
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	Clear glass	White	IK07
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	Clear glass	White	IK07
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	Clear glass	White	IK07
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	Clear glass	White	IK07
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	Clear glass	White	IK07
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	Clear glass	White	IK07
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	Clear glass	White	IK07
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	Clear glass	White	IK07
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	Clear glass	White	IK07
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	Clear glass	White	IK07

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	Clear glass	White	IK07
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	Clear glass	White	IK07
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	Clear glass	White	IK07
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	Clear glass	White	IK07
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	Clear glass	White	IK07
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	Clear glass	White	IK07
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	Clear glass	White	IK07
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	Clear glass	White	IK07
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	Clear glass	White	IK07
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	Clear glass	White	IK07
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	Clear glass	White	IK07
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	Clear glass	White	IK07
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	Clear glass	White	IK07
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	Clear glass	White	IK07
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	Clear glass	White	IK07
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	Clear glass	White	IK07
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	Clear glass	White	IK07
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	Clear glass	White	IK07
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	Clear glass	White	IK07
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	Clear glass	White	IK07
911401512342	BGP500 G4 LED85/NW PSU A-WB	Clear glass	White	IK07
911401512442	BGP500 G4 LED85/CW PSU A-WB	Clear glass	White	IK07
911401512542	BGP500 G4 LED125/NW PSU A-WB	Clear glass	White	IK07
911401512642	BGP500 G4 LED125/CW PSU A-WB	Clear glass	White	IK07

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401512742	BGP500 G4 LED140/NW PSU A-WB	Clear glass	White	IK07
911401512842	BGP500 G4 LED140/CW PSU A-WB	Clear glass	White	IK07
911401512942	BGP500 G4 LED180/NW PSU A-WB	Clear glass	White	IK07
911401513042	BGP500 G4 LED180/CW PSU A-WB	Clear glass	White	IK07
911401562142	BBP500 G4 LED125/NW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401562242	BBP500 G4 LED125/NW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401562342	BBP500 G4 LED125/NW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401562442	BBP500 G4 LED125/CW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401562542	BBP500 G4 LED125/CW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401562642	BBP500 G4 LED125/CW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401562742	BBP500 G4 LED140/NW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401562842	BBP500 G4 LED140/NW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401562942	BBP500 G4 LED140/NW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401563042	BBP500 G4 LED140/CW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401563142	BBP500 G4 LED140/CW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401563242	BBP500 G4 LED140/CW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401563342	BBP500 G4 LED180/NW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401563442	BBP500 G4 LED180/NW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401563542	BBP500 G4 LED180/NW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401563642	BBP500 G4 LED180/CW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401563742	BBP500 G4 LED180/CW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401563842	BBP500 G4 LED180/CW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401563942	BCP500 G4 LED125/NW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401564042	BCP500 G4 LED125/NW L1S H S-MB	Clear glass	Aluminum and white	IK03

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401564142	BCP500 G4 LED125/NW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401564242	BCP500 G4 LED125/CW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401564342	BCP500 G4 LED125/CW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401564442	BCP500 G4 LED125/CW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401564542	BCP500 G4 LED140/NW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401564642	BCP500 G4 LED140/NW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401564742	BCP500 G4 LED140/NW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401564842	BCP500 G4 LED140/CW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401564942	BCP500 G4 LED140/CW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401565042	BCP500 G4 LED140/CW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401565142	BCP500 G4 LED180/NW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401565242	BCP500 G4 LED180/NW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401565342	BCP500 G4 LED180/NW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401565442	BCP500 G4 LED180/CW L1S H S-WB	Clear glass	Aluminum and white	IK03
911401565542	BCP500 G4 LED180/CW L1S H S-MB	Clear glass	Aluminum and white	IK03
911401565642	BCP500 G4 LED180/CW L1S H A-WB	Clear glass	Aluminum and white	IK03
911401505142	BCP500 G4 LED85/NW PSD S-WB	Clear glass	White	IK07
911401505242	BCP500 G4 LED85/NW PSD S-MB	Clear glass	White	IK07
911401505342	BCP500 G4 LED85/NW PSD A-WB	Clear glass	White	IK07
911401505442	BCP500 G4 LED85/CW PSD S-WB	Clear glass	White	IK07
911401505542	BCP500 G4 LED85/CW PSD S-MB	Clear glass	White	IK07
911401505642	BCP500 G4 LED85/CW PSD A-WB	Clear glass	White	IK07
911401505742	BCP500 G4 LED125/NW PSD S-WB	Clear glass	White	IK07
911401505842	BCP500 G4 LED125/NW PSD S-MB	Clear glass	White	IK07

GreenPerform Canopy Mini500 G4

				Mech. impact protection
Order Code	Full Product Name	Optical cover type	Housing Color	code
911401505942	BCP500 G4 LED125/NW PSD A-WB	Clear glass	White	IK07
911401506042	BCP500 G4 LED125/CW PSD S-WB	Clear glass	White	IK07
911401506142	BCP500 G4 LED125/CW PSD S-MB	Clear glass	White	IK07
911401506242	BCP500 G4 LED125/CW PSD A-WB	Clear glass	White	IK07
911401506342	BCP500 G4 LED140/NW PSD S-WB	Clear glass	White	IK07
911401506442	BCP500 G4 LED140/NW PSD S-MB	Clear glass	White	IK07
911401506542	BCP500 G4 LED140/NW PSD A-WB	Clear glass	White	IK07
911401506642	BCP500 G4 LED140/CW PSD S-WB	Clear glass	White	IK07
911401506742	BCP500 G4 LED140/CW PSD S-MB	Clear glass	White	IK07
911401506842	BCP500 G4 LED140/CW PSD A-WB	Clear glass	White	IK07
911401506942	BCP500 G4 LED180/NW PSD S-WB	Clear glass	White	IK07
911401507042	BCP500 G4 LED180/NW PSD S-MB	Clear glass	White	IK07
911401507142	BCP500 G4 LED180/NW PSD A-WB	Clear glass	White	IK07
911401507242	BCP500 G4 LED180/CW PSD S-WB	Clear glass	White	IK07
911401507342	BCP500 G4 LED180/CW PSD S-MB	Clear glass	White	IK07
911401507442	BCP500 G4 LED180/CW PSD A-WB	Clear glass	White	IK07
911401638109	BCP500 G4 LED100/850 PSU S-MB JP	Clear glass	Aluminum and white	IK07
911401638209	BCP500 G4 LED190/850 PSU S-MB JP	Clear glass	Aluminum and white	IK07
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	Polycarbonate	White	IK08
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	Polycarbonate	White	IK08
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	Polycarbonate	White	IK08
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	Polycarbonate	White	IK08
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	Polycarbonate	White	IK08
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	Polycarbonate	White	IK08

				Mech. impact protection
Order Code	Full Product Name	Optical cover type	Housing Color	code
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	Polycarbonate	White	IK08
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	Polycarbonate	White	IK08
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	Polycarbonate	White	IK08
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	Polycarbonate	White	IK08
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	Polycarbonate	White	IK08
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	Polycarbonate	White	IK08
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	Polycarbonate	White	IK08
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	Polycarbonate	White	IK08
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	Polycarbonate	White	IK08
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	Polycarbonate	White	IK08
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	Polycarbonate	White	IK08
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	Polycarbonate	White	IK08
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	Polycarbonate	White	IK08
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	Polycarbonate	White	IK08
911401502342	BBP500 G4 LED180/NW PSU A-WB PC	Polycarbonate	White	IK08
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	Polycarbonate	White	IK08
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	Polycarbonate	White	IK08
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	Polycarbonate	White	IK08
911401593132	BBP500 G4 LED85/NW PSU S-WB	Clear glass	White	IK07
911401593232	BBP500 G4 LED85/NW PSU S-MB	Clear glass	White	IK07
911401593332	BBP500 G4 LED85/NW PSU A-WB	Clear glass	White	IK07
911401593432	BBP500 G4 LED85/CW PSU S-WB	Clear glass	White	IK07
911401593532	BBP500 G4 LED85/CW PSU S-MB	Clear glass	White	IK07
911401593632	BBP500 G4 LED85/CW PSU A-WB	Clear glass	White	IK07

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401593732	BBP500 G4 LED125/NW PSU S-WB	Clear glass	White	IK07
911401593832	BBP500 G4 LED125/NW PSU S-MB	Clear glass	White	IK07
911401593932	BBP500 G4 LED125/NW PSU A-WB	Clear glass	White	IK07
911401594032	BBP500 G4 LED125/CW PSU S-WB	Clear glass	White	IK07
911401594132	BBP500 G4 LED125/CW PSU S-MB	Clear glass	White	IK07
911401594232	BBP500 G4 LED125/CW PSU A-WB	Clear glass	White	IK07
911401594332	BBP500 G4 LED140/NW PSU S-WB	Clear glass	White	IK07
911401594432	BBP500 G4 LED140/NW PSU S-MB	Clear glass	White	IK07
911401594532	BBP500 G4 LED140/NW PSU A-WB	Clear glass	White	IK07
911401594632	BBP500 G4 LED140/CW PSU S-WB	Clear glass	White	IK07
911401594732	BBP500 G4 LED140/CW PSU S-MB	Clear glass	White	IK07
911401594832	BBP500 G4 LED140/CW PSU A-WB	Clear glass	White	IK07
911401594932	BBP500 G4 LED180/NW PSU S-WB	Clear glass	White	IK07
911401595032	BBP500 G4 LED180/NW PSU S-MB	Clear glass	White	IK07
911401595132	BBP500 G4 LED180/NW PSU A-WB	Clear glass	White	IK07
911401595232	BBP500 G4 LED180/CW PSU S-WB	Clear glass	White	IK07
911401595332	BBP500 G4 LED180/CW PSU S-MB	Clear glass	White	IK07
911401595432	BBP500 G4 LED180/CW PSU A-WB	Clear glass	White	IK07
911401595532	BBP500 G4 LED85/NW PSD S-WB	Clear glass	White	IK07
911401595632	BBP500 G4 LED85/NW PSD S-MB	Clear glass	White	IK07
911401595732	BBP500 G4 LED85/NW PSD A-WB	Clear glass	White	IK07

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401595832	BBP500 G4 LED85/CW PSD S-WB	Clear glass	White	IK07
911401595932	BBP500 G4 LED85/CW PSD S-MB	Clear glass	White	IK07
911401596032	BBP500 G4 LED85/CW PSD A-WB	Clear glass	White	IK07
911401596132	BBP500 G4 LED125/NW PSD S-WB	Clear glass	White	IK07
911401596232	BBP500 G4 LED125/NW PSD S-MB	Clear glass	White	IK07
911401596332	BBP500 G4 LED125/NW PSD A-WB	Clear glass	White	IK07
911401596432	BBP500 G4 LED125/CW PSD S-WB	Clear glass	White	IK07
911401596532	BBP500 G4 LED125/CW PSD S-MB	Clear glass	White	IK07
911401596632	BBP500 G4 LED125/CW PSD A-WB	Clear glass	White	IK07
911401596732	BBP500 G4 LED140/NW PSD S-WB	Clear glass	White	IK07
911401596832	BBP500 G4 LED140/NW PSD S-MB	Clear glass	White	IK07
911401596932	BBP500 G4 LED140/NW PSD A-WB	Clear glass	White	IK07
911401597032	BBP500 G4 LED140/CW PSD S-WB	Clear glass	White	IK07
911401597132	BBP500 G4 LED140/CW PSD S-MB	Clear glass	White	IK07
911401597232	BBP500 G4 LED140/CW PSD A-WB	Clear glass	White	IK07
911401597332	BBP500 G4 LED180/NW PSD S-WB	Clear glass	White	IK07
911401597432	BBP500 G4 LED180/NW PSD S-MB	Clear glass	White	IK07
911401597532	BBP500 G4 LED180/NW PSD A-WB	Clear glass	White	IK07
911401597632	BBP500 G4 LED180/CW PSD S-WB	Clear glass	White	IK07
911401597732	BBP500 G4 LED180/CW PSD S-MB	Clear glass	White	IK07
911401597832	BBP500 G4 LED180/CW PSD A-WB	Clear glass	White	IK07

Approval and Application

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401502742	BCP500 G4 LED85/NW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401502842	BCP500 G4 LED85/NW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401502942	BCP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401503042	BCP500 G4 LED85/CW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401503142	BCP500 G4 LED85/CW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401503242	BCP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401503342	BCP500 G4 LED125/NW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401503442	BCP500 G4 LED125/NW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401503542	BCP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401503642	BCP500 G4 LED125/CW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401503742	BCP500 G4 LED125/CW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401503842	BCP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401503942	BCP500 G4 LED140/NW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401504042	BCP500 G4 LED140/NW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401504142	BCP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401504242	BCP500 G4 LED140/CW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401504342	BCP500 G4 LED140/CW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401504442	BCP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401504542	BCP500 G4 LED180/NW PSU S-WB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401504642	BCP500 G4 LED180/NW PSU S-MB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401504742	BCP500 G4 LED180/NW PSU A-WB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401504842	BCP500 G4 LED180/CW PSU S-WB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401504942	BCP500 G4 LED180/CW PSU S-MB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401505042	BCP500 G4 LED180/CW PSU A-WB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401512342	BGP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	Yes	-	-
911401512442	BGP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	Yes	-	-
911401512542	BGP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	Yes	-	-
911401512642	BGP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	Yes	-	-
911401512742	BGP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	Yes	-	-
911401512842	BGP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	Yes	-	-
911401512942	BGP500 G4 LED180/NW PSU A-WB	-40 to +50 °C	Yes	-	-
911401513042	BGP500 G4 LED180/CW PSU A-WB	-40 to +50 °C	Yes	-	-
911401562142	BBP500 G4 LED125/NW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401562242	BBP500 G4 LED125/NW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401562342	BBP500 G4 LED125/NW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401562442	BBP500 G4 LED125/CW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401562542	BBP500 G4 LED125/CW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401562642	BBP500 G4 LED125/CW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401562742	BBP500 G4 LED140/NW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401562842	BBP500 G4 LED140/NW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401562942	BBP500 G4 LED140/NW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401563042	BBP500 G4 LED140/CW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401563142	BBP500 G4 LED140/CW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401563242	BBP500 G4 LED140/CW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401563342	BBP500 G4 LED180/NW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401563442	BBP500 G4 LED180/NW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401563542	BBP500 G4 LED180/NW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401563642	BBP500 G4 LED180/CW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401563742	BBP500 G4 LED180/CW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401563842	BBP500 G4 LED180/CW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401563942	BCP500 G4 LED125/NW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401564042	BCP500 G4 LED125/NW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401564142	BCP500 G4 LED125/NW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401564242	BCP500 G4 LED125/CW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401564342	BCP500 G4 LED125/CW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401564442	BCP500 G4 LED125/CW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401564542	BCP500 G4 LED140/NW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401564642	BCP500 G4 LED140/NW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401564742	BCP500 G4 LED140/NW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401564842	BCP500 G4 LED140/CW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401564942	BCP500 G4 LED140/CW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401565042	BCP500 G4 LED140/CW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401565142	BCP500 G4 LED180/NW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401565242	BCP500 G4 LED180/NW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401565342	BCP500 G4 LED180/NW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401565442	BCP500 G4 LED180/CW L1S H S-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401565542	BCP500 G4 LED180/CW L1S H S-MB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401565642	BCP500 G4 LED180/CW L1S H A-WB	-20 to +45 °C	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401505142	BCP500 G4 LED85/NW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401505242	BCP500 G4 LED85/NW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401505342	BCP500 G4 LED85/NW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401505442	BCP500 G4 LED85/CW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401505542	BCP500 G4 LED85/CW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401505642	BCP500 G4 LED85/CW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401505742	BCP500 G4 LED125/NW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401505842	BCP500 G4 LED125/NW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401505942	BCP500 G4 LED125/NW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401506042	BCP500 G4 LED125/CW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401506142	BCP500 G4 LED125/CW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401506242	BCP500 G4 LED125/CW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401506342	BCP500 G4 LED140/NW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401506442	BCP500 G4 LED140/NW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401506542	BCP500 G4 LED140/NW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401506642	BCP500 G4 LED140/CW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401506742	BCP500 G4 LED140/CW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401506842	BCP500 G4 LED140/CW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401506942	BCP500 G4 LED180/NW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401507042	BCP500 G4 LED180/NW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401507142	BCP500 G4 LED180/NW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401507242	BCP500 G4 LED180/CW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401507342	BCP500 G4 LED180/CW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401507442	BCP500 G4 LED180/CW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401638109	BCP500 G4 LED100/850 PSU S-MB JP	-30 °C to 45 °C	No	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401638209	BCP500 G4 LED190/850 PSU S-MB JP	-30 °C to 45 °C	No	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401502342	BBP500 G4 LED180/NW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	-20 to +40 °C	Yes	For mounting on normally flammable surfaces	-
911401593132	BBP500 G4 LED85/NW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401593232	BBP500 G4 LED85/NW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401593332	BBP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401593432	BBP500 G4 LED85/CW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401593532	BBP500 G4 LED85/CW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401593632	BBP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401593732	BBP500 G4 LED125/NW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401593832	BBP500 G4 LED125/NW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401593932	BBP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401594032	BBP500 G4 LED125/CW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401594132	BBP500 G4 LED125/CW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401594232	BBP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401594332	BBP500 G4 LED140/NW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401594432	BBP500 G4 LED140/NW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401594532	BBP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401594632	BBP500 G4 LED140/CW PSU S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401594732	BBP500 G4 LED140/CW PSU S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401594832	BBP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401594932	BBP500 G4 LED180/NW PSU S-WB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401595032	BBP500 G4 LED180/NW PSU S-MB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401595132	BBP500 G4 LED180/NW PSU A-WB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401595232	BBP500 G4 LED180/CW PSU S-WB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401595332	BBP500 G4 LED180/CW PSU S-MB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401595432	BBP500 G4 LED180/CW PSU A-WB	-40 to +45 °C	Yes	For mounting on normally flammable surfaces	-
911401595532	BBP500 G4 LED85/NW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401595632	BBP500 G4 LED85/NW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401595732	BBP500 G4 LED85/NW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401595832	BBP500 G4 LED85/CW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401595932	BBP500 G4 LED85/CW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401596032	BBP500 G4 LED85/CW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401596132	BBP500 G4 LED125/NW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401596232	BBP500 G4 LED125/NW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401596332	BBP500 G4 LED125/NW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401596432	BBP500 G4 LED125/CW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401596532	BBP500 G4 LED125/CW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401596632	BBP500 G4 LED125/CW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401596732	BBP500 G4 LED140/NW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401596832	BBP500 G4 LED140/NW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401596932	BBP500 G4 LED140/NW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401597032	BBP500 G4 LED140/CW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401597132	BBP500 G4 LED140/CW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401597232	BBP500 G4 LED140/CW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401597332	BBP500 G4 LED180/NW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401597432	BBP500 G4 LED180/NW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401597532	BBP500 G4 LED180/NW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401597632	BBP500 G4 LED180/CW PSD S-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-

Order Code	Full Product Name	Ambient temperature range	CE mark	Flammability mark	Glow-wire test
911401597732	BBP500 G4 LED180/CW PSD S-MB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-
911401597832	BBP500 G4 LED180/CW PSD A-WB	-40 to +50 °C	Yes	For mounting on normally flammable surfaces	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401502742	BCP500 G4 LED85/NW PSU S-WB	-
911401502842	BCP500 G4 LED85/NW PSU S-MB	-
911401502942	BCP500 G4 LED85/NW PSU A-WB	-
911401503042	BCP500 G4 LED85/CW PSU S-WB	-
911401503142	BCP500 G4 LED85/CW PSU S-MB	-
911401503242	BCP500 G4 LED85/CW PSU A-WB	-
911401503342	BCP500 G4 LED125/NW PSU S-WB	-
911401503442	BCP500 G4 LED125/NW PSU S-MB	-
911401503542	BCP500 G4 LED125/NW PSU A-WB	-
911401503642	BCP500 G4 LED125/CW PSU S-WB	-
911401503742	BCP500 G4 LED125/CW PSU S-MB	-
911401503842	BCP500 G4 LED125/CW PSU A-WB	-
911401503942	BCP500 G4 LED140/NW PSU S-WB	-
911401504042	BCP500 G4 LED140/NW PSU S-MB	-
911401504142	BCP500 G4 LED140/NW PSU A-WB	-
911401504242	BCP500 G4 LED140/CW PSU S-WB	-
911401504342	BCP500 G4 LED140/CW PSU S-MB	-
911401504442	BCP500 G4 LED140/CW PSU A-WB	-
911401504542	BCP500 G4 LED180/NW PSU S-WB	-
911401504642	BCP500 G4 LED180/NW PSU S-MB	-
911401504742	BCP500 G4 LED180/NW PSU A-WB	-
911401504842	BCP500 G4 LED180/CW PSU S-WB	-
911401504942	BCP500 G4 LED180/CW PSU S-MB	-
911401505042	BCP500 G4 LED180/CW PSU A-WB	-
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	-
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	-
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	-
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	-
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	-
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	-
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	-
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	-
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	-
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	-
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	-
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	-
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	-
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	-
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	-
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	-

Order Code	Full Product Name	Initial chromaticity
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	-
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	-
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	-
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	-
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	-
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	-
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	-
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	-
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	-
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	-
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	-
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	-
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	-
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	-
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	-
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	-
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	-
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	-
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	-
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	-
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	-
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	-
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	-
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	-
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	-
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	-
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	-
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	-
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	-
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	-
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	-
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	-
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	-
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	-
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	-
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	-
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	-
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	-
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	-
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Initial chromaticity
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	-
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	-
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	-
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	-
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	-
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	-
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	-
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	-
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	-
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	-
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	-
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	-
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	-
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	-
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	-
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	-
911401512342	BGP500 G4 LED85/NW PSU A-WB	-
911401512442	BGP500 G4 LED85/CW PSU A-WB	-
911401512542	BGP500 G4 LED125/NW PSU A-WB	-
911401512642	BGP500 G4 LED125/CW PSU A-WB	-
911401512742	BGP500 G4 LED140/NW PSU A-WB	-
911401512842	BGP500 G4 LED140/CW PSU A-WB	-
911401512942	BGP500 G4 LED180/NW PSU A-WB	-
911401513042	BGP500 G4 LED180/CW PSU A-WB	-
911401562142	BBP500 G4 LED125/NW L1S H S-WB	(0.3818, 0.3797) SDCM≤5
911401562242	BBP500 G4 LED125/NW L1S H S-MB	(0.3818, 0.3797) SDCM≤5
911401562342	BBP500 G4 LED125/NW L1S H A-WB	(0.3818, 0.3797) SDCM≤5
911401562442	BBP500 G4 LED125/CW L1S H S-WB	(0.3123, 0.3282) SDCM≤5
911401562542	BBP500 G4 LED125/CW L1S H S-MB	(0.3123, 0.3282) SDCM≤5
911401562642	BBP500 G4 LED125/CW L1S H A-WB	(0.3123, 0.3282) SDCM≤5
911401562742	BBP500 G4 LED140/NW L1S H S-WB	(0.3818, 0.3797) SDCM≤5
911401562842	BBP500 G4 LED140/NW L1S H S-MB	(0.3818, 0.3797) SDCM≤5
911401562942	BBP500 G4 LED140/NW L1S H A-WB	(0.3818, 0.3797) SDCM≤5
911401563042	BBP500 G4 LED140/CW L1S H S-WB	(0.3123, 0.3282) SDCM≤5
911401563142	BBP500 G4 LED140/CW L1S H S-MB	(0.3123, 0.3282) SDCM≤5
911401563242	BBP500 G4 LED140/CW L1S H A-WB	(0.3123, 0.3282) SDCM≤5
911401563342	BBP500 G4 LED180/NW L1S H S-WB	(0.3818, 0.3797) SDCM≤5
911401563442	BBP500 G4 LED180/NW L1S H S-MB	(0.3818, 0.3797) SDCM≤5

Order Code	Full Product Name	Initial chromaticity
911401563542	BBP500 G4 LED180/NW L1S H A-WB	(0.3818, 0.3797) SDCM≤5
911401563642	BBP500 G4 LED180/CW L1S H S-WB	(0.3123, 0.3282) SDCM≤5
911401563742	BBP500 G4 LED180/CW L1S H S-MB	(0.3123, 0.3282) SDCM≤5
911401563842	BBP500 G4 LED180/CW L1S H A-WB	(0.3123, 0.3282) SDCM≤5
911401563942	BCP500 G4 LED125/NW L1S H S-WB	(0.3818, 0.3797) SDCM≤5
911401564042	BCP500 G4 LED125/NW L1S H S-MB	(0.3818, 0.3797) SDCM≤5
911401564142	BCP500 G4 LED125/NW L1S H A-WB	(0.3818, 0.3797) SDCM≤5
911401564242	BCP500 G4 LED125/CW L1S H S-WB	(0.3123, 0.3282) SDCM≤5
911401564342	BCP500 G4 LED125/CW L1S H S-MB	(0.3123, 0.3282) SDCM≤5
911401564442	BCP500 G4 LED125/CW L1S H A-WB	(0.3123, 0.3282) SDCM≤5
911401564542	BCP500 G4 LED140/NW L1S H S-WB	(0.3818, 0.3797) SDCM≤5
911401564642	BCP500 G4 LED140/NW L1S H S-MB	(0.3818, 0.3797) SDCM≤5
911401564742	BCP500 G4 LED140/NW L1S H A-WB	(0.3818, 0.3797) SDCM≤5
911401564842	BCP500 G4 LED140/CW L1S H S-WB	(0.3123, 0.3282) SDCM≤5
911401564942	BCP500 G4 LED140/CW L1S H S-MB	(0.3123, 0.3282) SDCM≤5
911401565042	BCP500 G4 LED140/CW L1S H A-WB	(0.3123, 0.3282) SDCM≤5
911401565142	BCP500 G4 LED180/NW L1S H S-WB	(0.3818, 0.3797) SDCM≤5
911401565242	BCP500 G4 LED180/NW L1S H S-MB	(0.3818, 0.3797) SDCM≤5
911401565342	BCP500 G4 LED180/NW L1S H A-WB	(0.3818, 0.3797) SDCM≤5
911401565442	BCP500 G4 LED180/CW L1S H S-WB	(0.3123, 0.3282) SDCM≤5
911401565542	BCP500 G4 LED180/CW L1S H S-MB	(0.3123, 0.3282) SDCM≤5
911401565642	BCP500 G4 LED180/CW L1S H A-WB	(0.3123, 0.3282) SDCM≤5
911401505142	BCP500 G4 LED85/NW PSD S-WB	-
911401505242	BCP500 G4 LED85/NW PSD S-MB	-
911401505342	BCP500 G4 LED85/NW PSD A-WB	-
911401505442	BCP500 G4 LED85/CW PSD S-WB	-
911401505542	BCP500 G4 LED85/CW PSD S-MB	-
911401505642	BCP500 G4 LED85/CW PSD A-WB	-
911401505742	BCP500 G4 LED125/NW PSD S-WB	-
911401505842	BCP500 G4 LED125/NW PSD S-MB	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Initial chromaticity
911401505942	BCP500 G4 LED125/NW PSD A-WB	-
911401506042	BCP500 G4 LED125/CW PSD S-WB	-
911401506142	BCP500 G4 LED125/CW PSD S-MB	-
911401506242	BCP500 G4 LED125/CW PSD A-WB	-
911401506342	BCP500 G4 LED140/NW PSD S-WB	-
911401506442	BCP500 G4 LED140/NW PSD S-MB	-
911401506542	BCP500 G4 LED140/NW PSD A-WB	-
911401506642	BCP500 G4 LED140/CW PSD S-WB	-
911401506742	BCP500 G4 LED140/CW PSD S-MB	-
911401506842	BCP500 G4 LED140/CW PSD A-WB	-
911401506942	BCP500 G4 LED180/NW PSD S-WB	-
911401507042	BCP500 G4 LED180/NW PSD S-MB	-
911401507142	BCP500 G4 LED180/NW PSD A-WB	-
911401507242	BCP500 G4 LED180/CW PSD S-WB	-
911401507342	BCP500 G4 LED180/CW PSD S-MB	-
911401507442	BCP500 G4 LED180/CW PSD A-WB	-
911401638109	BCP500 G4 LED100/850 PSU S-MB JP	(0.3435, 0.3553)
911401638209	BCP500 G4 LED190/850 PSU S-MB JP	(0.3435, 0.3553)
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	-
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	-
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	-
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	-
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	-
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	-
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	-
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	-
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	-
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	-
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	-
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	-
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	-
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	-
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	-
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	-
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	-
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	-
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	-
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	-
911401502342	BBP500 G4 LED180/NW PSU A-WB PC	-
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	-
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	-
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	-
911401593132	BBP500 G4 LED85/NW PSU S-WB	-
911401593232	BBP500 G4 LED85/NW PSU S-MB	-
911401593332	BBP500 G4 LED85/NW PSU A-WB	-

Order Code	Full Product Name	Initial chromaticity
911401593432	BBP500 G4 LED85/CW PSU S-WB	-
911401593532	BBP500 G4 LED85/CW PSU S-MB	-
911401593632	BBP500 G4 LED85/CW PSU A-WB	-
911401593732	BBP500 G4 LED125/NW PSU S-WB	-
911401593832	BBP500 G4 LED125/NW PSU S-MB	-
911401593932	BBP500 G4 LED125/NW PSU A-WB	-
911401594032	BBP500 G4 LED125/CW PSU S-WB	-
911401594132	BBP500 G4 LED125/CW PSU S-MB	-
911401594232	BBP500 G4 LED125/CW PSU A-WB	-
911401594332	BBP500 G4 LED140/NW PSU S-WB	-
911401594432	BBP500 G4 LED140/NW PSU S-MB	-
911401594532	BBP500 G4 LED140/NW PSU A-WB	-
911401594632	BBP500 G4 LED140/CW PSU S-WB	-
911401594732	BBP500 G4 LED140/CW PSU S-MB	-
911401594832	BBP500 G4 LED140/CW PSU A-WB	-
911401594932	BBP500 G4 LED180/NW PSU S-WB	-
911401595032	BBP500 G4 LED180/NW PSU S-MB	-
911401595132	BBP500 G4 LED180/NW PSU A-WB	-
911401595232	BBP500 G4 LED180/CW PSU S-WB	-
911401595332	BBP500 G4 LED180/CW PSU S-MB	-
911401595432	BBP500 G4 LED180/CW PSU A-WB	-
911401595532	BBP500 G4 LED85/NW PSD S-WB	-
911401595632	BBP500 G4 LED85/NW PSD S-MB	-
911401595732	BBP500 G4 LED85/NW PSD A-WB	-
911401595832	BBP500 G4 LED85/CW PSD S-WB	-
911401595932	BBP500 G4 LED85/CW PSD S-MB	-
911401596032	BBP500 G4 LED85/CW PSD A-WB	-
911401596132	BBP500 G4 LED125/NW PSD S-WB	-
911401596232	BBP500 G4 LED125/NW PSD S-MB	-
911401596332	BBP500 G4 LED125/NW PSD A-WB	-
911401596432	BBP500 G4 LED125/CW PSD S-WB	-
911401596532	BBP500 G4 LED125/CW PSD S-MB	-
911401596632	BBP500 G4 LED125/CW PSD A-WB	-
911401596732	BBP500 G4 LED140/NW PSD S-WB	-
911401596832	BBP500 G4 LED140/NW PSD S-MB	-
911401596932	BBP500 G4 LED140/NW PSD A-WB	-
911401597032	BBP500 G4 LED140/CW PSD S-WB	-
911401597132	BBP500 G4 LED140/CW PSD S-MB	-
911401597232	BBP500 G4 LED140/CW PSD A-WB	-
911401597332	BBP500 G4 LED180/NW PSD S-WB	-
911401597432	BBP500 G4 LED180/NW PSD S-MB	-
911401597532	BBP500 G4 LED180/NW PSD A-WB	-
911401597632	BBP500 G4 LED180/CW PSD S-WB	-
911401597732	BBP500 G4 LED180/CW PSD S-MB	-
911401597832	BBP500 G4 LED180/CW PSD A-WB	-

GreenPerform Canopy Mini500 G4

