



Philips GreenPerform Canopy Mini500 Gen4: A high- performance, versatile, energy- saving LED

GreenPerform Canopy Mini500 G4

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

Benefits

- Excellent energy savings
- Long-term quality and reliability
- Choice of optics
- Flexible installation options
- Range of control and connectivity platforms

GreenPerform Canopy Mini500 G4

Features

- Up to 160 lm/W system efficacy
- 60,000 hours lifetime @Ta 35°C
- Outdoor and edge area (Asymmetry WB), general area (WB), emphasizing and limited area (NB)
- Recessed (BBP), Surface & frame (BCP), Pole (BGP)
- DALI control, GU5.3 for emergency lighting, EcoSet sensor

Application



- Petrol and Convenience
- Parking Garages
- Food Processing

Specifications

Mounting type	Recessed
	Surface
	Pole
Operating Temperature range	- 40 to +50 °C
Light Source	LED
Mains Voltage	2320-240V / 50-60Hz
Mains connection	Flying cable
Mechanical Accessories	Clamp
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
Control system input	DALI
Material	Housing: die-cast aluminium
Main color of the luminaire	RAL9003
Flicker / Pst / SVM	<3.2% / 0.5 / 0.4
Luminous flux	8.5klm - 18klm
Power consumption	53W - 128W
Luminaire efficacy	Up to 160lm/W
Correlated color temperature - CCT	4000K 6000K


Color Rendering index - 80	
CRI	
Beam angle	S-WB: 115°
	S-MB: 90°
	A-WB: 110°*80°
Optical cover/lens	Lens: PC
material	Cover: Glass
Optical cover/lens	Clear
finish	
Protection Class	Class I
IEC61140	
Mechanical impact	IK07
protection	
Ingress protection	IP65
Driver replaceable	Yes
Installation	Recessed
	Surface
	Pole

Dimensional drawing



GreenPerform Canopy Mini500 G4

Dimensional drawing



General Information	
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Housing Color	White
Ingress protection code	IP65
Approval and Application	
CE mark	Yes
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
54762900	BCP500 G4 LED85/NW PSU S-WB	4000 K	160 lm/W	8,496 lm
54855800	BCP500 G4 LED85/NW PSU S-MB	4000 K	160 lm/W	8,496 lm
54828200	BCP500 G4 LED85/NW PSU A-WB	4000 K	160 lm/W	8,496 lm
54793300	BCP500 G4 LED85/CW PSU S-WB	6500 K	160 lm/W	8,496 lm
54684400	BCP500 G4 LED85/CW PSU S-MB	6500 K	160 lm/W	8,496 lm
54764300	BCP500 G4 LED85/CW PSU A-WB	6500 K	160 lm/W	8,496 lm
54857200	BCP500 G4 LED125/NW PSU S-WB	4000 K	159 lm/W	12,638 lm
54830500	BCP500 G4 LED125/NW PSU S-MB	4000 K	159 lm/W	12,638 lm
54721600	BCP500 G4 LED125/NW PSU A-WB	4000 K	159 lm/W	12,638 lm
54801500	BCP500 G4 LED125/CW PSU S-WB	6500 K	159 lm/W	12,638 lm
54693600	BCP500 G4 LED125/CW PSU S-MB	6500 K	159 lm/W	12,638 lm
54775900	BCP500 G4 LED125/CW PSU A-WB	6500 K	159 lm/W	12,638 lm
54738400	BCP500 G4 LED140/NW PSU S-WB	4000 K	155 lm/W	14,079 lm
54723000	BCP500 G4 LED140/NW PSU S-MB	4000 K	155 lm/W	14,079 lm
54803900	BCP500 G4 LED140/NW PSU A-WB	4000 K	155 lm/W	14,079 lm
51909100	BCP500 G4 LED140/CW PSU S-WB	6500 K	155 lm/W	14,079 lm
54777300	BCP500 G4 LED140/CW PSU S-MB	6500 K	155 lm/W	14,079 lm
54740700	BCP500 G4 LED140/CW PSU A-WB	6500 K	155 lm/W	14,079 lm
54766700	BCP500 G4 LED180/NW PSU S-WB	4000 K	148 lm/W	18,066 lm
54860200	BCP500 G4 LED180/NW PSU S-MB	4000 K	148 lm/W	18,066 lm
54833600	BCP500 G4 LED180/NW PSU A-WB	4000 K	148 lm/W	18,066 lm
54724700	BCP500 G4 LED180/CW PSU S-WB	6500 K	148 lm/W	18,066 lm
54804600	BCP500 G4 LED180/CW PSU S-MB	6500 K	148 lm/W	18,066 lm
54768100	BCP500 G4 LED180/CW PSU A-WB	6500 K	148 lm/W	18,066 lm
54704900	BCP500 G4 LED85/NW PSU S-WB	4000 K	157 lm/W	8,313 lm
	PC			
54751300	BCP500 G4 LED85/NW PSU S-MB	4000 K	157 lm/W	8,313 lm
	PC			
54846600	BCP500 G4 LED85/NW PSU A-WB	4000 K	157 lm/W	8,313 lm
	PC			
54819000	BCP500 G4 LED85/CW PSU S-WB	6500 K	157 lm/W	8,313 lm
	PC			
54710000	BCP500 G4 LED85/CW PSU S-MB	6500 K	157 lm/W	8,313 lm
	PC			
54735300	BCP500 G4 LED85/CW PSU A-WB	6500 K	157 lm/W	8,313 lm
	PC			
54815200	BCP500 G4 LED125/NW PSU S-WB	4000 K	156 lm/W	12,366 lm
	PC			
54705600	BCP500 G4 LED125/NW PSU S-MB	4000 K	156 lm/W	12,366 lm
	PC			
54672100	BCP500 G4 LED125/NW PSU A-WB	4000 K	156 lm/W	12,366 lm
	PC			
54752000	BCP500 G4 LED125/CW PSU S-WB	6500 K	156 lm/W	12,366 lm
	PC			
54847300	BCP500 G4 LED125/CW PSU S-MB	6500 K	156 lm/W	12,366 lm
	PC			
54816900	BCP500 G4 LED125/CW PSU A-WB	6500 K	156 lm/W	12,366 lm
	PC			
54706300	BCP500 G4 LED140/NW PSU S-WB	4000 K	152 lm/W	13,777 lm
	PC			

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
54673800	BCP500 G4 LED140/NW PSU S-MB PC	4000 K	152 lm/W	13,777 lm
54753700	BCP500 G4 LED140/NW PSU A-WB PC	4000 K	152 lm/W	13,777 lm
54848000	BCP500 G4 LED140/CW PSU S-WB PC	6500 K	152 lm/W	13,777 lm
54820600	BCP500 G4 LED140/CW PSU S-MB PC	6500 K	152 lm/W	13,777 lm
54711700	BCP500 G4 LED140/CW PSU A-WB PC	6500 K	152 lm/W	13,777 lm
54736000	BCP500 G4 LED180/NW PSU S-WB PC	4000 K	145 lm/W	17,677 lm
54817600	BCP500 G4 LED180/NW PSU S-MB PC	4000 K	145 lm/W	17,677 lm
54707000	BCP500 G4 LED180/NW PSU A-WB PC	4000 K	145 lm/W	17,677 lm
54821300	BCP500 G4 LED180/CW PSU S-WB PC	6500 K	145 lm/W	17,677 lm
54712400	BCP500 G4 LED180/CW PSU S-MB PC	6500 K	145 lm/W	17,677 lm
54737700	BCP500 G4 LED180/CW PSU A-WB PC	6500 K	145 lm/W	17,677 lm
54747600	BCP500 G4 LED85/NW GU5.3 S-WB	4000 K	160 lm/W	8,496 lm
54774200	BCP500 G4 LED85/NW GU5.3 S-MB	4000 K	160 lm/W	8,496 lm
54868800	BCP500 G4 LED85/NW GU5.3 A-WB	4000 K	160 lm/W	8,496 lm
54840400	BCP500 G4 LED85/CW GU5.3 S-WB	6500 K	160 lm/W	8,496 lm
54732200	BCP500 G4 LED85/CW GU5.3 S-MB	6500 K	160 lm/W	8,496 lm
54748300	BCP500 G4 LED85/CW GU5.3 A-WB	6500 K	160 lm/W	8,496 lm
54843500	BCP500 G4 LED125/NW GU5.3 S-WB	4000 K	159 lm/W	12,638 lm
54869500	BCP500 G4 LED125/NW GU5.3 S-MB	4000 K	159 lm/W	12,638 lm
54841100	BCP500 G4 LED125/NW GU5.3 A-WB	4000 K	159 lm/W	12,638 lm
54733900	BCP500 G4 LED125/CW GU5.3 S-WB	6500 K	159 lm/W	12,638 lm
54812100	BCP500 G4 LED125/CW GU5.3 S-MB	6500 K	159 lm/W	12,638 lm
54702500	BCP500 G4 LED125/CW GU5.3 A-WB	6500 K	159 lm/W	12,638 lm
54786500	BCP500 G4 LED140/NW GU5.3 S-WB	4000 K	155 lm/W	14,079 lm
54749000	BCP500 G4 LED140/NW GU5.3 S-MB	4000 K	155 lm/W	14,079 lm
54844200	BCP500 G4 LED140/NW GU5.3 A-WB	4000 K	155 lm/W	14,079 lm
54813800	BCP500 G4 LED140/CW GU5.3 S-WB	6500 K	155 lm/W	14,079 lm
54703200	BCP500 G4 LED140/CW GU5.3 S-MB	6500 K	155 lm/W	14,079 lm
54671400	BCP500 G4 LED140/CW GU5.3 A-WB	6500 K	155 lm/W	14,079 lm

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
54750600	BCP500 G4 LED180/NW GU5.3 S-WB	4000 K	148 lm/W	18,066 lm
54845900	BCP500 G4 LED180/NW GU5.3 S-MB	4000 K	148 lm/W	18,066 lm
54870100	BCP500 G4 LED180/NW GU5.3 A-WB	4000 K	148 lm/W	18,066 lm
54842800	BCP500 G4 LED180/CW GU5.3 S-WB	6500 K	148 lm/W	18,066 lm
54734600	BCP500 G4 LED180/CW GU5.3 S-MB	6500 K	148 lm/W	18,066 lm
54814500	BCP500 G4 LED180/CW GU5.3 A-WB	6500 K	148 lm/W	18,066 lm
54676900	BBP500 G4 LED180/CW GU5.3 S-WB	6500 K	148 lm/W	18,066 lm
54756800	BBP500 G4 LED180/CW GU5.3 S-MB	6500 K	148 lm/W	18,066 lm
54850300	BBP500 G4 LED180/CW GU5.3 A-WB	6500 K	148 lm/W	18,066 lm
54742100	BBP500 G4 LED85/NW GU5.3 S-WB	4000 K	160 lm/W	8,496 lm
54727800	BBP500 G4 LED85/NW GU5.3 S-MB	4000 K	160 lm/W	8,496 lm
54807700	BBP500 G4 LED85/NW GU5.3 A-WB	4000 K	160 lm/W	8,496 lm
54697400	BBP500 G4 LED85/CW GU5.3 S-WB	6500 K	160 lm/W	8,496 lm
54781000	BBP500 G4 LED85/CW GU5.3 S-MB	6500 K	160 lm/W	8,496 lm
54744500	BBP500 G4 LED85/CW GU5.3 A-WB	6500 K	160 lm/W	8,496 lm
54770400	BBP500 G4 LED125/NW GU5.3 S-WB	4000 K	159 lm/W	12,638 lm
54864000	BBP500 G4 LED125/NW GU5.3 S-MB	4000 K	159 lm/W	12,638 lm
54836700	BBP500 G4 LED125/NW GU5.3 A-WB	4000 K	159 lm/W	12,638 lm
54728500	BBP500 G4 LED125/CW GU5.3 S-WB	6500 K	159 lm/W	12,638 lm
54808400	BBP500 G4 LED125/CW GU5.3 S-MB	6500 K	159 lm/W	12,638 lm
54772800	BBP500 G4 LED125/CW GU5.3 A-WB	6500 K	159 lm/W	12,638 lm
54866400	BBP500 G4 LED140/NW GU5.3 S-WB	4000 K	155 lm/W	14,079 lm
54838100	BBP500 G4 LED140/NW GU5.3 S-MB	4000 K	155 lm/W	14,079 lm
54730800	BBP500 G4 LED140/NW GU5.3 A-WB	4000 K	155 lm/W	14,079 lm
54810700	BBP500 G4 LED140/CW GU5.3 S-WB	6500 K	155 lm/W	14,079 lm
54700100	BBP500 G4 LED140/CW GU5.3 S-MB	6500 K	155 lm/W	14,079 lm
54784100	BBP500 G4 LED140/CW GU5.3 A-WB	6500 K	155 lm/W	14,079 lm
54746900	BBP500 G4 LED180/NW GU5.3 S-WB	4000 K	148 lm/W	18,066 lm
54773500	BBP500 G4 LED180/NW GU5.3 S-MB	4000 K	148 lm/W	18,066 lm

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
54867100	BBP500 G4 LED180/NW GU5.3 A-WB	4000 K	148 lm/W	18,066 lm
54818300	BGP500 G4 LED85/NW PSU A-WB	4000 K	160 lm/W	8,496 lm
54708700	BGP500 G4 LED85/CW PSU A-WB	6500 K	160 lm/W	8,496 lm
54674500	BGP500 G4 LED125/NW PSU A-WB	4000 K	159 lm/W	12,638 lm
54754400	BGP500 G4 LED125/CW PSU A-WB	6500 K	159 lm/W	12,638 lm
54849700	BGP500 G4 LED140/NW PSU A-WB	4000 K	155 lm/W	14,079 lm
54822000	BGP500 G4 LED140/CW PSU A-WB	6500 K	155 lm/W	14,079 lm
54713100	BGP500 G4 LED180/NW PSU A-WB	4000 K	148 lm/W	18,066 lm
54675200	BGP500 G4 LED180/CW PSU A-WB	6500 K	148 lm/W	18,066 lm
54862600	BCP500 G4 LED85/NW PSD S-WB	4000 K	147 lm/W	8,496 lm
54835000	BCP500 G4 LED85/NW PSD S-MB	4000 K	147 lm/W	8,496 lm
54726100	BCP500 G4 LED85/NW PSD A-WB	4000 K	147 lm/W	8,496 lm
54806000	BCP500 G4 LED85/CW PSD S-WB	6500 K	147 lm/W	8,496 lm
54696700	BCP500 G4 LED85/CW PSD S-MB	6500 K	147 lm/W	8,496 lm
54780300	BCP500 G4 LED85/CW PSD A-WB	6500 K	147 lm/W	8,496 lm
54743800	BCP500 G4 LED125/NW PSD S-WB	4000 K	149 lm/W	12,638 lm
54769800	BCP500 G4 LED125/NW PSD S-MB	4000 K	149 lm/W	12,638 lm
54863300	BCP500 G4 LED125/NW PSD A-WB	4000 K	149 lm/W	12,638 lm
54698100	BCP500 G4 LED125/CW PSD S-WB	6500 K	149 lm/W	12,638 lm
54782700	BCP500 G4 LED125/CW PSD S-MB	6500 K	149 lm/W	12,638 lm
54745200	BCP500 G4 LED125/CW PSD A-WB	6500 K	149 lm/W	12,638 lm
54771100	BCP500 G4 LED140/NW PSD S-WB	4000 K	147 lm/W	14,079 lm
54865700	BCP500 G4 LED140/NW PSD S-MB	4000 K	147 lm/W	14,079 lm
54837400	BCP500 G4 LED140/NW PSD A-WB	4000 K	147 lm/W	14,079 lm
54729200	BCP500 G4 LED140/CW PSD S-WB	6500 K	147 lm/W	14,079 lm
54809100	BCP500 G4 LED140/CW PSD S-MB	6500 K	147 lm/W	14,079 lm
54699800	BCP500 G4 LED140/CW PSD A-WB	6500 K	147 lm/W	14,079 lm
54783400	BCP500 G4 LED180/NW PSD S-WB	4000 K	142 lm/W	18,066 lm
54839800	BCP500 G4 LED180/NW PSD S-MB	4000 K	142 lm/W	18,066 lm
54731500	BCP500 G4 LED180/NW PSD A-WB	4000 K	142 lm/W	18,066 lm
54811400	BCP500 G4 LED180/CW PSD S-WB	6500 K	142 lm/W	18,066 lm
54701800	BCP500 G4 LED180/CW PSD S-MB	6500 K	142 lm/W	18,066 lm
54785800	BCP500 G4 LED180/CW PSD A-WB	6500 K	142 lm/W	18,066 lm
54823700	BBP500 G4 LED85/NW PSU S-WB PC	4000 K	157 lm/W	8,313 lm
54714800	BBP500 G4 LED85/NW PSU S-MB PC	4000 K	157 lm/W	8,313 lm
54709400	BBP500 G4 LED85/NW PSU A-WB PC	4000 K	157 lm/W	8,313 lm
54685100	BBP500 G4 LED85/CW PSU S-WB PC	6500 K	157 lm/W	8,313 lm
54787200	BBP500 G4 LED85/CW PSU S-MB PC	6500 K	157 lm/W	8,313 lm
54677600	BBP500 G4 LED85/CW PSU A-WB PC	6500 K	157 lm/W	8,313 lm
54757500	BBP500 G4 LED125/NW PSU S-WB PC	4000 K	156 lm/W	12,366 lm
54795700	BBP500 G4 LED125/NW PSU S-MB PC	4000 K	156 lm/W	12,366 lm

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
54687500	BBP500 G4 LED125/NW PSU A-WB PC	4000 K	156 lm/W	12,366 lm
54789600	BBP500 G4 LED125/CW PSU S-WB PC	6500 K	156 lm/W	12,366 lm
54679000	BBP500 G4 LED125/CW PSU S-MB PC	6500 K	156 lm/W	12,366 lm
54759900	BBP500 G4 LED125/CW PSU A-WB PC	6500 K	156 lm/W	12,366 lm
54852700	BBP500 G4 LED140/NW PSU S-WB PC	4000 K	152 lm/W	13,777 lm
54825100	BBP500 G4 LED140/NW PSU S-MB PC	4000 K	152 lm/W	13,777 lm
54717900	BBP500 G4 LED140/NW PSU A-WB PC	4000 K	152 lm/W	13,777 lm
54796400	BBP500 G4 LED140/CW PSU S-WB PC	6500 K	152 lm/W	13,777 lm
54688200	BBP500 G4 LED140/CW PSU S-MB PC	6500 K	152 lm/W	13,777 lm
54854100	BBP500 G4 LED140/CW PSU A-WB PC	6500 K	152 lm/W	13,777 lm
54827500	BBP500 G4 LED180/NW PSU S-WB PC	4000 K	145 lm/W	17,677 lm
54719300	BBP500 G4 LED180/NW PSU S-MB PC	4000 K	145 lm/W	17,677 lm
54798800	BBP500 G4 LED180/NW PSU A-WB PC	4000 K	145 lm/W	17,677 lm
54690500	BBP500 G4 LED180/CW PSU S-WB PC	6500 K	145 lm/W	17,677 lm
54791900	BBP500 G4 LED180/CW PSU S-MB PC	6500 K	145 lm/W	17,677 lm
54682000	BBP500 G4 LED180/CW PSU A-WB PC	6500 K	145 lm/W	17,677 lm
54715500	BBP500 G4 LED85/NW PSU S-WB	4000 K	160 lm/W	8,496 lm
54794000	BBP500 G4 LED85/NW PSU S-MB	4000 K	160 lm/W	8,496 lm
54686800	BBP500 G4 LED85/NW PSU A-WB	4000 K	160 lm/W	8,496 lm
54788900	BBP500 G4 LED85/CW PSU S-WB	6500 K	160 lm/W	8,496 lm
54678300	BBP500 G4 LED85/CW PSU S-MB	6500 K	160 lm/W	8,496 lm
54758200	BBP500 G4 LED85/CW PSU A-WB	6500 K	160 lm/W	8,496 lm
54851000	BBP500 G4 LED125/NW PSU S-WB	4000 K	159 lm/W	12,638 lm
54824400	BBP500 G4 LED125/NW PSU S-MB	4000 K	159 lm/W	12,638 lm
54716200	BBP500 G4 LED125/NW PSU A-WB	4000 K	159 lm/W	12,638 lm
54680600	BBP500 G4 LED125/CW PSU S-WB	6500 K	159 lm/W	12,638 lm
54760500	BBP500 G4 LED125/CW PSU S-MB	6500 K	159 lm/W	12,638 lm
54853400	BBP500 G4 LED125/CW PSU A-WB	6500 K	159 lm/W	12,638 lm
54826800	BBP500 G4 LED140/NW PSU S-WB	4000 K	155 lm/W	14,079 lm
54718600	BBP500 G4 LED140/NW PSU S-MB	4000 K	155 lm/W	14,079 lm
54797100	BBP500 G4 LED140/NW PSU A-WB	4000 K	155 lm/W	14,079 lm
54689900	BBP500 G4 LED140/CW PSU S-WB	6500 K	155 lm/W	14,079 lm
54790200	BBP500 G4 LED140/CW PSU S-MB	6500 K	155 lm/W	14,079 lm
54681300	BBP500 G4 LED140/CW PSU A-WB	6500 K	155 lm/W	14,079 lm
54761200	BBP500 G4 LED180/NW PSU S-WB	4000 K	148 lm/W	18,066 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
54799500	BBP500 G4 LED180/NW PSU S-MB	4000 K	148 lm/W	18,066 lm
54691200	BBP500 G4 LED180/NW PSU A-WB	4000 K	148 lm/W	18,066 lm
54792600	BBP500 G4 LED180/CW PSU S-WB	6500 K	148 lm/W	18,066 lm
54683700	BBP500 G4 LED180/CW PSU S-MB	6500 K	148 lm/W	18,066 lm
54763600	BBP500 G4 LED180/CW PSU A-WB	6500 K	148 lm/W	18,066 lm
54856500	BBP500 G4 LED85/NW PSD S-WB	4000 K	147 lm/W	8,496 lm
54829900	BBP500 G4 LED85/NW PSD S-MB	4000 K	147 lm/W	8,496 lm
54720900	BBP500 G4 LED85/NW PSD A-WB	4000 K	147 lm/W	8,496 lm
54800800	BBP500 G4 LED85/CW PSD S-WB	6500 K	147 lm/W	8,496 lm
54692900	BBP500 G4 LED85/CW PSD S-MB	6500 K	147 lm/W	8,496 lm
54858900	BBP500 G4 LED85/CW PSD A-WB	6500 K	147 lm/W	8,496 lm
54831200	BBP500 G4 LED125/NW PSD S-WB	4000 K	149 lm/W	12,638 lm
54722300	BBP500 G4 LED125/NW PSD S-MB	4000 K	149 lm/W	12,638 lm
54802200	BBP500 G4 LED125/NW PSD A-WB	4000 K	149 lm/W	12,638 lm
54694300	BBP500 G4 LED125/CW PSD S-WB	6500 K	149 lm/W	12,638 lm
54776600	BBP500 G4 LED125/CW PSD S-MB	6500 K	149 lm/W	12,638 lm
54739100	BBP500 G4 LED125/CW PSD A-WB	6500 K	149 lm/W	12,638 lm
54765000	BBP500 G4 LED140/NW PSD S-WB	4000 K	147 lm/W	14,079 lm
54859600	BBP500 G4 LED140/NW PSD S-MB	4000 K	147 lm/W	14,079 lm
54832900	BBP500 G4 LED140/NW PSD A-WB	4000 K	147 lm/W	14,079 lm
54778000	BBP500 G4 LED140/CW PSD S-WB	6500 K	147 lm/W	14,079 lm
54741400	BBP500 G4 LED140/CW PSD S-MB	6500 K	147 lm/W	14,079 lm
54767400	BBP500 G4 LED140/CW PSD A-WB	6500 K	147 lm/W	14,079 lm
54861900	BBP500 G4 LED180/NW PSD S-WB	4000 K	142 lm/W	18,066 lm
54834300	BBP500 G4 LED180/NW PSD S-MB	4000 K	142 lm/W	18,066 lm
54725400	BBP500 G4 LED180/NW PSD A-WB	4000 K	142 lm/W	18,066 lm
54805300	BBP500 G4 LED180/CW PSD S-WB	6500 K	142 lm/W	18,066 lm
54695000	BBP500 G4 LED180/CW PSD S-MB	6500 K	142 lm/W	18,066 lm
54779700	BBP500 G4 LED180/CW PSD A-WB	6500 K	142 lm/W	18,066 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
54762900	BCP500 G4 LED85/NW PSU S-WB	53 W	54766700	BCP500 G4 LED180/NW PSU S-WB	122 W
54855800	BCP500 G4 LED85/NW PSU S-MB	53 W	54860200	BCP500 G4 LED180/NW PSU S-MB	122 W
54828200	BCP500 G4 LED85/NW PSU A-WB	53 W	54833600	BCP500 G4 LED180/NW PSU A-WB	122 W
54793300	BCP500 G4 LED85/CW PSU S-WB	53 W	54724700	BCP500 G4 LED180/CW PSU S-WB	122 W
54684400	BCP500 G4 LED85/CW PSU S-MB	53 W	54804600	BCP500 G4 LED180/CW PSU S-MB	122 W
54764300	BCP500 G4 LED85/CW PSU A-WB	53 W	54768100	BCP500 G4 LED180/CW PSU A-WB	122 W
54857200	BCP500 G4 LED125/NW PSU S-WB	79 W	54704900	BCP500 G4 LED85/NW PSU S-WB PC	53 W
54830500	BCP500 G4 LED125/NW PSU S-MB	79 W	54751300	BCP500 G4 LED85/NW PSU S-MB PC	53 W
54721600	BCP500 G4 LED125/NW PSU A-WB	79 W	54846600	BCP500 G4 LED85/NW PSU A-WB PC	53 W
54801500	BCP500 G4 LED125/CW PSU S-WB	79 W	54819000	BCP500 G4 LED85/CW PSU S-WB PC	53 W
54693600	BCP500 G4 LED125/CW PSU S-MB	79 W	54710000	BCP500 G4 LED85/CW PSU S-MB PC	53 W
54775900	BCP500 G4 LED125/CW PSU A-WB	79 W	54735300	BCP500 G4 LED85/CW PSU A-WB PC	53 W
54738400	BCP500 G4 LED140/NW PSU S-WB	91 W	54815200	BCP500 G4 LED125/NW PSU S-WB PC	79 W
54723000	BCP500 G4 LED140/NW PSU S-MB	91 W	54705600	BCP500 G4 LED125/NW PSU S-MB PC	79 W
54803900	BCP500 G4 LED140/NW PSU A-WB	91 W	54672100	BCP500 G4 LED125/NW PSU A-WB PC	79 W
51909100	BCP500 G4 LED140/CW PSU S-WB	91 W	54752000	BCP500 G4 LED125/CW PSU S-WB PC	79 W
54777300	BCP500 G4 LED140/CW PSU S-MB	91 W	54847300	BCP500 G4 LED125/CW PSU S-MB PC	79 W
54740700	BCP500 G4 LED140/CW PSU A-WB	91 W	54816900	BCP500 G4 LED125/CW PSU A-WB PC	79 W

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Power Consumption
54706300	BCP500 G4 LED140/NW PSU S-WB PC	91 W
54673800	BCP500 G4 LED140/NW PSU S-MB PC	91 W
54753700	BCP500 G4 LED140/NW PSU A-WB PC	91 W
54848000	BCP500 G4 LED140/CW PSU S-WB PC	91 W
54820600	BCP500 G4 LED140/CW PSU S-MB PC	91 W
54711700	BCP500 G4 LED140/CW PSU A-WB PC	91 W
54736000	BCP500 G4 LED180/NW PSU S-WB PC	122 W
54817600	BCP500 G4 LED180/NW PSU S-MB PC	122 W
54707000	BCP500 G4 LED180/NW PSU A-WB PC	122 W
54821300	BCP500 G4 LED180/CW PSU S-WB PC	122 W
54712400	BCP500 G4 LED180/CW PSU S-MB PC	122 W
54737700	BCP500 G4 LED180/CW PSU A-WB PC	122 W
54747600	BCP500 G4 LED85/NW GU5.3 S-WB	53 W
54774200	BCP500 G4 LED85/NW GU5.3 S-MB	53 W
54868800	BCP500 G4 LED85/NW GU5.3 A-WB	53 W
54840400	BCP500 G4 LED85/CW GU5.3 S-WB	53 W
54732200	BCP500 G4 LED85/CW GU5.3 S-MB	53 W
54748300	BCP500 G4 LED85/CW GU5.3 A-WB	53 W
54843500	BCP500 G4 LED125/NW GU5.3 S-WB	79 W
54869500	BCP500 G4 LED125/NW GU5.3 S-MB	79 W
54841100	BCP500 G4 LED125/NW GU5.3 A-WB	79 W
54733900	BCP500 G4 LED125/CW GU5.3 S-WB	79 W
54812100	BCP500 G4 LED125/CW GU5.3 S-MB	79 W
54702500	BCP500 G4 LED125/CW GU5.3 A-WB	79 W
54786500	BCP500 G4 LED140/NW GU5.3 S-WB	91 W
54749000	BCP500 G4 LED140/NW GU5.3 S-MB	91 W
54844200	BCP500 G4 LED140/NW GU5.3 A-WB	91 W
54813800	BCP500 G4 LED140/CW GU5.3 S-WB	91 W
54703200	BCP500 G4 LED140/CW GU5.3 S-MB	91 W
54671400	BCP500 G4 LED140/CW GU5.3 A-WB	91 W
54750600	BCP500 G4 LED180/NW GU5.3 S-WB	122 W
54845900	BCP500 G4 LED180/NW GU5.3 S-MB	122 W
54870100	BCP500 G4 LED180/NW GU5.3 A-WB	122 W
54842800	BCP500 G4 LED180/CW GU5.3 S-WB	122 W
54734600	BCP500 G4 LED180/CW GU5.3 S-MB	122 W
54814500	BCP500 G4 LED180/CW GU5.3 A-WB	122 W
54676900	BBP500 G4 LED180/CW GU5.3 S-WB	122 W
54756800	BBP500 G4 LED180/CW GU5.3 S-MB	122 W
54850300	BBP500 G4 LED180/CW GU5.3 A-WB	122 W
54742100	BBP500 G4 LED85/NW GU5.3 S-WB	53 W
54727800	BBP500 G4 LED85/NW GU5.3 S-MB	53 W
54807700	BBP500 G4 LED85/NW GU5.3 A-WB	53 W
54697400	BBP500 G4 LED85/CW GU5.3 S-WB	53 W
54781000	BBP500 G4 LED85/CW GU5.3 S-MB	53 W
54744500	BBP500 G4 LED85/CW GU5.3 A-WB	53 W
54770400	BBP500 G4 LED125/NW GU5.3 S-WB	79 W
54864000	BBP500 G4 LED125/NW GU5.3 S-MB	79 W
54836700	BBP500 G4 LED125/NW GU5.3 A-WB	79 W
54728500	BBP500 G4 LED125/CW GU5.3 S-WB	79 W
54808400	BBP500 G4 LED125/CW GU5.3 S-MB	79 W
54772800	BBP500 G4 LED125/CW GU5.3 A-WB	79 W
54866400	BBP500 G4 LED140/NW GU5.3 S-WB	91 W

Order Code	Full Product Name	Power Consumption
54838100	BBP500 G4 LED140/NW GU5.3 S-MB	91 W
54730800	BBP500 G4 LED140/NW GU5.3 A-WB	91 W
54810700	BBP500 G4 LED140/CW GU5.3 S-WB	91 W
54700100	BBP500 G4 LED140/CW GU5.3 S-MB	91 W
54784100	BBP500 G4 LED140/CW GU5.3 A-WB	91 W
54746900	BBP500 G4 LED180/NW GU5.3 S-WB	122 W
54773500	BBP500 G4 LED180/NW GU5.3 S-MB	122 W
54867100	BBP500 G4 LED180/NW GU5.3 A-WB	122 W
54818300	BGP500 G4 LED85/NW PSU A-WB	53 W
54708700	BGP500 G4 LED85/CW PSU A-WB	53 W
54674500	BGP500 G4 LED125/NW PSU A-WB	79 W
54754400	BGP500 G4 LED125/CW PSU A-WB	79 W
54849700	BGP500 G4 LED140/NW PSU A-WB	91 W
54822000	BGP500 G4 LED140/CW PSU A-WB	91 W
54713100	BGP500 G4 LED180/NW PSU A-WB	122 W
54675200	BGP500 G4 LED180/CW PSU A-WB	122 W
54862600	BCP500 G4 LED85/NW PSD S-WB	58 W
54835000	BCP500 G4 LED85/NW PSD S-MB	58 W
54726100	BCP500 G4 LED85/NW PSD A-WB	58 W
54806000	BCP500 G4 LED85/CW PSD S-WB	58 W
54696700	BCP500 G4 LED85/CW PSD S-MB	58 W
54780300	BCP500 G4 LED85/CW PSD A-WB	58 W
54743800	BCP500 G4 LED125/NW PSD S-WB	85 W
54769800	BCP500 G4 LED125/NW PSD S-MB	85 W
54863300	BCP500 G4 LED125/NW PSD A-WB	85 W
54698100	BCP500 G4 LED125/CW PSD S-WB	85 W
54782700	BCP500 G4 LED125/CW PSD S-MB	85 W
54745200	BCP500 G4 LED125/CW PSD A-WB	85 W
54771100	BCP500 G4 LED140/NW PSD S-WB	96 W
54865700	BCP500 G4 LED140/NW PSD S-MB	96 W
54837400	BCP500 G4 LED140/NW PSD A-WB	96 W
54729200	BCP500 G4 LED140/CW PSD S-WB	96 W
54809100	BCP500 G4 LED140/CW PSD S-MB	96 W
54699800	BCP500 G4 LED140/CW PSD A-WB	96 W
54783400	BCP500 G4 LED180/NW PSD S-WB	128 W
54839800	BCP500 G4 LED180/NW PSD S-MB	128 W
54731500	BCP500 G4 LED180/NW PSD A-WB	128 W
54811400	BCP500 G4 LED180/CW PSD S-WB	128 W
54701800	BCP500 G4 LED180/CW PSD S-MB	128 W
54785800	BCP500 G4 LED180/CW PSD A-WB	128 W
54823700	BBP500 G4 LED85/NW PSU S-WB PC	53 W
54714800	BBP500 G4 LED85/NW PSU S-MB PC	53 W
54709400	BBP500 G4 LED85/NW PSU A-WB PC	53 W
54685100	BBP500 G4 LED85/CW PSU S-WB PC	53 W
54787200	BBP500 G4 LED85/CW PSU S-MB PC	53 W
54677600	BBP500 G4 LED85/CW PSU A-WB PC	53 W
54757500	BBP500 G4 LED125/NW PSU S-WB PC	79 W
54795700	BBP500 G4 LED125/NW PSU S-MB PC	79 W
54687500	BBP500 G4 LED125/NW PSU A-WB PC	79 W
54789600	BBP500 G4 LED125/CW PSU S-WB PC	79 W
54679000	BBP500 G4 LED125/CW PSU S-MB PC	79 W
54759900	BBP500 G4 LED125/CW PSU A-WB PC	79 W

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Power Consumption
54852700	BBP500 G4 LED140/NW PSU S-WB PC	91 W
54825100	BBP500 G4 LED140/NW PSU S-MB PC	91 W
54717900	BBP500 G4 LED140/NW PSU A-WB PC	91 W
54796400	BBP500 G4 LED140/CW PSU S-WB PC	91 W
54688200	BBP500 G4 LED140/CW PSU S-MB PC	91 W
54854100	BBP500 G4 LED140/CW PSU A-WB PC	91 W
54827500	BBP500 G4 LED180/NW PSU S-WB PC	122 W
54719300	BBP500 G4 LED180/NW PSU S-MB PC	122 W
54798800	BBP500 G4 LED180/NW PSU A-WB PC	122 W
54690500	BBP500 G4 LED180/CW PSU S-WB PC	122 W
54791900	BBP500 G4 LED180/CW PSU S-MB PC	122 W
54682000	BBP500 G4 LED180/CW PSU A-WB PC	122 W
54715500	BBP500 G4 LED85/NW PSU S-WB	53 W
54794000	BBP500 G4 LED85/NW PSU S-MB	53 W
54686800	BBP500 G4 LED85/NW PSU A-WB	53 W
54788900	BBP500 G4 LED85/CW PSU S-WB	53 W
54678300	BBP500 G4 LED85/CW PSU S-MB	53 W
54758200	BBP500 G4 LED85/CW PSU A-WB	53 W
54851000	BBP500 G4 LED125/NW PSU S-WB	79 W
54824400	BBP500 G4 LED125/NW PSU S-MB	79 W
54716200	BBP500 G4 LED125/NW PSU A-WB	79 W
54680600	BBP500 G4 LED125/CW PSU S-WB	79 W
54760500	BBP500 G4 LED125/CW PSU S-MB	79 W
54853400	BBP500 G4 LED125/CW PSU A-WB	79 W
54826800	BBP500 G4 LED140/NW PSU S-WB	91 W
54718600	BBP500 G4 LED140/NW PSU S-MB	91 W
54797100	BBP500 G4 LED140/NW PSU A-WB	91 W
54689900	BBP500 G4 LED140/CW PSU S-WB	91 W
54790200	BBP500 G4 LED140/CW PSU S-MB	91 W
54681300	BBP500 G4 LED140/CW PSU A-WB	91 W

Order Code	Full Product Name	Power Consumption
54761200	BBP500 G4 LED180/NW PSU S-WB	122 W
54799500	BBP500 G4 LED180/NW PSU S-MB	122 W
54691200	BBP500 G4 LED180/NW PSU A-WB	122 W
54792600	BBP500 G4 LED180/CW PSU S-WB	122 W
54683700	BBP500 G4 LED180/CW PSU S-MB	122 W
54763600	BBP500 G4 LED180/CW PSU A-WB	122 W
54856500	BBP500 G4 LED85/NW PSD S-WB	58 W
54829900	BBP500 G4 LED85/NW PSD S-MB	58 W
54720900	BBP500 G4 LED85/NW PSD A-WB	58 W
54800800	BBP500 G4 LED85/CW PSD S-WB	58 W
54692900	BBP500 G4 LED85/CW PSD S-MB	58 W
54858900	BBP500 G4 LED85/CW PSD A-WB	58 W
54831200	BBP500 G4 LED125/NW PSD S-WB	85 W
54722300	BBP500 G4 LED125/NW PSD S-MB	85 W
54802200	BBP500 G4 LED125/NW PSD A-WB	85 W
54694300	BBP500 G4 LED125/CW PSD S-WB	85 W
54776600	BBP500 G4 LED125/CW PSD S-MB	85 W
54739100	BBP500 G4 LED125/CW PSD A-WB	85 W
54765000	BBP500 G4 LED140/NW PSD S-WB	96 W
54859600	BBP500 G4 LED140/NW PSD S-MB	96 W
54832900	BBP500 G4 LED140/NW PSD A-WB	96 W
54778000	BBP500 G4 LED140/CW PSD S-WB	96 W
54741400	BBP500 G4 LED140/CW PSD S-MB	96 W
54767400	BBP500 G4 LED140/CW PSD A-WB	96 W
54861900	BBP500 G4 LED180/NW PSD S-WB	128 W
54834300	BBP500 G4 LED180/NW PSD S-MB	128 W
54725400	BBP500 G4 LED180/NW PSD A-WB	128 W
54805300	BBP500 G4 LED180/CW PSD S-WB	128 W
54695000	BBP500 G4 LED180/CW PSD S-MB	128 W
54779700	BBP500 G4 LED180/CW PSD A-WB	128 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
54762900	BCP500 G4 LED85/NW PSU S-WB	No
54855800	BCP500 G4 LED85/NW PSU S-MB	No
54828200	BCP500 G4 LED85/NW PSU A-WB	No
54793300	BCP500 G4 LED85/CW PSU S-WB	No
54684400	BCP500 G4 LED85/CW PSU S-MB	No
54764300	BCP500 G4 LED85/CW PSU A-WB	No
54857200	BCP500 G4 LED125/NW PSU S-WB	No
54830500	BCP500 G4 LED125/NW PSU S-MB	No
54721600	BCP500 G4 LED125/NW PSU A-WB	No
54801500	BCP500 G4 LED125/CW PSU S-WB	No
54693600	BCP500 G4 LED125/CW PSU S-MB	No
54775900	BCP500 G4 LED125/CW PSU A-WB	No
54738400	BCP500 G4 LED140/NW PSU S-WB	No
54723000	BCP500 G4 LED140/NW PSU S-MB	No
54803900	BCP500 G4 LED140/NW PSU A-WB	No
51909100	BCP500 G4 LED140/CW PSU S-WB	No
54777300	BCP500 G4 LED140/CW PSU S-MB	No
54740700	BCP500 G4 LED140/CW PSU A-WB	No

Order Code	Full Product Name	Dimmable
54766700	BCP500 G4 LED180/NW PSU S-WB	No
54860200	BCP500 G4 LED180/NW PSU S-MB	No
54833600	BCP500 G4 LED180/NW PSU A-WB	No
54724700	BCP500 G4 LED180/CW PSU S-WB	No
54804600	BCP500 G4 LED180/CW PSU S-MB	No
54768100	BCP500 G4 LED180/CW PSU A-WB	No
54704900	BCP500 G4 LED85/NW PSU S-WB PC	No
54751300	BCP500 G4 LED85/NW PSU S-MB PC	No
54846600	BCP500 G4 LED85/NW PSU A-WB PC	No
54819000	BCP500 G4 LED85/CW PSU S-WB PC	No
54710000	BCP500 G4 LED85/CW PSU S-MB PC	No
54735300	BCP500 G4 LED85/CW PSU A-WB PC	No
54815200	BCP500 G4 LED125/NW PSU S-WB PC	No
54705600	BCP500 G4 LED125/NW PSU S-MB PC	No
54672100	BCP500 G4 LED125/NW PSU A-WB PC	No
54752000	BCP500 G4 LED125/CW PSU S-WB PC	No
54847300	BCP500 G4 LED125/CW PSU S-MB PC	No
54816900	BCP500 G4 LED125/CW PSU A-WB PC	No

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Dimmable
54706300	BCP500 G4 LED140/NW PSU S-WB PC	No
54673800	BCP500 G4 LED140/NW PSU S-MB PC	No
54753700	BCP500 G4 LED140/NW PSU A-WB PC	No
54848000	BCP500 G4 LED140/CW PSU S-WB PC	No
54820600	BCP500 G4 LED140/CW PSU S-MB PC	No
54711700	BCP500 G4 LED140/CW PSU A-WB PC	No
54736000	BCP500 G4 LED180/NW PSU S-WB PC	No
54817600	BCP500 G4 LED180/NW PSU S-MB PC	No
54707000	BCP500 G4 LED180/NW PSU A-WB PC	No
54821300	BCP500 G4 LED180/CW PSU S-WB PC	No
54712400	BCP500 G4 LED180/CW PSU S-MB PC	No
54737700	BCP500 G4 LED180/CW PSU A-WB PC	No
54747600	BCP500 G4 LED85/NW GU5.3 S-WB	No
54774200	BCP500 G4 LED85/NW GU5.3 S-MB	No
54868800	BCP500 G4 LED85/NW GU5.3 A-WB	No
54840400	BCP500 G4 LED85/CW GU5.3 S-WB	No
54732200	BCP500 G4 LED85/CW GU5.3 S-MB	No
54748300	BCP500 G4 LED85/CW GU5.3 A-WB	No
54843500	BCP500 G4 LED125/NW GU5.3 S-WB	No
54869500	BCP500 G4 LED125/NW GU5.3 S-MB	No
54841100	BCP500 G4 LED125/NW GU5.3 A-WB	No
54733900	BCP500 G4 LED125/CW GU5.3 S-WB	No
54812100	BCP500 G4 LED125/CW GU5.3 S-MB	No
54702500	BCP500 G4 LED125/CW GU5.3 A-WB	No
54786500	BCP500 G4 LED140/NW GU5.3 S-WB	No
54749000	BCP500 G4 LED140/NW GU5.3 S-MB	No
54844200	BCP500 G4 LED140/NW GU5.3 A-WB	No
54813800	BCP500 G4 LED140/CW GU5.3 S-WB	No
54703200	BCP500 G4 LED140/CW GU5.3 S-MB	No
54671400	BCP500 G4 LED140/CW GU5.3 A-WB	No
54750600	BCP500 G4 LED180/NW GU5.3 S-WB	No
54845900	BCP500 G4 LED180/NW GU5.3 S-MB	No
54870100	BCP500 G4 LED180/NW GU5.3 A-WB	No
54842800	BCP500 G4 LED180/CW GU5.3 S-WB	No
54734600	BCP500 G4 LED180/CW GU5.3 S-MB	No
54814500	BCP500 G4 LED180/CW GU5.3 A-WB	No
54676900	BBP500 G4 LED180/CW GU5.3 S-WB	No
54756800	BBP500 G4 LED180/CW GU5.3 S-MB	No
54850300	BBP500 G4 LED180/CW GU5.3 A-WB	No
54742100	BBP500 G4 LED85/NW GU5.3 S-WB	No
54727800	BBP500 G4 LED85/NW GU5.3 S-MB	No
54807700	BBP500 G4 LED85/NW GU5.3 A-WB	No
54697400	BBP500 G4 LED85/CW GU5.3 S-WB	No
54781000	BBP500 G4 LED85/CW GU5.3 S-MB	No
54744500	BBP500 G4 LED85/CW GU5.3 A-WB	No
54770400	BBP500 G4 LED125/NW GU5.3 S-WB	No
54864000	BBP500 G4 LED125/NW GU5.3 S-MB	No
54836700	BBP500 G4 LED125/NW GU5.3 A-WB	No
54728500	BBP500 G4 LED125/CW GU5.3 S-WB	No
54808400	BBP500 G4 LED125/CW GU5.3 S-MB	No
54772800	BBP500 G4 LED125/CW GU5.3 A-WB	No
54866400	BBP500 G4 LED140/NW GU5.3 S-WB	No

Order Code	Full Product Name	Dimmable
54838100	BBP500 G4 LED140/NW GU5.3 S-MB	No
54730800	BBP500 G4 LED140/NW GU5.3 A-WB	No
54810700	BBP500 G4 LED140/CW GU5.3 S-WB	No
54700100	BBP500 G4 LED140/CW GU5.3 S-MB	No
54784100	BBP500 G4 LED140/CW GU5.3 A-WB	No
54746900	BBP500 G4 LED180/NW GU5.3 S-WB	No
54773500	BBP500 G4 LED180/NW GU5.3 S-MB	No
54867100	BBP500 G4 LED180/NW GU5.3 A-WB	No
54818300	BGP500 G4 LED85/NW PSU A-WB	No
54708700	BGP500 G4 LED85/CW PSU A-WB	No
54674500	BGP500 G4 LED125/NW PSU A-WB	No
54754400	BGP500 G4 LED125/CW PSU A-WB	No
54849700	BGP500 G4 LED140/NW PSU A-WB	No
54822000	BGP500 G4 LED140/CW PSU A-WB	No
54713100	BGP500 G4 LED180/NW PSU A-WB	No
54675200	BGP500 G4 LED180/CW PSU A-WB	No
54862600	BCP500 G4 LED85/NW PSD S-WB	DALI
54835000	BCP500 G4 LED85/NW PSD S-MB	DALI
54726100	BCP500 G4 LED85/NW PSD A-WB	DALI
54806000	BCP500 G4 LED85/CW PSD S-WB	DALI
54696700	BCP500 G4 LED85/CW PSD S-MB	DALI
54780300	BCP500 G4 LED85/CW PSD A-WB	DALI
54743800	BCP500 G4 LED125/NW PSD S-WB	DALI
54769800	BCP500 G4 LED125/NW PSD S-MB	DALI
54863300	BCP500 G4 LED125/NW PSD A-WB	DALI
54698100	BCP500 G4 LED125/CW PSD S-WB	DALI
54782700	BCP500 G4 LED125/CW PSD S-MB	DALI
54745200	BCP500 G4 LED125/CW PSD A-WB	DALI
54771100	BCP500 G4 LED140/NW PSD S-WB	DALI
54865700	BCP500 G4 LED140/NW PSD S-MB	DALI
54837400	BCP500 G4 LED140/NW PSD A-WB	DALI
54729200	BCP500 G4 LED140/CW PSD S-WB	DALI
54809100	BCP500 G4 LED140/CW PSD S-MB	DALI
54699800	BCP500 G4 LED140/CW PSD A-WB	DALI
54783400	BCP500 G4 LED180/NW PSD S-WB	DALI
54839800	BCP500 G4 LED180/NW PSD S-MB	DALI
54731500	BCP500 G4 LED180/NW PSD A-WB	DALI
54811400	BCP500 G4 LED180/CW PSD S-WB	DALI
54701800	BCP500 G4 LED180/CW PSD S-MB	DALI
54785800	BCP500 G4 LED180/CW PSD A-WB	DALI
54823700	BBP500 G4 LED85/NW PSU S-WB PC	No
54714800	BBP500 G4 LED85/NW PSU S-MB PC	No
54709400	BBP500 G4 LED85/NW PSU A-WB PC	No
54685100	BBP500 G4 LED85/CW PSU S-WB PC	No
54787200	BBP500 G4 LED85/CW PSU S-MB PC	No
54677600	BBP500 G4 LED85/CW PSU A-WB PC	No
54757500	BBP500 G4 LED125/NW PSU S-WB PC	No
54795700	BBP500 G4 LED125/NW PSU S-MB PC	No
54687500	BBP500 G4 LED125/NW PSU A-WB PC	No
54789600	BBP500 G4 LED125/CW PSU S-WB PC	No
54679000	BBP500 G4 LED125/CW PSU S-MB PC	No
54759900	BBP500 G4 LED125/CW PSU A-WB PC	No

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Dimmable
54852700	BBP500 G4 LED140/NW PSU S-WB PC	No
54825100	BBP500 G4 LED140/NW PSU S-MB PC	No
54717900	BBP500 G4 LED140/NW PSU A-WB PC	No
54796400	BBP500 G4 LED140/CW PSU S-WB PC	No
54688200	BBP500 G4 LED140/CW PSU S-MB PC	No
54854100	BBP500 G4 LED140/CW PSU A-WB PC	No
54827500	BBP500 G4 LED180/NW PSU S-WB PC	No
54719300	BBP500 G4 LED180/NW PSU S-MB PC	No
54798800	BBP500 G4 LED180/NW PSU A-WB PC	No
54690500	BBP500 G4 LED180/CW PSU S-WB PC	No
54791900	BBP500 G4 LED180/CW PSU S-MB PC	No
54682000	BBP500 G4 LED180/CW PSU A-WB PC	No
54715500	BBP500 G4 LED85/NW PSU S-WB	No
54794000	BBP500 G4 LED85/NW PSU S-MB	No
54686800	BBP500 G4 LED85/NW PSU A-WB	No
54788900	BBP500 G4 LED85/CW PSU S-WB	No
54678300	BBP500 G4 LED85/CW PSU S-MB	No
54758200	BBP500 G4 LED85/CW PSU A-WB	No
54851000	BBP500 G4 LED125/NW PSU S-WB	No
54824400	BBP500 G4 LED125/NW PSU S-MB	No
54716200	BBP500 G4 LED125/NW PSU A-WB	No
54680600	BBP500 G4 LED125/CW PSU S-WB	No
54760500	BBP500 G4 LED125/CW PSU S-MB	No
54853400	BBP500 G4 LED125/CW PSU A-WB	No
54826800	BBP500 G4 LED140/NW PSU S-WB	No
54718600	BBP500 G4 LED140/NW PSU S-MB	No
54797100	BBP500 G4 LED140/NW PSU A-WB	No
54689900	BBP500 G4 LED140/CW PSU S-WB	No
54790200	BBP500 G4 LED140/CW PSU S-MB	No
54681300	BBP500 G4 LED140/CW PSU A-WB	No

Order Code	Full Product Name	Dimmable
54761200	BBP500 G4 LED180/NW PSU S-WB	No
54799500	BBP500 G4 LED180/NW PSU S-MB	No
54691200	BBP500 G4 LED180/NW PSU A-WB	No
54792600	BBP500 G4 LED180/CW PSU S-WB	No
54683700	BBP500 G4 LED180/CW PSU S-MB	No
54763600	BBP500 G4 LED180/CW PSU A-WB	No
54856500	BBP500 G4 LED85/NW PSD S-WB	DALI
54829900	BBP500 G4 LED85/NW PSD S-MB	DALI
54720900	BBP500 G4 LED85/NW PSD A-WB	DALI
54800800	BBP500 G4 LED85/CW PSD S-WB	DALI
54692900	BBP500 G4 LED85/CW PSD S-MB	DALI
54858900	BBP500 G4 LED85/CW PSD A-WB	DALI
54831200	BBP500 G4 LED125/NW PSD S-WB	DALI
54722300	BBP500 G4 LED125/NW PSD S-MB	DALI
54802200	BBP500 G4 LED125/NW PSD A-WB	DALI
54694300	BBP500 G4 LED125/CW PSD S-WB	DALI
54776600	BBP500 G4 LED125/CW PSD S-MB	DALI
54739100	BBP500 G4 LED125/CW PSD A-WB	DALI
54765000	BBP500 G4 LED140/NW PSD S-WB	DALI
54859600	BBP500 G4 LED140/NW PSD S-MB	DALI
54832900	BBP500 G4 LED140/NW PSD A-WB	DALI
54778000	BBP500 G4 LED140/CW PSD S-WB	DALI
54741400	BBP500 G4 LED140/CW PSD S-MB	DALI
54767400	BBP500 G4 LED140/CW PSD A-WB	DALI
54861900	BBP500 G4 LED180/NW PSD S-WB	DALI
54834300	BBP500 G4 LED180/NW PSD S-MB	DALI
54725400	BBP500 G4 LED180/NW PSD A-WB	DALI
54805300	BBP500 G4 LED180/CW PSD S-WB	DALI
54695000	BBP500 G4 LED180/CW PSD S-MB	DALI
54779700	BBP500 G4 LED180/CW PSD A-WB	DALI

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
54762900	BCP500 G4 LED85/NW PSU S-WB	Clear glass	IK07
54855800	BCP500 G4 LED85/NW PSU S-MB	Clear glass	IK07
54828200	BCP500 G4 LED85/NW PSU A-WB	Clear glass	IK07
54793300	BCP500 G4 LED85/CW PSU S-WB	Clear glass	IK07
54684400	BCP500 G4 LED85/CW PSU S-MB	Clear glass	IK07
54764300	BCP500 G4 LED85/CW PSU A-WB	Clear glass	IK07
54857200	BCP500 G4 LED125/NW PSU S-WB	Clear glass	IK07
54830500	BCP500 G4 LED125/NW PSU S-MB	Clear glass	IK07
54721600	BCP500 G4 LED125/NW PSU A-WB	Clear glass	IK07
54801500	BCP500 G4 LED125/CW PSU S-WB	Clear glass	IK07
54693600	BCP500 G4 LED125/CW PSU S-MB	Clear glass	IK07
54775900	BCP500 G4 LED125/CW PSU A-WB	Clear glass	IK07
54738400	BCP500 G4 LED140/NW PSU S-WB	Clear glass	IK07
54723000	BCP500 G4 LED140/NW PSU S-MB	Clear glass	IK07
54803900	BCP500 G4 LED140/NW PSU A-WB	Clear glass	IK07
51909100	BCP500 G4 LED140/CW PSU S-WB	Clear glass	IK07

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
54777300	BCP500 G4 LED140/CW PSU S-MB	Clear glass	IK07
54740700	BCP500 G4 LED140/CW PSU A-WB	Clear glass	IK07
54766700	BCP500 G4 LED180/NW PSU S-WB	Clear glass	IK07
54860200	BCP500 G4 LED180/NW PSU S-MB	Clear glass	IK07
54833600	BCP500 G4 LED180/NW PSU A-WB	Clear glass	IK07
54724700	BCP500 G4 LED180/CW PSU S-WB	Clear glass	IK07
54804600	BCP500 G4 LED180/CW PSU S-MB	Clear glass	IK07
54768100	BCP500 G4 LED180/CW PSU A-WB	Clear glass	IK07
54704900	BCP500 G4 LED85/NW PSU S-WB PC	Polycarbonate	IK08
54751300	BCP500 G4 LED85/NW PSU S-MB PC	Polycarbonate	IK08
54846600	BCP500 G4 LED85/NW PSU A-WB PC	Polycarbonate	IK08
54819000	BCP500 G4 LED85/CW PSU S-WB PC	Polycarbonate	IK08
54710000	BCP500 G4 LED85/CW PSU S-MB PC	Polycarbonate	IK08
54735300	BCP500 G4 LED85/CW PSU A-WB PC	Polycarbonate	IK08
54815200	BCP500 G4 LED125/NW PSU S-WB PC	Polycarbonate	IK08
54705600	BCP500 G4 LED125/NW PSU S-MB PC	Polycarbonate	IK08

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
54672100	BCP500 G4 LED125/NW PSU A-WB PC	Polycarbonate	IK08
54752000	BCP500 G4 LED125/CW PSU S-WB PC	Polycarbonate	IK08
54847300	BCP500 G4 LED125/CW PSU S-MB PC	Polycarbonate	IK08
54816900	BCP500 G4 LED125/CW PSU A-WB PC	Polycarbonate	IK08
54706300	BCP500 G4 LED140/NW PSU S-WB PC	Polycarbonate	IK08
54673800	BCP500 G4 LED140/NW PSU S-MB PC	Polycarbonate	IK08
54753700	BCP500 G4 LED140/NW PSU A-WB PC	Polycarbonate	IK08
54848000	BCP500 G4 LED140/CW PSU S-WB PC	Polycarbonate	IK08
54820600	BCP500 G4 LED140/CW PSU S-MB PC	Polycarbonate	IK08
54711700	BCP500 G4 LED140/CW PSU A-WB PC	Polycarbonate	IK08
54736000	BCP500 G4 LED180/NW PSU S-WB PC	Polycarbonate	IK08
54817600	BCP500 G4 LED180/NW PSU S-MB PC	Polycarbonate	IK08
54707000	BCP500 G4 LED180/NW PSU A-WB PC	Polycarbonate	IK08
54821300	BCP500 G4 LED180/CW PSU S-WB PC	Polycarbonate	IK08
54712400	BCP500 G4 LED180/CW PSU S-MB PC	Polycarbonate	IK08
54737700	BCP500 G4 LED180/CW PSU A-WB PC	Polycarbonate	IK08
54747600	BCP500 G4 LED85/NW GU5.3 S-WB	Clear glass	IK07
54774200	BCP500 G4 LED85/NW GU5.3 S-MB	Clear glass	IK07
54868800	BCP500 G4 LED85/NW GU5.3 A-WB	Clear glass	IK07
54840400	BCP500 G4 LED85/CW GU5.3 S-WB	Clear glass	IK07
54732200	BCP500 G4 LED85/CW GU5.3 S-MB	Clear glass	IK07
54748300	BCP500 G4 LED85/CW GU5.3 A-WB	Clear glass	IK07
54843500	BCP500 G4 LED125/NW GU5.3 S-WB	Clear glass	IK07
54869500	BCP500 G4 LED125/NW GU5.3 S-MB	Clear glass	IK07
54841100	BCP500 G4 LED125/NW GU5.3 A-WB	Clear glass	IK07
54733900	BCP500 G4 LED125/CW GU5.3 S-WB	Clear glass	IK07
54812100	BCP500 G4 LED125/CW GU5.3 S-MB	Clear glass	IK07
54702500	BCP500 G4 LED125/CW GU5.3 A-WB	Clear glass	IK07
54786500	BCP500 G4 LED140/NW GU5.3 S-WB	Clear glass	IK07
54749000	BCP500 G4 LED140/NW GU5.3 S-MB	Clear glass	IK07
54844200	BCP500 G4 LED140/NW GU5.3 A-WB	Clear glass	IK07
54813800	BCP500 G4 LED140/CW GU5.3 S-WB	Clear glass	IK07
54703200	BCP500 G4 LED140/CW GU5.3 S-MB	Clear glass	IK07
54671400	BCP500 G4 LED140/CW GU5.3 A-WB	Clear glass	IK07
54750600	BCP500 G4 LED180/NW GU5.3 S-WB	Clear glass	IK07
54845900	BCP500 G4 LED180/NW GU5.3 S-MB	Clear glass	IK07
54870100	BCP500 G4 LED180/NW GU5.3 A-WB	Clear glass	IK07
54842800	BCP500 G4 LED180/CW GU5.3 S-WB	Clear glass	IK07

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
54734600	BCP500 G4 LED180/CW GU5.3 S-MB	Clear glass	IK07
54814500	BCP500 G4 LED180/CW GU5.3 A-WB	Clear glass	IK07
54676900	BBP500 G4 LED180/CW GU5.3 S-WB	Clear glass	IK07
54756800	BBP500 G4 LED180/CW GU5.3 S-MB	Clear glass	IK07
54850300	BBP500 G4 LED180/CW GU5.3 A-WB	Clear glass	IK07
54742100	BBP500 G4 LED85/NW GU5.3 S-WB	Clear glass	IK07
54727800	BBP500 G4 LED85/NW GU5.3 S-MB	Clear glass	IK07
54807700	BBP500 G4 LED85/NW GU5.3 A-WB	Clear glass	IK07
54697400	BBP500 G4 LED85/CW GU5.3 S-WB	Clear glass	IK07
54781000	BBP500 G4 LED85/CW GU5.3 S-MB	Clear glass	IK07
54744500	BBP500 G4 LED85/CW GU5.3 A-WB	Clear glass	IK07
54770400	BBP500 G4 LED125/NW GU5.3 S-WB	Clear glass	IK07
54864000	BBP500 G4 LED125/NW GU5.3 S-MB	Clear glass	IK07
54836700	BBP500 G4 LED125/NW GU5.3 A-WB	Clear glass	IK07
54728500	BBP500 G4 LED125/CW GU5.3 S-WB	Clear glass	IK07
54808400	BBP500 G4 LED125/CW GU5.3 S-MB	Clear glass	IK07
54772800	BBP500 G4 LED125/CW GU5.3 A-WB	Clear glass	IK07
54866400	BBP500 G4 LED140/NW GU5.3 S-WB	Clear glass	IK07
54838100	BBP500 G4 LED140/NW GU5.3 S-MB	Clear glass	IK07
54730800	BBP500 G4 LED140/NW GU5.3 A-WB	Clear glass	IK07
54810700	BBP500 G4 LED140/CW GU5.3 S-WB	Clear glass	IK07
54700100	BBP500 G4 LED140/CW GU5.3 S-MB	Clear glass	IK07
54784100	BBP500 G4 LED140/CW GU5.3 A-WB	Clear glass	IK07
54746900	BBP500 G4 LED180/NW GU5.3 S-WB	Clear glass	IK07
54773500	BBP500 G4 LED180/NW GU5.3 S-MB	Clear glass	IK07
54867100	BBP500 G4 LED180/NW GU5.3 A-WB	Clear glass	IK07
54818300	BGP500 G4 LED85/NW PSU A-WB	Clear glass	IK07
54708700	BGP500 G4 LED85/CW PSU A-WB	Clear glass	IK07
54674500	BGP500 G4 LED125/NW PSU A-WB	Clear glass	IK07
54754400	BGP500 G4 LED125/CW PSU A-WB	Clear glass	IK07
54849700	BGP500 G4 LED140/NW PSU A-WB	Clear glass	IK07
54822000	BGP500 G4 LED140/CW PSU A-WB	Clear glass	IK07
54713100	BGP500 G4 LED180/NW PSU A-WB	Clear glass	IK07
54675200	BGP500 G4 LED180/CW PSU A-WB	Clear glass	IK07
54862600	BCP500 G4 LED85/NW PSD S-WB	Clear glass	IK07
54835000	BCP500 G4 LED85/NW PSD S-MB	Clear glass	IK07
54726100	BCP500 G4 LED85/NW PSD A-WB	Clear glass	IK07
54806000	BCP500 G4 LED85/CW PSD S-WB	Clear glass	IK07
54696700	BCP500 G4 LED85/CW PSD S-MB	Clear glass	IK07
54780300	BCP500 G4 LED85/CW PSD A-WB	Clear glass	IK07
54743800	BCP500 G4 LED125/NW PSD S-WB	Clear glass	IK07
54769800	BCP500 G4 LED125/NW PSD S-MB	Clear glass	IK07
54863300	BCP500 G4 LED125/NW PSD A-WB	Clear glass	IK07
54698100	BCP500 G4 LED125/CW PSD S-WB	Clear glass	IK07
54782700	BCP500 G4 LED125/CW PSD S-MB	Clear glass	IK07
54745200	BCP500 G4 LED125/CW PSD A-WB	Clear glass	IK07
54771100	BCP500 G4 LED140/NW PSD S-WB	Clear glass	IK07
54865700	BCP500 G4 LED140/NW PSD S-MB	Clear glass	IK07
54837400	BCP500 G4 LED140/NW PSD A-WB	Clear glass	IK07
54729200	BCP500 G4 LED140/CW PSD S-WB	Clear glass	IK07

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Mech. impact protection	
			code	
54809100	BCP500 G4 LED140/CW PSD S-MB	Clear glass	IK07	
54699800	BCP500 G4 LED140/CW PSD A-WB	Clear glass	IK07	
54783400	BCP500 G4 LED180/NW PSD S-WB	Clear glass	IK07	
54839800	BCP500 G4 LED180/NW PSD S-MB	Clear glass	IK07	
54731500	BCP500 G4 LED180/NW PSD A-WB	Clear glass	IK07	
54811400	BCP500 G4 LED180/CW PSD S-WB	Clear glass	IK07	
54701800	BCP500 G4 LED180/CW PSD S-MB	Clear glass	IK07	
54785800	BCP500 G4 LED180/CW PSD A-WB	Clear glass	IK07	
54823700	BBP500 G4 LED85/NW PSU S-WB PC	Polycarbonate	IK08	
54714800	BBP500 G4 LED85/NW PSU S-MB PC	Polycarbonate	IK08	
54709400	BBP500 G4 LED85/NW PSU A-WB PC	Polycarbonate	IK08	
54685100	BBP500 G4 LED85/CW PSU S-WB PC	Polycarbonate	IK08	
54787200	BBP500 G4 LED85/CW PSU S-MB PC	Polycarbonate	IK08	
54677600	BBP500 G4 LED85/CW PSU A-WB PC	Polycarbonate	IK08	
54757500	BBP500 G4 LED125/NW PSU S-WB PC	Polycarbonate	IK08	
54795700	BBP500 G4 LED125/NW PSU S-MB PC	Polycarbonate	IK08	
54687500	BBP500 G4 LED125/NW PSU A-WB PC	Polycarbonate	IK08	
54789600	BBP500 G4 LED125/CW PSU S-WB PC	Polycarbonate	IK08	
54679000	BBP500 G4 LED125/CW PSU S-MB PC	Polycarbonate	IK08	
54759900	BBP500 G4 LED125/CW PSU A-WB PC	Polycarbonate	IK08	
54852700	BBP500 G4 LED140/NW PSU S-WB PC	Polycarbonate	IK08	
54825100	BBP500 G4 LED140/NW PSU S-MB PC	Polycarbonate	IK08	
54717900	BBP500 G4 LED140/NW PSU A-WB PC	Polycarbonate	IK08	
54796400	BBP500 G4 LED140/CW PSU S-WB PC	Polycarbonate	IK08	
54688200	BBP500 G4 LED140/CW PSU S-MB PC	Polycarbonate	IK08	
54854100	BBP500 G4 LED140/CW PSU A-WB PC	Polycarbonate	IK08	
54827500	BBP500 G4 LED180/NW PSU S-WB PC	Polycarbonate	IK08	
54719300	BBP500 G4 LED180/NW PSU S-MB PC	Polycarbonate	IK08	
54798800	BBP500 G4 LED180/NW PSU A-WB PC	Polycarbonate	IK08	
54690500	BBP500 G4 LED180/CW PSU S-WB PC	Polycarbonate	IK08	
54791900	BBP500 G4 LED180/CW PSU S-MB PC	Polycarbonate	IK08	
54682000	BBP500 G4 LED180/CW PSU A-WB PC	Polycarbonate	IK08	
54715500	BBP500 G4 LED85/NW PSU S-WB	Clear glass	IK07	
54794000	BBP500 G4 LED85/NW PSU S-MB	Clear glass	IK07	

Order Code	Full Product Name	Optical cover type	Mech. impact protection	
			code	
54686800	BBP500 G4 LED85/NW PSU A-WB	Clear glass	IK07	
54788900	BBP500 G4 LED85/CW PSU S-WB	Clear glass	IK07	
54678300	BBP500 G4 LED85/CW PSU S-MB	Clear glass	IK07	
54758200	BBP500 G4 LED85/CW PSU A-WB	Clear glass	IK07	
54851000	BBP500 G4 LED125/NW PSU S-WB	Clear glass	IK07	
54824400	BBP500 G4 LED125/NW PSU S-MB	Clear glass	IK07	
54716200	BBP500 G4 LED125/NW PSU A-WB	Clear glass	IK07	
54680600	BBP500 G4 LED125/CW PSU S-WB	Clear glass	IK07	
54760500	BBP500 G4 LED125/CW PSU S-MB	Clear glass	IK07	
54853400	BBP500 G4 LED125/CW PSU A-WB	Clear glass	IK07	
54826800	BBP500 G4 LED140/NW PSU S-WB	Clear glass	IK07	
54718600	BBP500 G4 LED140/NW PSU S-MB	Clear glass	IK07	
54797100	BBP500 G4 LED140/NW PSU A-WB	Clear glass	IK07	
54689900	BBP500 G4 LED140/CW PSU S-WB	Clear glass	IK07	
54790200	BBP500 G4 LED140/CW PSU S-MB	Clear glass	IK07	
54681300	BBP500 G4 LED140/CW PSU A-WB	Clear glass	IK07	
54761200	BBP500 G4 LED180/NW PSU S-WB	Clear glass	IK07	
54799500	BBP500 G4 LED180/NW PSU S-MB	Clear glass	IK07	
54691200	BBP500 G4 LED180/NW PSU A-WB	Clear glass	IK07	
54792600	BBP500 G4 LED180/CW PSU S-WB	Clear glass	IK07	
54683700	BBP500 G4 LED180/CW PSU S-MB	Clear glass	IK07	
54763600	BBP500 G4 LED180/CW PSU A-WB	Clear glass	IK07	
54856500	BBP500 G4 LED85/NW PSD S-WB	Clear glass	IK07	
54829900	BBP500 G4 LED85/NW PSD S-MB	Clear glass	IK07	
54720900	BBP500 G4 LED85/NW PSD A-WB	Clear glass	IK07	
54800800	BBP500 G4 LED85/CW PSD S-WB	Clear glass	IK07	
54692900	BBP500 G4 LED85/CW PSD S-MB	Clear glass	IK07	
54858900	BBP500 G4 LED85/CW PSD A-WB	Clear glass	IK07	
54831200	BBP500 G4 LED125/NW PSD S-WB	Clear glass	IK07	
54722300	BBP500 G4 LED125/NW PSD S-MB	Clear glass	IK07	
54802200	BBP500 G4 LED125/NW PSD A-WB	Clear glass	IK07	
54694300	BBP500 G4 LED125/CW PSD S-WB	Clear glass	IK07	
54776600	BBP500 G4 LED125/CW PSD S-MB	Clear glass	IK07	
54739100	BBP500 G4 LED125/CW PSD A-WB	Clear glass	IK07	
54765000	BBP500 G4 LED140/NW PSD S-WB	Clear glass	IK07	
54859600	BBP500 G4 LED140/NW PSD S-MB	Clear glass	IK07	
54832900	BBP500 G4 LED140/NW PSD A-WB	Clear glass	IK07	
54778000	BBP500 G4 LED140/CW PSD S-WB	Clear glass	IK07	
54741400	BBP500 G4 LED140/CW PSD S-MB	Clear glass	IK07	
54767400	BBP500 G4 LED140/CW PSD A-WB	Clear glass	IK07	
54861900	BBP500 G4 LED180/NW PSD S-WB	Clear glass	IK07	
54834300	BBP500 G4 LED180/NW PSD S-MB	Clear glass	IK07	
54725400	BBP500 G4 LED180/NW PSD A-WB	Clear glass	IK07	
54805300	BBP500 G4 LED180/CW PSD S-WB	Clear glass	IK07	
54695000	BBP500 G4 LED180/CW PSD S-MB	Clear glass	IK07	
54779700	BBP500 G4 LED180/CW PSD A-WB	Clear glass	IK07	

Approval and Application

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
54762900	BCP500 G4 LED85/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54855800	BCP500 G4 LED85/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54828200	BCP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54793300	BCP500 G4 LED85/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54684400	BCP500 G4 LED85/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54764300	BCP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54857200	BCP500 G4 LED125/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54830500	BCP500 G4 LED125/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54721600	BCP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54801500	BCP500 G4 LED125/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54693600	BCP500 G4 LED125/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54775900	BCP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54738400	BCP500 G4 LED140/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54723000	BCP500 G4 LED140/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54803900	BCP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
51909100	BCP500 G4 LED140/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54777300	BCP500 G4 LED140/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54740700	BCP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54766700	BCP500 G4 LED180/NW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
54860200	BCP500 G4 LED180/NW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces
54833600	BCP500 G4 LED180/NW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
54724700	BCP500 G4 LED180/CW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
54804600	BCP500 G4 LED180/CW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces
54768100	BCP500 G4 LED180/CW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
54704900	BCP500 G4 LED85/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
54751300	BCP500 G4 LED85/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54846600	BCP500 G4 LED85/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54819000	BCP500 G4 LED85/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54710000	BCP500 G4 LED85/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54735300	BCP500 G4 LED85/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54815200	BCP500 G4 LED125/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54705600	BCP500 G4 LED125/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54672100	BCP500 G4 LED125/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54752000	BCP500 G4 LED125/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54847300	BCP500 G4 LED125/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54816900	BCP500 G4 LED125/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54706300	BCP500 G4 LED140/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54673800	BCP500 G4 LED140/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54753700	BCP500 G4 LED140/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54848000	BCP500 G4 LED140/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54820600	BCP500 G4 LED140/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54711700	BCP500 G4 LED140/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54736000	BCP500 G4 LED180/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54817600	BCP500 G4 LED180/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54707000	BCP500 G4 LED180/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54821300	BCP500 G4 LED180/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54712400	BCP500 G4 LED180/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54737700	BCP500 G4 LED180/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54747600	BCP500 G4 LED85/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54774200	BCP500 G4 LED85/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
54868800	BCP500 G4 LED85/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54840400	BCP500 G4 LED85/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54732200	BCP500 G4 LED85/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54748300	BCP500 G4 LED85/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54843500	BCP500 G4 LED125/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54869500	BCP500 G4 LED125/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54841100	BCP500 G4 LED125/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54733900	BCP500 G4 LED125/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54812100	BCP500 G4 LED125/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54702500	BCP500 G4 LED125/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54786500	BCP500 G4 LED140/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54749000	BCP500 G4 LED140/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54844200	BCP500 G4 LED140/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54813800	BCP500 G4 LED140/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54703200	BCP500 G4 LED140/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54671400	BCP500 G4 LED140/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54750600	BCP500 G4 LED180/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54845900	BCP500 G4 LED180/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54870100	BCP500 G4 LED180/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54842800	BCP500 G4 LED180/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54734600	BCP500 G4 LED180/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54814500	BCP500 G4 LED180/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54676900	BBP500 G4 LED180/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54756800	BBP500 G4 LED180/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54850300	BBP500 G4 LED180/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
54742100	BBP500 G4 LED85/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54727800	BBP500 G4 LED85/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54807700	BBP500 G4 LED85/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54697400	BBP500 G4 LED85/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54781000	BBP500 G4 LED85/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54744500	BBP500 G4 LED85/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54770400	BBP500 G4 LED125/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54864000	BBP500 G4 LED125/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54836700	BBP500 G4 LED125/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54728500	BBP500 G4 LED125/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54808400	BBP500 G4 LED125/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54772800	BBP500 G4 LED125/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54866400	BBP500 G4 LED140/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54838100	BBP500 G4 LED140/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54730800	BBP500 G4 LED140/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54810700	BBP500 G4 LED140/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54700100	BBP500 G4 LED140/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54784100	BBP500 G4 LED140/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54746900	BBP500 G4 LED180/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54773500	BBP500 G4 LED180/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54867100	BBP500 G4 LED180/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54818300	BGP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	-
54708700	BGP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	-
54674500	BGP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	-
54754400	BGP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	-

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
54849700	BGP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	-
54822000	BGP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	-
54713100	BGP500 G4 LED180/NW PSU A-WB	-40 to +50 °C	-
54675200	BGP500 G4 LED180/CW PSU A-WB	-40 to +50 °C	-
54862600	BCP500 G4 LED85/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54835000	BCP500 G4 LED85/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54726100	BCP500 G4 LED85/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54806000	BCP500 G4 LED85/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54696700	BCP500 G4 LED85/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54780300	BCP500 G4 LED85/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54743800	BCP500 G4 LED125/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54769800	BCP500 G4 LED125/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54863300	BCP500 G4 LED125/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54698100	BCP500 G4 LED125/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54782700	BCP500 G4 LED125/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54745200	BCP500 G4 LED125/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54771100	BCP500 G4 LED140/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54865700	BCP500 G4 LED140/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54837400	BCP500 G4 LED140/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54729200	BCP500 G4 LED140/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54809100	BCP500 G4 LED140/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54699800	BCP500 G4 LED140/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54783400	BCP500 G4 LED180/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54839800	BCP500 G4 LED180/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54731500	BCP500 G4 LED180/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
54811400	BCP500 G4 LED180/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54701800	BCP500 G4 LED180/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54785800	BCP500 G4 LED180/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54823700	BBP500 G4 LED85/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54714800	BBP500 G4 LED85/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54709400	BBP500 G4 LED85/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54685100	BBP500 G4 LED85/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54787200	BBP500 G4 LED85/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54677600	BBP500 G4 LED85/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54757500	BBP500 G4 LED125/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54795700	BBP500 G4 LED125/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54687500	BBP500 G4 LED125/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54789600	BBP500 G4 LED125/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54679000	BBP500 G4 LED125/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54759900	BBP500 G4 LED125/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54852700	BBP500 G4 LED140/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54825100	BBP500 G4 LED140/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54717900	BBP500 G4 LED140/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54796400	BBP500 G4 LED140/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54688200	BBP500 G4 LED140/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54854100	BBP500 G4 LED140/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54827500	BBP500 G4 LED180/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54719300	BBP500 G4 LED180/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54798800	BBP500 G4 LED180/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54690500	BBP500 G4 LED180/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
54791900	BBP500 G4 LED180/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54682000	BBP500 G4 LED180/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
54715500	BBP500 G4 LED85/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54794000	BBP500 G4 LED85/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54686800	BBP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54788900	BBP500 G4 LED85/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54678300	BBP500 G4 LED85/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54758200	BBP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54851000	BBP500 G4 LED125/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54824400	BBP500 G4 LED125/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54716200	BBP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54680600	BBP500 G4 LED125/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54760500	BBP500 G4 LED125/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54853400	BBP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54826800	BBP500 G4 LED140/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54718600	BBP500 G4 LED140/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54797100	BBP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54689900	BBP500 G4 LED140/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54790200	BBP500 G4 LED140/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54681300	BBP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54761200	BBP500 G4 LED180/NW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
54799500	BBP500 G4 LED180/NW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces
54691200	BBP500 G4 LED180/NW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
54792600	BBP500 G4 LED180/CW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
54683700	BBP500 G4 LED180/CW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
54763600	BBP500 G4 LED180/CW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
54856500	BBP500 G4 LED85/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54829900	BBP500 G4 LED85/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54720900	BBP500 G4 LED85/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54800800	BBP500 G4 LED85/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54692900	BBP500 G4 LED85/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54858900	BBP500 G4 LED85/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54831200	BBP500 G4 LED125/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54722300	BBP500 G4 LED125/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54802200	BBP500 G4 LED125/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54694300	BBP500 G4 LED125/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54776600	BBP500 G4 LED125/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54739100	BBP500 G4 LED125/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54765000	BBP500 G4 LED140/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54859600	BBP500 G4 LED140/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54832900	BBP500 G4 LED140/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54778000	BBP500 G4 LED140/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54741400	BBP500 G4 LED140/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54767400	BBP500 G4 LED140/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54861900	BBP500 G4 LED180/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54834300	BBP500 G4 LED180/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54725400	BBP500 G4 LED180/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54805300	BBP500 G4 LED180/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
54695000	BBP500 G4 LED180/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
54779700	BBP500 G4 LED180/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

GreenPerform Canopy Mini500 G4

