



# Classic, economical and reliable highbay luminaire

## GreenUp Round Highbay

The GreenUp Round Highbay range of luminaires provides the optimal balance between basic performance and price. The family covers a wide product range with a variety of options, competitive specifications, and long-term quality and reliability. The range is suitable for most industrial applications.

### Benefits

- Excellent energy savings, great value for money
- High light quality with a range of lumen packages for different applications
- Robust and reliable

### Features

- 140 lm/W system efficacy
- Narrow and wide beam options
- IP65/IK06 protection
- 50,000 hours lifetime @Ta 35°C
- -20°C to 45°C working temperature

### Application

- Manufacturing
- Warehouse

### Specifications

|               |           |                             |               |
|---------------|-----------|-----------------------------|---------------|
| Mounting type | Surface   | Operating Temperature range | -20 to +45 °C |
|               | Suspended |                             |               |
|               | Pipe      | Light Source                | LED           |

# GreenUp Round Highbay

|                                                 |                            |
|-------------------------------------------------|----------------------------|
| Mains Voltage                                   | 220-240V / 50-60Hz         |
| Mains connection                                | Flying cable               |
| Mechanical Accessories                          | Mounting bracket           |
| Optical Accessories                             | Reflector                  |
| Dimming                                         | PSU: non-dimmable          |
| Material                                        | Housing: die-cast aluminum |
| Lumen maintenance at median useful life 50.000h | L70                        |
| Flicker / Pst / SVM                             | <15%                       |
| Luminous flux                                   | 11klm - 30klm              |
| Power consumption                               | 77W - 207W                 |
| Luminaire efficacy                              | Up to 143lm/W              |
| Correlated color temperature - CCT              | 4000K 6500K                |

|                                |          |
|--------------------------------|----------|
| Color Rendering index - 80 CRI |          |
| Beam angle                     | WB       |
|                                | NB       |
| Reflector material             | Aluminum |
| Optical cover/lens material    | PC       |
| Optical cover/lens finish      | Clear    |
| Protection Class               | Class I  |
| IEC61140                       |          |
| Mechanical impact protection   | IK06     |
| Ingress protection             | IP65     |

## Versions



GreenUp-Round-Highbay-  
Additional-Product-Photo-  
BY518P-SE



GreenUp Round Highbay BY518P  
LED260



Size L




GreenUp Round Highbay BY518P  
LED300




GreenUp Round Highbay BY518P  
LED210

Dimensional drawing



# GreenUp Round Highbay

## Dimensional drawing



| General Information                 |                |
|-------------------------------------|----------------|
| Gear                                | -              |
| Operating and Electrical            |                |
| Protection class IEC                | Safety class I |
| Line Frequency                      | 50 or 60 Hz    |
| Controls and Dimming                |                |
| Dimmable                            | No             |
| Mechanical and Housing              |                |
| Optical cover type                  | Lens           |
| Mech. impact protection code        | IK06           |
| Ingress protection code             | IP65           |
| Approval and Application            |                |
| ENEC mark                           | -              |
| Flammability mark                   | -              |
| Glow-wire test                      | -              |
| Initial Performance (IEC Compliant) |                |
| Luminous flux tolerance             | +/-10%         |

## General Information

| Order Code   | Full Product Name                     | Driver included | Number of gear |  | Service tag |
|--------------|---------------------------------------|-----------------|----------------|--|-------------|
|              |                                       |                 | units          |  |             |
| 911401588745 |                                       | Yes             | 1 unit         |  | -           |
| 911401588845 |                                       | Yes             | 1 unit         |  | -           |
| 911401588945 |                                       | Yes             | 1 unit         |  | -           |
| 911401589045 |                                       | Yes             | 1 unit         |  | -           |
| 911401646407 | BY518P LED210/NW PSU WB GC            | -               | -              |  | Yes         |
| 911401646507 | BY518P LED210/CW PSU WB GC            | -               | -              |  | Yes         |
| 911401647007 | BY518P LED210/NW PSU NB GC            | -               | -              |  | Yes         |
| 911401647107 | BY518P LED210/CW PSU NB GC            | -               | -              |  | Yes         |
| 911401647607 | BY518P LED210/NW PSU WB GM            | -               | -              |  | Yes         |
| 911401647707 | BY518P LED210/CW PSU WB GM            | -               | -              |  | Yes         |
| 911401648307 | BY518P LED210/CW PSU NB GM            | -               | -              |  | Yes         |
| 911401650407 | BY518P G2 LED210/CW PSU 220-240 WB LA | -               | -              |  | Yes         |
| 911401650507 | BY518P G2 LED210/CW PSU 220-240 NB LA | -               | -              |  | Yes         |
| 911401645208 | BY518P LED260/NW PSU WB CAU CL        | -               | -              |  | Yes         |
| 911401676808 | BY518P SE LED105/NW PSU WB GC         | Yes             | 1 unit         |  | Yes         |
| 911401676908 | BY518P SE LED105/CW PSU WB GC         | Yes             | 1 unit         |  | Yes         |
| 911401677008 | BY518P SE LED140/NW PSU WB GC         | Yes             | 1 unit         |  | Yes         |
| 911401677108 | BY518P SE LED140/CW PSU WB GC         | Yes             | 1 unit         |  | Yes         |
| 911401677208 | BY518P SE LED200/NW PSU WB GC         | Yes             | 1 unit         |  | Yes         |
| 911401677308 | BY518P SE LED200/CW PSU WB GC         | Yes             | 1 unit         |  | Yes         |
| 911401677408 | BY518P SE LED245/NW PSU WB GC         | Yes             | 1 unit         |  | Yes         |
| 911401677508 | BY518P SE LED245/CW PSU WB GC         | Yes             | 1 unit         |  | Yes         |
| 911401677608 | BY518P SE LED290/NW PSU WB GC         | Yes             | 1 unit         |  | Yes         |
| 911401677708 | BY518P SE LED290/CW PSU WB GC         | Yes             | 1 unit         |  | Yes         |

| Order Code   | Full Product Name                     | Driver included | Number of gear |  | Service tag |
|--------------|---------------------------------------|-----------------|----------------|--|-------------|
|              |                                       |                 | units          |  |             |
| 911401677808 | BY518P SE LED105/NW PSU WB GM         | Yes             | 1 unit         |  | Yes         |
| 911401677908 | BY518P SE LED105/CW PSU WB GM         | Yes             | 1 unit         |  | Yes         |
| 911401678008 | BY518P SE LED140/NW PSU WB GM         | Yes             | 1 unit         |  | Yes         |
| 911401678108 | BY518P SE LED140/CW PSU WB GM         | Yes             | 1 unit         |  | Yes         |
| 911401678208 | BY518P SE LED200/NW PSU WB GM         | Yes             | 1 unit         |  | Yes         |
| 911401678308 | BY518P SE LED200/CW PSU WB GM         | Yes             | 1 unit         |  | Yes         |
| 911401678408 | BY518P SE LED245/NW PSU WB GM         | Yes             | 1 unit         |  | Yes         |
| 911401678508 | BY518P SE LED245/CW PSU WB GM         | Yes             | 1 unit         |  | Yes         |
| 911401678608 | BY518P SE LED290/NW PSU WB GM         | Yes             | 1 unit         |  | Yes         |
| 911401678708 | BY518P SE LED290/CW PSU WB GM         | Yes             | 1 unit         |  | Yes         |
| 911401647507 | BY518P LED300/CW PSU NB GC            | -               | -              |  | Yes         |
| 911401648107 | BY518P LED300/CW PSU WB GM            | -               | -              |  | Yes         |
| 911401648707 | BY518P LED300/CW PSU NB GM            | -               | -              |  | Yes         |
| 911401650807 | BY518P G2 LED300/CW PSU 220-240 WB LA | -               | -              |  | Yes         |
| 911401650907 | BY518P G2 LED300/CW PSU 220-240 NB LA | -               | -              |  | Yes         |
| 911401645308 | BY518P LED300/NW PSU WB CAU CL        | -               | -              |  | Yes         |
| 911401671207 | BY518P LED110/NW PSU WB GC            | -               | -              |  | Yes         |
| 911401671307 | BY518P LED110/CW PSU WB GC            | -               | -              |  | Yes         |
| 911401671407 | BY518P LED160/NW PSU WB GC            | -               | -              |  | Yes         |
| 911401671507 | BY518P LED160/CW PSU WB GC            | -               | -              |  | Yes         |
| 911401671607 | BY518P LED110/NW PSU NB GC            | -               | -              |  | Yes         |
| 911401671707 | BY518P LED110/CW PSU NB GC            | -               | -              |  | Yes         |
| 911401671807 | BY518P LED160/NW PSU NB GC            | -               | -              |  | Yes         |
| 911401672007 | BY518P LED110/NW PSU WB GM            | -               | -              |  | Yes         |
| 911401672107 | BY518P LED110/CW PSU WB GM            | -               | -              |  | Yes         |
| 911401672207 | BY518P LED160/NW PSU WB GM            | -               | -              |  | Yes         |
| 911401672307 | BY518P LED160/CW PSU WB GM            | -               | -              |  | Yes         |
| 911401672507 | BY518P LED110/CW PSU NB GM            | -               | -              |  | Yes         |
| 911401672707 | BY518P LED160/CW PSU NB GM            | -               | -              |  | Yes         |
| 911401674407 | BY518P G2 LED110/CW PSU 220-240 WB LA | -               | -              |  | Yes         |
| 911401674607 | BY518P G2 LED160/CW PSU 220-240 WB LA | -               | -              |  | Yes         |
| 911401646607 | BY518P LED260/NW PSU WB GC            | -               | -              |  | Yes         |
| 911401646707 | BY518P LED260/CW PSU WB GC            | -               | -              |  | Yes         |
| 911401647207 | BY518P LED260/NW PSU NB GC            | -               | -              |  | Yes         |
| 911401647807 | BY518P LED260/NW PSU WB GM            | -               | -              |  | Yes         |
| 911401647907 | BY518P LED260/CW PSU WB GM            | -               | -              |  | Yes         |
| 911401650607 | BY518P G2 LED260/CW PSU 220-240 WB LA | -               | -              |  | Yes         |
| 911401650707 | BY518P G2 LED260/CW PSU 220-240 NB LA | -               | -              |  | Yes         |
| 911401645108 | BY518P LED210/NW PSU WB CAU CL        | -               | -              |  | Yes         |

Light Technical (1/2)

| Order Code   | Full Product Name | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Order Code   | Full Product Name | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|--------------|-------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
|              |                   | degree(s)                  |                                    |                             |                                 |              |                   | degree(s)                  |                                    |                             |                                 |
| 911401588745 |                   | 120                        | 4000 K                             | >80                         | 163 lm/W                        | 911401588945 |                   | 120                        | 4000 K                             | >80                         | 159 lm/W                        |
| 911401588845 |                   | 120                        | 6500 K                             | >80                         | 163 lm/W                        | 911401589045 |                   | 120                        | 6500 K                             | >80                         | 159 lm/W                        |

## GreenUp Round Highbay

| Order Code   | Full Product Name                              | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|------------------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401646407 | BY518P<br>LED210/NW<br>PSU WB GC               | -                          | 4000 K                             | >80                         | 137 lm/W                        |
| 911401646507 | BY518P<br>LED210/CW<br>PSU WB GC               | -                          | 6500 K                             | >80                         | 137 lm/W                        |
| 911401647007 | BY518P<br>LED210/NW<br>PSU NB GC               | -                          | 4000 K                             | >80                         | 137 lm/W                        |
| 911401647107 | BY518P<br>LED210/CW<br>PSU NB GC               | -                          | 6500 K                             | >80                         | 137 lm/W                        |
| 911401647607 | BY518P<br>LED210/NW<br>PSU WB GM               | -                          | 4000 K                             | >80                         | 137 lm/W                        |
| 911401647707 | BY518P<br>LED210/CW<br>PSU WB GM               | -                          | 6500 K                             | >80                         | 137 lm/W                        |
| 911401648307 | BY518P<br>LED210/CW<br>PSU NB GM               | -                          | 6500 K                             | >80                         | 137 lm/W                        |
| 911401650407 | BY518P G2<br>LED210/CW<br>PSU 220-240<br>WB LA | -                          | 6500 K                             | >80                         | 137 lm/W                        |
| 911401650507 | BY518P G2<br>LED210/CW<br>PSU 220-240<br>NB LA | -                          | 6500 K                             | >80                         | 137 lm/W                        |
| 911401645208 | BY518P<br>LED260/NW<br>PSU WB CAU<br>CL        | -                          | 4000 K                             | ≥80                         | 139 lm/W                        |
| 911401676808 | BY518P SE<br>LED105/NW<br>PSU WB GC            | 120 degree(s)              | 4000 K                             | >80                         | 150 lm/W                        |
| 911401676908 | BY518P SE<br>LED105/CW<br>PSU WB GC            | 120 degree(s)              | 6500 K                             | >80                         | 150 lm/W                        |
| 911401677008 | BY518P SE<br>LED140/NW<br>PSU WB GC            | 120 degree(s)              | 4000 K                             | >80                         | 143 lm/W                        |
| 911401677108 | BY518P SE<br>LED140/CW<br>PSU WB GC            | 120 degree(s)              | 6500 K                             | >80                         | 143 lm/W                        |
| 911401677208 | BY518P SE<br>LED200/NW<br>PSU WB GC            | 120 degree(s)              | 4000 K                             | >80                         | 148 lm/W                        |

| Order Code   | Full Product Name                   | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|-------------------------------------|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 911401677308 | BY518P SE<br>LED200/CW<br>PSU WB GC | 120 degree(s)              | 6500 K                             | >80                         | 148 lm/W                        |
| 911401677408 | BY518P SE<br>LED245/NW<br>PSU WB GC | 120 degree(s)              | 4000 K                             | >80                         | 153 lm/W                        |
| 911401677508 | BY518P SE<br>LED245/CW<br>PSU WB GC | 120 degree(s)              | 6500 K                             | >80                         | 153 lm/W                        |
| 911401677608 | BY518P SE<br>LED290/NW<br>PSU WB GC | 120 degree(s)              | 4000 K                             | >80                         | 151 lm/W                        |
| 911401677708 | BY518P SE<br>LED290/CW<br>PSU WB GC | 120 degree(s)              | 6500 K                             | >80                         | 151 lm/W                        |
| 911401677808 | BY518P SE<br>LED105/NW<br>PSU WB GM | 120 degree(s)              | 4000 K                             | >80                         | 150 lm/W                        |
| 911401677908 | BY518P SE<br>LED105/CW<br>PSU WB GM | 120 degree(s)              | 6500 K                             | >80                         | 150 lm/W                        |
| 911401678008 | BY518P SE<br>LED140/NW<br>PSU WB GM | 120 degree(s)              | 4000 K                             | >80                         | 143 lm/W                        |
| 911401678108 | BY518P SE<br>LED140/CW<br>PSU WB GM | 120 degree(s)              | 6500 K                             | >80                         | 143 lm/W                        |
| 911401678208 | BY518P SE<br>LED200/NW<br>PSU WB GM | 120 degree(s)              | 4000 K                             | >80                         | 148 lm/W                        |
| 911401678308 | BY518P SE<br>LED200/CW<br>PSU WB GM | 120 degree(s)              | 6500 K                             | >80                         | 148 lm/W                        |
| 911401678408 | BY518P SE<br>LED245/NW<br>PSU WB GM | 120 degree(s)              | 4000 K                             | >80                         | 153 lm/W                        |
| 911401678508 | BY518P SE<br>LED245/CW<br>PSU WB GM | 120 degree(s)              | 6500 K                             | >80                         | 153 lm/W                        |
| 911401678608 | BY518P SE<br>LED290/NW<br>PSU WB GM | 120 degree(s)              | 4000 K                             | >80                         | 151 lm/W                        |
| 911401678708 | BY518P SE<br>LED290/CW<br>PSU WB GM | 120 degree(s)              | 6500 K                             | >80                         | 151 lm/W                        |
| 911401647507 | BY518P<br>LED300/CW<br>PSU NB GC    | -                          | 6500 K                             | >80                         | 143 lm/W                        |

GreenUp Round Highbay

|              |                                                | Beam     | Correlated  | Color     | Luminous |
|--------------|------------------------------------------------|----------|-------------|-----------|----------|
|              | Full Product                                   | angle of | Color       | rendering | Efficacy |
| Order Code   | Name                                           | light    | Temperature | index     | (rated)  |
|              |                                                | source   | (Nom)       | (CRI)     | (Nom)    |
| 911401648107 | BY518P<br>LED300/CW<br>PSU WB GM               | -        | 6500 K      | >80       | 143 lm/W |
| 911401648707 | BY518P<br>LED300/CW<br>PSU NB GM               | -        | 6500 K      | >80       | 143 lm/W |
| 911401650807 | BY518P G2<br>LED300/CW<br>PSU 220-240<br>WB LA | -        | 6500 K      | >80       | 143 lm/W |
| 911401650907 | BY518P G2<br>LED300/CW<br>PSU 220-240<br>NB LA | -        | 6500 K      | >80       | 143 lm/W |
| 911401645308 | BY518P<br>LED300/NW<br>PSU WB CAU<br>CL        | -        | 4000 K      | ≥80       | 145 lm/W |
| 911401671207 | BY518P<br>LED110/NW<br>PSU WB GC               | -        | 4000 K      | >80       | 143 lm/W |
| 911401671307 | BY518P<br>LED110/CW<br>PSU WB GC               | -        | 6500 K      | >80       | 143 lm/W |
| 911401671407 | BY518P<br>LED160/NW<br>PSU WB GC               | -        | 4000 K      | >80       | 139 lm/W |
| 911401671507 | BY518P<br>LED160/CW<br>PSU WB GC               | -        | 6500 K      | >80       | 139 lm/W |
| 911401671607 | BY518P<br>LED110/NW<br>PSU NB GC               | -        | 4000 K      | >80       | 143 lm/W |
| 911401671707 | BY518P<br>LED110/CW<br>PSU NB GC               | -        | 6500 K      | >80       | 143 lm/W |
| 911401671807 | BY518P<br>LED160/NW<br>PSU NB GC               | -        | 4000 K      | >80       | 139 lm/W |
| 911401672007 | BY518P<br>LED110/NW<br>PSU WB GM               | -        | 4000 K      | >80       | 143 lm/W |
| 911401672107 | BY518P<br>LED110/CW<br>PSU WB GM               | -        | 6500 K      | >80       | 143 lm/W |
| 911401672207 | BY518P<br>LED160/NW<br>PSU WB GM               | -        | 4000 K      | >80       | 139 lm/W |

|              |                                                | Beam     | Correlated  | Color     | Luminous |
|--------------|------------------------------------------------|----------|-------------|-----------|----------|
|              | Full Product                                   | angle of | Color       | rendering | Efficacy |
| Order Code   | Name                                           | light    | Temperature | index     | (rated)  |
|              |                                                | source   | (Nom)       | (CRI)     | (Nom)    |
| 911401672307 | BY518P<br>LED160/CW<br>PSU WB GM               | -        | 6500 K      | >80       | 139 lm/W |
| 911401672507 | BY518P<br>LED110/CW<br>PSU NB GM               | -        | 6500 K      | >80       | 143 lm/W |
| 911401672707 | BY518P<br>LED160/CW<br>PSU NB GM               | -        | 6500 K      | >80       | 139 lm/W |
| 911401674407 | BY518P G2<br>LED110/CW<br>PSU 220-240<br>WB LA | -        | 6500 K      | >80       | 143 lm/W |
| 911401674607 | BY518P G2<br>LED160/CW<br>PSU 220-240<br>WB LA | -        | 6500 K      | >80       | 139 lm/W |
| 911401646607 | BY518P<br>LED260/NW<br>PSU WB GC               | -        | 4000 K      | >80       | 139 lm/W |
| 911401646707 | BY518P<br>LED260/CW<br>PSU WB GC               | -        | 6500 K      | >80       | 139 lm/W |
| 911401647207 | BY518P<br>LED260/NW<br>PSU NB GC               | -        | 4000 K      | >80       | 139 lm/W |
| 911401647807 | BY518P<br>LED260/NW<br>PSU WB GM               | -        | 4000 K      | >80       | 139 lm/W |
| 911401647907 | BY518P<br>LED260/CW<br>PSU WB GM               | -        | 6500 K      | >80       | 139 lm/W |
| 911401650607 | BY518P G2<br>LED260/CW<br>PSU 220-240<br>WB LA | -        | 6500 K      | >80       | 139 lm/W |
| 911401650707 | BY518P G2<br>LED260/CW<br>PSU 220-240<br>NB LA | -        | 6500 K      | >80       | 139 lm/W |
| 911401645108 | BY518P<br>LED210/NW<br>PSU WB CAU<br>CL        | -        | 4000 K      | ≥80       | 136 lm/W |

Light Technical (2/2)

## GreenUp Round Highbay

| Order Code   | Full Product Name                     | Luminous Flux | Number of light sources | Optic type |
|--------------|---------------------------------------|---------------|-------------------------|------------|
| 911401588745 |                                       | 5,000 lm      | 1                       | Wide beam  |
| 911401588845 |                                       | 5,000 lm      | 1                       | Wide beam  |
| 911401588945 |                                       | 7,000 lm      | 1                       | Wide beam  |
| 911401589045 |                                       | 7,000 lm      | 1                       | Wide beam  |
| 911401646407 | BY518P LED210/NW PSU WB GC            | 21,000 lm     | -                       | -          |
| 911401646507 | BY518P LED210/CW PSU WB GC            | 21,000 lm     | -                       | -          |
| 911401647007 | BY518P LED210/NW PSU NB GC            | 21,000 lm     | -                       | -          |
| 911401647107 | BY518P LED210/CW PSU NB GC            | 21,000 lm     | -                       | -          |
| 911401647607 | BY518P LED210/NW PSU WB GM            | 21,000 lm     | -                       | -          |
| 911401647707 | BY518P LED210/CW PSU WB GM            | 21,000 lm     | -                       | -          |
| 911401648307 | BY518P LED210/CW PSU NB GM            | 21,000 lm     | -                       | -          |
| 911401650407 | BY518P G2 LED210/CW PSU 220-240 WB LA | 21,000 lm     | -                       | -          |
| 911401650507 | BY518P G2 LED210/CW PSU 220-240 NB LA | 21,000 lm     | -                       | -          |
| 911401645208 | BY518P LED260/NW PSU WB CAU CL        | 26,000 lm     | -                       | -          |
| 911401676808 | BY518P SE LED105/NW PSU WB GC         | 10,500 lm     | 1                       | Wide beam  |
| 911401676908 | BY518P SE LED105/CW PSU WB GC         | 10,500 lm     | 1                       | Wide beam  |
| 911401677008 | BY518P SE LED140/NW PSU WB GC         | 14,000 lm     | 1                       | Wide beam  |
| 911401677108 | BY518P SE LED140/CW PSU WB GC         | 14,000 lm     | 1                       | Wide beam  |
| 911401677208 | BY518P SE LED200/NW PSU WB GC         | 20,000 lm     | 1                       | Wide beam  |
| 911401677308 | BY518P SE LED200/CW PSU WB GC         | 20,000 lm     | 1                       | Wide beam  |
| 911401677408 | BY518P SE LED245/NW PSU WB GC         | 24,500 lm     | 1                       | Wide beam  |
| 911401677508 | BY518P SE LED245/CW PSU WB GC         | 24,500 lm     | 1                       | Wide beam  |
| 911401677608 | BY518P SE LED290/NW PSU WB GC         | 29,000 lm     | 1                       | Wide beam  |
| 911401677708 | BY518P SE LED290/CW PSU WB GC         | 29,000 lm     | 1                       | Wide beam  |
| 911401677808 | BY518P SE LED105/NW PSU WB GM         | 10,500 lm     | 1                       | Wide beam  |

| Order Code   | Full Product Name                     | Luminous Flux | Number of light sources | Optic type |
|--------------|---------------------------------------|---------------|-------------------------|------------|
| 911401677908 | BY518P SE LED105/CW PSU WB GM         | 10,500 lm     | 1                       | Wide beam  |
| 911401678008 | BY518P SE LED140/NW PSU WB GM         | 14,000 lm     | 1                       | Wide beam  |
| 911401678108 | BY518P SE LED140/CW PSU WB GM         | 14,000 lm     | 1                       | Wide beam  |
| 911401678208 | BY518P SE LED200/NW PSU WB GM         | 20,000 lm     | 1                       | Wide beam  |
| 911401678308 | BY518P SE LED200/CW PSU WB GM         | 20,000 lm     | 1                       | Wide beam  |
| 911401678408 | BY518P SE LED245/NW PSU WB GM         | 24,500 lm     | 1                       | Wide beam  |
| 911401678508 | BY518P SE LED245/CW PSU WB GM         | 24,500 lm     | 1                       | Wide beam  |
| 911401678608 | BY518P SE LED290/NW PSU WB GM         | 29,000 lm     | 1                       | Wide beam  |
| 911401678708 | BY518P SE LED290/CW PSU WB GM         | 29,000 lm     | 1                       | Wide beam  |
| 911401647507 | BY518P LED300/CW PSU NB GC            | 30,000 lm     | -                       | -          |
| 911401648107 | BY518P LED300/CW PSU WB GM            | 30,000 lm     | -                       | -          |
| 911401648707 | BY518P LED300/CW PSU NB GM            | 30,000 lm     | -                       | -          |
| 911401650807 | BY518P G2 LED300/CW PSU 220-240 WB LA | 30,000 lm     | -                       | -          |
| 911401650907 | BY518P G2 LED300/CW PSU 220-240 NB LA | 30,000 lm     | -                       | -          |
| 911401645308 | BY518P LED300/NW PSU WB CAU CL        | 30,000 lm     | -                       | -          |
| 911401671207 | BY518P LED110/NW PSU WB GC            | 11,000 lm     | -                       | -          |
| 911401671307 | BY518P LED110/CW PSU WB GC            | 11,000 lm     | -                       | -          |
| 911401671407 | BY518P LED160/NW PSU WB GC            | 16,000 lm     | -                       | -          |
| 911401671507 | BY518P LED160/CW PSU WB GC            | 16,000 lm     | -                       | -          |
| 911401671607 | BY518P LED110/NW PSU NB GC            | 11,000 lm     | -                       | -          |
| 911401671707 | BY518P LED110/CW PSU NB GC            | 11,000 lm     | -                       | -          |
| 911401671807 | BY518P LED160/NW PSU NB GC            | 16,000 lm     | -                       | -          |
| 911401672007 | BY518P LED110/NW PSU WB GM            | 11,000 lm     | -                       | -          |
| 911401672107 | BY518P LED110/CW PSU WB GM            | 11,000 lm     | -                       | -          |
| 911401672207 | BY518P LED160/NW PSU WB GM            | 16,000 lm     | -                       | -          |



GreenUp Round Highbay

| Order Code   | Full Product Name                     | Luminous Flux | Number of light sources | Optic type |
|--------------|---------------------------------------|---------------|-------------------------|------------|
| 911401672307 | BY518P LED160/CW PSU WB GM            | 16,000 lm     | -                       | -          |
| 911401672507 | BY518P LED110/CW PSU NB GM            | 11,000 lm     | -                       | -          |
| 911401672707 | BY518P LED160/CW PSU NB GM            | 16,000 lm     | -                       | -          |
| 911401674407 | BY518P G2 LED110/CW PSU 220-240 WB LA | 11,000 lm     | -                       | -          |
| 911401674607 | BY518P G2 LED160/CW PSU 220-240 WB LA | 16,000 lm     | -                       | -          |
| 911401646607 | BY518P LED260/NW PSU WB GC            | 26,000 lm     | -                       | -          |
| 911401646707 | BY518P LED260/CW PSU WB GC            | 26,000 lm     | -                       | -          |

Operating and Electrical

| Order Code   | Full Product Name                     | Input Voltage | Power Consumption | Suitable for random switching |
|--------------|---------------------------------------|---------------|-------------------|-------------------------------|
| 911401588745 |                                       | 220-240 V     | 30.5 W            | No                            |
| 911401588845 |                                       | 220-240 V     | 30.5 W            | No                            |
| 911401588945 |                                       | 220-240 V     | 44 W              | No                            |
| 911401589045 |                                       | 220-240 V     | 44 W              | No                            |
| 911401646407 | BY518P LED210/NW PSU WB GC            | 220-240 V     | 154 W             | -                             |
| 911401646507 | BY518P LED210/CW PSU WB GC            | 220-240 V     | 154 W             | -                             |
| 911401647007 | BY518P LED210/NW PSU NB GC            | 220-240 V     | 154 W             | -                             |
| 911401647107 | BY518P LED210/CW PSU NB GC            | 220-240 V     | 154 W             | -                             |
| 911401647607 | BY518P LED210/NW PSU WB GM            | 220-240 V     | 154 W             | -                             |
| 911401647707 | BY518P LED210/CW PSU WB GM            | 220-240 V     | 154 W             | -                             |
| 911401648307 | BY518P LED210/CW PSU NB GM            | 220-240 V     | 154 W             | -                             |
| 911401650407 | BY518P G2 LED210/CW PSU 220-240 WB LA | 220-240 V     | 154 W             | -                             |
| 911401650507 | BY518P G2 LED210/CW PSU 220-240 NB LA | 220-240 V     | 154 W             | -                             |
| 911401645208 | BY518P LED260/NW PSU WB CAU CL        | 220-240 V     | 187 W             | -                             |
| 911401676808 | BY518P SE LED105/NW PSU WB GC         | 220 to 240 V  | 70 W              | No                            |
| 911401676908 | BY518P SE LED105/CW PSU WB GC         | 220 to 240 V  | 70 W              | No                            |
| 911401677008 | BY518P SE LED140/NW PSU WB GC         | 220 to 240 V  | 98 W              | No                            |

| Order Code   | Full Product Name                     | Luminous Flux | Number of light sources | Optic type |
|--------------|---------------------------------------|---------------|-------------------------|------------|
| 911401647207 | BY518P LED260/NW PSU NB GC            | 26,000 lm     | -                       | -          |
| 911401647807 | BY518P LED260/NW PSU WB GM            | 26,000 lm     | -                       | -          |
| 911401647907 | BY518P LED260/CW PSU WB GM            | 26,000 lm     | -                       | -          |
| 911401650607 | BY518P G2 LED260/CW PSU 220-240 WB LA | 26,000 lm     | -                       | -          |
| 911401650707 | BY518P G2 LED260/CW PSU 220-240 NB LA | 26,000 lm     | -                       | -          |
| 911401645108 | BY518P LED210/NW PSU WB CAU CL        | 21,000 lm     | -                       | -          |

| Order Code   | Full Product Name             | Input Voltage | Power Consumption | Suitable for random switching |
|--------------|-------------------------------|---------------|-------------------|-------------------------------|
| 911401677108 | BY518P SE LED140/CW PSU WB GC | 220 to 240 V  | 98 W              | No                            |
| 911401677208 | BY518P SE LED200/NW PSU WB GC | 220 to 240 V  | 135 W             | No                            |
| 911401677308 | BY518P SE LED200/CW PSU WB GC | 220 to 240 V  | 135 W             | No                            |
| 911401677408 | BY518P SE LED245/NW PSU WB GC | 220 to 240 V  | 160 W             | No                            |
| 911401677508 | BY518P SE LED245/CW PSU WB GC | 220 to 240 V  | 160 W             | No                            |
| 911401677608 | BY518P SE LED290/NW PSU WB GC | 220 to 240 V  | 192 W             | No                            |
| 911401677708 | BY518P SE LED290/CW PSU WB GC | 220 to 240 V  | 192 W             | No                            |
| 911401677808 | BY518P SE LED105/NW PSU WB GM | 220 to 240 V  | 70 W              | No                            |
| 911401677908 | BY518P SE LED105/CW PSU WB GM | 220 to 240 V  | 70 W              | No                            |
| 911401678008 | BY518P SE LED140/NW PSU WB GM | 220 to 240 V  | 98 W              | No                            |
| 911401678108 | BY518P SE LED140/CW PSU WB GM | 220 to 240 V  | 98 W              | No                            |
| 911401678208 | BY518P SE LED200/NW PSU WB GM | 220 to 240 V  | 135 W             | No                            |
| 911401678308 | BY518P SE LED200/CW PSU WB GM | 220 to 240 V  | 135 W             | No                            |
| 911401678408 | BY518P SE LED245/NW PSU WB GM | 220 to 240 V  | 160 W             | No                            |

GreenUp Round Highbay

| Order Code   | Full Product Name                     | Input Voltage | Power       | Suitable for random switching |
|--------------|---------------------------------------|---------------|-------------|-------------------------------|
|              |                                       |               | Consumption |                               |
| 911401678508 | BY518P SE LED245/CW PSU WB GM         | 220 to 240 V  | 160 W       | No                            |
| 911401678608 | BY518P SE LED290/NW PSU WB GM         | 220 to 240 V  | 192 W       | No                            |
| 911401678708 | BY518P SE LED290/CW PSU WB GM         | 220 to 240 V  | 192 W       | No                            |
| 911401647507 | BY518P LED300/CW PSU NB GC            | 220–240 V     | 207 W       | -                             |
| 911401648107 | BY518P LED300/CW PSU WB GM            | 220–240 V     | 207 W       | -                             |
| 911401648707 | BY518P LED300/CW PSU NB GM            | 220–240 V     | 207 W       | -                             |
| 911401650807 | BY518P G2 LED300/CW PSU 220–240 WB LA | 220–240 V     | 207 W       | -                             |
| 911401650907 | BY518P G2 LED300/CW PSU 220–240 NB LA | 220–240 V     | 207 W       | -                             |
| 911401645308 | BY518P LED300/NW PSU WB CAU CL        | 220–240 V     | 207 W       | -                             |
| 911401671207 | BY518P LED110/NW PSU WB GC            | 220–240 V     | 77 W        | -                             |
| 911401671307 | BY518P LED110/CW PSU WB GC            | 220–240 V     | 77 W        | -                             |
| 911401671407 | BY518P LED160/NW PSU WB GC            | 220–240 V     | 115 W       | -                             |
| 911401671507 | BY518P LED160/CW PSU WB GC            | 220–240 V     | 115 W       | -                             |
| 911401671607 | BY518P LED110/NW PSU NB GC            | 220–240 V     | 77 W        | -                             |
| 911401671707 | BY518P LED110/CW PSU NB GC            | 220–240 V     | 77 W        | -                             |
| 911401671807 | BY518P LED160/NW PSU NB GC            | 220–240 V     | 115 W       | -                             |

| Order Code   | Full Product Name                     | Input Voltage | Power       | Suitable for random switching |
|--------------|---------------------------------------|---------------|-------------|-------------------------------|
|              |                                       |               | Consumption |                               |
| 911401672007 | BY518P LED110/NW PSU WB GM            | 220–240 V     | 77 W        | -                             |
| 911401672107 | BY518P LED110/CW PSU WB GM            | 220–240 V     | 77 W        | -                             |
| 911401672207 | BY518P LED160/NW PSU WB GM            | 220–240 V     | 115 W       | -                             |
| 911401672307 | BY518P LED160/CW PSU WB GM            | 220–240 V     | 115 W       | -                             |
| 911401672507 | BY518P LED110/CW PSU NB GM            | 220–240 V     | 77 W        | -                             |
| 911401672707 | BY518P LED160/CW PSU NB GM            | 220–240 V     | 115 W       | -                             |
| 911401674407 | BY518P G2 LED110/CW PSU 220–240 WB LA | 220–240 V     | 77 W        | -                             |
| 911401674607 | BY518P G2 LED160/CW PSU 220–240 WB LA | 220–240 V     | 115 W       | -                             |
| 911401646607 | BY518P LED260/NW PSU WB GC            | 220–240 V     | 187 W       | -                             |
| 911401646707 | BY518P LED260/CW PSU WB GC            | 220–240 V     | 187 W       | -                             |
| 911401647207 | BY518P LED260/NW PSU NB GC            | 220–240 V     | 187 W       | -                             |
| 911401647807 | BY518P LED260/NW PSU WB GM            | 220–240 V     | 187 W       | -                             |
| 911401647907 | BY518P LED260/CW PSU WB GM            | 220–240 V     | 187 W       | -                             |
| 911401650607 | BY518P G2 LED260/CW PSU 220–240 WB LA | 220–240 V     | 187 W       | -                             |
| 911401650707 | BY518P G2 LED260/CW PSU 220–240 NB LA | 220–240 V     | 187 W       | -                             |
| 911401645108 | BY518P LED210/NW PSU WB CAU CL        | 220–240 V     | 154 W       | -                             |

Controls and Dimming

| Order Code   | Full Product Name                     | Maximum dim level |
|--------------|---------------------------------------|-------------------|
| 911401588745 |                                       | Not applicable    |
| 911401588845 |                                       | Not applicable    |
| 911401588945 |                                       | Not applicable    |
| 911401589045 |                                       | Not applicable    |
| 911401646407 | BY518P LED210/NW PSU WB GC            | -                 |
| 911401646507 | BY518P LED210/CW PSU WB GC            | -                 |
| 911401647007 | BY518P LED210/NW PSU NB GC            | -                 |
| 911401647107 | BY518P LED210/CW PSU NB GC            | -                 |
| 911401647607 | BY518P LED210/NW PSU WB GM            | -                 |
| 911401647707 | BY518P LED210/CW PSU WB GM            | -                 |
| 911401648307 | BY518P LED210/CW PSU NB GM            | -                 |
| 911401650407 | BY518P G2 LED210/CW PSU 220–240 WB LA | -                 |
| 911401650507 | BY518P G2 LED210/CW PSU 220–240 NB LA | -                 |
| 911401645208 | BY518P LED260/NW PSU WB CAU CL        | -                 |

| Order Code   | Full Product Name             | Maximum dim level |
|--------------|-------------------------------|-------------------|
| 911401676808 | BY518P SE LED105/NW PSU WB GC | Not applicable    |
| 911401676908 | BY518P SE LED105/CW PSU WB GC | Not applicable    |
| 911401677008 | BY518P SE LED140/NW PSU WB GC | Not applicable    |
| 911401677108 | BY518P SE LED140/CW PSU WB GC | Not applicable    |
| 911401677208 | BY518P SE LED200/NW PSU WB GC | Not applicable    |
| 911401677308 | BY518P SE LED200/CW PSU WB GC | Not applicable    |
| 911401677408 | BY518P SE LED245/NW PSU WB GC | Not applicable    |
| 911401677508 | BY518P SE LED245/CW PSU WB GC | Not applicable    |
| 911401677608 | BY518P SE LED290/NW PSU WB GC | Not applicable    |
| 911401677708 | BY518P SE LED290/CW PSU WB GC | Not applicable    |
| 911401677808 | BY518P SE LED105/NW PSU WB GM | Not applicable    |
| 911401677908 | BY518P SE LED105/CW PSU WB GM | Not applicable    |
| 911401678008 | BY518P SE LED140/NW PSU WB GM | Not applicable    |
| 911401678108 | BY518P SE LED140/CW PSU WB GM | Not applicable    |

GreenUp Round Highbay

| Order Code   | Full Product Name                     | Maximum dim level |
|--------------|---------------------------------------|-------------------|
| 911401678208 | BY518P SE LED200/NW PSU WB GM         | Not applicable    |
| 911401678308 | BY518P SE LED200/CW PSU WB GM         | Not applicable    |
| 911401678408 | BY518P SE LED245/NW PSU WB GM         | Not applicable    |
| 911401678508 | BY518P SE LED245/CW PSU WB GM         | Not applicable    |
| 911401678608 | BY518P SE LED290/NW PSU WB GM         | Not applicable    |
| 911401678708 | BY518P SE LED290/CW PSU WB GM         | Not applicable    |
| 911401647507 | BY518P LED300/CW PSU NB GC            | -                 |
| 911401648107 | BY518P LED300/CW PSU WB GM            | -                 |
| 911401648707 | BY518P LED300/CW PSU NB GM            | -                 |
| 911401650807 | BY518P G2 LED300/CW PSU 220-240 WB LA | -                 |
| 911401650907 | BY518P G2 LED300/CW PSU 220-240 NB LA | -                 |
| 911401645308 | BY518P LED300/NW PSU WB CAU CL        | -                 |
| 911401671207 | BY518P LED110/NW PSU WB GC            | -                 |
| 911401671307 | BY518P LED110/CW PSU WB GC            | -                 |
| 911401671407 | BY518P LED160/NW PSU WB GC            | -                 |
| 911401671507 | BY518P LED160/CW PSU WB GC            | -                 |
| 911401671607 | BY518P LED110/NW PSU NB GC            | -                 |
| 911401671707 | BY518P LED110/CW PSU NB GC            | -                 |

| Order Code   | Full Product Name                     | Maximum dim level |
|--------------|---------------------------------------|-------------------|
| 911401671807 | BY518P LED160/NW PSU NB GC            | -                 |
| 911401672007 | BY518P LED110/NW PSU WB GM            | -                 |
| 911401672107 | BY518P LED110/CW PSU WB GM            | -                 |
| 911401672207 | BY518P LED160/NW PSU WB GM            | -                 |
| 911401672307 | BY518P LED160/CW PSU WB GM            | -                 |
| 911401672507 | BY518P LED110/CW PSU NB GM            | -                 |
| 911401672707 | BY518P LED160/CW PSU NB GM            | -                 |
| 911401674407 | BY518P G2 LED110/CW PSU 220-240 WB LA | -                 |
| 911401674607 | BY518P G2 LED160/CW PSU 220-240 WB LA | -                 |
| 911401646607 | BY518P LED260/NW PSU WB GC            | -                 |
| 911401646707 | BY518P LED260/CW PSU WB GC            | -                 |
| 911401647207 | BY518P LED260/NW PSU NB GC            | -                 |
| 911401647807 | BY518P LED260/NW PSU WB GM            | -                 |
| 911401647907 | BY518P LED260/CW PSU WB GM            | -                 |
| 911401650607 | BY518P G2 LED260/CW PSU 220-240 WB LA | -                 |
| 911401650707 | BY518P G2 LED260/CW PSU 220-240 NB LA | -                 |
| 911401645108 | BY518P LED210/NW PSU WB CAU CL        | -                 |

Mechanical and Housing

| Order Code   | Full Product Name                     | Housing Color |
|--------------|---------------------------------------|---------------|
| 911401588745 |                                       | Grey          |
| 911401588845 |                                       | Grey          |
| 911401588945 |                                       | Grey          |
| 911401589045 |                                       | Grey          |
| 911401646407 | BY518P LED210/NW PSU WB GC            | Gray          |
| 911401646507 | BY518P LED210/CW PSU WB GC            | Gray          |
| 911401647007 | BY518P LED210/NW PSU NB GC            | Gray          |
| 911401647107 | BY518P LED210/CW PSU NB GC            | Gray          |
| 911401647607 | BY518P LED210/NW PSU WB GM            | Gray          |
| 911401647707 | BY518P LED210/CW PSU WB GM            | Gray          |
| 911401648307 | BY518P LED210/CW PSU NB GM            | Gray          |
| 911401650407 | BY518P G2 LED210/CW PSU 220-240 WB LA | Gray          |
| 911401650507 | BY518P G2 LED210/CW PSU 220-240 NB LA | Gray          |
| 911401645208 | BY518P LED260/NW PSU WB CAU CL        | Gray          |
| 911401676808 | BY518P SE LED105/NW PSU WB GC         | Grey          |
| 911401676908 | BY518P SE LED105/CW PSU WB GC         | Grey          |
| 911401677008 | BY518P SE LED140/NW PSU WB GC         | Grey          |
| 911401677108 | BY518P SE LED140/CW PSU WB GC         | Grey          |
| 911401677208 | BY518P SE LED200/NW PSU WB GC         | Grey          |
| 911401677308 | BY518P SE LED200/CW PSU WB GC         | Grey          |
| 911401677408 | BY518P SE LED245/NW PSU WB GC         | Grey          |
| 911401677508 | BY518P SE LED245/CW PSU WB GC         | Grey          |
| 911401677608 | BY518P SE LED290/NW PSU WB GC         | Grey          |
| 911401677708 | BY518P SE LED290/CW PSU WB GC         | Grey          |
| 911401677808 | BY518P SE LED105/NW PSU WB GM         | Grey          |
| 911401677908 | BY518P SE LED105/CW PSU WB GM         | Grey          |
| 911401678008 | BY518P SE LED140/NW PSU WB GM         | Grey          |
| 911401678108 | BY518P SE LED140/CW PSU WB GM         | Grey          |
| 911401678208 | BY518P SE LED200/NW PSU WB GM         | Grey          |
| 911401678308 | BY518P SE LED200/CW PSU WB GM         | Grey          |

| Order Code   | Full Product Name                     | Housing Color |
|--------------|---------------------------------------|---------------|
| 911401678408 | BY518P SE LED245/NW PSU WB GM         | Grey          |
| 911401678508 | BY518P SE LED245/CW PSU WB GM         | Grey          |
| 911401678608 | BY518P SE LED290/NW PSU WB GM         | Grey          |
| 911401678708 | BY518P SE LED290/CW PSU WB GM         | Grey          |
| 911401647507 | BY518P LED300/CW PSU NB GC            | Gray          |
| 911401648107 | BY518P LED300/CW PSU WB GM            | Gray          |
| 911401648707 | BY518P LED300/CW PSU NB GM            | Gray          |
| 911401650807 | BY518P G2 LED300/CW PSU 220-240 WB LA | Gray          |
| 911401650907 | BY518P G2 LED300/CW PSU 220-240 NB LA | Gray          |
| 911401645308 | BY518P LED300/NW PSU WB CAU CL        | Gray          |
| 911401671207 | BY518P LED110/NW PSU WB GC            | Gray          |
| 911401671307 | BY518P LED110/CW PSU WB GC            | Gray          |
| 911401671407 | BY518P LED160/NW PSU WB GC            | Gray          |
| 911401671507 | BY518P LED160/CW PSU WB GC            | Gray          |
| 911401671607 | BY518P LED110/NW PSU NB GC            | Gray          |
| 911401671707 | BY518P LED110/CW PSU NB GC            | Gray          |
| 911401671807 | BY518P LED160/NW PSU NB GC            | Gray          |
| 911401672007 | BY518P LED110/NW PSU WB GM            | Gray          |
| 911401672107 | BY518P LED110/CW PSU WB GM            | Gray          |
| 911401672207 | BY518P LED160/NW PSU WB GM            | Gray          |
| 911401672307 | BY518P LED160/CW PSU WB GM            | Gray          |
| 911401672507 | BY518P LED110/CW PSU NB GM            | Gray          |
| 911401672707 | BY518P LED160/CW PSU NB GM            | Gray          |
| 911401674407 | BY518P G2 LED110/CW PSU 220-240 WB LA | Gray          |
| 911401674607 | BY518P G2 LED160/CW PSU 220-240 WB LA | Gray          |
| 911401646607 | BY518P LED260/NW PSU WB GC            | Gray          |
| 911401646707 | BY518P LED260/CW PSU WB GC            | Gray          |
| 911401647207 | BY518P LED260/NW PSU NB GC            | Gray          |
| 911401647807 | BY518P LED260/NW PSU WB GM            | Gray          |
| 911401647907 | BY518P LED260/CW PSU WB GM            | Gray          |

| Order Code   | Full Product Name                     | Housing Color |
|--------------|---------------------------------------|---------------|
| 911401650607 | BY518P G2 LED260/CW PSU 220-240 WB LA | Gray          |
| 911401650707 | BY518P G2 LED260/CW PSU 220-240 NB LA | Gray          |

Approval and Application

| Order Code   | Full Product Name                     | Ambient temperature range | CE mark |
|--------------|---------------------------------------|---------------------------|---------|
| 911401588745 |                                       | -30 to +45 °C             | Yes     |
| 911401588845 |                                       | -30 to +45 °C             | Yes     |
| 911401588945 |                                       | -30 to +45 °C             | Yes     |
| 911401589045 |                                       | -30 to +45 °C             | Yes     |
| 911401646407 | BY518P LED210/NW PSU WB GC            | -20 to +45 °C             | Yes     |
| 911401646507 | BY518P LED210/CW PSU WB GC            | -20 to +45 °C             | Yes     |
| 911401647007 | BY518P LED210/NW PSU NB GC            | -20 to +45 °C             | Yes     |
| 911401647107 | BY518P LED210/CW PSU NB GC            | -20 to +45 °C             | Yes     |
| 911401647607 | BY518P LED210/NW PSU WB GM            | -20 to +45 °C             | Yes     |
| 911401647707 | BY518P LED210/CW PSU WB GM            | -20 to +45 °C             | Yes     |
| 911401648307 | BY518P LED210/CW PSU NB GM            | -20 to +45 °C             | Yes     |
| 911401650407 | BY518P G2 LED210/CW PSU 220-240 WB LA | -20 to +45 °C             | Yes     |
| 911401650507 | BY518P G2 LED210/CW PSU 220-240 NB LA | -20 to +45 °C             | Yes     |
| 911401645208 | BY518P LED260/NW PSU WB CAU CL        | -20 to +45 °C             | No      |
| 911401676808 | BY518P SE LED105/NW PSU WB GC         | -30 to +45 °C             | Yes     |
| 911401676908 | BY518P SE LED105/CW PSU WB GC         | -30 to +45 °C             | Yes     |
| 911401677008 | BY518P SE LED140/NW PSU WB GC         | -30 to +45 °C             | Yes     |
| 911401677108 | BY518P SE LED140/CW PSU WB GC         | -30 to +45 °C             | Yes     |
| 911401677208 | BY518P SE LED200/NW PSU WB GC         | -30 to +45 °C             | Yes     |
| 911401677308 | BY518P SE LED200/CW PSU WB GC         | -30 to +45 °C             | Yes     |
| 911401677408 | BY518P SE LED245/NW PSU WB GC         | -30 to +45 °C             | Yes     |
| 911401677508 | BY518P SE LED245/CW PSU WB GC         | -30 to +45 °C             | Yes     |
| 911401677608 | BY518P SE LED290/NW PSU WB GC         | -30 to +45 °C             | Yes     |
| 911401677708 | BY518P SE LED290/CW PSU WB GC         | -30 to +45 °C             | Yes     |
| 911401677808 | BY518P SE LED105/NW PSU WB GM         | -30 to +45 °C             | Yes     |
| 911401677908 | BY518P SE LED105/CW PSU WB GM         | -30 to +45 °C             | Yes     |
| 911401678008 | BY518P SE LED140/NW PSU WB GM         | -30 to +45 °C             | Yes     |
| 911401678108 | BY518P SE LED140/CW PSU WB GM         | -30 to +45 °C             | Yes     |

| Order Code   | Full Product Name              | Housing Color |
|--------------|--------------------------------|---------------|
| 911401645108 | BY518P LED210/NW PSU WB CAU CL | Gray          |

| Order Code   | Full Product Name                     | Ambient temperature range | CE mark |
|--------------|---------------------------------------|---------------------------|---------|
| 911401678208 | BY518P SE LED200/NW PSU WB GM         | -30 to +45 °C             | Yes     |
| 911401678308 | BY518P SE LED200/CW PSU WB GM         | -30 to +45 °C             | Yes     |
| 911401678408 | BY518P SE LED245/NW PSU WB GM         | -30 to +45 °C             | Yes     |
| 911401678508 | BY518P SE LED245/CW PSU WB GM         | -30 to +45 °C             | Yes     |
| 911401678608 | BY518P SE LED290/NW PSU WB GM         | -30 to +45 °C             | Yes     |
| 911401678708 | BY518P SE LED290/CW PSU WB GM         | -30 to +45 °C             | Yes     |
| 911401647507 | BY518P LED300/CW PSU NB GC            | -20 to +45 °C             | Yes     |
| 911401648107 | BY518P LED300/CW PSU WB GM            | -20 to +45 °C             | Yes     |
| 911401648707 | BY518P LED300/CW PSU NB GM            | -20 to +45 °C             | Yes     |
| 911401650807 | BY518P G2 LED300/CW PSU 220-240 WB LA | -20 to +45 °C             | Yes     |
| 911401650907 | BY518P G2 LED300/CW PSU 220-240 NB LA | -20 to +45 °C             | Yes     |
| 911401645308 | BY518P LED300/NW PSU WB CAU CL        | -20 to +45 °C             | No      |
| 911401671207 | BY518P LED110/NW PSU WB GC            | -20 to +45 °C             | Yes     |
| 911401671307 | BY518P LED110/CW PSU WB GC            | -20 to +45 °C             | Yes     |
| 911401671407 | BY518P LED160/NW PSU WB GC            | -20 to +45 °C             | Yes     |
| 911401671507 | BY518P LED160/CW PSU WB GC            | -20 to +45 °C             | Yes     |
| 911401671607 | BY518P LED110/NW PSU NB GC            | -20 to +45 °C             | Yes     |
| 911401671707 | BY518P LED110/CW PSU NB GC            | -20 to +45 °C             | Yes     |
| 911401671807 | BY518P LED160/NW PSU NB GC            | -20 to +45 °C             | Yes     |
| 911401672007 | BY518P LED110/NW PSU WB GM            | -20 to +45 °C             | Yes     |
| 911401672107 | BY518P LED110/CW PSU WB GM            | -20 to +45 °C             | Yes     |
| 911401672207 | BY518P LED160/NW PSU WB GM            | -20 to +45 °C             | Yes     |
| 911401672307 | BY518P LED160/CW PSU WB GM            | -20 to +45 °C             | Yes     |
| 911401672507 | BY518P LED110/CW PSU NB GM            | -20 to +45 °C             | Yes     |
| 911401672707 | BY518P LED160/CW PSU NB GM            | -20 to +45 °C             | Yes     |
| 911401674407 | BY518P G2 LED110/CW PSU 220-240 WB LA | -20 to +45 °C             | Yes     |
| 911401674607 | BY518P G2 LED160/CW PSU 220-240 WB LA | -20 to +45 °C             | Yes     |
| 911401646607 | BY518P LED260/NW PSU WB GC            | -20 to +45 °C             | Yes     |
| 911401646707 | BY518P LED260/CW PSU WB GC            | -20 to +45 °C             | Yes     |
| 911401647207 | BY518P LED260/NW PSU NB GC            | -20 to +45 °C             | Yes     |
| 911401647807 | BY518P LED260/NW PSU WB GM            | -20 to +45 °C             | Yes     |

GreenUp Round Highbay

| Order Code   | Full Product Name                     | Ambient temperature | CE mark |
|--------------|---------------------------------------|---------------------|---------|
|              |                                       | range               |         |
| 911401647907 | BY518P LED260/CW PSU WB GM            | -20 to +45 °C       | Yes     |
| 911401650607 | BY518P G2 LED260/CW PSU 220-240 WB LA | -20 to +45 °C       | Yes     |

| Order Code   | Full Product Name                     | Ambient temperature | CE mark |
|--------------|---------------------------------------|---------------------|---------|
|              |                                       | range               |         |
| 911401650707 | BY518P G2 LED260/CW PSU 220-240 NB LA | -20 to +45 °C       | Yes     |
| 911401645108 | BY518P LED210/NW PSU WB CAU CL        | -20 to +45 °C       | No      |

Initial Performance (IEC Compliant)

| Order Code   | Full Product Name                     | Initial chromaticity  |
|--------------|---------------------------------------|-----------------------|
| 911401588745 |                                       | (0.38, 0.375) SDCM<5  |
| 911401588845 |                                       | (0.313, 0.329) SDCM<5 |
| 911401588945 |                                       | (0.38, 0.375) SDCM<5  |
| 911401589045 |                                       | (0.313, 0.329) SDCM<5 |
| 911401646407 | BY518P LED210/NW PSU WB GC            | (0.385, 0.380) SDCM<5 |
| 911401646507 | BY518P LED210/CW PSU WB GC            | (0.316, 0.332) SDCM<5 |
| 911401647007 | BY518P LED210/NW PSU NB GC            | (0.385, 0.380) SDCM<5 |
| 911401647107 | BY518P LED210/CW PSU NB GC            | (0.316, 0.332) SDCM<5 |
| 911401647607 | BY518P LED210/NW PSU WB GM            | (0.385, 0.380) SDCM<5 |
| 911401647707 | BY518P LED210/CW PSU WB GM            | (0.316, 0.332) SDCM<5 |
| 911401648307 | BY518P LED210/CW PSU NB GM            | (0.316, 0.332) SDCM<5 |
| 911401650407 | BY518P G2 LED210/CW PSU 220-240 WB LA | (0.316, 0.332) SDCM<5 |
| 911401650507 | BY518P G2 LED210/CW PSU 220-240 NB LA | (0.316, 0.332) SDCM<5 |
| 911401645208 | BY518P LED260/NW PSU WB CAU CL        | SDCM<5                |
| 911401676808 | BY518P SE LED105/NW PSU WB GC         | (0.38, 0.375) SDCM<5  |
| 911401676908 | BY518P SE LED105/CW PSU WB GC         | (0.313, 0.329) SDCM<5 |
| 911401677008 | BY518P SE LED140/NW PSU WB GC         | (0.38, 0.375) SDCM<5  |
| 911401677108 | BY518P SE LED140/CW PSU WB GC         | (0.313, 0.329) SDCM<5 |
| 911401677208 | BY518P SE LED200/NW PSU WB GC         | (0.38, 0.375) SDCM<5  |
| 911401677308 | BY518P SE LED200/CW PSU WB GC         | (0.313, 0.329) SDCM<5 |
| 911401677408 | BY518P SE LED245/NW PSU WB GC         | (0.38, 0.375) SDCM<5  |
| 911401677508 | BY518P SE LED245/CW PSU WB GC         | (0.313, 0.329) SDCM<5 |
| 911401677608 | BY518P SE LED290/NW PSU WB GC         | (0.38, 0.375) SDCM<5  |
| 911401677708 | BY518P SE LED290/CW PSU WB GC         | (0.313, 0.329) SDCM<5 |
| 911401677808 | BY518P SE LED105/NW PSU WB GM         | (0.38, 0.375) SDCM<5  |
| 911401677908 | BY518P SE LED105/CW PSU WB GM         | (0.313, 0.329) SDCM<5 |
| 911401678008 | BY518P SE LED140/NW PSU WB GM         | (0.38, 0.375) SDCM<5  |
| 911401678108 | BY518P SE LED140/CW PSU WB GM         | (0.313, 0.329) SDCM<5 |
| 911401678208 | BY518P SE LED200/NW PSU WB GM         | (0.38, 0.375) SDCM<5  |
| 911401678308 | BY518P SE LED200/CW PSU WB GM         | (0.313, 0.329) SDCM<5 |
| 911401678408 | BY518P SE LED245/NW PSU WB GM         | (0.38, 0.375) SDCM<5  |
| 911401678508 | BY518P SE LED245/CW PSU WB GM         | (0.313, 0.329) SDCM<5 |

| Order Code   | Full Product Name                     | Initial chromaticity  |
|--------------|---------------------------------------|-----------------------|
| 911401678608 | BY518P SE LED290/NW PSU WB GM         | (0.38, 0.375) SDCM<5  |
| 911401678708 | BY518P SE LED290/CW PSU WB GM         | (0.313, 0.329) SDCM<5 |
| 911401647507 | BY518P LED300/CW PSU NB GC            | (0.316, 0.332) SDCM<5 |
| 911401648107 | BY518P LED300/CW PSU WB GM            | (0.316, 0.332) SDCM<5 |
| 911401648707 | BY518P LED300/CW PSU NB GM            | (0.316, 0.332) SDCM<5 |
| 911401650807 | BY518P G2 LED300/CW PSU 220-240 WB LA | (0.316, 0.332) SDCM<5 |
| 911401650907 | BY518P G2 LED300/CW PSU 220-240 NB LA | (0.316, 0.332) SDCM<5 |
| 911401645308 | BY518P LED300/NW PSU WB CAU CL        | SDCM<5                |
| 911401671207 | BY518P LED110/NW PSU WB GC            | (0.385, 0.380) SDCM<5 |
| 911401671307 | BY518P LED110/CW PSU WB GC            | (0.316, 0.332) SDCM<5 |
| 911401671407 | BY518P LED160/NW PSU WB GC            | (0.385, 0.380) SDCM<5 |
| 911401671507 | BY518P LED160/CW PSU WB GC            | (0.316, 0.332) SDCM<5 |
| 911401671607 | BY518P LED110/NW PSU NB GC            | (0.385, 0.380) SDCM<5 |
| 911401671707 | BY518P LED110/CW PSU NB GC            | (0.316, 0.332) SDCM<5 |
| 911401671807 | BY518P LED160/NW PSU NB GC            | (0.385, 0.380) SDCM<5 |
| 911401672007 | BY518P LED110/NW PSU WB GM            | (0.385, 0.380) SDCM<5 |
| 911401672107 | BY518P LED110/CW PSU WB GM            | (0.316, 0.332) SDCM<5 |
| 911401672207 | BY518P LED160/NW PSU WB GM            | (0.385, 0.380) SDCM<5 |
| 911401672307 | BY518P LED160/CW PSU WB GM            | (0.316, 0.332) SDCM<5 |
| 911401672507 | BY518P LED110/CW PSU NB GM            | (0.316, 0.332) SDCM<5 |
| 911401672707 | BY518P LED160/CW PSU NB GM            | (0.316, 0.332) SDCM<5 |
| 911401674407 | BY518P G2 LED110/CW PSU 220-240 WB LA | (0.316, 0.332) SDCM<5 |
| 911401674607 | BY518P G2 LED160/CW PSU 220-240 WB LA | (0.316, 0.332) SDCM<5 |
| 911401646607 | BY518P LED260/NW PSU WB GC            | (0.385, 0.380) SDCM<5 |
| 911401646707 | BY518P LED260/CW PSU WB GC            | (0.316, 0.332) SDCM<5 |
| 911401647207 | BY518P LED260/NW PSU NB GC            | (0.385, 0.380) SDCM<5 |
| 911401647807 | BY518P LED260/NW PSU WB GM            | (0.385, 0.380) SDCM<5 |
| 911401647907 | BY518P LED260/CW PSU WB GM            | (0.316, 0.332) SDCM<5 |
| 911401650607 | BY518P G2 LED260/CW PSU 220-240 WB LA | (0.316, 0.332) SDCM<5 |
| 911401650707 | BY518P G2 LED260/CW PSU 220-240 NB LA | (0.316, 0.332) SDCM<5 |
| 911401645108 | BY518P LED210/NW PSU WB CAU CL        | SDCM<5                |

