



Energy Saver Compact Fluorescents – Going green never looked so good

Energy Saver GU24

Looking for an energy saver that doesn't look like one? The Philips Energy Saver family provides energy-efficient lighting options that don't just deliver similar light as your standard incandescent light bulb, they also have the same classic shape. Try Philips Energy Savers and see how they truly offer advanced lighting to meet your needs.

Benefits

- Energy savings and reduced operating costs without sacrificing quality of light compared to standard incandescent equivalents
- Twist-and-lock connection with two pins for energy-efficient replacement
- Saves up to \$77 over the life of the lamp when you replace a 100W A19 incandescent lamp with a 23W Energy Saver Twister GU24+
- +Based on wattage saved (77W) x replacement lamp's rated average life (10,000 hrs) divided by 1000 x kWh rate (.10) = \$77 saved

Features

- Self-ballasted
- Instant-on
- Compact size fits most GU24 fixtures
- Meets California's Energy Efficiency Standards for Residential and Nonresidential Buildings (24 CCR 6)
- Long life – lasts 9 years*
- Available in 13, 18, and 23W versions
- * Based on an average daily usage of 3–4 hours/day, 7 days/week

Energy Saver GU24

Application


- Ideal for table/floor lamps, wall sconces, surface mounts, reading lamps, recessed fixtures, open hanging fixtures, ceiling fans

Versions

23 W (100 W) GU24 base Soft
White Spiral - RFT



Dimensional drawing



Product	D (max)	C (max)	F (max)
23 W (100 W) GU24 base Soft White Spiral	61.5 mm	110.0 mm	50.5 mm

