



The affordable LEDcandle solution

CorePro LEDcandle

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

优点

- Warm white light
- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Broad compatibility with transformers

特点

- Easy retrofit
- Lifetime of 15,000 hours
- UV- and IR-free light
- Free of mercury and hazardous materials

应用

- Hotels, restaurants, bars, cafés, museums, shops
- Lobbies, reception areas , exhibitions


CorePro LEDcandle

Versions



LEDcandle B35NDFR RCA

二维绘图



Product	D	C
CorePro candle ND 5-40W E14 827 B35 FR	45 mm	87 mm
CorePro candle ND 5-40W E14 840 B35 FR	38 mm	114 mm

CorePro LEDcandle

一般信息	
底盖	E14
切换循环	50,000
标称使用寿命	15,000 小时
灯技术	
显色指数 (CRI)	80
标称使用寿命结束时灯的光通维持率 (标称)	70 %
光通量	470 lm
操作和电气	
输入频率	50 至 60 Hz
线频率	50 to 60 Hz
功耗	5 W
启动时间 (标称)	0.5 s
瓦数相当	40 W
温度	
最大外壳温度 (标称)	81 °C
控制和调光	
可调光	否
机械和外壳	
灯泡外观	磨砂
灯泡外形	B35
审批和申请	
能耗 kWh/1000 h	5 kWh

灯技术

Order Code	Full Product Name	相关色温 (标称)	颜色代码
929002968402	CorePro candle ND 5-40W E14 827 B35 FR	2700 K	827
929002968802	CorePro candle ND 5-40W E14 840 B35 FR	4000 K	840

