



LEDspot-løsning til en overkommelig pris

CorePro LED-spot 12V MR16

CorePro LEDspots passer perfekt til spotbelysning og giver varmt lys tilsvarende halogen. De er kompatible med de fleste eksisterende armaturer med MR16 GU5.3-fatninger og er designede som erstatning for halogen eller glødepærespots. CorePro LED-spots giver store energibesparelser og minimerer vedligeholdelsesomkostningerne.

Fordele

- Op til 80 % energibesparelse sammenlignet med halogenlamper
- Lavere vedligeholdelsesomkostninger
- Bred kompatibilitet med transformere

Funktioner

- Nem eftermontering
- Levetid på 15.000 timer
- Udsender ikke UV- og IR-lys
- Indeholder ikke kviksølv og farlige materialer

Anvendelsesområder

- Hoteller, restauranter, barer, caféer, muséer, butikker
- Lobbyer, korridorer, trappeopgange, badeværelser, receptionsområder, udstillinger, montrér

CorePro LED-spot 12V MR16

Versions



MASTER LEDspot LV 35W GU5-3
827 36D VLE





LEDspots Corepro SLR 2 MR16
GU5,3



LEDspot GU4 Classic MR11

Målskitse



Product	D	C
CorePro LED spot ND 2.9-20W MR16 827 36D	50,5 mm	45,5 mm
CorePro LED spot ND 4.4-35W MR16 827 36D	50,5 mm	45,5 mm
CorePro LED spot ND 4.4-35W MR16 840 36D	50,5 mm	45,5 mm
CorePro LED spot ND 7-50W MR16 827 36D	50,5 mm	45 mm
CorePro LED spot ND 7-50W MR16 840 36D	50,5 mm	45 mm
CorePro LEDspot 4.4-35W MR16 827 36D 5CT	50,5 mm	45,5 mm

Product	D	C
CorePro LED spot 2.3-20W 827 MR11 36D	35,5 mm	39,5 mm

CorePro LED-spot 12V MR16

Generelle oplysninger	
Skiftecyklus	50.000
Lysteknisk	
Spredningsvinkel (nom.)	36 °
Farvegengivelsesindeks (CRI)	80
LLMF ved den nominelle levetids udløb (nom.)	70 %
Drift og el	
Indgangsfrekvens	- Hz
Linjefrekvens	- Hz
Opstartstid (nom.)	0,5 s
Lysstyringssystemer og dæmpning	
Dæmpbar	Nej

Generelle oplysninger

Order Code	Full Product Name	Fod	Normeret levetid
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	GU5.3	15.000 t
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	GU5.3	15.000 t
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	GU5.3	15.000 t
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	GU5.3	15.000 t
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	GU5.3	15.000 t
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	GU5.3	15.000 t
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	GU4	25.000 t

Lysteknisk

Order Code	Full Product Name	Korreleret		Lysstyrke	
		farvetemperatur (nom.)	Farvekode	Lysstrøm	(nom.)
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	2700 K	827	345 lm	650 cd
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	2700 K	827	345 lm	650 cd
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	4000 K	840	390 lm	750 cd
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	2700 K	827	621 lm	1.400 cd

Order Code	Full Product Name	Korreleret		Lysstyrke	
		farvetemperatur (nom.)	Farvekode	Lysstrøm	(nom.)
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	4000 K	840	660 lm	1.500 cd
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	2700 K	827	230 lm	560 cd
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	2700 K	827	184 lm	400 cd

Drift og el

Order Code	Full Product Name	Strømforbrug	Wattforbrugsækvivalent
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	4,4 W	35 W
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	4,4 W	35 W
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	4,4 W	35 W
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	7 W	50 W

Order Code	Full Product Name	Strømforbrug	Wattforbrugsækvivalent
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	7 W	50 W
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	2,9 W	20 W
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	2,3 W	20 W

Temperatur

CorePro LED-spot 12V MR16

Order Code	Full Product Name	T-kappe, maks. (nom.)
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	85 °C
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	85 °C
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	85 °C
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	85 °C

Order Code	Full Product Name	T-kappe, maks. (nom.)
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	85 °C
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	75 °C
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	60 °C



Mekanik og armaturhus

Order Code	Full Product Name	Pære finish	Lyskildeform
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	-	MR16
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	-	MR16
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	-	MR16


Order Code	Full Product Name	Pære finish	Lyskildeform
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	-	MR16
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	-	MR16
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	-	MR16
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	Klar	MR11

Godkendelse og anvendelsesområde


Order Code	Full Product Name	Energiforbrug kWh/1000 t.
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	5 kWh
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	5 kWh
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	5 kWh
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	7 kWh
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	7 kWh
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	3 kWh
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	3 kWh




CorePro LED-spot 12V MR16




Accent Diagrams




Accent Diagram - CorePro LED spot ND 2.9-20W MR16 827 36D




Accent Diagram - CorePro LED spot ND 7-50W MR16 840 36D




Accent Diagram - CorePro LED spot ND 7-50W MR16 827 36D



Accent Diagram - CorePro LED spot 2.3-20W 827 MR11 36D




Accent Diagram - CorePro LED spot ND 4.4-35W MR16 840 36D




Accent Diagram - CorePro LEDspot 4.4-35W MR16 827 36D 5CT

CorePro LED-spot 12V MR16


Beam Diagrams




Beam diagram - CorePro LED spot 2.3-20W 827 MR11 36D




Beam diagram - CorePro LED spot ND 7-50W MR16 827 36D




Beam diagram - CorePro LED spot ND 7-50W MR16 840 36D



Beam diagram - CorePro LED spot ND 4.4-35W MR16 840 36D



Beam diagram - CorePro LEDspot 4.4-35W MR16 827 36D 5CT



Beam diagram - CorePro LED spot ND 2.9-20W MR16 827 36D

