



Edullinen LED-kohdelamppu

CorePro LEDspot LV

CorePro LEDspot -lamput sopivat täydellisesti kohdevalaistukseen, ja niiden valo muistuttaa lämmintä halogeenilampun valoa. Ne sopivat olemassa oleviin valaisimiin, joissa on MR16- tai GU5.3-kanta, eli ne on suunniteltu jälkiasennettaviksi halogeeni- tai hehkulamppujen tilalle. CorePro LED -kohdelamput säästävät erittäin paljon energiaa ja minimoivat ylläpitokulut.

Hyödyt

- Jopa 80 prosentin energiansäästö halogeenilamppuihin verrattuna
- Alhaisemmat ylläpitokustannukset
- Sopii yhteen useampien muuntajien kanssa

Ominaisuudet

- Korvaa helposti perinteiset valonlähteet
- Käyttöikä 15 000 tuntia
- Ei UV- eikä infrapunasäteilyä
- Ei sisällä elohopeaa tai muita haitallisia materiaaleja

Käyttökohteet

- Hotellit, ravintolat, kahvilat, museot, myymälät
- Aulat, käytävät, portaikot, WC-tilat, vastaanottoalueet, näyttelyt, vitriinit

CorePro LEDspot LV

Versions





LEDspots Corepro SLR 2 MR16 GU5,3



LEDspot GU4 Classic MR11

Mittapiirros



Product	D	C
CorePro LED spot ND 2.9-20W MR16 827 36D	50,5 mm	45,5 mm
CorePro LED spot ND 4.4-35W MR16 827 36D	50,5 mm	45,5 mm
CorePro LED spot ND 4.4-35W MR16 840 36D	50,5 mm	45,5 mm
CorePro LED spot ND 7-50W MR16 827 36D	50,5 mm	45 mm
CorePro LED spot ND 7-50W MR16 840 36D	50,5 mm	45 mm
CorePro LEDspot 4.4-35W MR16 827 36D 5CT	50,5 mm	45,5 mm

Product	D	C
CorePro LED spot 2.3-20W 827 MR11 36D	35,5 mm	39,5 mm

CorePro LEDspot LV

Yleistä tietoa	
Sytytys	50 000
Valaistuksen tekniset tiedot	
Keilakulma (nim.)	36 °
Värintoistoindeksi (CRI)	80
LLMF nimelliskäyttöiän lopussa (nim.)	70 %
Käyttö- ja sähkö tiedot	
Syöttötaajuus	- Hz
Viivatiheys	- Hz
Syttymisaika (nim.)	0,5 s
Ohjausjärjestelmät ja himmennys	
Himmennettävä	Ei

Order Code	Full Product Name	Kanta	Nimelliskäyttöikä
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	GU5.3	15 000 tuntia
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	GU5.3	15 000 tuntia
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	GU5.3	15 000 tuntia
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	GU5.3	15 000 tuntia
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	GU5.3	15 000 tuntia
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	GU5.3	15 000 tuntia
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	GU4	25 000 tuntia

Valaistuksen tekniset tiedot

Order Code	Full Product Name	Väriämpötila (nim.)	Värikoodi	Valovirta (nim.)	Valovoima
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	2700 K	827	345 lm	650 cd
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	2700 K	827	345 lm	650 cd
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	4000 K	840	390 lm	750 cd
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	2700 K	827	621 lm	1 400 cd

Order Code	Full Product Name	Väriämpötila (nim.)	Värikoodi	Valovirta (nim.)	Valovoima
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	4000 K	840	660 lm	1 500 cd
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	2700 K	827	230 lm	560 cd
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	2700 K	827	184 lm	400 cd

Käyttö- ja sähkö tiedot

Order Code	Full Product Name	Virrankulutus	Vastaa teholtaan
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	4,4 W	35 W
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	4,4 W	35 W
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	4,4 W	35 W
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	7 W	50 W

Order Code	Full Product Name	Virrankulutus	Vastaa teholtaan
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	7 W	50 W
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	2,9 W	20 W
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	2,3 W	20 W

Käyttölämpötila

Order Code	Full Product Name	T-Case, maksimi (nim.)
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	85 °C

Order Code	Full Product Name	T-Case, maksimi (nim.)
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	85 °C

CorePro LEDspot LV


Order Code	Full Product Name	T-Case, maksimi (nim.)
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	85 °C
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	85 °C
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	85 °C

Mekaaniset tiedot ja runko

Order Code	Full Product Name	Lampun pinta	Hehkulampun muoto
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	-	MR16
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	-	MR16
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	-	MR16
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	-	MR16




Merkinnät ja luokitukset

Order Code	Full Product Name	Energiankulutus kWh/1000 h
929002494602	CorePro LED spot ND 4.4-35W MR16 827 36D	5 kWh
929002494652	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	5 kWh
929002494702	CorePro LED spot ND 4.4-35W MR16 840 36D	5 kWh
929001904802	CorePro LED spot ND 7-50W MR16 827 36D	7 kWh
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	7 kWh
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	3 kWh
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	3 kWh





Order Code	Full Product Name	T-Case, maksimi (nim.)
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	75 °C
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	60 °C


Order Code	Full Product Name	Lampun pinta	Hehkulampun muoto
929001905002	CorePro LED spot ND 7-50W MR16 840 36D	-	MR16
929002494502	CorePro LED spot ND 2.9-20W MR16 827 36D	-	MR16
929002066402	CorePro LED spot 2.3-20W 827 MR11 36D	Kirkas	MR11




CorePro LEDspot LV




Accent Diagrams




Accent Diagram - CorePro LED spot ND
2.9-20W MR16 827 36D




Accent Diagram - CorePro LED spot ND 7-50W
MR16 840 36D




Accent Diagram - CorePro LED spot ND 7-50W
MR16 827 36D



Accent Diagram - CorePro LED spot 2.3-20W
827 MR11 36D




Accent Diagram - CorePro LED spot ND
4.4-35W MR16 840 36D




Accent Diagram - CorePro LEDspot 4.4-35W
MR16 827 36D 5CT


Beam Diagrams




Beam diagram - CorePro LED spot 2.3-20W 827 MR11 36D




Beam diagram - CorePro LED spot ND 7-50W MR16 827 36D




Beam diagram - CorePro LED spot ND 7-50W MR16 840 36D



Beam diagram - CorePro LED spot ND 4.4-35W MR16 840 36D



Beam diagram - CorePro LEDspot 4.4-35W MR16 827 36D 5CT



Beam diagram - CorePro LED spot ND 2.9-20W MR16 827 36D

