



Ekonomik LEDspot çözümü

CorePro LEDspot LV

Versions



CorePro LEDspot LV 35W GU5-3
827 36D ND




MASTER LEDspot LV 35W GU5-3
827 36D VLE



LEDspots Corepro SLR 2 MR16
GU5,3

Boyutlu çizim



Product	D	C
CorePro LED spot ND 2.9-20W MR16 827 36D	50,5 mm	45,5 mm
CorePro LED spot ND 4.4-35W MR16 840 36D	50,5 mm	45,5 mm
CorePro LED spot ND 7-50W MR16 827 36D	50,5 mm	45 mm
CorePro LED spot ND 7-50W MR16 830 36D	50,5 mm	45 mm
CorePro LEDspot 4.4-35W MR16 827 36D 5CT	50,5 mm	45,5 mm

CorePro LEDspot LV

Genel Bilgiler

Kapak Tabanı	GU5.3
Anahtar Döngüsü	50.000
Nominal kullanım ömrü	15.000 h

Işık Teknik Ayrıntıları

Işın Açısı (Nom)	36 °
Renk oluşturma dizini (CRI)	80
Nominal Kullanım Ömrü Sonundaki LLMF (Nom)	70 %

Çalıştırma ve Elektrik

Giriş Frekansı	- Hz
Hat Frekansı	- Hz
Başlangıç Saati (Nom)	0,5 s

Kontroller ve Dim Etme

Dim Edilebilir	Hayır
----------------	-------

Mekanik ve Muhafaza

Lamba Biçimi	MR16
--------------	------

Işık Teknik Ayrıntıları

Order Code	Full Product Name	İlişkili Renk Sıcaklığı (Nom.)	Renk Kodu	Işık Akısı (Nom)	Işık Yoğunluğu
30758200	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	2700 K	827	345 lm	650 cd
30708700	CorePro LED spot ND 4.4-35W MR16 840 36D	4000 K	840	390 lm	750 cd
81471000	CorePro LED spot ND 7-50W MR16 827 36D	2700 K	827	621 lm	1.400 cd
81477200	CorePro LED spot ND 7-50W MR16 830 36D	3000 K	830	621 lm	1.400 cd
30704900	CorePro LED spot ND 2.9-20W MR16 827 36D	2700 K	827	230 lm	560 cd

Çalıştırma ve Elektrik

Order Code	Full Product Name	Güç Tüketimi	Güç Eşleniği
30758200	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	4,4 W	35 W
30708700	CorePro LED spot ND 4.4-35W MR16 840 36D	4,4 W	35 W
81471000	CorePro LED spot ND 7-50W MR16 827 36D	7 W	50 W

Order Code	Full Product Name	Güç Tüketimi	Güç Eşleniği
81477200	CorePro LED spot ND 7-50W MR16 830 36D	7 W	50 W
30704900	CorePro LED spot ND 2.9-20W MR16 827 36D	2,9 W	20 W


Sıcaklık

Order Code	Full Product Name	Muhafaza Maksimumu (Nom.)
30758200	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	85 °C
30708700	CorePro LED spot ND 4.4-35W MR16 840 36D	85 °C
81471000	CorePro LED spot ND 7-50W MR16 827 36D	85 °C



Order Code	Full Product Name	Muhafaza Maksimumu (Nom.)
81477200	CorePro LED spot ND 7-50W MR16 830 36D	85 °C
30704900	CorePro LED spot ND 2.9-20W MR16 827 36D	75 °C

Onay ve Uygulama


Order Code	Full Product Name	Enerji Tüketimi kWh/1000 sa.
30758200	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	5 kWh
30708700	CorePro LED spot ND 4.4-35W MR16 840 36D	5 kWh
81471000	CorePro LED spot ND 7-50W MR16 827 36D	7 kWh
81477200	CorePro LED spot ND 7-50W MR16 830 36D	7 kWh
30704900	CorePro LED spot ND 2.9-20W MR16 827 36D	3 kWh




CorePro LEDspot LV




Accent Diagrams




Accent Diagram - CorePro LED spot ND
2.9-20W MR16 827 36D



Accent Diagram - CorePro LED spot ND 7-50W
MR16 827 36D




Accent Diagram - CorePro LED spot ND
4.4-35W MR16 840 36D




Accent Diagram - CorePro LEDspot 4.4-35W
MR16 827 36D 5CT


Beam Diagrams




Beam diagram - CorePro LED spot ND 7-50W
MR16 827 36D



Beam diagram - CorePro LED spot ND 4.4-35W
MR16 840 36D



Beam diagram - CorePro LEDspot 4.4-35W
MR16 827 36D 5CT



Beam diagram - CorePro LED spot ND 2.9-20W
MR16 827 36D

