



价格实惠的 LEDspot 解决方案

CorePro LEDspot LV

CorePro LEDspot 非常适合用于聚光照明，可以提供如同卤素灯般的暖光。本产品兼容大多数带 MR16 GU5.3 支座的现有灯具，经过设计改造，可替代卤素灯或白炽射灯。CorePro LEDspot 不仅节能效果出众，而且还最大限度地降低了维护成本。

优点

- 与卤素灯相比，节能达 80%
- 降低维护成本
- 广泛兼容各类变压器

特点

- 轻松改造
- 使用寿命长达 15,000 小时
- 无 UV 和 IR 的光
- 无汞和有害材料

应用

- 酒店、餐厅、酒吧、咖啡馆、博物馆、商店
- 大厅、走廊、楼梯间、盥洗室、接待区、展示会、陈列柜

CorePro LEDspot LV

Versions




LEDspot Essential 50W GU5.3
MR16 827 24D ND



LEDspots GMGC 2 MR16 GU5,3

二维绘图



Product	D	C
CorePro LED 3-35W 2700K MR16 24D CN	50 mm	46 mm
CorePro LED 3-35W 6500K MR16 24D CN	50 mm	46 mm
CorePro LED 5-50W 2700K MR16 24D CN	50 mm	46 mm
CorePro LED 5-50W 6500K MR16 24D CN	50 mm	46 mm



一般信息	
底座	GU5.3
额定使用寿命 (小时)	15,000 小时
切换循环	50,000
标称使用寿命	15,000 小时
灯技术	
光束角度 (标称)	24 °
显色指数 (CRI)	80
标称使用寿命结束时灯的光通维持率 (标称)	70 %
操作和电气	
输入频率	- Hz
线频率	- Hz
启动时间 (标称)	0.5 s
温度	
最大外壳温度 (标称)	76 °C
控制和调光	
可调光	否
机械和外壳	
灯泡外形	MR16

灯技术


Order Code	Full Product Name	相关色温 (标称)	颜色代码	光通量	发光强度 (标称)
929001240110	CorePro LED 5-50W 2700K MR16 24D CN	2700 K	827	400 lm	1,700 cd
929001240210	CorePro LED 5-50W 6500K MR16 24D CN	6500 K	865	435 lm	1,700 cd
929001239710	CorePro LED 3-35W 2700K MR16 24D CN	2700 K	827	260 lm	1,000 cd
929001239810	CorePro LED 3-35W 6500K MR16 24D CN	6500 K	865	290 lm	1,000 cd

操作和电气


Order Code	Full Product Name	功耗	瓦数相当
929001240110	CorePro LED 5-50W 2700K MR16 24D CN	5 W	50 W
929001240210	CorePro LED 5-50W 6500K MR16 24D CN	5 W	50 W
929001239710	CorePro LED 3-35W 2700K MR16 24D CN	3 W	35 W
929001239810	CorePro LED 3-35W 6500K MR16 24D CN	3 W	35 W




Accent Diagrams



Accent Diagram - CorePro LED 5-50W 6500K MR16 24D CN




Accent Diagram - CorePro LED 5-50W 2700K MR16 24D CN




Accent Diagram - CorePro LED 3-35W 6500K MR16 24D CN

Accent Diagrams




Accent Diagram - CorePro LED 3-35W 2700K
MR16 24D CN


Beam Diagrams




Beam diagram - CorePro LED 5-50W 2700K
MR16 24D CN



Beam diagram - CorePro LED 5-50W 6500K
MR16 24D CN



Beam diagram - CorePro LED 3-35W 6500K
MR16 24D CN



Beam diagram - CorePro LED 3-35W 2700K
MR16 24D CN

