



The affordable LEDspot solution

CorePro LEDspot MV

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Benefits

- Warm white light
- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Broad compatibility with transformers

Features

- Easy retrofit
- Lifetime of 15,000 hours
- Compatible with an extensive range of dimmers
- UV- and IR-free light
- Free of mercury and hazardous materials

Application

- Hotels, restaurants, bars, cafés, museums, shops
- Lobbies, corridors, stairwells, washrooms, reception areas , exhibitions, display cabinets



CorePro LEDspot MV

Versions



LEDspots switch EU PAR16 GU11

Dimensional drawing





Product	D	C
CorePro LEDspot 3-35W GU10 827 36D DIM	50 mm	54 mm
CorePro LEDspot 3-35W GU10 830 36D DIM	50 mm	54 mm
CorePro LEDspot 3-35W GU10 840 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 827 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 830 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 840 36D DIM	50 mm	54 mm
CorePro LEDspot 4.6-50W GU10 827 36D 5CT	50 mm	54 mm
Corepro LEDspot 2.7-25W GU10 827 36D	50 mm	53 mm
Corepro LEDspot 2.7-25W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 2.7-25W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 827 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 827 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 865 36D	50 mm	54 mm

Product	D	C
CorePro LEDspot 4.9-65W GU10 830 36D ND	50 mm	54 mm
CorePro LEDspot 4.9-65W GU10 840 36D ND	50 mm	54 mm
Corepro LEDspot 550lm GU10 830 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 840 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 865 120D	50 mm	54 mm

CorePro LEDspot MV

Dimensional drawing



Product	D	C
CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	50 mm	61.5 mm

Product	D	C
Corepro LEDspot 670lm GU10 830 60D	50 mm	54 mm
Corepro LEDspot 730lm GU10 840 60D	50 mm	54 mm

General Information	
Cap-Base	GU10
Switching Cycle	50,000
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Mechanical and Housing	
Bulb Shape	PAR16

General Information

Order Code	Full Product Name	Nominal lifetime
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	15,000 hour(s)
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	15,000 hour(s)
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	15,000 hour(s)
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	15,000 hour(s)
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	15,000 hour(s)
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	15,000 hour(s)
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	15,000 hour(s)
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	15,000 hour(s)

Order Code	Full Product Name	Nominal lifetime
30875600	Corepro LEDspot 550lm GU10 830 120D	15,000 hour(s)
30865700	Corepro LEDspot 550lm GU10 840 120D	15,000 hour(s)
30867100	Corepro LEDspot 550lm GU10 865 120D	15,000 hour(s)
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	15,000 hour(s)
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	15,000 hour(s)
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	15,000 hour(s)
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	15,000 hour(s)
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	15,000 hour(s)

CorePro LEDspot MV

Order Code	Full Product Name	Nominal lifetime
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	15,000 hour(s)
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	15,000 hour(s)
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	15,000 hour(s)
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	15,000 hour(s)
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	15,000 hour(s)

Order Code	Full Product Name	Nominal lifetime
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	15,000 hour(s)
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	15,000 hour(s)
81333101	Corepro LEDspot 670lm GU10 830 60D	25,000 hour(s)
81335501	Corepro LEDspot 730lm GU10 840 60D	25,000 hour(s)

Light Technical

		Correlated Color Temperature				
Order Code	Full Product Name	Beam Angle (Nom)	(Nom)	Color Code	Luminous Flux	Luminous Intensity (Nom)
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	36 degree(s)	4000 K	840	240 lm	500 cd
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	36 degree(s)	3000 K	830	230 lm	500 cd
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	36 degree(s)	2700 K	827	230 lm	500 cd
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	36 degree(s)	2700 K	827	345 lm	700 cd
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	36 degree(s)	2700 K	827	355 lm	700 cd
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	36 degree(s)	2700 K	827	355 lm	700 cd
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	36 degree(s)	2700 K	827	215 lm	470 cd
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	36 degree(s)	2700 K	827	255 lm	545 cd
30875600	Corepro LEDspot 550lm GU10 830 120D	120 degree(s)	3000 K	830	550 lm	-
30865700	Corepro LEDspot 550lm GU10 840 120D	120 degree(s)	4000 K	840	550 lm	-
30867100	Corepro LEDspot 550lm GU10 865 120D	120 degree(s)	6500 K	865	550 lm	-
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	36 degree(s)	4000 K	840	350 lm	700 cd
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	36 degree(s)	3000 K	830	345 lm	700 cd
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	36 degree(s)	3000 K	830	460 lm	800 cd
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	36 degree(s)	4000 K	840	485 lm	800 cd
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	36 degree(s)	3000 K	830	225 lm	490 cd
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	36 degree(s)	4000 K	840	230 lm	500 cd
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	36 degree(s)	3000 K	830	265 lm	565 cd
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	36 degree(s)	4000 K	840	275 lm	590 cd
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	36 degree(s)	3000 K	830	370 lm	740 cd
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	36 degree(s)	4000 K	840	390 lm	770 cd
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	36 degree(s)	6500 K	865	390 lm	770 cd
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	36 degree(s)	2700 K	2700/3000/4000	360 lm	550 cd
81333101	Corepro LEDspot 670lm GU10 830 60D	60 degree(s)	3000 K	830	670 lm	750 cd
81335501	Corepro LEDspot 730lm GU10 840 60D	60 degree(s)	4000 K	840	730 lm	750 cd

Operating and Electrical

Order Code	Full Product Name	Power		Wattage
		Line Frequency	Consumption	Equivalent
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	50 to 60 Hz	3 W	35 W
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	50 to 60 Hz	3 W	35 W
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	50 to 60 Hz	3 W	35 W

Order Code	Full Product Name	Power		Wattage
		Line Frequency	Consumption	Equivalent
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	50 to 60 Hz	4 W	50 W
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	50 to 60 Hz	4.6 W	50 W
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	50 to 60 Hz	4.6 W	50 W

CorePro LEDspot MV

Order Code	Full Product Name	Line Frequency	Power	Wattage
			Consumption	Equivalent
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	50 to 60 Hz	2.7 W	25 W
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	50 to 60 Hz	3.5 W	35 W
30875600	Corepro LEDspot 550lm GU10 830 120D	50 to 60 Hz	4.9 W	-
30865700	Corepro LEDspot 550lm GU10 840 120D	50 to 60 Hz	4.9 W	-
30867100	Corepro LEDspot 550lm GU10 865 120D	50 to 60 Hz	4.9 W	-
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	50 to 60 Hz	4 W	50 W
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	50 to 60 Hz	4 W	50 W
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	50 to 60 Hz	4.9 W	65 W
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	50 to 60 Hz	4.9 W	65 W
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	50 to 60 Hz	2.7 W	25 W

Order Code	Full Product Name	Line Frequency	Power	Wattage
			Consumption	Equivalent
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	50 to 60 Hz	2.7 W	25 W
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	50 to 60 Hz	3.5 W	35 W
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	50 to 60 Hz	3.5 W	35 W
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	50 to 60 Hz	4.6 W	50 W
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	50 to 60 Hz	4.6 W	50 W
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	50 to 60 Hz	4.6 W	50 W
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	-	4.8 W	50 W
81333101	Corepro LEDspot 670lm GU10 830 60D	50 to 60 Hz	6.7 W	90 W
81335501	Corepro LEDspot 730lm GU10 840 60D	50 to 60 Hz	6.7 W	100 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	65 °C
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	65 °C
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	65 °C
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	70 °C
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	72 °C
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	72 °C
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	50 °C
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	65 °C
30875600	Corepro LEDspot 550lm GU10 830 120D	85 °C
30865700	Corepro LEDspot 550lm GU10 840 120D	85 °C
30867100	Corepro LEDspot 550lm GU10 865 120D	85 °C
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	70 °C
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	70 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	85 °C
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	85 °C
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	50 °C
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	50 °C
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	65 °C
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	65 °C
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	72 °C
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	72 °C
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	72 °C
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	60 °C
81333101	Corepro LEDspot 670lm GU10 830 60D	75 °C
81335501	Corepro LEDspot 730lm GU10 840 60D	75 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	Only with specific dimmers
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	Only with specific dimmers

Order Code	Full Product Name	Dimmable
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	Only with specific dimmers
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	Only with specific dimmers

CorePro LEDspot MV

Order Code	Full Product Name	Dimmable
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	No
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	No
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	No
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	No
30875600	Corepro LEDspot 550lm GU10 830 120D	No
30865700	Corepro LEDspot 550lm GU10 840 120D	No
30867100	Corepro LEDspot 550lm GU10 865 120D	No
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	Only with specific dimmers
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	Only with specific dimmers
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	No
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	No

Order Code	Full Product Name	Dimmable
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	No
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	No
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	No
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	No
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	No
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	No
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	No
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	Only with specific dimmers
81333101	Corepro LEDspot 670lm GU10 830 60D	No
81335501	Corepro LEDspot 730lm GU10 840 60D	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	-
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	-
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	-
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	-
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	-
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	-
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	-
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	-
30875600	Corepro LEDspot 550lm GU10 830 120D	-
30865700	Corepro LEDspot 550lm GU10 840 120D	-
30867100	Corepro LEDspot 550lm GU10 865 120D	-
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	-
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	-

Order Code	Full Product Name	Bulb Finish
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	-
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	-
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	-
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	-
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	-
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	-
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	-
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	-
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	-
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	Clear
81333101	Corepro LEDspot 670lm GU10 830 60D	-
81335501	Corepro LEDspot 730lm GU10 840 60D	-


Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	-	3 kWh
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	-	3 kWh
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	-	3 kWh
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	-	4 kWh
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	-	5 kWh
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	-	5 kWh
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	-	3 kWh
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	-	4 kWh

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
30875600	Corepro LEDspot 550lm GU10 830 120D	-	5 kWh
30865700	Corepro LEDspot 550lm GU10 840 120D	-	5 kWh
30867100	Corepro LEDspot 550lm GU10 865 120D	-	5 kWh
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	-	4 kWh
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	-	4 kWh
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	-	5 kWh
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	-	5 kWh
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	-	3 kWh


CorePro LEDspot MV

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	-	3 kWh
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	-	4 kWh
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	-	4 kWh
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	-	5 kWh
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	-	5 kWh
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	-	5 kWh
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	-20 to +45 °C	5 kWh
81333101	Corepro LEDspot 670lm GU10 830 60D	-	7 kWh
81335501	Corepro LEDspot 730lm GU10 840 60D	-	7 kWh




90°


60°




(cd/1000lm) 0°
— 0-180° — 90-270°




(cd/1000lm) 0°
— 0-180° — 90-270°




(cd) 0°
— 0-180° — 90-270°




(cd) 0°
— 0-180° — 90-270°




(cd) 0°
— 0-180° — 90-270°




(cd) 0°
— 0-180° — 90-270°




(cd) 0°
— 0-180° — 90-270°



(cd) 0°
— 0-180° — 90-270°





(cd) 0°
— 0-180° — 90-270°




(cd) 0°
— 0-180° — 90-270°


CorePro LEDspot MV




Accent Diagrams



Accent Diagram - CorePro LEDspot 4.9-65W
GU10 830 36D ND




Accent Diagram - Corepro LEDspot 2.7-25W
GU10 827 36D




Accent Diagram - Corepro LEDspot 3.5-35W
GU10 827 36D


Accent Diagrams




Accent Diagram - CorePro LEDspot 4.6-50W
GU10 827 36D 5CT




Accent Diagram - Corepro LEDspot 2.7-25W
GU10 830 36D




Accent Diagram - Corepro LEDspot 3.5-35W
GU10 840 36D




Accent Diagram - Corepro LEDspot 4.6-50W
GU10 865 36D




Accent Diagram - CorePro LEDspot 4-50W
GU10 827 36D DIM




Accent Diagram - CorePro LEDspot 4-50W
GU10 840 36D DIM



Accent Diagram - CorePro LEDspot 4-50W
GU10 830 36D DIM




Accent Diagram - CorePro LEDspot 4.8-50W
GU10 3CCT 36DDIM




Accent Diagram - CorePro LEDspot 3-35W GU10
830 36D DIM

CorePro LEDspot MV


Accent Diagrams




Accent Diagram - CorePro LEDspot 3-35W GU10 840 36D DIM




Accent Diagram - Corepro LEDspot 730lm GU10 840 60D



Accent Diagram - Corepro LEDspot 670lm GU10 830 60D




Accent Diagram - CorePro LEDspot 3-35W GU10 827 36D DIM




Accent Diagram - CorePro LEDspot 4.9-65W GU10 840 36D ND


Beam Diagrams



Beam diagram - CorePro LEDspot 3-35W GU10 840 36D DIM




Beam diagram - CorePro LEDspot 4.9-65W GU10 840 36D ND




Beam diagram - Corepro LEDspot 2.7-25W GU10 827 36D


Beam Diagrams




Beam diagram - CorePro LEDspot 3.5-35W
GU10 827 36D




Beam diagram - CorePro LEDspot 4.6-50W
GU10 827 36D 5CT




Beam diagram - CorePro LEDspot 2.7-25W GU10
830 36D




Beam diagram - CorePro LEDspot 3.5-35W
GU10 840 36D




Beam diagram - CorePro LEDspot 4.6-50W
GU10 865 36D




Beam diagram - CorePro LEDspot 4-50W GU10
830 36D DIM



Beam diagram - CorePro LEDspot 4-50W GU10
840 36D DIM




Beam diagram - CorePro LEDspot 4.8-50W
GU10 3CCT 36DDIM




Beam diagram - CorePro LEDspot 730lm GU10
840 60D


Beam Diagrams




Beam diagram - CorePro LEDspot 3-35W GU10
830 36D DIM




Beam diagram - CorePro LEDspot 4-50W GU10
827 36D DIM



Beam diagram - CorePro LEDspot 3-35W GU10
827 36D DIM



Beam diagram - CorePro LEDspot 4.9-65W
GU10 830 36D ND



Beam diagram - Corepro LEDspot 670lm GU10
830 60D

