



The affordable way to install or replace T8 LEDtubes

CorePro LEDtube EM/Mains T8

Philips CorePro LEDtubes are the quick and easy way to replace T8 fluorescent or other LED tubes with a fast pay back time. Not only does the Core range of LEDtubes require a low initial investment, but LED energy efficiency also delivers instant savings that you can bank on over a long and reliable lifetime. Plus, with the same lamp size and light distribution as fluorescent alternatives, you'll never know the difference. There are two ways to install these LED tubes: Rewire your existing fluorescent-based luminaires so the CorePro LEDtubes work directly on the Mains. Or simply change the fluorescent starter to an LED starter that can be used with your Electromagnetic ballasts.

Benefits

- Optimized energy savings – about 50% more than fluorescent alternatives
- Easy Installation – retrofit or rewire
- Same look and feel as fluorescent lamps
- Minimize maintenance costs – Last twice as long as fluorescent tubes to reduce replacement costs

Features

- Choice of colors: 3000K, 4000K and 6500K
- The right fit – 600mm, 1200mm or 1500mm
- Longer lifetime – Lasts twice as long as fluorescent lamps
- Wide range of applications
- Enable implementation of HACCP, supported by product level NSF certificate

CorePro LEDtube EM/Mains T8

Application

- Offices
- Banks
- Education
- Food and Large Retailers
- Light Commercial


Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.
- Installation must be done according to the installation diagrams provided with the lamp or available online. Installation must be done by a certified professional.


Versions




LEDtube_COR_8ft_32W_FA8_CL



Product standard image



LEDtube 9W G13



LEDtube COR 21W G13




LEDtube_COR_LATAM1_32W_G13

LEDtube_COR_8ft_32W_FA8_FR

LEDtube 18W G13

CorePro LEDtube EM/Mains T8

Dimensional drawing




Product	D1	D2	A1	A2	A3
CorePro LEDTube 8ft 32W 3800lm 865 T8 BR	27.8 mm	27.8 mm	2,373.1 mm	2,380.2 mm	2,387.3 mm
CorePro LEDtube 1800mm 21W 840 T8	25.8 mm	28 mm	1,762.6 mm	1,769.7 mm	1,776.8 mm
CorePro LEDtube 1800mm 21W 865 T8	25.8 mm	28 mm	1,762.6 mm	1,769.7 mm	1,776.8 mm
CorePro LEDtube 1800mm 21W830 T8	25.8 mm	28 mm	1,762.6 mm	1,769.7 mm	1,776.8 mm

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 15.7W 840 T8 KSA	25.6 mm	27.8 mm	1,199.4 mm	1,205.3 mm	1,213.6 mm
CorePro LEDtube 1200mm 15.7W 865 T8 KSA	25.6 mm	27.8 mm	1,199.4 mm	1,205.3 mm	1,213.6 mm
CorePro LEDtube 1200mm 18W 830 T8C W G	25.6 mm	27.8 mm	1,199.4 mm	1,205.3 mm	1,213.6 mm
CorePro LEDtube 1200mm 18W 840 T8C W G	25.6 mm	27.8 mm	1,199.4 mm	1,205.3 mm	1,213.6 mm
CorePro LEDtube 1200mm 18W 865 T8C W G	25.6 mm	27.8 mm	1,199.4 mm	1,205.3 mm	1,213.6 mm
CorePro LEDtube 1200mm HO 18W840 C W G	25.6 mm	27.8 mm	1,199.4 mm	1,205.3 mm	1,213.6 mm
CorePro LEDtube 1200mm HO 18W865 C W G	25.6 mm	27.8 mm	1,199.4 mm	1,205.3 mm	1,213.6 mm
CorePro LEDtube 600mm 8.6W 840 T8 KSA	25.6 mm	27.8 mm	589.8 mm	595.7 mm	604 mm
CorePro LEDtube 600mm 8.6W 865 T8 KSA	25.6 mm	27.8 mm	589.8 mm	595.7 mm	604 mm
CorePro LEDtube 600mm 9W 830 T8C W G	25.6 mm	27.8 mm	589.8 mm	595.7 mm	604 mm
CorePro LEDtube 600mm 9W 840 T8 C W G	25.6 mm	27.8 mm	589.8 mm	595.7 mm	604 mm
CorePro LEDtube 600mm 9W 865 T8 C W G	25.6 mm	27.8 mm	589.8 mm	595.7 mm	604 mm

Product	D1	D2	A1	A2	A3
CorePro LEDTube 1200mm 16W 865 T8 FA8 WV	25.8 mm	28 mm	1,150 mm	1,156 mm	1,168 mm
CorePro LEDTube 36 8ft 32W 865 T8 CT WV	25.8 mm	28 mm	2,374.3 mm	2,380.2 mm	2,388.5 mm
CorePro LEDTube 36 8ft 32W 865 T8 WV	25.8 mm	28 mm	2,374.3 mm	2,380.2 mm	2,388.5 mm

CorePro LEDtube EM/Mains T8

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 15.5W 830 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 840 T8 AP I	28 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 840 T8 CL	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 865 T8 AP I	28 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 865 T8 CL	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 865 T8 PH	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 17.6W 840 T8 AU	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 17.6W 865 T8 AU	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 17W 840 T8 AU ICT	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 17W 840 T8 AU 2CT	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 17W 865 T8 AU ICT	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 17W 865 T8 AU 2CT	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 18W 5CCT T8 AU	25.7 mm	26.6 mm	1,199.4 mm	1,206.5 mm	1,213.6 mm
CorePro LEDtube 1200mm 18W 830 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 18W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 18W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 18W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 18W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 17.7W 830 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 17.7W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 17.7W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 21.5W 830 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

CorePro LEDtube EM/Mains T8

Dimensional drawing

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm UO 21.5W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm UO 21.5W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1500mm 20W 830 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 840 T8 CL	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 865 T8 CL	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 22W 840 T8 AU	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 22W 840 T8AU1CT	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 22W 840 T8AU2CT	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 22W 865 T8 AU	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 22W 865 T8AU1CT	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 22W 865 T8AU2CT	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 24W 5CCT T8 AU	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm HO 24W 830 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm HO 24W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm HO 24W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm HO 24W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm HO 24W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm UO 25.9W 830 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm UO 25.9W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm UO 25.9W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm UO 31.5W 830 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm

CorePro LEDtube EM/Mains T8

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1500mm UO 31.5W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm UO 31.5W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 50k 1200mm 18W865T8 MY	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 600mm 8.8W 840 T8 AU 1CT	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8.8W 840 T8 AU 2CT	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8.8W 865 T8 AU 2CT	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 830 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 840 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 840 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 840 T8 AP I	28 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 840 T8 CL	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 840 VWV T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 865 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 865 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 865 T8 AP I	28 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 865 T8 CL	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 865 VWV T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 9.9W 840 T8 AU	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 9.9W 865 T8 AU	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 9W 5CCT T8 AU	25.7 mm	26.6 mm	589.8 mm	596.9 mm	604 mm
CorePro LEDtube 600mm HO 8W 830 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm HO 8W 840 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm HO 8W 840 T8 CN	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm HO 8W 865 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm HO 8W 865 T8 CN	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

CorePro LEDtube EM/Mains T8

Product	D1	D2	A1	A2	A3
CorePro LEDtube HO 1200mm 18W 865 T8 PH	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube HO 1200mm 18W840 VWV T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube HO 1200mm 18W865 VWV T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube HO 1200mm 18W865T8 AP	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube HO 1200mm 18W865T8 CN	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube HO 1200mm 18W865T8 ID	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Corepro LEDtube 50k 1200mm 18W840T8 MY	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Corepro LEDtube HO 1200mm 18W840T8 AP	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Corepro LEDtube HO 1200mm 18W840T8 CN	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No

General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime
929004265519	CorePro LEDtube 600mm 9W 5CCT T8 AU	G13	200,000	50,000 hour(s)
929004265619	CorePro LEDtube 1200mm 18W 5CCT T8 AU	G13	200,000	50,000 hour(s)
929004265719	CorePro LEDtube 1500mm 24W 5CCT T8 AU	G13	200,000	50,000 hour(s)
929003605012	CorePro LEDTube 36 8ft 32W 865 T8 CT WV	FA8	50,000	30,000 hour(s)
929004253112	CorePro LEDTube 1200mm 16W 865 T8 FA8 WV	FA8	50,000	30,000 hour(s)
929002000372	CorePro LEDtube 600mm 9W 830 T8C W G	G13	50,000	25,000 hour(s)
929002000472	CorePro LEDtube 600mm 9W 840 T8 C W G	G13	50,000	25,000 hour(s)
929002000572	CorePro LEDtube 600mm 9W 865 T8 C W G	G13	50,000	25,000 hour(s)

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime
929002998802	CorePro LEDtube 1800mm 21W 840 T8	G13	200,000	50,000 hour(s)
929003561802	CorePro LEDtube 1800mm 21W 865 T8	G13	200,000	50,000 hour(s)
929003584702	CorePro LEDtube 1800mm 21W830 T8	G13	200,000	50,000 hour(s)
929001874802	CorePro LEDtube 1200mm HO 18W 865 T8	G13	200,000	50,000 hour(s)
929001874832	CorePro LEDtube 1200mm HO 18W 865 T8	G13	200,000	50,000 hour(s)
929001874902	CorePro LEDtube 1200mm HO 18W 840 T8	G13	200,000	50,000 hour(s)
929001874932	CorePro LEDtube 1200mm HO 18W 840 T8	G13	200,000	50,000 hour(s)
929001875002	CorePro LEDtube 1500mm HO 24W 865 T8	G13	200,000	50,000 hour(s)

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime
929001875032	CorePro LEDtube 1500mm HO 24W 865 T8	G13	200,000	50,000 hour(s)
929001875102	CorePro LEDtube 1500mm HO 24W 840 T8	G13	200,000	50,000 hour(s)
929001875132	CorePro LEDtube 1500mm HO 24W 840 T8	G13	200,000	50,000 hour(s)
929003022102	CorePro LEDtube 600mm 8W 840 T8	G13	200,000	50,000 hour(s)
929003022202	CorePro LEDtube 600mm 8W 865 T8	G13	200,000	50,000 hour(s)
929003022502	CorePro LEDtube 1500mm 20W 840 T8	G13	200,000	50,000 hour(s)
929003022602	CorePro LEDtube 1500mm 20W 865 T8	G13	200,000	50,000 hour(s)
929003154202	CorePro LEDtube 1200mm UO 21.5W 840 T8	G13	200,000	50,000 hour(s)
929003154302	CorePro LEDtube 1200mm UO 21.5W 865 T8	G13	200,000	50,000 hour(s)
929003154402	CorePro LEDtube 1500mm UO 31.5W 840 T8	G13	200,000	50,000 hour(s)
929003154502	CorePro LEDtube 1500mm UO 31.5W 865 T8	G13	200,000	50,000 hour(s)
929003158602	CorePro LEDtube 600mm HO 8W 840 T8	G13	200,000	50,000 hour(s)
929003158610	CorePro LEDtube 600mm HO 8W 840 T8 CN	G13	200,000	50,000 hour(s)
929003158702	CorePro LEDtube 600mm HO 8W 865 T8	G13	200,000	50,000 hour(s)
929003158710	CorePro LEDtube 600mm HO 8W 865 T8 CN	G13	200,000	50,000 hour(s)
929003519702	CorePro LEDtube 1200mm 15.5W 840 T8	G13	200,000	50,000 hour(s)
929003519708	CorePro LEDtube 1200mm 15.5W 840 T8 AP I	G13	200,000	50,000 hour(s)
929003519720	CorePro LEDtube 1200mm 17W 840 T8 AU 1CT	G13	200,000	50,000 hour(s)
929003519721	CorePro LEDtube 1200mm 17W 840 T8 AU 2CT	G13	200,000	50,000 hour(s)
929003519762	CorePro LEDtube 1200mm 15.5W 840 T8 CL	G13	200,000	50,000 hour(s)
929003519802	CorePro LEDtube 1200mm 15.5W 865 T8	G13	200,000	50,000 hour(s)
929003519808	CorePro LEDtube 1200mm 15.5W 865 T8 AP I	G13	200,000	50,000 hour(s)
929003519820	CorePro LEDtube 1200mm 17W 865 T8 AU 1CT	G13	200,000	50,000 hour(s)
929003519821	CorePro LEDtube 1200mm 17W 865 T8 AU 2CT	G13	200,000	50,000 hour(s)
929003519832	CorePro LEDtube 1200mm 15.5W 865 T8	G13	200,000	50,000 hour(s)

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime
929003519862	CorePro LEDtube 1200mm 15.5W 865 T8 CL	G13	200,000	50,000 hour(s)
929003519888	CorePro LEDtube 1200mm 15.5W 865 T8 PH	G13	200,000	50,000 hour(s)
929003520119	CorePro LEDtube 600mm 9.9W 840 T8 AU	G13	200,000	30,000 hour(s)
929003520219	CorePro LEDtube 600mm 9.9W 865 T8 AU	G13	200,000	30,000 hour(s)
929003520319	CorePro LEDtube 1200mm 17.6W 840 T8 AU	G13	200,000	30,000 hour(s)
929003520419	CorePro LEDtube 1200mm 17.6W 865 T8 AU	G13	200,000	30,000 hour(s)
929003520519	CorePro LEDtube 1500mm 22W 840 T8 AU	G13	200,000	30,000 hour(s)
929003520619	CorePro LEDtube 1500mm 22W 865 T8 AU	G13	200,000	30,000 hour(s)
929003520708	Corepro LEDtube HO 1200mm 18W840T8 AP	G13	200,000	50,000 hour(s)
929003520710	Corepro LEDtube HO 1200mm 18W840T8 CN	G13	200,000	50,000 hour(s)
929003520738	Corepro LEDtube 50k 1200mm 18W840T8 MY	G13	200,000	50,000 hour(s)
929003520808	CorePro LEDtube HO 1200mm 18W865T8 AP	G13	200,000	50,000 hour(s)
929003520810	CorePro LEDtube HO 1200mm 18W865T8 CN	G13	200,000	50,000 hour(s)
929003520838	CorePro LEDtube 50k 1200mm 18W865T8 MY	G13	200,000	50,000 hour(s)
929003520888	CorePro LEDtube HO 1200mm 18W 865 T8 PH	G13	200,000	50,000 hour(s)
929003534411	CorePro LEDtube 600mm 8W 840 VWV T8	G13	200,000	30,000 hour(s)
929003534511	CorePro LEDtube 600mm 8W 865 VWV T8	G13	200,000	30,000 hour(s)
929003534811	CorePro LEDtube HO 1200mm 18W840 VWV T8	G13	200,000	30,000 hour(s)
929003534911	CorePro LEDtube HO 1200mm 18W865 VWV T8	G13	200,000	30,000 hour(s)
929003547202	CorePro LEDtube 600mm 8W 840 T8	G13	200,000	50,000 hour(s)
929003547208	CorePro LEDtube 600mm 8W 840 T8 AP I	G13	200,000	50,000 hour(s)
929003547220	CorePro LEDtube 600mm 8.8W 840 T8 AU 1CT	G13	200,000	50,000 hour(s)
929003547221	CorePro LEDtube 600mm 8.8W 840 T8 AU 2CT	G13	200,000	50,000 hour(s)
929003547262	CorePro LEDtube 600mm 8W 840 T8 CL	G13	200,000	50,000 hour(s)
929003547302	CorePro LEDtube 600mm 8W 865 T8	G13	200,000	50,000 hour(s)

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime
929003547308	CorePro LEDtube 600mm 8W 865 T8 AP I	G13	200,000	50,000 hour(s)
929003547320	CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT	G13	200,000	50,000 hour(s)
929003547321	CorePro LEDtube 600mm 8.8W 865 T8 AU 2CT	G13	200,000	50,000 hour(s)
929003547362	CorePro LEDtube 600mm 8W 865 T8 CL	G13	200,000	50,000 hour(s)
929003547402	CorePro LEDtube 1500mm 20W 840 T8	G13	200,000	50,000 hour(s)
929003547420	CorePro LEDtube 1500mm 22W 840 T8AU1CT	G13	200,000	50,000 hour(s)
929003547421	CorePro LEDtube 1500mm 22W 840 T8AU2CT	G13	200,000	50,000 hour(s)
929003547462	CorePro LEDtube 1500mm 20W 840 T8 CL	G13	200,000	50,000 hour(s)
929003547502	CorePro LEDtube 1500mm 20W 865 T8	G13	200,000	50,000 hour(s)
929003547520	CorePro LEDtube 1500mm 22W 865 T8AU1CT	G13	200,000	50,000 hour(s)
929003547521	CorePro LEDtube 1500mm 22W 865 T8AU2CT	G13	200,000	50,000 hour(s)
929003547562	CorePro LEDtube 1500mm 20W 865 T8 CL	G13	200,000	50,000 hour(s)
929003577132	CorePro LEDtube 600mm 8W 830 T8	G13	200,000	50,000 hour(s)
929003577232	CorePro LEDtube 1200mm 15.5W 830 T8	G13	200,000	50,000 hour(s)
929003577332	CorePro LEDtube 1500mm 20W 830 T8	G13	200,000	50,000 hour(s)
929003577402	CorePro LEDtube 600mm HO 8W 830 T8	G13	200,000	50,000 hour(s)
929003577532	CorePro LEDtube 1200mm HO 18W 830 T8	G13	200,000	50,000 hour(s)
929003577632	CorePro LEDtube 1500mm HO 24W 830 T8	G13	200,000	50,000 hour(s)
929003577702	CorePro LEDtube 1200mm UO 21.5W 830 T8	G13	200,000	50,000 hour(s)

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime
929003577802	CorePro LEDtube 1500mm UO 31.5W 830 T8	G13	200,000	50,000 hour(s)
929003746102	CorePro LEDtube 1200mm UO 17.7W 830 T8	G13	200,000	50,000 hour(s)
929003746202	CorePro LEDtube 1200mm UO 17.7W 840 T8	G13	200,000	50,000 hour(s)
929003746302	CorePro LEDtube 1200mm UO 17.7W 865 T8	G13	200,000	50,000 hour(s)
929003746402	CorePro LEDtube 1500mm UO 25.9W 830 T8	G13	200,000	50,000 hour(s)
929003746502	CorePro LEDtube 1500mm UO 25.9W 840 T8	G13	200,000	50,000 hour(s)
929003746602	CorePro LEDtube 1500mm UO 25.9W 865 T8	G13	200,000	50,000 hour(s)
929003771708	CorePro LEDtube HO 1200mm 18W865T8 ID	G13	200,000	50,000 hour(s)
929001999772	CorePro LEDtube 1200mm 18W 830 T8C W G	G13	50,000	25,000 hour(s)
929001999868	CorePro LEDtube 1200mm 15.7W 840 T8 KSA	G13	50,000	30,000 hour(s)
929001999872	CorePro LEDtube 1200mm 18W 840 T8C W G	G13	50,000	25,000 hour(s)
929001999968	CorePro LEDtube 1200mm 15.7W 865 T8 KSA	G13	50,000	30,000 hour(s)
929001999972	CorePro LEDtube 1200mm 18W 865 T8C W G	G13	50,000	25,000 hour(s)
929002000468	CorePro LEDtube 600mm 8.6W 840 T8 KSA	G13	50,000	30,000 hour(s)
929002000568	CorePro LEDtube 600mm 8.6W 865 T8 KSA	G13	50,000	30,000 hour(s)
929002474472	CorePro LEDTube 8ft 32W 3800lm 865 T8 BR	G13	50,000	25,000 hour(s)
929003604912	CorePro LEDTube 36 8ft 32W 865 T8 WV	FA8	50,000	30,000 hour(s)
929002000072	CorePro LEDtube 1200mm HO 18W840 C W G	G13	50,000	25,000 hour(s)
929002000172	CorePro LEDtube 1200mm HO 18W865 C W G	G13	50,000	25,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929004265519	CorePro LEDtube 600mm 9W 5CCT T8 AU	190 degree(s)	2700 K	83	2700K/3000K/4000K/5000K/6500K	1,000 lm
929004265619	CorePro LEDtube 1200mm 18W 5CCT T8 AU	190 degree(s)	2700 K	83	2700K/3000K/4000K/5000K/6500K	2,000 lm

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature	Color rendering index (CRI)	Color Code	Luminous Flux
			(Nom)			
929004265719	CorePro LEDtube 1500mm 24W 5CCT T8 AU	160 degree(s)	2700 K	83	2700K/3000K/ 4000K/5000K/ 6500K	2,500 lm
929003605012	CorePro LEDTube 36 8ft 32W 865 T8 CT WV	120 degree(s)	6500 K	80	865	3,600 lm
929004253112	CorePro LEDTube 1200mm 16W 865 T8 FA8 WV	240 degree(s)	6500 K	80	865	1,800 lm
929002000372	CorePro LEDtube 600mm 9W 830 T8C W G	240 degree(s)	3000 K	80	830	900 lm
929002000472	CorePro LEDtube 600mm 9W 840 T8 C W G	240 degree(s)	4000 K	80	840	900 lm
929002000572	CorePro LEDtube 600mm 9W 865 T8 C W G	240 degree(s)	6500 K	80	865	900 lm
929002998802	CorePro LEDtube 1800mm 21W 840 T8	160 degree(s)	4000 K	80	840	3,100 lm
929003561802	CorePro LEDtube 1800mm 21W 865 T8	160 degree(s)	6500 K	80	865	3,100 lm
929003584702	CorePro LEDtube 1800mm 21W830 T8	160 degree(s)	3000 K	80	830	2,900 lm
929001874802	CorePro LEDtube 1200mm HO 18W 865 T8	240 degree(s)	6500 K	80	865	2,000 lm
929001874832	CorePro LEDtube 1200mm HO 18W 865 T8	240 degree(s)	6500 K	80	865	2,000 lm
929001874902	CorePro LEDtube 1200mm HO 18W 840 T8	240 degree(s)	4000 K	80	840	2,000 lm
929001874932	CorePro LEDtube 1200mm HO 18W 840 T8	240 degree(s)	4000 K	80	840	2,000 lm
929001875002	CorePro LEDtube 1500mm HO 24W 865 T8	240 degree(s)	6500 K	80	865	2,700 lm
929001875032	CorePro LEDtube 1500mm HO 24W 865 T8	240 degree(s)	6500 K	80	865	2,700 lm
929001875102	CorePro LEDtube 1500mm HO 24W 840 T8	240 degree(s)	4000 K	80	840	2,700 lm
929001875132	CorePro LEDtube 1500mm HO 24W 840 T8	240 degree(s)	4000 K	80	840	2,700 lm
929003022102	CorePro LEDtube 600mm 8W 840 T8	240 degree(s)	4000 K	80	840	800 lm
929003022202	CorePro LEDtube 600mm 8W 865 T8	240 degree(s)	6500 K	80	865	800 lm
929003022502	CorePro LEDtube 1500mm 20W 840 T8	240 degree(s)	4000 K	80	840	2,200 lm
929003022602	CorePro LEDtube 1500mm 20W 865 T8	240 degree(s)	6500 K	80	865	2,200 lm
929003154202	CorePro LEDtube 1200mm UO 21.5W 840 T8	240 degree(s)	4000 K	80	840	2,400 lm
929003154302	CorePro LEDtube 1200mm UO 21.5W 865 T8	240 degree(s)	6500 K	80	865	2,400 lm
929003154402	CorePro LEDtube 1500mm UO 31.5W 840 T8	240 degree(s)	4000 K	80	840	3,500 lm
929003154502	CorePro LEDtube 1500mm UO 31.5W 865 T8	240 degree(s)	6500 K	80	865	3,500 lm
929003158602	CorePro LEDtube 600mm HO 8W 840 T8	240 degree(s)	4000 K	80	840	900 lm
929003158610	CorePro LEDtube 600mm HO 8W 840 T8 CN	240 degree(s)	4000 K	80	840	900 lm
929003158702	CorePro LEDtube 600mm HO 8W 865 T8	240 degree(s)	6500 K	80	865	900 lm
929003158710	CorePro LEDtube 600mm HO 8W 865 T8 CN	240 degree(s)	6500 K	80	865	900 lm
929003519702	CorePro LEDtube 1200mm 15.5W 840 T8	240 degree(s)	4000 K	80	840	1,800 lm
929003519708	CorePro LEDtube 1200mm 15.5W 840 T8 AP I	240 degree(s)	4000 K	80	840	1,800 lm
929003519720	CorePro LEDtube 1200mm 17W 840 T8 AU 1CT	240 degree(s)	4000 K	80	840	1,800 lm
929003519721	CorePro LEDtube 1200mm 17W 840 T8 AU 2CT	240 degree(s)	4000 K	80	840	1,800 lm
929003519762	CorePro LEDtube 1200mm 15.5W 840 T8 CL	240 degree(s)	4000 K	80	840	1,800 lm
929003519802	CorePro LEDtube 1200mm 15.5W 865 T8	240 degree(s)	6500 K	80	865	1,800 lm
929003519808	CorePro LEDtube 1200mm 15.5W 865 T8 AP I	240 degree(s)	6500 K	80	865	1,800 lm
929003519820	CorePro LEDtube 1200mm 17W 865 T8 AU 1CT	240 degree(s)	6500 K	80	865	1,800 lm
929003519821	CorePro LEDtube 1200mm 17W 865 T8 AU 2CT	240 degree(s)	6500 K	80	865	1,800 lm
929003519832	CorePro LEDtube 1200mm 15.5W 865 T8	240 degree(s)	6500 K	80	865	1,800 lm
929003519862	CorePro LEDtube 1200mm 15.5W 865 T8 CL	240 degree(s)	6500 K	80	865	1,800 lm
929003519888	CorePro LEDtube 1200mm 15.5W 865 T8 PH	240 degree(s)	6500 K	80	865	1,800 lm
929003520119	CorePro LEDtube 600mm 9.9W 840 T8 AU	240 degree(s)	4000 K	80	840	900 lm
929003520219	CorePro LEDtube 600mm 9.9W 865 T8 AU	240 degree(s)	6500 K	80	865	900 lm
929003520319	CorePro LEDtube 1200mm 17.6W 840 T8 AU	240 degree(s)	4000 K	80	840	1,800 lm
929003520419	CorePro LEDtube 1200mm 17.6W 865 T8 AU	240 degree(s)	6500 K	80	865	1,800 lm
929003520519	CorePro LEDtube 1500mm 22W 840 T8 AU	240 degree(s)	4000 K	80	840	2,200 lm
929003520619	CorePro LEDtube 1500mm 22W 865 T8 AU	240 degree(s)	6500 K	80	865	2,200 lm
929003520708	Corepro LEDtube HO 1200mm 18W840T8 AP	240 degree(s)	4000 K	80	840	2,100 lm
929003520710	Corepro LEDtube HO 1200mm 18W840T8 CN	240 degree(s)	4000 K	80	840	2,100 lm

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature	Color rendering index (CRI)	Color Code	Luminous Flux
			(Nom)			
929003520738	Corepro LEDtube 50k 1200mm 18W840T8 MY	240 degree(s)	4000 K	80	840	2,100 lm
929003520808	CorePro LEDtube HO 1200mm 18W865T8 AP	240 degree(s)	6500 K	80	865	2,100 lm
929003520810	CorePro LEDtube HO 1200mm 18W865T8 CN	240 degree(s)	6500 K	80	865	2,100 lm
929003520838	CorePro LEDtube 50k 1200mm 18W865T8 MY	240 degree(s)	6500 K	80	865	2,100 lm
929003520888	CorePro LEDtube HO 1200mm 18W 865 T8 PH	240 degree(s)	6500 K	80	865	2,100 lm
929003534411	CorePro LEDtube 600mm 8W 840 VVW T8	240 degree(s)	4000 K	80	840	800 lm
929003534511	CorePro LEDtube 600mm 8W 865 VVW T8	240 degree(s)	6500 K	80	865	800 lm
929003534811	CorePro LEDtube HO 1200mm 18W840 VVW T8	240 degree(s)	4000 K	80	840	2,100 lm
929003534911	CorePro LEDtube HO 1200mm 18W865 VVW T8	240 degree(s)	6500 K	80	865	2,100 lm
929003547202	CorePro LEDtube 600mm 8W 840 T8	240 degree(s)	4000 K	80	840	800 lm
929003547208	CorePro LEDtube 600mm 8W 840 T8 AP I	240 degree(s)	4000 K	80	840	800 lm
929003547220	CorePro LEDtube 600mm 8.8W 840 T8 AU 1CT	240 degree(s)	4000 K	80	840	800 lm
929003547221	CorePro LEDtube 600mm 8.8W 840 T8 AU 2CT	240 degree(s)	4000 K	80	840	800 lm
929003547262	CorePro LEDtube 600mm 8W 840 T8 CL	240 degree(s)	4000 K	80	840	800 lm
929003547302	CorePro LEDtube 600mm 8W 865 T8	240 degree(s)	6500 K	80	865	800 lm
929003547308	CorePro LEDtube 600mm 8W 865 T8 AP I	240 degree(s)	6500 K	80	865	800 lm
929003547320	CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT	240 degree(s)	6500 K	80	865	800 lm
929003547321	CorePro LEDtube 600mm 8.8W 865 T8 AU 2CT	240 degree(s)	6500 K	80	865	800 lm
929003547362	CorePro LEDtube 600mm 8W 865 T8 CL	240 degree(s)	6500 K	80	865	800 lm
929003547402	CorePro LEDtube 1500mm 20W 840 T8	240 degree(s)	4000 K	80	840	2,200 lm
929003547420	CorePro LEDtube 1500mm 22W 840 T8AU1CT	240 degree(s)	4000 K	80	840	2,200 lm
929003547421	CorePro LEDtube 1500mm 22W 840 T8AU2CT	240 degree(s)	4000 K	80	840	2,200 lm
929003547462	CorePro LEDtube 1500mm 20W 840 T8 CL	240 degree(s)	4000 K	80	840	2,200 lm
929003547502	CorePro LEDtube 1500mm 20W 865 T8	240 degree(s)	6500 K	80	865	2,200 lm
929003547520	CorePro LEDtube 1500mm 22W 865 T8AU1CT	240 degree(s)	6500 K	80	865	2,200 lm
929003547521	CorePro LEDtube 1500mm 22W 865 T8AU2CT	240 degree(s)	6500 K	80	865	2,200 lm
929003547562	CorePro LEDtube 1500mm 20W 865 T8 CL	240 degree(s)	6500 K	80	865	2,200 lm
929003577132	CorePro LEDtube 600mm 8W 830 T8	240 degree(s)	3000 K	80	830	750 lm
929003577232	CorePro LEDtube 1200mm 15.5W 830 T8	240 degree(s)	3000 K	80	830	1,700 lm
929003577332	CorePro LEDtube 1500mm 20W 830 T8	240 degree(s)	3000 K	80	830	2,050 lm
929003577402	CorePro LEDtube 600mm HO 8W 830 T8	240 degree(s)	3000 K	80	830	850 lm
929003577532	CorePro LEDtube 1200mm HO 18W 830 T8	240 degree(s)	3000 K	80	830	1,850 lm
929003577632	CorePro LEDtube 1500mm HO 24W 830 T8	240 degree(s)	3000 K	80	830	2,500 lm
929003577702	CorePro LEDtube 1200mm UO 21.5W 830 T8	240 degree(s)	3000 K	80	830	2,250 lm
929003577802	CorePro LEDtube 1500mm UO 31.5W 830 T8	240 degree(s)	3000 K	80	830	3,320 lm
929003746102	CorePro LEDtube 1200mm UO 17.7W 830 T8	240 degree(s)	3000 K	80	830	2,250 lm
929003746202	CorePro LEDtube 1200mm UO 17.7W 840 T8	240 degree(s)	4000 K	80	840	2,400 lm
929003746302	CorePro LEDtube 1200mm UO 17.7W 865 T8	240 degree(s)	6500 K	80	865	2,400 lm
929003746402	CorePro LEDtube 1500mm UO 25.9W 830 T8	240 degree(s)	3000 K	80	830	3,320 lm
929003746502	CorePro LEDtube 1500mm UO 25.9W 840 T8	240 degree(s)	4000 K	80	840	3,500 lm
929003746602	CorePro LEDtube 1500mm UO 25.9W 865 T8	240 degree(s)	6500 K	80	865	3,500 lm
929003771708	CorePro LEDtube HO 1200mm 18W865T8 ID	240 degree(s)	6500 K	80	865	2,100 lm
929001999772	CorePro LEDtube 1200mm 18W 830 T8C W G	240 degree(s)	3000 K	80	830	1,850 lm
929001999868	CorePro LEDtube 1200mm 15.7W 840 T8 KSA	240 degree(s)	4000 K	80	840	1,850 lm
929001999872	CorePro LEDtube 1200mm 18W 840 T8C W G	240 degree(s)	4000 K	80	840	1,850 lm
929001999968	CorePro LEDtube 1200mm 15.7W 865 T8 KSA	240 degree(s)	6500 K	80	865	1,850 lm
929001999972	CorePro LEDtube 1200mm 18W 865 T8C W G	240 degree(s)	6500 K	80	865	1,850 lm
929002000468	CorePro LEDtube 600mm 8.6W 840 T8 KSA	240 degree(s)	4000 K	80	840	950 lm
929002000568	CorePro LEDtube 600mm 8.6W 865 T8 KSA	240 degree(s)	6500 K	80	865	950 lm
929002474472	CorePro LEDTube 8ft 32W 3800lm 865 T8 BR	240 degree(s)	6500 K	80	865	3,800 lm
929003604912	CorePro LEDTube 36 8ft 32W 865 T8 WV	240 degree(s)	6500 K	80	865	3,600 lm

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Correlated Color Temperature		Color rendering index (CRI)	Color Code	Luminous Flux
		Beam Angle (Nom)	(Nom)			
929002000072	CorePro LEDtube 1200mm HO 18W840 C W G	240 degree(s)	4000 K	80	840	2,100 lm
929002000172	CorePro LEDtube 1200mm HO 18W865 C W G	240 degree(s)	6500 K	80	865	2,100 lm

Operating and Electrical

Order Code	Full Product Name	Line	Power	Wattage	Order Code	Full Product Name	Line	Power	Wattage
		Frequency	Consumption	Equivalent			Frequency	Consumption	Equivalent
929004265519	CorePro LEDtube 600mm 9W 5CCT T8 AU	-	9 W	18 W	929001875002	CorePro LEDtube 1500mm HO 24W 865 T8	50 to 60 Hz	24 W	-
929004265619	CorePro LEDtube 1200mm 18W 5CCT T8 AU	-	18 W	36 W	929001875032	CorePro LEDtube 1500mm HO 24W 865 T8	50 to 60 Hz	24 W	-
929004265719	CorePro LEDtube 1500mm 24W 5CCT T8 AU	-	24 W	58 W	929001875102	CorePro LEDtube 1500mm HO 24W 840 T8	50 to 60 Hz	24 W	-
929003605012	CorePro LEDTube 36 8ft 32W 865 T8 CT WV	50 to 60 Hz	32 W	-	929001875132	CorePro LEDtube 1500mm HO 24W 840 T8	50 to 60 Hz	24 W	-
929004253112	CorePro LEDTube 1200mm 16W 865 T8 FA8 WV	-	16 W	36 W	929003022102	CorePro LEDtube 600mm 8W 840 T8	50 to 60 Hz	8 W	-
929002000372	CorePro LEDtube 600mm 9W 830 T8C W G	50 to 60 Hz	9 W	18 W	929003022202	CorePro LEDtube 600mm 8W 865 T8	50 to 60 Hz	8 W	-
929002000472	CorePro LEDtube 600mm 9W 840 T8 C W G	50 to 60 Hz	9 W	18 W	929003022502	CorePro LEDtube 1500mm 20W 840 T8	50 to 60 Hz	20 W	-
929002000572	CorePro LEDtube 600mm 9W 865 T8 C W G	50 to 60 Hz	9 W	18 W	929003022602	CorePro LEDtube 1500mm 20W 865 T8	50 to 60 Hz	20 W	-
929002998802	CorePro LEDtube 1800mm 21W 840 T8	50 to 60 Hz	21 W	-	929003154202	CorePro LEDtube 1200mm UO 21.5W 840 T8	50 to 60 Hz	21.5 W	-
929003561802	CorePro LEDtube 1800mm 21W 865 T8	50 to 60 Hz	21 W	-	929003154302	CorePro LEDtube 1200mm UO 21.5W 865 T8	50 to 60 Hz	21.5 W	-
929003584702	CorePro LEDtube 1800mm 21W830 T8	50 to 60 Hz	21 W	-	929003154402	CorePro LEDtube 1500mm UO 31.5W 840 T8	50 to 60 Hz	31.5 W	-
929001874802	CorePro LEDtube 1200mm HO 18W 865 T8	50 to 60 Hz	18 W	-	929003154502	CorePro LEDtube 1500mm UO 31.5W 865 T8	50 to 60 Hz	31.5 W	-
929001874832	CorePro LEDtube 1200mm HO 18W 865 T8	50 to 60 Hz	18 W	-	929003158602	CorePro LEDtube 600mm HO 8W 840 T8	50 to 60 Hz	8 W	-
929001874902	CorePro LEDtube 1200mm HO 18W 840 T8	50 to 60 Hz	18 W	-	929003158610	CorePro LEDtube 600mm HO 8W 840 T8 CN	-	8 W	18 W
929001874932	CorePro LEDtube 1200mm HO 18W 840 T8	50 to 60 Hz	18 W	-	929003158702	CorePro LEDtube 600mm HO 8W 865 T8	50 to 60 Hz	8 W	-

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003158710	CorePro LEDtube 600mm HO 8W 865 T8 CN	-	8 W	18 W
929003519702	CorePro LEDtube 1200mm 15.5W 840 T8	50 to 60 Hz	15.5 W	-
929003519708	CorePro LEDtube 1200mm 15.5W 840 T8 AP I	-	15.5 W	-
929003519720	CorePro LEDtube 1200mm 17W 840 T8 AU 1CT	-	17 W	36 W
929003519721	CorePro LEDtube 1200mm 17W 840 T8 AU 2CT	-	17 W	36 W
929003519762	CorePro LEDtube 1200mm 15.5W 840 T8 CL	50 to 60 Hz	15.5 W	-
929003519802	CorePro LEDtube 1200mm 15.5W 865 T8	50 to 60 Hz	15.5 W	-
929003519808	CorePro LEDtube 1200mm 15.5W 865 T8 AP I	-	15.5 W	-
929003519820	CorePro LEDtube 1200mm 17W 865 T8 AU 1CT	-	17 W	36 W
929003519821	CorePro LEDtube 1200mm 17W 865 T8 AU 2CT	-	17 W	36 W
929003519832	CorePro LEDtube 1200mm 15.5W 865 T8	50 to 60 Hz	15.5 W	-
929003519862	CorePro LEDtube 1200mm 15.5W 865 T8 CL	50 to 60 Hz	15.5 W	-
929003519888	CorePro LEDtube 1200mm 15.5W 865 T8 PH	-	15.5 W	36 W
929003520119	CorePro LEDtube 600mm 9.9W 840 T8 AU	50 to 60 Hz	9.9 W	-
929003520219	CorePro LEDtube 600mm 9.9W 865 T8 AU	50 to 60 Hz	9.9 W	-
929003520319	CorePro LEDtube 1200mm 17.6W 840 T8 AU	50 to 60 Hz	17.6 W	-
929003520419	CorePro LEDtube 1200mm 17.6W 865 T8 AU	50 to 60 Hz	17.6 W	-

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003520519	CorePro LEDtube 1500mm 22W 840 T8 AU	50 to 60 Hz	22 W	-
929003520619	CorePro LEDtube 1500mm 22W 865 T8 AU	50 to 60 Hz	22 W	-
929003520708	Corepro LEDtube HO 1200mm 18W840T8 AP	50 to 60 Hz	18 W	-
929003520710	Corepro LEDtube HO 1200mm 18W840T8 CN	-	18 W	36 W
929003520738	Corepro LEDtube 50k 1200mm 18W840T8 MY	-	18 W	36 W
929003520808	CorePro LEDtube HO 1200mm 18W865T8 AP	50 to 60 Hz	18 W	-
929003520810	CorePro LEDtube HO 1200mm 18W865T8 CN	-	18 W	36 W
929003520838	CorePro LEDtube 50k 1200mm 18W865T8 MY	-	18 W	36 W
929003520888	CorePro LEDtube HO 1200mm 18W 865 T8 PH	-	18 W	36 W
929003534411	CorePro LEDtube 600mm 8W 840 VWV T8	50 to 60 Hz	8 W	-
929003534511	CorePro LEDtube 600mm 8W 865 VWV T8	50 to 60 Hz	8 W	-
929003534811	CorePro LEDtube HO 1200mm 18W840 VWV T8	50 to 60 Hz	18 W	-
929003534911	CorePro LEDtube HO 1200mm 18W865 VWV T8	50 to 60 Hz	18 W	-
929003547202	CorePro LEDtube 600mm 8W 840 T8	50 to 60 Hz	8 W	-
929003547208	CorePro LEDtube 600mm 8W 840 T8 AP I	-	8 W	-
929003547220	CorePro LEDtube 600mm 8.8W 840 T8 AU 1CT	-	8.8 W	18 W
929003547221	CorePro LEDtube 600mm 8.8W 840 T8 AU 2CT	-	8.8 W	18 W

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003547262	CorePro LEDtube 600mm 8W 840 T8 CL	50 to 60 Hz	8 W	-
929003547302	CorePro LEDtube 600mm 8W 865 T8	50 to 60 Hz	8 W	-
929003547308	CorePro LEDtube 600mm 8W 865 T8 AP I	-	8 W	-
929003547320	CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT	-	8.8 W	18 W
929003547321	CorePro LEDtube 600mm 8.8W 865 T8 AU 2CT	-	8.8 W	18 W
929003547362	CorePro LEDtube 600mm 8W 865 T8 CL	50 to 60 Hz	8 W	-
929003547402	CorePro LEDtube 1500mm 20W 840 T8	50 to 60 Hz	20 W	-
929003547420	CorePro LEDtube 1500mm 22W 840 T8AU1CT	-	22 W	58 W
929003547421	CorePro LEDtube 1500mm 22W 840 T8AU2CT	-	22 W	58 W
929003547462	CorePro LEDtube 1500mm 20W 840 T8 CL	50 to 60 Hz	20 W	-
929003547502	CorePro LEDtube 1500mm 20W 865 T8	50 to 60 Hz	20 W	-
929003547520	CorePro LEDtube 1500mm 22W 865 T8AU1CT	-	22 W	58 W
929003547521	CorePro LEDtube 1500mm 22W 865 T8AU2CT	-	22 W	58 W
929003547562	CorePro LEDtube 1500mm 20W 865 T8 CL	50 to 60 Hz	20 W	-
929003577132	CorePro LEDtube 600mm 8W 830 T8	50 to 60 Hz	8 W	-
929003577232	CorePro LEDtube 1200mm 15.5W 830 T8	50 to 60 Hz	15.5 W	-
929003577332	CorePro LEDtube 1500mm 20W 830 T8	50 to 60 Hz	20 W	-
929003577402	CorePro LEDtube 600mm HO 8W 830 T8	50 to 60 Hz	8 W	-

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003577532	CorePro LEDtube 1200mm HO 18W 830 T8	50 to 60 Hz	18 W	-
929003577632	CorePro LEDtube 1500mm HO 24W 830 T8	50 to 60 Hz	24 W	-
929003577702	CorePro LEDtube 1200mm UO 21.5W 830 T8	50 to 60 Hz	21.5 W	-
929003577802	CorePro LEDtube 1500mm UO 31.5W 830 T8	50 to 60 Hz	31.5 W	-
929003746102	CorePro LEDtube 1200mm UO 17.7W 830 T8	-	17.7 W	-
929003746202	CorePro LEDtube 1200mm UO 17.7W 840 T8	-	17.7 W	-
929003746302	CorePro LEDtube 1200mm UO 17.7W 865 T8	-	17.7 W	-
929003746402	CorePro LEDtube 1500mm UO 25.9W 830 T8	-	25.9 W	-
929003746502	CorePro LEDtube 1500mm UO 25.9W 840 T8	-	25.9 W	-
929003746602	CorePro LEDtube 1500mm UO 25.9W 865 T8	-	25.9 W	-
929003771708	CorePro LEDtube HO 1200mm 18W865T8 ID	-	18 W	36 W
929001999772	CorePro LEDtube 1200mm 18W 830 T8C W G	50 to 60 Hz	18 W	36 W
929001999868	CorePro LEDtube 1200mm 15.7W 840 T8 KSA	-	15.7 W	36 W
929001999872	CorePro LEDtube 1200mm 18W 840 T8C W G	50 to 60 Hz	18 W	36 W
929001999968	CorePro LEDtube 1200mm 15.7W 865 T8 KSA	-	15.7 W	36 W
929001999972	CorePro LEDtube 1200mm 18W 865 T8C W G	50 to 60 Hz	18 W	36 W
929002000468	CorePro LEDtube 600mm 8.6W 840 T8 KSA	-	8.6 W	18 W

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Line	Power	Wattage
		Frequency	Consumption	Equivalent
929002000568	CorePro LEDtube 600mm 8.6W 865 T8 KSA	-	8.6 W	18 W
929002474472	CorePro LEDTube 8ft 32W 3800lm 865 T8 BR	-	32 W	110 W
929003604912	CorePro LEDTube 36 8ft 32W 865 T8 WV	50 to 60 Hz	32 W	-

Order Code	Full Product Name	Line	Power	Wattage
		Frequency	Consumption	Equivalent
929002000072	CorePro LEDtube 1200mm HO 18W840 C W G	50 to 60 Hz	18 W	-
929002000172	CorePro LEDtube 1200mm HO 18W865 C W G	50 to 60 Hz	18 W	-

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929004265519	CorePro LEDtube 600mm 9W 5CCT T8 AU	60 °C
929004265619	CorePro LEDtube 1200mm 18W 5CCT T8 AU	70 °C
929004265719	CorePro LEDtube 1500mm 24W 5CCT T8 AU	65 °C
929003605012	CorePro LEDTube 36 8ft 32W 865 T8 CT WV	60 °C
929004253112	CorePro LEDTube 1200mm 16W 865 T8 FA8 WV	63 °C
929002000372	CorePro LEDtube 600mm 9W 830 T8C W G	56 °C
929002000472	CorePro LEDtube 600mm 9W 840 T8 C W G	56 °C
929002000572	CorePro LEDtube 600mm 9W 865 T8 C W G	56 °C
929002998802	CorePro LEDtube 1800mm 21W 840 T8	60 °C
929003561802	CorePro LEDtube 1800mm 21W 865 T8	60 °C
929003584702	CorePro LEDtube 1800mm 21W830 T8	60 °C
929001874802	CorePro LEDtube 1200mm HO 18W 865 T8	60 °C
929001874832	CorePro LEDtube 1200mm HO 18W 865 T8	60 °C
929001874902	CorePro LEDtube 1200mm HO 18W 840 T8	60 °C
929001874932	CorePro LEDtube 1200mm HO 18W 840 T8	60 °C
929001875002	CorePro LEDtube 1500mm HO 24W 865 T8	60 °C
929001875032	CorePro LEDtube 1500mm HO 24W 865 T8	60 °C
929001875102	CorePro LEDtube 1500mm HO 24W 840 T8	60 °C
929001875132	CorePro LEDtube 1500mm HO 24W 840 T8	60 °C
929003022102	CorePro LEDtube 600mm 8W 840 T8	50 °C
929003022202	CorePro LEDtube 600mm 8W 865 T8	50 °C
929003022502	CorePro LEDtube 1500mm 20W 840 T8	60 °C
929003022602	CorePro LEDtube 1500mm 20W 865 T8	60 °C
929003154202	CorePro LEDtube 1200mm UO 21.5W 840 T8	50 °C
929003154302	CorePro LEDtube 1200mm UO 21.5W 865 T8	50 °C
929003154402	CorePro LEDtube 1500mm UO 31.5W 840 T8	55 °C
929003154502	CorePro LEDtube 1500mm UO 31.5W 865 T8	55 °C
929003158602	CorePro LEDtube 600mm HO 8W 840 T8	50 °C
929003158610	CorePro LEDtube 600mm HO 8W 840 T8 CN	50 °C
929003158702	CorePro LEDtube 600mm HO 8W 865 T8	50 °C
929003158710	CorePro LEDtube 600mm HO 8W 865 T8 CN	50 °C
929003519702	CorePro LEDtube 1200mm 15.5W 840 T8	60 °C
929003519708	CorePro LEDtube 1200mm 15.5W 840 T8 AP I	60 °C
929003519720	CorePro LEDtube 1200mm 17W 840 T8 AU 1CT	60 °C
929003519721	CorePro LEDtube 1200mm 17W 840 T8 AU 2CT	60 °C
929003519762	CorePro LEDtube 1200mm 15.5W 840 T8 CL	60 °C
929003519802	CorePro LEDtube 1200mm 15.5W 865 T8	60 °C
929003519808	CorePro LEDtube 1200mm 15.5W 865 T8 AP I	60 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003519820	CorePro LEDtube 1200mm 17W 865 T8 AU 1CT	60 °C
929003519821	CorePro LEDtube 1200mm 17W 865 T8 AU 2CT	60 °C
929003519832	CorePro LEDtube 1200mm 15.5W 865 T8	60 °C
929003519862	CorePro LEDtube 1200mm 15.5W 865 T8 CL	60 °C
929003519888	CorePro LEDtube 1200mm 15.5W 865 T8 PH	60 °C
929003520119	CorePro LEDtube 600mm 9.9W 840 T8 AU	45 °C
929003520219	CorePro LEDtube 600mm 9.9W 865 T8 AU	45 °C
929003520319	CorePro LEDtube 1200mm 17.6W 840 T8 AU	50 °C
929003520419	CorePro LEDtube 1200mm 17.6W 865 T8 AU	50 °C
929003520519	CorePro LEDtube 1500mm 22W 840 T8 AU	50 °C
929003520619	CorePro LEDtube 1500mm 22W 865 T8 AU	50 °C
929003520708	Corepro LEDtube HO 1200mm 18W840T8 AP	55 °C
929003520710	Corepro LEDtube HO 1200mm 18W840T8 CN	55 °C
929003520738	Corepro LEDtube 50k 1200mm 18W840T8 MY	55 °C
929003520808	CorePro LEDtube HO 1200mm 18W865T8 AP	55 °C
929003520810	CorePro LEDtube HO 1200mm 18W865T8 CN	55 °C
929003520838	CorePro LEDtube 50k 1200mm 18W865T8 MY	55 °C
929003520888	CorePro LEDtube HO 1200mm 18W 865 T8 PH	55 °C
929003534411	CorePro LEDtube 600mm 8W 840 VWV T8	50 °C
929003534511	CorePro LEDtube 600mm 8W 865 VWV T8	50 °C
929003534811	CorePro LEDtube HO 1200mm 18W840 VWV T8	60 °C
929003534911	CorePro LEDtube HO 1200mm 18W865 VWV T8	60 °C
929003547202	CorePro LEDtube 600mm 8W 840 T8	50 °C
929003547208	CorePro LEDtube 600mm 8W 840 T8 AP I	50 °C
929003547220	CorePro LEDtube 600mm 8.8W 840 T8 AU 1CT	50 °C
929003547221	CorePro LEDtube 600mm 8.8W 840 T8 AU 2CT	50 °C
929003547262	CorePro LEDtube 600mm 8W 840 T8 CL	50 °C
929003547302	CorePro LEDtube 600mm 8W 865 T8	50 °C
929003547308	CorePro LEDtube 600mm 8W 865 T8 AP I	50 °C
929003547320	CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT	50 °C
929003547321	CorePro LEDtube 600mm 8.8W 865 T8 AU 2CT	50 °C
929003547362	CorePro LEDtube 600mm 8W 865 T8 CL	50 °C
929003547402	CorePro LEDtube 1500mm 20W 840 T8	60 °C
929003547420	CorePro LEDtube 1500mm 22W 840 T8AU1CT	60 °C
929003547421	CorePro LEDtube 1500mm 22W 840 T8AU2CT	60 °C
929003547462	CorePro LEDtube 1500mm 20W 840 T8 CL	60 °C
929003547502	CorePro LEDtube 1500mm 20W 865 T8	60 °C
929003547520	CorePro LEDtube 1500mm 22W 865 T8AU1CT	60 °C

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	T-Case Maximum (Nom)
929003547521	CorePro LEDtube 1500mm 22W 865 T8AU2CT	60 °C
929003547562	CorePro LEDtube 1500mm 20W 865 T8 CL	60 °C
929003577132	CorePro LEDtube 600mm 8W 830 T8	50 °C
929003577232	CorePro LEDtube 1200mm 15.5W 830 T8	60 °C
929003577332	CorePro LEDtube 1500mm 20W 830 T8	60 °C
929003577402	CorePro LEDtube 600mm HO 8W 830 T8	50 °C
929003577532	CorePro LEDtube 1200mm HO 18W 830 T8	60 °C
929003577632	CorePro LEDtube 1500mm HO 24W 830 T8	60 °C
929003577702	CorePro LEDtube 1200mm UO 21.5W 830 T8	50 °C
929003577802	CorePro LEDtube 1500mm UO 31.5W 830 T8	55 °C
929003746102	CorePro LEDtube 1200mm UO 17.7W 830 T8	55 °C
929003746202	CorePro LEDtube 1200mm UO 17.7W 840 T8	55 °C
929003746302	CorePro LEDtube 1200mm UO 17.7W 865 T8	55 °C
929003746402	CorePro LEDtube 1500mm UO 25.9W 830 T8	55 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929004265519	CorePro LEDtube 600mm 9W 5CCT T8 AU	Frosted	Tube, double-ended
929004265619	CorePro LEDtube 1200mm 18W 5CCT T8 AU	Frosted	Tube, double-ended
929004265719	CorePro LEDtube 1500mm 24W 5CCT T8 AU	Frosted	Tube, double-ended
929003605012	CorePro LEDTube 36 8ft 32W 865 T8 CT WV	Clear	T8
929004253112	CorePro LEDTube 1200mm 16W 865 T8 FA8 WV	Frosted	T8
929002000372	CorePro LEDtube 600mm 9W 830 T8C W G	Frosted	Tube, double-ended
929002000472	CorePro LEDtube 600mm 9W 840 T8 C W G	Frosted	Tube, double-ended
929002000572	CorePro LEDtube 600mm 9W 865 T8 C W G	Frosted	Tube, double-ended
929002998802	CorePro LEDtube 1800mm 21W 840 T8	Frosted	T8
929003561802	CorePro LEDtube 1800mm 21W 865 T8	Frosted	T8
929003584702	CorePro LEDtube 1800mm 21W830 T8	Frosted	T8
929001874802	CorePro LEDtube 1200mm HO 18W 865 T8	Frosted	T8
929001874832	CorePro LEDtube 1200mm HO 18W 865 T8	Frosted	T8
929001874902	CorePro LEDtube 1200mm HO 18W 840 T8	Frosted	T8
929001874932	CorePro LEDtube 1200mm HO 18W 840 T8	Frosted	T8
929001875002	CorePro LEDtube 1500mm HO 24W 865 T8	Frosted	T8
929001875032	CorePro LEDtube 1500mm HO 24W 865 T8	Frosted	T8

Order Code	Full Product Name	T-Case Maximum (Nom)
929003746502	CorePro LEDtube 1500mm UO 25.9W 840 T8	55 °C
929003746602	CorePro LEDtube 1500mm UO 25.9W 865 T8	55 °C
929003771708	CorePro LEDtube HO 1200mm 18W865T8 ID	55 °C
929001999772	CorePro LEDtube 1200mm 18W 830 T8C W G	65 °C
929001999868	CorePro LEDtube 1200mm 15.7W 840 T8 KSA	65 °C
929001999872	CorePro LEDtube 1200mm 18W 840 T8C W G	65 °C
929001999968	CorePro LEDtube 1200mm 15.7W 865 T8 KSA	65 °C
929001999972	CorePro LEDtube 1200mm 18W 865 T8C W G	65 °C
929002000468	CorePro LEDtube 600mm 8.6W 840 T8 KSA	55 °C
929002000568	CorePro LEDtube 600mm 8.6W 865 T8 KSA	55 °C
929002474472	CorePro LEDTube 8ft 32W 3800lm 865 T8 BR	65 °C
929003604912	CorePro LEDTube 36 8ft 32W 865 T8 WV	60 °C
929002000072	CorePro LEDtube 1200mm HO 18W840 C W G	65 °C
929002000172	CorePro LEDtube 1200mm HO 18W865 C W G	65 °C

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001875102	CorePro LEDtube 1500mm HO 24W 840 T8	Frosted	T8
929001875132	CorePro LEDtube 1500mm HO 24W 840 T8	Frosted	T8
929003022102	CorePro LEDtube 600mm 8W 840 T8	Frosted	T8
929003022202	CorePro LEDtube 600mm 8W 865 T8	Frosted	T8
929003022502	CorePro LEDtube 1500mm 20W 840 T8	Frosted	T8
929003022602	CorePro LEDtube 1500mm 20W 865 T8	Frosted	T8
929003154202	CorePro LEDtube 1200mm UO 21.5W 840 T8	Frosted	T8
929003154302	CorePro LEDtube 1200mm UO 21.5W 865 T8	Frosted	T8
929003154402	CorePro LEDtube 1500mm UO 31.5W 840 T8	Frosted	T8
929003154502	CorePro LEDtube 1500mm UO 31.5W 865 T8	Frosted	T8
929003158602	CorePro LEDtube 600mm HO 8W 840 T8	Frosted	T8
929003158610	CorePro LEDtube 600mm HO 8W 840 T8 CN	Frosted	T8
929003158702	CorePro LEDtube 600mm HO 8W 865 T8	Frosted	T8
929003158710	CorePro LEDtube 600mm HO 8W 865 T8 CN	Frosted	T8
929003519702	CorePro LEDtube 1200mm 15.5W 840 T8	Frosted	T8
929003519708	CorePro LEDtube 1200mm 15.5W 840 T8 AP I	Frosted	T8
929003519720	CorePro LEDtube 1200mm 17W 840 T8 AU 1CT	Frosted	T8
929003519721	CorePro LEDtube 1200mm 17W 840 T8 AU 2CT	Frosted	T8
929003519762	CorePro LEDtube 1200mm 15.5W 840 T8 CL	Frosted	T8
929003519802	CorePro LEDtube 1200mm 15.5W 865 T8	Frosted	T8

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003519808	CorePro LEDtube 1200mm 15.5W 865 T8 AP I	Frosted	T8
929003519820	CorePro LEDtube 1200mm 17W 865 T8 AU 1CT	Frosted	T8
929003519821	CorePro LEDtube 1200mm 17W 865 T8 AU 2CT	Frosted	T8
929003519832	CorePro LEDtube 1200mm 15.5W 865 T8	Frosted	T8
929003519862	CorePro LEDtube 1200mm 15.5W 865 T8 CL	Frosted	T8
929003519888	CorePro LEDtube 1200mm 15.5W 865 T8 PH	Frosted	T8
929003520119	CorePro LEDtube 600mm 9.9W 840 T8 AU	Frosted	T8
929003520219	CorePro LEDtube 600mm 9.9W 865 T8 AU	Frosted	T8
929003520319	CorePro LEDtube 1200mm 17.6W 840 T8 AU	Frosted	T8
929003520419	CorePro LEDtube 1200mm 17.6W 865 T8 AU	Frosted	T8
929003520519	CorePro LEDtube 1500mm 22W 840 T8 AU	Frosted	T8
929003520619	CorePro LEDtube 1500mm 22W 865 T8 AU	Frosted	T8
929003520708	Corepro LEDtube HO 1200mm 18W840T8 AP	Frosted	T8
929003520710	Corepro LEDtube HO 1200mm 18W840T8 CN	Frosted	T8
929003520738	Corepro LEDtube 50k 1200mm 18W840T8 MY	Frosted	T8
929003520808	CorePro LEDtube HO 1200mm 18W865T8 AP	Frosted	T8
929003520810	CorePro LEDtube HO 1200mm 18W865T8 CN	Frosted	T8
929003520838	CorePro LEDtube 50k 1200mm 18W865T8 MY	Frosted	T8
929003520888	CorePro LEDtube HO 1200mm 18W 865 T8 PH	Frosted	T8
929003534411	CorePro LEDtube 600mm 8W 840 VWV T8	Frosted	T8
929003534511	CorePro LEDtube 600mm 8W 865 VWV T8	Frosted	T8
929003534811	CorePro LEDtube HO 1200mm 18W840 VWV T8	Frosted	T8
929003534911	CorePro LEDtube HO 1200mm 18W865 VWV T8	Frosted	T8
929003547202	CorePro LEDtube 600mm 8W 840 T8	Frosted	T8
929003547208	CorePro LEDtube 600mm 8W 840 T8 AP I	Frosted	T8
929003547220	CorePro LEDtube 600mm 8.8W 840 T8 AU 1CT	Frosted	T8
929003547221	CorePro LEDtube 600mm 8.8W 840 T8 AU 2CT	Frosted	T8
929003547262	CorePro LEDtube 600mm 8W 840 T8 CL	Frosted	T8
929003547302	CorePro LEDtube 600mm 8W 865 T8	Frosted	T8
929003547308	CorePro LEDtube 600mm 8W 865 T8 AP I	Frosted	T8
929003547320	CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT	Frosted	T8

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003547321	CorePro LEDtube 600mm 8.8W 865 T8 AU 2CT	Frosted	T8
929003547362	CorePro LEDtube 600mm 8W 865 T8 CL	Frosted	T8
929003547402	CorePro LEDtube 1500mm 20W 840 T8	Frosted	T8
929003547420	CorePro LEDtube 1500mm 22W 840 T8AU1CT	Frosted	T8
929003547421	CorePro LEDtube 1500mm 22W 840 T8AU2CT	Frosted	T8
929003547462	CorePro LEDtube 1500mm 20W 840 T8 CL	Frosted	T8
929003547502	CorePro LEDtube 1500mm 20W 865 T8	Frosted	T8
929003547520	CorePro LEDtube 1500mm 22W 865 T8AU1CT	Frosted	T8
929003547521	CorePro LEDtube 1500mm 22W 865 T8AU2CT	Frosted	T8
929003547562	CorePro LEDtube 1500mm 20W 865 T8 CL	Frosted	T8
929003577132	CorePro LEDtube 600mm 8W 830 T8	Frosted	T8
929003577232	CorePro LEDtube 1200mm 15.5W 830 T8	Frosted	T8
929003577332	CorePro LEDtube 1500mm 20W 830 T8	Frosted	T8
929003577402	CorePro LEDtube 600mm HO 8W 830 T8	Frosted	T8
929003577532	CorePro LEDtube 1200mm HO 18W 830 T8	Frosted	T8
929003577632	CorePro LEDtube 1500mm HO 24W 830 T8	Frosted	T8
929003577702	CorePro LEDtube 1200mm UO 21.5W 830 T8	Frosted	T8
929003577802	CorePro LEDtube 1500mm UO 31.5W 830 T8	Frosted	T8
929003746102	CorePro LEDtube 1200mm UO 17.7W 830 T8	Frosted	T8
929003746202	CorePro LEDtube 1200mm UO 17.7W 840 T8	Frosted	T8
929003746302	CorePro LEDtube 1200mm UO 17.7W 865 T8	Frosted	T8
929003746402	CorePro LEDtube 1500mm UO 25.9W 830 T8	Frosted	T8
929003746502	CorePro LEDtube 1500mm UO 25.9W 840 T8	Frosted	T8
929003746602	CorePro LEDtube 1500mm UO 25.9W 865 T8	Frosted	T8
929003771708	CorePro LEDtube HO 1200mm 18W865T8 ID	Frosted	T8
929001999772	CorePro LEDtube 1200mm 18W 830 T8C W G	Frosted	Tube, double-ended
929001999868	CorePro LEDtube 1200mm 15.7W 840 T8 KSA	-	T8
929001999872	CorePro LEDtube 1200mm 18W 840 T8C W G	Frosted	Tube, double-ended
929001999968	CorePro LEDtube 1200mm 15.7W 865 T8 KSA	-	T8

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001999972	CorePro LEDtube 1200mm 18W 865 T8C W G	Frosted	Tube, double-ended
929002000468	CorePro LEDtube 600mm 8.6W 840 T8 KSA	-	T8
929002000568	CorePro LEDtube 600mm 8.6W 865 T8 KSA	-	T8
929002474472	CorePro LEDTube 8ft 32W 3800lm 865 T8 BR	Frosted	Tube, double-ended

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003604912	CorePro LEDTube 36 8ft 32W 865 T8 WV	Frosted	T8
929002000072	CorePro LEDtube 1200mm HO 18W840 C W G	-	T8
929002000172	CorePro LEDtube 1200mm HO 18W865 C W G	-	T8

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929004265519	CorePro LEDtube 600mm 9W 5CCT T8 AU	-20 to +45 °C	-
929004265619	CorePro LEDtube 1200mm 18W 5CCT T8 AU	-20 to +45 °C	-
929004265719	CorePro LEDtube 1500mm 24W 5CCT T8 AU	-20 to +45 °C	-
929003605012	CorePro LEDTube 36 8ft 32W 865 T8 CT WV	-20 °C to 45 °C	-
929004253112	CorePro LEDTube 1200mm 16W 865 T8 FA8 WV	-20 to +45 °C	-
929002000372	CorePro LEDtube 600mm 9W 830 T8C W G	-20 to +45 °C	9 kWh
929002000472	CorePro LEDtube 600mm 9W 840 T8 C W G	-20 to +45 °C	9 kWh
929002000572	CorePro LEDtube 600mm 9W 865 T8 C W G	-20 to +45 °C	9 kWh
929002998802	CorePro LEDtube 1800mm 21W 840 T8	-20 °C to 45 °C	21 kWh
929003561802	CorePro LEDtube 1800mm 21W 865 T8	-20 °C to 45 °C	21 kWh
929003584702	CorePro LEDtube 1800mm 21W830 T8	-20 °C to 45 °C	21 kWh
929001874802	CorePro LEDtube 1200mm HO 18W 865 T8	-20 to +45 °C	18 kWh
929001874832	CorePro LEDtube 1200mm HO 18W 865 T8	-20 to +45 °C	18 kWh
929001874902	CorePro LEDtube 1200mm HO 18W 840 T8	-20 to +45 °C	18 kWh
929001874932	CorePro LEDtube 1200mm HO 18W 840 T8	-20 to +45 °C	18 kWh
929001875002	CorePro LEDtube 1500mm HO 24W 865 T8	-20 to +45 °C	24 kWh
929001875032	CorePro LEDtube 1500mm HO 24W 865 T8	-20 to +45 °C	24 kWh
929001875102	CorePro LEDtube 1500mm HO 24W 840 T8	-20 to +45 °C	24 kWh

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929001875132	CorePro LEDtube 1500mm HO 24W 840 T8	-20 to +45 °C	24 kWh
929003022102	CorePro LEDtube 600mm 8W 840 T8	-20 to +45 °C	8 kWh
929003022202	CorePro LEDtube 600mm 8W 865 T8	-20 to +45 °C	8 kWh
929003022502	CorePro LEDtube 1500mm 20W 840 T8	-20 °C to 45 °C	20 kWh
929003022602	CorePro LEDtube 1500mm 20W 865 T8	-20 °C to 45 °C	20 kWh
929003154202	CorePro LEDtube 1200mm UO 21.5W 840 T8	-20 to +45 °C	22 kWh
929003154302	CorePro LEDtube 1200mm UO 21.5W 865 T8	-20 to +45 °C	22 kWh
929003154402	CorePro LEDtube 1500mm UO 31.5W 840 T8	-20 to +45 °C	32 kWh
929003154502	CorePro LEDtube 1500mm UO 31.5W 865 T8	-20 to +45 °C	32 kWh
929003158602	CorePro LEDtube 600mm HO 8W 840 T8	-20 to +45 °C	8 kWh
929003158610	CorePro LEDtube 600mm HO 8W 840 T8 CN	-20 to +45 °C	-
929003158702	CorePro LEDtube 600mm HO 8W 865 T8	-20 to +45 °C	8 kWh
929003158710	CorePro LEDtube 600mm HO 8W 865 T8 CN	-20 to +45 °C	-
929003519702	CorePro LEDtube 1200mm 15.5W 840 T8	-20 to +45 °C	16 kWh
929003519708	CorePro LEDtube 1200mm 15.5W 840 T8 AP I	-20 to +45 °C	-
929003519720	CorePro LEDtube 1200mm 17W 840 T8 AU 1CT	-20 to +45 °C	-
929003519721	CorePro LEDtube 1200mm 17W 840 T8 AU 2CT	-20 to +45 °C	-
929003519762	CorePro LEDtube 1200mm 15.5W 840 T8 CL	-20 to +45 °C	16 kWh







CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003519802	CorePro LEDtube 1200mm 15.5W 865 T8	-20 to +45 °C	16 kWh
929003519808	CorePro LEDtube 1200mm 15.5W 865 T8 AP I	-20 to +45 °C	-
929003519820	CorePro LEDtube 1200mm 17W 865 T8 AU 1CT	-20 to +45 °C	-
929003519821	CorePro LEDtube 1200mm 17W 865 T8 AU 2CT	-20 to +45 °C	-
929003519832	CorePro LEDtube 1200mm 15.5W 865 T8	-20 °C to 45 °C	16 kWh
929003519862	CorePro LEDtube 1200mm 15.5W 865 T8 CL	-20 to +45 °C	16 kWh
929003519888	CorePro LEDtube 1200mm 15.5W 865 T8 PH	-20 to +45 °C	-
929003520119	CorePro LEDtube 600mm 9.9W 840 T8 AU	-20 °C to 45 °C	-
929003520219	CorePro LEDtube 600mm 9.9W 865 T8 AU	-20 °C to 45 °C	-
929003520319	CorePro LEDtube 1200mm 17.6W 840 T8 AU	-20 °C to 45 °C	-
929003520419	CorePro LEDtube 1200mm 17.6W 865 T8 AU	-20 °C to 45 °C	-
929003520519	CorePro LEDtube 1500mm 22W 840 T8 AU	-20 °C to 45 °C	-
929003520619	CorePro LEDtube 1500mm 22W 865 T8 AU	-20 °C to 45 °C	-
929003520708	Corepro LEDtube HO 1200mm 18W840T8 AP	-20 °C to 45 °C	-
929003520710	Corepro LEDtube HO 1200mm 18W840T8 CN	-20 to +45 °C	-
929003520738	Corepro LEDtube 50k 1200mm 18W840T8 MY	-20 to +45 °C	-
929003520808	CorePro LEDtube HO 1200mm 18W865T8 AP	-20 °C to 45 °C	-
929003520810	CorePro LEDtube HO 1200mm 18W865T8 CN	-20 to +45 °C	-
929003520838	CorePro LEDtube 50k 1200mm 18W865T8 MY	-20 to +45 °C	-
929003520888	CorePro LEDtube HO 1200mm 18W 865 T8 PH	-20 to +45 °C	-
929003534411	CorePro LEDtube 600mm 8W 840 VWV T8	-20 °C to 45 °C	-
929003534511	CorePro LEDtube 600mm 8W 865 VWV T8	-20 °C to 45 °C	-
929003534811	CorePro LEDtube HO 1200mm 18W840 VWV T8	-20 °C to 45 °C	-
929003534911	CorePro LEDtube HO 1200mm 18W865 VWV T8	-20 °C to 45 °C	-
929003547202	CorePro LEDtube 600mm 8W 840 T8	-20 to +45 °C	8 kWh



Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003547208	CorePro LEDtube 600mm 8W 840 T8 AP I	-20 to +45 °C	-
929003547220	CorePro LEDtube 600mm 8.8W 840 T8 AU 1CT	-20 to +45 °C	-
929003547221	CorePro LEDtube 600mm 8.8W 840 T8 AU 2CT	-20 to +45 °C	-
929003547262	CorePro LEDtube 600mm 8W 840 T8 CL	-20 to +45 °C	8 kWh
929003547302	CorePro LEDtube 600mm 8W 865 T8	-20 to +45 °C	8 kWh
929003547308	CorePro LEDtube 600mm 8W 865 T8 AP I	-20 to +45 °C	-
929003547320	CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT	-20 to +45 °C	-
929003547321	CorePro LEDtube 600mm 8.8W 865 T8 AU 2CT	-20 to +45 °C	-
929003547362	CorePro LEDtube 600mm 8W 865 T8 CL	-20 to +45 °C	8 kWh
929003547402	CorePro LEDtube 1500mm 20W 840 T8	-20 to +45 °C	20 kWh
929003547420	CorePro LEDtube 1500mm 22W 840 T8AU1CT	-20 to +45 °C	-
929003547421	CorePro LEDtube 1500mm 22W 840 T8AU2CT	-20 to +45 °C	-
929003547462	CorePro LEDtube 1500mm 20W 840 T8 CL	-20 to +45 °C	20 kWh
929003547502	CorePro LEDtube 1500mm 20W 865 T8	-20 to +45 °C	20 kWh
929003547520	CorePro LEDtube 1500mm 22W 865 T8AU1CT	-20 to +45 °C	-
929003547521	CorePro LEDtube 1500mm 22W 865 T8AU2CT	-20 to +45 °C	-
929003547562	CorePro LEDtube 1500mm 20W 865 T8 CL	-20 to +45 °C	20 kWh
929003577132	CorePro LEDtube 600mm 8W 830 T8	-20 to +45 °C	8 kWh
929003577232	CorePro LEDtube 1200mm 15.5W 830 T8	-20 to +45 °C	16 kWh
929003577332	CorePro LEDtube 1500mm 20W 830 T8	-20 to +45 °C	20 kWh
929003577402	CorePro LEDtube 600mm HO 8W 830 T8	-20 to +45 °C	8 kWh
929003577532	CorePro LEDtube 1200mm HO 18W 830 T8	-20 to +45 °C	18 kWh
929003577632	CorePro LEDtube 1500mm HO 24W 830 T8	-20 to +45 °C	24 kWh
929003577702	CorePro LEDtube 1200mm UO 21.5W 830 T8	-20 to +45 °C	22 kWh
929003577802	CorePro LEDtube 1500mm UO 31.5W 830 T8	-20 to +45 °C	32 kWh

CorePro LEDtube EM/Mains T8











Order Code	Full Product Name	Ambient temperature range	Energy
			Consumption kWh/1000 h
929003746102	CorePro LEDtube 1200mm UO 17.7W 830 T8	-20 to +45 °C	18 kWh
929003746202	CorePro LEDtube 1200mm UO 17.7W 840 T8	-20 to +45 °C	18 kWh
929003746302	CorePro LEDtube 1200mm UO 17.7W 865 T8	-20 to +45 °C	18 kWh
929003746402	CorePro LEDtube 1500mm UO 25.9W 830 T8	-20 to +45 °C	26 kWh
929003746502	CorePro LEDtube 1500mm UO 25.9W 840 T8	-20 to +45 °C	26 kWh
929003746602	CorePro LEDtube 1500mm UO 25.9W 865 T8	-20 to +45 °C	26 kWh
929003771708	CorePro LEDtube HO 1200mm 18W865T8 ID	-20 to +45 °C	-
929001999772	CorePro LEDtube 1200mm 18W 830 T8C W G	-20 to +45 °C	18 kWh
929001999868	CorePro LEDtube 1200mm 15.7W 840 T8 KSA	-20 to +45 °C	-
929001999872	CorePro LEDtube 1200mm 18W 840 T8C W G	-20 to +45 °C	18 kWh
929001999968	CorePro LEDtube 1200mm 15.7W 865 T8 KSA	-20 to +45 °C	-
929001999972	CorePro LEDtube 1200mm 18W 865 T8C W G	-20 to +45 °C	18 kWh
929002000468	CorePro LEDtube 600mm 8.6W 840 T8 KSA	-20 to +45 °C	-
929002000568	CorePro LEDtube 600mm 8.6W 865 T8 KSA	-20 to +45 °C	-
929002474472	CorePro LEDtube 8ft 32W 3800lm 865 T8 BR	-20 to +45 °C	-
929003604912	CorePro LEDtube 36 8ft 32W 865 T8 WV	-20 °C to 45 °C	-
929002000072	CorePro LEDtube 1200mm HO 18W840 C W G	-20 °C to 45 °C	18 kWh
929002000172	CorePro LEDtube 1200mm HO 18W865 C W G	-20 °C to 45 °C	18 kWh













CorePro LEDtube EM/Mains T8





CorePro LEDtube EM/Mains T8





CorePro LEDtube EM/Mains T8





CorePro LEDtube EM/Mains T8



CorePro LEDtube EM/Mains T8



CorePro LEDtube EM/Mains T8



CorePro LEDtube EM/Mains T8

