



Product Description

MASTER PL-C 4 Pin

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

Features

- 4-pin base without starter and capacitor
- Lamp characteristics are influenced by operating conditions and control gear used
- Dimming is possible

Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-C 4 Pin

Versions



26 W 4 Pin Non integrated
compact fluorescent - RFT




LPPR PLC4P 13W



LPPR PLC4P 18W

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
26 W 4 Pin Cool white Non integrated compact fluorescent	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm
MASTER PL-C 13W/830/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 18W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm

Light Technical	
Color rendering index (CRI)	82
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

General Information

MASTER PL-C 4 Pin

Order Code	Full Product Name	Nominal	
		Cap-Base	lifetime
927907384002	26 W 4 Pin Cool white Non integrated compact fluorescent	G24q-3	10,000 h

Order Code	Full Product Name	Nominal	
		Cap-Base	lifetime
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	G24q-1	-
927907284065	MASTER PL-C 18W/840/4P 1CT/5X10BOX	G24q-2	-

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature	Luminous Efficacy	Luminous Flux
			(Nom)	(rated) (Nom)	(Nom)
927907384002	26 W 4 Pin Cool white Non integrated compact fluorescent	Cool White (CW)	4000 K	67 lm/W	1,800 lm

Order Code	Full Product Name	Color Designation	Correlated Color Temperature	Luminous Efficacy	Luminous Flux
			(Nom)	(rated) (Nom)	(Nom)
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	Warm White (WW)	3000 K	72 lm/W	900 lm
927907284065	MASTER PL-C 18W/840/4P 1CT/5X10BOX	Cool White (CW)	4000 K	67 lm/W	1,200 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current	Power
		(Nom)	Consumption
927907384002	26 W 4 Pin Cool white Non integrated compact fluorescent	0.335 A	26.0 W
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	0.170 A	13.0 W

Order Code	Full Product Name	Lamp Current	Power
		(Nom)	Consumption
927907284065	MASTER PL-C 18W/840/4P 1CT/5X10BOX	0.230 A	18.0 W

Approval and Application

Order Code	Full Product Name	Energy Consumption
		kWh/1000 h
927907384002	26 W 4 Pin Cool white Non integrated compact fluorescent	29 kWh

Order Code	Full Product Name	Energy Consumption
		kWh/1000 h
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	15 kWh
927907284065	MASTER PL-C 18W/840/4P 1CT/5X10BOX	20 kWh

