



Product Description

MASTER PL-C 4 Pin

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

Features

- 4-pin base without starter and capacitor
- Lamp characteristics are influenced by operating conditions and control gear used
- Dimming is possible

Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-C 4 Pin

Versions




LPPR PLC4P 13W



LPPR PLC4P 26W

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/827/4P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 13W/830/4P 1CT/5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm
MASTER PL-C 18W/830/4P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 18W/865/4P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 26W/827/4P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

Controls and Dimming

Dimmable Yes

Approval and Application

Mercury (Hg) Content (Nom) 1.4 mg

General Information

Order Code	Full Product Name	Cap-Base
927907182701	MASTER PL-C 13W/827/4P 1CT/5X10BOX	G24q-1
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	G24q-1
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	G24q-2

Order Code	Full Product Name	Cap-Base
927907286501	MASTER PL-C 18W/865/4P 1CT/5X10BOX	G24q-2
927907382701	MASTER PL-C 26W/827/4P 1CT/5X10BOX	G24q-3

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
927907182701	MASTER PL-C 13W/827/4P 1CT/5X10BOX	Incandescent White	2700 K	82	69 lm/W	925 lm
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	Warm White (WW)	3000 K	82	72 lm/W	900 lm
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	Warm White (WW)	3000 K	82	67 lm/W	1,200 lm
927907286501	MASTER PL-C 18W/865/4P 1CT/5X10BOX	Cool Daylight	6500 K	80	62.3 lm/W	1,120 lm
927907382701	MASTER PL-C 26W/827/4P 1CT/5X10BOX	Incandescent White	2700 K	82	67 lm/W	1,800 lm

MASTER PL-C 4 Pin

Operating and Electrical

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
927907182701	MASTER PL-C 13W/827/4P 1CT/ 5X10BOX	0.170 A	13.0 W
927907183001	MASTER PL-C 13W/830/4P 1CT/ 5X10BOX	0.170 A	13.0 W
927907283001	MASTER PL-C 18W/830/4P 1CT/ 5X10BOX	0.230 A	16.5 W

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
927907286501	MASTER PL-C 18W/865/4P 1CT/ 5X10BOX	0.230 A	18.0 W
927907382701	MASTER PL-C 26W/827/4P 1CT/ 5X10BOX	0.335 A	26.0 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/	
		1000 h	
927907182701	MASTER PL-C 13W/827/4P 1CT/5X10BOX	15 kWh	
927907183001	MASTER PL-C 13W/830/4P 1CT/5X10BOX	15 kWh	
927907283001	MASTER PL-C 18W/830/4P 1CT/5X10BOX	20 kWh	

Order Code	Full Product Name	Energy Consumption kWh/	
		1000 h	
927907286501	MASTER PL-C 18W/865/4P 1CT/5X10BOX	20 kWh	
927907382701	MASTER PL-C 26W/827/4P 1CT/5X10BOX	29 kWh	

