



Product Description

PL-Q 4 Pin

Compact fluorescent lamps with a quadrant-like shape

Benefits

- High light quality and optimum lumen output provide increased value for money
- Energy-saving light with good colour rendering
- Long service lifetime
- The Philips Lighting stamp of quality

Features

- Retrofit in already installed 2D luminaires
- Assembled with the same high-quality components as all other Philips CFL-NI lamps
- Dimming is possible

Application

- Ideal for applications such as
- corridors
- toilets
- stairwells
- reception areas

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


PL-Q 4 Pin

Versions



LPPR PLQ4P

Dimensional drawing



Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 28W/840/4P	46.5 mm	18.9 mm	33 mm	203 mm	76 mm	41 mm	200 mm
1CT/10BOX							

