



Product Description

TORNADO

The Helix range is a twist-shape compact fluorescent lamp, with optimal light distribution. It is available in 11W, 15W, 20W and 23W (25W), with lumen equivalence of 60W, 75W, 100W and 125W incandescent light bulb. It is also available in two color temperatures: warm white (2700K) and cool daylight (6500K). It is available in both 220–240V and 120–127V and able to operate under a wide voltage range (Power supply fluctuation). It consumes up to 80% less energy than the incandescent light bulb and lasts for 3 years.

Benefits

- Very compact size and wide range allowing easy replacement of most GLS lamps from 25 W up to 150 W
- More than 80% energy saving effect compared with incandescent lamps of similar light output
- Fewer lamp replacements. Fit & forget.

Features

- Spiral-shaped alternative to incandescent lamps
- High energy efficiency
- Long-life alternative to incandescent lamps

Application

- The Helix range is widely used to replace incandescent light bulb at all kinds of applications, especially where require intensive light output.
- It is not suitable for dimming and electronic devices

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Versions



8718291138198 - RFT






8718291138112 - RFT



8718291138037 - RFT

Dimensional drawing






Product	D (max)	C (max)	F (max)
15 W (60 W) E27 cap Cool daylight Spiral energy saving bulb	51.5 mm	107.5 mm	42.5 mm
15 W (60 W) E27 cap Warm white Spiral energy saving bulb	51.5 mm	107.5 mm	42.5 mm

Product	D (max)	C (max)	F (max)
24 W (100 W) E27 cap Cool daylight Spiral energy saving bulb	61.5 mm	118.5 mm	50.5 mm
24 W (100 W) E27 cap Warm white Spiral energy saving bulb	61.5 mm	118.5 mm	50.5 mm

Product	D (max)	C (max)	F (max)
20 W (75 W) E27 cap Cool daylight Spiral energy saving bulb	56.5 mm	111.5 mm	47 mm
20 W (75 W) E27 cap Warm white Spiral energy saving bulb	56.5 mm	111.5 mm	47 mm

Dimensional drawing



Product	D (max)	C (max)	F (max)
15 W (60 W) B22 cap Cool daylight Spiral energy saving bulb	51.5 mm	106.0 mm	42.5 mm
15 W (60 W) B22 cap Warm white Spiral energy saving bulb	51.5 mm	106.0 mm	42.5 mm

Product	D (max)	C (max)	F (max)
20 W (75 W) B22 cap Cool daylight Spiral energy saving bulb	56.5 mm	110.0 mm	47 mm
20 W (75 W) B22 cap Warm white Spiral energy saving bulb	56.5 mm	110.0 mm	47 mm

Product	D (max)	C (max)	F (max)
24 W (100 W) B22 cap Cool daylight Spiral energy saving bulb	61.5 mm	117 mm	50.5 mm
24 W (100 W) B22 cap Warm white Spiral energy saving bulb	61.5 mm	117 mm	50.5 mm

General Information	
Rated Lifetime (Hours)	8,000 hour(s)
Switching Cycle	5,000
Nominal lifetime	8,000 hour(s)
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 or 60 Hz
Line Frequency	50 or 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.3 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Spiral

General Information

Order Code	Full Product Name	Cap-Base
929689858502	24 W (100 W) B22 cap Warm white Spiral energy saving bulb	B22
929689858602	24 W (100 W) B22 cap Cool daylight Spiral energy saving bulb	B22
929689858302	20 W (75 W) B22 cap Warm white Spiral energy saving bulb	B22
929689858402	20 W (75 W) B22 cap Cool daylight Spiral energy saving bulb	B22
929689858102	15 W (60 W) B22 cap Warm white Spiral energy saving bulb	B22
929689858202	15 W (60 W) B22 cap Cool daylight Spiral energy saving bulb	B22
929689848506	24 W (100 W) E27 cap Warm white Spiral energy saving bulb	E27
929689848605	24 W (100 W) E27 cap Cool daylight Spiral energy saving bulb	E27
929689848306	20 W (75 W) E27 cap Warm white Spiral energy saving bulb	E27
929689848405	20 W (75 W) E27 cap Cool daylight Spiral energy saving bulb	E27
929689848105	15 W (60 W) E27 cap Warm white Spiral energy saving bulb	E27
929689848205	15 W (60 W) E27 cap Cool daylight Spiral energy saving bulb	E27

Light Technical (1/2)

	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color Designation	Correlated Color Temperature (Nom)
929689858502	24 W (100 W) B22 cap Warm white Spiral energy saving bulb	463	420	Warm White (WW)	2700 K
929689858602	24 W (100 W) B22 cap Cool daylight Spiral energy saving bulb	313	337	Cool Daylight	6500 K
929689858302	20 W (75 W) B22 cap Warm white Spiral energy saving bulb	463	420	Warm White (WW)	2700 K
929689858402	20 W (75 W) B22 cap Cool daylight Spiral	313	337	Cool Daylight	6500 K

	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color Designation	Correlated Color Temperature (Nom)
	energy saving bulb				
929689858102	15 W (60 W) B22 cap Warm white Spiral energy saving bulb	463	420	Warm White (WW)	2700 K
929689858202	15 W (60 W) B22 cap Cool daylight Spiral energy saving bulb	313	337	Cool Daylight	6500 K
929689848506	24 W (100 W) E27 cap Warm white Spiral energy saving bulb	463	420	Warm White (WW)	2700 K
929689848605	24 W (100 W) E27 cap Cool daylight Spiral energy saving bulb	313	337	Cool Daylight	6500 K

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color Designation	Correlated Color Temperature (Nom)
	daylight				
	Spiral				
	energy				
	saving bulb				
929689848306	20 W (75 W) E27 cap	463	420	Warm White (WW)	2700 K
	Warm white				
	Spiral				
	energy				
	saving bulb				
929689848405	20 W (75 W) E27 cap	313	337	Cool Daylight	6500 K
	Cool daylight				
	Spiral				

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color Designation	Correlated Color Temperature (Nom)
	energy				
	saving bulb				
929689848105	15 W (60 W) E27 cap	463	420	Warm White (WW)	2700 K
	Warm white				
	Spiral				
	energy				
	saving bulb				
929689848205	15 W (60 W) E27 cap	313	337	Cool Daylight	6500 K
	Cool daylight				
	Spiral				
	energy				
	saving bulb				

Light Technical (2/2)

Order Code	Full Product Name	Color rendering		Luminous Efficacy	
		index (CRI)	Color Code	(rated) (Nom)	Luminous Flux
929689858502	24 W (100 W) B22 cap Warm white	82	827	67 lm/W	1,550 lm
	Spiral energy saving bulb				
929689858602	24 W (100 W) B22 cap Cool daylight	80	865	63 lm/W	1,450 lm
	Spiral energy saving bulb				
929689858302	20 W (75 W) B22 cap Warm white	82	827	65 lm/W	1,250 lm
	Spiral energy saving bulb				
929689858402	20 W (75 W) B22 cap Cool daylight	80	865	61 lm/W	1,200 lm
	Spiral energy saving bulb				
929689858102	15 W (60 W) B22 cap Warm white	82	827	65 lm/W	950 lm
	Spiral energy saving bulb				
929689858202	15 W (60 W) B22 cap Cool daylight	80	865	61 lm/W	900 lm
	Spiral energy saving bulb				
929689848506	24 W (100 W) E27 cap Warm white	82	827	67 lm/W	1,550 lm

Order Code	Full Product Name	Color rendering		Luminous Efficacy	
		index (CRI)	Color Code	(rated) (Nom)	Luminous Flux
	Spiral energy saving bulb				
929689848605	24 W (100 W) E27 cap Cool daylight	80	865	63 lm/W	1,450 lm
	Spiral energy saving bulb				
929689848306	20 W (75 W) E27 cap Warm white	82	827	65 lm/W	1,250 lm
	Spiral energy saving bulb				
929689848405	20 W (75 W) E27 cap Cool daylight	80	865	61 lm/W	1,200 lm
	Spiral energy saving bulb				
929689848105	15 W (60 W) E27 cap Warm white	82	827	65 lm/W	950 lm
	Spiral energy saving bulb				
929689848205	15 W (60 W) E27 cap Cool daylight	80	865	61 lm/W	900 lm
	Spiral energy saving bulb				

Operating and Electrical

Order Code	Full Product Name	Lamp	Power
		Current (Nom)	Consumption
929689858502	24 W (100 W) B22 cap Warm white Spiral energy saving bulb	170 mA	24 W
929689858602	24 W (100 W) B22 cap Cool daylight Spiral energy saving bulb	170 mA	24 W
929689858302	20 W (75 W) B22 cap Warm white Spiral energy saving bulb	150 mA	20 W
929689858402	20 W (75 W) B22 cap Cool daylight Spiral energy saving bulb	150 mA	20 W
929689858102	15 W (60 W) B22 cap Warm white Spiral energy saving bulb	110 mA	15 W
929689858202	15 W (60 W) B22 cap Cool daylight Spiral energy saving bulb	110 mA	15 W

Order Code	Full Product Name	Lamp	Power
		Current (Nom)	Consumption
929689848506	24 W (100 W) E27 cap Warm white Spiral energy saving bulb	170 mA	24 W
929689848605	24 W (100 W) E27 cap Cool daylight Spiral energy saving bulb	170 mA	24 W
929689848306	20 W (75 W) E27 cap Warm white Spiral energy saving bulb	150 mA	20 W
929689848405	20 W (75 W) E27 cap Cool daylight Spiral energy saving bulb	150 mA	20 W
929689848105	15 W (60 W) E27 cap Warm white Spiral energy saving bulb	110 mA	15 W
929689848205	15 W (60 W) E27 cap Cool daylight Spiral energy saving bulb	110 mA	15 W

Approval and Application

Order Code	Full Product Name	Energy	Mercury (Hg)
		Consumption kWh/1000 h	Content (Nom)
929689858502	24 W (100 W) B22 cap Warm white Spiral energy saving bulb	23 kWh	2 mg
929689858602	24 W (100 W) B22 cap Cool daylight Spiral energy saving bulb	23 kWh	2 mg
929689858302	20 W (75 W) B22 cap Warm white Spiral energy saving bulb	20 kWh	1.5 mg
929689858402	20 W (75 W) B22 cap Cool daylight Spiral energy saving bulb	20 kWh	1.5 mg
929689858102	15 W (60 W) B22 cap Warm white Spiral energy saving bulb	15 kWh	1.5 mg
929689858202	15 W (60 W) B22 cap Cool daylight Spiral energy saving bulb	15 kWh	1.5 mg

Order Code	Full Product Name	Energy	Mercury (Hg)
		Consumption kWh/1000 h	Content (Nom)
929689848506	24 W (100 W) E27 cap Warm white Spiral energy saving bulb	23 kWh	2 mg
929689848605	24 W (100 W) E27 cap Cool daylight Spiral energy saving bulb	23 kWh	2 mg
929689848306	20 W (75 W) E27 cap Warm white Spiral energy saving bulb	20 kWh	1.5 mg
929689848405	20 W (75 W) E27 cap Cool daylight Spiral energy saving bulb	20 kWh	1.5 mg
929689848105	15 W (60 W) E27 cap Warm white Spiral energy saving bulb	15 kWh	-
929689848205	15 W (60 W) E27 cap Cool daylight Spiral energy saving bulb	15 kWh	-

