



產品說明

MASTERColour CDM-TC Elite

體積精巧，高效率的單端陶瓷金屬鹵化物放電燈管

优点

- 高演色性 (Ra 90) 結合高流明輸出，讓展示商品呈現出色外觀；市面上「提升商品質感」的最佳選擇
- 使用壽命期間維持穩定的優異色彩品質
- 使用壽命期間的光線輸出能維持展示亮度
- 高效率、使用壽命長，維持最低的營運成本，散發的熱度亦低
- 產生的熱能相當低，確保購物者和員工置身更舒適環境
- 紫外線阻隔設計，減少商品褪色的風險
- 能設計出體積非常精巧，光束強度極高的優質燈具

特点

- 清澈的白色燈光
- 優異的演色性 (Ra 90)
- 使用壽命期間效能可靠
- 使用壽命期間呈現穩定色彩
- 提供更出色的光線輸出，超越一般的 MASTERColour 燈管
- 維護保養更方便，超越一般的 MASTERColour 燈管

应用

- 展現閃亮效果，適合作為重點與展示照明，是優異的零售店面解決方案
- 一般和裝飾照明

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTERColour CDM-TC Elite

Versions



LPPR CDM-TC 0001





LPPR_CDMTC-E_0001-Product photo



LPPR CDMTC-E 0003

二维绘图



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	15 mm	4.8 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	15 mm	6 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	15 mm	7.15 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 70W/942 G8.5 1CT	15 mm	7.75 mm	51 mm	53 mm	52 mm	85 mm

Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	15 mm	0.55 in	4 mm	51 mm	53 mm	52 mm	85 mm

一般資訊	
燈座基底	G8.5
操作位置	UNIVERSAL
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明
燈泡形狀	T14

照明技術

MASTERColour CDM-TC Elite

Order Code	Full Product Name	色度坐標 X (標稱)	色度坐標 Y (Nom)	色彩名稱	相關色溫 (標稱)	演色性指數 (CRI)	光效 (額定) (標準)	光通量
928183405125	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	0.434	0.398	暖白光 (WW)	3000 K	85	87 lm/W	1,750 lm
928189105129	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	0.435	0.396	暖白光 (WW)	3000 K	90	102 lm/W	-
928189505129	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	0.435	0.396	暖白光 (WW)	3000 K	90	107 lm/W	-
928193905129	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	0.365	0.363	冷白光 (CW)	4200 K	92	102 lm/W	-
928191805131	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	0.434	0.398	暖白光 (WW)	3000 K	91	108 lm/W	5,400 lm

運轉與電力

Order Code	Full Product Name	電壓 (標稱)	耗電量	Order Code	Full Product Name	電壓 (標稱)	耗電量
928183405125	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	95 V	20.1 W	928193905129	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	88 V	73.2 W
928189105129	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	85 V	39.1 W	928191805131	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	90 V	50.2 W
928189505129	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	85 V	73.2 W				

機械與外罩

Order Code	Full Product Name	燈泡材質	Order Code	Full Product Name	燈泡材質
928183405125	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	抗 UV 石英	928193905129	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	-
928189105129	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	-	928191805131	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	-
928189505129	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	-			

認證與應用

Order Code	Full Product Name	能源消耗 kWh/1000 h	汞 (Hg) 含量 (最大)	汞 (Hg) 含量 (標稱)
928183405125	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	21 kWh	3.5 mg	3.5 mg
928189105129	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	43 kWh	-	4.7 mg
928189505129	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	80 kWh	-	6.6 mg
928193905129	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	80 kWh	-	6.6 mg
928191805131	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	51 kWh	6.6 mg	6.6 mg

